

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1191305

Luminaire Tested: SQ2-FA-0U-075D-L830-UNV-STD-W-4

Issue Date: 9/23/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1191305  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-9, G2-2502-345-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 9/23/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-FA-0U-075D-L830-UNV-STD-W-4  
Description: CORELITE SQ2 LED LUMINAIRE  
FROSTED CONTINUOUS ASYMMETRIC ROLL LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3153.2 lumens  
Efficiency: N/A  
Efficacy: 118.1 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1191305

CATALOG NUMBER: SQ2-FA-0U-075D-L830-UNV-STD-W-4

### Luminous Intensity Polar Plot



TEST NUMBER: P1191305

CATALOG NUMBER: SQ2-FA-0U-075D-L830-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 |
| 1   | 109 | 105 | 101 | 97  | 107 | 102 | 99  | 95  | 98  | 95  | 92  | 94  | 92  | 90  | 91  | 89  | 87  |
| 2   | 100 | 92  | 85  | 80  | 97  | 90  | 84  | 79  | 86  | 81  | 77  | 83  | 79  | 75  | 80  | 76  | 73  |
| 3   | 91  | 81  | 73  | 66  | 89  | 79  | 72  | 66  | 76  | 70  | 65  | 73  | 68  | 64  | 71  | 66  | 62  |
| 4   | 83  | 72  | 63  | 57  | 81  | 70  | 62  | 56  | 68  | 61  | 55  | 66  | 60  | 55  | 63  | 58  | 54  |
| 5   | 77  | 64  | 55  | 49  | 75  | 63  | 55  | 49  | 61  | 54  | 48  | 59  | 53  | 47  | 57  | 52  | 47  |
| 6   | 71  | 58  | 49  | 43  | 69  | 57  | 49  | 43  | 55  | 48  | 42  | 53  | 47  | 42  | 52  | 46  | 41  |
| 7   | 66  | 53  | 44  | 38  | 64  | 52  | 43  | 38  | 50  | 43  | 37  | 49  | 42  | 37  | 47  | 41  | 37  |
| 8   | 61  | 48  | 40  | 34  | 60  | 47  | 39  | 34  | 46  | 39  | 33  | 45  | 38  | 33  | 44  | 38  | 33  |
| 9   | 57  | 44  | 36  | 30  | 56  | 43  | 36  | 30  | 42  | 35  | 30  | 41  | 35  | 30  | 40  | 34  | 30  |
| 10  | 54  | 41  | 33  | 28  | 53  | 40  | 33  | 28  | 39  | 32  | 27  | 38  | 32  | 27  | 37  | 31  | 27  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    | 90°   | 180°  | 270°  |
|-----|-------|-------|-------|-------|
| 0°  | 20499 | 20499 | 20499 | 20499 |
| 5°  | 20258 | 21216 | 20258 | 16909 |
| 10° | 20171 | 21461 | 20171 | 15329 |
| 15° | 19824 | 21633 | 19824 | 16944 |
| 20° | 19278 | 21476 | 19278 | 17672 |
| 25° | 18323 | 21303 | 18323 | 17884 |
| 30° | 16882 | 20827 | 16882 | 18073 |
| 35° | 14937 | 20369 | 14937 | 17749 |
| 40° | 12861 | 19810 | 12861 | 17943 |
| 45° | 12698 | 19103 | 12698 | 17979 |
| 50° | 12115 | 18171 | 12115 | 18048 |
| 55° | 12051 | 16760 | 12051 | 17869 |
| 60° | 10805 | 14938 | 10805 | 17799 |
| 65° | 9211  | 13161 | 9211  | 17295 |
| 70° | 7435  | 11150 | 7435  | 16032 |
| 75° | 6444  | 9208  | 6444  | 14735 |
| 80° | 5495  | 6862  | 5495  | 11892 |
| 85° | 3649  | 3649  | 3649  | 7299  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 19776 cd/sqm

TEST NUMBER: P1191305

CATALOG NUMBER: SQ2-FA-0U-075D-L830-UNV-STD-W-4

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 114.2  | 3.6       |
| 10°-20°   | 319.2  | 10.1      |
| 20°-30°   | 484.8  | 15.4      |
| 30°-40°   | 569.1  | 18.0      |
| 40°-50°   | 577.5  | 18.3      |
| 50°-60°   | 505.9  | 16.0      |
| 60°-70°   | 358.9  | 11.4      |
| 70°-80°   | 184.8  | 5.9       |
| 80°-90°   | 38.8   | 1.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 918.2  | 29.1      |
| 0°-40°    | 1487.3 | 47.2      |
| 0°-60°    | 2570.7 | 81.5      |
| 0°-90°    | 3153.2 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 3153.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 90°  | 180° | 270° | 360° | Flux |
|-----|------|------|------|------|------|------|
| 0°  | 1270 | 1270 | 1270 | 1270 | 1270 |      |
| 5°  | 1250 | 1309 | 1250 | 1043 | 1250 | 119  |
| 15° | 1186 | 1294 | 1186 | 1014 | 1186 | 333  |
| 25° | 1028 | 1196 | 1028 | 1004 | 1028 | 470  |
| 35° | 758  | 1033 | 758  | 900  | 758  | 472  |
| 45° | 556  | 837  | 556  | 787  | 556  | 425  |
| 55° | 428  | 595  | 428  | 635  | 428  | 370  |
| 65° | 241  | 344  | 241  | 453  | 241  | 241  |
| 75° | 103  | 148  | 103  | 236  | 103  | 112  |
| 85° | 20   | 20   | 20   | 39   | 20   | 25   |
| 90° | 0    | 0    | 0    | 0    | 0    |      |

TEST NUMBER: P1191305

CATALOG NUMBER: SQ2-FA-0U-075D-L830-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    | 112.5° | 135°   | 157.5° | 180°   | 202.5° | 225°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1269.6 | 1269.6 | 1269.6 | 1269.6 | 1269.6 | 1269.6 | 1269.6 | 1269.6 | 1269.6 | 1269.6 | 1269.6 |
| 2.5°  | 1261.7 | 1281.0 | 1281.4 | 1281.4 | 1281.4 | 1281.4 | 1281.4 | 1281.0 | 1261.7 | 1261.7 | 1242.1 |
| 5°    | 1249.9 | 1283.6 | 1294.2 | 1299.4 | 1309.0 | 1299.4 | 1294.2 | 1283.6 | 1249.9 | 1235.5 | 1156.4 |
| 7.5°  | 1238.1 | 1283.4 | 1299.1 | 1308.1 | 1312.9 | 1308.1 | 1299.1 | 1283.4 | 1238.1 | 1173.7 | 1007.8 |
| 10°   | 1230.3 | 1283.2 | 1299.1 | 1304.2 | 1309.0 | 1304.2 | 1299.1 | 1283.2 | 1230.3 | 1100.3 | 964.5  |
| 12.5° | 1218.4 | 1275.2 | 1295.2 | 1300.2 | 1305.1 | 1300.2 | 1295.2 | 1275.2 | 1218.4 | 1034.6 | 933.0  |
| 15°   | 1186.0 | 1263.0 | 1279.5 | 1289.4 | 1294.2 | 1289.4 | 1279.5 | 1263.0 | 1186.0 | 979.1  | 910.4  |
| 17.5° | 1145.6 | 1239.0 | 1260.8 | 1269.7 | 1273.6 | 1269.7 | 1260.8 | 1239.0 | 1145.6 | 929.1  | 911.4  |
| 20°   | 1122.0 | 1223.0 | 1245.0 | 1249.9 | 1249.9 | 1249.9 | 1245.0 | 1223.0 | 1122.0 | 905.5  | 935.0  |
| 22.5° | 1090.5 | 1203.1 | 1225.3 | 1226.4 | 1230.3 | 1226.4 | 1225.3 | 1203.1 | 1090.5 | 877.8  | 946.8  |
| 25°   | 1028.5 | 1158.4 | 1190.9 | 1186.2 | 1195.8 | 1186.2 | 1190.9 | 1158.4 | 1028.5 | 840.8  | 944.8  |
| 27.5° | 952.7  | 1116.3 | 1139.7 | 1144.6 | 1144.6 | 1144.6 | 1139.7 | 1116.3 | 952.7  | 804.5  | 925.2  |
| 30°   | 905.5  | 1088.3 | 1112.1 | 1117.1 | 1117.1 | 1117.1 | 1112.1 | 1088.3 | 905.5  | 780.4  | 905.5  |
| 32.5° | 846.4  | 1063.9 | 1084.6 | 1085.6 | 1085.6 | 1085.6 | 1084.6 | 1063.9 | 846.4  | 756.0  | 874.0  |
| 35°   | 757.8  | 1022.5 | 1038.3 | 1038.2 | 1033.4 | 1038.2 | 1038.3 | 1022.5 | 757.8  | 719.3  | 836.6  |
| 37.5° | 669.3  | 969.5  | 991.1  | 984.1  | 979.3  | 984.1  | 991.1  | 969.5  | 669.3  | 681.8  | 805.1  |
| 40°   | 610.2  | 937.4  | 959.6  | 944.7  | 939.9  | 944.7  | 959.6  | 937.4  | 610.2  | 653.5  | 777.5  |
| 42.5° | 578.7  | 902.1  | 924.2  | 905.4  | 900.5  | 905.4  | 924.2  | 902.1  | 578.7  | 625.9  | 753.9  |
| 45°   | 556.1  | 844.8  | 866.1  | 846.2  | 836.6  | 846.2  | 866.1  | 844.8  | 556.1  | 584.9  | 713.5  |
| 47.5° | 521.6  | 775.7  | 806.1  | 776.3  | 766.7  | 776.3  | 806.1  | 775.7  | 521.6  | 542.8  | 677.1  |
| 50°   | 482.3  | 732.5  | 762.8  | 733.0  | 723.4  | 733.0  | 762.8  | 732.5  | 482.3  | 511.1  | 649.6  |
| 52.5° | 454.7  | 689.5  | 715.5  | 681.8  | 672.2  | 681.8  | 715.5  | 689.5  | 454.7  | 472.0  | 626.0  |
| 55°   | 428.1  | 625.4  | 644.7  | 609.9  | 595.4  | 609.9  | 644.7  | 625.4  | 428.1  | 413.7  | 580.7  |
| 57.5° | 366.1  | 553.8  | 573.8  | 534.1  | 517.7  | 534.1  | 573.8  | 553.8  | 366.1  | 353.6  | 533.4  |
| 60°   | 334.6  | 503.0  | 526.5  | 486.6  | 462.6  | 486.6  | 526.5  | 503.0  | 334.6  | 310.6  | 501.9  |
| 62.5° | 299.2  | 448.4  | 479.3  | 439.4  | 415.3  | 439.4  | 479.3  | 448.4  | 299.2  | 282.8  | 466.5  |
| 65°   | 241.1  | 371.0  | 408.4  | 368.5  | 344.5  | 368.5  | 408.4  | 371.0  | 241.1  | 250.8  | 408.4  |
| 67.5° | 189.0  | 300.6  | 342.5  | 298.8  | 279.5  | 298.8  | 342.5  | 300.6  | 189.0  | 220.7  | 355.3  |
| 70°   | 157.5  | 253.7  | 295.3  | 255.5  | 236.2  | 255.5  | 295.3  | 253.7  | 157.5  | 200.8  | 319.9  |
| 72.5° | 137.8  | 210.9  | 255.9  | 212.2  | 196.8  | 212.2  | 255.9  | 210.9  | 137.8  | 181.1  | 276.6  |
| 75°   | 103.3  | 146.6  | 196.8  | 157.3  | 147.6  | 157.3  | 196.8  | 146.6  | 103.3  | 146.6  | 216.5  |
| 77.5° | 74.8   | 95.0   | 138.8  | 105.2  | 101.4  | 105.2  | 138.8  | 95.0   | 74.8   | 110.4  | 157.5  |
| 80°   | 59.1   | 63.9   | 103.3  | 73.8   | 73.8   | 73.8   | 103.3  | 63.9   | 59.1   | 83.1   | 118.1  |
| 82.5° | 39.4   | 44.2   | 71.8   | 50.1   | 46.3   | 50.1   | 71.8   | 44.2   | 39.4   | 59.6   | 82.7   |
| 85°   | 19.7   | 19.7   | 29.5   | 19.7   | 19.7   | 19.7   | 29.5   | 19.7   | 19.7   | 29.3   | 39.4   |
| 87.5° | 3.9    | 3.9    | 7.9    | 3.9    | 3.9    | 3.9    | 7.9    | 3.9    | 3.9    | 7.8    | 7.9    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

TEST NUMBER: P1191305

CATALOG NUMBER: SQ2-FA-0U-075D-L830-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

|       | 247.5° | 270°   | 292.5° | 315°   | 337.5° | 360°   |
|-------|--------|--------|--------|--------|--------|--------|
| 0°    | 1269.6 | 1269.6 | 1269.6 | 1269.6 | 1269.6 | 1269.6 |
| 2.5°  | 1230.2 | 1226.3 | 1230.2 | 1242.1 | 1261.7 | 1261.7 |
| 5°    | 1067.3 | 1043.3 | 1067.3 | 1156.4 | 1235.5 | 1249.9 |
| 7.5°  | 970.2  | 962.6  | 970.2  | 1007.8 | 1173.7 | 1238.1 |
| 10°   | 935.0  | 935.0  | 935.0  | 964.5  | 1100.3 | 1230.3 |
| 12.5° | 931.5  | 950.7  | 931.5  | 933.0  | 1034.6 | 1218.4 |
| 15°   | 989.7  | 1013.7 | 989.7  | 910.4  | 979.1  | 1186.0 |
| 17.5° | 1009.2 | 1028.5 | 1009.2 | 911.4  | 929.1  | 1145.6 |
| 20°   | 1009.2 | 1028.5 | 1009.2 | 935.0  | 905.5  | 1122.0 |
| 22.5° | 1005.3 | 1024.6 | 1005.3 | 946.8  | 877.8  | 1090.5 |
| 25°   | 994.3  | 1003.9 | 994.3  | 944.8  | 840.8  | 1028.5 |
| 27.5° | 974.5  | 981.3  | 974.5  | 925.2  | 804.5  | 952.7  |
| 30°   | 955.0  | 969.4  | 955.0  | 905.5  | 780.4  | 905.5  |
| 32.5° | 935.1  | 937.9  | 935.1  | 874.0  | 756.0  | 846.4  |
| 35°   | 905.4  | 900.5  | 905.4  | 836.6  | 719.3  | 757.8  |
| 37.5° | 865.2  | 871.0  | 865.2  | 805.1  | 681.8  | 669.3  |
| 40°   | 841.7  | 851.3  | 841.7  | 777.5  | 653.5  | 610.2  |
| 42.5° | 818.1  | 827.7  | 818.1  | 753.9  | 625.9  | 578.7  |
| 45°   | 782.6  | 787.4  | 782.6  | 713.5  | 584.9  | 556.1  |
| 47.5° | 741.2  | 746.0  | 741.2  | 677.1  | 542.8  | 521.6  |
| 50°   | 713.7  | 718.5  | 713.7  | 649.6  | 511.1  | 482.3  |
| 52.5° | 682.2  | 687.0  | 682.2  | 626.0  | 472.0  | 454.7  |
| 55°   | 634.8  | 634.8  | 634.8  | 580.7  | 413.7  | 428.1  |
| 57.5° | 580.8  | 586.6  | 580.8  | 533.4  | 353.6  | 366.1  |
| 60°   | 541.5  | 551.2  | 541.5  | 501.9  | 310.6  | 334.6  |
| 62.5° | 506.0  | 511.8  | 506.0  | 466.5  | 282.8  | 299.2  |
| 65°   | 447.9  | 452.7  | 447.9  | 408.4  | 250.8  | 241.1  |
| 67.5° | 382.9  | 386.8  | 382.9  | 355.3  | 220.7  | 189.0  |
| 70°   | 339.6  | 339.6  | 339.6  | 319.9  | 200.8  | 157.5  |
| 72.5° | 296.3  | 300.2  | 296.3  | 276.6  | 181.1  | 137.8  |
| 75°   | 231.4  | 236.2  | 231.4  | 216.5  | 146.6  | 103.3  |
| 77.5° | 166.4  | 171.3  | 166.4  | 157.5  | 110.4  | 74.8   |
| 80°   | 123.1  | 127.9  | 123.1  | 118.1  | 83.1   | 59.1   |
| 82.5° | 87.6   | 88.6   | 87.6   | 82.7   | 59.6   | 39.4   |
| 85°   | 39.4   | 39.4   | 39.4   | 39.4   | 29.3   | 19.7   |
| 87.5° | 7.9    | 7.9    | 7.9    | 7.9    | 7.8    | 3.9    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

TEST NUMBER: P1191305

CATALOG NUMBER: SQ2-FA-0U-075D-L830-UNV-STD-W-4

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |       |       |       |       |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7   | 0.5   | 0.5   | 0.3   |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3   | 0.5   | 0.3   | 0.3   |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2   | 0.2   | 0.2   | 0.2   |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |       |       |       |       |
| X=2H            | Y=2H | 20.67            | 22.28 | 21.04 | 22.59 | 22.91 | 21.90          | 23.50 | 22.26 | 23.82 | 24.13 |
|                 | 3H   | 21.81            | 23.26 | 22.19 | 23.59 | 23.95 | 23.19          | 24.64 | 23.57 | 24.97 | 25.33 |
|                 | 4H   | 22.20            | 23.56 | 22.60 | 23.91 | 24.29 | 23.62          | 24.98 | 24.01 | 25.33 | 25.70 |
|                 | 6H   | 22.40            | 23.66 | 22.81 | 24.02 | 24.42 | 23.81          | 25.07 | 24.22 | 25.44 | 25.83 |
|                 | 8H   | 22.45            | 23.66 | 22.88 | 24.05 | 24.45 | 23.86          | 25.06 | 24.28 | 25.45 | 25.85 |
|                 | 12H  | 22.48            | 23.63 | 22.90 | 24.01 | 24.44 | 23.87          | 25.02 | 24.30 | 25.40 | 25.83 |
| 4H              | 2H   | 21.69            | 23.05 | 22.08 | 23.40 | 23.77 | 22.60          | 23.96 | 23.00 | 24.31 | 24.68 |
|                 | 3H   | 23.12            | 24.26 | 23.53 | 24.65 | 25.05 | 24.11          | 25.25 | 24.52 | 25.65 | 26.05 |
|                 | 4H   | 23.59            | 24.62 | 24.03 | 25.03 | 25.47 | 24.61          | 25.64 | 25.04 | 26.05 | 26.49 |
|                 | 6H   | 23.86            | 24.76 | 24.32 | 25.20 | 25.65 | 24.87          | 25.77 | 25.33 | 26.21 | 26.66 |
|                 | 8H   | 23.94            | 24.77 | 24.40 | 25.21 | 25.68 | 24.94          | 25.77 | 25.40 | 26.22 | 26.68 |
|                 | 12H  | 23.97            | 24.72 | 24.45 | 25.20 | 25.67 | 24.96          | 25.71 | 25.44 | 26.19 | 26.66 |
| 8H              | 4H   | 24.05            | 24.89 | 24.51 | 25.33 | 25.79 | 24.88          | 25.71 | 25.34 | 26.16 | 26.62 |
|                 | 6H   | 24.43            | 25.12 | 24.92 | 25.61 | 26.08 | 25.22          | 25.91 | 25.71 | 26.40 | 26.88 |
|                 | 8H   | 24.55            | 25.17 | 25.06 | 25.68 | 26.16 | 25.32          | 25.94 | 25.83 | 26.45 | 26.93 |
|                 | 12H  | 24.62            | 25.17 | 25.13 | 25.66 | 26.22 | 25.37          | 25.91 | 25.88 | 26.41 | 26.97 |
| 12H             | 4H   | 24.09            | 24.84 | 24.57 | 25.31 | 25.78 | 24.88          | 25.63 | 25.36 | 26.11 | 26.58 |
|                 | 6H   | 24.51            | 25.13 | 25.02 | 25.63 | 26.12 | 25.25          | 25.87 | 25.76 | 26.37 | 26.86 |
|                 | 8H   | 24.68            | 25.23 | 25.19 | 25.72 | 26.28 | 25.39          | 25.94 | 25.90 | 26.43 | 26.99 |

END OF REPORT