

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1191324

Luminaire Tested: SQ2-FA-100U-050D-L835-UNV-STD-W-4

Issue Date: 9/23/2025

Test Information

Test Method: LM-79-2019
Report Number: P1191324
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-9, G2-2502-345-2)
Test Lab: INNOVATION CENTER
Issue Date: 9/23/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FA-100U-050D-L835-UNV-STD-W-4
Description: CORELITE SQ2 LED LUMINAIRE
FROSTED CONTINUOUS ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6674.3 lumens
Efficiency: N/A
Efficacy: 132.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 50.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1191324

CATALOG NUMBER: SQ2-FA-100U-050D-L835-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P1191324

CATALOG NUMBER: SQ2-FA-100U-050D-L835-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	78	73	68	77	71	66	62	57	53	50	44	41	39	31	30	29
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21
5	65	54	46	40	59	49	42	37	40	35	31	31	27	24	22	20	18
6	60	48	41	35	54	44	37	32	36	30	27	28	24	21	20	18	16
7	55	44	36	30	50	40	33	28	32	27	23	25	21	19	18	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	16	13	11
10	45	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14223	14223	14223	14223
5°	14055	14720	14055	11731
10°	13995	14890	13995	10635
15°	13755	15010	13755	11758
20°	13376	14900	13376	12261
25°	12713	14781	12713	12408
30°	11712	14451	11712	12540
35°	10364	14132	10364	12315
40°	8924	13744	8924	12450
45°	8809	13253	8809	12474
50°	8405	12607	8405	12522
55°	8363	11629	8363	12400
60°	7498	10366	7498	12348
65°	6392	9131	6392	12000
70°	5160	7737	5160	11122
75°	4473	6388	4473	10225
80°	3812	4761	3812	8257
85°	2538	2538	2538	5057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 13721 cd/sqm

TEST NUMBER: P1191324

CATALOG NUMBER: SQ2-FA-100U-050D-L835-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.3	1.2
10°-20°	221.5	3.3
20°-30°	336.4	5.0
30°-40°	394.9	5.9
40°-50°	400.7	6.0
50°-60°	351.0	5.3
60°-70°	249.0	3.7
70°-80°	128.2	1.9
80°-90°	28.2	0.4
90°-100°	301.0	4.5
100°-110°	910.3	13.6
110°-120°	888.6	13.3
120°-130°	726.2	10.9
130°-140°	592.7	8.9
140°-150°	461.4	6.9
150°-160°	332.6	5.0
160°-170°	203.6	3.1
170°-180°	68.8	1.0
0°-30°	637.1	9.5
0°-40°	1031.9	15.5
0°-60°	1783.6	26.7
0°-90°	2189.0	32.8
90°-120°	2099.9	31.5
90°-150°	3880.2	58.1
90°-180°	4485.0	67.2
0°-180°	6674.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	881	881	881	881	881	
5°	867	908	867	724	867	82
15°	823	898	823	703	823	231
25°	714	830	714	696	714	326
35°	526	717	526	625	526	328
45°	386	580	386	546	386	295
55°	297	413	297	440	297	257
65°	167	239	167	314	167	167
75°	72	102	72	164	72	78
85°	14	14	14	27	14	17
90°	0	7	0	7	0	2
95°	37	132	37	132	37	44
105°	158	1613	158	1613	158	166
115°	282	1757	282	1757	282	279
125°	394	1390	394	1390	394	350
135°	472	1146	472	1146	472	365
145°	551	958	551	958	551	345
155°	628	816	628	816	628	289
165°	687	752	687	752	687	194
175°	718	723	718	723	718	68
180°	721	721	721	721	721	

TEST NUMBER: P1191324

CATALOG NUMBER: SQ2-FA-100U-050D-L835-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	875.4	888.8	889.1	889.1	889.1	889.1	889.1	888.8	875.4	875.4	861.8
5°	867.2	890.6	898.0	901.5	908.2	901.5	898.0	890.6	867.2	857.2	802.4
7.5°	859.1	890.4	901.4	907.6	911.0	907.6	901.4	890.4	859.1	814.3	699.3
10°	853.6	890.3	901.4	904.9	908.2	904.9	901.4	890.3	853.6	763.5	669.2
12.5°	845.4	884.8	898.7	902.2	905.5	902.2	898.7	884.8	845.4	717.9	647.4
15°	822.9	876.3	887.7	894.6	898.0	894.6	887.7	876.3	822.9	679.3	631.7
17.5°	794.9	859.6	874.8	881.0	883.6	881.0	874.8	859.6	794.9	644.6	632.3
20°	778.5	848.6	863.8	867.2	867.2	867.2	863.8	848.6	778.5	628.2	648.7
22.5°	756.6	834.7	850.2	850.9	853.6	850.9	850.2	834.7	756.6	609.1	656.9
25°	713.6	803.7	826.3	823.0	829.7	823.0	826.3	803.7	713.6	583.4	655.6
27.5°	661.0	774.5	790.8	794.2	794.2	794.2	790.8	774.5	661.0	558.2	641.9
30°	628.2	755.1	771.6	775.1	775.1	775.1	771.6	755.1	628.2	541.4	628.2
32.5°	587.3	738.2	752.5	753.2	753.2	753.2	752.5	738.2	587.3	524.5	606.4
35°	525.8	709.4	720.4	720.4	717.0	720.4	720.4	709.4	525.8	499.1	580.4
37.5°	464.4	672.7	687.7	682.8	679.5	682.8	687.7	672.7	464.4	473.0	558.6
40°	423.4	650.4	665.8	655.5	652.1	655.5	665.8	650.4	423.4	453.4	539.5
42.5°	401.5	625.9	641.2	628.2	624.8	628.2	641.2	625.9	401.5	434.2	523.1
45°	385.8	586.1	600.9	587.1	580.4	587.1	600.9	586.1	385.8	405.9	495.1
47.5°	361.9	538.2	559.3	538.6	532.0	538.6	559.3	538.2	361.9	376.6	469.8
50°	334.6	508.2	529.2	508.6	501.9	508.6	529.2	508.2	334.6	354.6	450.7
52.5°	315.5	478.4	496.4	473.1	466.4	473.1	496.4	478.4	315.5	327.5	434.3
55°	297.1	433.9	447.3	423.2	413.1	423.2	447.3	433.9	297.1	287.0	402.9
57.5°	254.0	384.2	398.1	370.5	359.2	370.5	398.1	384.2	254.0	245.3	370.1
60°	232.2	349.0	365.3	337.6	321.0	337.6	365.3	349.0	232.2	215.5	348.3
62.5°	207.6	311.1	332.6	304.9	288.2	304.9	332.6	311.1	207.6	196.2	323.7
65°	167.3	257.4	283.4	255.7	239.0	255.7	283.4	257.4	167.3	174.0	283.4
67.5°	131.1	208.6	237.6	207.3	193.9	207.3	237.6	208.6	131.1	153.1	246.5
70°	109.3	176.0	204.9	177.2	163.9	177.2	204.9	176.0	109.3	139.3	221.9
72.5°	95.6	146.3	177.5	147.3	136.6	147.3	177.5	146.3	95.6	125.6	191.9
75°	71.7	101.7	136.6	109.1	102.4	109.1	136.6	101.7	71.7	101.7	150.2
77.5°	51.9	65.9	96.3	73.0	70.3	73.0	96.3	65.9	51.9	76.6	109.3
80°	41.0	44.3	71.7	51.2	51.2	51.2	71.7	44.3	41.0	57.7	81.9
82.5°	27.3	30.7	49.8	34.8	32.1	34.8	49.8	30.7	27.3	41.3	57.4
85°	13.7	13.7	20.5	13.7	13.7	13.7	20.5	13.7	13.7	20.3	27.3
87.5°	2.7	3.2	8.2	4.3	4.1	4.3	8.2	3.2	2.7	5.8	8.2
90°	0.0	2.2	13.6	7.9	6.8	7.9	13.6	2.2	0.0	2.2	13.6
92.5°	12.7	51.2	183.7	60.9	43.9	60.9	183.7	51.2	12.7	51.2	183.7
95°	37.3	118.1	567.9	209.8	132.4	209.8	567.9	118.1	37.3	118.1	567.9
97.5°	72.2	150.3	895.1	592.3	360.7	592.3	895.1	150.3	72.2	150.3	895.1
100°	93.9	170.2	1000.1	966.9	649.4	966.9	1000.1	170.2	93.9	170.2	1000.1
102.5°	118.3	192.0	978.4	1356.1	1081.1	1356.1	978.4	192.0	118.3	192.0	978.4
105°	158.4	222.6	893.8	1697.4	1613.3	1697.4	893.8	222.6	158.4	222.6	893.8
107.5°	196.4	257.7	812.3	1731.2	1828.5	1731.2	812.3	257.7	196.4	257.7	812.3
110°	221.7	280.4	771.6	1688.6	1865.6	1688.6	771.6	280.4	221.7	280.4	771.6

TEST NUMBER: P1191324

CATALOG NUMBER: SQ2-FA-100U-050D-L835-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	246.2	303.0	747.2	1617.3	1841.2	1617.3	747.2	303.0	246.2	303.0	747.2
115°	281.7	335.9	722.9	1495.9	1757.0	1495.9	722.9	335.9	281.7	335.9	722.9
117.5°	317.0	368.3	714.3	1382.3	1649.5	1382.3	714.3	368.3	317.0	368.3	714.3
120°	340.5	389.2	711.6	1316.0	1572.6	1316.0	711.6	389.2	340.5	389.2	711.6
122.5°	362.3	408.3	711.6	1257.6	1494.8	1257.6	711.6	408.3	362.3	408.3	711.6
125°	393.7	436.9	712.8	1181.4	1390.4	1181.4	712.8	436.9	393.7	436.9	712.8
127.5°	419.3	464.0	711.6	1123.9	1302.2	1123.9	711.6	464.0	419.3	464.0	711.6
130°	435.6	482.0	711.6	1090.9	1252.4	1090.9	711.6	482.0	435.6	482.0	711.6
132.5°	450.1	497.4	710.7	1060.8	1209.9	1060.8	710.7	497.4	450.1	497.4	710.7
135°	471.8	521.6	708.2	1018.9	1146.1	1018.9	708.2	521.6	471.8	521.6	708.2
137.5°	496.0	543.3	708.2	974.1	1092.0	974.1	708.2	543.3	496.0	543.3	708.2
140°	511.4	557.8	708.2	945.0	1056.7	945.0	708.2	557.8	511.4	557.8	708.2
142.5°	526.8	571.5	707.3	918.4	1016.0	918.4	707.3	571.5	526.8	571.5	707.3
145°	551.0	591.9	708.2	876.4	958.3	876.4	708.2	591.9	551.0	591.9	708.2
147.5°	575.2	609.9	709.6	841.8	904.6	841.8	709.6	609.9	575.2	609.9	709.6
150°	590.6	622.7	710.5	822.6	875.7	822.6	710.5	622.7	590.6	622.7	710.5
152.5°	605.1	633.6	711.4	806.1	849.4	806.1	711.4	633.6	605.1	633.6	711.4
155°	627.9	648.9	712.8	785.8	815.7	785.8	712.8	648.9	627.9	648.9	712.8
157.5°	647.8	664.9	714.1	770.9	791.7	770.9	714.1	664.9	647.8	664.9	714.1
160°	659.6	674.0	715.0	761.8	777.2	761.8	715.0	674.0	659.6	674.0	715.0
162.5°	671.4	682.2	715.9	753.6	766.4	753.6	715.9	682.2	671.4	682.2	715.9
165°	686.7	694.5	716.2	743.5	752.4	743.5	716.2	694.5	686.7	694.5	716.2
167.5°	699.9	703.8	717.5	735.7	739.5	735.7	717.5	703.8	699.9	703.8	717.5
170°	707.1	709.3	718.4	732.0	733.1	732.0	718.4	709.3	707.1	709.3	718.4
172.5°	711.6	713.0	718.4	728.4	728.6	728.4	718.4	713.0	711.6	713.0	718.4
175°	718.4	718.4	719.5	725.2	722.9	725.2	719.5	718.4	718.4	718.4	719.5
177.5°	721.6	720.7	719.8	722.4	720.7	722.4	719.8	720.7	721.6	720.7	719.8
180°	720.7	720.7	720.7	720.7	720.7	720.7	720.7	720.7	720.7	720.7	720.7

TEST NUMBER: P1191324

CATALOG NUMBER: SQ2-FA-100U-050D-L835-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	853.5	850.9	853.5	861.8	875.4	875.4
5°	740.5	723.8	740.5	802.4	857.2	867.2
7.5°	673.2	667.9	673.2	699.3	814.3	859.1
10°	648.7	648.7	648.7	669.2	763.5	853.6
12.5°	646.3	659.7	646.3	647.4	717.9	845.4
15°	686.7	703.4	686.7	631.7	679.3	822.9
17.5°	700.2	713.6	700.2	632.3	644.6	794.9
20°	700.2	713.6	700.2	648.7	628.2	778.5
22.5°	697.5	710.9	697.5	656.9	609.1	756.6
25°	689.9	696.5	689.9	655.6	583.4	713.6
27.5°	676.2	680.8	676.2	641.9	558.2	661.0
30°	662.6	672.6	662.6	628.2	541.4	628.2
32.5°	648.8	650.8	648.8	606.4	524.5	587.3
35°	628.2	624.8	628.2	580.4	499.1	525.8
37.5°	600.3	604.3	600.3	558.6	473.0	464.4
40°	584.0	590.7	584.0	539.5	453.4	423.4
42.5°	567.6	574.3	567.6	523.1	434.2	401.5
45°	543.0	546.3	543.0	495.1	405.9	385.8
47.5°	514.3	517.6	514.3	469.8	376.6	361.9
50°	495.2	498.5	495.2	450.7	354.6	334.6
52.5°	473.3	476.6	473.3	434.3	327.5	315.5
55°	440.5	440.5	440.5	402.9	287.0	297.1
57.5°	403.0	407.0	403.0	370.1	245.3	254.0
60°	375.7	382.4	375.7	348.3	215.5	232.2
62.5°	351.1	355.1	351.1	323.7	196.2	207.6
65°	310.8	314.1	310.8	283.4	174.0	167.3
67.5°	265.7	268.4	265.7	246.5	153.1	131.1
70°	235.6	235.6	235.6	221.9	139.3	109.3
72.5°	205.6	208.3	205.6	191.9	125.6	95.6
75°	160.6	163.9	160.6	150.2	101.7	71.7
77.5°	115.5	118.8	115.5	109.3	76.6	51.9
80°	85.4	88.8	85.4	81.9	57.7	41.0
82.5°	60.8	61.5	60.8	57.4	41.3	27.3
85°	27.3	27.3	27.3	27.3	20.3	13.7
87.5°	7.0	6.8	7.0	8.2	5.8	2.7
90°	7.9	6.8	7.9	13.6	2.2	0.0
92.5°	60.9	43.9	60.9	183.7	51.2	12.7
95°	209.8	132.4	209.8	567.9	118.1	37.3
97.5°	592.3	360.7	592.3	895.1	150.3	72.2
100°	966.9	649.4	966.9	1000.1	170.2	93.9
102.5°	1356.1	1081.1	1356.1	978.4	192.0	118.3
105°	1697.4	1613.3	1697.4	893.8	222.6	158.4
107.5°	1731.2	1828.5	1731.2	812.3	257.7	196.4
110°	1688.6	1865.6	1688.6	771.6	280.4	221.7

TEST NUMBER: P1191324

CATALOG NUMBER: SQ2-FA-100U-050D-L835-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	1617.3	1841.2	1617.3	747.2	303.0	246.2
115°	1495.9	1757.0	1495.9	722.9	335.9	281.7
117.5°	1382.3	1649.5	1382.3	714.3	368.3	317.0
120°	1316.0	1572.6	1316.0	711.6	389.2	340.5
122.5°	1257.6	1494.8	1257.6	711.6	408.3	362.3
125°	1181.4	1390.4	1181.4	712.8	436.9	393.7
127.5°	1123.9	1302.2	1123.9	711.6	464.0	419.3
130°	1090.9	1252.4	1090.9	711.6	482.0	435.6
132.5°	1060.8	1209.9	1060.8	710.7	497.4	450.1
135°	1018.9	1146.1	1018.9	708.2	521.6	471.8
137.5°	974.1	1092.0	974.1	708.2	543.3	496.0
140°	945.0	1056.7	945.0	708.2	557.8	511.4
142.5°	918.4	1016.0	918.4	707.3	571.5	526.8
145°	876.4	958.3	876.4	708.2	591.9	551.0
147.5°	841.8	904.6	841.8	709.6	609.9	575.2
150°	822.6	875.7	822.6	710.5	622.7	590.6
152.5°	806.1	849.4	806.1	711.4	633.6	605.1
155°	785.8	815.7	785.8	712.8	648.9	627.9
157.5°	770.9	791.7	770.9	714.1	664.9	647.8
160°	761.8	777.2	761.8	715.0	674.0	659.6
162.5°	753.6	766.4	753.6	715.9	682.2	671.4
165°	743.5	752.4	743.5	716.2	694.5	686.7
167.5°	735.7	739.5	735.7	717.5	703.8	699.9
170°	732.0	733.1	732.0	718.4	709.3	707.1
172.5°	728.4	728.6	728.4	718.4	713.0	711.6
175°	725.2	722.9	725.2	719.5	718.4	718.4
177.5°	722.4	720.7	722.4	719.8	720.7	721.6
180°	720.7	720.7	720.7	720.7	720.7	720.7

TEST NUMBER: P1191324

CATALOG NUMBER: SQ2-FA-100U-050D-L835-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.73	14.45	14.82	15.54	17.04	14.95	15.68	16.05	16.77	18.27
	3H	14.81	15.46	15.91	16.56	18.07	16.19	16.83	17.29	17.93	19.45
	4H	15.15	15.77	16.27	16.87	18.39	16.57	17.19	17.68	18.29	19.81
	6H	15.31	15.88	16.43	16.98	18.51	16.72	17.29	17.84	18.39	19.92
	8H	15.34	15.88	16.46	17.00	18.52	16.74	17.28	17.87	18.40	19.93
	12H	15.33	15.84	16.46	16.96	18.51	16.72	17.23	17.85	18.35	19.90
4H	2H	14.64	15.26	15.76	16.36	17.88	15.55	16.17	16.67	17.27	18.79
	3H	16.00	16.51	17.12	17.63	19.17	16.99	17.50	18.12	18.63	20.16
	4H	16.43	16.91	17.56	18.02	19.57	17.45	17.92	18.58	19.04	20.59
	6H	16.65	17.06	17.79	18.20	19.74	17.66	18.07	18.80	19.21	20.75
	8H	16.71	17.08	17.84	18.22	19.78	17.71	18.09	18.84	19.22	20.78
	12H	16.70	17.04	17.86	18.19	19.75	17.69	18.03	18.84	19.18	20.74
8H	4H	16.82	17.20	17.96	18.33	19.89	17.65	18.03	18.79	19.16	20.72
	6H	17.16	17.47	18.32	18.65	20.20	17.95	18.26	19.11	19.44	21.00
	8H	17.28	17.55	18.44	18.70	20.28	18.05	18.32	19.21	19.47	21.05
	12H	17.31	17.54	18.47	18.69	20.31	18.05	18.29	19.22	19.44	21.05
12H	4H	16.82	17.16	17.97	18.30	19.87	17.61	17.95	18.76	19.09	20.66
	6H	17.23	17.50	18.40	18.66	20.24	17.97	18.24	19.14	19.40	20.98
	8H	17.37	17.61	18.54	18.76	20.37	18.08	18.32	19.25	19.47	21.08