

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1191229

Luminaire Tested: SQ2-FA-025U-050D-L840-UNV-STD-W-4

Issue Date: 9/23/2025

Test Information

Test Method: LM-79-2019
Report Number: P1191229
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-9, G2-2502-345-2)
Test Lab: INNOVATION CENTER
Issue Date: 9/23/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FA-025U-050D-L840-UNV-STD-W-4
Description: CORELITE SQ2 LED LUMINAIRE
FROSTED CONTINUOUS ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3432.0 lumens
Efficiency: N/A
Efficacy: 136.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 25.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1191229

CATALOG NUMBER: SQ2-FA-025U-050D-L840-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P1191229

CATALOG NUMBER: SQ2-FA-025U-050D-L840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	101	97	93	90	95	92	88	85	81	78	76	71	70	68	63	61	60
2	92	85	79	73	87	80	75	70	71	67	63	63	60	57	55	53	51
3	84	75	67	61	79	71	64	58	63	58	53	56	51	48	49	46	43
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37
5	71	59	51	45	67	56	48	43	50	44	39	45	40	36	39	35	32
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	28
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	28	25
8	56	44	36	30	53	41	34	29	37	31	27	34	28	25	30	26	23
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	20
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14648	14648	14648	14648
5°	14475	15159	14475	12081
10°	14411	15334	14411	10953
15°	14165	15457	14165	12107
20°	13775	15345	13775	12627
25°	13092	15221	13092	12779
30°	12062	14881	12062	12914
35°	10673	14554	10673	12684
40°	9190	14155	9190	12821
45°	9072	13648	9072	12846
50°	8656	12984	8656	12896
55°	8611	11978	8611	12769
60°	7721	10672	7721	12716
65°	6583	9402	6583	12359
70°	5311	7969	5311	11452
75°	4604	6581	4604	10530
80°	3924	4900	3924	8498
85°	2612	2612	2612	5206

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 14129 cd/sqm

TEST NUMBER: P1191229

CATALOG NUMBER: SQ2-FA-025U-050D-L840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.6	2.4
10°-20°	228.1	6.6
20°-30°	346.4	10.1
30°-40°	406.6	11.8
40°-50°	412.6	12.0
50°-60°	361.5	10.5
60°-70°	256.4	7.5
70°-80°	132.0	3.8
80°-90°	28.2	0.8
90°-100°	76.8	2.2
100°-110°	239.0	7.0
110°-120°	233.9	6.8
120°-130°	190.9	5.6
130°-140°	156.2	4.6
140°-150°	121.9	3.6
150°-160°	88.0	2.6
160°-170°	53.8	1.6
170°-180°	18.1	0.5
0°-30°	656.1	19.1
0°-40°	1062.7	31.0
0°-60°	1836.8	53.5
0°-90°	2253.5	65.7
90°-120°	549.7	16.0
90°-150°	1018.7	29.7
90°-180°	1179.0	34.4
0°-180°	3432.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	907	907	907	907	907	
5°	893	935	893	745	893	85
15°	847	925	847	724	847	238
25°	735	854	735	717	735	335
35°	542	738	542	644	542	337
45°	397	598	397	563	397	304
55°	306	426	306	454	306	265
65°	172	246	172	324	172	172
75°	74	106	74	169	74	80
85°	14	14	14	28	14	18
90°	0	4	0	4	0	1
95°	10	34	10	34	10	12
105°	42	429	42	429	42	44
115°	75	461	75	461	75	74
125°	104	364	104	364	104	92
135°	125	301	125	301	125	96
145°	146	252	146	252	146	91
155°	167	214	167	214	167	77
165°	183	198	183	198	183	51
175°	190	190	190	190	190	18
180°	190	190	190	190	190	

TEST NUMBER: P1191229

CATALOG NUMBER: SQ2-FA-025U-050D-L840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	907.2	907.2	907.2	907.2	907.2	907.2	907.2	907.2	907.2	907.2	907.2
2.5°	901.5	915.3	915.6	915.6	915.6	915.6	915.6	915.3	901.5	901.5	887.5
5°	893.1	917.2	924.7	928.4	935.3	928.4	924.7	917.2	893.1	882.8	826.3
7.5°	884.7	917.0	928.3	934.7	938.1	934.7	928.3	917.0	884.7	838.6	720.1
10°	879.0	916.9	928.3	931.9	935.3	931.9	928.3	916.9	879.0	786.2	689.2
12.5°	870.6	911.2	925.5	929.0	932.5	929.0	925.5	911.2	870.6	739.3	666.7
15°	847.4	902.4	914.2	921.3	924.7	921.3	914.2	902.4	847.4	699.6	650.5
17.5°	818.6	885.3	900.8	907.2	910.0	907.2	900.8	885.3	818.6	663.9	651.2
20°	801.7	873.9	889.6	893.1	893.1	889.6	873.9	801.7	647.0	668.1	
22.5°	779.2	859.6	875.5	876.3	879.0	876.3	875.5	859.6	779.2	627.2	676.5
25°	734.9	827.7	850.9	847.6	854.4	847.6	850.9	827.7	734.9	600.8	675.1
27.5°	680.7	797.6	814.3	817.9	817.9	814.3	797.6	680.7	574.8	661.0	
30°	647.0	777.6	794.7	798.2	798.2	794.7	777.6	647.0	557.6	647.0	
32.5°	604.8	760.2	775.0	775.7	775.7	775.0	760.2	604.8	540.1	624.5	
35°	541.5	730.6	741.9	741.8	738.4	741.8	741.9	730.6	541.5	514.0	597.7
37.5°	478.2	692.7	708.2	703.2	699.7	703.2	708.2	692.7	478.2	487.1	575.2
40°	436.0	669.8	685.7	675.0	671.6	675.0	685.7	669.8	436.0	466.9	555.6
42.5°	413.5	644.5	660.3	646.9	643.5	646.9	660.3	644.5	413.5	447.2	538.7
45°	397.3	603.6	618.8	604.6	597.7	604.6	618.8	603.6	397.3	418.0	509.8
47.5°	372.7	554.2	575.9	554.7	547.8	554.7	575.9	554.2	372.7	387.8	483.8
50°	344.6	523.4	545.0	523.8	516.9	523.8	545.0	523.4	344.6	365.2	464.1
52.5°	324.9	492.7	511.2	487.2	480.3	487.2	511.2	492.7	324.9	337.3	447.3
55°	305.9	446.9	460.6	435.8	425.5	435.8	460.6	446.9	305.9	295.6	414.9
57.5°	261.6	395.7	410.0	381.6	369.9	381.6	410.0	395.7	261.6	252.7	381.2
60°	239.1	359.4	376.2	347.7	330.5	347.7	376.2	359.4	239.1	221.9	358.6
62.5°	213.8	320.4	342.5	314.0	296.8	314.0	342.5	320.4	213.8	202.1	333.3
65°	172.3	265.1	291.8	263.3	246.1	263.3	291.8	265.1	172.3	179.2	291.8
67.5°	135.0	214.8	244.7	213.5	199.7	213.5	244.7	214.8	135.0	157.7	253.9
70°	112.5	181.3	211.0	182.5	168.8	182.5	211.0	181.3	112.5	143.5	228.6
72.5°	98.5	150.7	182.8	151.6	140.6	151.6	182.8	150.7	98.5	129.4	197.6
75°	73.8	104.8	140.6	112.4	105.5	112.4	140.6	104.8	73.8	104.8	154.7
77.5°	53.4	67.9	99.2	75.2	72.4	75.2	99.2	67.9	53.4	78.9	112.5
80°	42.2	45.6	73.8	52.7	52.7	52.7	73.8	45.6	42.2	59.4	84.4
82.5°	28.1	31.6	51.3	35.8	33.1	35.8	51.3	31.6	28.1	42.6	59.1
85°	14.1	14.1	21.1	14.1	14.1	14.1	21.1	14.1	14.1	20.9	28.1
87.5°	2.8	3.0	6.3	3.5	3.5	3.5	6.3	3.0	2.8	5.8	6.3
90°	0.0	1.1	3.5	3.5	3.5	3.5	3.5	1.1	0.0	1.1	3.5
92.5°	3.7	13.1	44.5	14.6	11.9	14.6	44.5	13.1	3.7	13.1	44.5
95°	10.5	31.0	141.0	52.0	33.8	52.0	141.0	31.0	10.5	31.0	141.0
97.5°	19.1	40.3	233.5	145.3	91.6	145.3	233.5	40.3	19.1	40.3	233.5
100°	25.6	45.0	263.3	246.3	164.3	246.3	263.3	45.0	25.6	45.0	263.3
102.5°	32.2	50.6	257.7	351.7	276.1	351.7	257.7	50.6	32.2	50.6	257.7
105°	41.9	59.0	235.3	449.2	428.7	449.2	235.3	59.0	41.9	59.0	235.3
107.5°	51.7	67.7	213.9	456.7	479.3	456.7	213.9	67.7	51.7	67.7	213.9
110°	58.3	74.2	202.7	446.0	490.5	446.0	202.7	74.2	58.3	74.2	202.7

TEST NUMBER: P1191229

CATALOG NUMBER: SQ2-FA-025U-050D-L840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	64.8	79.8	197.1	426.7	483.0	426.7	197.1	79.8	64.8	79.8	197.1
115°	74.6	88.2	191.1	394.1	461.3	394.1	191.1	88.2	74.6	88.2	191.1
117.5°	84.1	96.6	188.5	363.0	431.8	363.0	188.5	96.6	84.1	96.6	188.5
120°	89.7	102.2	187.6	345.2	411.3	345.2	187.6	102.2	89.7	102.2	187.6
122.5°	95.3	107.8	188.5	330.1	390.7	330.1	188.5	107.8	95.3	107.8	188.5
125°	103.7	115.1	188.7	309.9	363.5	309.9	188.7	115.1	103.7	115.1	188.7
127.5°	110.4	122.1	188.7	294.9	340.4	294.9	188.7	122.1	110.4	122.1	188.7
130°	114.2	126.7	188.7	286.4	327.4	286.4	188.7	126.7	114.2	126.7	188.7
132.5°	118.8	131.4	187.8	278.8	317.1	278.8	187.8	131.4	118.8	131.4	187.8
135°	124.7	138.3	187.6	267.5	300.6	267.5	187.6	138.3	124.7	138.3	187.6
137.5°	131.4	143.9	187.6	256.3	286.4	256.3	187.6	143.9	131.4	143.9	187.6
140°	135.1	147.7	187.6	248.8	276.1	248.8	187.6	147.7	135.1	147.7	187.6
142.5°	139.8	151.4	187.6	241.3	265.9	241.3	187.6	151.4	139.8	151.4	187.6
145°	145.6	157.0	187.6	231.1	251.6	231.1	187.6	157.0	145.6	157.0	187.6
147.5°	152.6	162.4	188.7	221.7	237.9	221.7	188.7	162.4	152.6	162.4	188.7
150°	157.3	165.3	188.7	217.0	229.5	217.0	188.7	165.3	157.3	165.3	188.7
152.5°	161.0	168.1	188.7	212.3	223.0	212.3	188.7	168.1	161.0	168.1	188.7
155°	166.6	172.3	188.7	207.5	214.4	207.5	188.7	172.3	166.6	172.3	188.7
157.5°	172.2	176.5	188.7	203.3	207.6	203.3	188.7	176.5	172.2	176.5	188.7
160°	175.9	179.3	188.7	200.5	203.9	200.5	188.7	179.3	175.9	179.3	188.7
162.5°	178.7	181.2	188.7	198.6	201.1	198.6	188.7	181.2	178.7	181.2	188.7
165°	182.9	184.0	189.9	195.8	198.1	195.8	189.9	184.0	182.9	184.0	189.9
167.5°	185.5	185.7	188.7	194.1	195.3	194.1	188.7	185.7	185.5	185.7	188.7
170°	186.4	187.5	188.7	192.3	193.4	192.3	188.7	187.5	186.4	187.5	188.7
172.5°	188.3	188.5	189.7	191.3	191.5	191.3	189.7	188.5	188.3	188.5	189.7
175°	189.9	189.9	189.9	191.0	189.9	191.0	189.9	189.9	189.9	189.9	189.9
177.5°	189.9	189.9	189.9	189.9	189.9	189.9	189.9	189.9	189.9	189.9	189.9
180°	189.9	189.9	189.9	189.9	189.9	189.9	189.9	189.9	189.9	189.9	189.9

TEST NUMBER: P1191229

CATALOG NUMBER: SQ2-FA-025U-050D-L840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	907.2	907.2	907.2	907.2	907.2	907.2
2.5°	879.0	876.2	879.0	887.5	901.5	901.5
5°	762.6	745.4	762.6	826.3	882.8	893.1
7.5°	693.3	687.8	693.3	720.1	838.6	884.7
10°	668.1	668.1	668.1	689.2	786.2	879.0
12.5°	665.6	679.3	665.6	666.7	739.3	870.6
15°	707.1	724.3	707.1	650.5	699.6	847.4
17.5°	721.1	734.9	721.1	651.2	663.9	818.6
20°	721.1	734.9	721.1	668.1	647.0	801.7
22.5°	718.3	732.1	718.3	676.5	627.2	779.2
25°	710.4	717.3	710.4	675.1	600.8	734.9
27.5°	696.3	701.1	696.3	661.0	574.8	680.7
30°	682.4	692.7	682.4	647.0	557.6	647.0
32.5°	668.1	670.2	668.1	624.5	540.1	604.8
35°	646.9	643.5	646.9	597.7	514.0	541.5
37.5°	618.2	622.4	618.2	575.2	487.1	478.2
40°	601.4	608.3	601.4	555.6	466.9	436.0
42.5°	584.5	591.4	584.5	538.7	447.2	413.5
45°	559.1	562.6	559.1	509.8	418.0	397.3
47.5°	529.6	533.0	529.6	483.8	387.8	372.7
50°	509.9	513.4	509.9	464.1	365.2	344.6
52.5°	487.4	490.9	487.4	447.3	337.3	324.9
55°	453.6	453.6	453.6	414.9	295.6	305.9
57.5°	415.0	419.1	415.0	381.2	252.7	261.6
60°	386.9	393.8	386.9	358.6	221.9	239.1
62.5°	361.6	365.7	361.6	333.3	202.1	213.8
65°	320.0	323.5	320.0	291.8	179.2	172.3
67.5°	273.6	276.4	273.6	253.9	157.7	135.0
70°	242.6	242.6	242.6	228.6	143.5	112.5
72.5°	211.7	214.5	211.7	197.6	129.4	98.5
75°	165.3	168.8	165.3	154.7	104.8	73.8
77.5°	118.9	122.4	118.9	112.5	78.9	53.4
80°	88.0	91.4	88.0	84.4	59.4	42.2
82.5°	62.6	63.3	62.6	59.1	42.6	28.1
85°	28.1	28.1	28.1	28.1	20.9	14.1
87.5°	6.3	6.3	6.3	6.3	5.8	2.8
90°	3.5	3.5	3.5	3.5	1.1	0.0
92.5°	14.6	11.9	14.6	44.5	13.1	3.7
95°	52.0	33.8	52.0	141.0	31.0	10.5
97.5°	145.3	91.6	145.3	233.5	40.3	19.1
100°	246.3	164.3	246.3	263.3	45.0	25.6
102.5°	351.7	276.1	351.7	257.7	50.6	32.2
105°	449.2	428.7	449.2	235.3	59.0	41.9
107.5°	456.7	479.3	456.7	213.9	67.7	51.7
110°	446.0	490.5	446.0	202.7	74.2	58.3

TEST NUMBER: P1191229

CATALOG NUMBER: SQ2-FA-025U-050D-L840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	426.7	483.0	426.7	197.1	79.8	64.8
115°	394.1	461.3	394.1	191.1	88.2	74.6
117.5°	363.0	431.8	363.0	188.5	96.6	84.1
120°	345.2	411.3	345.2	187.6	102.2	89.7
122.5°	330.1	390.7	330.1	188.5	107.8	95.3
125°	309.9	363.5	309.9	188.7	115.1	103.7
127.5°	294.9	340.4	294.9	188.7	122.1	110.4
130°	286.4	327.4	286.4	188.7	126.7	114.2
132.5°	278.8	317.1	278.8	187.8	131.4	118.8
135°	267.5	300.6	267.5	187.6	138.3	124.7
137.5°	256.3	286.4	256.3	187.6	143.9	131.4
140°	248.8	276.1	248.8	187.6	147.7	135.1
142.5°	241.3	265.9	241.3	187.6	151.4	139.8
145°	231.1	251.6	231.1	187.6	157.0	145.6
147.5°	221.7	237.9	221.7	188.7	162.4	152.6
150°	217.0	229.5	217.0	188.7	165.3	157.3
152.5°	212.3	223.0	212.3	188.7	168.1	161.0
155°	207.5	214.4	207.5	188.7	172.3	166.6
157.5°	203.3	207.6	203.3	188.7	176.5	172.2
160°	200.5	203.9	200.5	188.7	179.3	175.9
162.5°	198.6	201.1	198.6	188.7	181.2	178.7
165°	195.8	198.1	195.8	189.9	184.0	182.9
167.5°	194.1	195.3	194.1	188.7	185.7	185.5
170°	192.3	193.4	192.3	188.7	187.5	186.4
172.5°	191.3	191.5	191.3	189.7	188.5	188.3
175°	191.0	189.9	191.0	189.9	189.9	189.9
177.5°	189.9	189.9	189.9	189.9	189.9	189.9
180°	189.9	189.9	189.9	189.9	189.9	189.9

TEST NUMBER: P1191229

CATALOG NUMBER: SQ2-FA-025U-050D-L840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.01	18.03	17.82	18.86	19.89	18.23	19.25	19.04	20.09	21.12
	3H	18.11	19.03	18.93	19.87	20.93	19.49	20.40	20.31	21.25	22.30
	4H	18.47	19.33	19.31	20.18	21.25	19.89	20.75	20.73	21.60	22.67
	6H	18.64	19.44	19.50	20.30	21.38	20.06	20.85	20.91	21.71	22.79
	8H	18.68	19.44	19.54	20.32	21.40	20.09	20.84	20.95	21.72	22.80
	12H	18.68	19.41	19.55	20.28	21.38	20.08	20.80	20.94	21.67	22.77
4H	2H	17.96	18.82	18.80	19.67	20.74	18.87	19.73	19.71	20.58	21.65
	3H	19.34	20.06	20.20	20.94	22.03	20.33	21.05	21.19	21.94	23.02
	4H	19.79	20.45	20.66	21.33	22.44	20.81	21.46	21.68	22.34	23.45
	6H	20.03	20.59	20.91	21.50	22.61	21.04	21.60	21.92	22.51	23.62
	8H	20.09	20.62	20.98	21.52	22.64	21.09	21.62	21.98	22.52	23.64
	12H	20.10	20.57	21.01	21.49	22.62	21.09	21.56	21.99	22.48	23.61
8H	4H	20.20	20.73	21.09	21.63	22.76	21.03	21.56	21.92	22.46	23.58
	6H	20.56	20.99	21.47	21.93	23.06	21.35	21.78	22.26	22.72	23.85
	8H	20.67	21.06	21.60	21.99	23.14	21.44	21.83	22.37	22.76	23.91
	12H	20.72	21.06	21.64	21.98	23.18	21.46	21.80	22.39	22.73	23.92
12H	4H	20.21	20.69	21.12	21.61	22.74	21.01	21.48	21.91	22.40	23.53
	6H	20.63	21.02	21.56	21.95	23.09	21.37	21.76	22.29	22.69	23.83
	8H	20.78	21.12	21.71	22.05	23.24	21.49	21.83	22.42	22.75	23.95