

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855359

Luminaire Tested: SQ2-PH1-125U-100D-840-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855359
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PH1-125U-100D-840-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11047.9 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 81.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855359
CATALOG NUMBER: SQ2-PH1-125U-100D-840-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855359

CATALOG NUMBER: SQ2-PH1-125U-100D-840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48				48
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	41	39				34	
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	38	35	33				29	
4	74	64	56	50	68	59	52	47	50	45	40	41	38	35	34	31	29				25	
5	68	57	49	43	62	52	45	40	45	39	35	37	33	30	30	27	25				22	
6	63	51	43	37	58	47	40	35	40	35	30	34	29	26	28	24	22				19	
7	58	46	38	32	53	43	36	31	36	31	27	31	26	23	25	22	20				17	
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16				14	
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	38358	38358	38358
5°	38577	36269	35060
10°	37689	33019	31870
15°	37857	31057	31246
20°	36508	30100	31498
25°	35838	29959	30765
30°	35061	29880	31016
35°	34795	29538	36356
40°	34825	29347	28823
45°	34837	28232	24825
50°	34350	28788	23277
55°	33914	31240	22334
60°	33577	27370	20951
65°	32986	22197	18220
70°	31162	18888	13015
75°	27779	14242	9875
80°	22706	9242	9242
85°	14227	8373	6280

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34837 cd/sqm



TEST NUMBER: P855359

CATALOG NUMBER: SQ2-PH1-125U-100D-840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.0	1.9
10°-20°	549.8	5.0
20°-30°	806.2	7.3
30°-40°	976.4	8.8
40°-50°	960.2	8.7
50°-60°	835.8	7.6
60°-70°	581.1	5.3
70°-80°	275.5	2.5
80°-90°	61.7	0.6
90°-100°	359.1	3.3
100°-110°	1169.2	10.6
110°-120°	1156.5	10.5
120°-130°	945.1	8.6
130°-140°	772.4	7.0
140°-150°	601.7	5.4
150°-160°	433.7	3.9
160°-170°	265.1	2.4
170°-180°	89.4	0.8
0°-30°	1565.1	14.2
0°-40°	2541.5	23.0
0°-60°	4337.4	39.3
0°-90°	5255.7	47.6
90°-120°	2684.8	24.3
90°-150°	5004.0	45.3
90°-180°	5792.0	52.4
0°-180°	11047.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2376	2376	2376	2376	2376	
5°	2380	2378	2238	2168	2163	224
15°	2265	2017	1858	1845	1869	631
25°	2012	1711	1682	1734	1727	925
35°	1765	1427	1499	1628	1844	1106
45°	1526	1130	1236	1280	1087	1173
55°	1205	880	1110	800	793	1076
65°	863	605	581	477	477	848
75°	445	308	228	163	158	472
85°	77	50	45	36	34	103
90°	0	3	8	7	7	5
95°	48	148	658	235	144	56
105°	199	287	1158	2212	2095	212
115°	367	438	943	1944	2288	363
125°	510	569	931	1535	1810	454
135°	617	681	926	1325	1494	476
145°	721	774	924	1141	1249	451
155°	822	849	930	1022	1060	379
165°	897	905	932	967	978	253
175°	935	935	935	942	940	89
180°	939	939	939	939	939	



TEST NUMBER: P855359

CATALOG NUMBER: SQ2-PH1-125U-100D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2375.7	2375.7	2375.7	2375.7	2375.7
2.5°	2370.2	2395.0	2339.4	2317.7	2314.1
5°	2380.2	2378.0	2237.8	2167.6	2163.2
7.5°	2336.7	2268.2	2100.8	2023.4	2019.9
10°	2298.8	2194.9	2014.0	1943.9	1943.9
12.5°	2289.8	2125.8	1943.4	1891.7	1902.3
15°	2264.8	2017.3	1858.0	1845.1	1869.3
17.5°	2182.6	1916.0	1791.6	1821.2	1849.5
20°	2124.8	1861.7	1751.8	1806.6	1833.2
22.5°	2075.9	1809.4	1722.8	1782.8	1797.0
25°	2011.7	1711.2	1681.7	1733.5	1726.9
27.5°	1934.9	1621.1	1640.5	1672.4	1676.3
30°	1880.6	1566.8	1602.7	1634.9	1663.6
32.5°	1828.2	1503.7	1561.1	1637.5	1703.5
35°	1765.3	1427.2	1498.6	1627.8	1844.5
37.5°	1699.4	1336.8	1435.8	1544.5	1613.5
40°	1652.3	1272.2	1392.4	1526.7	1367.5
42.5°	1601.7	1221.6	1327.3	1500.7	1231.9
45°	1525.7	1130.1	1236.4	1279.5	1087.2
47.5°	1436.2	1059.2	1175.0	1067.0	991.9
50°	1367.5	1011.7	1146.1	975.3	926.7
52.5°	1300.6	962.5	1126.1	899.8	867.1
55°	1204.8	879.9	1109.8	800.0	793.4
57.5°	1103.1	795.9	981.5	713.2	724.6
60°	1039.8	741.4	847.6	661.9	648.8
62.5°	972.9	688.6	722.9	596.9	583.6
65°	863.4	604.8	581.0	476.9	476.9
67.5°	743.2	517.8	470.6	390.3	337.3
70°	660.1	461.1	400.1	311.2	275.7
72.5°	571.4	400.8	327.7	255.0	214.3
75°	445.3	308.2	228.3	162.7	158.3
77.5°	321.9	222.0	153.7	120.7	121.2
80°	244.2	169.0	99.4	97.2	99.4
82.5°	171.8	116.1	74.1	77.3	77.7
85°	76.8	50.3	45.2	36.1	33.9
87.5°	16.3	15.2	10.6	10.4	10.4
90°	0.0	3.4	8.0	6.9	6.9
92.5°	16.7	59.8	191.0	62.9	48.5
95°	48.5	147.9	658.2	234.7	144.4
97.5°	91.3	192.4	1117.0	680.4	415.2
100°	119.0	218.3	1289.9	1150.1	746.0
102.5°	150.3	246.1	1268.5	1701.6	1293.7
105°	198.6	286.7	1158.2	2212.2	2094.7
107.5°	250.8	333.7	1053.4	2256.4	2380.8
110°	288.7	364.3	1003.4	2201.4	2426.1



TEST NUMBER: P855359

CATALOG NUMBER: SQ2-PH1-125U-100D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	320.1	394.8	972.1	2102.2	2391.9
115°	367.2	438.3	943.4	1944.2	2287.6
117.5°	415.7	479.8	932.3	1799.7	2141.3
120°	443.4	506.6	929.5	1710.8	2041.5
122.5°	470.2	532.6	930.5	1633.5	1941.8
125°	510.4	569.1	930.7	1535.1	1809.5
127.5°	544.8	604.8	930.5	1461.3	1690.1
130°	567.0	627.9	929.5	1419.2	1623.5
132.5°	586.4	650.1	928.6	1380.1	1571.8
135°	616.6	680.9	926.1	1324.8	1494.3
137.5°	646.2	711.0	923.6	1268.8	1419.2
140°	667.4	729.5	922.6	1230.7	1373.0
142.5°	687.7	747.1	922.6	1194.3	1321.2
145°	720.6	773.6	923.8	1141.0	1249.4
147.5°	752.4	798.5	925.4	1095.7	1179.5
150°	773.7	814.3	927.3	1068.6	1139.8
152.5°	794.9	828.4	928.1	1047.9	1104.6
155°	822.2	849.2	929.5	1021.7	1060.0
157.5°	848.1	867.4	930.9	1002.2	1029.0
160°	863.8	879.5	931.9	990.1	1011.6
162.5°	877.5	889.8	931.9	979.8	995.8
165°	897.2	905.2	931.9	966.8	978.0
167.5°	911.1	916.0	932.1	956.9	962.9
170°	920.3	922.5	933.0	950.4	952.6
172.5°	926.8	928.1	934.9	946.7	946.2
175°	935.4	935.4	935.4	942.2	939.9
177.5°	938.8	937.9	937.0	941.5	937.9
180°	938.8	938.8	938.8	938.8	938.8



TEST NUMBER: P855359

CATALOG NUMBER: SQ2-PH1-125U-100D-840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.77	20.60	20.75	21.59	22.90	18.44	19.28	19.42	20.27	21.57
	3H	21.79	22.54	22.78	23.54	24.87	19.47	20.22	20.46	21.22	22.55
	4H	22.52	23.23	23.53	24.23	25.57	19.69	20.39	20.69	21.40	22.73
	6H	23.01	23.66	24.02	24.66	26.01	19.83	20.48	20.84	21.49	22.84
	8H	23.13	23.75	24.15	24.77	26.12	19.86	20.48	20.88	21.50	22.85
	12H	23.17	23.76	24.20	24.78	26.15	19.86	20.44	20.88	21.46	22.83
4H	2H	20.14	20.85	21.15	21.85	23.19	19.08	19.79	20.09	20.79	22.13
	3H	22.25	22.83	23.26	23.86	25.21	20.26	20.84	21.28	21.88	23.23
	4H	23.06	23.60	24.09	24.62	25.99	20.53	21.07	21.56	22.09	23.47
	6H	23.64	24.10	24.68	25.15	26.52	20.74	21.20	21.78	22.25	23.62
	8H	23.81	24.24	24.85	25.28	26.67	20.79	21.22	21.83	22.27	23.65
	12H	23.88	24.27	24.93	25.32	26.71	20.80	21.19	21.86	22.24	23.63
8H	4H	23.07	23.50	24.11	24.55	25.93	20.75	21.18	21.78	22.22	23.60
	6H	23.72	24.08	24.79	25.16	26.54	21.02	21.37	22.08	22.45	23.84
	8H	23.95	24.26	25.02	25.33	26.73	21.12	21.43	22.19	22.50	23.90
	12H	24.06	24.34	25.14	25.40	26.84	21.16	21.44	22.23	22.50	23.94
12H	4H	23.02	23.41	24.08	24.47	25.86	20.74	21.13	21.80	22.19	23.57
	6H	23.70	24.01	24.77	25.08	26.48	21.05	21.36	22.12	22.43	23.83
	8H	23.93	24.20	25.00	25.27	26.71	21.16	21.43	22.23	22.50	23.94