

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-PR1-025U-050D-927-1D-UNV-STD-W-4

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number:
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32)
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-PR1-025U-050D-927-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2236.5 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 22.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-PR1-025U-050D-927-1D-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-PR1-025U-050D-927-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71
1	102	98	94	90	96	92	89	86	82	79	77	72	71	69	64	62	61
2	93	86	80	74	88	81	76	71	72	68	64	64	61	58	57	54	52
3	85	76	68	63	80	72	65	60	64	59	55	57	53	50	51	47	45
4	78	67	59	53	73	64	57	51	57	51	47	51	47	43	45	42	39
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34
6	66	54	46	40	62	52	44	39	46	40	36	42	37	33	37	33	30
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24
9	53	41	33	28	50	39	32	27	35	30	25	32	27	24	29	25	22
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5507	5507	5507
5°	5556	5513	5485
10°	5539	5500	5471
15°	5514	5480	5450
20°	5486	5451	5411
25°	5448	5412	5349
30°	5390	5351	5275
35°	5309	5263	5188
40°	5189	5133	5040
45°	4978	4890	4790
50°	4605	4494	4405
55°	4018	3928	3846
60°	3386	3358	3292
65°	2930	2941	2919
70°	2689	2703	2703
75°	2584	2584	2602
80°	2433	2460	2433
85°	1958	2181	2181

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4978 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-PR1-025U-050D-927-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.4	2.5
10°-20°	161.5	7.2
20°-30°	243.6	10.9
30°-40°	290.2	13.0
40°-50°	286.1	12.8
50°-60°	218.7	9.8
60°-70°	135.3	6.1
70°-80°	76.9	3.4
80°-90°	24.0	1.1
90°-100°	55.9	2.5
100°-110°	147.0	6.6
110°-120°	152.5	6.8
120°-130°	122.3	5.5
130°-140°	95.9	4.3
140°-150°	73.6	3.3
150°-160°	53.0	2.4
160°-170°	32.5	1.5
170°-180°	11.0	0.5
0°-30°	461.5	20.6
0°-40°	751.7	33.6
0°-60°	1256.5	56.2
0°-90°	1492.7	66.7
90°-120°	355.4	15.9
90°-150°	647.3	28.9
90°-180°	744.0	33.3
0°-180°	2236.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	597	597	597	597	597	
5°	600	593	595	593	592	57
15°	577	571	574	572	571	163
25°	535	529	532	526	525	246
35°	471	466	467	461	461	294
45°	382	376	375	368	367	292
55°	250	246	244	240	239	224
65°	134	133	135	134	134	136
75°	72	72	72	73	73	77
85°	18	20	21	21	21	22
90°	1	2	6	3	3	1
95°	7	29	96	50	34	8
105°	26	40	163	247	230	28
115°	47	57	130	260	296	46
125°	66	73	118	200	236	58
135°	78	86	115	162	183	60
145°	90	96	113	138	149	57
155°	102	105	113	124	128	47
165°	110	112	113	118	119	31
175°	115	115	114	116	116	11
180°	115	115	115	115	115	

TEST NUMBER:

CATALOG NUMBER: SQ4-PR1-025U-050D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	596.9	596.9	596.9	596.9	596.9
2.5°	600.6	595.3	596.9	595.6	592.7
5°	599.9	593.4	595.3	593.2	592.2
7.5°	595.3	588.9	590.8	588.7	588.1
10°	591.2	585.2	587.1	585.0	584.0
12.5°	586.7	580.2	582.6	580.1	579.1
15°	577.3	571.3	573.7	571.6	570.6
17.5°	567.0	560.6	563.0	560.6	559.3
20°	558.8	552.8	555.2	551.6	551.1
22.5°	549.8	543.7	546.2	541.3	541.2
25°	535.2	528.6	531.6	525.9	525.4
27.5°	517.8	511.8	514.2	508.4	507.8
30°	505.9	499.8	502.3	496.1	495.1
32.5°	492.3	486.7	488.7	482.5	481.9
35°	471.4	465.9	467.3	461.1	460.6
37.5°	447.7	442.6	443.5	436.7	436.2
40°	430.8	425.8	426.2	419.0	418.5
42.5°	412.3	407.3	406.8	399.6	399.1
45°	381.5	376.4	374.8	368.1	367.1
47.5°	346.3	341.3	338.2	332.7	332.0
50°	320.8	315.8	313.1	308.4	306.9
52.5°	293.2	288.2	285.9	281.7	280.2
55°	249.8	245.8	244.2	240.1	239.1
57.5°	208.6	205.9	205.4	201.4	201.0
60°	183.5	182.0	182.0	178.4	178.4
62.5°	162.1	161.0	161.8	159.5	159.1
65°	134.2	133.2	134.7	133.7	133.7
67.5°	112.1	112.1	113.0	112.6	112.6
70°	99.7	99.7	100.2	100.2	100.2
72.5°	88.6	88.2	89.6	89.5	89.1
75°	72.5	72.5	72.5	73.0	73.0
77.5°	56.4	56.5	57.0	56.8	56.4
80°	45.8	46.3	46.3	45.8	45.8
82.5°	35.1	35.6	35.6	35.5	35.1
85°	18.5	19.5	20.6	20.6	20.6
87.5°	5.5	7.4	9.4	8.8	8.4
90°	0.7	2.2	5.9	2.9	2.9
92.5°	3.1	14.9	33.0	14.6	9.4
95°	7.4	28.9	96.4	49.7	33.8
97.5°	12.8	31.8	144.2	114.7	84.4
100°	16.9	34.2	158.9	161.0	125.0
102.5°	20.4	36.6	163.0	200.6	169.8
105°	26.5	40.1	162.6	246.8	230.2
107.5°	32.7	45.3	153.3	270.8	274.8
110°	36.8	48.3	145.6	277.0	294.2

TEST NUMBER:

CATALOG NUMBER: SQ4-PR1-025U-050D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	40.9	51.8	138.6	273.1	299.5
115°	47.1	57.1	130.2	259.8	296.4
117.5°	53.1	62.3	124.5	241.3	282.0
120°	56.6	65.3	122.1	228.9	268.5
122.5°	60.2	68.8	120.3	216.6	255.5
125°	65.5	73.4	118.4	200.2	236.1
127.5°	69.7	77.8	116.8	186.9	217.3
130°	72.1	80.7	116.2	178.6	206.7
132.5°	74.4	83.1	115.6	171.5	196.7
135°	78.0	85.9	114.7	161.6	183.2
137.5°	81.6	89.4	114.6	154.1	171.8
140°	84.6	91.8	114.0	148.2	164.8
142.5°	86.9	93.6	114.0	144.1	158.3
145°	90.5	96.2	113.3	137.8	148.6
147.5°	94.0	99.6	113.3	132.6	141.5
150°	96.4	101.4	113.3	129.6	136.8
152.5°	98.7	102.6	113.3	127.2	132.7
155°	102.2	105.1	113.3	124.4	128.0
157.5°	104.9	107.6	113.3	121.9	124.5
160°	106.7	108.8	113.3	120.7	122.1
162.5°	108.4	110.0	113.3	119.5	120.9
165°	110.3	111.8	113.3	117.7	119.2
167.5°	112.1	112.8	114.0	117.0	117.5
170°	113.3	114.0	114.0	117.0	117.0
172.5°	113.9	114.0	114.0	116.4	115.8
175°	114.7	114.7	114.0	115.5	115.5
177.5°	114.7	114.7	114.2	115.3	114.7
180°	114.7	114.7	114.7	114.7	114.7

(END OF REPORT)