

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-PR1-050U-100D-927-1D-UNV-STD-W-4

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number:
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21)
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-PR1-050U-100D-927-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4456.7 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 45.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-PR1-050U-100D-927-1D-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-PR1-050U-100D-927-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70
1	102	97	94	90	95	92	88	85	81	79	76	72	70	68	63	62	60
2	93	85	79	74	87	81	75	71	72	68	64	63	60	57	56	53	51
3	85	76	68	62	80	71	65	60	64	58	54	56	52	49	50	47	44
4	78	67	59	53	73	64	56	51	57	51	47	51	46	42	45	41	38
5	72	60	52	46	67	57	50	44	51	45	40	46	41	37	40	37	34
6	66	54	46	40	62	51	44	38	46	40	35	41	36	33	37	33	30
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	26
8	57	45	37	31	54	42	35	30	38	32	28	34	30	26	31	27	24
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	24	21
10	50	37	30	25	47	36	29	24	33	27	23	29	25	21	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10785	10785	10785
5°	10881	10797	10741
10°	10847	10771	10715
15°	10799	10732	10674
20°	10745	10675	10597
25°	10669	10597	10474
30°	10554	10479	10329
35°	10398	10308	10160
40°	10161	10052	9870
45°	9747	9576	9379
50°	9017	8800	8626
55°	7871	7692	7530
60°	6632	6576	6445
65°	5737	5759	5715
70°	5268	5295	5295
75°	5062	5062	5098
80°	4761	4814	4761
85°	3832	4266	4266

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9747 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-PR1-050U-100D-927-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.5	2.5
10°-20°	316.2	7.1
20°-30°	477.0	10.7
30°-40°	568.3	12.8
40°-50°	560.3	12.6
50°-60°	428.2	9.6
60°-70°	265.0	5.9
70°-80°	150.5	3.4
80°-90°	46.7	1.0
90°-100°	112.8	2.5
100°-110°	306.3	6.9
110°-120°	315.0	7.1
120°-130°	251.8	5.7
130°-140°	197.9	4.4
140°-150°	151.7	3.4
150°-160°	109.1	2.4
160°-170°	66.7	1.5
170°-180°	22.5	0.5
0°-30°	903.8	20.3
0°-40°	1472.1	33.0
0°-60°	2460.7	55.2
0°-90°	2922.9	65.6
90°-120°	734.1	16.5
90°-150°	1335.5	30.0
90°-180°	1534.0	34.4
0°-180°	4456.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1169	1169	1169	1169	1169	
5°	1175	1162	1166	1162	1160	111
15°	1131	1119	1124	1120	1118	319
25°	1048	1035	1041	1030	1029	482
35°	923	912	915	903	902	576
45°	747	737	734	721	719	572
55°	489	481	478	470	468	438
65°	263	261	264	262	262	266
75°	142	142	142	143	143	150
85°	36	38	40	40	40	42
90°	1	3	5	7	7	3
95°	17	62	196	86	57	18
105°	54	85	337	513	483	58
115°	97	117	270	536	611	95
125°	133	151	244	411	485	118
135°	160	178	237	335	378	124
145°	185	198	234	284	306	116
155°	209	217	233	256	263	96
165°	227	230	233	243	244	64
175°	235	236	234	237	236	22
180°	235	235	235	235	235	

TEST NUMBER:

CATALOG NUMBER: SQ4-PR1-050U-100D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.9	1168.9	1168.9	1168.9	1168.9
2.5°	1176.1	1165.9	1168.9	1166.3	1160.8
5°	1174.9	1162.1	1165.8	1161.8	1159.8
7.5°	1165.8	1153.2	1157.0	1152.9	1151.7
10°	1157.8	1146.0	1149.7	1145.7	1143.7
12.5°	1148.9	1136.3	1140.9	1136.0	1134.0
15°	1130.6	1118.8	1123.6	1119.5	1117.5
17.5°	1110.5	1097.9	1102.6	1097.9	1095.4
20°	1094.4	1082.5	1087.3	1080.2	1079.3
22.5°	1076.6	1064.8	1069.6	1060.1	1059.9
25°	1048.0	1035.2	1041.0	1029.9	1028.9
27.5°	1014.0	1002.2	1007.0	995.7	994.5
30°	990.7	978.8	983.6	971.5	969.5
32.5°	964.1	953.1	957.0	944.9	943.7
35°	923.2	912.4	915.2	903.0	902.1
37.5°	876.7	866.8	868.4	855.1	854.1
40°	843.7	833.8	834.6	820.5	819.5
42.5°	807.4	797.6	796.8	782.6	781.7
45°	747.0	737.2	733.9	720.8	718.8
47.5°	678.2	668.3	662.3	651.5	650.2
50°	628.2	618.4	613.1	604.0	601.0
52.5°	574.3	564.4	560.0	551.6	548.7
55°	489.3	481.4	478.2	470.1	468.1
57.5°	408.5	403.2	402.3	394.4	393.6
60°	359.4	356.5	356.4	349.3	349.3
62.5°	317.5	315.4	316.9	312.3	311.5
65°	262.8	260.8	263.8	261.8	261.8
67.5°	219.5	219.5	221.3	220.5	220.5
70°	195.3	195.3	196.3	196.3	196.3
72.5°	173.6	172.8	175.4	175.4	174.6
75°	142.0	142.0	142.0	143.0	143.0
77.5°	110.5	110.7	111.5	111.3	110.5
80°	89.6	90.6	90.6	89.6	89.6
82.5°	68.7	69.6	69.7	69.4	68.7
85°	36.2	38.2	40.3	40.3	40.3
87.5°	10.6	14.2	17.2	17.4	16.7
90°	0.8	3.0	5.3	6.8	6.8
92.5°	6.8	30.9	53.6	23.0	19.5
95°	16.6	61.7	196.4	85.5	57.4
97.5°	27.5	68.1	301.1	234.2	164.5
100°	34.7	72.4	333.1	337.7	272.7
102.5°	42.0	76.7	341.6	417.6	360.3
105°	54.4	84.7	336.9	512.9	482.7
107.5°	67.2	94.0	317.4	562.2	570.6
110°	76.3	100.7	302.9	571.8	608.0

TEST NUMBER:

CATALOG NUMBER: SQ4-PR1-050U-100D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	84.1	107.3	288.4	563.8	618.3
115°	96.7	117.4	269.7	536.5	611.1
117.5°	108.5	128.3	257.7	497.7	581.8
120°	116.3	135.5	252.3	471.7	555.2
122.5°	123.0	142.2	248.7	445.7	526.2
125°	132.9	151.4	244.0	411.1	484.9
127.5°	141.9	160.2	241.4	384.8	448.2
130°	147.3	165.0	240.2	368.4	425.2
132.5°	152.7	170.5	239.0	354.3	404.7
135°	160.1	177.9	237.2	334.8	377.7
137.5°	168.1	184.2	236.3	317.6	353.6
140°	173.0	188.5	235.7	306.6	339.1
142.5°	177.8	192.1	235.1	298.1	325.2
145°	185.1	198.3	234.2	284.5	305.9
147.5°	193.2	204.6	233.4	273.8	290.6
150°	198.7	208.3	233.4	267.7	281.0
152.5°	202.9	211.3	232.8	262.2	273.1
155°	209.2	216.6	232.6	255.5	262.9
157.5°	215.4	221.2	232.6	250.9	256.5
160°	219.0	224.2	232.6	247.8	252.3
162.5°	222.7	226.7	233.2	245.4	248.7
165°	226.6	229.6	233.4	243.2	244.0
167.5°	230.7	232.2	234.2	240.7	241.3
170°	231.9	233.4	234.2	239.4	239.4
172.5°	233.1	234.0	234.2	238.2	238.2
175°	234.9	235.6	234.2	237.2	236.4
177.5°	235.5	235.5	233.7	236.1	234.9
180°	234.9	234.9	234.9	234.9	234.9

(END OF REPORT)