

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-F-075U-125D-927-1D-UNV-STD-W-4

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number:
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G3-1910-536-20)
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-F-075U-125D-927-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6175.0 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-F-075U-125D-927-1D-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-F-075U-125D-927-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	53	50	48
3	83	74	66	60	78	69	63	57	61	56	52	54	49	46	47	43	41
4	76	65	57	51	71	61	54	48	54	48	44	48	43	39	41	38	35
5	70	58	50	44	65	55	47	42	49	42	38	43	38	34	37	34	30
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24
8	55	43	35	29	52	41	33	28	36	30	26	32	27	24	28	24	21
9	52	39	31	26	48	37	30	25	33	27	23	30	25	21	26	22	19
10	48	36	28	24	45	34	27	23	31	25	21	27	23	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13084	13084	13084
5°	13126	12960	13069
10°	13066	12905	13007
15°	12979	12822	12926
20°	12858	12713	12812
25°	12712	12577	12680
30°	12555	12446	12514
35°	12377	12271	12280
40°	12173	12042	12079
45°	11945	11812	11833
50°	11684	11549	11516
55°	11387	11223	11199
60°	11016	10773	10715
65°	10444	10223	10086
70°	9727	9474	9347
75°	8652	8459	8206
80°	7051	6843	6801
85°	4213	4795	4795

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11945 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-F-075U-125D-927-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.8	2.2
10°-20°	381.1	6.2
20°-30°	572.5	9.3
30°-40°	683.1	11.1
40°-50°	700.2	11.3
50°-60°	624.1	10.1
60°-70°	464.6	7.5
70°-80°	251.7	4.1
80°-90°	58.7	1.0
90°-100°	166.9	2.7
100°-110°	459.2	7.4
110°-120°	473.9	7.7
120°-130°	379.7	6.1
130°-140°	298.2	4.8
140°-150°	228.6	3.7
150°-160°	164.3	2.7
160°-170°	100.5	1.6
170°-180°	33.9	0.5
0°-30°	1087.4	17.6
0°-40°	1770.5	28.7
0°-60°	3094.8	50.1
0°-90°	3869.8	62.7
90°-120°	1100.0	17.8
90°-150°	2006.5	32.5
90°-180°	2305.0	37.3
0°-180°	6175.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1418	1418	1418	1418	1418	
5°	1417	1415	1399	1412	1411	134
15°	1359	1356	1342	1354	1353	383
25°	1249	1246	1236	1243	1246	575
35°	1099	1098	1090	1090	1090	687
45°	916	913	905	904	907	705
55°	708	706	698	692	696	632
65°	478	475	468	465	462	474
75°	243	243	237	232	230	258
85°	40	45	45	46	45	55
90°	1	3	5	7	7	3
95°	25	91	295	126	81	26
105°	82	126	506	770	719	87
115°	145	177	406	808	917	143
125°	200	228	368	623	730	179
135°	242	268	358	504	570	186
145°	279	298	352	429	462	175
155°	316	326	350	386	397	145
165°	342	346	352	366	368	96
175°	354	355	352	357	356	34
180°	354	354	354	354	354	

TEST NUMBER:

CATALOG NUMBER: SQ4-F-075U-125D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1418.1	1418.1	1418.1	1418.1	1418.1
2.5°	1422.5	1420.0	1407.5	1418.0	1416.2
5°	1417.3	1415.0	1399.4	1411.8	1411.1
7.5°	1405.3	1402.4	1388.1	1399.8	1398.4
10°	1394.7	1392.4	1377.5	1389.2	1388.4
12.5°	1381.6	1379.3	1364.4	1376.1	1375.9
15°	1358.8	1355.7	1342.4	1354.1	1353.3
17.5°	1331.5	1327.9	1314.8	1324.0	1325.5
20°	1309.6	1307.3	1294.8	1303.4	1304.9
22.5°	1287.1	1284.2	1271.0	1280.9	1282.4
25°	1248.7	1246.4	1235.5	1242.6	1245.6
27.5°	1206.6	1206.6	1196.4	1201.5	1203.3
30°	1178.5	1178.5	1168.3	1171.5	1174.6
32.5°	1148.5	1146.1	1136.5	1139.1	1142.1
35°	1098.9	1098.1	1089.5	1089.5	1090.3
37.5°	1047.5	1045.4	1036.0	1036.7	1040.3
40°	1010.7	1009.2	999.8	999.8	1002.9
42.5°	973.2	971.7	963.5	962.3	963.5
45°	915.5	913.2	905.3	903.8	906.9
47.5°	854.0	854.6	845.2	843.1	844.8
50°	814.0	814.0	804.6	800.0	802.3
52.5°	772.2	771.0	761.6	756.4	761.7
55°	707.9	705.6	697.7	692.3	696.2
57.5°	642.0	638.5	630.6	624.7	626.9
60°	597.0	591.7	583.8	579.1	580.7
62.5°	550.2	547.3	538.8	531.7	535.1
65°	478.4	475.4	468.3	465.1	462.0
67.5°	408.0	406.0	398.0	394.7	392.7
70°	360.6	356.8	351.2	347.3	346.5
72.5°	314.4	309.9	304.4	301.1	299.1
75°	242.7	242.7	237.3	232.5	230.2
77.5°	174.5	175.1	170.6	169.0	168.0
80°	132.7	132.7	128.8	127.2	128.0
82.5°	92.7	94.5	93.2	91.0	89.9
85°	39.8	45.1	45.3	46.0	45.3
87.5°	7.0	11.7	12.9	11.9	10.7
90°	0.8	3.0	5.3	6.8	6.8
92.5°	10.4	44.4	76.9	29.5	24.2
95°	24.8	91.1	295.1	126.2	80.6
97.5°	40.5	101.0	450.4	347.0	244.8
100°	51.9	107.2	499.2	503.8	411.1
102.5°	62.8	114.5	511.8	625.1	540.0
105°	82.1	126.2	505.9	770.5	719.0
107.5°	100.4	140.8	477.2	841.8	857.1
110°	113.7	150.5	455.5	859.5	912.5

TEST NUMBER:

CATALOG NUMBER: SQ4-F-075U-125D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	125.7	161.4	433.8	848.1	928.8
115°	145.3	177.0	405.8	808.1	917.0
117.5°	164.0	193.1	388.0	751.9	875.1
120°	175.4	203.4	380.2	709.8	837.2
122.5°	185.7	213.6	374.8	673.0	793.8
125°	200.3	228.2	368.2	622.8	729.5
127.5°	214.1	240.8	363.8	580.9	674.6
130°	221.3	248.6	361.4	556.1	641.5
132.5°	229.8	257.0	359.6	534.2	611.3
135°	241.7	268.2	357.6	503.7	569.9
137.5°	252.8	277.4	356.0	479.0	533.6
140°	261.2	284.1	355.4	462.6	512.0
142.5°	268.5	289.5	354.2	448.0	490.3
145°	279.3	298.5	352.3	429.1	462.3
147.5°	290.9	307.4	351.4	412.4	438.9
150°	298.1	312.9	350.8	403.3	423.9
152.5°	304.8	318.3	350.2	395.3	412.4
155°	316.2	326.5	350.1	385.7	396.8
157.5°	324.5	332.9	350.1	377.8	385.5
160°	330.5	337.1	350.1	373.6	379.5
162.5°	335.3	340.8	350.7	369.9	374.6
165°	341.8	346.2	351.6	365.9	368.2
167.5°	346.3	349.7	352.3	362.6	363.2
170°	349.3	351.5	352.3	361.4	361.4
172.5°	351.7	352.8	352.3	359.6	359.0
175°	353.9	354.6	352.3	356.8	356.1
177.5°	354.5	354.5	352.0	355.6	354.5
180°	353.9	353.9	353.9	353.9	353.9

(END OF REPORT)