

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-PC3-025U-075D-927-1D-UNV-STD-W-4

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number:
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32)
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-PC3-025U-075D-927-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2977.4 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 29.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-PC3-025U-075D-927-1D-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-PC3-025U-075D-927-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79
1	103	99	95	91	98	94	91	88	86	83	80	78	75	73	70	69	67
2	94	87	80	75	89	83	77	72	75	70	67	68	65	61	62	59	56
3	86	76	68	62	81	73	66	60	66	61	56	60	56	52	55	51	48
4	79	67	59	53	75	64	57	51	59	53	48	54	49	45	49	45	41
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36
6	67	54	46	39	63	52	44	38	48	41	36	44	38	34	40	35	32
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	36	32	28
8	57	45	36	31	55	43	35	30	39	33	28	36	31	27	33	29	25
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	31	26	23
10	50	38	30	25	48	36	29	24	33	27	23	31	26	22	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7549	7549	7549
5°	7605	7556	7529
10°	7588	7552	7530
15°	7548	7548	7540
20°	7498	7520	7520
25°	7427	7481	7458
30°	7336	7425	7394
35°	7228	7338	7287
40°	7108	7208	7135
45°	6979	7028	6919
50°	6796	6796	6687
55°	6581	6495	6397
60°	6263	6137	6039
65°	5790	5674	5624
70°	5069	5109	5088
75°	4078	4509	4538
80°	2896	3825	3863
85°	1768	3208	3208

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 7028 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-PC3-025U-075D-927-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	2.6
10°-20°	222.2	7.5
20°-30°	336.5	11.3
30°-40°	403.4	13.5
40°-50°	411.4	13.8
50°-60°	359.1	12.1
60°-70°	257.1	8.6
70°-80°	132.4	4.4
80°-90°	34.1	1.1
90°-100°	55.9	1.9
100°-110°	147.0	4.9
110°-120°	152.5	5.1
120°-130°	122.3	4.1
130°-140°	95.9	3.2
140°-150°	73.6	2.5
150°-160°	53.0	1.8
160°-170°	32.5	1.1
170°-180°	11.0	0.4
0°-30°	636.2	21.4
0°-40°	1039.6	34.9
0°-60°	1810.0	60.8
0°-90°	2233.6	75.0
90°-120°	355.4	11.9
90°-150°	647.3	21.7
90°-180°	744.0	25.0
0°-180°	2977.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	818	818	818	818	818	
5°	821	813	816	814	813	78
15°	790	784	790	790	789	223
25°	730	724	735	733	733	336
35°	642	640	652	647	647	401
45°	535	533	539	532	530	412
55°	409	404	404	398	398	365
65°	265	259	260	258	258	262
75°	114	120	126	127	127	124
85°	17	26	30	31	30	23
90°	1	2	6	3	3	1
95°	7	29	96	50	34	8
105°	26	40	163	247	230	28
115°	47	57	130	260	296	46
125°	66	73	118	200	236	58
135°	78	86	115	162	183	60
145°	90	96	113	138	149	57
155°	102	105	113	124	128	47
165°	110	112	113	118	119	31
175°	115	115	114	116	116	11
180°	115	115	115	115	115	

TEST NUMBER:

CATALOG NUMBER: SQ4-PC3-025U-075D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	818.2	818.2	818.2	818.2	818.2
2.5°	823.0	815.9	818.2	816.3	813.3
5°	821.2	813.1	815.9	813.6	812.9
7.5°	815.3	807.2	810.9	809.4	808.7
10°	809.9	801.7	806.1	804.5	803.8
12.5°	802.6	795.0	800.0	798.5	798.3
15°	790.2	783.5	790.2	790.1	789.4
17.5°	774.6	768.5	775.6	776.1	775.6
20°	763.7	757.0	765.9	765.2	765.9
22.5°	750.3	744.8	754.4	752.5	753.2
25°	729.6	724.4	734.9	732.6	732.6
27.5°	705.0	701.3	712.7	710.3	710.3
30°	688.6	684.9	697.0	694.0	694.0
32.5°	670.5	667.9	679.4	675.8	675.8
35°	641.7	640.2	651.5	647.0	647.0
37.5°	612.0	610.6	620.9	615.4	613.6
40°	590.2	589.4	598.5	592.4	592.4
42.5°	568.3	567.6	575.5	568.2	568.2
45°	534.9	533.4	538.6	531.8	530.3
47.5°	498.3	496.9	500.2	492.7	492.0
50°	473.5	472.0	473.5	466.7	465.9
52.5°	448.0	445.4	445.6	438.8	438.6
55°	409.1	403.9	403.8	397.7	397.7
57.5°	367.9	361.1	361.7	356.5	355.8
60°	339.4	332.0	332.6	328.0	327.3
62.5°	311.5	302.9	304.7	299.5	299.4
65°	265.2	259.2	259.9	257.6	257.6
67.5°	220.6	215.1	219.1	217.3	217.1
70°	187.9	184.2	189.4	189.4	188.6
72.5°	157.6	157.4	163.9	164.0	164.4
75°	114.4	119.6	126.5	127.3	127.3
77.5°	76.4	85.6	93.2	93.5	93.3
80°	54.5	64.9	72.0	73.5	72.7
82.5°	37.0	47.9	53.8	55.3	54.5
85°	16.7	25.6	30.3	31.0	30.3
87.5°	5.0	10.6	13.3	12.7	11.5
90°	0.7	2.2	5.9	2.9	2.9
92.5°	3.1	14.9	33.0	14.6	9.4
95°	7.4	28.9	96.4	49.7	33.8
97.5°	12.8	31.8	144.2	114.7	84.4
100°	16.9	34.2	158.9	161.0	125.0
102.5°	20.4	36.6	163.0	200.6	169.8
105°	26.5	40.1	162.6	246.8	230.2
107.5°	32.7	45.3	153.3	270.8	274.8
110°	36.8	48.3	145.6	277.0	294.2

TEST NUMBER:

CATALOG NUMBER: SQ4-PC3-025U-075D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	40.9	51.8	138.6	273.1	299.5
115°	47.1	57.1	130.2	259.8	296.4
117.5°	53.1	62.3	124.5	241.3	282.0
120°	56.6	65.3	122.1	228.9	268.5
122.5°	60.2	68.8	120.3	216.6	255.5
125°	65.5	73.4	118.4	200.2	236.1
127.5°	69.7	77.8	116.8	186.9	217.3
130°	72.1	80.7	116.2	178.6	206.7
132.5°	74.4	83.1	115.6	171.5	196.7
135°	78.0	85.9	114.7	161.6	183.2
137.5°	81.6	89.4	114.6	154.1	171.8
140°	84.6	91.8	114.0	148.2	164.8
142.5°	86.9	93.6	114.0	144.1	158.3
145°	90.5	96.2	113.3	137.8	148.6
147.5°	94.0	99.6	113.3	132.6	141.5
150°	96.4	101.4	113.3	129.6	136.8
152.5°	98.7	102.6	113.3	127.2	132.7
155°	102.2	105.1	113.3	124.4	128.0
157.5°	104.9	107.6	113.3	121.9	124.5
160°	106.7	108.8	113.3	120.7	122.1
162.5°	108.4	110.0	113.3	119.5	120.9
165°	110.3	111.8	113.3	117.7	119.2
167.5°	112.1	112.8	114.0	117.0	117.5
170°	113.3	114.0	114.0	117.0	117.0
172.5°	113.9	114.0	114.0	116.4	115.8
175°	114.7	114.7	114.0	115.5	115.5
177.5°	114.7	114.7	114.2	115.3	114.7
180°	114.7	114.7	114.7	114.7	114.7

(END OF REPORT)