

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-PP3-125U-075D-927-1D-UNV-STD-W-4

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number:
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-075D-927-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6063.2 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-125U-075D-927-1D-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-125U-075D-927-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37		
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31		
2	87	79	73	68	78	72	67	63	59	55	52	46	44	41	34	33	32	26		
3	79	70	63	57	71	64	57	53	52	47	44	41	38	35	31	29	27	22		
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19		
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17		
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15		
7	56	44	37	31	51	41	34	29	33	28	24	27	23	20	20	18	16	13		
8	52	40	33	27	47	37	30	26	30	25	22	24	21	18	19	16	14	12		
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13	11		
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	13	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7975	7975	7975
5°	8033	7984	7957
10°	8020	7963	7928
15°	7967	7924	7880
20°	7915	7869	7810
25°	7820	7766	7689
30°	7676	7635	7538
35°	7474	7424	7330
40°	7236	7190	7108
45°	7038	6988	6919
50°	6785	6742	6677
55°	6434	6349	6301
60°	5857	5689	5661
65°	5161	4945	4929
70°	4456	4270	4270
75°	3836	3782	3725
80°	3379	3422	3342
85°	2646	2890	2890

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7038 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-125U-075D-927-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.7	1.3
10°-20°	233.4	3.8
20°-30°	349.6	5.8
30°-40°	410.0	6.8
40°-50°	411.3	6.8
50°-60°	350.9	5.8
60°-70°	228.8	3.8
70°-80°	114.8	1.9
80°-90°	33.2	0.5
90°-100°	278.9	4.6
100°-110°	751.4	12.4
110°-120°	788.6	13.0
120°-130°	639.9	10.6
130°-140°	501.9	8.3
140°-150°	385.3	6.4
150°-160°	277.0	4.6
160°-170°	169.3	2.8
170°-180°	57.1	0.9
0°-30°	664.7	11.0
0°-40°	1074.7	17.7
0°-60°	1837.0	30.3
0°-90°	2213.8	36.5
90°-120°	1819.0	30.0
90°-150°	3346.1	55.2
90°-180°	3849.0	63.5
0°-180°	6063.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	864	864	864	864	864	
5°	867	859	862	859	859	82
15°	834	826	830	826	825	235
25°	768	759	763	756	755	353
35°	664	657	659	652	651	415
45°	539	536	536	530	530	415
55°	400	398	395	392	392	355
65°	236	232	226	225	226	236
75°	108	108	106	105	104	117
85°	25	27	27	27	27	29
90°	2	4	9	10	10	4
95°	42	152	457	234	162	44
105°	139	216	831	1243	1167	146
115°	245	300	692	1337	1512	241
125°	335	385	621	1050	1236	299
135°	403	450	604	847	959	311
145°	466	503	596	724	778	293
155°	530	549	591	650	671	244
165°	574	581	593	617	620	162
175°	597	596	594	602	601	57
180°	596	596	596	596	596	

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-125U-075D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	864.4	864.4	864.4	864.4	864.4
2.5°	869.9	862.7	864.4	863.1	859.6
5°	867.4	859.3	862.1	859.1	859.1
7.5°	861.5	852.6	855.5	852.4	852.3
10°	856.1	847.2	850.0	847.0	846.2
12.5°	848.2	839.3	842.7	839.1	838.9
15°	834.1	825.9	829.6	826.5	825.0
17.5°	818.2	809.3	813.6	809.4	808.8
20°	806.1	797.2	801.5	795.5	795.5
22.5°	791.5	782.6	787.6	779.7	779.7
25°	768.2	759.3	762.9	756.0	755.3
27.5°	740.5	731.7	735.5	727.7	727.6
30°	720.5	712.3	716.7	708.3	707.6
32.5°	698.6	691.1	694.2	685.9	685.2
35°	663.6	657.0	659.1	651.5	650.8
37.5°	626.8	620.0	622.4	615.9	615.6
40°	600.8	596.3	597.0	591.6	590.2
42.5°	576.5	571.5	572.1	566.8	566.5
45°	539.4	535.7	535.6	530.3	530.3
47.5°	500.0	497.2	496.4	492.0	491.8
50°	472.7	470.5	469.7	465.9	465.2
52.5°	444.2	443.2	440.6	437.4	437.3
55°	400.0	398.5	394.7	392.4	391.7
57.5°	352.0	349.0	344.7	341.4	342.0
60°	317.4	314.5	308.3	306.8	306.8
62.5°	284.1	280.5	274.4	272.3	273.5
65°	236.4	231.9	226.5	225.0	225.8
67.5°	193.0	189.0	183.2	183.2	182.6
70°	165.2	162.9	158.3	158.3	158.3
72.5°	140.3	139.3	135.9	135.9	135.3
75°	107.6	107.6	106.1	105.3	104.5
77.5°	80.6	80.9	80.2	79.4	78.0
80°	63.6	65.1	64.4	63.6	62.9
82.5°	47.9	49.4	49.2	47.9	47.7
85°	25.0	27.2	27.3	27.3	27.3
87.5°	7.0	9.9	11.5	11.7	12.3
90°	1.5	4.5	9.1	9.9	9.9
92.5°	18.5	65.5	129.4	62.3	43.3
95°	42.5	151.7	457.3	233.8	161.8
97.5°	67.9	173.7	717.2	599.2	451.8
100°	87.4	182.4	799.9	836.9	694.3
102.5°	106.2	194.7	827.2	1014.9	897.9
105°	139.0	216.3	831.0	1243.3	1166.8
107.5°	170.0	238.9	795.6	1360.6	1380.4
110°	190.7	256.0	763.4	1397.1	1469.1

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-125U-075D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	212.5	273.1	732.4	1389.0	1507.4
115°	245.4	300.3	692.0	1337.1	1512.4
117.5°	275.3	326.8	660.7	1254.3	1449.5
120°	294.7	344.5	644.9	1194.9	1395.4
122.5°	311.7	360.9	633.4	1134.1	1334.0
125°	335.0	384.8	621.4	1050.2	1235.9
127.5°	357.3	406.3	613.8	976.2	1142.0
130°	370.7	419.7	610.7	933.8	1079.4
132.5°	384.1	432.5	607.7	896.5	1030.2
135°	403.4	450.2	603.9	847.2	959.4
137.5°	421.7	466.6	601.9	805.5	897.6
140°	434.5	477.6	600.1	779.7	862.9
142.5°	447.9	488.0	598.9	755.7	825.9
145°	466.4	502.8	596.3	724.4	777.8
147.5°	486.5	518.1	593.7	698.0	740.0
150°	499.8	527.3	592.5	681.4	716.3
152.5°	512.0	535.9	591.9	667.9	696.3
155°	529.5	548.8	591.0	649.9	670.7
157.5°	544.8	559.8	591.1	637.3	651.3
160°	554.5	567.1	591.7	630.0	640.4
162.5°	563.0	573.3	592.4	623.8	631.2
165°	574.3	581.0	593.3	616.9	619.8
167.5°	583.4	587.2	594.0	611.5	612.7
170°	589.5	590.9	594.0	608.5	608.5
172.5°	593.1	593.4	594.6	605.4	605.4
175°	597.1	596.3	594.0	602.3	600.9
177.5°	598.7	597.5	594.5	599.3	598.1
180°	596.3	596.3	596.3	596.3	596.3

(END OF REPORT)