

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-PP3-125U-125D-927-1D-UNV-STD-W-4

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number:
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-125D-927-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7602.1 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-125U-125D-927-1D-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-125U-125D-927-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13523	13523	13523
5°	13622	13538	13491
10°	13598	13503	13442
15°	13509	13435	13362
20°	13420	13344	13243
25°	13259	13168	13038
30°	13014	12946	12782
35°	12674	12588	12428
40°	12268	12191	12052
45°	11934	11850	11733
50°	11506	11431	11321
55°	10909	10764	10682
60°	9931	9647	9599
65°	8750	8385	8357
70°	7553	7243	7243
75°	6502	6409	6320
80°	5733	5802	5664
85°	4488	4891	4891

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11934 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-125U-125D-927-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.6	1.8
10°-20°	395.7	5.2
20°-30°	592.7	7.8
30°-40°	695.3	9.1
40°-50°	697.4	9.2
50°-60°	595.0	7.8
60°-70°	388.0	5.1
70°-80°	194.7	2.6
80°-90°	55.3	0.7
90°-100°	278.9	3.7
100°-110°	751.4	9.9
110°-120°	788.6	10.4
120°-130°	639.9	8.4
130°-140°	501.9	6.6
140°-150°	385.3	5.1
150°-160°	277.0	3.6
160°-170°	169.3	2.2
170°-180°	57.1	0.8
0°-30°	1127.1	14.8
0°-40°	1822.3	24.0
0°-60°	3114.7	41.0
0°-90°	3752.7	49.4
90°-120°	1819.0	23.9
90°-150°	3346.1	44.0
90°-180°	3849.0	50.6
0°-180°	7602.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1466	1466	1466	1466	1466	
5°	1471	1457	1462	1457	1457	140
15°	1414	1400	1407	1401	1399	399
25°	1302	1288	1294	1282	1281	599
35°	1125	1114	1118	1105	1103	703
45°	915	908	908	899	899	704
55°	678	676	669	665	664	603
65°	401	393	384	382	383	400
75°	182	182	180	178	177	198
85°	42	46	46	46	46	50
90°	2	4	9	10	10	5
95°	42	152	457	234	162	44
105°	139	216	831	1243	1167	146
115°	245	300	692	1337	1512	241
125°	335	385	621	1050	1236	299
135°	403	450	604	847	959	311
145°	466	503	596	724	778	293
155°	530	549	591	650	671	244
165°	574	581	593	617	620	162
175°	597	596	594	602	601	57
180°	596	596	596	596	596	

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-125U-125D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1465.7	1465.7	1465.7	1465.7	1465.7
2.5°	1474.9	1462.9	1465.7	1463.5	1457.4
5°	1470.8	1457.0	1461.8	1456.7	1456.7
7.5°	1460.8	1445.7	1450.5	1445.4	1445.1
10°	1451.5	1436.5	1441.3	1436.1	1434.8
12.5°	1438.2	1423.1	1428.9	1422.8	1422.5
15°	1414.3	1400.5	1406.6	1401.4	1398.9
17.5°	1387.3	1372.2	1379.6	1372.4	1371.4
20°	1366.8	1351.7	1359.1	1348.8	1348.8
22.5°	1342.1	1327.0	1335.4	1322.1	1322.1
25°	1302.5	1287.5	1293.5	1281.9	1280.7
27.5°	1255.5	1240.7	1247.0	1233.9	1233.7
30°	1221.6	1207.8	1215.2	1201.0	1199.8
32.5°	1184.6	1171.8	1177.2	1163.0	1161.7
35°	1125.3	1114.0	1117.6	1104.7	1103.4
37.5°	1062.8	1051.3	1055.4	1044.3	1043.8
40°	1018.6	1011.1	1012.2	1003.2	1000.7
42.5°	977.5	969.0	970.1	961.1	960.6
45°	914.6	908.3	908.2	899.2	899.2
47.5°	847.8	843.0	841.6	834.2	833.9
50°	801.6	797.8	796.4	790.0	788.7
52.5°	753.3	751.5	747.1	741.7	741.4
55°	678.2	675.7	669.2	665.4	664.1
57.5°	596.8	591.8	584.5	578.8	579.8
60°	538.2	533.2	522.8	520.2	520.2
62.5°	481.7	475.7	465.3	461.7	463.7
65°	400.8	393.2	384.1	381.5	382.8
67.5°	327.3	320.5	310.6	310.6	309.6
70°	280.0	276.3	268.5	268.5	268.5
72.5°	237.9	236.1	230.4	230.4	229.4
75°	182.4	182.4	179.8	178.5	177.3
77.5°	136.7	137.2	135.9	134.6	132.3
80°	107.9	110.4	109.2	107.9	106.6
82.5°	81.2	83.7	83.5	81.2	80.9
85°	42.4	46.2	46.2	46.2	46.2
87.5°	11.6	16.2	18.3	18.4	19.4
90°	1.5	4.5	9.1	9.9	9.9
92.5°	18.5	65.5	129.4	62.3	43.3
95°	42.5	151.7	457.3	233.8	161.8
97.5°	67.9	173.7	717.2	599.2	451.8
100°	87.4	182.4	799.9	836.9	694.3
102.5°	106.2	194.7	827.2	1014.9	897.9
105°	139.0	216.3	831.0	1243.3	1166.8
107.5°	170.0	238.9	795.6	1360.6	1380.4
110°	190.7	256.0	763.4	1397.1	1469.1

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-125U-125D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	212.5	273.1	732.4	1389.0	1507.4
115°	245.4	300.3	692.0	1337.1	1512.4
117.5°	275.3	326.8	660.7	1254.3	1449.5
120°	294.7	344.5	644.9	1194.9	1395.4
122.5°	311.7	360.9	633.4	1134.1	1334.0
125°	335.0	384.8	621.4	1050.2	1235.9
127.5°	357.3	406.3	613.8	976.2	1142.0
130°	370.7	419.7	610.7	933.8	1079.4
132.5°	384.1	432.5	607.7	896.5	1030.2
135°	403.4	450.2	603.9	847.2	959.4
137.5°	421.7	466.6	601.9	805.5	897.6
140°	434.5	477.6	600.1	779.7	862.9
142.5°	447.9	488.0	598.9	755.7	825.9
145°	466.4	502.8	596.3	724.4	777.8
147.5°	486.5	518.1	593.7	698.0	740.0
150°	499.8	527.3	592.5	681.4	716.3
152.5°	512.0	535.9	591.9	667.9	696.3
155°	529.5	548.8	591.0	649.9	670.7
157.5°	544.8	559.8	591.1	637.3	651.3
160°	554.5	567.1	591.7	630.0	640.4
162.5°	563.0	573.3	592.4	623.8	631.2
165°	574.3	581.0	593.3	616.9	619.8
167.5°	583.4	587.2	594.0	611.5	612.7
170°	589.5	590.9	594.0	608.5	608.5
172.5°	593.1	593.4	594.6	605.4	605.4
175°	597.1	596.3	594.0	602.3	600.9
177.5°	598.7	597.5	594.5	599.3	598.1
180°	596.3	596.3	596.3	596.3	596.3

(END OF REPORT)