

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-F-150U-075D-927-1D-UNV-STD-W-6

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number: REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G3-1910-536-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-F-150U-075D-927-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8671.2 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 97.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-F-150U-075D-927-1D-UNV-STD-W-6

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-F-150U-075D-927-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	88	88	88	88	67	67	67	47	47	47	28	28	28
1	91	87	83	80	80	77	74	71	58	56	54	41	40	39	25	24	24
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20
3	75	66	60	54	66	59	53	48	45	41	38	32	29	27	19	18	17
4	69	59	51	45	61	52	46	41	40	35	32	28	25	23	17	16	15
5	63	52	44	39	55	46	40	35	35	31	27	25	22	20	15	14	13
6	58	46	39	33	51	41	35	30	32	27	24	22	19	17	14	12	11
7	53	42	34	29	47	37	31	26	28	24	21	20	17	15	13	11	10
8	49	38	30	25	43	34	27	23	26	21	18	18	15	13	12	10	9
9	46	34	27	22	40	31	24	20	24	19	16	17	14	12	11	9	8
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	8	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3856	3856	3856
5°	3871	3821	3849
10°	3855	3805	3834
15°	3825	3778	3810
20°	3791	3746	3775
25°	3749	3710	3737
30°	3701	3661	3681
35°	3653	3615	3631
40°	3592	3555	3551
45°	3530	3486	3495
50°	3431	3405	3405
55°	3352	3309	3279
60°	3244	3189	3160
65°	3068	3011	2969
70°	2883	2811	2739
75°	2593	2498	2445
80°	2072	2033	2012
85°	1242	1404	1447

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3530 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-F-150U-075D-927-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.2	0.7
10°-20°	168.4	1.9
20°-30°	253.1	2.9
30°-40°	302.0	3.5
40°-50°	309.7	3.6
50°-60°	276.0	3.2
60°-70°	205.8	2.4
70°-80°	111.6	1.3
80°-90°	27.9	0.3
90°-100°	501.5	5.8
100°-110°	1356.0	15.6
110°-120°	1425.6	16.4
120°-130°	1158.0	13.4
130°-140°	908.4	10.5
140°-150°	697.2	8.0
150°-160°	501.4	5.8
160°-170°	306.3	3.5
170°-180°	103.3	1.2
0°-30°	480.7	5.5
0°-40°	782.7	9.0
0°-60°	1368.3	15.8
0°-90°	1713.5	19.8
90°-120°	3283.2	37.9
90°-150°	6046.7	69.7
90°-180°	6958.0	80.2
0°-180°	8671.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	627	627	627	627	627	
5°	627	626	619	624	623	59
15°	601	600	593	598	598	169
25°	552	552	547	550	551	254
35°	486	485	481	481	484	304
45°	406	404	401	401	402	312
55°	313	312	309	306	306	279
65°	211	211	207	205	204	210
75°	109	107	105	103	103	115
85°	18	19	20	20	20	24
90°	2	7	15	16	15	6
95°	78	273	834	432	257	81
105°	252	390	1504	2219	2128	265
115°	444	543	1248	2415	2726	438
125°	608	696	1124	1898	2229	542
135°	728	815	1094	1532	1734	563
145°	847	910	1079	1311	1411	530
155°	956	994	1070	1176	1215	441
165°	1041	1051	1074	1116	1122	293
175°	1080	1079	1076	1090	1087	103
180°	1079	1079	1079	1079	1079	

TEST NUMBER:

CATALOG NUMBER: SQ4-F-150U-075D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	626.9	626.9	626.9	626.9	626.9
2.5°	629.1	627.8	622.3	626.8	626.4
5°	626.9	625.7	618.9	624.0	623.4
7.5°	621.7	620.5	613.8	618.9	618.8
10°	617.2	615.5	609.2	614.3	613.8
12.5°	611.3	609.6	603.3	608.4	607.9
15°	600.7	599.6	593.3	597.9	598.4
17.5°	588.7	586.6	580.9	585.4	585.9
20°	579.1	577.4	572.3	576.3	576.8
22.5°	569.1	567.4	562.3	566.3	566.8
25°	552.4	551.8	546.7	549.6	550.7
27.5°	534.3	532.8	528.6	530.8	531.9
30°	521.1	520.0	515.5	517.2	518.3
32.5°	507.5	506.8	502.7	503.6	505.1
35°	486.5	485.4	481.4	481.4	483.6
37.5°	463.2	462.0	458.6	458.1	459.0
40°	447.3	445.6	442.7	442.2	442.2
42.5°	430.9	429.7	425.9	424.9	426.2
45°	405.8	404.1	400.7	400.7	401.8
47.5°	378.6	377.9	374.0	372.1	372.6
50°	358.6	359.7	355.8	353.5	355.8
52.5°	341.3	340.7	337.1	334.9	335.8
55°	312.6	312.0	308.6	305.8	305.8
57.5°	283.7	282.3	278.7	276.6	278.2
60°	263.7	263.1	259.2	255.2	256.9
62.5°	243.7	242.7	238.7	236.1	237.3
65°	210.8	210.8	206.9	204.6	204.0
67.5°	182.1	179.4	177.2	174.5	173.7
70°	160.3	158.0	156.3	154.0	152.3
72.5°	138.9	137.6	134.9	132.6	132.3
75°	109.1	106.9	105.1	103.4	102.9
77.5°	77.6	77.2	75.6	74.7	75.0
80°	58.5	58.5	57.4	57.4	56.8
82.5°	41.3	41.7	41.5	40.6	40.5
85°	17.6	18.7	19.9	19.9	20.5
87.5°	3.6	6.8	8.0	8.2	8.0
90°	2.3	6.9	15.1	16.2	15.1
92.5°	33.0	120.2	237.2	103.0	74.6
95°	77.8	273.2	834.0	431.6	256.7
97.5°	125.0	313.3	1300.1	1075.9	790.1
100°	160.3	329.5	1445.1	1507.0	1218.5
102.5°	192.8	352.1	1496.2	1833.9	1618.1
105°	252.1	389.5	1504.3	2219.0	2128.1
107.5°	306.9	432.3	1438.6	2459.1	2489.4
110°	349.6	463.2	1380.0	2523.6	2652.0

TEST NUMBER:

CATALOG NUMBER: SQ4-F-150U-075D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	387.7	494.1	1326.1	2510.7	2726.3
115°	443.7	542.6	1247.6	2415.1	2726.3
117.5°	498.6	591.2	1195.8	2269.0	2621.8
120°	532.0	622.9	1165.1	2164.2	2524.2
122.5°	563.6	652.7	1146.5	2051.8	2414.5
125°	607.5	696.1	1124.4	1897.5	2229.1
127.5°	648.0	735.0	1111.4	1771.6	2063.3
130°	670.3	760.0	1105.9	1693.8	1957.3
132.5°	693.5	782.3	1100.3	1623.7	1866.3
135°	728.3	814.7	1094.2	1532.1	1734.3
137.5°	763.4	845.0	1089.1	1457.9	1622.6
140°	787.6	863.7	1087.3	1410.1	1556.6
142.5°	810.8	882.4	1083.6	1366.9	1495.2
145°	846.8	910.4	1079.1	1311.4	1411.4
147.5°	879.6	935.9	1074.0	1261.2	1338.0
150°	903.7	953.7	1072.2	1233.9	1295.2
152.5°	926.0	969.7	1071.2	1208.5	1259.0
155°	956.0	993.5	1069.9	1176.4	1215.1
157.5°	987.1	1013.3	1070.1	1154.1	1179.5
160°	1004.8	1026.4	1071.0	1140.0	1158.1
162.5°	1018.7	1036.7	1071.9	1128.7	1142.3
165°	1040.8	1051.0	1074.5	1116.4	1122.1
167.5°	1055.9	1063.0	1074.7	1105.9	1108.7
170°	1065.2	1068.6	1075.7	1101.2	1101.2
172.5°	1072.6	1073.3	1075.7	1095.6	1094.7
175°	1080.3	1079.2	1075.7	1089.5	1087.3
177.5°	1082.9	1080.1	1075.4	1084.7	1081.9
180°	1079.1	1079.1	1079.1	1079.1	1079.1

(END OF REPORT)