

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-F-150U-125D-927-1D-UNV-STD-W-6

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number:
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G3-1910-536-20)
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-F-150U-125D-927-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9861.6 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 127.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-F-150U-125D-927-1D-UNV-STD-W-6

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-F-150U-125D-927-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20					20				20
RC	80				70				50					30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	28	26	21
3	77	68	61	55	69	61	55	50	48	44	41	37	34	31	26	24	22	17
4	71	60	52	47	63	54	48	43	43	38	35	32	29	27	23	21	19	15
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	17	13
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	15	11
7	55	43	35	30	49	39	32	27	31	26	22	24	20	18	17	15	13	10
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6542	6542	6542
5°	6563	6480	6534
10°	6533	6452	6504
15°	6489	6411	6463
20°	6429	6356	6406
25°	6356	6289	6340
30°	6278	6224	6256
35°	6189	6135	6140
40°	6086	6020	6040
45°	5972	5906	5917
50°	5842	5775	5758
55°	5693	5612	5599
60°	5509	5386	5357
65°	5222	5111	5043
70°	4863	4737	4674
75°	4325	4228	4104
80°	3524	3422	3400
85°	2110	2392	2392

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5972 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-F-150U-125D-927-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.3	1.0
10°-20°	285.8	2.9
20°-30°	429.4	4.4
30°-40°	512.3	5.2
40°-50°	525.2	5.3
50°-60°	468.1	4.7
60°-70°	348.4	3.5
70°-80°	188.8	1.9
80°-90°	45.6	0.5
90°-100°	501.5	5.1
100°-110°	1356.0	13.8
110°-120°	1425.6	14.5
120°-130°	1158.0	11.7
130°-140°	908.4	9.2
140°-150°	697.2	7.1
150°-160°	501.4	5.1
160°-170°	306.3	3.1
170°-180°	103.3	1.0
0°-30°	815.5	8.3
0°-40°	1327.9	13.5
0°-60°	2321.1	23.5
0°-90°	2903.9	29.4
90°-120°	3283.2	33.3
90°-150°	6046.7	61.3
90°-180°	6958.0	70.6
0°-180°	9861.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1064	1064	1064	1064	1064	
5°	1063	1061	1050	1059	1058	101
15°	1019	1017	1007	1016	1015	287
25°	936	935	927	932	934	431
35°	824	824	817	817	818	515
45°	687	685	679	678	680	529
55°	531	529	523	519	522	474
65°	359	356	351	349	346	355
75°	182	182	178	174	173	193
85°	30	34	34	34	34	41
90°	2	7	15	16	15	6
95°	78	273	834	432	257	81
105°	252	390	1504	2219	2128	265
115°	444	543	1248	2415	2726	438
125°	608	696	1124	1898	2229	542
135°	728	815	1094	1532	1734	563
145°	847	910	1079	1311	1411	530
155°	956	994	1070	1176	1215	441
165°	1041	1051	1074	1116	1122	293
175°	1080	1079	1076	1090	1087	103
180°	1079	1079	1079	1079	1079	

TEST NUMBER:

CATALOG NUMBER: SQ4-F-150U-125D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1063.6	1063.6	1063.6	1063.6	1063.6
2.5°	1066.8	1065.0	1055.6	1063.5	1062.2
5°	1063.0	1061.3	1049.5	1058.9	1058.3
7.5°	1054.0	1051.8	1041.1	1049.8	1048.8
10°	1046.0	1044.3	1033.1	1041.9	1041.3
12.5°	1036.2	1034.5	1023.3	1032.1	1032.0
15°	1019.1	1016.8	1006.8	1015.6	1015.0
17.5°	998.6	996.0	986.1	993.0	994.1
20°	982.2	980.5	971.1	977.5	978.7
22.5°	965.3	963.2	953.3	960.7	961.8
25°	936.5	934.8	926.6	931.9	934.2
27.5°	904.9	904.9	897.3	901.1	902.5
30°	883.9	883.9	876.3	878.6	880.9
32.5°	861.4	859.6	852.4	854.3	856.6
35°	824.2	823.6	817.1	817.1	817.7
37.5°	785.6	784.0	777.0	777.5	780.3
40°	758.0	756.9	749.8	749.9	752.2
42.5°	729.9	728.8	722.7	721.7	722.7
45°	686.6	684.9	679.0	677.9	680.2
47.5°	640.5	640.9	633.9	632.3	633.6
50°	610.5	610.5	603.5	600.0	601.7
52.5°	579.1	578.2	571.2	567.3	571.3
55°	530.9	529.2	523.3	519.3	522.1
57.5°	481.5	478.9	473.0	468.5	470.1
60°	447.8	443.8	437.8	434.3	435.5
62.5°	412.7	410.5	404.1	398.8	401.3
65°	358.8	356.5	351.2	348.8	346.5
67.5°	306.0	304.5	298.5	296.0	294.5
70°	270.4	267.6	263.4	260.5	259.9
72.5°	235.8	232.5	228.3	225.8	224.3
75°	182.0	182.0	177.9	174.4	172.7
77.5°	130.9	131.3	128.0	126.8	126.0
80°	99.5	99.5	96.6	95.4	96.0
82.5°	69.5	70.9	69.9	68.2	67.4
85°	29.9	33.9	33.9	34.5	33.9
87.5°	5.6	9.7	11.9	11.2	10.0
90°	2.3	6.9	15.1	16.2	15.1
92.5°	33.0	120.2	237.2	103.0	74.6
95°	77.8	273.2	834.0	431.6	256.7
97.5°	125.0	313.3	1300.1	1075.9	790.1
100°	160.3	329.5	1445.1	1507.0	1218.5
102.5°	192.8	352.1	1496.2	1833.9	1618.1
105°	252.1	389.5	1504.3	2219.0	2128.1
107.5°	306.9	432.3	1438.6	2459.1	2489.4
110°	349.6	463.2	1380.0	2523.6	2652.0

TEST NUMBER:

CATALOG NUMBER: SQ4-F-150U-125D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	387.7	494.1	1326.1	2510.7	2726.3
115°	443.7	542.6	1247.6	2415.1	2726.3
117.5°	498.6	591.2	1195.8	2269.0	2621.8
120°	532.0	622.9	1165.1	2164.2	2524.2
122.5°	563.6	652.7	1146.5	2051.8	2414.5
125°	607.5	696.1	1124.4	1897.5	2229.1
127.5°	648.0	735.0	1111.4	1771.6	2063.3
130°	670.3	760.0	1105.9	1693.8	1957.3
132.5°	693.5	782.3	1100.3	1623.7	1866.3
135°	728.3	814.7	1094.2	1532.1	1734.3
137.5°	763.4	845.0	1089.1	1457.9	1622.6
140°	787.6	863.7	1087.3	1410.1	1556.6
142.5°	810.8	882.4	1083.6	1366.9	1495.2
145°	846.8	910.4	1079.1	1311.4	1411.4
147.5°	879.6	935.9	1074.0	1261.2	1338.0
150°	903.7	953.7	1072.2	1233.9	1295.2
152.5°	926.0	969.7	1071.2	1208.5	1259.0
155°	956.0	993.5	1069.9	1176.4	1215.1
157.5°	987.1	1013.3	1070.1	1154.1	1179.5
160°	1004.8	1026.4	1071.0	1140.0	1158.1
162.5°	1018.7	1036.7	1071.9	1128.7	1142.3
165°	1040.8	1051.0	1074.5	1116.4	1122.1
167.5°	1055.9	1063.0	1074.7	1105.9	1108.7
170°	1065.2	1068.6	1075.7	1101.2	1101.2
172.5°	1072.6	1073.3	1075.7	1095.6	1094.7
175°	1080.3	1079.2	1075.7	1089.5	1087.3
177.5°	1082.9	1080.1	1075.4	1084.7	1081.9
180°	1079.1	1079.1	1079.1	1079.1	1079.1

(END OF REPORT)