

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-PW1-125U-125D-927-1D-UNV-STD-W-4

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number:
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-PW1-125U-125D-927-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7560.3 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-PW1-125U-125D-927-1D-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-PW1-125U-125D-927-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47
2	89	82	76	70	82	75	70	66	64	60	57	53	50	48	43	41	40
3	81	72	65	59	75	66	60	55	56	52	48	47	44	41	38	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29
5	68	57	49	43	63	53	45	40	45	39	35	38	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22
7	58	46	38	32	53	43	36	31	37	31	27	31	27	23	26	22	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	31	25	46	35	29	24	31	25	21	26	22	19	22	18	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13452	13452	13452
5°	13538	13432	13372
10°	13431	13322	13250
15°	13288	13141	13092
20°	13129	12928	12902
25°	12946	12711	12671
30°	12672	12481	12399
35°	12313	12138	12066
40°	11928	11743	11696
45°	11464	11314	11263
50°	10989	10897	10822
55°	10476	10476	10311
60°	9837	10027	9671
65°	9001	9451	8778
70°	7936	8697	7729
75°	6777	7785	6595
80°	5255	6551	5324
85°	3398	5028	4488

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11464 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-PW1-125U-125D-927-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.3	1.8
10°-20°	387.6	5.1
20°-30°	575.0	7.6
30°-40°	672.8	8.9
40°-50°	669.8	8.9
50°-60°	578.4	7.7
60°-70°	416.3	5.5
70°-80°	218.3	2.9
80°-90°	55.5	0.7
90°-100°	278.9	3.7
100°-110°	751.4	9.9
110°-120°	788.6	10.4
120°-130°	639.9	8.5
130°-140°	501.9	6.6
140°-150°	385.3	5.1
150°-160°	277.0	3.7
160°-170°	169.3	2.2
170°-180°	57.1	0.8
0°-30°	1099.9	14.5
0°-40°	1772.6	23.4
0°-60°	3020.7	40.0
0°-90°	3710.9	49.1
90°-120°	1819.0	24.1
90°-150°	3346.1	44.3
90°-180°	3849.0	50.9
0°-180°	7560.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1458	1458	1458	1458	1458	
5°	1462	1446	1450	1446	1444	138
15°	1391	1374	1376	1373	1371	392
25°	1272	1250	1249	1241	1245	585
35°	1093	1078	1078	1068	1071	683
45°	879	871	867	864	863	678
55°	651	650	651	642	641	581
65°	412	425	433	416	402	409
75°	190	208	218	204	185	204
85°	32	42	48	45	42	42
90°	2	4	9	10	10	4
95°	42	152	457	234	162	44
105°	139	216	831	1243	1167	146
115°	245	300	692	1337	1512	241
125°	335	385	621	1050	1236	299
135°	403	450	604	847	959	311
145°	466	503	596	724	778	293
155°	530	549	591	650	671	244
165°	574	581	593	617	620	162
175°	597	596	594	602	601	57
180°	596	596	596	596	596	

TEST NUMBER:

CATALOG NUMBER: SQ4-PW1-125U-125D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1458.0	1458.0	1458.0	1458.0	1458.0
2.5°	1466.2	1454.1	1458.0	1454.7	1447.7
5°	1461.8	1445.5	1450.3	1446.4	1443.8
7.5°	1446.9	1431.9	1435.4	1431.2	1429.7
10°	1433.6	1418.5	1422.0	1416.8	1414.3
12.5°	1418.2	1402.1	1405.6	1400.4	1398.9
15°	1391.2	1373.6	1375.8	1373.1	1370.6
17.5°	1359.8	1342.0	1342.4	1338.2	1337.7
20°	1337.2	1318.4	1316.7	1311.6	1314.1
22.5°	1312.6	1292.7	1291.0	1283.9	1287.4
25°	1271.7	1250.4	1248.6	1241.0	1244.7
27.5°	1224.4	1203.3	1203.4	1192.7	1196.7
30°	1189.5	1169.4	1171.5	1158.8	1163.8
32.5°	1152.5	1134.4	1135.6	1122.8	1127.8
35°	1093.2	1078.1	1077.7	1067.6	1071.3
37.5°	1032.5	1019.2	1017.1	1011.2	1012.2
40°	990.4	979.1	975.0	971.1	971.1
42.5°	946.2	935.9	931.8	929.0	928.0
45°	878.6	871.1	867.1	864.5	863.2
47.5°	811.8	804.8	801.3	799.5	798.2
50°	765.6	760.6	759.2	755.3	754.0
52.5°	719.4	716.3	715.0	710.1	708.8
55°	651.3	650.0	651.3	642.3	641.0
57.5°	580.4	582.4	586.5	574.4	571.4
60°	533.1	538.1	543.4	529.1	524.1
62.5°	484.8	492.8	500.2	483.9	476.8
65°	412.3	424.9	432.9	415.9	402.1
67.5°	342.5	358.0	367.6	349.3	333.7
70°	294.2	311.7	322.4	304.0	286.5
72.5°	252.0	271.6	280.3	262.9	245.4
75°	190.1	207.7	218.4	203.8	185.0
77.5°	134.9	151.5	160.3	147.6	132.1
80°	98.9	116.5	123.3	112.8	100.2
82.5°	70.1	84.7	89.4	83.0	74.5
85°	32.1	42.2	47.5	44.9	42.4
87.5°	8.5	16.2	21.3	21.5	22.5
90°	1.5	4.5	9.1	9.9	9.9
92.5°	18.5	65.5	129.4	62.3	43.3
95°	42.5	151.7	457.3	233.8	161.8
97.5°	67.9	173.7	717.2	599.2	451.8
100°	87.4	182.4	799.9	836.9	694.3
102.5°	106.2	194.7	827.2	1014.9	897.9
105°	139.0	216.3	831.0	1243.3	1166.8
107.5°	170.0	238.9	795.6	1360.6	1380.4
110°	190.7	256.0	763.4	1397.1	1469.1

TEST NUMBER:

CATALOG NUMBER: SQ4-PW1-125U-125D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	212.5	273.1	732.4	1389.0	1507.4
115°	245.4	300.3	692.0	1337.1	1512.4
117.5°	275.3	326.8	660.7	1254.3	1449.5
120°	294.7	344.5	644.9	1194.9	1395.4
122.5°	311.7	360.9	633.4	1134.1	1334.0
125°	335.0	384.8	621.4	1050.2	1235.9
127.5°	357.3	406.3	613.8	976.2	1142.0
130°	370.7	419.7	610.7	933.8	1079.4
132.5°	384.1	432.5	607.7	896.5	1030.2
135°	403.4	450.2	603.9	847.2	959.4
137.5°	421.7	466.6	601.9	805.5	897.6
140°	434.5	477.6	600.1	779.7	862.9
142.5°	447.9	488.0	598.9	755.7	825.9
145°	466.4	502.8	596.3	724.4	777.8
147.5°	486.5	518.1	593.7	698.0	740.0
150°	499.8	527.3	592.5	681.4	716.3
152.5°	512.0	535.9	591.9	667.9	696.3
155°	529.5	548.8	591.0	649.9	670.7
157.5°	544.8	559.8	591.1	637.3	651.3
160°	554.5	567.1	591.7	630.0	640.4
162.5°	563.0	573.3	592.4	623.8	631.2
165°	574.3	581.0	593.3	616.9	619.8
167.5°	583.4	587.2	594.0	611.5	612.7
170°	589.5	590.9	594.0	608.5	608.5
172.5°	593.1	593.4	594.6	605.4	605.4
175°	597.1	596.3	594.0	602.3	600.9
177.5°	598.7	597.5	594.5	599.3	598.1
180°	596.3	596.3	596.3	596.3	596.3

(END OF REPORT)