

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-WB-025U-100D-927-1D-UNV-STD-W-4

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number:
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32)
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-WB-025U-100D-927-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3279.0 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 38.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-WB-025U-100D-927-1D-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-WB-025U-100D-927-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	108	108	108	108	99	99	99	89	89	89	81	81	81
1	106	102	98	95	101	97	94	92	89	87	85	82	80	78	75	73	72
2	98	91	86	81	93	87	82	78	80	76	73	74	71	68	68	66	64
3	90	82	75	70	86	79	73	68	73	68	64	67	63	60	62	59	56
4	84	74	67	61	80	71	65	59	66	61	56	61	57	53	57	53	50
5	78	67	60	54	74	65	58	53	60	54	50	56	51	48	52	48	45
6	73	61	54	48	69	59	52	47	55	49	45	51	47	43	48	44	41
7	68	56	49	43	65	54	47	42	51	45	41	48	43	39	45	40	37
8	63	52	44	39	61	50	43	38	47	41	37	44	39	35	41	37	34
9	60	48	41	36	57	46	40	35	44	38	34	41	36	33	39	34	31
10	56	44	37	33	54	43	37	32	41	35	31	38	33	30	36	32	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16048	16048	16048
5°	15848	15792	15883
10°	14973	15109	15459
15°	13822	14143	14777
20°	12552	13024	13886
25°	11258	11872	12937
30°	10066	10725	11953
35°	8803	9438	10789
40°	7409	7997	9340
45°	6114	6643	7797
50°	5106	5565	6496
55°	4333	4776	5364
60°	3703	4141	4281
65°	2949	3482	2766
70°	2614	2716	1689
75°	2420	2203	1034
80°	2232	2030	893
85°	2022	1863	730

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 7797 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-WB-025U-100D-927-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.5	4.9
10°-20°	415.0	12.7
20°-30°	537.5	16.4
30°-40°	526.4	16.1
40°-50°	402.9	12.3
50°-60°	268.5	8.2
60°-70°	146.5	4.5
70°-80°	61.0	1.9
80°-90°	17.9	0.5
90°-100°	55.9	1.7
100°-110°	147.0	4.5
110°-120°	152.5	4.6
120°-130°	122.3	3.7
130°-140°	95.9	2.9
140°-150°	73.6	2.2
150°-160°	53.0	1.6
160°-170°	32.5	1.0
170°-180°	11.0	0.3
0°-30°	1112.1	33.9
0°-40°	1638.4	50.0
0°-60°	2309.8	70.4
0°-90°	2535.3	77.3
90°-120°	355.4	10.8
90°-150°	647.3	19.7
90°-180°	744.0	22.7
0°-180°	3279.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1739	1739	1739	1739	1739	
5°	1711	1694	1705	1709	1715	159
15°	1447	1442	1481	1521	1547	404
25°	1106	1109	1166	1217	1271	509
35°	782	785	838	894	958	486
45°	469	478	509	548	598	365
55°	269	281	297	308	334	244
65°	135	146	160	139	127	140
75°	68	68	62	42	29	73
85°	19	19	18	11	7	21
90°	1	2	6	3	3	2
95°	7	29	96	50	34	8
105°	26	40	163	247	230	28
115°	47	57	130	260	296	46
125°	66	73	118	200	236	58
135°	78	86	115	162	183	60
145°	90	96	113	138	149	57
155°	102	105	113	124	128	47
165°	110	112	113	118	119	31
175°	115	115	114	116	116	11
180°	115	115	115	115	115	

TEST NUMBER:

CATALOG NUMBER: SQ4-WB-025U-100D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1739.4	1739.4	1739.4	1739.4	1739.4
2.5°	1743.7	1728.2	1732.1	1732.0	1727.2
5°	1711.2	1694.0	1705.1	1709.0	1715.0
7.5°	1647.7	1634.7	1654.9	1669.8	1681.9
10°	1598.2	1587.0	1612.7	1634.5	1650.1
12.5°	1540.8	1531.4	1563.3	1592.4	1612.9
15°	1447.1	1441.9	1480.7	1521.0	1547.1
17.5°	1346.8	1344.3	1388.8	1435.8	1469.2
20°	1278.4	1277.7	1326.5	1375.5	1414.3
22.5°	1209.4	1211.1	1262.4	1313.3	1357.5
25°	1105.9	1108.9	1166.2	1217.1	1270.8
27.5°	1010.2	1011.6	1070.8	1124.5	1181.8
30°	944.9	948.6	1006.7	1062.3	1122.0
32.5°	879.6	883.9	940.8	998.2	1059.1
35°	781.6	785.3	838.0	894.4	957.9
37.5°	680.5	685.6	732.4	785.7	848.1
40°	615.2	622.6	664.0	714.3	775.5
42.5°	552.3	561.5	599.9	647.6	702.8
45°	468.6	477.6	509.1	547.6	597.6
47.5°	396.6	406.9	431.1	464.3	506.9
50°	355.7	365.4	387.7	412.3	452.6
52.5°	319.6	329.3	349.3	368.2	402.5
55°	269.4	280.6	296.9	308.2	333.5
57.5°	228.2	239.0	251.9	257.0	272.3
60°	200.7	212.7	224.4	223.8	232.0
62.5°	175.7	185.8	197.5	189.4	189.9
65°	135.1	146.3	159.5	139.4	126.7
67.5°	109.1	111.5	125.2	97.2	82.1
70°	96.9	96.9	100.7	75.3	62.6
72.5°	85.3	85.3	81.8	61.2	47.9
75°	67.9	67.9	61.8	42.4	29.0
77.5°	52.4	51.8	47.3	31.7	21.1
80°	42.0	42.0	38.2	25.0	16.8
82.5°	32.8	32.8	29.6	19.5	12.5
85°	19.1	19.1	17.6	11.3	6.9
87.5°	6.9	7.2	7.3	4.2	3.6
90°	0.7	2.2	5.9	2.9	2.9
92.5°	3.1	14.9	33.0	14.6	9.4
95°	7.4	28.9	96.4	49.7	33.8
97.5°	12.8	31.8	144.2	114.7	84.4
100°	16.9	34.2	158.9	161.0	125.0
102.5°	20.4	36.6	163.0	200.6	169.8
105°	26.5	40.1	162.6	246.8	230.2
107.5°	32.7	45.3	153.3	270.8	274.8
110°	36.8	48.3	145.6	277.0	294.2

TEST NUMBER:

CATALOG NUMBER: SQ4-WB-025U-100D-927-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	40.9	51.8	138.6	273.1	299.5
115°	47.1	57.1	130.2	259.8	296.4
117.5°	53.1	62.3	124.5	241.3	282.0
120°	56.6	65.3	122.1	228.9	268.5
122.5°	60.2	68.8	120.3	216.6	255.5
125°	65.5	73.4	118.4	200.2	236.1
127.5°	69.7	77.8	116.8	186.9	217.3
130°	72.1	80.7	116.2	178.6	206.7
132.5°	74.4	83.1	115.6	171.5	196.7
135°	78.0	85.9	114.7	161.6	183.2
137.5°	81.6	89.4	114.6	154.1	171.8
140°	84.6	91.8	114.0	148.2	164.8
142.5°	86.9	93.6	114.0	144.1	158.3
145°	90.5	96.2	113.3	137.8	148.6
147.5°	94.0	99.6	113.3	132.6	141.5
150°	96.4	101.4	113.3	129.6	136.8
152.5°	98.7	102.6	113.3	127.2	132.7
155°	102.2	105.1	113.3	124.4	128.0
157.5°	104.9	107.6	113.3	121.9	124.5
160°	106.7	108.8	113.3	120.7	122.1
162.5°	108.4	110.0	113.3	119.5	120.9
165°	110.3	111.8	113.3	117.7	119.2
167.5°	112.1	112.8	114.0	117.0	117.5
170°	113.3	114.0	114.0	117.0	117.0
172.5°	113.9	114.0	114.0	116.4	115.8
175°	114.7	114.7	114.0	115.5	115.5
177.5°	114.7	114.7	114.2	115.3	114.7
180°	114.7	114.7	114.7	114.7	114.7

(END OF REPORT)