

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-PP3-075U-125D-927-1D-UNV-STD-W-6

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number:
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22)
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-125D-927-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6272.6 lumens
Efficiency: N/A
Efficacy: 64.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 97.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-075U-125D-927-1D-UNV-STD-W-6

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-075U-125D-927-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	93	89	85	89	85	82	79	71	69	66	58	56	55	46	45	44
2	88	81	75	70	81	75	69	65	62	58	55	51	48	46	40	39	37
3	81	71	64	58	74	66	59	54	55	50	47	45	42	39	36	34	32
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	30	27
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24
6	62	50	42	37	57	47	40	34	39	34	30	33	29	25	26	23	21
7	58	45	38	32	53	42	35	30	36	30	26	30	26	22	24	21	19
8	53	41	34	28	49	38	31	27	33	27	23	27	23	20	22	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15
10	46	34	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6762	6762	6762
5°	6811	6769	6745
10°	6800	6751	6721
15°	6754	6717	6681
20°	6710	6672	6621
25°	6630	6584	6519
30°	6507	6473	6391
35°	6337	6294	6214
40°	6134	6096	6026
45°	5966	5925	5866
50°	5753	5716	5660
55°	5455	5382	5341
60°	4966	4823	4800
65°	4375	4193	4178
70°	3777	3622	3622
75°	3251	3206	3161
80°	2866	2901	2834
85°	2244	2449	2449

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5966 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-075U-125D-927-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.9	1.7
10°-20°	296.8	4.7
20°-30°	444.6	7.1
30°-40°	521.4	8.3
40°-50°	523.1	8.3
50°-60°	446.2	7.1
60°-70°	291.0	4.6
70°-80°	146.0	2.3
80°-90°	41.8	0.7
90°-100°	250.3	4.0
100°-110°	688.7	11.0
110°-120°	710.9	11.3
120°-130°	569.6	9.1
130°-140°	447.4	7.1
140°-150°	342.8	5.5
150°-160°	246.5	3.9
160°-170°	150.7	2.4
170°-180°	50.8	0.8
0°-30°	845.3	13.5
0°-40°	1366.8	21.8
0°-60°	2336.0	37.2
0°-90°	2814.8	44.9
90°-120°	1650.0	26.3
90°-150°	3009.8	48.0
90°-180°	3458.0	55.1
0°-180°	6272.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1099	1099	1099	1099	1099	
5°	1103	1093	1096	1092	1092	105
15°	1061	1050	1055	1051	1049	299
25°	977	966	970	962	960	449
35°	844	836	838	828	828	527
45°	686	681	681	674	674	528
55°	509	507	502	499	498	452
65°	301	295	288	286	287	300
75°	137	137	135	134	133	148
85°	32	35	35	35	35	37
90°	1	4	8	10	10	4
95°	37	137	443	189	121	39
105°	123	189	759	1156	1078	130
115°	218	265	609	1212	1376	215
125°	300	342	552	934	1094	268
135°	362	402	536	756	855	280
145°	419	448	528	644	693	263
155°	474	490	525	579	595	218
165°	513	519	527	549	552	144
175°	531	532	528	535	534	50
180°	531	531	531	531	531	

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-075U-125D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1099.3	1099.3	1099.3	1099.3	1099.3
2.5°	1106.2	1097.1	1099.3	1097.6	1093.1
5°	1103.1	1092.7	1096.4	1092.5	1092.5
7.5°	1095.6	1084.3	1087.9	1084.0	1083.8
10°	1088.7	1077.3	1080.9	1077.1	1076.1
12.5°	1078.6	1067.3	1071.7	1067.1	1066.9
15°	1060.7	1050.4	1054.9	1051.0	1049.2
17.5°	1040.5	1029.2	1034.7	1029.3	1028.5
20°	1025.1	1013.8	1019.3	1011.6	1011.6
22.5°	1006.6	995.3	1001.6	991.5	991.5
25°	976.9	965.6	970.2	961.5	960.5
27.5°	941.6	930.5	935.3	925.4	925.3
30°	916.2	905.8	911.4	900.8	899.8
32.5°	888.5	878.8	882.9	872.3	871.3
35°	843.9	835.5	838.2	828.5	827.6
37.5°	797.1	788.5	791.5	783.2	782.9
40°	764.0	758.3	759.2	752.4	750.5
42.5°	733.2	726.7	727.6	720.8	720.4
45°	685.9	681.2	681.1	674.4	674.4
47.5°	635.9	632.3	631.2	625.6	625.4
50°	601.2	598.3	597.3	592.5	591.5
52.5°	564.9	563.6	560.3	556.3	556.1
55°	508.7	506.8	501.9	499.0	498.1
57.5°	447.6	443.8	438.4	434.1	434.9
60°	403.7	399.9	392.1	390.2	390.2
62.5°	361.3	356.8	348.9	346.3	347.8
65°	300.6	294.9	288.1	286.2	287.1
67.5°	245.5	240.4	233.0	232.9	232.2
70°	210.0	207.2	201.4	201.4	201.4
72.5°	178.4	177.1	172.8	172.8	172.1
75°	136.8	136.8	134.9	133.9	133.0
77.5°	102.5	102.9	101.9	100.9	99.2
80°	80.9	82.8	81.9	80.9	80.0
82.5°	60.9	62.8	62.6	60.9	60.7
85°	31.8	34.6	34.7	34.7	34.7
87.5°	8.7	12.4	13.9	14.4	15.1
90°	1.1	4.4	7.9	10.2	10.2
92.5°	15.6	66.6	115.4	44.3	36.4
95°	37.3	136.6	442.7	189.3	120.8
97.5°	60.8	151.5	675.6	520.5	367.3
100°	77.9	160.7	748.7	755.7	616.6
102.5°	94.2	171.7	767.7	937.6	809.9
105°	123.1	189.3	758.9	1155.8	1078.5
107.5°	150.7	211.2	715.8	1262.6	1285.6
110°	170.5	225.7	683.2	1289.2	1368.7

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-075U-125D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.6	242.0	650.7	1272.1	1393.1
115°	218.0	265.4	608.7	1212.1	1375.5
117.5°	246.0	289.7	582.0	1127.9	1312.7
120°	263.1	305.1	570.3	1064.8	1255.8
122.5°	278.5	320.4	562.2	1009.4	1190.8
125°	300.4	342.4	552.2	934.2	1094.3
127.5°	321.2	361.2	545.7	871.4	1011.9
130°	332.0	372.9	542.1	834.1	962.2
132.5°	344.7	385.5	539.4	801.3	917.0
135°	362.5	402.3	536.4	755.5	854.9
137.5°	379.2	416.1	533.9	718.5	800.5
140°	391.9	426.1	533.0	694.0	767.9
142.5°	402.7	434.3	531.2	672.0	735.4
145°	419.0	447.7	528.5	643.7	693.4
147.5°	436.4	461.1	527.2	618.6	658.4
150°	447.2	469.3	526.3	604.9	635.8
152.5°	457.1	477.5	525.4	593.0	618.6
155°	474.3	489.8	525.1	578.6	595.1
157.5°	486.7	499.3	525.1	566.7	578.2
160°	495.8	505.7	525.1	560.3	569.2
162.5°	503.0	511.2	526.0	554.9	561.9
165°	512.7	519.3	527.4	548.9	552.2
167.5°	519.5	524.6	528.5	543.9	544.8
170°	524.0	527.3	528.5	542.1	542.1
172.5°	527.6	529.2	528.5	539.3	538.5
175°	530.8	531.9	528.5	535.3	534.2
177.5°	531.7	531.7	528.1	533.4	531.7
180°	530.8	530.8	530.8	530.8	530.8

(END OF REPORT)