

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-PP3-0U-050D-927-1D-UNV-STD-W-6

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number:
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA ()
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-050D-927-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1125.8 lumens
Efficiency: N/A
Efficacy: 42.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Direct

Input Watts (W): 26.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-0U-050D-927-1D-UNV-STD-W-6

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-0U-050D-927-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85		
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72		
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61		
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53		
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46		
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40		
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36		
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32		
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29		
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2706	2706	2706
5°	2725	2709	2699
10°	2721	2701	2689
15°	2702	2688	2673
20°	2685	2670	2650
25°	2653	2635	2608
30°	2604	2590	2558
35°	2536	2518	2486
40°	2455	2439	2411
45°	2388	2371	2348
50°	2302	2287	2265
55°	2182	2153	2137
60°	1987	1930	1920
65°	1751	1678	1672
70°	1511	1449	1449
75°	1300	1283	1264
80°	1148	1162	1133
85°	896	981	981

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2388 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-0U-050D-927-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	3.7
10°-20°	118.8	10.5
20°-30°	177.9	15.8
30°-40°	208.7	18.5
40°-50°	209.3	18.6
50°-60°	178.5	15.9
60°-70°	116.5	10.3
70°-80°	58.4	5.2
80°-90°	16.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	338.2	30.0
0°-40°	546.9	48.6
0°-60°	934.8	83.0
0°-90°	1125.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1125.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	440	440	440	440	440	
5°	441	437	439	437	437	42
15°	424	420	422	421	420	120
25°	391	386	388	385	384	180
35°	338	334	335	332	331	211
45°	274	273	273	270	270	211
55°	204	203	201	200	199	181
65°	120	118	115	114	115	120
75°	55	55	54	54	53	59
85°	13	14	14	14	14	15
90°	0	0	0	0	0	

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-0U-050D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	439.9	439.9	439.9	439.9	439.9
2.5°	442.6	439.0	439.9	439.2	437.4
5°	441.4	437.3	438.7	437.2	437.2
7.5°	438.4	433.9	435.3	433.8	433.7
10°	435.6	431.1	432.5	431.0	430.6
12.5°	431.6	427.1	428.8	427.0	426.9
15°	424.4	420.3	422.1	420.6	419.8
17.5°	416.3	411.8	414.0	411.9	411.6
20°	410.2	405.7	407.9	404.8	404.8
22.5°	402.8	398.2	400.8	396.8	396.8
25°	390.9	386.4	388.2	384.7	384.3
27.5°	376.8	372.3	374.2	370.3	370.2
30°	366.6	362.5	364.7	360.4	360.1
32.5°	355.5	351.7	353.3	349.0	348.6
35°	337.7	334.3	335.4	331.5	331.1
37.5°	319.0	315.5	316.7	313.4	313.3
40°	305.7	303.4	303.8	301.1	300.3
42.5°	293.4	290.8	291.1	288.4	288.3
45°	274.5	272.6	272.6	269.9	269.9
47.5°	254.4	253.0	252.6	250.3	250.3
50°	240.6	239.4	239.0	237.1	236.7
52.5°	226.1	225.5	224.2	222.6	222.5
55°	203.5	202.8	200.8	199.7	199.3
57.5°	179.1	177.6	175.4	173.7	174.0
60°	161.5	160.0	156.9	156.1	156.1
62.5°	144.6	142.8	139.6	138.6	139.2
65°	120.3	118.0	115.3	114.5	114.9
67.5°	98.2	96.2	93.2	93.2	92.9
70°	84.0	82.9	80.6	80.6	80.6
72.5°	71.4	70.9	69.2	69.2	68.9
75°	54.7	54.7	54.0	53.6	53.2
77.5°	41.0	41.2	40.8	40.4	39.7
80°	32.4	33.1	32.8	32.4	32.0
82.5°	24.4	25.1	25.1	24.4	24.3
85°	12.7	13.9	13.9	13.9	13.9
87.5°	3.4	4.6	4.9	4.9	5.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)