

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-PP3-0U-075D-927-1D-UNV-STD-W-6

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number:
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA ()
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-075D-927-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1659.3 lumens
Efficiency: N/A
Efficacy: 41.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-0U-075D-927-1D-UNV-STD-W-6

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-0U-075D-927-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	105	101	97	107	103	99	96	98	95	93		95	92	90		91
2	100	92	86	80	97	90	84	79	87	82	77		84	79	76		81
3	92	81	74	67	89	80	73	67	77	71	66		74	69	64		72
4	84	72	64	57	82	71	63	57	69	62	56		66	60	56		64
5	77	65	56	50	75	64	56	49	62	54	49		60	53	48		58
6	72	59	50	44	70	58	49	43	56	49	43		54	48	43		53
7	66	53	45	39	65	52	44	39	51	44	38		49	43	38		48
8	62	49	40	35	60	48	40	34	47	39	34		45	39	34		44
9	58	45	37	31	56	44	36	31	43	36	31		42	35	31		41
10	54	41	34	28	53	41	33	28	40	33	28		39	33	28		38

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3988	3988	3988
5°	4017	3992	3978
10°	4010	3982	3964
15°	3984	3962	3940
20°	3957	3935	3905
25°	3910	3883	3845
30°	3837	3818	3769
35°	3737	3712	3665
40°	3618	3595	3554
45°	3519	3494	3459
50°	3392	3371	3339
55°	3217	3174	3151
60°	2929	2845	2831
65°	2580	2473	2464
70°	2228	2136	2136
75°	1918	1889	1863
80°	1690	1711	1672
85°	1327	1447	1447

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3519 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-0U-075D-927-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.3	3.7
10°-20°	175.0	10.5
20°-30°	262.2	15.8
30°-40°	307.5	18.5
40°-50°	308.5	18.6
50°-60°	263.2	15.9
60°-70°	171.6	10.3
70°-80°	86.1	5.2
80°-90°	23.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	498.5	30.0
0°-40°	806.1	48.6
0°-60°	1377.7	83.0
0°-90°	1659.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1659.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	648	648	648	648	648	
5°	651	644	647	644	644	62
15°	626	620	622	620	619	176
25°	576	570	572	567	566	265
35°	498	493	494	489	488	311
45°	404	402	402	398	398	311
55°	300	299	296	294	294	267
65°	177	174	170	169	169	177
75°	81	81	80	79	78	88
85°	19	20	20	20	20	23
90°	0	0	0	0	0	

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-0U-075D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	648.3	648.3	648.3	648.3	648.3
2.5°	652.4	647.1	648.3	647.3	644.7
5°	650.6	644.5	646.6	644.3	644.3
7.5°	646.1	639.5	641.6	639.3	639.2
10°	642.0	635.4	637.5	635.2	634.7
12.5°	636.1	629.5	632.0	629.3	629.2
15°	625.6	619.5	622.2	619.9	618.8
17.5°	613.6	607.0	610.2	607.0	606.6
20°	604.5	597.9	601.1	596.6	596.6
22.5°	593.6	587.0	590.7	584.8	584.8
25°	576.1	569.5	572.2	567.0	566.5
27.5°	555.3	548.8	551.6	545.8	545.7
30°	540.3	534.2	537.5	531.2	530.7
32.5°	524.0	518.3	520.7	514.4	513.9
35°	497.7	492.7	494.3	488.6	488.1
37.5°	470.1	465.0	466.8	461.9	461.7
40°	450.6	447.2	447.7	443.7	442.6
42.5°	432.4	428.6	429.1	425.1	424.9
45°	404.5	401.8	401.7	397.7	397.7
47.5°	375.0	372.9	372.3	369.0	368.9
50°	354.5	352.9	352.3	349.4	348.9
52.5°	333.2	332.4	330.5	328.1	328.0
55°	300.0	298.9	296.0	294.3	293.8
57.5°	264.0	261.8	258.5	256.0	256.5
60°	238.1	235.8	231.3	230.1	230.1
62.5°	213.1	210.4	205.8	204.2	205.1
65°	177.3	173.9	169.9	168.8	169.3
67.5°	144.8	141.8	137.4	137.4	136.9
70°	123.9	122.2	118.8	118.8	118.8
72.5°	105.2	104.5	101.9	101.9	101.5
75°	80.7	80.7	79.5	79.0	78.4
77.5°	60.5	60.7	60.1	59.5	58.5
80°	47.7	48.8	48.3	47.7	47.2
82.5°	35.9	37.0	36.9	35.9	35.8
85°	18.8	20.4	20.5	20.5	20.5
87.5°	5.0	6.8	7.3	7.3	7.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)