

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-PP3-150U-125D-927-1D-UNV-STD-W-6

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number:
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25)
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-125D-927-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9773.4 lumens
Efficiency: N/A
Efficacy: 76.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 127.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-150U-125D-927-1D-UNV-STD-W-6

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-150U-125D-927-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26
3	77	68	61	56	69	62	56	51	49	44	41	37	34	32	26	24	23
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	19
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	21	19	17
6	60	48	40	35	53	43	37	32	35	30	26	26	23	20	19	17	15
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	17	15	13
8	51	39	32	27	46	35	29	24	28	24	20	22	18	16	16	13	12
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	23	19	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6762	6762	6762
5°	6811	6769	6745
10°	6800	6751	6721
15°	6754	6717	6681
20°	6710	6672	6621
25°	6630	6584	6519
30°	6507	6473	6391
35°	6337	6294	6214
40°	6134	6096	6026
45°	5966	5925	5866
50°	5753	5716	5660
55°	5455	5382	5341
60°	4966	4823	4800
65°	4375	4193	4178
70°	3777	3622	3622
75°	3251	3206	3161
80°	2866	2901	2834
85°	2244	2449	2449

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5966 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-150U-125D-927-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.9	1.1
10°-20°	296.8	3.0
20°-30°	444.6	4.5
30°-40°	521.4	5.3
40°-50°	523.1	5.4
50°-60°	446.2	4.6
60°-70°	291.0	3.0
70°-80°	146.0	1.5
80°-90°	42.7	0.4
90°-100°	501.5	5.1
100°-110°	1356.0	13.9
110°-120°	1425.6	14.6
120°-130°	1158.0	11.8
130°-140°	908.4	9.3
140°-150°	697.2	7.1
150°-160°	501.4	5.1
160°-170°	306.3	3.1
170°-180°	103.3	1.1
0°-30°	845.3	8.6
0°-40°	1366.8	14.0
0°-60°	2336.0	23.9
0°-90°	2815.7	28.8
90°-120°	3283.2	33.6
90°-150°	6046.7	61.9
90°-180°	6958.0	71.2
0°-180°	9773.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1099	1099	1099	1099	1099	
5°	1103	1093	1096	1092	1092	105
15°	1061	1050	1055	1051	1049	299
25°	977	966	970	962	960	449
35°	844	836	838	828	828	527
45°	686	681	681	674	674	528
55°	509	507	502	499	498	452
65°	301	295	288	286	287	300
75°	137	137	135	134	133	148
85°	32	35	35	35	35	37
90°	2	7	15	16	15	6
95°	78	273	834	432	257	81
105°	252	390	1504	2219	2128	265
115°	444	543	1248	2415	2726	438
125°	608	696	1124	1898	2229	542
135°	728	815	1094	1532	1734	563
145°	847	910	1079	1311	1411	530
155°	956	994	1070	1176	1215	441
165°	1041	1051	1074	1116	1122	293
175°	1080	1079	1076	1090	1087	103
180°	1079	1079	1079	1079	1079	

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-150U-125D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1099.3	1099.3	1099.3	1099.3	1099.3
2.5°	1106.2	1097.1	1099.3	1097.6	1093.1
5°	1103.1	1092.7	1096.4	1092.5	1092.5
7.5°	1095.6	1084.3	1087.9	1084.0	1083.8
10°	1088.7	1077.3	1080.9	1077.1	1076.1
12.5°	1078.6	1067.3	1071.7	1067.1	1066.9
15°	1060.7	1050.4	1054.9	1051.0	1049.2
17.5°	1040.5	1029.2	1034.7	1029.3	1028.5
20°	1025.1	1013.8	1019.3	1011.6	1011.6
22.5°	1006.6	995.3	1001.6	991.5	991.5
25°	976.9	965.6	970.2	961.5	960.5
27.5°	941.6	930.5	935.3	925.4	925.3
30°	916.2	905.8	911.4	900.8	899.8
32.5°	888.5	878.8	882.9	872.3	871.3
35°	843.9	835.5	838.2	828.5	827.6
37.5°	797.1	788.5	791.5	783.2	782.9
40°	764.0	758.3	759.2	752.4	750.5
42.5°	733.2	726.7	727.6	720.8	720.4
45°	685.9	681.2	681.1	674.4	674.4
47.5°	635.9	632.3	631.2	625.6	625.4
50°	601.2	598.3	597.3	592.5	591.5
52.5°	564.9	563.6	560.3	556.3	556.1
55°	508.7	506.8	501.9	499.0	498.1
57.5°	447.6	443.8	438.4	434.1	434.9
60°	403.7	399.9	392.1	390.2	390.2
62.5°	361.3	356.8	348.9	346.3	347.8
65°	300.6	294.9	288.1	286.2	287.1
67.5°	245.5	240.4	233.0	232.9	232.2
70°	210.0	207.2	201.4	201.4	201.4
72.5°	178.4	177.1	172.8	172.8	172.1
75°	136.8	136.8	134.9	133.9	133.0
77.5°	102.5	102.9	101.9	100.9	99.2
80°	80.9	82.8	81.9	80.9	80.0
82.5°	60.9	62.8	62.6	60.9	60.7
85°	31.8	34.6	34.7	34.7	34.7
87.5°	8.9	12.9	15.4	15.6	16.1
90°	2.3	6.9	15.1	16.2	15.1
92.5°	33.0	120.2	237.2	103.0	74.6
95°	77.8	273.2	834.0	431.6	256.7
97.5°	125.0	313.3	1300.1	1075.9	790.1
100°	160.3	329.5	1445.1	1507.0	1218.5
102.5°	192.8	352.1	1496.2	1833.9	1618.1
105°	252.1	389.5	1504.3	2219.0	2128.1
107.5°	306.9	432.3	1438.6	2459.1	2489.4
110°	349.6	463.2	1380.0	2523.6	2652.0

TEST NUMBER:

CATALOG NUMBER: SQ4-PP3-150U-125D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	387.7	494.1	1326.1	2510.7	2726.3
115°	443.7	542.6	1247.6	2415.1	2726.3
117.5°	498.6	591.2	1195.8	2269.0	2621.8
120°	532.0	622.9	1165.1	2164.2	2524.2
122.5°	563.6	652.7	1146.5	2051.8	2414.5
125°	607.5	696.1	1124.4	1897.5	2229.1
127.5°	648.0	735.0	1111.4	1771.6	2063.3
130°	670.3	760.0	1105.9	1693.8	1957.3
132.5°	693.5	782.3	1100.3	1623.7	1866.3
135°	728.3	814.7	1094.2	1532.1	1734.3
137.5°	763.4	845.0	1089.1	1457.9	1622.6
140°	787.6	863.7	1087.3	1410.1	1556.6
142.5°	810.8	882.4	1083.6	1366.9	1495.2
145°	846.8	910.4	1079.1	1311.4	1411.4
147.5°	879.6	935.9	1074.0	1261.2	1338.0
150°	903.7	953.7	1072.2	1233.9	1295.2
152.5°	926.0	969.7	1071.2	1208.5	1259.0
155°	956.0	993.5	1069.9	1176.4	1215.1
157.5°	987.1	1013.3	1070.1	1154.1	1179.5
160°	1004.8	1026.4	1071.0	1140.0	1158.1
162.5°	1018.7	1036.7	1071.9	1128.7	1142.3
165°	1040.8	1051.0	1074.5	1116.4	1122.1
167.5°	1055.9	1063.0	1074.7	1105.9	1108.7
170°	1065.2	1068.6	1075.7	1101.2	1101.2
172.5°	1072.6	1073.3	1075.7	1095.6	1094.7
175°	1080.3	1079.2	1075.7	1089.5	1087.3
177.5°	1082.9	1080.1	1075.4	1084.7	1081.9
180°	1079.1	1079.1	1079.1	1079.1	1079.1

(END OF REPORT)