

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-PC3-0U-125D-927-1D-UNV-STD-W-6

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number:
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA ()
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-125D-927-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2839.8 lumens
Efficiency: N/A
Efficacy: 40.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Direct

Input Watts (W): 69.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-PC3-0U-125D-927-1D-UNV-STD-W-6

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-PC3-0U-125D-927-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	105	100	97	106	102	98	95	98	95	92		94	92	89		91
2	99	91	85	79	97	90	83	78	86	81	76		83	78	75		80
3	91	80	72	66	88	79	71	65	76	70	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	48	74	63	54	48	61	53	48		59	52	47		57
6	71	58	49	42	69	57	48	42	55	47	42		53	46	41		52
7	66	52	43	37	64	51	43	37	50	42	37		48	42	37		47
8	61	48	39	33	60	47	39	33	46	38	33		44	38	33		43
9	57	44	36	30	56	43	35	30	42	35	30		41	34	30		40
10	54	40	32	27	52	40	32	27	39	32	27		38	31	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6400	6400	6400
5°	6448	6406	6383
10°	6432	6402	6384
15°	6399	6399	6393
20°	6356	6375	6375
25°	6297	6342	6322
30°	6220	6296	6268
35°	6127	6222	6178
40°	6026	6111	6049
45°	5917	5959	5866
50°	5761	5761	5670
55°	5579	5507	5424
60°	5309	5202	5120
65°	4908	4810	4768
70°	4296	4332	4314
75°	3458	3824	3848
80°	2458	3241	3276
85°	1496	2717	2717

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 5959 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-PC3-0U-125D-927-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.5	3.5
10°-20°	282.6	10.0
20°-30°	427.9	15.1
30°-40°	513.0	18.1
40°-50°	523.1	18.4
50°-60°	456.7	16.1
60°-70°	326.9	11.5
70°-80°	168.4	5.9
80°-90°	42.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	809.0	28.5
0°-40°	1322.1	46.6
0°-60°	2301.9	81.1
0°-90°	2839.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2839.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1040	1040	1040	1040	1040	
5°	1044	1034	1038	1035	1034	99
15°	1005	996	1005	1005	1004	283
25°	928	921	934	932	932	427
35°	816	814	829	823	823	510
45°	680	678	685	676	674	524
55°	520	514	514	506	506	464
65°	337	330	330	328	328	334
75°	146	152	161	162	162	157
85°	21	32	38	40	38	30
90°	0	0	0	0	0	

TEST NUMBER:

CATALOG NUMBER: SQ4-PC3-0U-125D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1040.5	1040.5	1040.5	1040.5	1040.5
2.5°	1046.7	1037.6	1040.5	1038.1	1034.3
5°	1044.4	1034.0	1037.6	1034.7	1033.8
7.5°	1036.9	1026.5	1031.3	1029.3	1028.4
10°	1029.9	1019.6	1025.1	1023.1	1022.2
12.5°	1020.7	1011.1	1017.4	1015.5	1015.3
15°	1004.9	996.4	1004.9	1004.8	1003.9
17.5°	985.0	977.3	986.4	986.9	986.4
20°	971.1	962.7	974.0	973.1	974.0
22.5°	954.2	947.2	959.4	956.9	957.8
25°	927.8	921.2	934.5	931.6	931.6
27.5°	896.6	891.9	906.4	903.3	903.3
30°	875.8	871.1	886.4	882.5	882.5
32.5°	852.6	849.4	864.0	859.4	859.4
35°	816.0	814.1	828.6	822.8	822.8
37.5°	778.3	776.6	789.6	782.6	780.4
40°	750.5	749.6	761.1	753.4	753.4
42.5°	722.8	721.8	731.8	722.6	722.6
45°	680.2	678.3	685.0	676.3	674.4
47.5°	633.7	631.9	636.1	626.6	625.7
50°	602.1	600.3	602.1	593.5	592.5
52.5°	569.8	566.4	566.7	558.0	557.8
55°	520.3	513.7	513.5	505.8	505.8
57.5°	467.8	459.2	459.9	453.4	452.4
60°	431.6	422.2	422.9	417.1	416.2
62.5°	396.2	385.2	387.5	380.9	380.8
65°	337.2	329.7	330.5	327.6	327.6
67.5°	280.6	273.6	278.6	276.3	276.1
70°	238.9	234.2	240.9	240.8	239.9
72.5°	200.4	200.2	208.5	208.5	209.1
75°	145.5	152.1	160.9	161.9	161.9
77.5°	97.1	108.8	118.5	118.9	118.7
80°	69.4	82.6	91.5	93.4	92.5
82.5°	47.0	61.0	68.4	70.3	69.4
85°	21.2	32.5	38.5	39.5	38.5
87.5°	6.2	12.9	15.4	15.4	13.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)