

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number:

Luminaire Tested: SQ4-PW1-050U-050D-927-1D-UNV-STD-W-6

Issue Date: 8/1/2024

Test Information

Test Method: LM-79-2019
Report Number:
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21)
Test Lab: INNOVATION CENTER
Issue Date: 8/1/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-PW1-050U-050D-927-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3415.3 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 44.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:

CATALOG NUMBER: SQ4-PW1-050U-050D-927-1D-UNV-STD-W-6

Luminous Intensity Polar Plot



TEST NUMBER:

CATALOG NUMBER: SQ4-PW1-050U-050D-927-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	84	81	78	75	65	62	60	49	48	47	36	35	34
2	86	78	72	68	77	71	66	62	57	53	50	43	41	39	31	30	29
3	78	69	62	56	70	62	56	51	50	46	42	38	36	33	28	26	24
4	71	61	53	47	64	55	49	44	44	40	36	34	31	28	25	23	21
5	65	54	46	40	59	49	42	37	40	35	31	31	27	24	22	20	18
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16
7	56	44	36	31	50	40	33	28	32	27	23	25	22	19	18	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	18	21	18	15	16	13	12
10	45	33	26	21	40	30	24	20	25	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2691	2691	2691
5°	2709	2687	2675
10°	2687	2666	2651
15°	2659	2629	2619
20°	2627	2586	2582
25°	2590	2543	2535
30°	2536	2497	2481
35°	2464	2428	2414
40°	2386	2349	2340
45°	2294	2263	2254
50°	2199	2180	2165
55°	2096	2096	2063
60°	1968	2006	1935
65°	1800	1891	1757
70°	1588	1741	1547
75°	1357	1557	1319
80°	1052	1311	1066
85°	677	1009	896

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2294 cd/sqm

TEST NUMBER:

CATALOG NUMBER: SQ4-PW1-050U-050D-927-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.2	1.2
10°-20°	116.3	3.4
20°-30°	172.5	5.1
30°-40°	201.9	5.9
40°-50°	201.0	5.9
50°-60°	173.6	5.1
60°-70°	124.9	3.7
70°-80°	65.5	1.9
80°-90°	17.6	0.5
90°-100°	169.1	5.0
100°-110°	459.5	13.5
110°-120°	472.4	13.8
120°-130°	377.7	11.1
130°-140°	296.8	8.7
140°-150°	227.6	6.7
150°-160°	163.7	4.8
160°-170°	100.1	2.9
170°-180°	33.7	1.0
0°-30°	330.1	9.7
0°-40°	532.0	15.6
0°-60°	906.5	26.5
0°-90°	1114.6	32.6
90°-120°	1101.1	32.2
90°-150°	2003.2	58.7
90°-180°	2301.0	67.4
0°-180°	3415.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	438	438	438	438	438	
5°	439	434	435	434	433	42
15°	418	412	413	412	411	118
25°	382	375	375	372	374	175
35°	328	324	323	320	322	205
45°	264	261	260	259	259	203
55°	196	195	196	193	192	174
65°	124	128	130	125	121	123
75°	57	62	66	61	56	61
85°	10	13	14	14	13	13
90°	1	4	8	10	10	2
95°	25	92	295	128	86	26
105°	82	127	505	769	724	87
115°	145	176	404	805	917	143
125°	199	227	366	617	727	178
135°	240	267	356	502	566	186
145°	278	298	351	427	459	174
155°	314	325	349	383	394	145
165°	340	344	350	365	366	96
175°	352	354	351	356	355	33
180°	352	352	352	352	352	

TEST NUMBER:

CATALOG NUMBER: SQ4-PW1-050U-050D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	437.5	437.5	437.5	437.5	437.5
2.5°	440.0	436.4	437.5	436.6	434.5
5°	438.7	433.8	435.2	434.1	433.3
7.5°	434.2	429.7	430.8	429.5	429.1
10°	430.2	425.7	426.8	425.2	424.4
12.5°	425.6	420.8	421.8	420.3	419.8
15°	417.5	412.2	412.9	412.1	411.3
17.5°	408.1	402.7	402.9	401.6	401.5
20°	401.3	395.7	395.1	393.6	394.4
22.5°	393.9	388.0	387.4	385.3	386.4
25°	381.6	375.2	374.7	372.4	373.6
27.5°	367.5	361.1	361.1	357.9	359.1
30°	357.0	350.9	351.6	347.8	349.3
32.5°	345.9	340.4	340.8	337.0	338.5
35°	328.1	323.5	323.4	320.4	321.5
37.5°	309.9	305.9	305.2	303.5	303.8
40°	297.2	293.8	292.6	291.4	291.4
42.5°	284.0	280.9	279.6	278.8	278.5
45°	263.7	261.4	260.2	259.4	259.1
47.5°	243.6	241.5	240.5	239.9	239.6
50°	229.8	228.3	227.8	226.7	226.3
52.5°	215.9	215.0	214.6	213.1	212.7
55°	195.5	195.1	195.5	192.7	192.4
57.5°	174.2	174.8	176.0	172.4	171.5
60°	160.0	161.5	163.1	158.8	157.3
62.5°	145.5	147.9	150.1	145.2	143.1
65°	123.7	127.5	129.9	124.8	120.7
67.5°	102.8	107.4	110.3	104.8	100.2
70°	88.3	93.6	96.8	91.2	86.0
72.5°	75.6	81.5	84.1	78.9	73.6
75°	57.1	62.3	65.5	61.2	55.5
77.5°	40.5	45.5	48.1	44.3	39.6
80°	29.7	35.0	37.0	33.8	30.1
82.5°	21.0	25.4	26.8	24.9	22.4
85°	9.6	12.7	14.3	13.5	12.7
87.5°	2.7	5.5	7.4	7.9	8.2
90°	1.1	4.5	7.9	10.2	10.2
92.5°	10.2	46.3	80.4	34.5	29.2
95°	24.9	92.5	294.6	128.2	86.1
97.5°	41.2	102.2	451.6	351.3	246.8
100°	52.1	108.6	499.6	506.5	409.0
102.5°	63.0	115.1	512.3	626.4	540.4
105°	81.6	127.0	505.3	769.4	724.0
107.5°	100.8	140.9	476.1	843.2	855.9
110°	114.4	151.0	454.3	857.8	912.1

TEST NUMBER:

CATALOG NUMBER: SQ4-PW1-050U-050D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	126.2	161.0	432.6	845.7	927.5
115°	145.0	176.0	404.5	804.7	916.6
117.5°	162.7	192.4	386.6	746.6	872.6
120°	174.5	203.3	378.4	707.6	832.7
122.5°	184.5	213.3	373.0	668.5	789.2
125°	199.4	227.1	366.0	616.6	727.4
127.5°	212.8	240.2	362.1	577.3	672.3
130°	220.9	247.5	360.3	552.6	637.9
132.5°	229.1	255.7	358.5	531.5	607.1
135°	240.2	266.8	355.8	502.2	566.5
137.5°	252.2	276.4	354.4	476.4	530.5
140°	259.5	282.7	353.5	460.0	508.7
142.5°	266.7	288.2	352.6	447.1	487.9
145°	277.6	297.5	351.2	426.7	458.9
147.5°	289.8	306.9	350.1	410.7	436.0
150°	298.0	312.4	350.1	401.5	421.5
152.5°	304.3	317.0	349.2	393.3	409.7
155°	313.8	324.9	349.0	383.2	394.3
157.5°	323.1	331.8	349.0	376.3	384.8
160°	328.6	336.3	349.0	371.8	378.4
162.5°	334.0	340.0	349.9	368.1	373.0
165°	339.9	344.3	350.1	364.8	366.0
167.5°	346.0	348.2	351.2	361.0	361.9
170°	347.8	350.0	351.2	359.2	359.2
172.5°	349.6	351.0	351.2	357.3	357.3
175°	352.4	353.5	351.2	355.7	354.6
177.5°	353.3	353.3	350.5	354.1	352.4
180°	352.4	352.4	352.4	352.4	352.4

(END OF REPORT)