

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519698

Luminaire Tested: **SQ4-075U-0D-835-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519698
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-835-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5987.5 lumens
Efficiency: N/A
Efficacy: 163.6 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Indirect

Input Watts (W): 36.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519698
CATALOG NUMBER: SQ4-075U-0D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P519698

CATALOG NUMBER: SQ4-075U-0D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0		
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0		
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0		
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0		
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0		
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0		
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0		
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0		
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0		
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0		
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	3414	40576	11073
100°	3584	34443	28364
105°	3800	23422	33286
110°	3983	15957	31967
115°	4120	11505	25999
120°	4203	9111	20063
125°	4184	7691	15240
130°	4126	6737	11957
135°	4095	6060	9657
140°	4087	5558	8008
145°	4086	5154	6762
150°	4125	4854	5865
155°	4180	4628	5246
160°	4215	4464	4838
165°	4240	4361	4567
170°	4251	4287	4397
175°	4256	4238	4283



TEST NUMBER: P519698

CATALOG NUMBER: SQ4-075U-0D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	433.5	7.2
100°-110°	1192.6	19.9
110°-120°	1231.0	20.6
120°-130°	986.3	16.5
130°-140°	774.7	12.9
140°-150°	593.7	9.9
150°-160°	426.8	7.1
160°-170°	261.0	4.4
170°-180°	88.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2857.1	47.7
90°-150°	5211.7	87.0
90°-180°	5988.0	100.0
0°-180°	5987.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	8	14	18	18	
95°	64	237	767	328	209	72
105°	213	328	1314	2001	1868	225
115°	377	460	1054	2099	2382	372
125°	520	593	956	1618	1895	464
135°	628	697	929	1308	1480	484
145°	726	775	915	1115	1201	455
155°	821	848	909	1002	1031	377
165°	888	899	913	950	956	250
175°	919	921	915	927	925	87
180°	919	919	919	919	919	



TEST NUMBER: P519698

CATALOG NUMBER: SQ4-075U-0D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	2.0	7.7	13.7	17.6	17.6
92.5°	27.0	115.3	199.9	76.7	63.0
95°	64.5	236.6	766.6	327.8	209.2
97.5°	105.2	262.4	1169.8	901.3	635.9
100°	134.9	278.3	1296.5	1308.6	1067.7
102.5°	163.1	297.3	1329.4	1623.5	1402.5
105°	213.2	327.9	1314.1	2001.4	1867.5
107.5°	260.9	365.6	1239.4	2186.4	2226.2
110°	295.3	390.9	1183.1	2232.4	2370.1
112.5°	326.6	419.1	1126.8	2202.8	2412.3
115°	377.4	459.6	1054.0	2098.8	2381.8
117.5°	425.9	501.6	1007.9	1953.0	2273.1
120°	455.6	528.3	987.5	1843.8	2174.6
122.5°	482.2	554.9	973.5	1747.9	2061.9
125°	520.2	592.8	956.3	1617.7	1894.9
127.5°	556.2	625.4	944.9	1508.9	1752.2
130°	574.9	645.7	938.7	1444.3	1666.1
132.5°	596.8	667.6	934.0	1387.5	1587.9
135°	627.7	696.6	928.9	1308.3	1480.3
137.5°	656.7	720.5	924.6	1244.2	1386.1
140°	678.6	737.8	923.0	1201.7	1329.8
142.5°	697.3	752.0	919.9	1163.7	1273.4
145°	725.5	775.2	915.2	1114.7	1200.7
147.5°	755.6	798.4	912.8	1071.2	1140.1
150°	774.4	812.6	911.3	1047.4	1101.0
152.5°	791.6	826.8	909.7	1026.9	1071.2
155°	821.3	848.1	909.3	1001.9	1030.6
157.5°	842.8	864.6	909.3	981.3	1001.2
160°	858.5	875.7	909.3	970.3	985.6
162.5°	871.0	885.1	910.9	960.8	973.1
165°	887.8	899.3	913.2	950.5	956.3
167.5°	899.5	908.3	915.2	941.8	943.3
170°	907.4	913.1	915.2	938.7	938.7
172.5°	913.6	916.3	915.2	933.9	932.4
175°	919.1	921.0	915.2	926.9	925.0
177.5°	920.7	920.7	914.4	923.7	920.7
180°	919.1	919.1	919.1	919.1	919.1

(END OF REPORT)