

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563793

Luminaire Tested: **SQ4-PP3-150U-075D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563793
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23196.9 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 194.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563793
CATALOG NUMBER: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563793

CATALOG NUMBER: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32				
1	94	90	86	83	84	81	78	75	65	62	60	49	48	47	35	35	34	27				
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23				
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	25	20				
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17				
5	65	54	46	41	59	49	42	37	40	35	31	31	27	25	22	20	18	15				
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13				
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	14	12				
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10				
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9				
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8999	8999	8999
5°	9065	9010	8978
10°	9050	8986	8946
15°	8990	8941	8892
20°	8930	8880	8813
25°	8824	8763	8676
30°	8661	8615	8506
35°	8434	8376	8271
40°	8165	8113	8020
45°	7941	7886	7808
50°	7657	7607	7534
55°	7260	7164	7109
60°	6609	6420	6388
65°	5822	5580	5561
70°	5027	4820	4820
75°	4328	4266	4205
80°	3815	3861	3771
85°	2985	3257	3257



TEST NUMBER: P563793

CATALOG NUMBER: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.7	1.2
10°-20°	790.1	3.4
20°-30°	1183.4	5.1
30°-40°	1388.0	6.0
40°-50°	1392.4	6.0
50°-60°	1187.8	5.1
60°-70°	774.7	3.3
70°-80°	388.6	1.7
80°-90°	112.6	0.5
90°-100°	1131.9	4.9
100°-110°	3060.3	13.2
110°-120°	3217.5	13.9
120°-130°	2613.5	11.3
130°-140°	2050.0	8.8
140°-150°	1573.4	6.8
150°-160°	1131.6	4.9
160°-170°	691.3	3.0
170°-180°	233.1	1.0
0°-30°	2250.1	9.7
0°-40°	3638.2	15.7
0°-60°	6218.4	26.8
0°-90°	7494.3	32.3
90°-120°	7409.7	31.9
90°-150°	13646.6	58.8
90°-180°	15703.0	67.7
0°-180°	23196.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2926	2926	2926	2926	2926	
5°	2936	2909	2918	2908	2908	279
15°	2824	2796	2808	2798	2793	797
25°	2600	2570	2582	2559	2557	1196
35°	2246	2224	2231	2205	2203	1403
45°	1826	1813	1813	1795	1795	1406
55°	1354	1349	1336	1328	1326	1203
65°	800	785	767	762	764	799
75°	364	364	359	356	354	395
85°	85	92	92	92	92	100
90°	5	16	34	37	34	15
95°	176	616	1882	974	579	184
105°	569	879	3395	5008	4803	599
115°	1002	1224	2816	5451	6153	989
125°	1371	1571	2538	4282	5031	1222
135°	1644	1839	2470	3458	3914	1270
145°	1911	2055	2436	2960	3185	1196
155°	2158	2242	2414	2655	2742	995
165°	2349	2372	2425	2520	2532	662
175°	2438	2436	2428	2459	2454	231
180°	2436	2436	2436	2436	2436	

TEST NUMBER: P563793

CATALOG NUMBER: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2926.1	2926.1	2926.1	2926.1	2926.1
2.5°	2944.6	2920.5	2926.1	2921.7	2909.7
5°	2936.4	2908.8	2918.4	2908.2	2908.2
7.5°	2916.4	2886.3	2895.9	2885.6	2885.1
10°	2897.9	2867.8	2877.4	2867.1	2864.6
12.5°	2871.2	2841.2	2852.8	2840.5	2840.0
15°	2823.5	2796.0	2808.2	2797.8	2792.8
17.5°	2769.7	2739.6	2754.3	2739.9	2737.9
20°	2728.7	2698.6	2713.3	2692.8	2692.8
22.5°	2679.4	2649.3	2666.1	2639.4	2639.4
25°	2600.4	2570.3	2582.5	2559.3	2556.8
27.5°	2506.6	2477.0	2489.6	2463.5	2463.0
30°	2438.9	2411.3	2426.0	2397.8	2395.3
32.5°	2365.0	2339.4	2350.1	2321.9	2319.4
35°	2246.5	2224.0	2231.1	2205.4	2202.9
37.5°	2121.9	2098.8	2107.0	2084.9	2083.9
40°	2033.7	2018.6	2020.8	2002.8	1997.8
42.5°	1951.6	1934.6	1936.7	1918.8	1917.8
45°	1825.9	1813.4	1813.1	1795.2	1795.2
47.5°	1692.6	1683.1	1680.3	1665.4	1664.9
50°	1600.3	1592.7	1590.0	1577.1	1574.6
52.5°	1503.8	1500.3	1491.5	1480.7	1480.2
55°	1354.1	1349.1	1336.1	1328.4	1325.9
57.5°	1191.5	1181.4	1166.9	1155.6	1157.6
60°	1074.5	1064.5	1043.8	1038.6	1038.6
62.5°	961.7	949.7	928.9	921.8	925.8
65°	800.1	785.1	766.8	761.7	764.2
67.5°	653.4	639.9	620.1	620.1	618.1
70°	559.1	551.5	536.0	536.0	536.0
72.5°	475.0	471.4	460.1	460.0	458.0
75°	364.2	364.2	359.0	356.4	353.9
77.5°	272.9	273.9	271.3	268.7	264.1
80°	215.4	220.4	218.0	215.4	212.9
82.5°	162.1	167.1	166.7	162.1	161.6
85°	84.6	92.2	92.3	92.3	92.3
87.5°	23.6	33.7	39.6	40.2	41.7
90°	5.2	15.5	34.1	36.6	34.1
92.5°	74.5	271.3	535.3	232.4	168.3
95°	175.6	616.5	1882.3	974.1	579.4
97.5°	282.1	707.1	2934.1	2428.2	1783.2
100°	361.8	743.7	3261.3	3401.2	2750.1
102.5°	435.2	794.6	3376.7	4139.0	3651.9
105°	568.9	879.1	3395.0	5007.9	4802.8
107.5°	692.6	975.6	3246.6	5550.0	5618.1
110°	789.1	1045.4	3114.5	5695.5	5985.2

TEST NUMBER: P563793

CATALOG NUMBER: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	875.1	1115.0	2992.8	5666.4	6153.0
115°	1001.5	1224.5	2815.6	5450.6	6153.0
117.5°	1125.2	1334.4	2698.7	5120.8	5917.0
120°	1200.7	1405.8	2629.5	4884.2	5696.8
122.5°	1272.0	1473.0	2587.5	4630.6	5449.3
125°	1371.1	1571.1	2537.7	4282.4	5030.9
127.5°	1462.3	1658.7	2508.4	3998.3	4656.5
130°	1512.7	1715.2	2495.8	3822.7	4417.4
132.5°	1565.1	1765.6	2483.2	3664.4	4211.9
135°	1643.8	1838.6	2469.6	3457.8	3914.1
137.5°	1722.9	1907.0	2458.0	3290.2	3661.9
140°	1777.5	1949.2	2453.8	3182.3	3513.0
142.5°	1829.9	1991.4	2445.5	3084.9	3374.6
145°	1911.2	2054.7	2435.5	2959.7	3185.3
147.5°	1985.1	2112.2	2424.0	2846.3	3019.6
150°	2039.6	2152.4	2419.8	2784.7	2923.1
152.5°	2090.0	2188.4	2417.7	2727.5	2841.3
155°	2157.6	2242.2	2414.5	2655.1	2742.2
157.5°	2227.9	2286.8	2415.0	2604.6	2662.0
160°	2267.7	2316.4	2417.1	2572.7	2613.8
162.5°	2299.2	2339.7	2419.2	2547.3	2578.1
165°	2349.0	2372.0	2425.0	2519.7	2532.5
167.5°	2383.1	2399.0	2425.5	2495.9	2502.1
170°	2404.0	2411.7	2427.6	2485.3	2485.3
172.5°	2420.8	2422.3	2427.6	2472.7	2470.6
175°	2438.1	2435.5	2427.6	2459.0	2453.8
177.5°	2443.9	2437.7	2427.1	2447.9	2441.8
180°	2435.5	2435.5	2435.5	2435.5	2435.5

(END OF REPORT)