

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563140

Luminaire Tested: **SQ4-PC3-150U-100D-840-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563140
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-100D-840-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19958.6 lumens
Efficiency: N/A
Efficacy: 134.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 148.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563140
CATALOG NUMBER: SQ4-PC3-150U-100D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563140

CATALOG NUMBER: SQ4-PC3-150U-100D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	80	74	69	79	73	67	63	59	56	52	47	45	42	36	34	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	17	14	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13160	13160	13160
5°	13259	13173	13124
10°	13226	13165	13128
15°	13157	13157	13145
20°	13071	13109	13109
25°	12947	13041	13001
30°	12790	12945	12888
35°	12599	12793	12703
40°	12391	12566	12438
45°	12166	12252	12063
50°	11848	11848	11658
55°	11471	11323	11153
60°	10917	10699	10528
65°	10091	9889	9803
70°	8836	8906	8871
75°	7108	7862	7908
80°	5053	6665	6737
85°	3075	5595	5595



TEST NUMBER: P563140

CATALOG NUMBER: SQ4-PC3-150U-100D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	270.0	1.4
10°-20°	774.7	3.9
20°-30°	1173.3	5.9
30°-40°	1406.6	7.0
40°-50°	1434.2	7.2
50°-60°	1252.0	6.3
60°-70°	896.3	4.5
70°-80°	461.6	2.3
80°-90°	120.7	0.6
90°-100°	877.2	4.4
100°-110°	2371.7	11.9
110°-120°	2493.5	12.5
120°-130°	2025.4	10.1
130°-140°	1588.7	8.0
140°-150°	1219.4	6.1
150°-160°	877.0	4.4
160°-170°	535.7	2.7
170°-180°	180.6	0.9
0°-30°	2218.0	11.1
0°-40°	3624.6	18.2
0°-60°	6310.8	31.6
0°-90°	7789.4	39.0
90°-120°	5742.4	28.8
90°-150°	10575.8	53.0
90°-180°	12169.0	61.0
0°-180°	19958.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2853	2853	2853	2853	2853	
5°	2863	2835	2845	2837	2834	272
15°	2755	2732	2755	2755	2752	777
25°	2544	2526	2562	2554	2554	1171
35°	2237	2232	2272	2256	2256	1399
45°	1865	1860	1878	1854	1849	1435
55°	1426	1408	1408	1387	1387	1271
65°	924	904	906	898	898	914
75°	399	417	441	444	444	431
85°	58	89	106	108	106	79
90°	4	12	26	28	26	11
95°	136	478	1459	755	449	142
105°	441	681	2631	3881	3722	464
115°	776	949	2182	4224	4768	766
125°	1063	1218	1967	3319	3899	947
135°	1274	1425	1914	2680	3033	984
145°	1481	1592	1888	2294	2468	927
155°	1672	1738	1871	2058	2125	771
165°	1820	1838	1879	1953	1963	513
175°	1890	1888	1881	1906	1902	179
180°	1888	1888	1888	1888	1888	

TEST NUMBER: P563140

CATALOG NUMBER: SQ4-PC3-150U-100D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2852.7	2852.7	2852.7	2852.7	2852.7
2.5°	2869.6	2844.8	2852.7	2846.1	2835.8
5°	2863.2	2834.8	2844.8	2836.8	2834.2
7.5°	2842.6	2814.2	2827.3	2822.0	2819.4
10°	2823.6	2795.2	2810.4	2805.1	2802.5
12.5°	2798.3	2771.9	2789.3	2784.0	2783.5
15°	2754.9	2731.7	2754.9	2754.9	2752.3
17.5°	2700.5	2679.4	2704.2	2705.8	2704.2
20°	2662.5	2639.3	2670.4	2667.8	2670.4
22.5°	2616.0	2596.9	2630.3	2623.5	2626.0
25°	2543.6	2525.6	2562.1	2554.2	2554.2
27.5°	2458.1	2445.1	2485.0	2476.5	2476.5
30°	2401.0	2388.1	2430.1	2419.5	2419.5
32.5°	2337.6	2328.8	2368.8	2356.1	2356.1
35°	2237.2	2232.1	2271.6	2255.7	2255.7
37.5°	2133.7	2129.0	2164.9	2145.7	2139.5
40°	2057.6	2055.0	2086.7	2065.5	2065.5
42.5°	1981.6	1979.0	2006.4	1981.0	1981.0
45°	1864.8	1859.6	1878.0	1854.1	1849.0
47.5°	1737.5	1732.3	1743.8	1717.9	1715.3
50°	1650.9	1645.7	1650.9	1627.0	1624.4
52.5°	1562.1	1552.8	1553.7	1529.9	1529.4
55°	1426.3	1408.3	1407.8	1386.7	1386.7
57.5°	1282.6	1258.9	1261.0	1243.0	1240.4
60°	1183.3	1157.5	1159.6	1143.7	1141.1
62.5°	1086.1	1056.2	1062.4	1044.4	1043.9
65°	924.5	903.8	906.0	898.1	898.1
67.5°	769.2	750.1	763.9	757.5	757.0
70°	655.1	642.1	660.3	660.3	657.7
72.5°	549.4	548.9	571.6	571.6	573.2
75°	398.8	416.9	441.1	443.7	443.7
77.5°	266.2	298.3	324.9	325.9	325.4
80°	190.2	226.3	250.9	256.2	253.6
82.5°	128.9	167.1	187.5	192.8	190.2
85°	58.1	89.1	105.7	108.2	105.7
87.5°	17.7	37.9	47.5	47.8	43.3
90°	4.1	12.0	26.4	28.4	26.4
92.5°	57.7	210.3	414.9	180.1	130.4
95°	136.1	477.8	1458.8	754.9	449.0
97.5°	218.6	548.0	2273.9	1881.8	1382.0
100°	280.4	576.4	2527.4	2635.8	2131.3
102.5°	337.3	615.8	2616.8	3207.6	2830.2
105°	440.9	681.3	2631.1	3881.0	3722.1
107.5°	536.8	756.1	2516.1	4301.1	4354.0
110°	611.5	810.2	2413.7	4413.9	4638.4

TEST NUMBER: P563140

CATALOG NUMBER: SQ4-PC3-150U-100D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	678.2	864.1	2319.4	4391.4	4768.4
115°	776.1	948.9	2182.1	4224.1	4768.4
117.5°	872.0	1034.1	2091.4	3968.5	4585.6
120°	930.5	1089.4	2037.8	3785.2	4414.9
122.5°	985.8	1141.5	2005.3	3588.6	4223.1
125°	1062.6	1217.5	1966.7	3318.8	3898.8
127.5°	1133.3	1285.5	1943.9	3098.6	3608.7
130°	1172.3	1329.2	1934.2	2962.5	3423.4
132.5°	1212.9	1368.3	1924.4	2839.8	3264.1
135°	1273.9	1424.9	1913.9	2679.7	3033.3
137.5°	1335.2	1477.9	1904.9	2549.8	2837.9
140°	1377.5	1510.6	1901.7	2466.2	2722.5
142.5°	1418.1	1543.3	1895.2	2390.7	2615.2
145°	1481.1	1592.4	1887.5	2293.7	2468.5
147.5°	1538.4	1636.9	1878.5	2205.8	2340.1
150°	1580.7	1668.1	1875.3	2158.1	2265.4
152.5°	1619.7	1696.0	1873.6	2113.8	2202.0
155°	1672.1	1737.7	1871.2	2057.6	2125.2
157.5°	1726.5	1772.2	1871.6	2018.5	2063.0
160°	1757.4	1795.2	1873.2	1993.8	2025.6
162.5°	1781.8	1813.2	1874.9	1974.1	1998.0
165°	1820.4	1838.3	1879.3	1952.7	1962.6
167.5°	1846.8	1859.1	1879.7	1934.3	1939.1
170°	1863.1	1869.0	1881.4	1926.1	1926.1
172.5°	1876.1	1877.3	1881.4	1916.3	1914.7
175°	1889.5	1887.5	1881.4	1905.7	1901.7
177.5°	1894.0	1889.2	1881.0	1897.1	1892.3
180°	1887.5	1887.5	1887.5	1887.5	1887.5

(END OF REPORT)