

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562874

Luminaire Tested: **SQ4-PC3-0U-125D-840-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562874
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-125D-840-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4967.7 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 43.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562874
CATALOG NUMBER: SQ4-PC3-0U-125D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562874

CATALOG NUMBER: SQ4-PC3-0U-125D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16794	16794	16794
5°	16920	16810	16748
10°	16879	16800	16753
15°	16790	16790	16775
20°	16680	16729	16729
25°	16522	16642	16591
30°	16321	16518	16447
35°	16078	16325	16211
40°	15813	16035	15874
45°	15526	15635	15394
50°	15120	15120	14877
55°	14639	14450	14232
60°	13932	13653	13435
65°	12878	12621	12509
70°	11276	11365	11322
75°	9072	10035	10092
80°	6445	8506	8597
85°	3927	7135	7135



TEST NUMBER: P562874

CATALOG NUMBER: SQ4-PC3-0U-125D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.3	3.5
10°-20°	494.3	10.0
20°-30°	748.6	15.1
30°-40°	897.5	18.1
40°-50°	915.1	18.4
50°-60°	798.9	16.1
60°-70°	571.9	11.5
70°-80°	294.6	5.9
80°-90°	74.5	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1415.2	28.5
0°-40°	2312.7	46.6
0°-60°	4026.7	81.1
0°-90°	4967.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4967.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1820	1820	1820	1820	1820	
5°	1827	1809	1815	1810	1808	173
15°	1758	1743	1758	1758	1756	496
25°	1623	1612	1635	1630	1630	747
35°	1428	1424	1449	1439	1439	893
45°	1190	1187	1198	1183	1180	916
55°	910	899	898	885	885	811
65°	590	577	578	573	573	583
75°	254	266	282	283	283	275
85°	37	57	67	69	67	52
90°	0	0	0	0	0	



TEST NUMBER: P562874

CATALOG NUMBER: SQ4-PC3-0U-125D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1820.2	1820.2	1820.2	1820.2	1820.2
2.5°	1831.0	1815.2	1820.2	1816.0	1809.4
5°	1826.9	1808.8	1815.1	1810.0	1808.4
7.5°	1813.8	1795.7	1804.0	1800.6	1799.0
10°	1801.7	1783.5	1793.2	1789.8	1788.2
12.5°	1785.5	1768.7	1779.7	1776.4	1776.0
15°	1757.8	1743.0	1757.8	1757.8	1756.2
17.5°	1723.1	1709.6	1725.5	1726.5	1725.5
20°	1698.9	1684.0	1703.9	1702.3	1703.9
22.5°	1669.2	1657.0	1678.3	1673.9	1675.6
25°	1623.0	1611.5	1634.8	1629.8	1629.8
27.5°	1568.4	1560.2	1585.6	1580.2	1580.2
30°	1532.0	1523.8	1550.5	1543.8	1543.8
32.5°	1491.6	1485.9	1511.4	1503.3	1503.3
35°	1427.5	1424.2	1449.4	1439.3	1439.3
37.5°	1361.4	1358.5	1381.3	1369.1	1365.1
40°	1312.9	1311.3	1331.4	1318.0	1318.0
42.5°	1264.4	1262.7	1280.2	1264.0	1264.0
45°	1189.9	1186.6	1198.3	1183.1	1179.8
47.5°	1108.6	1105.3	1112.7	1096.1	1094.5
50°	1053.4	1050.1	1053.4	1038.1	1036.5
52.5°	996.7	990.8	991.3	976.2	975.8
55°	910.1	898.6	898.3	884.8	884.8
57.5°	818.4	803.3	804.6	793.1	791.4
60°	755.0	738.6	739.9	729.7	728.1
62.5°	693.0	673.9	677.9	666.4	666.1
65°	589.9	576.7	578.1	573.0	573.0
67.5°	490.8	478.6	487.4	483.4	483.0
70°	418.0	409.7	421.3	421.3	419.7
72.5°	350.6	350.2	364.7	364.7	365.7
75°	254.5	266.0	281.5	283.1	283.1
77.5°	169.9	190.3	207.3	208.0	207.6
80°	121.3	144.4	160.1	163.4	161.8
82.5°	82.2	106.6	119.7	123.0	121.3
85°	37.1	56.9	67.4	69.1	67.4
87.5°	10.8	22.7	27.0	26.9	24.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)