

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P571637

Luminaire Tested: **DL2-BB-M-0U-XD-935-UNV-X-BSL6-W-6**

Issue Date: 3/5/2020


Test Information

Test Method: LM-79-2019
Report Number: P571637
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-1)
Test Lab: INNOVATION CENTER
Issue Date: 3/5/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: DL2-BB-M-0U-XD-935-UNV-X-BSL6-W-6
Description: CORELITE DL2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: -
Ballast/Driver: BODINE 6 WATT (OUTPUT POWER) EMERGENCY BATTERY PACK

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 783.1 lumens
Efficiency: N/A
Efficacy: 130.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.17 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 6' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P571637
CATALOG NUMBER: DL2-BB-M-0U-XD-935-UNV-X-BSL6-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P571637

CATALOG NUMBER: DL2-BB-M-OU-XD-935-UNV-X-BSL6-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84				84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70				70
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63				63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	60	58				58
7	78	67	61	56	76	67	60	56	65	59	55	64	59	55	63	58	55	53				53
8	73	63	56	51	72	62	55	51	61	55	51	60	54	51	59	54	50	49				49
9	69	58	52	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45				45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	47	43	42				42

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5646	5646	5646
5°	5685	5621	5693
10°	5750	5699	5746
15°	5854	5776	5750
20°	5869	5745	5638
25°	5715	5576	5488
30°	5399	5254	5113
35°	4787	4731	4596
40°	3908	3853	3698
45°	2303	2719	2143
50°	777	1515	692
55°	263	542	278
60°	26	159	9
65°	0	10	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P571637

CATALOG NUMBER: DL2-BB-M-OU-XD-935-UNV-X-BSL6-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.1	6.4
10°-20°	146.7	18.7
20°-30°	215.9	27.6
30°-40°	220.6	28.2
40°-50°	126.8	16.2
50°-60°	22.2	2.8
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	412.7	52.7
0°-40°	633.3	80.9
0°-60°	782.3	99.9
0°-90°	783.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	783.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	524	524	524	524	524	
5°	526	525	520	528	527	50
15°	525	530	518	519	516	148
25°	481	486	470	464	462	220
35°	364	366	360	354	350	225
45°	151	176	179	169	141	118
55°	14	17	29	16	15	16
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P571637

CATALOG NUMBER: DL2-BB-M-OU-XD-935-UNV-X-BSL6-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	524.5	524.5	524.5	524.5	524.5
2.5°	526.7	525.5	521.4	526.1	524.8
5°	526.1	525.0	520.2	527.7	526.9
7.5°	525.8	524.9	521.7	528.2	526.6
10°	526.1	526.1	521.4	527.2	525.7
12.5°	526.7	528.2	520.5	525.0	522.9
15°	525.3	529.9	518.3	518.6	516.0
17.5°	519.6	525.8	510.0	506.2	502.2
20°	512.4	518.9	501.5	495.6	492.2
22.5°	501.5	507.7	489.4	484.4	480.6
25°	481.2	485.5	469.5	464.4	462.1
27.5°	454.7	456.9	443.0	437.7	433.9
30°	434.4	434.4	422.7	416.8	411.4
32.5°	409.2	408.0	400.3	393.4	388.4
35°	364.3	366.2	360.0	354.0	349.8
37.5°	314.6	316.4	310.0	303.3	300.4
40°	278.1	279.6	274.2	267.1	263.2
42.5°	233.1	241.4	236.4	228.7	223.6
45°	151.3	176.1	178.6	169.4	140.8
47.5°	78.9	104.8	123.9	94.6	66.3
50°	46.4	63.2	90.5	51.6	41.3
52.5°	29.9	37.2	63.6	33.0	27.9
55°	14.0	16.7	28.9	16.3	14.8
57.5°	5.2	7.8	13.0	7.9	5.7
60°	1.2	3.5	7.4	2.3	0.4
62.5°	0.2	1.0	4.3	0.5	0.1
65°	0.0	0.0	0.4	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)