

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P933892

Luminaire Tested: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P933892
REPORT IS A COMBINATION OF REPORTS P933676 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5589.6 lumens
Efficiency: N/A
Efficacy: 127.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P933892

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K

Luminous Intensity Polar Plot



TEST NUMBER: P933892

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66		
1	101	97	93	89	95	91	88	85	81	78	76	71	69	68	62	61	60	55		
2	92	85	78	73	87	80	74	70	71	67	63	63	59	56	55	52	50	46		
3	84	75	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39		
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	43	40	37	34		
5	71	59	50	44	66	56	48	43	50	44	39	44	39	35	39	35	32	29		
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28	26		
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25	23		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18		
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6552	6552	6552	6552
5°	6601	6613	6601	5200
10°	6556	6515	6556	4657
15°	6485	6373	6485	5322
20°	6349	6206	6349	5333
25°	6072	5962	6072	5220
30°	5713	5760	5713	4972
35°	5093	5504	5093	4699
40°	4244	5202	4244	4494
45°	3792	4849	3792	4256
50°	4028	4429	4028	4018
55°	3790	3975	3790	3881
60°	3907	3376	3907	3554
65°	3542	2791	3542	3120
70°	2452	2224	2452	2615
75°	2151	1645	2151	1969
80°	1732	1087	1732	1183
85°	997	576	997	489

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 5812 cd/sqm

TEST NUMBER: P933892

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.5	2.3
10°-20°	361.9	6.5
20°-30°	559.4	10.0
30°-40°	667.9	11.9
40°-50°	671.8	12.0
50°-60°	584.5	10.5
60°-70°	414.4	7.4
70°-80°	219.3	3.9
80°-90°	55.8	1.0
90°-100°	144.9	2.6
100°-110°	381.0	6.8
110°-120°	395.0	7.1
120°-130°	316.9	5.7
130°-140°	248.6	4.4
140°-150°	190.8	3.4
150°-160°	137.4	2.5
160°-170°	84.1	1.5
170°-180°	28.4	0.5
0°-30°	1048.8	18.8
0°-40°	1716.7	30.7
0°-60°	2973.0	53.2
0°-90°	3662.4	65.5
90°-120°	920.9	16.5
90°-150°	1677.2	30.0
90°-180°	1927.0	34.5
0°-180°	5589.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1412	1412	1412	1412	1412	
5°	1419	1463	1419	1150	1419	135
15°	1355	1450	1355	1210	1355	381
25°	1193	1352	1193	1184	1193	548
35°	907	1206	907	1030	907	561
45°	585	994	585	872	585	469
55°	477	734	477	716	477	438
65°	331	442	331	494	331	317
75°	126	210	126	251	126	132
85°	21	54	21	45	21	29
90°	2	8	2	8	2	3
95°	19	88	19	88	19	21
105°	69	596	69	596	69	73
115°	122	768	122	768	122	120
125°	170	612	170	612	170	151
135°	202	475	202	475	202	156
145°	234	385	234	385	234	147
155°	265	332	265	332	265	122
165°	286	309	286	309	286	81
175°	297	299	297	299	297	28
180°	297	297	297	297	297	

TEST NUMBER: P933892

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1
2.5°	1424.1	1424.1	1432.1	1434.8	1434.8	1430.8	1426.8	1430.8	1442.8	1446.8	1445.5
5°	1418.8	1429.5	1444.2	1446.8	1449.5	1448.2	1445.5	1448.2	1461.5	1464.2	1465.5
7.5°	1408.0	1428.2	1446.8	1450.9	1454.9	1450.9	1449.5	1452.2	1465.5	1468.2	1468.2
10°	1394.7	1422.8	1444.2	1446.8	1450.9	1446.8	1446.8	1452.2	1465.5	1468.2	1469.5
12.5°	1376.0	1414.7	1434.8	1437.4	1442.8	1441.5	1440.1	1445.5	1458.8	1461.5	1461.5
15°	1354.7	1400.1	1418.8	1421.4	1430.8	1428.2	1428.2	1433.4	1448.2	1452.2	1450.9
17.5°	1325.3	1381.4	1402.8	1406.8	1413.4	1412.1	1413.4	1418.8	1432.1	1434.8	1436.1
20°	1291.8	1356.0	1381.4	1385.3	1392.0	1392.0	1392.0	1398.7	1412.1	1417.4	1417.4
22.5°	1246.4	1329.3	1356.0	1358.6	1366.7	1366.7	1369.3	1378.7	1390.7	1392.0	1392.0
25°	1193.0	1299.9	1322.6	1330.6	1338.6	1342.6	1346.6	1352.0	1356.0	1354.7	1356.0
27.5°	1136.9	1262.4	1291.8	1297.2	1307.8	1311.9	1317.2	1318.6	1319.9	1323.9	1321.3
30°	1074.1	1210.3	1254.5	1259.8	1277.2	1279.9	1274.5	1277.2	1283.8	1286.5	1289.2
32.5°	1003.3	1132.9	1215.7	1227.8	1243.8	1235.7	1234.4	1238.4	1249.1	1249.1	1251.8
35°	907.1	1072.8	1179.7	1190.3	1202.4	1193.0	1198.4	1199.7	1206.4	1210.3	1209.0
37.5°	801.6	1020.7	1142.2	1150.3	1159.6	1147.6	1155.6	1159.6	1164.9	1162.2	1162.2
40°	708.1	939.1	1098.2	1103.5	1111.5	1102.2	1110.1	1112.8	1115.5	1112.8	1111.5
42.5°	638.5	849.7	1051.4	1058.1	1052.7	1059.4	1062.0	1067.4	1063.4	1058.1	1058.1
45°	585.2	825.6	1000.6	1008.6	1000.6	1011.3	1015.3	1015.3	1003.3	1000.6	999.3
47.5°	567.8	777.5	949.9	949.9	945.8	959.2	965.9	956.6	944.5	940.5	940.5
50°	566.4	724.1	880.4	875.1	893.7	909.7	903.1	893.7	884.3	869.7	869.7
52.5°	514.3	658.7	790.9	810.9	840.3	849.7	838.9	829.7	813.6	806.9	801.6
55°	476.9	590.5	709.4	749.5	780.2	792.2	772.2	762.8	738.7	734.7	732.1
57.5°	468.9	491.6	634.6	685.3	722.7	721.4	709.4	692.0	672.0	668.0	666.6
60°	430.2	355.4	554.4	614.5	653.3	649.3	638.5	622.5	603.9	601.2	598.5
62.5°	390.1	257.9	463.5	531.7	586.4	585.2	575.8	551.8	538.3	531.7	526.4
65°	331.3	216.4	330.0	442.2	521.0	523.7	503.7	486.2	471.6	463.5	462.2
67.5°	252.5	176.4	223.1	368.7	458.3	455.6	430.2	422.2	403.5	399.5	391.4
70°	187.0	117.5	155.0	299.3	396.8	390.1	370.0	360.8	343.3	334.0	328.7
72.5°	155.0	94.8	113.5	232.5	334.0	326.0	308.6	297.9	283.3	275.2	269.8
75°	125.6	100.2	86.9	172.3	271.2	265.8	249.8	239.1	227.1	216.4	217.7
77.5°	92.2	93.5	69.4	126.9	215.1	207.1	197.7	184.4	179.0	168.3	168.3
80°	69.4	73.5	52.1	86.9	155.0	155.0	146.9	137.6	128.3	122.9	122.9
82.5°	46.7	46.7	38.7	54.8	105.6	101.5	96.2	93.5	88.1	85.5	85.5
85°	21.4	26.7	24.0	33.4	57.5	60.2	60.2	57.5	56.1	53.5	54.8
87.5°	6.7	12.1	14.7	18.7	29.4	30.8	32.1	32.1	32.1	33.4	33.4
90°	2.0	3.6	5.2	5.6	8.8	13.0	15.1	13.4	10.1	7.6	7.6
92.5°	8.0	21.5	35.2	38.5	54.2	75.0	85.4	74.8	53.8	37.9	36.5
95°	19.1	43.9	68.8	75.0	133.2	210.8	249.6	222.7	169.0	128.7	124.1
97.5°	33.2	55.1	76.9	82.4	179.4	308.8	373.5	356.6	322.6	297.1	288.4
100°	43.9	63.7	83.6	88.5	196.2	339.7	411.5	412.8	415.3	417.2	406.9
102.5°	53.1	71.6	90.1	94.7	204.0	349.6	422.4	444.0	487.2	519.7	510.8
105°	68.6	84.4	100.1	104.0	209.8	350.7	421.2	469.7	566.7	639.4	634.7
107.5°	84.6	99.2	113.8	117.5	210.8	335.1	397.2	464.8	600.2	701.7	702.9
110°	95.4	108.6	121.8	125.1	209.2	321.2	377.3	452.9	604.2	717.6	722.6

TEST NUMBER: P933892

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	106.0	118.5	131.1	134.3	209.3	309.2	359.2	436.5	591.3	707.5	715.1
115°	121.9	133.5	145.1	148.0	211.2	295.3	337.3	411.9	561.1	673.0	683.6
117.5°	137.6	148.2	158.8	161.5	215.1	286.6	322.4	389.7	524.3	625.3	637.0
120°	146.8	156.8	166.7	169.2	218.3	283.8	316.4	377.9	500.9	593.1	604.5
122.5°	155.8	165.8	175.9	178.4	222.9	282.2	311.8	367.2	478.0	561.0	572.3
125°	169.6	178.8	187.8	190.1	229.1	281.0	306.9	353.9	448.0	518.5	528.9
127.5°	180.8	189.9	199.2	201.5	235.3	280.2	302.7	343.1	423.9	484.5	493.2
130°	186.8	196.7	206.6	209.1	239.7	280.7	301.1	337.0	409.0	462.8	470.9
132.5°	192.9	202.9	212.7	215.2	243.4	281.0	299.7	331.9	396.2	444.5	451.8
135°	202.1	211.2	220.2	222.5	247.4	280.7	297.3	324.3	378.2	418.6	424.8
137.5°	211.5	220.4	229.4	231.7	253.4	282.4	296.9	319.7	365.2	399.4	404.5
140°	219.2	227.5	235.8	237.8	257.1	282.7	295.5	315.2	354.6	384.1	388.8
142.5°	225.3	232.9	240.5	242.4	260.2	283.8	295.5	312.8	347.4	373.3	377.4
145°	234.5	241.1	247.7	249.4	264.1	283.8	293.5	307.7	336.0	357.2	360.3
147.5°	243.6	250.1	256.6	258.2	269.9	285.7	293.5	304.7	326.9	343.5	346.1
150°	249.6	255.5	261.3	262.7	273.0	286.6	293.5	302.9	321.7	335.8	337.8
152.5°	255.8	260.2	264.6	265.7	275.0	287.3	293.5	301.5	317.5	329.6	331.2
155°	264.9	268.2	271.5	272.3	279.4	288.8	293.5	299.9	312.6	322.2	323.2
157.5°	271.7	274.9	278.1	278.9	283.8	290.2	293.5	298.5	308.4	315.8	316.5
160°	276.3	278.8	281.3	281.9	285.8	290.9	293.5	297.8	306.3	312.6	313.0
162.5°	280.9	282.8	284.6	285.1	287.8	291.6	293.5	297.1	304.3	309.7	310.1
165°	286.0	287.6	289.3	289.7	291.0	292.7	293.5	296.1	301.2	305.1	305.5
167.5°	290.5	291.3	292.1	292.3	293.4	294.8	295.5	297.2	300.6	303.1	303.3
170°	293.5	294.3	295.1	295.3	295.4	295.5	295.5	297.2	300.6	303.1	303.1
172.5°	295.1	295.3	295.5	295.5	295.5	295.5	295.5	296.8	299.5	301.5	301.3
175°	297.3	297.3	297.3	297.3	296.7	295.9	295.5	296.3	298.0	299.3	299.3
177.5°	297.3	297.3	297.3	297.3	296.8	296.2	295.9	296.6	297.9	298.9	298.7
180°	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3

TEST NUMBER: P933892

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1
2.5°	1448.2	1444.2	1448.2	1445.5	1446.8	1442.8	1430.8	1426.8	1430.8	1434.8	1434.8
5°	1465.5	1462.8	1465.5	1465.5	1464.2	1461.5	1448.2	1445.5	1448.2	1449.5	1446.8
7.5°	1470.9	1466.9	1470.9	1468.2	1468.2	1465.5	1452.2	1449.5	1450.9	1454.9	1450.9
10°	1470.9	1466.9	1470.9	1469.5	1468.2	1465.5	1452.2	1446.8	1446.8	1450.9	1446.8
12.5°	1464.2	1461.5	1464.2	1461.5	1461.5	1458.8	1445.5	1440.1	1441.5	1442.8	1437.4
15°	1453.5	1449.5	1453.5	1450.9	1452.2	1448.2	1433.4	1428.2	1428.2	1430.8	1421.4
17.5°	1437.4	1432.1	1437.4	1436.1	1434.8	1432.1	1418.8	1413.4	1412.1	1413.4	1406.8
20°	1418.8	1414.7	1418.8	1417.4	1417.4	1412.1	1398.7	1392.0	1392.0	1392.0	1385.3
22.5°	1389.4	1385.3	1389.4	1392.0	1392.0	1390.7	1378.7	1369.3	1366.7	1366.7	1358.6
25°	1356.0	1352.0	1356.0	1356.0	1354.7	1356.0	1352.0	1346.6	1342.6	1338.6	1330.6
27.5°	1323.9	1321.3	1323.9	1321.3	1323.9	1319.9	1318.6	1317.2	1311.9	1307.8	1297.2
30°	1291.8	1289.2	1291.8	1289.2	1286.5	1283.8	1277.2	1274.5	1279.9	1277.2	1259.8
32.5°	1251.8	1249.1	1251.8	1251.8	1249.1	1249.1	1238.4	1234.4	1235.7	1243.8	1227.8
35°	1210.3	1206.4	1210.3	1209.0	1210.3	1206.4	1199.7	1198.4	1193.0	1202.4	1190.3
37.5°	1162.2	1158.2	1162.2	1162.2	1162.2	1164.9	1159.6	1155.6	1147.6	1159.6	1150.3
40°	1112.8	1107.5	1112.8	1111.5	1112.8	1115.5	1112.8	1110.1	1102.2	1111.5	1103.5
42.5°	1056.8	1055.4	1056.8	1058.1	1058.1	1063.4	1067.4	1062.0	1059.4	1052.7	1058.1
45°	996.6	993.9	996.6	999.3	1000.6	1003.3	1015.3	1015.3	1011.3	1000.6	1008.6
47.5°	932.5	925.8	932.5	940.5	940.5	944.5	956.6	965.9	959.2	945.8	949.9
50°	864.3	865.7	864.3	869.7	869.7	884.3	893.7	903.1	909.7	893.7	875.1
52.5°	797.6	796.2	797.6	801.6	806.9	813.6	829.7	838.9	849.7	840.3	810.9
55°	730.8	733.5	730.8	732.1	734.7	738.7	762.8	772.2	792.2	780.2	749.5
57.5°	663.9	659.9	663.9	666.6	668.0	672.0	692.0	709.4	721.4	722.7	685.3
60°	586.4	581.2	586.4	598.5	601.2	603.9	622.5	638.5	649.3	653.3	614.5
62.5°	518.3	509.0	518.3	526.4	531.7	538.3	551.8	575.8	585.2	586.4	531.7
65°	446.2	442.2	446.2	462.2	463.5	471.6	486.2	503.7	523.7	521.0	442.2
67.5°	380.8	380.8	380.8	391.4	399.5	403.5	422.2	430.2	455.6	458.3	368.7
70°	320.6	319.3	320.6	328.7	334.0	343.3	360.8	370.0	390.1	396.8	299.3
72.5°	263.1	261.8	263.1	269.8	275.2	283.3	297.9	308.6	326.0	334.0	232.5
75°	212.4	209.8	212.4	217.7	216.4	227.1	239.1	249.8	265.8	271.2	172.3
77.5°	162.9	162.9	162.9	168.3	168.3	179.0	184.4	197.7	207.1	215.1	126.9
80°	121.6	120.2	121.6	122.9	122.9	128.3	137.6	146.9	155.0	155.0	86.9
82.5°	85.5	82.9	85.5	85.5	85.5	88.1	93.5	96.2	101.5	105.6	54.8
85°	53.5	53.5	53.5	54.8	53.5	56.1	57.5	60.2	60.2	57.5	33.4
87.5°	34.8	33.4	34.8	33.4	33.4	32.1	32.1	32.1	30.8	29.4	18.7
90°	7.6	7.6	7.6	7.6	7.6	10.1	13.4	15.1	13.0	8.8	5.6
92.5°	30.4	24.3	30.4	36.5	37.9	53.8	74.8	85.4	75.0	54.2	38.5
95°	105.9	87.5	105.9	124.1	128.7	169.0	222.7	249.6	210.8	133.2	75.0
97.5°	253.6	218.8	253.6	288.4	297.1	322.6	356.6	373.5	308.8	179.4	82.4
100°	365.4	324.0	365.4	406.9	417.2	415.3	412.8	411.5	339.7	196.2	88.5
102.5°	475.4	439.9	475.4	510.8	519.7	487.2	444.0	422.4	349.6	204.0	94.7
105°	615.6	596.5	615.6	634.7	639.4	566.7	469.7	421.2	350.7	209.8	104.0
107.5°	707.5	712.0	707.5	702.9	701.7	600.2	464.8	397.2	335.1	210.8	117.5
110°	742.4	762.3	742.4	722.6	717.6	604.2	452.9	377.3	321.2	209.2	125.1

TEST NUMBER: P933892

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	745.6	776.1	745.6	715.1	707.5	591.3	436.5	359.2	309.2	209.3	134.3
115°	725.9	768.1	725.9	683.6	673.0	561.1	411.9	337.3	295.3	211.2	148.0
117.5°	684.0	730.9	684.0	637.0	625.3	524.3	389.7	322.4	286.6	215.1	161.5
120°	650.1	695.7	650.1	604.5	593.1	500.9	377.9	316.4	283.8	218.3	169.2
122.5°	617.2	662.1	617.2	572.3	561.0	478.0	367.2	311.8	282.2	222.9	178.4
125°	570.3	611.7	570.3	528.9	518.5	448.0	353.9	306.9	281.0	229.1	190.1
127.5°	528.1	563.0	528.1	493.2	484.5	423.9	343.1	302.7	280.2	235.3	201.5
130°	503.2	535.4	503.2	470.9	462.8	409.0	337.0	301.1	280.7	239.7	209.1
132.5°	480.7	509.6	480.7	451.8	444.5	396.2	331.9	299.7	281.0	243.4	215.2
135°	449.7	474.6	449.7	424.8	418.6	378.2	324.3	297.3	280.7	247.4	222.5
137.5°	424.9	445.3	424.9	404.5	399.4	365.2	319.7	296.9	282.4	253.4	231.7
140°	407.9	427.0	407.9	388.8	384.1	354.6	315.2	295.5	282.7	257.1	237.8
142.5°	393.8	410.2	393.8	377.4	373.3	347.4	312.8	295.5	283.8	260.2	242.4
145°	372.7	385.1	372.7	360.3	357.2	336.0	307.7	293.5	283.8	264.1	249.4
147.5°	356.4	366.7	356.4	346.1	343.5	326.9	304.7	293.5	285.7	269.9	258.2
150°	346.2	354.6	346.2	337.8	335.8	321.7	302.9	293.5	286.6	273.0	262.7
152.5°	337.4	343.7	337.4	331.2	329.6	317.5	301.5	293.5	287.3	275.0	265.7
155°	327.4	331.6	327.4	323.2	322.2	312.6	299.9	293.5	288.8	279.4	272.3
157.5°	319.5	322.4	319.5	316.5	315.8	308.4	298.5	293.5	290.2	283.8	278.9
160°	314.7	316.4	314.7	313.0	312.6	306.3	297.8	293.5	290.9	285.8	281.9
162.5°	311.6	313.2	311.6	310.1	309.7	304.3	297.1	293.5	291.6	287.8	285.1
165°	307.2	308.9	307.2	305.5	305.1	301.2	296.1	293.5	292.7	291.0	289.7
167.5°	304.0	304.7	304.0	303.3	303.1	300.6	297.2	295.5	294.8	293.4	292.3
170°	303.1	303.1	303.1	303.1	303.1	300.6	297.2	295.5	295.5	295.4	295.3
172.5°	300.7	300.1	300.7	301.3	301.5	299.5	296.8	295.5	295.5	295.5	295.5
175°	299.3	299.3	299.3	299.3	299.3	298.0	296.3	295.5	295.9	296.7	297.3
177.5°	298.0	297.3	298.0	298.7	298.9	297.9	296.6	295.9	296.2	296.8	297.3
180°	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3

TEST NUMBER: P933892

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1
2.5°	1432.1	1424.1	1424.1	1410.7	1405.5	1401.4	1394.7	1374.7	1369.3	1364.0	1372.0
5°	1444.2	1429.5	1418.8	1394.7	1374.7	1366.7	1341.3	1293.2	1261.1	1237.0	1223.7
7.5°	1446.8	1428.2	1408.0	1370.7	1322.6	1301.2	1223.7	1135.5	1111.5	1090.1	1076.8
10°	1444.2	1422.8	1394.7	1338.6	1225.1	1187.6	1110.1	1052.7	1038.0	1034.0	1038.0
12.5°	1434.8	1414.7	1376.0	1282.5	1123.5	1098.2	1052.7	1019.3	1016.6	1023.3	1059.4
15°	1418.8	1400.1	1354.7	1207.6	1067.4	1048.7	1016.6	1004.7	1019.3	1066.1	1174.3
17.5°	1402.8	1381.4	1325.3	1134.2	1024.7	1011.3	988.6	1012.6	1095.5	1158.2	1194.3
20°	1381.4	1356.0	1291.8	1080.8	993.9	982.0	971.2	1079.5	1142.2	1164.9	1184.9
22.5°	1356.0	1329.3	1246.4	1043.4	961.8	952.6	959.2	1116.8	1142.2	1158.2	1175.6
25°	1322.6	1299.9	1193.0	1014.0	936.5	925.8	951.2	1112.8	1127.6	1131.6	1166.3
27.5°	1291.8	1262.4	1136.9	987.2	905.8	901.8	957.9	1095.5	1106.2	1110.1	1147.6
30°	1254.5	1210.3	1074.1	959.2	873.7	872.4	959.2	1074.1	1071.4	1082.2	1119.5
32.5°	1215.7	1132.9	1003.3	924.5	843.0	841.6	949.9	1042.0	1039.3	1054.1	1082.2
35°	1179.7	1072.8	907.1	884.3	804.3	805.6	927.2	1004.7	1006.0	1019.3	1036.7
37.5°	1142.2	1020.7	801.6	840.3	766.8	766.8	896.4	969.9	967.2	971.2	995.3
40°	1098.2	939.1	708.1	782.9	732.1	728.1	859.0	932.5	923.1	921.8	955.2
42.5°	1051.4	849.7	638.5	706.8	692.0	686.6	813.6	887.0	869.7	873.7	916.4
45°	1000.6	825.6	585.2	597.2	650.6	646.6	764.1	834.9	822.9	833.7	877.7
47.5°	949.9	777.5	567.8	495.6	606.6	605.2	709.4	784.2	777.5	788.2	834.9
50°	880.4	724.1	566.4	424.8	557.1	562.4	643.9	734.7	734.7	744.1	793.5
52.5°	790.9	658.7	514.3	384.8	499.6	515.6	586.4	692.0	694.7	704.1	748.1
55°	709.4	590.5	476.9	354.0	431.5	466.2	530.4	647.9	653.3	662.6	702.7
57.5°	634.6	491.6	468.9	317.9	368.7	402.1	481.0	605.2	607.9	615.8	654.6
60°	554.4	355.4	430.2	279.2	313.9	339.3	435.6	554.4	563.7	569.1	602.5
62.5°	463.5	257.9	390.1	252.5	287.2	292.5	398.1	506.4	518.3	522.4	542.4
65°	330.0	216.4	331.3	229.8	259.2	260.6	358.1	456.9	467.6	474.3	488.9
67.5°	223.1	176.4	252.5	208.4	237.8	239.1	319.3	399.5	414.1	419.5	428.9
70°	155.0	117.5	187.0	185.7	213.7	216.4	277.9	347.3	360.8	364.7	370.0
72.5°	113.5	94.8	155.0	167.0	188.3	191.0	235.2	288.5	301.9	306.0	308.6
75°	86.9	100.2	125.6	145.6	160.4	161.7	192.3	235.2	244.5	247.1	248.5
77.5°	69.4	93.5	92.2	117.5	130.9	128.3	151.0	181.7	189.7	189.7	189.7
80°	52.1	73.5	69.4	84.2	96.2	93.5	108.2	129.6	132.3	135.0	133.6
82.5°	38.7	46.7	46.7	53.5	64.1	61.5	72.1	84.2	84.2	84.2	86.9
85°	24.0	26.7	21.4	28.1	36.1	34.8	40.0	45.4	46.7	46.7	44.1
87.5°	14.7	12.1	6.7	10.7	16.0	16.0	18.7	20.0	18.7	18.7	18.7
90°	5.2	3.6	2.0	3.6	5.2	5.6	8.8	13.0	15.1	13.4	10.1
92.5°	35.2	21.5	8.0	21.5	35.2	38.5	54.2	75.0	85.4	74.8	53.8
95°	68.8	43.9	19.1	43.9	68.8	75.0	133.2	210.8	249.6	222.7	169.0
97.5°	76.9	55.1	33.2	55.1	76.9	82.4	179.4	308.8	373.5	356.6	322.6
100°	83.6	63.7	43.9	63.7	83.6	88.5	196.2	339.7	411.5	412.8	415.3
102.5°	90.1	71.6	53.1	71.6	90.1	94.7	204.0	349.6	422.4	444.0	487.2
105°	100.1	84.4	68.6	84.4	100.1	104.0	209.8	350.7	421.2	469.7	566.7
107.5°	113.8	99.2	84.6	99.2	113.8	117.5	210.8	335.1	397.2	464.8	600.2
110°	121.8	108.6	95.4	108.6	121.8	125.1	209.2	321.2	377.3	452.9	604.2

TEST NUMBER: P933892

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	131.1	118.5	106.0	118.5	131.1	134.3	209.3	309.2	359.2	436.5	591.3
115°	145.1	133.5	121.9	133.5	145.1	148.0	211.2	295.3	337.3	411.9	561.1
117.5°	158.8	148.2	137.6	148.2	158.8	161.5	215.1	286.6	322.4	389.7	524.3
120°	166.7	156.8	146.8	156.8	166.7	169.2	218.3	283.8	316.4	377.9	500.9
122.5°	175.9	165.8	155.8	165.8	175.9	178.4	222.9	282.2	311.8	367.2	478.0
125°	187.8	178.8	169.6	178.8	187.8	190.1	229.1	281.0	306.9	353.9	448.0
127.5°	199.2	189.9	180.8	189.9	199.2	201.5	235.3	280.2	302.7	343.1	423.9
130°	206.6	196.7	186.8	196.7	206.6	209.1	239.7	280.7	301.1	337.0	409.0
132.5°	212.7	202.9	192.9	202.9	212.7	215.2	243.4	281.0	299.7	331.9	396.2
135°	220.2	211.2	202.1	211.2	220.2	222.5	247.4	280.7	297.3	324.3	378.2
137.5°	229.4	220.4	211.5	220.4	229.4	231.7	253.4	282.4	296.9	319.7	365.2
140°	235.8	227.5	219.2	227.5	235.8	237.8	257.1	282.7	295.5	315.2	354.6
142.5°	240.5	232.9	225.3	232.9	240.5	242.4	260.2	283.8	295.5	312.8	347.4
145°	247.7	241.1	234.5	241.1	247.7	249.4	264.1	283.8	293.5	307.7	336.0
147.5°	256.6	250.1	243.6	250.1	256.6	258.2	269.9	285.7	293.5	304.7	326.9
150°	261.3	255.5	249.6	255.5	261.3	262.7	273.0	286.6	293.5	302.9	321.7
152.5°	264.6	260.2	255.8	260.2	264.6	265.7	275.0	287.3	293.5	301.5	317.5
155°	271.5	268.2	264.9	268.2	271.5	272.3	279.4	288.8	293.5	299.9	312.6
157.5°	278.1	274.9	271.7	274.9	278.1	278.9	283.8	290.2	293.5	298.5	308.4
160°	281.3	278.8	276.3	278.8	281.3	281.9	285.8	290.9	293.5	297.8	306.3
162.5°	284.6	282.8	280.9	282.8	284.6	285.1	287.8	291.6	293.5	297.1	304.3
165°	289.3	287.6	286.0	287.6	289.3	289.7	291.0	292.7	293.5	296.1	301.2
167.5°	292.1	291.3	290.5	291.3	292.1	292.3	293.4	294.8	295.5	297.2	300.6
170°	295.1	294.3	293.5	294.3	295.1	295.3	295.4	295.5	295.5	297.2	300.6
172.5°	295.5	295.3	295.1	295.3	295.5	295.5	295.5	295.5	295.5	296.8	299.5
175°	297.3	297.3	297.3	297.3	297.3	297.3	296.7	295.9	295.5	296.3	298.0
177.5°	297.3	297.3	297.3	297.3	297.3	297.3	296.8	296.2	295.9	296.6	297.9
180°	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3

TEST NUMBER: P933892

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1	1412.1
2.5°	1362.6	1358.6	1364.0	1349.3	1364.0	1358.6	1362.6	1372.0	1364.0	1369.3	1374.7
5°	1195.7	1189.0	1167.6	1150.3	1167.6	1189.0	1195.7	1223.7	1237.0	1261.1	1293.2
7.5°	1068.7	1063.4	1058.1	1047.4	1058.1	1063.4	1068.7	1076.8	1090.1	1111.5	1135.5
10°	1040.7	1042.0	1050.1	1048.7	1050.1	1042.0	1040.7	1038.0	1034.0	1038.0	1052.7
12.5°	1112.8	1124.9	1168.9	1166.3	1168.9	1124.9	1112.8	1059.4	1023.3	1016.6	1019.3
15°	1195.7	1199.7	1209.0	1210.3	1209.0	1199.7	1195.7	1174.3	1066.1	1019.3	1004.7
17.5°	1203.7	1205.1	1211.7	1211.7	1211.7	1205.1	1203.7	1194.3	1158.2	1095.5	1012.6
20°	1197.0	1199.7	1213.0	1215.7	1213.0	1199.7	1197.0	1184.9	1164.9	1142.2	1079.5
22.5°	1194.3	1199.7	1210.3	1209.0	1210.3	1199.7	1194.3	1175.6	1158.2	1142.2	1116.8
25°	1181.0	1181.0	1182.4	1183.6	1182.4	1181.0	1181.0	1166.3	1131.6	1127.6	1112.8
27.5°	1152.9	1155.6	1163.6	1162.2	1163.6	1155.6	1152.9	1147.6	1110.1	1106.2	1095.5
30°	1127.6	1124.9	1118.2	1112.8	1118.2	1124.9	1127.6	1119.5	1082.2	1071.4	1074.1
32.5°	1084.7	1078.1	1071.4	1067.4	1071.4	1078.1	1084.7	1082.2	1054.1	1039.3	1042.0
35°	1034.0	1035.3	1034.0	1030.0	1034.0	1035.3	1034.0	1036.7	1019.3	1006.0	1004.7
37.5°	998.0	1000.6	999.3	993.9	999.3	1000.6	998.0	995.3	971.2	967.2	969.9
40°	960.5	961.8	960.5	956.6	960.5	961.8	960.5	955.2	921.8	923.1	932.5
42.5°	924.5	923.1	919.1	916.4	919.1	923.1	924.5	916.4	873.7	869.7	887.0
45°	883.1	884.3	876.4	872.4	876.4	884.3	883.1	877.7	833.7	822.9	834.9
47.5°	841.6	841.6	834.9	831.0	834.9	841.6	841.6	834.9	788.2	777.5	784.2
50°	797.6	796.2	786.8	785.5	786.8	796.2	797.6	793.5	744.1	734.7	734.7
52.5°	746.8	746.8	748.1	750.8	748.1	746.8	746.8	748.1	704.1	694.7	692.0
55°	702.7	704.1	713.4	716.0	713.4	704.1	702.7	702.7	662.6	653.3	647.9
57.5°	657.3	657.3	663.9	663.9	663.9	657.3	657.3	654.6	615.8	607.9	605.2
60°	605.2	607.9	613.2	611.8	613.2	607.9	605.2	602.5	569.1	563.7	554.4
62.5°	550.4	553.1	554.4	551.8	554.4	553.1	550.4	542.4	522.4	518.3	506.4
65°	492.9	495.6	497.0	494.3	497.0	495.6	492.9	488.9	474.3	467.6	456.9
67.5°	434.2	432.9	431.5	436.8	431.5	432.9	434.2	428.9	419.5	414.1	399.5
70°	374.1	374.1	372.7	375.4	372.7	374.1	374.1	370.0	364.7	360.8	347.3
72.5°	310.0	308.6	313.9	310.0	313.9	308.6	310.0	308.6	306.0	301.9	288.5
75°	247.1	249.8	247.1	251.2	247.1	249.8	247.1	248.5	247.1	244.5	235.2
77.5°	188.3	191.0	188.3	188.3	188.3	191.0	188.3	189.7	189.7	189.7	181.7
80°	133.6	132.3	132.3	130.9	132.3	132.3	133.6	133.6	135.0	132.3	129.6
82.5°	85.5	84.2	84.2	86.9	84.2	84.2	85.5	86.9	84.2	84.2	84.2
85°	46.7	48.1	45.4	45.4	45.4	48.1	46.7	44.1	46.7	46.7	45.4
87.5°	17.3	16.0	16.0	16.0	16.0	16.0	17.3	18.7	18.7	18.7	20.0
90°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	10.1	13.4	15.1	13.0
92.5°	37.9	36.5	30.4	24.3	30.4	36.5	37.9	53.8	74.8	85.4	75.0
95°	128.7	124.1	105.9	87.5	105.9	124.1	128.7	169.0	222.7	249.6	210.8
97.5°	297.1	288.4	253.6	218.8	253.6	288.4	297.1	322.6	356.6	373.5	308.8
100°	417.2	406.9	365.4	324.0	365.4	406.9	417.2	415.3	412.8	411.5	339.7
102.5°	519.7	510.8	475.4	439.9	475.4	510.8	519.7	487.2	444.0	422.4	349.6
105°	639.4	634.7	615.6	596.5	615.6	634.7	639.4	566.7	469.7	421.2	350.7
107.5°	701.7	702.9	707.5	712.0	707.5	702.9	701.7	600.2	464.8	397.2	335.1
110°	717.6	722.6	742.4	762.3	742.4	722.6	717.6	604.2	452.9	377.3	321.2

TEST NUMBER: P933892

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	707.5	715.1	745.6	776.1	745.6	715.1	707.5	591.3	436.5	359.2	309.2
115°	673.0	683.6	725.9	768.1	725.9	683.6	673.0	561.1	411.9	337.3	295.3
117.5°	625.3	637.0	684.0	730.9	684.0	637.0	625.3	524.3	389.7	322.4	286.6
120°	593.1	604.5	650.1	695.7	650.1	604.5	593.1	500.9	377.9	316.4	283.8
122.5°	561.0	572.3	617.2	662.1	617.2	572.3	561.0	478.0	367.2	311.8	282.2
125°	518.5	528.9	570.3	611.7	570.3	528.9	518.5	448.0	353.9	306.9	281.0
127.5°	484.5	493.2	528.1	563.0	528.1	493.2	484.5	423.9	343.1	302.7	280.2
130°	462.8	470.9	503.2	535.4	503.2	470.9	462.8	409.0	337.0	301.1	280.7
132.5°	444.5	451.8	480.7	509.6	480.7	451.8	444.5	396.2	331.9	299.7	281.0
135°	418.6	424.8	449.7	474.6	449.7	424.8	418.6	378.2	324.3	297.3	280.7
137.5°	399.4	404.5	424.9	445.3	424.9	404.5	399.4	365.2	319.7	296.9	282.4
140°	384.1	388.8	407.9	427.0	407.9	388.8	384.1	354.6	315.2	295.5	282.7
142.5°	373.3	377.4	393.8	410.2	393.8	377.4	373.3	347.4	312.8	295.5	283.8
145°	357.2	360.3	372.7	385.1	372.7	360.3	357.2	336.0	307.7	293.5	283.8
147.5°	343.5	346.1	356.4	366.7	356.4	346.1	343.5	326.9	304.7	293.5	285.7
150°	335.8	337.8	346.2	354.6	346.2	337.8	335.8	321.7	302.9	293.5	286.6
152.5°	329.6	331.2	337.4	343.7	337.4	331.2	329.6	317.5	301.5	293.5	287.3
155°	322.2	323.2	327.4	331.6	327.4	323.2	322.2	312.6	299.9	293.5	288.8
157.5°	315.8	316.5	319.5	322.4	319.5	316.5	315.8	308.4	298.5	293.5	290.2
160°	312.6	313.0	314.7	316.4	314.7	313.0	312.6	306.3	297.8	293.5	290.9
162.5°	309.7	310.1	311.6	313.2	311.6	310.1	309.7	304.3	297.1	293.5	291.6
165°	305.1	305.5	307.2	308.9	307.2	305.5	305.1	301.2	296.1	293.5	292.7
167.5°	303.1	303.3	304.0	304.7	304.0	303.3	303.1	300.6	297.2	295.5	294.8
170°	303.1	303.1	303.1	303.1	303.1	303.1	303.1	300.6	297.2	295.5	295.5
172.5°	301.5	301.3	300.7	300.1	300.7	301.3	301.5	299.5	296.8	295.5	295.5
175°	299.3	299.3	299.3	299.3	299.3	299.3	299.3	298.0	296.3	295.5	295.9
177.5°	298.9	298.7	298.0	297.3	298.0	298.7	298.9	297.9	296.6	295.9	296.2
180°	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3

TEST NUMBER: P933892

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1412.1	1412.1	1412.1	1412.1	1412.1
2.5°	1394.7	1401.4	1405.5	1410.7	1424.1
5°	1341.3	1366.7	1374.7	1394.7	1418.8
7.5°	1223.7	1301.2	1322.6	1370.7	1408.0
10°	1110.1	1187.6	1225.1	1338.6	1394.7
12.5°	1052.7	1098.2	1123.5	1282.5	1376.0
15°	1016.6	1048.7	1067.4	1207.6	1354.7
17.5°	988.6	1011.3	1024.7	1134.2	1325.3
20°	971.2	982.0	993.9	1080.8	1291.8
22.5°	959.2	952.6	961.8	1043.4	1246.4
25°	951.2	925.8	936.5	1014.0	1193.0
27.5°	957.9	901.8	905.8	987.2	1136.9
30°	959.2	872.4	873.7	959.2	1074.1
32.5°	949.9	841.6	843.0	924.5	1003.3
35°	927.2	805.6	804.3	884.3	907.1
37.5°	896.4	766.8	766.8	840.3	801.6
40°	859.0	728.1	732.1	782.9	708.1
42.5°	813.6	686.6	692.0	706.8	638.5
45°	764.1	646.6	650.6	597.2	585.2
47.5°	709.4	605.2	606.6	495.6	567.8
50°	643.9	562.4	557.1	424.8	566.4
52.5°	586.4	515.6	499.6	384.8	514.3
55°	530.4	466.2	431.5	354.0	476.9
57.5°	481.0	402.1	368.7	317.9	468.9
60°	435.6	339.3	313.9	279.2	430.2
62.5°	398.1	292.5	287.2	252.5	390.1
65°	358.1	260.6	259.2	229.8	331.3
67.5°	319.3	239.1	237.8	208.4	252.5
70°	277.9	216.4	213.7	185.7	187.0
72.5°	235.2	191.0	188.3	167.0	155.0
75°	192.3	161.7	160.4	145.6	125.6
77.5°	151.0	128.3	130.9	117.5	92.2
80°	108.2	93.5	96.2	84.2	69.4
82.5°	72.1	61.5	64.1	53.5	46.7
85°	40.0	34.8	36.1	28.1	21.4
87.5°	18.7	16.0	16.0	10.7	6.7
90°	8.8	5.6	5.2	3.6	2.0
92.5°	54.2	38.5	35.2	21.5	8.0
95°	133.2	75.0	68.8	43.9	19.1
97.5°	179.4	82.4	76.9	55.1	33.2
100°	196.2	88.5	83.6	63.7	43.9
102.5°	204.0	94.7	90.1	71.6	53.1
105°	209.8	104.0	100.1	84.4	68.6
107.5°	210.8	117.5	113.8	99.2	84.6
110°	209.2	125.1	121.8	108.6	95.4

TEST NUMBER: P933892

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	209.3	134.3	131.1	118.5	106.0
115°	211.2	148.0	145.1	133.5	121.9
117.5°	215.1	161.5	158.8	148.2	137.6
120°	218.3	169.2	166.7	156.8	146.8
122.5°	222.9	178.4	175.9	165.8	155.8
125°	229.1	190.1	187.8	178.8	169.6
127.5°	235.3	201.5	199.2	189.9	180.8
130°	239.7	209.1	206.6	196.7	186.8
132.5°	243.4	215.2	212.7	202.9	192.9
135°	247.4	222.5	220.2	211.2	202.1
137.5°	253.4	231.7	229.4	220.4	211.5
140°	257.1	237.8	235.8	227.5	219.2
142.5°	260.2	242.4	240.5	232.9	225.3
145°	264.1	249.4	247.7	241.1	234.5
147.5°	269.9	258.2	256.6	250.1	243.6
150°	273.0	262.7	261.3	255.5	249.6
152.5°	275.0	265.7	264.6	260.2	255.8
155°	279.4	272.3	271.5	268.2	264.9
157.5°	283.8	278.9	278.1	274.9	271.7
160°	285.8	281.9	281.3	278.8	276.3
162.5°	287.8	285.1	284.6	282.8	280.9
165°	291.0	289.7	289.3	287.6	286.0
167.5°	293.4	292.3	292.1	291.3	290.5
170°	295.4	295.3	295.1	294.3	293.5
172.5°	295.5	295.5	295.5	295.3	295.1
175°	296.7	297.3	297.3	297.3	297.3
177.5°	296.8	297.3	297.3	297.3	297.3
180°	297.3	297.3	297.3	297.3	297.3

TEST NUMBER: P933892

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.66	13.68	13.47	14.51	15.55	15.50	16.52	16.31	17.35	18.38
	3H	13.15	14.06	13.97	14.91	15.97	16.86	17.77	17.68	18.62	19.68
	4H	13.35	14.21	14.19	15.06	16.13	17.31	18.17	18.15	19.03	20.10
	6H	13.47	14.27	14.33	15.13	16.21	17.60	18.40	18.46	19.26	20.34
	8H	13.48	14.24	14.34	15.12	16.20	17.69	18.44	18.55	19.32	20.40
	12H	13.46	14.18	14.32	15.05	16.16	17.73	18.45	18.60	19.32	20.43
4H	2H	13.71	14.58	14.56	15.43	16.50	15.93	16.79	16.77	17.64	18.71
	3H	14.76	15.48	15.61	16.36	17.45	17.45	18.17	18.31	19.05	20.14
	4H	15.04	15.69	15.91	16.58	17.69	17.98	18.64	18.85	19.52	20.63
	6H	15.17	15.74	16.06	16.64	17.76	18.36	18.93	19.25	19.83	20.95
	8H	15.18	15.71	16.07	16.61	17.74	18.47	19.00	19.36	19.90	21.03
	12H	15.16	15.63	16.06	16.55	17.69	18.54	19.01	19.45	19.93	21.07
8H	4H	15.51	16.03	16.39	16.93	18.06	18.12	18.65	19.01	19.55	20.68
	6H	15.77	16.21	16.69	17.15	18.28	18.57	19.00	19.48	19.95	21.07
	8H	15.82	16.21	16.74	17.14	18.29	18.72	19.11	19.65	20.04	21.19
	12H	15.81	16.15	16.74	17.08	18.27	18.83	19.17	19.76	20.10	21.29
12H	4H	15.52	16.00	16.43	16.92	18.05	18.09	18.57	19.00	19.49	20.62
	6H	15.84	16.23	16.76	17.16	18.30	18.56	18.95	19.49	19.89	21.03
	8H	15.91	16.25	16.84	17.18	18.38	18.73	19.08	19.66	20.00	21.20

END OF REPORT