

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934082

Luminaire Tested: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934082
REPORT IS A COMBINATION OF REPORTS P933682 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4570.6 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 38.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934082

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K

Luminous Intensity Polar Plot



TEST NUMBER: P934082

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	73	72	70
2	95	87	81	76	91	84	78	73	77	72	68	70	67	64	65	62	59
3	87	77	69	63	83	74	67	61	68	62	57	62	58	54	57	54	50
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43
5	73	61	52	46	70	58	51	45	54	47	42	50	44	40	46	41	38
6	67	55	46	40	64	53	45	39	49	42	37	45	39	35	42	37	33
7	62	50	41	35	59	48	40	34	44	38	33	41	35	31	38	33	30
8	58	45	37	31	55	44	36	31	40	34	29	38	32	28	35	30	26
9	54	41	33	28	52	40	33	27	37	31	26	35	29	25	32	27	24
10	51	38	30	25	48	37	30	25	34	28	24	32	27	23	30	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12906	12906	12906	12906
5°	12990	13029	12990	10244
10°	12889	12834	12889	9176
15°	12733	12556	12733	10484
20°	12452	12227	12452	10506
25°	11894	11747	11894	10284
30°	11176	11348	11176	9795
35°	9947	10843	9947	9258
40°	8275	10249	8275	8852
45°	7380	9554	7380	8385
50°	7822	8725	7822	7917
55°	7338	7832	7338	7646
60°	7537	6651	7537	7003
65°	6802	5498	6802	6146
70°	4679	4382	4679	5152
75°	4056	3239	4056	3879
80°	3201	2141	3201	2332
85°	1739	1133	1739	963

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 11331 cd/sqm

TEST NUMBER: P934082

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.6	2.7
10°-20°	356.5	7.8
20°-30°	551.1	12.1
30°-40°	657.9	14.4
40°-50°	661.7	14.5
50°-60°	575.8	12.6
60°-70°	408.2	8.9
70°-80°	216.0	4.7
80°-90°	54.4	1.2
90°-100°	72.5	1.6
100°-110°	190.5	4.2
110°-120°	197.5	4.3
120°-130°	158.4	3.5
130°-140°	124.3	2.7
140°-150°	95.4	2.1
150°-160°	68.7	1.5
160°-170°	42.0	0.9
170°-180°	14.2	0.3
0°-30°	1033.1	22.6
0°-40°	1691.0	37.0
0°-60°	2928.5	64.1
0°-90°	3607.1	78.9
90°-120°	460.5	10.1
90°-150°	838.6	18.3
90°-180°	964.0	21.1
0°-180°	4570.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1391	1391	1391	1391	1391	
5°	1398	1441	1398	1133	1398	133
15°	1334	1428	1334	1192	1334	375
25°	1175	1332	1175	1166	1175	540
35°	894	1188	894	1015	894	553
45°	576	979	576	859	576	462
55°	470	722	470	705	470	432
65°	326	436	326	487	326	312
75°	124	207	124	247	124	130
85°	21	53	21	45	21	28
90°	1	4	1	4	1	2
95°	10	44	10	44	10	11
105°	34	298	34	298	34	36
115°	61	384	61	384	61	60
125°	85	306	85	306	85	75
135°	101	237	101	237	101	78
145°	117	192	117	192	117	73
155°	132	166	132	166	132	61
165°	143	154	143	154	143	40
175°	149	150	149	150	149	14
180°	149	149	149	149	149	

TEST NUMBER: P934082

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9
2.5°	1402.8	1402.8	1410.7	1413.3	1413.3	1409.3	1405.5	1409.3	1421.2	1425.2	1423.9
5°	1397.6	1408.0	1422.6	1425.2	1427.8	1426.5	1423.9	1426.5	1439.6	1442.3	1443.6
7.5°	1387.0	1406.8	1425.2	1429.2	1433.0	1429.2	1427.8	1430.5	1443.6	1446.2	1446.2
10°	1373.9	1401.5	1422.6	1425.2	1429.2	1425.2	1425.2	1430.5	1443.6	1446.2	1447.6
12.5°	1355.5	1393.6	1413.3	1416.0	1421.2	1419.9	1418.6	1423.9	1437.0	1439.6	1439.6
15°	1334.3	1379.2	1397.6	1400.2	1409.3	1406.8	1406.8	1412.0	1426.5	1430.5	1429.2
17.5°	1305.5	1360.7	1381.8	1385.7	1392.3	1390.9	1392.3	1397.6	1410.7	1413.3	1414.6
20°	1272.5	1335.7	1360.7	1364.6	1371.2	1371.2	1371.2	1377.8	1390.9	1396.2	1396.2
22.5°	1227.8	1309.3	1335.7	1338.3	1346.2	1346.2	1348.9	1358.0	1369.9	1371.2	1371.2
25°	1175.2	1280.5	1302.8	1310.7	1318.6	1322.5	1326.5	1331.8	1335.7	1334.3	1335.7
27.5°	1119.9	1243.6	1272.5	1277.8	1288.3	1292.3	1297.5	1298.9	1300.2	1304.1	1301.5
30°	1058.1	1192.2	1235.6	1240.9	1258.0	1260.6	1255.5	1258.0	1264.6	1267.3	1269.9
32.5°	988.2	1115.9	1197.5	1209.3	1225.2	1217.2	1215.9	1219.9	1230.5	1230.5	1233.0
35°	893.5	1056.8	1162.0	1172.5	1184.3	1175.2	1180.4	1181.8	1188.3	1192.2	1190.9
37.5°	789.5	1005.4	1125.2	1133.0	1142.2	1130.4	1138.3	1142.2	1147.5	1144.9	1144.9
40°	697.5	925.1	1081.8	1086.9	1094.9	1085.6	1093.5	1096.2	1098.8	1096.2	1094.9
42.5°	629.1	836.9	1035.6	1042.2	1036.9	1043.5	1046.2	1051.5	1047.5	1042.2	1042.2
45°	576.4	813.2	985.6	993.5	985.6	996.2	1000.1	1000.1	988.2	985.6	984.3
47.5°	559.3	765.9	935.6	935.6	931.7	944.8	951.5	942.2	930.4	926.5	926.5
50°	558.0	713.2	867.2	861.9	880.4	896.2	889.6	880.4	871.2	856.7	856.7
52.5°	506.7	648.8	779.1	798.8	827.8	836.9	826.4	817.2	801.4	794.8	789.5
55°	469.8	581.7	698.8	738.2	768.5	780.4	760.6	751.4	727.7	723.8	721.1
57.5°	461.9	484.3	625.1	675.1	711.9	710.6	698.8	681.7	661.9	658.0	656.7
60°	423.7	350.0	546.1	605.4	643.5	639.5	629.1	613.2	594.8	592.2	589.5
62.5°	384.3	254.0	456.7	523.8	577.7	576.4	567.2	543.5	530.4	523.8	518.5
65°	326.4	213.1	325.0	435.6	513.2	515.8	496.1	479.0	464.5	456.7	455.3
67.5°	248.7	173.7	219.7	363.2	451.4	448.7	423.7	415.8	397.4	393.4	385.6
70°	184.3	115.8	152.7	294.8	390.8	384.3	364.5	355.3	338.2	329.0	323.7
72.5°	152.7	93.4	111.9	229.0	329.0	321.1	304.0	293.4	279.0	271.1	265.8
75°	123.7	98.7	85.6	169.7	267.1	261.8	246.1	235.6	223.7	213.1	214.5
77.5°	90.8	92.1	68.4	125.0	211.8	204.0	194.7	181.6	176.3	165.8	165.8
80°	68.4	72.4	51.3	85.6	152.7	152.7	144.7	135.6	126.3	121.1	121.1
82.5°	46.0	46.0	38.1	54.0	104.0	100.0	94.7	92.1	86.9	84.3	84.3
85°	21.0	26.3	23.7	32.9	56.6	59.3	59.3	56.6	55.3	52.6	54.0
87.5°	6.6	11.9	14.4	18.4	29.0	30.3	31.6	31.6	31.6	32.9	32.9
90°	1.0	1.8	2.6	2.8	4.4	6.5	7.6	6.8	5.1	3.8	3.8
92.5°	4.0	10.8	17.5	19.2	27.1	37.5	42.7	37.4	26.9	18.9	18.1
95°	9.6	22.0	34.5	37.5	66.6	105.4	124.8	111.4	84.5	64.3	62.1
97.5°	16.5	27.5	38.4	41.2	89.7	154.4	186.8	178.3	161.3	148.5	144.1
100°	21.9	31.9	41.8	44.3	98.1	169.9	205.8	206.4	207.7	208.6	203.4
102.5°	26.5	35.8	45.1	47.4	102.0	174.8	211.2	222.0	243.6	259.9	255.4
105°	34.4	42.2	50.0	52.0	104.9	175.3	210.6	234.9	283.4	319.7	317.3
107.5°	42.3	49.6	57.0	58.8	105.4	167.5	198.6	232.5	300.1	350.9	351.5
110°	47.7	54.3	60.9	62.5	104.6	160.7	188.6	226.5	302.1	358.9	361.3

TEST NUMBER: P934082

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	53.0	59.3	65.5	67.1	104.6	154.6	179.6	218.3	295.7	353.8	357.6
115°	61.0	66.7	72.5	74.0	105.6	147.7	168.7	206.0	280.6	336.4	341.7
117.5°	68.8	74.1	79.4	80.7	107.6	143.3	161.3	194.9	262.1	312.6	318.5
120°	73.4	78.4	83.4	84.6	109.1	141.8	158.2	188.9	250.5	296.6	302.3
122.5°	77.9	82.9	87.8	89.1	111.4	141.0	155.9	183.6	238.9	280.5	286.1
125°	84.8	89.3	93.9	95.1	114.5	140.4	153.4	176.9	224.0	259.3	264.4
127.5°	90.3	95.0	99.6	100.8	117.6	140.0	151.3	171.5	211.9	242.2	246.6
130°	93.3	98.3	103.3	104.6	119.9	140.3	150.5	168.5	204.5	231.5	235.5
132.5°	96.5	101.5	106.5	107.7	121.7	140.4	149.8	165.9	198.1	222.3	225.9
135°	101.1	105.6	110.2	111.3	123.7	140.3	148.6	162.0	189.0	209.3	212.3
137.5°	105.8	110.3	114.7	115.8	126.7	141.1	148.4	159.8	182.6	199.7	202.3
140°	109.7	113.7	117.9	118.9	128.5	141.3	147.7	157.6	177.3	192.0	194.4
142.5°	112.6	116.4	120.2	121.2	130.1	141.8	147.7	156.4	173.7	186.7	188.7
145°	117.2	120.5	123.9	124.7	132.1	141.8	146.7	153.8	167.9	178.6	180.2
147.5°	121.8	125.0	128.3	129.1	135.0	142.8	146.7	152.3	163.4	171.8	173.1
150°	124.8	127.7	130.7	131.4	136.5	143.3	146.7	151.4	160.9	167.9	168.9
152.5°	127.9	130.1	132.3	132.9	137.4	143.6	146.7	150.7	158.8	164.8	165.6
155°	132.5	134.1	135.8	136.2	139.6	144.3	146.7	149.9	156.4	161.2	161.7
157.5°	135.9	137.4	139.0	139.4	141.8	145.1	146.7	149.2	154.2	157.9	158.3
160°	138.1	139.3	140.6	140.9	142.8	145.4	146.7	148.8	153.1	156.3	156.5
162.5°	140.4	141.3	142.3	142.5	143.9	145.8	146.7	148.5	152.1	154.8	155.0
165°	142.9	143.7	144.6	144.8	145.4	146.3	146.7	148.0	150.6	152.5	152.7
167.5°	145.2	145.6	146.0	146.1	146.6	147.3	147.7	148.5	150.2	151.5	151.6
170°	146.7	147.1	147.5	147.6	147.6	147.7	147.7	148.5	150.2	151.5	151.5
172.5°	147.5	147.6	147.7	147.7	147.7	147.7	147.7	148.4	149.7	150.7	150.6
175°	148.6	148.6	148.6	148.6	148.3	147.9	147.7	148.1	149.0	149.6	149.6
177.5°	148.6	148.6	148.6	148.6	148.4	148.1	147.9	148.2	148.9	149.4	149.3
180°	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6

TEST NUMBER: P934082

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9
2.5°	1426.5	1422.6	1426.5	1423.9	1425.2	1421.2	1409.3	1405.5	1409.3	1413.3	1413.3
5°	1443.6	1441.0	1443.6	1443.6	1442.3	1439.6	1426.5	1423.9	1426.5	1427.8	1425.2
7.5°	1448.9	1444.9	1448.9	1446.2	1446.2	1443.6	1430.5	1427.8	1429.2	1433.0	1429.2
10°	1448.9	1444.9	1448.9	1447.6	1446.2	1443.6	1430.5	1425.2	1425.2	1429.2	1425.2
12.5°	1442.3	1439.6	1442.3	1439.6	1439.6	1437.0	1423.9	1418.6	1419.9	1421.2	1416.0
15°	1431.8	1427.8	1431.8	1429.2	1430.5	1426.5	1412.0	1406.8	1406.8	1409.3	1400.2
17.5°	1416.0	1410.7	1416.0	1414.6	1413.3	1410.7	1397.6	1392.3	1390.9	1392.3	1385.7
20°	1397.6	1393.6	1397.6	1396.2	1396.2	1390.9	1377.8	1371.2	1371.2	1371.2	1364.6
22.5°	1368.6	1364.6	1368.6	1371.2	1371.2	1369.9	1358.0	1348.9	1346.2	1346.2	1338.3
25°	1335.7	1331.8	1335.7	1335.7	1334.3	1335.7	1331.8	1326.5	1322.5	1318.6	1310.7
27.5°	1304.1	1301.5	1304.1	1301.5	1304.1	1300.2	1298.9	1297.5	1292.3	1288.3	1277.8
30°	1272.5	1269.9	1272.5	1269.9	1267.3	1264.6	1258.0	1255.5	1260.6	1258.0	1240.9
32.5°	1233.0	1230.5	1233.0	1233.0	1230.5	1230.5	1219.9	1215.9	1217.2	1225.2	1209.3
35°	1192.2	1188.3	1192.2	1190.9	1192.2	1188.3	1181.8	1180.4	1175.2	1184.3	1172.5
37.5°	1144.9	1140.9	1144.9	1144.9	1144.9	1147.5	1142.2	1138.3	1130.4	1142.2	1133.0
40°	1096.2	1090.9	1096.2	1094.9	1096.2	1098.8	1096.2	1093.5	1085.6	1094.9	1086.9
42.5°	1040.9	1039.6	1040.9	1042.2	1042.2	1047.5	1051.5	1046.2	1043.5	1036.9	1042.2
45°	981.7	979.1	981.7	984.3	985.6	988.2	1000.1	1000.1	996.2	985.6	993.5
47.5°	918.5	911.9	918.5	926.5	926.5	930.4	942.2	951.5	944.8	931.7	935.6
50°	851.4	852.8	851.4	856.7	856.7	871.2	880.4	889.6	896.2	880.4	861.9
52.5°	785.6	784.4	785.6	789.5	794.8	801.4	817.2	826.4	836.9	827.8	798.8
55°	719.8	722.5	719.8	721.1	723.8	727.7	751.4	760.6	780.4	768.5	738.2
57.5°	654.1	650.1	654.1	656.7	658.0	661.9	681.7	698.8	710.6	711.9	675.1
60°	577.7	572.4	577.7	589.5	592.2	594.8	613.2	629.1	639.5	643.5	605.4
62.5°	510.5	501.4	510.5	518.5	523.8	530.4	543.5	567.2	576.4	577.7	523.8
65°	439.5	435.6	439.5	455.3	456.7	464.5	479.0	496.1	515.8	513.2	435.6
67.5°	375.1	375.1	375.1	385.6	393.4	397.4	415.8	423.7	448.7	451.4	363.2
70°	315.8	314.5	315.8	323.7	329.0	338.2	355.3	364.5	384.3	390.8	294.8
72.5°	259.3	258.0	259.3	265.8	271.1	279.0	293.4	304.0	321.1	329.0	229.0
75°	209.3	206.6	209.3	214.5	213.1	223.7	235.6	246.1	261.8	267.1	169.7
77.5°	160.6	160.6	160.6	165.8	165.8	176.3	181.6	194.7	204.0	211.8	125.0
80°	119.7	118.4	119.7	121.1	121.1	126.3	135.6	144.7	152.7	152.7	85.6
82.5°	84.3	81.6	84.3	84.3	84.3	86.9	92.1	94.7	100.0	104.0	54.0
85°	52.6	52.6	52.6	54.0	52.6	55.3	56.6	59.3	59.3	56.6	32.9
87.5°	34.3	32.9	34.3	32.9	32.9	31.6	31.6	31.6	30.3	29.0	18.4
90°	3.8	3.8	3.8	3.8	3.8	5.1	6.8	7.6	6.5	4.4	2.8
92.5°	15.1	12.2	15.1	18.1	18.9	26.9	37.4	42.7	37.5	27.1	19.2
95°	53.0	43.8	53.0	62.1	64.3	84.5	111.4	124.8	105.4	66.6	37.5
97.5°	126.8	109.5	126.8	144.1	148.5	161.3	178.3	186.8	154.4	89.7	41.2
100°	182.8	162.0	182.8	203.4	208.6	207.7	206.4	205.8	169.9	98.1	44.3
102.5°	237.6	219.9	237.6	255.4	259.9	243.6	222.0	211.2	174.8	102.0	47.4
105°	307.9	298.3	307.9	317.3	319.7	283.4	234.9	210.6	175.3	104.9	52.0
107.5°	353.8	356.1	353.8	351.5	350.9	300.1	232.5	198.6	167.5	105.4	58.8
110°	371.2	381.2	371.2	361.3	358.9	302.1	226.5	188.6	160.7	104.6	62.5

TEST NUMBER: P934082

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	372.8	388.0	372.8	357.6	353.8	295.7	218.3	179.6	154.6	104.6	67.1
115°	362.9	384.1	362.9	341.7	336.4	280.6	206.0	168.7	147.7	105.6	74.0
117.5°	341.9	365.4	341.9	318.5	312.6	262.1	194.9	161.3	143.3	107.6	80.7
120°	325.1	347.8	325.1	302.3	296.6	250.5	188.9	158.2	141.8	109.1	84.6
122.5°	308.6	331.1	308.6	286.1	280.5	238.9	183.6	155.9	141.0	111.4	89.1
125°	285.2	305.9	285.2	264.4	259.3	224.0	176.9	153.4	140.4	114.5	95.1
127.5°	264.0	281.5	264.0	246.6	242.2	211.9	171.5	151.3	140.0	117.6	100.8
130°	251.6	267.7	251.6	235.5	231.5	204.5	168.5	150.5	140.3	119.9	104.6
132.5°	240.3	254.8	240.3	225.9	222.3	198.1	165.9	149.8	140.4	121.7	107.7
135°	224.9	237.3	224.9	212.3	209.3	189.0	162.0	148.6	140.3	123.7	111.3
137.5°	212.4	222.7	212.4	202.3	199.7	182.6	159.8	148.4	141.1	126.7	115.8
140°	203.9	213.4	203.9	194.4	192.0	177.3	157.6	147.7	141.3	128.5	118.9
142.5°	196.9	205.1	196.9	188.7	186.7	173.7	156.4	147.7	141.8	130.1	121.2
145°	186.4	192.5	186.4	180.2	178.6	167.9	153.8	146.7	141.8	132.1	124.7
147.5°	178.2	183.4	178.2	173.1	171.8	163.4	152.3	146.7	142.8	135.0	129.1
150°	173.1	177.3	173.1	168.9	167.9	160.9	151.4	146.7	143.3	136.5	131.4
152.5°	168.7	171.9	168.7	165.6	164.8	158.8	150.7	146.7	143.6	137.4	132.9
155°	163.7	165.8	163.7	161.7	161.2	156.4	149.9	146.7	144.3	139.6	136.2
157.5°	159.8	161.3	159.8	158.3	157.9	154.2	149.2	146.7	145.1	141.8	139.4
160°	157.4	158.2	157.4	156.5	156.3	153.1	148.8	146.7	145.4	142.8	140.9
162.5°	155.8	156.6	155.8	155.0	154.8	152.1	148.5	146.7	145.8	143.9	142.5
165°	153.6	154.4	153.6	152.7	152.5	150.6	148.0	146.7	146.3	145.4	144.8
167.5°	151.9	152.3	151.9	151.6	151.5	150.2	148.5	147.7	147.3	146.6	146.1
170°	151.5	151.5	151.5	151.5	151.5	150.2	148.5	147.7	147.7	147.6	147.6
172.5°	150.3	150.0	150.3	150.6	150.7	149.7	148.4	147.7	147.7	147.7	147.7
175°	149.6	149.6	149.6	149.6	149.6	149.0	148.1	147.7	147.9	148.3	148.6
177.5°	149.0	148.6	149.0	149.3	149.4	148.9	148.2	147.9	148.1	148.4	148.6
180°	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6

TEST NUMBER: P934082

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9
2.5°	1410.7	1402.8	1402.8	1389.6	1384.3	1380.5	1373.9	1354.2	1348.9	1343.6	1351.5
5°	1422.6	1408.0	1397.6	1373.9	1354.2	1346.2	1321.2	1273.9	1242.2	1218.6	1205.5
7.5°	1425.2	1406.8	1387.0	1350.2	1302.8	1281.8	1205.5	1118.6	1094.9	1073.8	1060.6
10°	1422.6	1401.5	1373.9	1318.6	1206.8	1169.9	1093.5	1036.9	1022.5	1018.5	1022.5
12.5°	1413.3	1393.6	1355.5	1263.3	1106.8	1081.8	1036.9	1004.1	1001.5	1008.1	1043.5
15°	1397.6	1379.2	1334.3	1189.6	1051.5	1033.1	1001.5	989.6	1004.1	1050.1	1156.8
17.5°	1381.8	1360.7	1305.5	1117.2	1009.3	996.2	973.8	997.5	1079.1	1140.9	1176.5
20°	1360.7	1335.7	1272.5	1064.6	979.1	967.2	956.7	1063.3	1125.2	1147.5	1167.2
22.5°	1335.7	1309.3	1227.8	1027.8	947.5	938.2	944.8	1100.2	1125.2	1140.9	1158.0
25°	1302.8	1280.5	1175.2	998.8	922.5	911.9	936.9	1096.2	1110.6	1114.6	1148.8
27.5°	1272.5	1243.6	1119.9	972.5	892.2	888.2	943.5	1079.1	1089.6	1093.5	1130.4
30°	1235.6	1192.2	1058.1	944.8	860.6	859.3	944.8	1058.1	1055.4	1065.9	1102.8
32.5°	1197.5	1115.9	988.2	910.6	830.4	829.1	935.6	1026.5	1023.8	1038.3	1065.9
35°	1162.0	1056.8	893.5	871.2	792.2	793.5	913.2	989.6	990.9	1004.1	1021.2
37.5°	1125.2	1005.4	789.5	827.8	755.4	755.4	883.0	955.4	952.8	956.7	980.4
40°	1081.8	925.1	697.5	771.1	721.1	717.2	846.2	918.5	909.3	908.1	940.9
42.5°	1035.6	836.9	629.1	696.1	681.7	676.4	801.4	873.8	856.7	860.6	902.8
45°	985.6	813.2	576.4	588.2	640.8	636.9	752.7	822.5	810.6	821.2	864.6
47.5°	935.6	765.9	559.3	488.2	597.4	596.1	698.8	772.5	765.9	776.4	822.5
50°	867.2	713.2	558.0	418.5	548.8	554.0	634.3	723.8	723.8	733.0	781.7
52.5°	779.1	648.8	506.7	379.0	492.1	508.0	577.7	681.7	684.3	693.5	736.9
55°	698.8	581.7	469.8	348.7	425.1	459.3	522.4	638.2	643.5	652.7	692.2
57.5°	625.1	484.3	461.9	313.2	363.2	396.1	473.7	596.1	598.8	606.7	644.8
60°	546.1	350.0	423.7	275.0	309.3	334.3	429.0	546.1	555.4	560.5	593.5
62.5°	456.7	254.0	384.3	248.7	283.0	288.2	392.1	498.7	510.5	514.5	534.3
65°	325.0	213.1	326.4	226.4	255.3	256.6	352.7	450.1	460.6	467.1	481.7
67.5°	219.7	173.7	248.7	205.3	234.3	235.6	314.5	393.4	408.0	413.2	422.4
70°	152.7	115.8	184.3	183.0	210.6	213.1	273.7	342.1	355.3	359.3	364.5
72.5°	111.9	93.4	152.7	164.5	185.6	188.1	231.6	284.3	297.4	301.4	304.0
75°	85.6	98.7	123.7	143.4	157.9	159.3	189.5	231.6	240.8	243.4	244.7
77.5°	68.4	92.1	90.8	115.8	129.0	126.3	148.7	179.0	186.8	186.8	186.8
80°	51.3	72.4	68.4	82.9	94.7	92.1	106.6	127.7	130.3	132.9	131.6
82.5°	38.1	46.0	46.0	52.6	63.1	60.6	71.0	82.9	82.9	82.9	85.6
85°	23.7	26.3	21.0	27.6	35.6	34.3	39.4	44.7	46.0	46.0	43.4
87.5°	14.4	11.9	6.6	10.6	15.8	15.8	18.4	19.7	18.4	18.4	18.4
90°	2.6	1.8	1.0	1.8	2.6	2.8	4.4	6.5	7.6	6.8	5.1
92.5°	17.5	10.8	4.0	10.8	17.5	19.2	27.1	37.5	42.7	37.4	26.9
95°	34.5	22.0	9.6	22.0	34.5	37.5	66.6	105.4	124.8	111.4	84.5
97.5°	38.4	27.5	16.5	27.5	38.4	41.2	89.7	154.4	186.8	178.3	161.3
100°	41.8	31.9	21.9	31.9	41.8	44.3	98.1	169.9	205.8	206.4	207.7
102.5°	45.1	35.8	26.5	35.8	45.1	47.4	102.0	174.8	211.2	222.0	243.6
105°	50.0	42.2	34.4	42.2	50.0	52.0	104.9	175.3	210.6	234.9	283.4
107.5°	57.0	49.6	42.3	49.6	57.0	58.8	105.4	167.5	198.6	232.5	300.1
110°	60.9	54.3	47.7	54.3	60.9	62.5	104.6	160.7	188.6	226.5	302.1

TEST NUMBER: P934082

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	65.5	59.3	53.0	59.3	65.5	67.1	104.6	154.6	179.6	218.3	295.7
115°	72.5	66.7	61.0	66.7	72.5	74.0	105.6	147.7	168.7	206.0	280.6
117.5°	79.4	74.1	68.8	74.1	79.4	80.7	107.6	143.3	161.3	194.9	262.1
120°	83.4	78.4	73.4	78.4	83.4	84.6	109.1	141.8	158.2	188.9	250.5
122.5°	87.8	82.9	77.9	82.9	87.8	89.1	111.4	141.0	155.9	183.6	238.9
125°	93.9	89.3	84.8	89.3	93.9	95.1	114.5	140.4	153.4	176.9	224.0
127.5°	99.6	95.0	90.3	95.0	99.6	100.8	117.6	140.0	151.3	171.5	211.9
130°	103.3	98.3	93.3	98.3	103.3	104.6	119.9	140.3	150.5	168.5	204.5
132.5°	106.5	101.5	96.5	101.5	106.5	107.7	121.7	140.4	149.8	165.9	198.1
135°	110.2	105.6	101.1	105.6	110.2	111.3	123.7	140.3	148.6	162.0	189.0
137.5°	114.7	110.3	105.8	110.3	114.7	115.8	126.7	141.1	148.4	159.8	182.6
140°	117.9	113.7	109.7	113.7	117.9	118.9	128.5	141.3	147.7	157.6	177.3
142.5°	120.2	116.4	112.6	116.4	120.2	121.2	130.1	141.8	147.7	156.4	173.7
145°	123.9	120.5	117.2	120.5	123.9	124.7	132.1	141.8	146.7	153.8	167.9
147.5°	128.3	125.0	121.8	125.0	128.3	129.1	135.0	142.8	146.7	152.3	163.4
150°	130.7	127.7	124.8	127.7	130.7	131.4	136.5	143.3	146.7	151.4	160.9
152.5°	132.3	130.1	127.9	130.1	132.3	132.9	137.4	143.6	146.7	150.7	158.8
155°	135.8	134.1	132.5	134.1	135.8	136.2	139.6	144.3	146.7	149.9	156.4
157.5°	139.0	137.4	135.9	137.4	139.0	139.4	141.8	145.1	146.7	149.2	154.2
160°	140.6	139.3	138.1	139.3	140.6	140.9	142.8	145.4	146.7	148.8	153.1
162.5°	142.3	141.3	140.4	141.3	142.3	142.5	143.9	145.8	146.7	148.5	152.1
165°	144.6	143.7	142.9	143.7	144.6	144.8	145.4	146.3	146.7	148.0	150.6
167.5°	146.0	145.6	145.2	145.6	146.0	146.1	146.6	147.3	147.7	148.5	150.2
170°	147.5	147.1	146.7	147.1	147.5	147.6	147.6	147.7	147.7	148.5	150.2
172.5°	147.7	147.6	147.5	147.6	147.7	147.7	147.7	147.7	147.7	148.4	149.7
175°	148.6	148.6	148.6	148.6	148.6	148.6	148.3	147.9	147.7	148.1	149.0
177.5°	148.6	148.6	148.6	148.6	148.6	148.6	148.4	148.1	147.9	148.2	148.9
180°	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6

TEST NUMBER: P934082

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9	1390.9
2.5°	1342.3	1338.3	1343.6	1329.1	1343.6	1338.3	1342.3	1351.5	1343.6	1348.9	1354.2
5°	1177.8	1171.2	1150.2	1133.0	1150.2	1171.2	1177.8	1205.5	1218.6	1242.2	1273.9
7.5°	1052.8	1047.5	1042.2	1031.7	1042.2	1047.5	1052.8	1060.6	1073.8	1094.9	1118.6
10°	1025.1	1026.5	1034.3	1033.1	1034.3	1026.5	1025.1	1022.5	1018.5	1022.5	1036.9
12.5°	1096.2	1108.0	1151.5	1148.8	1151.5	1108.0	1096.2	1043.5	1008.1	1001.5	1004.1
15°	1177.8	1181.8	1190.9	1192.2	1190.9	1181.8	1177.8	1156.8	1050.1	1004.1	989.6
17.5°	1185.6	1187.0	1193.6	1193.6	1193.6	1187.0	1185.6	1176.5	1140.9	1079.1	997.5
20°	1179.1	1181.8	1194.9	1197.5	1194.9	1181.8	1179.1	1167.2	1147.5	1125.2	1063.3
22.5°	1176.5	1181.8	1192.2	1190.9	1192.2	1181.8	1176.5	1158.0	1140.9	1125.2	1100.2
25°	1163.3	1163.3	1164.6	1165.9	1164.6	1163.3	1163.3	1148.8	1114.6	1110.6	1096.2
27.5°	1135.6	1138.3	1146.2	1144.9	1146.2	1138.3	1135.6	1130.4	1093.5	1089.6	1079.1
30°	1110.6	1108.0	1101.5	1096.2	1101.5	1108.0	1110.6	1102.8	1065.9	1055.4	1058.1
32.5°	1068.5	1061.9	1055.4	1051.5	1055.4	1061.9	1068.5	1065.9	1038.3	1023.8	1026.5
35°	1018.5	1019.9	1018.5	1014.6	1018.5	1019.9	1018.5	1021.2	1004.1	990.9	989.6
37.5°	983.1	985.6	984.3	979.1	984.3	985.6	983.1	980.4	956.7	952.8	955.4
40°	946.2	947.5	946.2	942.2	946.2	947.5	946.2	940.9	908.1	909.3	918.5
42.5°	910.6	909.3	905.4	902.8	905.4	909.3	910.6	902.8	860.6	856.7	873.8
45°	869.8	871.2	863.2	859.3	863.2	871.2	869.8	864.6	821.2	810.6	822.5
47.5°	829.1	829.1	822.5	818.5	822.5	829.1	829.1	822.5	776.4	765.9	772.5
50°	785.6	784.4	775.1	773.8	775.1	784.4	785.6	781.7	733.0	723.8	723.8
52.5°	735.6	735.6	736.9	739.5	736.9	735.6	735.6	736.9	693.5	684.3	681.7
55°	692.2	693.5	702.7	705.4	702.7	693.5	692.2	692.2	652.7	643.5	638.2
57.5°	647.4	647.4	654.1	654.1	654.1	647.4	647.4	644.8	606.7	598.8	596.1
60°	596.1	598.8	604.0	602.7	604.0	598.8	596.1	593.5	560.5	555.4	546.1
62.5°	542.1	544.8	546.1	543.5	546.1	544.8	542.1	534.3	514.5	510.5	498.7
65°	485.6	488.2	489.5	486.9	489.5	488.2	485.6	481.7	467.1	460.6	450.1
67.5°	427.7	426.4	425.1	430.3	425.1	426.4	427.7	422.4	413.2	408.0	393.4
70°	368.4	368.4	367.1	369.8	367.1	368.4	368.4	364.5	359.3	355.3	342.1
72.5°	305.3	304.0	309.3	305.3	309.3	304.0	305.3	304.0	301.4	297.4	284.3
75°	243.4	246.1	243.4	247.4	243.4	246.1	243.4	244.7	243.4	240.8	231.6
77.5°	185.6	188.1	185.6	185.6	185.6	188.1	185.6	186.8	186.8	186.8	179.0
80°	131.6	130.3	130.3	129.0	130.3	130.3	131.6	131.6	132.9	130.3	127.7
82.5°	84.3	82.9	82.9	85.6	82.9	82.9	84.3	85.6	82.9	82.9	82.9
85°	46.0	47.4	44.7	44.7	44.7	47.4	46.0	43.4	46.0	46.0	44.7
87.5°	17.1	15.8	15.8	15.8	15.8	15.8	17.1	18.4	18.4	18.4	19.7
90°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	5.1	6.8	7.6	6.5
92.5°	18.9	18.1	15.1	12.2	15.1	18.1	18.9	26.9	37.4	42.7	37.5
95°	64.3	62.1	53.0	43.8	53.0	62.1	64.3	84.5	111.4	124.8	105.4
97.5°	148.5	144.1	126.8	109.5	126.8	144.1	148.5	161.3	178.3	186.8	154.4
100°	208.6	203.4	182.8	162.0	182.8	203.4	208.6	207.7	206.4	205.8	169.9
102.5°	259.9	255.4	237.6	219.9	237.6	255.4	259.9	243.6	222.0	211.2	174.8
105°	319.7	317.3	307.9	298.3	307.9	317.3	319.7	283.4	234.9	210.6	175.3
107.5°	350.9	351.5	353.8	356.1	353.8	351.5	350.9	300.1	232.5	198.6	167.5
110°	358.9	361.3	371.2	381.2	371.2	361.3	358.9	302.1	226.5	188.6	160.7

TEST NUMBER: P934082

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	353.8	357.6	372.8	388.0	372.8	357.6	353.8	295.7	218.3	179.6	154.6
115°	336.4	341.7	362.9	384.1	362.9	341.7	336.4	280.6	206.0	168.7	147.7
117.5°	312.6	318.5	341.9	365.4	341.9	318.5	312.6	262.1	194.9	161.3	143.3
120°	296.6	302.3	325.1	347.8	325.1	302.3	296.6	250.5	188.9	158.2	141.8
122.5°	280.5	286.1	308.6	331.1	308.6	286.1	280.5	238.9	183.6	155.9	141.0
125°	259.3	264.4	285.2	305.9	285.2	264.4	259.3	224.0	176.9	153.4	140.4
127.5°	242.2	246.6	264.0	281.5	264.0	246.6	242.2	211.9	171.5	151.3	140.0
130°	231.5	235.5	251.6	267.7	251.6	235.5	231.5	204.5	168.5	150.5	140.3
132.5°	222.3	225.9	240.3	254.8	240.3	225.9	222.3	198.1	165.9	149.8	140.4
135°	209.3	212.3	224.9	237.3	224.9	212.3	209.3	189.0	162.0	148.6	140.3
137.5°	199.7	202.3	212.4	222.7	212.4	202.3	199.7	182.6	159.8	148.4	141.1
140°	192.0	194.4	203.9	213.4	203.9	194.4	192.0	177.3	157.6	147.7	141.3
142.5°	186.7	188.7	196.9	205.1	196.9	188.7	186.7	173.7	156.4	147.7	141.8
145°	178.6	180.2	186.4	192.5	186.4	180.2	178.6	167.9	153.8	146.7	141.8
147.5°	171.8	173.1	178.2	183.4	178.2	173.1	171.8	163.4	152.3	146.7	142.8
150°	167.9	168.9	173.1	177.3	173.1	168.9	167.9	160.9	151.4	146.7	143.3
152.5°	164.8	165.6	168.7	171.9	168.7	165.6	164.8	158.8	150.7	146.7	143.6
155°	161.2	161.7	163.7	165.8	163.7	161.7	161.2	156.4	149.9	146.7	144.3
157.5°	157.9	158.3	159.8	161.3	159.8	158.3	157.9	154.2	149.2	146.7	145.1
160°	156.3	156.5	157.4	158.2	157.4	156.5	156.3	153.1	148.8	146.7	145.4
162.5°	154.8	155.0	155.8	156.6	155.8	155.0	154.8	152.1	148.5	146.7	145.8
165°	152.5	152.7	153.6	154.4	153.6	152.7	152.5	150.6	148.0	146.7	146.3
167.5°	151.5	151.6	151.9	152.3	151.9	151.6	151.5	150.2	148.5	147.7	147.3
170°	151.5	151.5	151.5	151.5	151.5	151.5	151.5	150.2	148.5	147.7	147.7
172.5°	150.7	150.6	150.3	150.0	150.3	150.6	150.7	149.7	148.4	147.7	147.7
175°	149.6	149.6	149.6	149.6	149.6	149.6	149.6	149.0	148.1	147.7	147.9
177.5°	149.4	149.3	149.0	148.6	149.0	149.3	149.4	148.9	148.2	147.9	148.1
180°	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6	148.6

TEST NUMBER: P934082

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1390.9	1390.9	1390.9	1390.9	1390.9
2.5°	1373.9	1380.5	1384.3	1389.6	1402.8
5°	1321.2	1346.2	1354.2	1373.9	1397.6
7.5°	1205.5	1281.8	1302.8	1350.2	1387.0
10°	1093.5	1169.9	1206.8	1318.6	1373.9
12.5°	1036.9	1081.8	1106.8	1263.3	1355.5
15°	1001.5	1033.1	1051.5	1189.6	1334.3
17.5°	973.8	996.2	1009.3	1117.2	1305.5
20°	956.7	967.2	979.1	1064.6	1272.5
22.5°	944.8	938.2	947.5	1027.8	1227.8
25°	936.9	911.9	922.5	998.8	1175.2
27.5°	943.5	888.2	892.2	972.5	1119.9
30°	944.8	859.3	860.6	944.8	1058.1
32.5°	935.6	829.1	830.4	910.6	988.2
35°	913.2	793.5	792.2	871.2	893.5
37.5°	883.0	755.4	755.4	827.8	789.5
40°	846.2	717.2	721.1	771.1	697.5
42.5°	801.4	676.4	681.7	696.1	629.1
45°	752.7	636.9	640.8	588.2	576.4
47.5°	698.8	596.1	597.4	488.2	559.3
50°	634.3	554.0	548.8	418.5	558.0
52.5°	577.7	508.0	492.1	379.0	506.7
55°	522.4	459.3	425.1	348.7	469.8
57.5°	473.7	396.1	363.2	313.2	461.9
60°	429.0	334.3	309.3	275.0	423.7
62.5°	392.1	288.2	283.0	248.7	384.3
65°	352.7	256.6	255.3	226.4	326.4
67.5°	314.5	235.6	234.3	205.3	248.7
70°	273.7	213.1	210.6	183.0	184.3
72.5°	231.6	188.1	185.6	164.5	152.7
75°	189.5	159.3	157.9	143.4	123.7
77.5°	148.7	126.3	129.0	115.8	90.8
80°	106.6	92.1	94.7	82.9	68.4
82.5°	71.0	60.6	63.1	52.6	46.0
85°	39.4	34.3	35.6	27.6	21.0
87.5°	18.4	15.8	15.8	10.6	6.6
90°	4.4	2.8	2.6	1.8	1.0
92.5°	27.1	19.2	17.5	10.8	4.0
95°	66.6	37.5	34.5	22.0	9.6
97.5°	89.7	41.2	38.4	27.5	16.5
100°	98.1	44.3	41.8	31.9	21.9
102.5°	102.0	47.4	45.1	35.8	26.5
105°	104.9	52.0	50.0	42.2	34.4
107.5°	105.4	58.8	57.0	49.6	42.3
110°	104.6	62.5	60.9	54.3	47.7

TEST NUMBER: P934082

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	104.6	67.1	65.5	59.3	53.0
115°	105.6	74.0	72.5	66.7	61.0
117.5°	107.6	80.7	79.4	74.1	68.8
120°	109.1	84.6	83.4	78.4	73.4
122.5°	111.4	89.1	87.8	82.9	77.9
125°	114.5	95.1	93.9	89.3	84.8
127.5°	117.6	100.8	99.6	95.0	90.3
130°	119.9	104.6	103.3	98.3	93.3
132.5°	121.7	107.7	106.5	101.5	96.5
135°	123.7	111.3	110.2	105.6	101.1
137.5°	126.7	115.8	114.7	110.3	105.8
140°	128.5	118.9	117.9	113.7	109.7
142.5°	130.1	121.2	120.2	116.4	112.6
145°	132.1	124.7	123.9	120.5	117.2
147.5°	135.0	129.1	128.3	125.0	121.8
150°	136.5	131.4	130.7	127.7	124.8
152.5°	137.4	132.9	132.3	130.1	127.9
155°	139.6	136.2	135.8	134.1	132.5
157.5°	141.8	139.4	139.0	137.4	135.9
160°	142.8	140.9	140.6	139.3	138.1
162.5°	143.9	142.5	142.3	141.3	140.4
165°	145.4	144.8	144.6	143.7	142.9
167.5°	146.6	146.1	146.0	145.6	145.2
170°	147.6	147.6	147.5	147.1	146.7
172.5°	147.7	147.7	147.7	147.6	147.5
175°	148.3	148.6	148.6	148.6	148.6
177.5°	148.4	148.6	148.6	148.6	148.6
180°	148.6	148.6	148.6	148.6	148.6

TEST NUMBER: P934082

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-4-2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.01	17.21	16.68	17.89	18.68	18.81	20.01	19.47	20.69	21.48
	3H	16.52	17.59	17.19	18.28	19.10	20.17	21.25	20.85	21.94	22.76
	4H	16.72	17.74	17.42	18.44	19.27	20.63	21.64	21.32	22.34	23.18
	6H	16.86	17.80	17.57	18.51	19.36	20.92	21.86	21.63	22.57	23.42
	8H	16.87	17.76	17.59	18.49	19.35	21.00	21.89	21.72	22.62	23.48
	12H	16.85	17.71	17.58	18.43	19.31	21.05	21.90	21.77	22.62	23.50
4H	2H	17.08	18.10	17.78	18.80	19.63	19.26	20.28	19.96	20.98	21.81
	3H	18.14	18.98	18.85	19.72	20.57	20.79	21.64	21.50	22.37	23.23
	4H	18.43	19.20	19.15	19.93	20.82	21.33	22.09	22.05	22.83	23.72
	6H	18.57	19.24	19.32	20.00	20.89	21.70	22.37	22.45	23.13	24.02
	8H	18.59	19.21	19.34	19.97	20.87	21.81	22.43	22.56	23.19	24.10
	12H	18.57	19.13	19.34	19.91	20.82	21.88	22.44	22.65	23.22	24.13
8H	4H	18.90	19.53	19.65	20.29	21.19	21.48	22.10	22.23	22.86	23.76
	6H	19.18	19.69	19.96	20.50	21.40	21.92	22.44	22.70	23.24	24.14
	8H	19.22	19.68	20.02	20.49	21.41	22.07	22.53	22.86	23.33	24.25
	12H	19.22	19.63	20.02	20.42	21.40	22.18	22.58	22.97	23.38	24.36
12H	4H	18.92	19.48	19.69	20.27	21.18	21.46	22.02	22.23	22.80	23.71
	6H	19.24	19.70	20.03	20.50	21.42	21.92	22.38	22.71	23.18	24.10
	8H	19.32	19.73	20.12	20.52	21.50	22.09	22.50	22.89	23.29	24.27

END OF REPORT