

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934487

Luminaire Tested: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934487
REPORT IS A COMBINATION OF REPORTS P933699 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8385.3 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934487

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K

Luminous Intensity Polar Plot



TEST NUMBER: P934487

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69
1	101	97	93	89	95	91	88	84	80	78	75	71	69	67	62	60	59
2	92	85	78	73	86	80	74	69	70	66	63	62	59	56	54	52	50
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42
4	77	66	58	52	72	62	55	49	55	49	45	49	44	41	43	39	36
5	71	59	50	44	66	56	48	42	49	43	39	44	39	35	39	35	32
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25
8	56	43	35	30	52	41	34	29	37	31	27	33	28	24	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12906	12906	12906	12906
5°	12997	13028	12997	10244
10°	12906	12833	12906	9175
15°	12761	12555	12761	10484
20°	12489	12226	12489	10506
25°	11937	11746	11937	10283
30°	11227	11347	11227	9794
35°	10004	10841	10004	9257
40°	8331	10248	8331	8851
45°	7439	9553	7439	8384
50°	7896	8724	7896	7916
55°	7424	7830	7424	7646
60°	7642	6651	7642	7002
65°	6918	5497	6918	6145
70°	4779	4381	4779	5151
75°	4176	3239	4176	3879
80°	3339	2142	3339	2331
85°	1884	1135	1884	964

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 11410 cd/sqm

TEST NUMBER: P934487

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.3	2.2
10°-20°	534.7	6.4
20°-30°	826.5	9.9
30°-40°	986.7	11.8
40°-50°	992.5	11.8
50°-60°	863.6	10.3
60°-70°	612.3	7.3
70°-80°	323.9	3.9
80°-90°	82.4	1.0
90°-100°	223.7	2.7
100°-110°	588.0	7.0
110°-120°	609.7	7.3
120°-130°	489.0	5.8
130°-140°	383.7	4.6
140°-150°	294.5	3.5
150°-160°	212.1	2.5
160°-170°	129.8	1.5
170°-180°	43.8	0.5
0°-30°	1549.6	18.5
0°-40°	2536.3	30.2
0°-60°	4392.4	52.4
0°-90°	5411.0	64.5
90°-120°	1421.3	17.0
90°-150°	2588.6	30.9
90°-180°	2974.0	35.5
0°-180°	8385.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2086	2086	2086	2086	2086	
5°	2096	2161	2096	1699	2096	199
15°	2001	2142	2001	1788	2001	563
25°	1762	1998	1762	1749	1762	809
35°	1340	1782	1340	1522	1340	829
45°	864	1468	864	1289	864	692
55°	705	1084	705	1058	705	647
65°	490	653	490	730	490	468
75°	186	310	186	371	186	195
85°	32	79	32	67	32	43
90°	3	12	3	12	3	4
95°	30	135	30	135	30	33
105°	106	921	106	921	106	112
115°	188	1186	188	1186	188	186
125°	262	944	262	944	262	232
135°	312	733	312	733	312	241
145°	362	594	362	594	362	227
155°	409	512	409	512	409	188
165°	441	477	441	477	441	125
175°	459	462	459	462	459	44
180°	459	459	459	459	459	

TEST NUMBER: P934487

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2
2.5°	2104.0	2104.0	2115.9	2119.8	2119.8	2113.9	2107.9	2113.9	2131.6	2137.6	2135.6
5°	2096.1	2111.9	2133.6	2137.6	2141.5	2139.5	2135.6	2139.5	2159.2	2163.2	2165.2
7.5°	2080.3	2109.9	2137.6	2143.5	2149.4	2143.5	2141.5	2145.5	2165.2	2169.2	2169.2
10°	2060.6	2102.1	2133.6	2137.6	2143.5	2137.6	2137.6	2145.5	2165.2	2169.2	2171.1
12.5°	2032.9	2090.2	2119.8	2123.8	2131.6	2129.6	2127.7	2135.6	2155.3	2159.2	2159.2
15°	2001.4	2068.5	2096.1	2100.1	2113.9	2109.9	2109.9	2117.8	2139.5	2145.5	2143.5
17.5°	1957.9	2040.8	2072.5	2078.4	2088.2	2086.2	2088.2	2096.1	2115.9	2119.8	2121.8
20°	1908.6	2003.4	2040.8	2046.8	2056.6	2056.6	2056.6	2066.5	2086.2	2094.2	2094.2
22.5°	1841.5	1963.9	2003.4	2007.3	2019.2	2019.2	2023.1	2036.9	2054.6	2056.6	2056.6
25°	1762.5	1920.5	1954.1	1965.8	1977.7	1983.6	1989.5	1997.5	2003.4	2001.4	2003.4
27.5°	1679.7	1865.2	1908.6	1916.5	1932.3	1938.2	1946.1	1948.1	1950.1	1955.9	1952.1
30°	1586.9	1788.2	1853.4	1861.2	1886.9	1890.8	1882.9	1886.9	1896.8	1900.8	1904.7
32.5°	1482.2	1673.8	1796.1	1813.9	1837.5	1825.7	1823.8	1829.7	1845.5	1845.5	1849.4
35°	1340.2	1584.9	1742.8	1758.6	1776.4	1762.5	1770.5	1772.4	1782.2	1788.2	1786.2
37.5°	1184.2	1507.9	1687.5	1699.4	1713.2	1695.5	1707.2	1713.2	1721.1	1717.2	1717.2
40°	1046.1	1387.5	1622.4	1630.4	1642.2	1628.4	1640.2	1644.1	1648.1	1644.1	1642.2
42.5°	943.4	1255.3	1553.4	1563.2	1555.4	1565.2	1569.1	1577.1	1571.1	1563.2	1563.2
45°	864.5	1219.8	1478.4	1490.2	1478.4	1494.1	1500.1	1500.1	1482.2	1478.4	1476.4
47.5°	838.8	1148.7	1403.4	1403.4	1397.4	1417.1	1427.0	1413.2	1395.4	1389.5	1389.5
50°	836.8	1069.8	1300.7	1292.8	1320.4	1344.1	1334.2	1320.4	1306.7	1284.9	1284.9
52.5°	759.8	973.1	1168.4	1198.1	1241.5	1255.3	1239.5	1225.7	1202.0	1192.1	1184.2
55°	704.7	872.4	1048.1	1107.3	1152.7	1170.4	1140.8	1127.0	1091.5	1085.5	1081.7
57.5°	692.8	726.4	937.5	1012.5	1067.8	1065.8	1048.1	1022.4	992.8	986.8	984.9
60°	635.5	525.0	819.1	908.0	965.1	959.2	943.4	919.8	892.1	888.2	884.2
62.5°	576.3	381.0	684.8	785.5	866.5	864.5	850.7	815.1	795.4	785.5	777.7
65°	489.5	319.7	487.5	653.3	769.8	773.7	744.1	718.4	696.7	684.8	683.0
67.5°	373.0	260.6	329.6	544.7	677.0	673.1	635.5	623.7	596.1	590.1	578.3
70°	276.3	173.7	229.0	442.1	586.2	576.3	546.7	533.0	507.3	493.4	485.6
72.5°	229.0	140.1	167.7	343.4	493.4	481.6	456.0	440.1	418.4	406.6	398.7
75°	185.6	148.0	128.3	254.6	400.7	392.8	369.1	353.3	335.6	319.7	321.7
77.5°	136.2	138.1	102.6	187.5	317.7	306.0	292.1	272.4	264.4	248.7	248.7
80°	102.6	108.6	77.0	128.3	229.0	229.0	217.1	203.3	189.4	181.6	181.6
82.5°	69.1	69.1	57.3	80.9	156.0	150.0	142.1	138.1	130.3	126.3	126.3
85°	31.6	39.4	35.6	49.3	84.9	88.8	88.8	84.9	82.9	79.0	80.9
87.5°	9.9	17.7	21.7	27.6	43.4	45.4	47.4	47.4	47.4	49.3	49.3
90°	3.1	5.6	8.1	8.7	13.5	20.1	23.4	20.8	15.5	11.7	11.7
92.5°	12.4	33.3	54.2	59.5	83.6	115.7	131.8	115.4	82.9	58.5	56.2
95°	29.6	67.8	106.2	115.7	205.6	325.4	385.3	343.8	260.9	198.6	191.5
97.5°	51.1	85.0	118.7	127.2	277.0	476.7	576.5	550.3	497.8	458.5	445.0
100°	67.7	98.4	129.1	136.8	302.9	524.5	635.2	637.1	641.0	643.9	628.0
102.5°	81.9	110.6	139.1	146.3	314.8	539.5	651.9	685.2	752.1	802.2	788.5
105°	106.0	130.2	154.4	160.5	323.6	541.2	650.0	724.9	874.6	986.9	979.6
107.5°	130.6	153.2	175.7	181.4	325.3	517.1	613.0	717.4	926.3	1083.0	1084.7
110°	147.2	167.5	187.9	193.0	322.8	495.8	582.3	699.0	932.6	1107.7	1115.3

TEST NUMBER: P934487

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	163.5	183.0	202.4	207.3	322.9	477.2	554.3	673.8	912.7	1091.9	1103.7
115°	188.1	206.1	224.0	228.5	325.9	455.8	520.7	635.8	866.0	1038.6	1055.0
117.5°	212.4	228.8	245.0	249.1	332.0	442.4	497.6	601.5	809.2	965.0	983.2
120°	226.6	241.9	257.3	261.2	336.8	437.8	488.3	583.3	773.1	915.4	933.1
122.5°	240.5	256.0	271.4	275.3	343.9	435.5	481.3	566.7	737.7	865.9	883.3
125°	261.7	275.8	289.9	293.4	353.5	433.6	473.6	546.2	691.4	800.3	816.2
127.5°	279.0	293.2	307.5	311.1	363.0	432.5	467.1	529.5	654.1	747.6	761.0
130°	288.2	303.6	318.9	322.7	370.0	433.1	464.6	520.1	631.2	714.4	726.9
132.5°	297.8	313.1	328.5	332.3	375.7	433.6	462.5	512.2	611.5	686.0	697.2
135°	311.9	325.9	339.8	343.3	381.9	433.2	458.9	500.5	583.7	646.0	655.7
137.5°	326.4	340.2	354.0	357.5	391.0	435.8	458.2	493.3	563.6	616.4	624.3
140°	338.4	351.2	363.8	367.0	396.7	436.2	456.1	486.4	547.2	592.7	600.1
142.5°	347.6	359.4	371.1	374.1	401.4	437.8	456.1	482.8	536.0	576.1	582.5
145°	361.8	372.1	382.4	385.0	407.7	437.8	453.0	474.8	518.4	551.2	556.0
147.5°	376.0	386.0	396.0	398.5	416.6	440.8	453.0	470.1	504.5	530.3	534.3
150°	385.3	394.3	403.3	405.6	421.4	442.4	453.0	467.5	496.5	518.2	521.4
152.5°	394.7	401.6	408.5	410.2	424.4	443.4	453.0	465.3	490.1	508.7	511.0
155°	409.0	414.0	419.0	420.3	431.2	445.7	453.0	462.8	482.6	497.3	498.9
157.5°	419.4	424.3	429.3	430.5	437.9	448.0	453.0	460.6	476.0	487.4	488.5
160°	426.5	430.3	434.1	435.1	441.0	449.0	453.0	459.6	472.7	482.6	483.2
162.5°	433.6	436.4	439.3	440.0	444.3	450.1	453.0	458.6	469.6	477.9	478.5
165°	441.2	443.8	446.4	447.1	449.1	451.7	453.0	457.0	464.8	470.8	471.5
167.5°	448.3	449.5	450.8	451.1	452.8	455.0	456.1	458.7	463.8	467.7	468.0
170°	453.0	454.2	455.5	455.8	455.9	456.0	456.1	458.7	463.8	467.7	467.7
172.5°	455.5	455.8	456.0	456.1	456.1	456.1	456.1	458.1	462.1	465.2	465.0
175°	458.9	458.9	458.9	458.9	458.0	456.7	456.1	457.4	460.0	461.8	461.8
177.5°	458.9	458.9	458.9	458.9	458.2	457.2	456.7	457.7	459.8	461.2	460.9
180°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9

TEST NUMBER: P934487

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2
2.5°	2139.5	2133.6	2139.5	2135.6	2137.6	2131.6	2113.9	2107.9	2113.9	2119.8	2119.8
5°	2165.2	2161.2	2165.2	2165.2	2163.2	2159.2	2139.5	2135.6	2139.5	2141.5	2137.6
7.5°	2173.1	2167.2	2173.1	2169.2	2169.2	2165.2	2145.5	2141.5	2143.5	2149.4	2143.5
10°	2173.1	2167.2	2173.1	2171.1	2169.2	2165.2	2145.5	2137.6	2137.6	2143.5	2137.6
12.5°	2163.2	2159.2	2163.2	2159.2	2159.2	2155.3	2135.6	2127.7	2129.6	2131.6	2123.8
15°	2147.5	2141.5	2147.5	2143.5	2145.5	2139.5	2117.8	2109.9	2109.9	2113.9	2100.1
17.5°	2123.8	2115.9	2123.8	2121.8	2119.8	2115.9	2096.1	2088.2	2086.2	2088.2	2078.4
20°	2096.1	2090.2	2096.1	2094.2	2094.2	2086.2	2066.5	2056.6	2056.6	2056.6	2046.8
22.5°	2052.7	2046.8	2052.7	2056.6	2056.6	2054.6	2036.9	2023.1	2019.2	2019.2	2007.3
25°	2003.4	1997.5	2003.4	2003.4	2001.4	2003.4	1997.5	1989.5	1983.6	1977.7	1965.8
27.5°	1955.9	1952.1	1955.9	1952.1	1955.9	1950.1	1948.1	1946.1	1938.2	1932.3	1916.5
30°	1908.6	1904.7	1908.6	1904.7	1900.8	1896.8	1886.9	1882.9	1890.8	1886.9	1861.2
32.5°	1849.4	1845.5	1849.4	1849.4	1845.5	1845.5	1829.7	1823.8	1825.7	1837.5	1813.9
35°	1788.2	1782.2	1788.2	1786.2	1788.2	1782.2	1772.4	1770.5	1762.5	1776.4	1758.6
37.5°	1717.2	1711.2	1717.2	1717.2	1717.2	1721.1	1713.2	1707.2	1695.5	1713.2	1699.4
40°	1644.1	1636.2	1644.1	1642.2	1644.1	1648.1	1644.1	1640.2	1628.4	1642.2	1630.4
42.5°	1561.2	1559.2	1561.2	1563.2	1563.2	1571.1	1577.1	1569.1	1565.2	1555.4	1563.2
45°	1472.4	1468.5	1472.4	1476.4	1478.4	1482.2	1500.1	1500.1	1494.1	1478.4	1490.2
47.5°	1377.7	1367.8	1377.7	1389.5	1389.5	1395.4	1413.2	1427.0	1417.1	1397.4	1403.4
50°	1277.0	1279.0	1277.0	1284.9	1284.9	1306.7	1320.4	1334.2	1344.1	1320.4	1292.8
52.5°	1178.4	1176.4	1178.4	1184.2	1192.1	1202.0	1225.7	1239.5	1255.3	1241.5	1198.1
55°	1079.7	1083.5	1079.7	1081.7	1085.5	1091.5	1127.0	1140.8	1170.4	1152.7	1107.3
57.5°	981.0	975.0	981.0	984.9	986.8	992.8	1022.4	1048.1	1065.8	1067.8	1012.5
60°	866.5	858.6	866.5	884.2	888.2	892.1	919.8	943.4	959.2	965.1	908.0
62.5°	765.8	752.0	765.8	777.7	785.5	795.4	815.1	850.7	864.5	866.5	785.5
65°	659.3	653.3	659.3	683.0	684.8	696.7	718.4	744.1	773.7	769.8	653.3
67.5°	562.5	562.5	562.5	578.3	590.1	596.1	623.7	635.5	673.1	677.0	544.7
70°	473.7	471.7	473.7	485.6	493.4	507.3	533.0	546.7	576.3	586.2	442.1
72.5°	388.8	386.8	388.8	398.7	406.6	418.4	440.1	456.0	481.6	493.4	343.4
75°	313.8	309.9	313.8	321.7	319.7	335.6	353.3	369.1	392.8	400.7	254.6
77.5°	240.8	240.8	240.8	248.7	248.7	264.4	272.4	292.1	306.0	317.7	187.5
80°	179.6	177.7	179.6	181.6	181.6	189.4	203.3	217.1	229.0	229.0	128.3
82.5°	126.3	122.4	126.3	126.3	126.3	130.3	138.1	142.1	150.0	156.0	80.9
85°	79.0	79.0	79.0	80.9	79.0	82.9	84.9	88.8	88.8	84.9	49.3
87.5°	51.3	49.3	51.3	49.3	49.3	47.4	47.4	47.4	45.4	43.4	27.6
90°	11.7	11.7	11.7	11.7	11.7	15.5	20.8	23.4	20.1	13.5	8.7
92.5°	46.8	37.5	46.8	56.2	58.5	82.9	115.4	131.8	115.7	83.6	59.5
95°	163.3	135.2	163.3	191.5	198.6	260.9	343.8	385.3	325.4	205.6	115.7
97.5°	391.4	337.8	391.4	445.0	458.5	497.8	550.3	576.5	476.7	277.0	127.2
100°	564.0	500.1	564.0	628.0	643.9	641.0	637.1	635.2	524.5	302.9	136.8
102.5°	733.8	679.0	733.8	788.5	802.2	752.1	685.2	651.9	539.5	314.8	146.3
105°	950.2	920.7	950.2	979.6	986.9	874.6	724.9	650.0	541.2	323.6	160.5
107.5°	1091.8	1099.0	1091.8	1084.7	1083.0	926.3	717.4	613.0	517.1	325.3	181.4
110°	1145.9	1176.6	1145.9	1115.3	1107.7	932.6	699.0	582.3	495.8	322.8	193.0

TEST NUMBER: P934487

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1150.8	1197.8	1150.8	1103.7	1091.9	912.7	673.8	554.3	477.2	322.9	207.3
115°	1120.2	1185.5	1120.2	1055.0	1038.6	866.0	635.8	520.7	455.8	325.9	228.5
117.5°	1055.6	1128.0	1055.6	983.2	965.0	809.2	601.5	497.6	442.4	332.0	249.1
120°	1003.4	1073.8	1003.4	933.1	915.4	773.1	583.3	488.3	437.8	336.8	261.2
122.5°	952.7	1022.0	952.7	883.3	865.9	737.7	566.7	481.3	435.5	343.9	275.3
125°	880.2	944.1	880.2	816.2	800.3	691.4	546.2	473.6	433.6	353.5	293.4
127.5°	815.0	869.0	815.0	761.0	747.6	654.1	529.5	467.1	432.5	363.0	311.1
130°	776.7	826.5	776.7	726.9	714.4	631.2	520.1	464.6	433.1	370.0	322.7
132.5°	741.8	786.4	741.8	697.2	686.0	611.5	512.2	462.5	433.6	375.7	332.3
135°	694.1	732.6	694.1	655.7	646.0	583.7	500.5	458.9	433.2	381.9	343.3
137.5°	655.9	687.3	655.9	624.3	616.4	563.6	493.3	458.2	435.8	391.0	357.5
140°	629.5	659.0	629.5	600.1	592.7	547.2	486.4	456.1	436.2	396.7	367.0
142.5°	607.8	633.1	607.8	582.5	576.1	536.0	482.8	456.1	437.8	401.4	374.1
145°	575.2	594.3	575.2	556.0	551.2	518.4	474.8	453.0	437.8	407.7	385.0
147.5°	550.1	565.9	550.1	534.3	530.3	504.5	470.1	453.0	440.8	416.6	398.5
150°	534.4	547.2	534.4	521.4	518.2	496.5	467.5	453.0	442.4	421.4	405.6
152.5°	520.8	530.6	520.8	511.0	508.7	490.1	465.3	453.0	443.4	424.4	410.2
155°	505.4	511.7	505.4	498.9	497.3	482.6	462.8	453.0	445.7	431.2	420.3
157.5°	493.1	497.6	493.1	488.5	487.4	476.0	460.6	453.0	448.0	437.9	430.5
160°	485.7	488.3	485.7	483.2	482.6	472.7	459.6	453.0	449.0	441.0	435.1
162.5°	481.0	483.5	481.0	478.5	477.9	469.6	458.6	453.0	450.1	444.3	440.0
165°	474.1	476.7	474.1	471.5	470.8	464.8	457.0	453.0	451.7	449.1	447.1
167.5°	469.1	470.2	469.1	468.0	467.7	463.8	458.7	456.1	455.0	452.8	451.1
170°	467.7	467.7	467.7	467.7	467.7	463.8	458.7	456.1	456.0	455.9	455.8
172.5°	464.0	463.1	464.0	465.0	465.2	462.1	458.1	456.1	456.1	456.1	456.1
175°	461.8	461.8	461.8	461.8	461.8	460.0	457.4	456.1	456.7	458.0	458.9
177.5°	460.0	458.9	460.0	460.9	461.2	459.8	457.7	456.7	457.2	458.2	458.9
180°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9

TEST NUMBER: P934487

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2
2.5°	2115.9	2104.0	2104.0	2084.2	2076.4	2070.5	2060.6	2030.9	2023.1	2015.2	2027.1
5°	2133.6	2111.9	2096.1	2060.6	2030.9	2019.2	1981.6	1910.6	1863.2	1827.7	1807.9
7.5°	2137.6	2109.9	2080.3	2025.1	1954.1	1922.4	1807.9	1677.7	1642.2	1610.5	1590.8
10°	2133.6	2102.1	2060.6	1977.7	1809.9	1754.7	1640.2	1555.4	1533.6	1527.7	1533.6
12.5°	2119.8	2090.2	2032.9	1894.8	1659.9	1622.4	1555.4	1506.0	1502.1	1511.9	1565.2
15°	2096.1	2068.5	2001.4	1784.2	1577.1	1549.4	1502.1	1484.2	1506.0	1575.1	1734.9
17.5°	2072.5	2040.8	1957.9	1675.7	1513.8	1494.1	1460.5	1496.1	1618.5	1711.2	1764.5
20°	2040.8	2003.4	1908.6	1596.8	1468.5	1450.7	1434.9	1594.8	1687.5	1721.1	1750.7
22.5°	2003.4	1963.9	1841.5	1541.5	1421.1	1407.2	1417.1	1650.1	1687.5	1711.2	1736.9
25°	1954.1	1920.5	1762.5	1498.1	1383.6	1367.8	1405.4	1644.1	1665.8	1671.8	1723.1
27.5°	1908.6	1865.2	1679.7	1458.6	1338.2	1332.2	1415.2	1618.5	1634.2	1640.2	1695.5
30°	1853.4	1788.2	1586.9	1417.1	1290.8	1288.8	1417.1	1586.9	1582.9	1598.8	1654.0
32.5°	1796.1	1673.8	1482.2	1365.8	1245.4	1243.5	1403.4	1539.5	1535.5	1557.2	1598.8
35°	1742.8	1584.9	1340.2	1306.7	1188.2	1190.1	1369.8	1484.2	1486.2	1506.0	1531.6
37.5°	1687.5	1507.9	1184.2	1241.5	1133.0	1133.0	1324.4	1432.9	1429.0	1434.9	1470.4
40°	1622.4	1387.5	1046.1	1156.7	1081.7	1075.7	1269.1	1377.7	1363.8	1361.9	1411.2
42.5°	1553.4	1255.3	943.4	1044.1	1022.4	1014.5	1202.0	1310.5	1284.9	1290.8	1354.0
45°	1478.4	1219.8	864.5	882.3	961.2	955.3	1129.0	1233.5	1215.8	1231.7	1296.8
47.5°	1403.4	1148.7	838.8	732.3	896.1	894.1	1048.1	1158.5	1148.7	1164.5	1233.5
50°	1300.7	1069.8	836.8	627.7	823.1	831.0	951.4	1085.5	1085.5	1099.4	1172.4
52.5°	1168.4	973.1	759.8	568.4	738.1	761.8	866.5	1022.4	1026.4	1040.1	1105.3
55°	1048.1	872.4	704.7	523.0	637.5	688.8	783.6	957.3	965.1	979.0	1038.2
57.5°	937.5	726.4	692.8	469.7	544.7	594.1	710.5	894.1	898.1	909.9	967.1
60°	819.1	525.0	635.5	412.5	463.8	501.3	643.4	819.1	833.0	840.8	890.1
62.5°	684.8	381.0	576.3	373.0	424.4	432.3	588.1	748.1	765.8	771.7	801.4
65°	487.5	319.7	489.5	339.4	382.9	384.9	529.0	675.0	690.8	700.7	722.4
67.5°	329.6	260.6	373.0	307.9	351.3	353.3	471.7	590.1	611.8	619.7	633.6
70°	229.0	173.7	276.3	274.4	315.8	319.7	410.6	513.1	533.0	538.8	546.7
72.5°	167.7	140.1	229.0	246.7	278.3	282.3	347.4	426.3	446.1	452.0	456.0
75°	128.3	148.0	185.6	215.1	236.8	238.8	284.3	347.4	361.1	365.1	367.1
77.5°	102.6	138.1	136.2	173.7	193.4	189.4	223.0	268.4	280.3	280.3	280.3
80°	77.0	108.6	102.6	124.3	142.1	138.1	159.9	191.4	195.4	199.3	197.4
82.5°	57.3	69.1	69.1	79.0	94.7	90.8	106.6	124.3	124.3	124.3	128.3
85°	35.6	39.4	31.6	41.4	53.3	51.3	59.3	67.1	69.1	69.1	65.1
87.5°	21.7	17.7	9.9	15.8	23.7	23.7	27.6	29.6	27.6	27.6	27.6
90°	8.1	5.6	3.1	5.6	8.1	8.7	13.5	20.1	23.4	20.8	15.5
92.5°	54.2	33.3	12.4	33.3	54.2	59.5	83.6	115.7	131.8	115.4	82.9
95°	106.2	67.8	29.6	67.8	106.2	115.7	205.6	325.4	385.3	343.8	260.9
97.5°	118.7	85.0	51.1	85.0	118.7	127.2	277.0	476.7	576.5	550.3	497.8
100°	129.1	98.4	67.7	98.4	129.1	136.8	302.9	524.5	635.2	637.1	641.0
102.5°	139.1	110.6	81.9	110.6	139.1	146.3	314.8	539.5	651.9	685.2	752.1
105°	154.4	130.2	106.0	130.2	154.4	160.5	323.6	541.2	650.0	724.9	874.6
107.5°	175.7	153.2	130.6	153.2	175.7	181.4	325.3	517.1	613.0	717.4	926.3
110°	187.9	167.5	147.2	167.5	187.9	193.0	322.8	495.8	582.3	699.0	932.6

TEST NUMBER: P934487

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	202.4	183.0	163.5	183.0	202.4	207.3	322.9	477.2	554.3	673.8	912.7
115°	224.0	206.1	188.1	206.1	224.0	228.5	325.9	455.8	520.7	635.8	866.0
117.5°	245.0	228.8	212.4	228.8	245.0	249.1	332.0	442.4	497.6	601.5	809.2
120°	257.3	241.9	226.6	241.9	257.3	261.2	336.8	437.8	488.3	583.3	773.1
122.5°	271.4	256.0	240.5	256.0	271.4	275.3	343.9	435.5	481.3	566.7	737.7
125°	289.9	275.8	261.7	275.8	289.9	293.4	353.5	433.6	473.6	546.2	691.4
127.5°	307.5	293.2	279.0	293.2	307.5	311.1	363.0	432.5	467.1	529.5	654.1
130°	318.9	303.6	288.2	303.6	318.9	322.7	370.0	433.1	464.6	520.1	631.2
132.5°	328.5	313.1	297.8	313.1	328.5	332.3	375.7	433.6	462.5	512.2	611.5
135°	339.8	325.9	311.9	325.9	339.8	343.3	381.9	433.2	458.9	500.5	583.7
137.5°	354.0	340.2	326.4	340.2	354.0	357.5	391.0	435.8	458.2	493.3	563.6
140°	363.8	351.2	338.4	351.2	363.8	367.0	396.7	436.2	456.1	486.4	547.2
142.5°	371.1	359.4	347.6	359.4	371.1	374.1	401.4	437.8	456.1	482.8	536.0
145°	382.4	372.1	361.8	372.1	382.4	385.0	407.7	437.8	453.0	474.8	518.4
147.5°	396.0	386.0	376.0	386.0	396.0	398.5	416.6	440.8	453.0	470.1	504.5
150°	403.3	394.3	385.3	394.3	403.3	405.6	421.4	442.4	453.0	467.5	496.5
152.5°	408.5	401.6	394.7	401.6	408.5	410.2	424.4	443.4	453.0	465.3	490.1
155°	419.0	414.0	409.0	414.0	419.0	420.3	431.2	445.7	453.0	462.8	482.6
157.5°	429.3	424.3	419.4	424.3	429.3	430.5	437.9	448.0	453.0	460.6	476.0
160°	434.1	430.3	426.5	430.3	434.1	435.1	441.0	449.0	453.0	459.6	472.7
162.5°	439.3	436.4	433.6	436.4	439.3	440.0	444.3	450.1	453.0	458.6	469.6
165°	446.4	443.8	441.2	443.8	446.4	447.1	449.1	451.7	453.0	457.0	464.8
167.5°	450.8	449.5	448.3	449.5	450.8	451.1	452.8	455.0	456.1	458.7	463.8
170°	455.5	454.2	453.0	454.2	455.5	455.8	455.9	456.0	456.1	458.7	463.8
172.5°	456.0	455.8	455.5	455.8	456.0	456.1	456.1	456.1	456.1	458.1	462.1
175°	458.9	458.9	458.9	458.9	458.9	458.9	458.0	456.7	456.1	457.4	460.0
177.5°	458.9	458.9	458.9	458.9	458.9	458.9	458.2	457.2	456.7	457.7	459.8
180°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9

TEST NUMBER: P934487

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2	2086.2
2.5°	2013.2	2007.3	2015.2	1993.5	2015.2	2007.3	2013.2	2027.1	2015.2	2023.1	2030.9
5°	1766.5	1756.6	1725.1	1699.4	1725.1	1756.6	1766.5	1807.9	1827.7	1863.2	1910.6
7.5°	1579.0	1571.1	1563.2	1547.4	1563.2	1571.1	1579.0	1590.8	1610.5	1642.2	1677.7
10°	1537.5	1539.5	1551.4	1549.4	1551.4	1539.5	1537.5	1533.6	1527.7	1533.6	1555.4
12.5°	1644.1	1661.9	1727.1	1723.1	1727.1	1661.9	1644.1	1565.2	1511.9	1502.1	1506.0
15°	1766.5	1772.4	1786.2	1788.2	1786.2	1772.4	1766.5	1734.9	1575.1	1506.0	1484.2
17.5°	1778.4	1780.4	1790.2	1790.2	1790.2	1780.4	1778.4	1764.5	1711.2	1618.5	1496.1
20°	1768.5	1772.4	1792.2	1796.1	1792.2	1772.4	1768.5	1750.7	1721.1	1687.5	1594.8
22.5°	1764.5	1772.4	1788.2	1786.2	1788.2	1772.4	1764.5	1736.9	1711.2	1687.5	1650.1
25°	1744.8	1744.8	1746.8	1748.8	1746.8	1744.8	1744.8	1723.1	1671.8	1665.8	1644.1
27.5°	1703.4	1707.2	1719.1	1717.2	1719.1	1707.2	1703.4	1695.5	1640.2	1634.2	1618.5
30°	1665.8	1661.9	1652.1	1644.1	1652.1	1661.9	1665.8	1654.0	1598.8	1582.9	1586.9
32.5°	1602.7	1592.8	1582.9	1577.1	1582.9	1592.8	1602.7	1598.8	1557.2	1535.5	1539.5
35°	1527.7	1529.7	1527.7	1521.8	1527.7	1529.7	1527.7	1531.6	1506.0	1486.2	1484.2
37.5°	1474.4	1478.4	1476.4	1468.5	1476.4	1478.4	1474.4	1470.4	1434.9	1429.0	1432.9
40°	1419.1	1421.1	1419.1	1413.2	1419.1	1421.1	1419.1	1411.2	1361.9	1363.8	1377.7
42.5°	1365.8	1363.8	1357.9	1354.0	1357.9	1363.8	1365.8	1354.0	1290.8	1284.9	1310.5
45°	1304.7	1306.7	1294.8	1288.8	1294.8	1306.7	1304.7	1296.8	1231.7	1215.8	1233.5
47.5°	1243.5	1243.5	1233.5	1227.7	1233.5	1243.5	1243.5	1233.5	1164.5	1148.7	1158.5
50°	1178.4	1176.4	1162.5	1160.5	1162.5	1176.4	1178.4	1172.4	1099.4	1085.5	1085.5
52.5°	1103.4	1103.4	1105.3	1109.2	1105.3	1103.4	1103.4	1105.3	1040.1	1026.4	1022.4
55°	1038.2	1040.1	1054.0	1058.0	1054.0	1040.1	1038.2	1038.2	979.0	965.1	957.3
57.5°	971.1	971.1	981.0	981.0	981.0	971.1	971.1	967.1	909.9	898.1	894.1
60°	894.1	898.1	906.0	904.0	906.0	898.1	894.1	890.1	840.8	833.0	819.1
62.5°	813.1	817.1	819.1	815.1	819.1	817.1	813.1	801.4	771.7	765.8	748.1
65°	728.3	732.3	734.3	730.3	734.3	732.3	728.3	722.4	700.7	690.8	675.0
67.5°	641.4	639.5	637.5	645.4	637.5	639.5	641.4	633.6	619.7	611.8	590.1
70°	552.7	552.7	550.7	554.6	550.7	552.7	552.7	546.7	538.8	533.0	513.1
72.5°	457.9	456.0	463.8	457.9	463.8	456.0	457.9	456.0	452.0	446.1	426.3
75°	365.1	369.1	365.1	371.1	365.1	369.1	365.1	367.1	365.1	361.1	347.4
77.5°	278.3	282.3	278.3	278.3	278.3	282.3	278.3	280.3	280.3	280.3	268.4
80°	197.4	195.4	195.4	193.4	195.4	195.4	197.4	197.4	199.3	195.4	191.4
82.5°	126.3	124.3	124.3	128.3	124.3	124.3	126.3	128.3	124.3	124.3	124.3
85°	69.1	71.0	67.1	67.1	67.1	71.0	69.1	65.1	69.1	69.1	67.1
87.5°	25.7	23.7	23.7	23.7	23.7	23.7	25.7	27.6	27.6	27.6	29.6
90°	11.7	11.7	11.7	11.7	11.7	11.7	11.7	15.5	20.8	23.4	20.1
92.5°	58.5	56.2	46.8	37.5	46.8	56.2	58.5	82.9	115.4	131.8	115.7
95°	198.6	191.5	163.3	135.2	163.3	191.5	198.6	260.9	343.8	385.3	325.4
97.5°	458.5	445.0	391.4	337.8	391.4	445.0	458.5	497.8	550.3	576.5	476.7
100°	643.9	628.0	564.0	500.1	564.0	628.0	643.9	641.0	637.1	635.2	524.5
102.5°	802.2	788.5	733.8	679.0	733.8	788.5	802.2	752.1	685.2	651.9	539.5
105°	986.9	979.6	950.2	920.7	950.2	979.6	986.9	874.6	724.9	650.0	541.2
107.5°	1083.0	1084.7	1091.8	1099.0	1091.8	1084.7	1083.0	926.3	717.4	613.0	517.1
110°	1107.7	1115.3	1145.9	1176.6	1145.9	1115.3	1107.7	932.6	699.0	582.3	495.8

TEST NUMBER: P934487

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1091.9	1103.7	1150.8	1197.8	1150.8	1103.7	1091.9	912.7	673.8	554.3	477.2
115°	1038.6	1055.0	1120.2	1185.5	1120.2	1055.0	1038.6	866.0	635.8	520.7	455.8
117.5°	965.0	983.2	1055.6	1128.0	1055.6	983.2	965.0	809.2	601.5	497.6	442.4
120°	915.4	933.1	1003.4	1073.8	1003.4	933.1	915.4	773.1	583.3	488.3	437.8
122.5°	865.9	883.3	952.7	1022.0	952.7	883.3	865.9	737.7	566.7	481.3	435.5
125°	800.3	816.2	880.2	944.1	880.2	816.2	800.3	691.4	546.2	473.6	433.6
127.5°	747.6	761.0	815.0	869.0	815.0	761.0	747.6	654.1	529.5	467.1	432.5
130°	714.4	726.9	776.7	826.5	776.7	726.9	714.4	631.2	520.1	464.6	433.1
132.5°	686.0	697.2	741.8	786.4	741.8	697.2	686.0	611.5	512.2	462.5	433.6
135°	646.0	655.7	694.1	732.6	694.1	655.7	646.0	583.7	500.5	458.9	433.2
137.5°	616.4	624.3	655.9	687.3	655.9	624.3	616.4	563.6	493.3	458.2	435.8
140°	592.7	600.1	629.5	659.0	629.5	600.1	592.7	547.2	486.4	456.1	436.2
142.5°	576.1	582.5	607.8	633.1	607.8	582.5	576.1	536.0	482.8	456.1	437.8
145°	551.2	556.0	575.2	594.3	575.2	556.0	551.2	518.4	474.8	453.0	437.8
147.5°	530.3	534.3	550.1	565.9	550.1	534.3	530.3	504.5	470.1	453.0	440.8
150°	518.2	521.4	534.4	547.2	534.4	521.4	518.2	496.5	467.5	453.0	442.4
152.5°	508.7	511.0	520.8	530.6	520.8	511.0	508.7	490.1	465.3	453.0	443.4
155°	497.3	498.9	505.4	511.7	505.4	498.9	497.3	482.6	462.8	453.0	445.7
157.5°	487.4	488.5	493.1	497.6	493.1	488.5	487.4	476.0	460.6	453.0	448.0
160°	482.6	483.2	485.7	488.3	485.7	483.2	482.6	472.7	459.6	453.0	449.0
162.5°	477.9	478.5	481.0	483.5	481.0	478.5	477.9	469.6	458.6	453.0	450.1
165°	470.8	471.5	474.1	476.7	474.1	471.5	470.8	464.8	457.0	453.0	451.7
167.5°	467.7	468.0	469.1	470.2	469.1	468.0	467.7	463.8	458.7	456.1	455.0
170°	467.7	467.7	467.7	467.7	467.7	467.7	467.7	463.8	458.7	456.1	456.0
172.5°	465.2	465.0	464.0	463.1	464.0	465.0	465.2	462.1	458.1	456.1	456.1
175°	461.8	461.8	461.8	461.8	461.8	461.8	461.8	460.0	457.4	456.1	456.7
177.5°	461.2	460.9	460.0	458.9	460.0	460.9	461.2	459.8	457.7	456.7	457.2
180°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9

TEST NUMBER: P934487

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2086.2	2086.2	2086.2	2086.2	2086.2
2.5°	2060.6	2070.5	2076.4	2084.2	2104.0
5°	1981.6	2019.2	2030.9	2060.6	2096.1
7.5°	1807.9	1922.4	1954.1	2025.1	2080.3
10°	1640.2	1754.7	1809.9	1977.7	2060.6
12.5°	1555.4	1622.4	1659.9	1894.8	2032.9
15°	1502.1	1549.4	1577.1	1784.2	2001.4
17.5°	1460.5	1494.1	1513.8	1675.7	1957.9
20°	1434.9	1450.7	1468.5	1596.8	1908.6
22.5°	1417.1	1407.2	1421.1	1541.5	1841.5
25°	1405.4	1367.8	1383.6	1498.1	1762.5
27.5°	1415.2	1332.2	1338.2	1458.6	1679.7
30°	1417.1	1288.8	1290.8	1417.1	1586.9
32.5°	1403.4	1243.5	1245.4	1365.8	1482.2
35°	1369.8	1190.1	1188.2	1306.7	1340.2
37.5°	1324.4	1133.0	1133.0	1241.5	1184.2
40°	1269.1	1075.7	1081.7	1156.7	1046.1
42.5°	1202.0	1014.5	1022.4	1044.1	943.4
45°	1129.0	955.3	961.2	882.3	864.5
47.5°	1048.1	894.1	896.1	732.3	838.8
50°	951.4	831.0	823.1	627.7	836.8
52.5°	866.5	761.8	738.1	568.4	759.8
55°	783.6	688.8	637.5	523.0	704.7
57.5°	710.5	594.1	544.7	469.7	692.8
60°	643.4	501.3	463.8	412.5	635.5
62.5°	588.1	432.3	424.4	373.0	576.3
65°	529.0	384.9	382.9	339.4	489.5
67.5°	471.7	353.3	351.3	307.9	373.0
70°	410.6	319.7	315.8	274.4	276.3
72.5°	347.4	282.3	278.3	246.7	229.0
75°	284.3	238.8	236.8	215.1	185.6
77.5°	223.0	189.4	193.4	173.7	136.2
80°	159.9	138.1	142.1	124.3	102.6
82.5°	106.6	90.8	94.7	79.0	69.1
85°	59.3	51.3	53.3	41.4	31.6
87.5°	27.6	23.7	23.7	15.8	9.9
90°	13.5	8.7	8.1	5.6	3.1
92.5°	83.6	59.5	54.2	33.3	12.4
95°	205.6	115.7	106.2	67.8	29.6
97.5°	277.0	127.2	118.7	85.0	51.1
100°	302.9	136.8	129.1	98.4	67.7
102.5°	314.8	146.3	139.1	110.6	81.9
105°	323.6	160.5	154.4	130.2	106.0
107.5°	325.3	181.4	175.7	153.2	130.6
110°	322.8	193.0	187.9	167.5	147.2

TEST NUMBER: P934487

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	322.9	207.3	202.4	183.0	163.5
115°	325.9	228.5	224.0	206.1	188.1
117.5°	332.0	249.1	245.0	228.8	212.4
120°	336.8	261.2	257.3	241.9	226.6
122.5°	343.9	275.3	271.4	256.0	240.5
125°	353.5	293.4	289.9	275.8	261.7
127.5°	363.0	311.1	307.5	293.2	279.0
130°	370.0	322.7	318.9	303.6	288.2
132.5°	375.7	332.3	328.5	313.1	297.8
135°	381.9	343.3	339.8	325.9	311.9
137.5°	391.0	357.5	354.0	340.2	326.4
140°	396.7	367.0	363.8	351.2	338.4
142.5°	401.4	374.1	371.1	359.4	347.6
145°	407.7	385.0	382.4	372.1	361.8
147.5°	416.6	398.5	396.0	386.0	376.0
150°	421.4	405.6	403.3	394.3	385.3
152.5°	424.4	410.2	408.5	401.6	394.7
155°	431.2	420.3	419.0	414.0	409.0
157.5°	437.9	430.5	429.3	424.3	419.4
160°	441.0	435.1	434.1	430.3	426.5
162.5°	444.3	440.0	439.3	436.4	433.6
165°	449.1	447.1	446.4	443.8	441.2
167.5°	452.8	451.1	450.8	449.5	448.3
170°	455.9	455.8	455.5	454.2	453.0
172.5°	456.1	456.1	456.0	455.8	455.5
175°	458.0	458.9	458.9	458.9	458.9
177.5°	458.2	458.9	458.9	458.9	458.9
180°	458.9	458.9	458.9	458.9	458.9

TEST NUMBER: P934487

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-6-2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.93	15.94	15.75	16.78	17.83	17.76	18.76	18.58	19.61	20.66
	3H	15.42	16.32	16.25	17.18	18.25	19.11	20.02	19.95	20.87	21.94
	4H	15.62	16.47	16.47	17.33	18.42	19.56	20.42	20.41	21.28	22.36
	6H	15.74	16.53	16.61	17.40	18.50	19.85	20.64	20.72	21.51	22.61
	8H	15.75	16.50	16.62	17.39	18.49	19.93	20.68	20.80	21.57	22.67
	12H	15.73	16.44	16.60	17.32	18.45	19.97	20.69	20.85	21.57	22.69
4H	2H	15.98	16.84	16.84	17.70	18.78	18.18	19.04	19.04	19.90	20.98
	3H	17.02	17.73	17.89	18.63	19.73	19.70	20.41	20.57	21.31	22.41
	4H	17.30	17.95	18.18	18.84	19.97	20.23	20.88	21.11	21.77	22.90
	6H	17.44	18.00	18.33	18.91	20.04	20.61	21.17	21.50	22.08	23.21
	8H	17.45	17.97	18.34	18.88	20.02	20.72	21.24	21.61	22.15	23.29
	12H	17.42	17.89	18.34	18.82	19.97	20.78	21.25	21.70	22.18	23.33
8H	4H	17.77	18.29	18.67	19.20	20.34	20.37	20.89	21.27	21.80	22.95
	6H	18.04	18.47	18.96	19.42	20.56	20.81	21.24	21.74	22.20	23.34
	8H	18.08	18.46	19.02	19.41	20.57	20.96	21.35	21.90	22.29	23.45
	12H	18.07	18.41	19.01	19.34	20.56	21.07	21.41	22.01	22.34	23.55
12H	4H	17.78	18.25	18.70	19.18	20.33	20.34	20.81	21.26	21.74	22.89
	6H	18.10	18.48	19.03	19.42	20.59	20.81	21.19	21.74	22.14	23.30
	8H	18.17	18.51	19.11	19.44	20.66	20.98	21.32	21.92	22.25	23.46

END OF REPORT