

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936492

Luminaire Tested: SQ4-FB-025U-100D-B2750-1D-UNV-W2A-W-8-2700K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936492
REPORT IS A COMBINATION OF REPORTS P933455 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-100D-B2750-1D-UNV-W2A-W-8-2700K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8260.9 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 77.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936492

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-W2A-W-8-2700K

Luminous Intensity Polar Plot



TEST NUMBER: P936492

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-W2A-W-8-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81
1	103	98	94	90	98	94	90	86	85	82	79	77	75	73	70	68	66
2	93	85	78	72	88	81	75	69	73	68	64	67	63	59	61	57	55
3	84	74	65	59	80	70	63	57	64	58	53	58	53	49	53	49	45
4	77	65	56	49	73	62	54	47	56	50	44	51	46	41	47	42	38
5	70	57	48	42	66	55	46	40	50	43	38	46	40	35	41	37	33
6	64	51	42	36	61	49	41	35	45	38	32	41	35	30	37	32	28
7	59	46	37	31	56	44	36	30	40	33	28	37	31	27	34	29	25
8	55	42	33	27	52	40	32	26	37	30	25	34	28	23	31	26	22
9	51	38	30	24	49	36	29	23	33	27	22	31	25	21	28	23	20
10	48	35	27	21	45	33	26	21	31	24	20	28	23	19	26	21	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3798	3798	3798
5°	3710	4389	5105
10°	3365	6399	8463
15°	2860	8360	10220
20°	2329	9687	10415
25°	1943	10138	10203
30°	1638	10202	10184
35°	1449	10032	10447
40°	1262	9812	10720
45°	1143	9651	10762
50°	1048	9506	10583
55°	1004	9293	10115
60°	1027	8885	9374
65°	1069	8264	8356
70°	1140	7208	7058
75°	1262	5876	5509
80°	1380	4075	3713
85°	1225	2163	1900

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 10762 cd/sqm

TEST NUMBER: P936492

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-W2A-W-8-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.9	1.3
10°-20°	469.3	5.7
20°-30°	820.9	9.9
30°-40°	1056.7	12.8
40°-50°	1180.3	14.3
50°-60°	1130.4	13.7
60°-70°	895.9	10.8
70°-80°	526.8	6.4
80°-90°	147.5	1.8
90°-100°	144.9	1.8
100°-110°	381.0	4.6
110°-120°	395.0	4.8
120°-130°	316.9	3.8
130°-140°	248.6	3.0
140°-150°	190.8	2.3
150°-160°	137.4	1.7
160°-170°	84.1	1.0
170°-180°	28.4	0.3
0°-30°	1396.1	16.9
0°-40°	2452.8	29.7
0°-60°	4763.5	57.7
0°-90°	6333.7	76.7
90°-120°	920.9	11.1
90°-150°	1677.2	20.3
90°-180°	1927.0	23.3
0°-180°	8260.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	819	819	819	819	819	
5°	798	856	963	1090	1129	74
15°	598	1103	1858	2253	2324	166
25°	382	1250	2214	2311	2314	176
35°	258	1195	2085	2203	2290	161
45°	176	953	1842	2111	2206	136
55°	126	605	1563	1816	1866	115
65°	100	321	1161	1306	1324	99
75°	74	197	637	700	703	77
85°	26	61	158	174	176	28
90°	2	6	15	8	8	3
95°	19	75	250	129	88	21
105°	69	104	421	639	596	73
115°	122	148	337	673	768	120
125°	170	190	307	518	612	151
135°	202	222	297	419	475	156
145°	234	249	294	357	385	147
155°	265	272	294	322	332	122
165°	286	290	294	305	309	81
175°	297	297	296	299	299	28
180°	297	297	297	297	297	

TEST NUMBER: P936492

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	818.6	818.6	818.6	818.6	818.6	818.6	818.6	818.6	818.6	818.6	818.6
2.5°	818.6	818.6	823.9	826.5	831.8	834.3	839.6	844.9	860.7	863.3	868.6
5°	797.5	808.1	842.3	855.5	892.3	942.3	963.3	997.6	1068.6	1089.7	1102.9
7.5°	765.9	789.6	873.9	894.9	987.0	1118.6	1173.9	1247.6	1360.8	1416.1	1460.8
10°	715.9	765.9	916.0	966.0	1116.0	1316.0	1418.7	1521.4	1692.4	1768.8	1797.7
12.5°	660.6	742.2	960.7	1029.2	1245.0	1537.1	1660.8	1774.1	1968.8	2071.5	2087.2
15°	597.5	708.1	1002.9	1102.9	1381.9	1721.4	1858.2	1997.8	2179.3	2253.1	2271.5
17.5°	542.2	681.8	1042.3	1147.6	1487.1	1887.2	2026.8	2142.5	2289.9	2339.9	2353.1
20°	473.8	639.6	1068.6	1205.5	1597.7	2008.3	2142.5	2232.0	2332.0	2363.6	2368.9
22.5°	423.8	594.8	1084.4	1226.6	1671.4	2082.0	2195.2	2266.2	2334.7	2345.2	2347.9
25°	381.7	544.8	1081.8	1250.3	1734.5	2126.8	2213.6	2266.2	2305.7	2311.0	2311.0
27.5°	342.1	489.5	1071.3	1255.6	1781.9	2137.3	2205.7	2242.6	2261.0	2271.5	2271.5
30°	308.0	436.9	1044.9	1245.0	1803.0	2126.8	2182.0	2200.5	2218.9	2234.6	2242.6
32.5°	281.7	386.9	1005.5	1223.9	1805.6	2100.5	2139.9	2150.5	2176.8	2213.6	2226.8
35°	258.0	336.9	960.7	1195.0	1789.8	2058.3	2084.6	2095.2	2147.8	2203.1	2221.5
37.5°	234.3	300.1	902.8	1145.0	1766.1	2008.3	2026.8	2045.2	2126.8	2192.5	2213.6
40°	210.6	268.5	834.3	1089.7	1729.3	1947.8	1963.5	1992.5	2100.5	2176.8	2197.8
42.5°	192.1	242.1	760.6	1031.8	1681.9	1879.4	1903.1	1945.1	2068.8	2150.5	2174.2
45°	176.4	215.8	681.8	952.8	1621.4	1808.2	1842.5	1900.4	2031.9	2110.9	2132.0
47.5°	160.6	197.4	600.1	871.2	1555.6	1737.2	1781.9	1847.8	1981.9	2058.3	2076.8
50°	147.4	179.0	518.5	784.4	1484.5	1660.8	1713.5	1781.9	1918.8	1989.9	2013.5
52.5°	136.9	163.1	442.2	697.5	1402.9	1581.8	1642.4	1713.5	1842.5	1910.9	1926.7
55°	126.3	150.0	376.4	605.4	1318.7	1497.7	1563.4	1631.9	1758.2	1816.1	1826.7
57.5°	121.1	139.5	321.1	518.5	1229.2	1402.9	1476.6	1539.8	1658.2	1703.0	1713.5
60°	113.1	131.6	279.0	444.8	1131.9	1313.4	1376.6	1439.7	1539.8	1576.7	1584.5
62.5°	105.3	126.3	247.4	373.8	1031.8	1208.1	1271.3	1329.3	1413.4	1439.7	1450.3
65°	100.0	121.1	223.7	321.1	929.2	1097.6	1160.7	1210.7	1279.2	1305.6	1310.8
67.5°	94.7	115.8	205.3	276.4	826.5	987.0	1034.4	1081.8	1134.4	1160.7	1163.4
70°	86.9	110.6	189.5	244.8	721.2	860.7	900.2	950.2	992.3	1005.5	1013.3
72.5°	81.6	102.7	179.0	221.1	613.2	739.6	776.5	805.5	842.3	855.5	855.5
75°	73.7	92.1	168.4	197.4	502.8	605.4	636.9	665.9	694.9	700.2	692.2
77.5°	65.8	81.6	144.7	165.8	392.2	479.1	505.4	521.1	544.8	550.1	552.8
80°	55.3	71.1	113.1	129.0	284.3	352.7	371.1	384.3	405.4	405.4	410.7
82.5°	42.1	55.3	81.6	92.1	192.1	242.1	258.0	265.8	279.0	279.0	279.0
85°	26.3	34.3	52.7	60.6	115.8	147.4	158.0	160.6	171.1	173.7	173.7
87.5°	13.1	18.4	34.3	36.9	60.6	76.3	76.3	81.6	81.6	79.0	76.3
90°	2.0	3.6	5.2	5.6	8.8	13.0	15.1	13.4	10.1	7.6	7.6
92.5°	8.0	21.5	35.2	38.5	54.2	75.0	85.4	74.8	53.8	37.9	36.5
95°	19.1	43.9	68.8	75.0	133.2	210.8	249.6	222.7	169.0	128.7	124.1
97.5°	33.2	55.1	76.9	82.4	179.4	308.8	373.5	356.6	322.6	297.1	288.4
100°	43.9	63.7	83.6	88.5	196.2	339.7	411.5	412.8	415.3	417.2	406.9
102.5°	53.1	71.6	90.1	94.7	204.0	349.6	422.4	444.0	487.2	519.7	510.8
105°	68.6	84.4	100.1	104.0	209.8	350.7	421.2	469.7	566.7	639.4	634.7
107.5°	84.6	99.2	113.8	117.5	210.8	335.1	397.2	464.8	600.2	701.7	702.9
110°	95.4	108.6	121.8	125.1	209.2	321.2	377.3	452.9	604.2	717.6	722.6

TEST NUMBER: P936492

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	106.0	118.5	131.1	134.3	209.3	309.2	359.2	436.5	591.3	707.5	715.1
115°	121.9	133.5	145.1	148.0	211.2	295.3	337.3	411.9	561.1	673.0	683.6
117.5°	137.6	148.2	158.8	161.5	215.1	286.6	322.4	389.7	524.3	625.3	637.0
120°	146.8	156.8	166.7	169.2	218.3	283.8	316.4	377.9	500.9	593.1	604.5
122.5°	155.8	165.8	175.9	178.4	222.9	282.2	311.8	367.2	478.0	561.0	572.3
125°	169.6	178.8	187.8	190.1	229.1	281.0	306.9	353.9	448.0	518.5	528.9
127.5°	180.8	189.9	199.2	201.5	235.3	280.2	302.7	343.1	423.9	484.5	493.2
130°	186.8	196.7	206.6	209.1	239.7	280.7	301.1	337.0	409.0	462.8	470.9
132.5°	192.9	202.9	212.7	215.2	243.4	281.0	299.7	331.9	396.2	444.5	451.8
135°	202.1	211.2	220.2	222.5	247.4	280.7	297.3	324.3	378.2	418.6	424.8
137.5°	211.5	220.4	229.4	231.7	253.4	282.4	296.9	319.7	365.2	399.4	404.5
140°	219.2	227.5	235.8	237.8	257.1	282.7	295.5	315.2	354.6	384.1	388.8
142.5°	225.3	232.9	240.5	242.4	260.2	283.8	295.5	312.8	347.4	373.3	377.4
145°	234.5	241.1	247.7	249.4	264.1	283.8	293.5	307.7	336.0	357.2	360.3
147.5°	243.6	250.1	256.6	258.2	269.9	285.7	293.5	304.7	326.9	343.5	346.1
150°	249.6	255.5	261.3	262.7	273.0	286.6	293.5	302.9	321.7	335.8	337.8
152.5°	255.8	260.2	264.6	265.7	275.0	287.3	293.5	301.5	317.5	329.6	331.2
155°	264.9	268.2	271.5	272.3	279.4	288.8	293.5	299.9	312.6	322.2	323.2
157.5°	271.7	274.9	278.1	278.9	283.8	290.2	293.5	298.5	308.4	315.8	316.5
160°	276.3	278.8	281.3	281.9	285.8	290.9	293.5	297.8	306.3	312.6	313.0
162.5°	280.9	282.8	284.6	285.1	287.8	291.6	293.5	297.1	304.3	309.7	310.1
165°	286.0	287.6	289.3	289.7	291.0	292.7	293.5	296.1	301.2	305.1	305.5
167.5°	290.5	291.3	292.1	292.3	293.4	294.8	295.5	297.2	300.6	303.1	303.3
170°	293.5	294.3	295.1	295.3	295.4	295.5	295.5	297.2	300.6	303.1	303.1
172.5°	295.1	295.3	295.5	295.5	295.5	295.5	295.5	296.8	299.5	301.5	301.3
175°	297.3	297.3	297.3	297.3	296.7	295.9	295.5	296.3	298.0	299.3	299.3
177.5°	297.3	297.3	297.3	297.3	296.8	296.2	295.9	296.6	297.9	298.9	298.7
180°	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3	297.3

TEST NUMBER: P936492

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	818.6	818.6
2.5°	873.9	868.6
5°	1123.9	1129.2
7.5°	1513.4	1510.8
10°	1881.9	1905.6
12.5°	2150.5	2155.7
15°	2313.6	2324.2
17.5°	2376.8	2379.4
20°	2379.4	2374.2
22.5°	2350.5	2345.2
25°	2316.3	2313.6
27.5°	2284.6	2287.3
30°	2271.5	2279.4
32.5°	2271.5	2284.6
35°	2276.8	2289.9
37.5°	2274.2	2289.9
40°	2263.6	2282.0
42.5°	2234.6	2247.8
45°	2189.9	2205.7
47.5°	2132.0	2142.5
50°	2058.3	2068.8
52.5°	1966.2	1968.8
55°	1855.6	1866.2
57.5°	1737.2	1739.8
60°	1605.6	1613.5
62.5°	1466.1	1466.1
65°	1318.7	1324.0
67.5°	1166.0	1179.2
70°	1010.7	1013.3
72.5°	858.1	858.1
75°	700.2	702.8
77.5°	550.1	550.1
80°	408.0	410.7
82.5°	281.7	286.9
85°	176.4	176.4
87.5°	81.6	73.7
90°	7.6	7.6
92.5°	30.4	24.3
95°	105.9	87.5
97.5°	253.6	218.8
100°	365.4	324.0
102.5°	475.4	439.9
105°	615.6	596.5
107.5°	707.5	712.0
110°	742.4	762.3

TEST NUMBER: P936492

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	745.6	776.1
115°	725.9	768.1
117.5°	684.0	730.9
120°	650.1	695.7
122.5°	617.2	662.1
125°	570.3	611.7
127.5°	528.1	563.0
130°	503.2	535.4
132.5°	480.7	509.6
135°	449.7	474.6
137.5°	424.9	445.3
140°	407.9	427.0
142.5°	393.8	410.2
145°	372.7	385.1
147.5°	356.4	366.7
150°	346.2	354.6
152.5°	337.4	343.7
155°	327.4	331.6
157.5°	319.5	322.4
160°	314.7	316.4
162.5°	311.6	313.2
165°	307.2	308.9
167.5°	304.0	304.7
170°	303.1	303.1
172.5°	300.7	300.1
175°	299.3	299.3
177.5°	298.0	297.3
180°	297.3	297.3

TEST NUMBER: P936492

CATALOG NUMBER: SQ4-FB-025U-100D-B2750-1D-UNV-W2A-W-8-2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.77	9.01	8.45	9.71	10.54	20.95	22.18	21.63	22.89	23.72
	3H	8.50	9.62	9.20	10.33	11.19	22.82	23.93	23.51	24.65	25.51
	4H	8.82	9.87	9.53	10.60	11.47	23.48	24.53	24.19	25.26	26.13
	6H	9.09	10.06	9.82	10.80	11.69	23.93	24.90	24.66	25.64	26.53
	8H	9.17	10.10	9.90	10.86	11.75	24.06	24.99	24.80	25.75	26.64
	12H	9.20	10.09	9.94	10.84	11.76	24.14	25.03	24.89	25.78	26.70
4H	2H	15.03	16.08	15.75	16.81	17.68	21.27	22.32	21.98	23.05	23.92
	3H	16.63	17.52	17.36	18.28	19.17	23.35	24.23	24.08	24.99	25.89
	4H	16.74	17.55	17.49	18.31	19.23	24.13	24.94	24.88	25.70	26.62
	6H	16.78	17.48	17.54	18.27	19.19	24.69	25.39	25.46	26.18	27.11
	8H	16.76	17.42	17.53	18.20	19.14	24.86	25.52	25.63	26.31	27.25
	12H	16.74	17.33	17.53	18.14	19.08	24.98	25.57	25.77	26.38	27.32
8H	4H	18.22	18.88	18.99	19.66	20.60	24.22	24.88	24.99	25.66	26.60
	6H	18.48	19.03	19.28	19.85	20.79	24.87	25.42	25.67	26.24	27.18
	8H	18.50	18.99	19.31	19.81	20.77	25.10	25.58	25.90	26.41	27.36
	12H	18.49	18.92	19.30	19.73	20.75	25.26	25.69	26.07	26.50	27.52
12H	4H	18.38	18.97	19.17	19.78	20.73	24.19	24.79	24.98	25.59	26.54
	6H	18.74	19.23	19.55	20.06	21.01	24.86	25.35	25.67	26.17	27.13
	8H	18.83	19.26	19.64	20.08	21.09	25.11	25.54	25.92	26.35	27.37

END OF REPORT