

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938592

Luminaire Tested: SQ4-FB-150U-125D-B2750-1D-UNV-W2A-W-8-2700K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938592
REPORT IS A COMBINATION OF REPORTS P933648 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-125D-B2750-1D-UNV-W2A-W-8-2700K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20118.2 lumens
Efficiency: N/A
Efficacy: 120.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 166.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938592

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-W2A-W-8-2700K

Luminous Intensity Polar Plot



TEST NUMBER: P938592

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-W2A-W-8-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	95	91	87	83	86	83	79	76	68	65	63	54	52	51	41	40	39
2	86	79	72	67	78	72	66	62	59	55	51	47	44	42	36	34	32
3	78	69	61	55	71	63	56	51	51	47	43	41	37	35	31	29	27
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	27	25	23
5	65	53	45	39	59	49	42	36	40	35	30	32	28	25	24	22	19
6	60	48	39	34	54	44	36	31	36	30	26	29	25	21	22	19	17
7	55	43	35	29	50	39	32	27	32	27	23	26	22	19	20	17	15
8	51	39	31	25	46	35	28	24	29	24	20	23	19	16	18	15	13
9	47	35	27	22	43	32	25	21	27	21	18	21	17	15	17	14	11
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4864	4864	4864
5°	4752	5622	6538
10°	4310	8195	10840
15°	3663	10706	13088
20°	2982	12408	13339
25°	2488	12984	13068
30°	2098	13066	13044
35°	1855	12849	13380
40°	1617	12567	13730
45°	1464	12360	13783
50°	1342	12175	13555
55°	1286	11903	12954
60°	1316	11379	12005
65°	1370	10585	10702
70°	1460	9231	9041
75°	1617	7527	7055
80°	1766	5220	4754
85°	1570	2770	2434

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 13783 cd/sqm

TEST NUMBER: P938592

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-W2A-W-8-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.6	0.7
10°-20°	601.1	3.0
20°-30°	1051.3	5.2
30°-40°	1353.4	6.7
40°-50°	1511.7	7.5
50°-60°	1447.8	7.2
60°-70°	1147.4	5.7
70°-80°	674.7	3.4
80°-90°	194.5	1.0
90°-100°	902.4	4.5
100°-110°	2372.4	11.8
110°-120°	2459.9	12.2
120°-130°	1973.1	9.8
130°-140°	1548.2	7.7
140°-150°	1188.3	5.9
150°-160°	855.8	4.3
160°-170°	523.6	2.6
170°-180°	176.9	0.9
0°-30°	1788.0	8.9
0°-40°	3141.4	15.6
0°-60°	6100.9	30.3
0°-90°	8117.5	40.3
90°-120°	5734.7	28.5
90°-150°	10444.4	51.9
90°-180°	12001.0	59.7
0°-180°	20118.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1048	1048	1048	1048	1048	
5°	1021	1096	1234	1396	1446	94
15°	765	1412	2380	2886	2977	213
25°	489	1601	2835	2960	2963	225
35°	330	1530	2670	2822	2933	206
45°	226	1220	2360	2704	2825	175
55°	162	775	2002	2326	2390	147
65°	128	411	1487	1672	1696	127
75°	94	253	816	897	900	99
85°	34	78	202	222	226	36
90°	12	35	94	47	47	13
95°	119	467	1554	801	545	132
105°	427	647	2623	3982	3715	453
115°	759	922	2101	4191	4783	750
125°	1056	1184	1911	3229	3809	938
135°	1258	1385	1851	2607	2956	974
145°	1460	1553	1828	2224	2398	915
155°	1650	1696	1828	2006	2065	758
165°	1780	1804	1828	1900	1923	502
175°	1851	1851	1840	1864	1864	176
180°	1851	1851	1851	1851	1851	

TEST NUMBER: P938592

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4
2.5°	1048.4	1048.4	1055.2	1058.5	1065.2	1068.6	1075.4	1082.2	1102.4	1105.8	1112.4
5°	1021.4	1034.9	1078.8	1095.6	1142.8	1206.9	1233.8	1277.7	1368.6	1395.6	1412.4
7.5°	981.0	1011.3	1119.2	1146.2	1264.1	1432.7	1503.5	1597.9	1742.8	1813.6	1871.0
10°	916.9	981.0	1173.1	1237.1	1429.4	1685.5	1817.0	1948.5	2167.6	2265.4	2302.5
12.5°	846.1	950.7	1230.5	1318.1	1594.5	1968.7	2127.2	2272.1	2521.6	2653.0	2673.3
15°	765.2	906.9	1284.3	1412.4	1769.8	2204.6	2379.9	2558.6	2791.3	2885.6	2909.2
17.5°	694.4	873.1	1334.9	1469.8	1904.7	2417.1	2595.7	2744.1	2932.8	2996.9	3013.7
20°	606.8	819.2	1368.6	1543.9	2046.3	2572.2	2744.1	2858.6	2986.8	3027.2	3033.9
22.5°	542.7	761.8	1388.9	1570.9	2140.6	2666.5	2811.5	2902.4	2990.1	3003.6	3007.0
25°	488.8	697.8	1385.5	1601.3	2221.6	2723.9	2835.1	2902.4	2953.0	2959.8	2959.8
27.5°	438.2	627.0	1372.0	1608.0	2282.2	2737.3	2825.0	2872.2	2895.8	2909.2	2909.2
30°	394.4	559.6	1338.3	1594.5	2309.2	2723.9	2794.6	2818.2	2841.8	2862.0	2872.2
32.5°	360.8	495.5	1287.7	1567.5	2312.5	2690.1	2740.7	2754.1	2787.9	2835.1	2851.9
35°	330.4	431.5	1230.5	1530.5	2292.3	2636.2	2669.9	2683.3	2750.8	2821.6	2845.2
37.5°	300.0	384.3	1156.3	1466.4	2262.0	2572.2	2595.7	2619.3	2723.9	2808.1	2835.1
40°	269.7	343.8	1068.6	1395.6	2214.8	2494.6	2514.8	2551.9	2690.1	2787.9	2814.8
42.5°	246.1	310.2	974.3	1321.5	2154.1	2406.9	2437.3	2491.2	2649.7	2754.1	2784.5
45°	225.9	276.4	873.1	1220.3	2076.6	2315.9	2359.7	2433.9	2602.4	2703.6	2730.5
47.5°	205.7	252.8	768.6	1115.8	1992.3	2224.9	2282.2	2366.5	2538.4	2636.2	2659.8
50°	188.7	229.3	664.1	1004.6	1901.3	2127.2	2194.6	2282.2	2457.5	2548.6	2578.8
52.5°	175.3	209.0	566.3	893.3	1796.8	2026.0	2103.6	2194.6	2359.7	2447.4	2467.6
55°	161.8	192.1	482.1	775.4	1688.9	1918.1	2002.5	2090.1	2251.9	2326.1	2339.5
57.5°	155.1	178.7	411.2	664.1	1574.3	1796.8	1891.2	1972.1	2123.8	2181.0	2194.6
60°	144.9	168.5	357.4	569.7	1449.6	1682.1	1763.0	1844.0	1972.1	2019.3	2029.4
62.5°	134.9	161.8	316.9	478.7	1321.5	1547.3	1628.3	1702.4	1810.2	1844.0	1857.4
65°	128.1	155.1	286.5	411.2	1190.0	1405.8	1486.6	1550.7	1638.3	1672.1	1678.8
67.5°	121.3	148.3	262.9	354.0	1058.5	1264.1	1324.8	1385.5	1453.0	1486.6	1490.0
70°	111.3	141.6	242.7	313.5	923.7	1102.4	1152.9	1216.9	1270.9	1287.7	1297.9
72.5°	104.5	131.5	229.3	283.2	785.4	947.3	994.5	1031.6	1078.8	1095.6	1095.6
75°	94.4	118.0	215.7	252.8	643.9	775.4	815.8	852.9	889.9	896.7	886.6
77.5°	84.3	104.5	185.5	212.3	502.3	613.5	647.2	667.5	697.8	704.6	708.0
80°	70.8	91.0	144.9	165.1	364.0	451.7	475.3	492.2	519.1	519.1	525.9
82.5°	54.0	70.8	104.5	118.0	246.1	310.2	330.4	340.4	357.4	357.4	357.4
85°	33.7	43.8	67.4	77.5	148.3	188.7	202.3	205.7	219.1	222.5	222.5
87.5°	16.8	23.6	43.8	47.2	77.5	97.8	97.8	104.5	104.5	101.1	97.8
90°	12.4	22.4	32.3	34.8	54.7	81.2	94.4	84.0	62.9	47.2	47.2
92.5°	49.7	134.2	218.7	239.8	337.1	466.9	531.8	466.0	334.7	236.1	226.7
95°	119.3	273.9	428.5	467.1	829.5	1312.6	1554.3	1386.9	1052.4	801.4	772.9
97.5°	206.3	342.6	479.1	513.1	1117.4	1923.1	2325.9	2220.1	2008.6	1850.0	1795.9
100°	273.3	397.0	520.7	551.7	1222.2	2116.1	2563.1	2570.9	2586.3	2597.9	2533.4
102.5°	330.5	445.9	561.2	590.1	1270.2	2176.9	2630.2	2765.0	3034.4	3236.5	3181.3
105°	427.4	525.1	622.9	647.3	1305.8	2183.7	2622.8	2924.9	3528.9	3982.0	3952.3
107.5°	526.8	617.9	709.0	731.8	1312.4	2086.6	2473.7	2895.0	3737.7	4369.7	4376.8
110°	593.9	676.2	758.5	779.0	1302.5	2000.5	2349.5	2820.5	3762.5	4469.1	4499.9

TEST NUMBER: P938592

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	659.8	738.1	816.5	836.1	1302.9	1925.2	2236.3	2718.4	3682.5	4405.6	4453.1
115°	759.2	831.5	903.8	921.9	1314.9	1838.9	2101.0	2565.3	3494.1	4190.7	4256.5
117.5°	857.3	923.0	988.7	1005.2	1339.3	1784.9	2007.7	2426.9	3265.1	3893.8	3966.8
120°	914.4	976.3	1038.1	1053.6	1359.2	1766.7	1970.5	2353.4	3119.4	3693.8	3764.7
122.5°	970.3	1032.8	1095.1	1110.7	1387.8	1757.2	1941.9	2286.7	2976.4	3493.7	3563.7
125°	1056.1	1112.9	1169.8	1184.0	1426.3	1749.3	1910.8	2203.7	2789.6	3229.0	3293.5
127.5°	1125.7	1183.0	1240.5	1254.9	1464.8	1744.8	1884.7	2136.2	2639.3	3016.6	3071.0
130°	1162.9	1224.8	1286.6	1302.1	1493.0	1747.5	1874.8	2098.7	2546.6	2882.4	2932.7
132.5°	1201.5	1263.3	1325.2	1340.6	1515.8	1749.4	1866.1	2066.5	2467.4	2768.1	2813.1
135°	1258.5	1314.9	1371.3	1385.3	1540.6	1747.7	1851.2	2019.1	2354.8	2606.6	2645.4
137.5°	1317.0	1372.8	1428.5	1442.4	1577.9	1758.4	1848.8	1990.7	2274.5	2487.3	2519.1
140°	1365.4	1416.8	1468.1	1481.0	1600.7	1760.2	1840.0	1962.6	2207.8	2391.7	2421.4
142.5°	1402.7	1450.2	1497.7	1509.5	1619.7	1766.6	1840.0	1947.7	2163.0	2324.6	2350.1
145°	1459.8	1501.3	1542.7	1553.1	1644.6	1766.6	1827.6	1915.6	2091.8	2224.0	2243.3
147.5°	1517.0	1557.3	1597.7	1607.7	1681.0	1778.8	1827.6	1896.9	2035.4	2139.4	2155.4
150°	1554.3	1590.7	1627.2	1636.2	1700.0	1785.0	1827.6	1886.1	2003.2	2091.0	2104.0
152.5°	1592.8	1620.4	1648.1	1655.0	1712.5	1789.2	1827.6	1877.6	1977.5	2052.5	2062.2
155°	1650.0	1670.4	1690.8	1695.9	1739.8	1798.3	1827.6	1867.3	1946.9	2006.5	2013.0
157.5°	1692.2	1712.1	1731.9	1736.9	1767.1	1807.4	1827.6	1858.5	1920.4	1966.8	1971.4
160°	1720.8	1736.2	1751.7	1755.5	1779.6	1811.5	1827.6	1854.1	1907.1	1946.9	1949.5
162.5°	1749.4	1760.9	1772.6	1775.5	1792.8	1816.0	1827.6	1850.0	1894.7	1928.3	1930.7
165°	1780.4	1790.8	1801.4	1804.0	1811.8	1822.3	1827.6	1843.6	1875.7	1899.7	1902.3
167.5°	1808.9	1813.9	1818.9	1820.2	1826.8	1835.6	1840.0	1850.5	1871.5	1887.2	1888.3
170°	1827.6	1832.5	1837.5	1838.8	1839.2	1839.7	1840.0	1850.5	1871.5	1887.2	1887.2
172.5°	1837.5	1838.6	1839.7	1840.0	1840.0	1840.0	1840.0	1848.3	1864.8	1877.3	1876.3
175°	1851.2	1851.2	1851.2	1851.2	1847.5	1842.5	1840.0	1845.3	1855.7	1863.6	1863.6
177.5°	1851.2	1851.2	1851.2	1851.2	1848.3	1844.4	1842.5	1846.7	1855.0	1861.1	1860.0
180°	1851.2	1851.2	1851.2	1851.2	1851.2	1851.2	1851.2	1851.2	1851.2	1851.2	1851.2

TEST NUMBER: P938592

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1048.4	1048.4
2.5°	1119.2	1112.4
5°	1439.4	1446.2
7.5°	1938.3	1935.0
10°	2410.3	2440.7
12.5°	2754.1	2760.9
15°	2963.2	2976.6
17.5°	3044.1	3047.5
20°	3047.5	3040.7
22.5°	3010.4	3003.6
25°	2966.6	2963.2
27.5°	2926.0	2929.4
30°	2909.2	2919.4
32.5°	2909.2	2926.0
35°	2916.0	2932.8
37.5°	2912.6	2932.8
40°	2899.2	2922.8
42.5°	2862.0	2878.9
45°	2804.7	2825.0
47.5°	2730.5	2744.1
50°	2636.2	2649.7
52.5°	2518.2	2521.6
55°	2376.6	2390.1
57.5°	2224.9	2228.3
60°	2056.3	2066.5
62.5°	1877.7	1877.7
65°	1688.9	1695.7
67.5°	1493.4	1510.2
70°	1294.5	1297.9
72.5°	1099.0	1099.0
75°	896.7	900.1
77.5°	704.6	704.6
80°	522.5	525.9
82.5°	360.8	367.4
85°	225.9	225.9
87.5°	104.5	94.4
90°	47.2	47.2
92.5°	189.1	151.6
95°	659.2	545.4
97.5°	1579.4	1362.9
100°	2275.6	2017.7
102.5°	2960.4	2739.6
105°	3833.6	3714.9
107.5°	4405.5	4434.2
110°	4623.6	4747.3



TEST NUMBER: P938592

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	4643.1	4833.0
115°	4519.9	4783.3
117.5°	4258.9	4551.0
120°	4048.5	4332.3
122.5°	3843.7	4123.6
125°	3551.4	3809.3
127.5°	3288.6	3506.1
130°	3133.7	3334.7
132.5°	2993.1	3173.2
135°	2800.6	2955.7
137.5°	2646.1	2773.1
140°	2540.1	2658.8
142.5°	2452.3	2554.4
145°	2320.6	2397.9
147.5°	2219.5	2283.5
150°	2155.9	2207.8
152.5°	2101.5	2140.7
155°	2039.0	2064.9
157.5°	1989.5	2007.7
160°	1960.0	1970.5
162.5°	1940.6	1950.6
165°	1912.8	1923.3
167.5°	1892.8	1897.2
170°	1887.2	1887.2
172.5°	1872.5	1868.6
175°	1863.6	1863.6
177.5°	1855.5	1851.2
180°	1851.2	1851.2

TEST NUMBER: P938592

CATALOG NUMBER: SQ4-FB-150U-125D-B2750-1D-UNV-W2A-W-8-2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.55	6.36	6.58	7.40	8.80	18.73	19.54	19.76	20.58	21.98
	3H	6.25	6.98	7.29	8.03	9.45	20.56	21.29	21.60	22.34	23.76
	4H	6.55	7.24	7.60	8.29	9.71	21.21	21.90	22.26	22.95	24.37
	6H	6.79	7.43	7.85	8.49	9.92	21.63	22.27	22.70	23.33	24.77
	8H	6.86	7.47	7.93	8.54	9.97	21.75	22.36	22.82	23.43	24.87
	12H	6.88	7.45	7.95	8.52	9.98	21.82	22.40	22.89	23.46	24.92
4H	2H	12.76	13.45	13.82	14.50	15.93	19.00	19.69	20.05	20.74	22.16
	3H	14.32	14.90	15.39	15.98	17.42	21.04	21.61	22.10	22.69	24.13
	4H	14.41	14.94	15.49	16.01	17.47	21.80	22.33	22.87	23.40	24.86
	6H	14.42	14.88	15.50	15.97	17.43	22.34	22.79	23.42	23.89	25.34
	8H	14.40	14.82	15.48	15.91	17.38	22.50	22.93	23.58	24.01	25.48
	12H	14.35	14.74	15.45	15.84	17.31	22.59	22.98	23.69	24.08	25.55
8H	4H	15.85	16.28	16.94	17.37	18.84	21.86	22.28	22.94	23.37	24.84
	6H	16.09	16.45	17.20	17.57	19.04	22.48	22.84	23.59	23.97	25.43
	8H	16.11	16.42	17.22	17.53	19.02	22.70	23.01	23.81	24.12	25.61
	12H	16.08	16.35	17.19	17.46	18.98	22.85	23.12	23.96	24.22	25.75
12H	4H	15.99	16.38	17.09	17.48	18.96	21.81	22.19	22.91	23.29	24.77
	6H	16.35	16.66	17.46	17.77	19.26	22.47	22.78	23.58	23.89	25.37
	8H	16.42	16.69	17.53	17.80	19.32	22.69	22.97	23.81	24.07	25.60

END OF REPORT