

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P933878

Luminaire Tested: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P933878
REPORT IS A COMBINATION OF REPORTS P933673 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8300.1 lumens
Efficiency: N/A
Efficacy: 125.8 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 66
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P933878

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P933878

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66		
1	101	97	93	89	95	91	88	85	81	78	76	71	69	68	62	61	60	55		
2	92	85	78	73	87	80	74	70	71	67	63	63	59	56	55	52	50	46		
3	84	75	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39		
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	43	40	37	34		
5	71	59	50	44	66	56	48	43	50	44	39	44	39	35	39	35	32	29		
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28	26		
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25	23		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18		
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6486	6486	6486	6486
5°	6537	6547	6537	5148
10°	6495	6449	6495	4611
15°	6427	6309	6427	5269
20°	6295	6144	6295	5280
25°	6022	5903	6022	5167
30°	5669	5702	5669	4922
35°	5057	5449	5057	4652
40°	4216	5150	4216	4448
45°	3769	4801	3769	4214
50°	4008	4384	4008	3978
55°	3774	3935	3774	3842
60°	3895	3342	3895	3519
65°	3538	2763	3538	3088
70°	2456	2202	2456	2589
75°	2162	1628	2162	1949
80°	1754	1076	1754	1172
85°	1027	570	1027	484

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 5774 cd/sqm

TEST NUMBER: P933878

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.3	2.3
10°-20°	537.4	6.5
20°-30°	830.7	10.0
30°-40°	991.7	11.9
40°-50°	997.6	12.0
50°-60°	868.0	10.5
60°-70°	615.4	7.4
70°-80°	325.6	3.9
80°-90°	82.8	1.0
90°-100°	215.2	2.6
100°-110°	565.7	6.8
110°-120°	586.6	7.1
120°-130°	470.5	5.7
130°-140°	369.2	4.4
140°-150°	283.4	3.4
150°-160°	204.1	2.5
160°-170°	124.9	1.5
170°-180°	42.2	0.5
0°-30°	1557.4	18.8
0°-40°	2549.2	30.7
0°-60°	4414.7	53.2
0°-90°	5438.5	65.5
90°-120°	1367.5	16.5
90°-150°	2490.5	30.0
90°-180°	2862.0	34.5
0°-180°	8300.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2097	2097	2097	2097	2097	
5°	2107	2172	2107	1708	2107	200
15°	2012	2152	2012	1797	2012	566
25°	1772	2008	1772	1758	1772	813
35°	1347	1791	1347	1530	1347	833
45°	869	1476	869	1295	869	696
55°	708	1089	708	1063	708	651
65°	492	657	492	734	492	470
75°	186	312	186	373	186	196
85°	32	79	32	67	32	43
90°	3	11	3	11	3	4
95°	28	130	28	130	28	32
105°	102	886	102	886	102	108
115°	181	1141	181	1141	181	179
125°	252	908	252	908	252	224
135°	300	705	300	705	300	232
145°	348	572	348	572	348	218
155°	393	492	393	492	393	181
165°	425	459	425	459	425	120
175°	441	444	441	444	441	42
180°	441	441	441	441	441	

TEST NUMBER: P933878

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8
2.5°	2114.7	2114.7	2126.6	2130.5	2130.5	2124.6	2118.7	2124.6	2142.5	2148.4	2146.4
5°	2106.8	2122.7	2144.5	2148.4	2152.4	2150.5	2146.4	2150.5	2170.3	2174.2	2176.2
7.5°	2090.9	2120.7	2148.4	2154.4	2160.3	2154.4	2152.4	2156.4	2176.2	2180.1	2180.1
10°	2071.1	2112.7	2144.5	2148.4	2154.4	2148.4	2148.4	2156.4	2176.2	2180.1	2182.2
12.5°	2043.3	2100.9	2130.5	2134.6	2142.5	2140.5	2138.5	2146.4	2166.3	2170.3	2170.3
15°	2011.5	2079.0	2106.8	2110.7	2124.6	2120.7	2120.7	2128.6	2150.5	2156.4	2154.4
17.5°	1968.0	2051.3	2083.0	2088.9	2098.9	2096.8	2098.9	2106.8	2126.6	2130.5	2132.6
20°	1918.4	2013.5	2051.3	2057.2	2067.1	2067.1	2067.1	2077.0	2096.8	2104.8	2104.8
22.5°	1850.9	1973.9	2013.5	2017.6	2029.4	2029.4	2033.4	2047.2	2065.1	2067.1	2067.1
25°	1771.5	1930.2	1963.9	1975.8	1987.8	1993.7	1999.7	2007.6	2013.5	2011.5	2013.5
27.5°	1688.2	1874.7	1918.4	1926.2	1942.1	1948.0	1956.0	1958.0	1960.0	1965.9	1961.9
30°	1595.0	1797.3	1862.8	1870.7	1896.5	1900.5	1892.5	1896.5	1906.4	1910.4	1914.3
32.5°	1489.8	1682.2	1805.3	1823.1	1846.9	1835.0	1833.0	1839.0	1854.9	1854.9	1858.8
35°	1347.0	1593.0	1751.7	1767.6	1785.4	1771.5	1779.4	1781.4	1791.4	1797.3	1795.3
37.5°	1190.3	1515.6	1696.1	1708.0	1722.0	1704.1	1715.9	1722.0	1729.8	1725.9	1725.9
40°	1051.4	1394.6	1630.6	1638.6	1650.5	1636.7	1648.5	1652.5	1656.5	1652.5	1650.5
42.5°	948.2	1261.7	1561.2	1571.2	1563.2	1573.2	1577.1	1585.1	1579.1	1571.2	1571.2
45°	868.9	1226.0	1485.9	1497.7	1485.9	1501.8	1507.7	1507.7	1489.8	1485.9	1483.8
47.5°	843.1	1154.6	1410.5	1410.5	1404.6	1424.4	1434.2	1420.4	1402.6	1396.6	1396.6
50°	841.2	1075.2	1307.3	1299.4	1327.2	1350.9	1341.1	1327.2	1313.3	1291.5	1291.5
52.5°	763.8	978.0	1174.4	1204.2	1247.8	1261.7	1245.8	1231.9	1208.1	1198.2	1190.3
55°	708.2	876.8	1053.3	1112.9	1158.6	1176.4	1146.6	1132.7	1097.0	1091.1	1087.2
57.5°	696.3	730.0	942.3	1017.7	1073.3	1071.3	1053.3	1027.6	997.8	991.9	989.9
60°	638.8	527.7	823.3	912.5	970.0	964.1	948.2	924.5	896.7	892.7	888.8
62.5°	579.3	382.9	688.3	789.6	870.8	868.9	855.1	819.3	799.4	789.6	781.6
65°	492.0	321.3	490.0	656.7	773.7	777.7	747.9	722.1	700.3	688.3	686.4
67.5°	375.0	261.9	331.3	547.5	680.4	676.5	638.8	626.9	599.1	593.2	581.2
70°	277.8	174.6	230.1	444.4	589.2	579.3	549.5	535.6	509.9	496.0	488.0
72.5°	230.1	140.8	168.6	345.2	496.0	484.0	458.3	442.4	420.5	408.7	400.7
75°	186.5	148.8	129.0	255.9	402.7	394.8	370.9	355.1	337.2	321.3	323.3
77.5°	136.9	138.8	103.1	188.4	319.4	307.5	293.6	273.8	265.8	250.0	250.0
80°	103.1	109.2	77.4	129.0	230.1	230.1	218.2	204.3	190.4	182.5	182.5
82.5°	69.4	69.4	57.5	81.3	156.7	150.8	142.9	138.8	130.9	127.0	127.0
85°	31.7	39.6	35.7	49.6	85.3	89.2	89.2	85.3	83.3	79.4	81.3
87.5°	10.0	17.8	21.8	27.8	43.7	45.7	47.6	47.6	47.6	49.6	49.6
90°	3.0	5.3	7.7	8.3	13.0	19.3	22.5	20.0	15.0	11.2	11.2
92.5°	11.8	31.9	52.2	57.2	80.4	111.3	126.8	111.1	79.8	56.3	54.0
95°	28.4	65.3	102.1	111.4	197.8	313.1	370.6	330.7	250.9	191.1	184.3
97.5°	49.2	81.7	114.3	122.4	266.4	458.6	554.6	529.4	479.0	441.1	428.2
100°	65.2	94.7	124.1	131.5	291.5	504.6	611.2	613.1	616.7	619.5	604.1
102.5°	78.8	106.3	133.8	140.7	302.9	519.1	627.2	659.3	723.5	771.7	758.5
105°	102.0	125.2	148.5	154.3	311.4	520.7	625.4	697.4	841.5	949.5	942.4
107.5°	125.6	147.3	169.1	174.5	313.0	497.5	589.8	690.3	891.2	1042.0	1043.7
110°	141.6	161.2	180.8	185.8	310.6	477.0	560.2	672.6	897.2	1065.7	1073.1

TEST NUMBER: P933878

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	157.4	176.0	194.7	199.4	310.7	459.1	533.3	648.3	878.1	1050.6	1061.9
115°	181.0	198.3	215.5	219.9	313.5	438.5	501.0	611.7	833.2	999.3	1015.0
117.5°	204.4	220.1	235.8	239.7	319.4	425.7	478.8	578.8	778.6	928.5	946.0
120°	218.0	232.8	247.6	251.2	324.1	421.2	469.8	561.1	743.8	880.8	897.8
122.5°	231.4	246.3	261.1	264.8	330.9	419.0	463.0	545.3	709.7	833.1	849.7
125°	251.8	265.4	279.0	282.4	340.2	417.2	455.6	525.4	665.2	770.0	785.3
127.5°	268.4	282.1	295.8	299.3	349.3	416.1	449.4	509.4	629.4	719.3	732.3
130°	277.3	292.1	306.8	310.5	356.0	416.7	447.1	500.5	607.3	687.3	699.4
132.5°	286.5	301.2	316.0	319.7	361.5	417.2	445.0	492.8	588.4	660.1	670.9
135°	300.1	313.5	327.0	330.3	367.4	416.8	441.4	481.5	561.5	621.6	630.8
137.5°	314.0	327.4	340.6	343.9	376.3	419.3	440.8	474.7	542.3	593.1	600.7
140°	325.6	337.8	350.1	353.2	381.7	419.7	438.8	468.0	526.4	570.3	577.4
142.5°	334.5	345.8	357.1	360.0	386.2	421.2	438.8	464.4	515.8	554.3	560.4
145°	348.2	358.0	367.9	370.3	392.1	421.2	435.8	456.8	498.8	530.3	534.9
147.5°	361.8	371.3	381.0	383.4	400.8	424.2	435.8	452.4	485.4	510.2	514.0
150°	370.6	379.3	388.0	390.2	405.3	425.7	435.8	449.8	477.7	498.6	501.7
152.5°	379.8	386.4	392.9	394.6	408.3	426.6	435.8	447.7	471.6	489.5	491.8
155°	393.4	398.2	403.2	404.4	414.8	428.8	435.8	445.3	464.3	478.5	480.1
157.5°	403.5	408.2	413.0	414.2	421.4	431.0	435.8	443.2	457.9	468.9	470.0
160°	410.4	414.0	417.8	418.7	424.4	432.0	435.8	442.1	454.7	464.2	464.8
162.5°	417.2	419.9	422.7	423.4	427.5	433.1	435.8	441.1	451.8	459.8	460.4
165°	424.6	427.0	429.6	430.2	432.1	434.5	435.8	439.7	447.2	453.0	453.6
167.5°	431.4	432.6	433.7	434.0	435.6	437.7	438.8	441.2	446.3	450.0	450.3
170°	435.8	437.0	438.2	438.5	438.6	438.7	438.8	441.2	446.3	450.0	450.0
172.5°	438.2	438.5	438.7	438.8	438.8	438.8	438.8	440.7	444.7	447.6	447.4
175°	441.4	441.4	441.4	441.4	440.5	439.4	438.8	440.1	442.5	444.4	444.4
177.5°	441.4	441.4	441.4	441.4	440.7	439.9	439.4	440.3	442.3	443.8	443.5
180°	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4

TEST NUMBER: P933878

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8
2.5°	2150.5	2144.5	2150.5	2146.4	2148.4	2142.5	2124.6	2118.7	2124.6	2130.5	2130.5
5°	2176.2	2172.3	2176.2	2176.2	2174.2	2170.3	2150.5	2146.4	2150.5	2152.4	2148.4
7.5°	2184.2	2178.2	2184.2	2180.1	2180.1	2176.2	2156.4	2152.4	2154.4	2160.3	2154.4
10°	2184.2	2178.2	2184.2	2182.2	2180.1	2176.2	2156.4	2148.4	2148.4	2154.4	2148.4
12.5°	2174.2	2170.3	2174.2	2170.3	2170.3	2166.3	2146.4	2138.5	2140.5	2142.5	2134.6
15°	2158.4	2152.4	2158.4	2154.4	2156.4	2150.5	2128.6	2120.7	2120.7	2124.6	2110.7
17.5°	2134.6	2126.6	2134.6	2132.6	2130.5	2126.6	2106.8	2098.9	2096.8	2098.9	2088.9
20°	2106.8	2100.9	2106.8	2104.8	2104.8	2096.8	2077.0	2067.1	2067.1	2067.1	2057.2
22.5°	2063.1	2057.2	2063.1	2067.1	2067.1	2065.1	2047.2	2033.4	2029.4	2029.4	2017.6
25°	2013.5	2007.6	2013.5	2013.5	2011.5	2013.5	2007.6	1999.7	1993.7	1987.8	1975.8
27.5°	1965.9	1961.9	1965.9	1961.9	1965.9	1960.0	1958.0	1956.0	1948.0	1942.1	1926.2
30°	1918.4	1914.3	1918.4	1914.3	1910.4	1906.4	1896.5	1892.5	1900.5	1896.5	1870.7
32.5°	1858.8	1854.9	1858.8	1858.8	1854.9	1854.9	1839.0	1833.0	1835.0	1846.9	1823.1
35°	1797.3	1791.4	1797.3	1795.3	1797.3	1791.4	1781.4	1779.4	1771.5	1785.4	1767.6
37.5°	1725.9	1720.0	1725.9	1725.9	1725.9	1729.8	1722.0	1715.9	1704.1	1722.0	1708.0
40°	1652.5	1644.5	1652.5	1650.5	1652.5	1656.5	1652.5	1648.5	1636.7	1650.5	1638.6
42.5°	1569.2	1567.1	1569.2	1571.2	1571.2	1579.1	1585.1	1577.1	1573.2	1563.2	1571.2
45°	1479.9	1475.9	1479.9	1483.8	1485.9	1489.8	1507.7	1507.7	1501.8	1485.9	1497.7
47.5°	1384.6	1374.8	1384.6	1396.6	1396.6	1402.6	1420.4	1434.2	1424.4	1404.6	1410.5
50°	1283.5	1285.4	1283.5	1291.5	1291.5	1313.3	1327.2	1341.1	1350.9	1327.2	1299.4
52.5°	1184.3	1182.3	1184.3	1190.3	1198.2	1208.1	1231.9	1245.8	1261.7	1247.8	1204.2
55°	1085.1	1089.1	1085.1	1087.2	1091.1	1097.0	1132.7	1146.6	1176.4	1158.6	1112.9
57.5°	985.9	980.0	985.9	989.9	991.9	997.8	1027.6	1053.3	1071.3	1073.3	1017.7
60°	870.8	862.9	870.8	888.8	892.7	896.7	924.5	948.2	964.1	970.0	912.5
62.5°	769.7	755.9	769.7	781.6	789.6	799.4	819.3	855.1	868.9	870.8	789.6
65°	662.6	656.7	662.6	686.4	688.3	700.3	722.1	747.9	777.7	773.7	656.7
67.5°	565.4	565.4	565.4	581.2	593.2	599.1	626.9	638.8	676.5	680.4	547.5
70°	476.1	474.2	476.1	488.0	496.0	509.9	535.6	549.5	579.3	589.2	444.4
72.5°	390.9	388.8	390.9	400.7	408.7	420.5	442.4	458.3	484.0	496.0	345.2
75°	315.4	311.5	315.4	323.3	321.3	337.2	355.1	370.9	394.8	402.7	255.9
77.5°	242.1	242.1	242.1	250.0	250.0	265.8	273.8	293.6	307.5	319.4	188.4
80°	180.5	178.6	180.5	182.5	182.5	190.4	204.3	218.2	230.1	230.1	129.0
82.5°	127.0	123.0	127.0	127.0	127.0	130.9	138.8	142.9	150.8	156.7	81.3
85°	79.4	79.4	79.4	81.3	79.4	83.3	85.3	89.2	89.2	85.3	49.6
87.5°	51.6	49.6	51.6	49.6	49.6	47.6	47.6	47.6	45.7	43.7	27.8
90°	11.2	11.2	11.2	11.2	11.2	15.0	20.0	22.5	19.3	13.0	8.3
92.5°	45.2	36.2	45.2	54.0	56.3	79.8	111.1	126.8	111.3	80.4	57.2
95°	157.2	130.1	157.2	184.3	191.1	250.9	330.7	370.6	313.1	197.8	111.4
97.5°	376.7	325.0	376.7	428.2	441.1	479.0	529.4	554.6	458.6	266.4	122.4
100°	542.7	481.2	542.7	604.1	619.5	616.7	613.1	611.2	504.6	291.5	131.5
102.5°	705.9	653.2	705.9	758.5	771.7	723.5	659.3	627.2	519.1	302.9	140.7
105°	914.1	885.8	914.1	942.4	949.5	841.5	697.4	625.4	520.7	311.4	154.3
107.5°	1050.6	1057.4	1050.6	1043.7	1042.0	891.2	690.3	589.8	497.5	313.0	174.5
110°	1102.5	1132.0	1102.5	1073.1	1065.7	897.2	672.6	560.2	477.0	310.6	185.8

TEST NUMBER: P933878

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1107.2	1152.4	1107.2	1061.9	1050.6	878.1	648.3	533.3	459.1	310.7	199.4
115°	1077.8	1140.6	1077.8	1015.0	999.3	833.2	611.7	501.0	438.5	313.5	219.9
117.5°	1015.6	1085.2	1015.6	946.0	928.5	778.6	578.8	478.8	425.7	319.4	239.7
120°	965.4	1033.0	965.4	897.8	880.8	743.8	561.1	469.8	421.2	324.1	251.2
122.5°	916.6	983.3	916.6	849.7	833.1	709.7	545.3	463.0	419.0	330.9	264.8
125°	846.8	908.3	846.8	785.3	770.0	665.2	525.4	455.6	417.2	340.2	282.4
127.5°	784.2	836.0	784.2	732.3	719.3	629.4	509.4	449.4	416.1	349.3	299.3
130°	747.3	795.2	747.3	699.4	687.3	607.3	500.5	447.1	416.7	356.0	310.5
132.5°	713.8	756.7	713.8	670.9	660.1	588.4	492.8	445.0	417.2	361.5	319.7
135°	667.8	704.8	667.8	630.8	621.6	561.5	481.5	441.4	416.8	367.4	330.3
137.5°	630.9	661.3	630.9	600.7	593.1	542.3	474.7	440.8	419.3	376.3	343.9
140°	605.7	634.0	605.7	577.4	570.3	526.4	468.0	438.8	419.7	381.7	353.2
142.5°	584.8	609.2	584.8	560.4	554.3	515.8	464.4	438.8	421.2	386.2	360.0
145°	553.3	571.8	553.3	534.9	530.3	498.8	456.8	435.8	421.2	392.1	370.3
147.5°	529.3	544.6	529.3	514.0	510.2	485.4	452.4	435.8	424.2	400.8	383.4
150°	514.1	526.4	514.1	501.7	498.6	477.7	449.8	435.8	425.7	405.3	390.2
152.5°	501.1	510.5	501.1	491.8	489.5	471.6	447.7	435.8	426.6	408.3	394.6
155°	486.2	492.4	486.2	480.1	478.5	464.3	445.3	435.8	428.8	414.8	404.4
157.5°	474.5	478.8	474.5	470.0	468.9	457.9	443.2	435.8	431.0	421.4	414.2
160°	467.4	469.8	467.4	464.8	464.2	454.7	442.1	435.8	432.0	424.4	418.7
162.5°	462.7	465.1	462.7	460.4	459.8	451.8	441.1	435.8	433.1	427.5	423.4
165°	456.1	458.6	456.1	453.6	453.0	447.2	439.7	435.8	434.5	432.1	430.2
167.5°	451.3	452.4	451.3	450.3	450.0	446.3	441.2	438.8	437.7	435.6	434.0
170°	450.0	450.0	450.0	450.0	450.0	446.3	441.2	438.8	438.7	438.6	438.5
172.5°	446.5	445.6	446.5	447.4	447.6	444.7	440.7	438.8	438.8	438.8	438.8
175°	444.4	444.4	444.4	444.4	444.4	442.5	440.1	438.8	439.4	440.5	441.4
177.5°	442.5	441.4	442.5	443.5	443.8	442.3	440.3	439.4	439.9	440.7	441.4
180°	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4

TEST NUMBER: P933878

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8
2.5°	2126.6	2114.7	2114.7	2094.9	2087.0	2081.0	2071.1	2041.3	2033.4	2025.4	2037.4
5°	2144.5	2122.7	2106.8	2071.1	2041.3	2029.4	1991.7	1920.3	1872.7	1837.0	1817.2
7.5°	2148.4	2120.7	2090.9	2035.4	1963.9	1932.2	1817.2	1686.3	1650.5	1618.8	1598.9
10°	2144.5	2112.7	2071.1	1987.8	1819.2	1763.6	1648.5	1563.2	1541.4	1535.5	1541.4
12.5°	2130.5	2100.9	2043.3	1904.5	1668.4	1630.6	1563.2	1513.6	1509.7	1519.6	1573.2
15°	2106.8	2079.0	2011.5	1793.3	1585.1	1557.3	1509.7	1491.8	1513.6	1583.0	1743.7
17.5°	2083.0	2051.3	1968.0	1684.3	1521.6	1501.8	1468.0	1503.7	1626.7	1720.0	1773.5
20°	2051.3	2013.5	1918.4	1604.9	1475.9	1458.1	1442.2	1602.9	1696.1	1729.8	1759.6
22.5°	2013.5	1973.9	1850.9	1549.3	1428.3	1414.4	1424.4	1658.5	1696.1	1720.0	1745.7
25°	1963.9	1930.2	1771.5	1505.7	1390.7	1374.8	1412.4	1652.5	1674.3	1680.2	1731.8
27.5°	1918.4	1874.7	1688.2	1466.0	1345.0	1339.1	1422.4	1626.7	1642.6	1648.5	1704.1
30°	1862.8	1797.3	1595.0	1424.4	1297.4	1295.4	1424.4	1595.0	1591.0	1606.9	1662.4
32.5°	1805.3	1682.2	1489.8	1372.8	1251.7	1249.8	1410.5	1547.3	1543.4	1565.2	1606.9
35°	1751.7	1593.0	1347.0	1313.3	1194.2	1196.2	1376.8	1491.8	1493.8	1513.6	1539.4
37.5°	1696.1	1515.6	1190.3	1247.8	1138.7	1138.7	1331.1	1440.3	1436.3	1442.2	1477.9
40°	1630.6	1394.6	1051.4	1162.5	1087.2	1081.1	1275.6	1384.6	1370.8	1368.9	1418.4
42.5°	1561.2	1261.7	948.2	1049.4	1027.6	1019.6	1208.1	1317.2	1291.5	1297.4	1360.9
45°	1485.9	1226.0	868.9	886.7	966.1	960.2	1134.7	1239.9	1222.0	1237.9	1303.4
47.5°	1410.5	1154.6	843.1	736.0	900.6	898.6	1053.3	1164.5	1154.6	1170.5	1239.9
50°	1307.3	1075.2	841.2	630.8	827.3	835.1	956.2	1091.1	1091.1	1105.0	1178.4
52.5°	1174.4	978.0	763.8	571.3	742.0	765.7	870.8	1027.6	1031.6	1045.5	1110.9
55°	1053.3	876.8	708.2	525.7	640.8	692.4	787.5	962.1	970.0	983.9	1043.5
57.5°	942.3	730.0	696.3	472.1	547.5	597.1	714.2	898.6	902.6	914.5	972.1
60°	823.3	527.7	638.8	414.6	466.2	503.8	646.7	823.3	837.1	845.1	894.7
62.5°	688.3	382.9	579.3	375.0	426.5	434.4	591.2	751.8	769.7	775.7	805.5
65°	490.0	321.3	492.0	341.3	384.8	386.8	531.7	678.5	694.3	704.2	726.1
67.5°	331.3	261.9	375.0	309.5	353.1	355.1	474.2	593.2	615.0	623.0	636.8
70°	230.1	174.6	277.8	275.8	317.4	321.3	412.6	515.8	535.6	541.6	549.5
72.5°	168.6	140.8	230.1	248.0	279.7	283.7	349.1	428.5	448.3	454.3	458.3
75°	129.0	148.8	186.5	216.2	238.0	240.0	285.6	349.1	363.0	367.0	369.0
77.5°	103.1	138.8	136.9	174.6	194.4	190.4	224.2	269.8	281.7	281.7	281.7
80°	77.4	109.2	103.1	125.0	142.9	138.8	160.7	192.5	196.4	200.4	198.4
82.5°	57.5	69.4	69.4	79.4	95.2	91.3	107.1	125.0	125.0	125.0	129.0
85°	35.7	39.6	31.7	41.7	53.5	51.6	59.6	67.4	69.4	69.4	65.5
87.5°	21.8	17.8	10.0	15.9	23.8	23.8	27.8	29.8	27.8	27.8	27.8
90°	7.7	5.3	3.0	5.3	7.7	8.3	13.0	19.3	22.5	20.0	15.0
92.5°	52.2	31.9	11.8	31.9	52.2	57.2	80.4	111.3	126.8	111.1	79.8
95°	102.1	65.3	28.4	65.3	102.1	111.4	197.8	313.1	370.6	330.7	250.9
97.5°	114.3	81.7	49.2	81.7	114.3	122.4	266.4	458.6	554.6	529.4	479.0
100°	124.1	94.7	65.2	94.7	124.1	131.5	291.5	504.6	611.2	613.1	616.7
102.5°	133.8	106.3	78.8	106.3	133.8	140.7	302.9	519.1	627.2	659.3	723.5
105°	148.5	125.2	102.0	125.2	148.5	154.3	311.4	520.7	625.4	697.4	841.5
107.5°	169.1	147.3	125.6	147.3	169.1	174.5	313.0	497.5	589.8	690.3	891.2
110°	180.8	161.2	141.6	161.2	180.8	185.8	310.6	477.0	560.2	672.6	897.2

TEST NUMBER: P933878

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	194.7	176.0	157.4	176.0	194.7	199.4	310.7	459.1	533.3	648.3	878.1
115°	215.5	198.3	181.0	198.3	215.5	219.9	313.5	438.5	501.0	611.7	833.2
117.5°	235.8	220.1	204.4	220.1	235.8	239.7	319.4	425.7	478.8	578.8	778.6
120°	247.6	232.8	218.0	232.8	247.6	251.2	324.1	421.2	469.8	561.1	743.8
122.5°	261.1	246.3	231.4	246.3	261.1	264.8	330.9	419.0	463.0	545.3	709.7
125°	279.0	265.4	251.8	265.4	279.0	282.4	340.2	417.2	455.6	525.4	665.2
127.5°	295.8	282.1	268.4	282.1	295.8	299.3	349.3	416.1	449.4	509.4	629.4
130°	306.8	292.1	277.3	292.1	306.8	310.5	356.0	416.7	447.1	500.5	607.3
132.5°	316.0	301.2	286.5	301.2	316.0	319.7	361.5	417.2	445.0	492.8	588.4
135°	327.0	313.5	300.1	313.5	327.0	330.3	367.4	416.8	441.4	481.5	561.5
137.5°	340.6	327.4	314.0	327.4	340.6	343.9	376.3	419.3	440.8	474.7	542.3
140°	350.1	337.8	325.6	337.8	350.1	353.2	381.7	419.7	438.8	468.0	526.4
142.5°	357.1	345.8	334.5	345.8	357.1	360.0	386.2	421.2	438.8	464.4	515.8
145°	367.9	358.0	348.2	358.0	367.9	370.3	392.1	421.2	435.8	456.8	498.8
147.5°	381.0	371.3	361.8	371.3	381.0	383.4	400.8	424.2	435.8	452.4	485.4
150°	388.0	379.3	370.6	379.3	388.0	390.2	405.3	425.7	435.8	449.8	477.7
152.5°	392.9	386.4	379.8	386.4	392.9	394.6	408.3	426.6	435.8	447.7	471.6
155°	403.2	398.2	393.4	398.2	403.2	404.4	414.8	428.8	435.8	445.3	464.3
157.5°	413.0	408.2	403.5	408.2	413.0	414.2	421.4	431.0	435.8	443.2	457.9
160°	417.8	414.0	410.4	414.0	417.8	418.7	424.4	432.0	435.8	442.1	454.7
162.5°	422.7	419.9	417.2	419.9	422.7	423.4	427.5	433.1	435.8	441.1	451.8
165°	429.6	427.0	424.6	427.0	429.6	430.2	432.1	434.5	435.8	439.7	447.2
167.5°	433.7	432.6	431.4	432.6	433.7	434.0	435.6	437.7	438.8	441.2	446.3
170°	438.2	437.0	435.8	437.0	438.2	438.5	438.6	438.7	438.8	441.2	446.3
172.5°	438.7	438.5	438.2	438.5	438.7	438.8	438.8	438.8	438.8	440.7	444.7
175°	441.4	441.4	441.4	441.4	441.4	441.4	440.5	439.4	438.8	440.1	442.5
177.5°	441.4	441.4	441.4	441.4	441.4	441.4	440.7	439.9	439.4	440.3	442.3
180°	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4

TEST NUMBER: P933878

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8	2096.8
2.5°	2023.5	2017.6	2025.4	2003.7	2025.4	2017.6	2023.5	2037.4	2025.4	2033.4	2041.3
5°	1775.5	1765.5	1733.9	1708.0	1733.9	1765.5	1775.5	1817.2	1837.0	1872.7	1920.3
7.5°	1587.1	1579.1	1571.2	1555.3	1571.2	1579.1	1587.1	1598.9	1618.8	1650.5	1686.3
10°	1545.4	1547.3	1559.3	1557.3	1559.3	1547.3	1545.4	1541.4	1535.5	1541.4	1563.2
12.5°	1652.5	1670.4	1735.9	1731.8	1735.9	1670.4	1652.5	1573.2	1519.6	1509.7	1513.6
15°	1775.5	1781.4	1795.3	1797.3	1795.3	1781.4	1775.5	1743.7	1583.0	1513.6	1491.8
17.5°	1787.4	1789.4	1799.3	1799.3	1799.3	1789.4	1787.4	1773.5	1720.0	1626.7	1503.7
20°	1777.5	1781.4	1801.3	1805.3	1801.3	1781.4	1777.5	1759.6	1729.8	1696.1	1602.9
22.5°	1773.5	1781.4	1797.3	1795.3	1797.3	1781.4	1773.5	1745.7	1720.0	1696.1	1658.5
25°	1753.7	1753.7	1755.7	1757.6	1755.7	1753.7	1753.7	1731.8	1680.2	1674.3	1652.5
27.5°	1712.0	1715.9	1727.9	1725.9	1727.9	1715.9	1712.0	1704.1	1648.5	1642.6	1626.7
30°	1674.3	1670.4	1660.4	1652.5	1660.4	1670.4	1674.3	1662.4	1606.9	1591.0	1595.0
32.5°	1610.8	1600.9	1591.0	1585.1	1591.0	1600.9	1610.8	1606.9	1565.2	1543.4	1547.3
35°	1535.5	1537.5	1535.5	1529.5	1535.5	1537.5	1535.5	1539.4	1513.6	1493.8	1491.8
37.5°	1481.9	1485.9	1483.8	1475.9	1483.8	1485.9	1481.9	1477.9	1442.2	1436.3	1440.3
40°	1426.3	1428.3	1426.3	1420.4	1426.3	1428.3	1426.3	1418.4	1368.9	1370.8	1384.6
42.5°	1372.8	1370.8	1364.8	1360.9	1364.8	1370.8	1372.8	1360.9	1297.4	1291.5	1317.2
45°	1311.3	1313.3	1301.3	1295.4	1301.3	1313.3	1311.3	1303.4	1237.9	1222.0	1239.9
47.5°	1249.8	1249.8	1239.9	1233.9	1239.9	1249.8	1249.8	1239.9	1170.5	1154.6	1164.5
50°	1184.3	1182.3	1168.4	1166.4	1168.4	1182.3	1184.3	1178.4	1105.0	1091.1	1091.1
52.5°	1109.0	1109.0	1110.9	1114.9	1110.9	1109.0	1109.0	1110.9	1045.5	1031.6	1027.6
55°	1043.5	1045.5	1059.4	1063.3	1059.4	1045.5	1043.5	1043.5	983.9	970.0	962.1
57.5°	976.0	976.0	985.9	985.9	985.9	976.0	976.0	972.1	914.5	902.6	898.6
60°	898.6	902.6	910.6	908.6	910.6	902.6	898.6	894.7	845.1	837.1	823.3
62.5°	817.3	821.3	823.3	819.3	823.3	821.3	817.3	805.5	775.7	769.7	751.8
65°	732.0	736.0	737.9	734.0	737.9	736.0	732.0	726.1	704.2	694.3	678.5
67.5°	644.7	642.8	640.8	648.7	640.8	642.8	644.7	636.8	623.0	615.0	593.2
70°	555.4	555.4	553.4	557.5	553.4	555.4	555.4	549.5	541.6	535.6	515.8
72.5°	460.3	458.3	466.2	460.3	466.2	458.3	460.3	458.3	454.3	448.3	428.5
75°	367.0	370.9	367.0	372.9	367.0	370.9	367.0	369.0	367.0	363.0	349.1
77.5°	279.7	283.7	279.7	279.7	279.7	283.7	279.7	281.7	281.7	281.7	269.8
80°	198.4	196.4	196.4	194.4	196.4	196.4	198.4	198.4	200.4	196.4	192.5
82.5°	127.0	125.0	125.0	129.0	125.0	125.0	127.0	129.0	125.0	125.0	125.0
85°	69.4	71.4	67.4	67.4	67.4	71.4	69.4	65.5	69.4	69.4	67.4
87.5°	25.8	23.8	23.8	23.8	23.8	23.8	25.8	27.8	27.8	27.8	29.8
90°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	15.0	20.0	22.5	19.3
92.5°	56.3	54.0	45.2	36.2	45.2	54.0	56.3	79.8	111.1	126.8	111.3
95°	191.1	184.3	157.2	130.1	157.2	184.3	191.1	250.9	330.7	370.6	313.1
97.5°	441.1	428.2	376.7	325.0	376.7	428.2	441.1	479.0	529.4	554.6	458.6
100°	619.5	604.1	542.7	481.2	542.7	604.1	619.5	616.7	613.1	611.2	504.6
102.5°	771.7	758.5	705.9	653.2	705.9	758.5	771.7	723.5	659.3	627.2	519.1
105°	949.5	942.4	914.1	885.8	914.1	942.4	949.5	841.5	697.4	625.4	520.7
107.5°	1042.0	1043.7	1050.6	1057.4	1050.6	1043.7	1042.0	891.2	690.3	589.8	497.5
110°	1065.7	1073.1	1102.5	1132.0	1102.5	1073.1	1065.7	897.2	672.6	560.2	477.0

TEST NUMBER: P933878

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1050.6	1061.9	1107.2	1152.4	1107.2	1061.9	1050.6	878.1	648.3	533.3	459.1
115°	999.3	1015.0	1077.8	1140.6	1077.8	1015.0	999.3	833.2	611.7	501.0	438.5
117.5°	928.5	946.0	1015.6	1085.2	1015.6	946.0	928.5	778.6	578.8	478.8	425.7
120°	880.8	897.8	965.4	1033.0	965.4	897.8	880.8	743.8	561.1	469.8	421.2
122.5°	833.1	849.7	916.6	983.3	916.6	849.7	833.1	709.7	545.3	463.0	419.0
125°	770.0	785.3	846.8	908.3	846.8	785.3	770.0	665.2	525.4	455.6	417.2
127.5°	719.3	732.3	784.2	836.0	784.2	732.3	719.3	629.4	509.4	449.4	416.1
130°	687.3	699.4	747.3	795.2	747.3	699.4	687.3	607.3	500.5	447.1	416.7
132.5°	660.1	670.9	713.8	756.7	713.8	670.9	660.1	588.4	492.8	445.0	417.2
135°	621.6	630.8	667.8	704.8	667.8	630.8	621.6	561.5	481.5	441.4	416.8
137.5°	593.1	600.7	630.9	661.3	630.9	600.7	593.1	542.3	474.7	440.8	419.3
140°	570.3	577.4	605.7	634.0	605.7	577.4	570.3	526.4	468.0	438.8	419.7
142.5°	554.3	560.4	584.8	609.2	584.8	560.4	554.3	515.8	464.4	438.8	421.2
145°	530.3	534.9	553.3	571.8	553.3	534.9	530.3	498.8	456.8	435.8	421.2
147.5°	510.2	514.0	529.3	544.6	529.3	514.0	510.2	485.4	452.4	435.8	424.2
150°	498.6	501.7	514.1	526.4	514.1	501.7	498.6	477.7	449.8	435.8	425.7
152.5°	489.5	491.8	501.1	510.5	501.1	491.8	489.5	471.6	447.7	435.8	426.6
155°	478.5	480.1	486.2	492.4	486.2	480.1	478.5	464.3	445.3	435.8	428.8
157.5°	468.9	470.0	474.5	478.8	474.5	470.0	468.9	457.9	443.2	435.8	431.0
160°	464.2	464.8	467.4	469.8	467.4	464.8	464.2	454.7	442.1	435.8	432.0
162.5°	459.8	460.4	462.7	465.1	462.7	460.4	459.8	451.8	441.1	435.8	433.1
165°	453.0	453.6	456.1	458.6	456.1	453.6	453.0	447.2	439.7	435.8	434.5
167.5°	450.0	450.3	451.3	452.4	451.3	450.3	450.0	446.3	441.2	438.8	437.7
170°	450.0	450.0	450.0	450.0	450.0	450.0	450.0	446.3	441.2	438.8	438.7
172.5°	447.6	447.4	446.5	445.6	446.5	447.4	447.6	444.7	440.7	438.8	438.8
175°	444.4	444.4	444.4	444.4	444.4	444.4	444.4	442.5	440.1	438.8	439.4
177.5°	443.8	443.5	442.5	441.4	442.5	443.5	443.8	442.3	440.3	439.4	439.9
180°	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4	441.4

TEST NUMBER: P933878

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2096.8	2096.8	2096.8	2096.8	2096.8
2.5°	2071.1	2081.0	2087.0	2094.9	2114.7
5°	1991.7	2029.4	2041.3	2071.1	2106.8
7.5°	1817.2	1932.2	1963.9	2035.4	2090.9
10°	1648.5	1763.6	1819.2	1987.8	2071.1
12.5°	1563.2	1630.6	1668.4	1904.5	2043.3
15°	1509.7	1557.3	1585.1	1793.3	2011.5
17.5°	1468.0	1501.8	1521.6	1684.3	1968.0
20°	1442.2	1458.1	1475.9	1604.9	1918.4
22.5°	1424.4	1414.4	1428.3	1549.3	1850.9
25°	1412.4	1374.8	1390.7	1505.7	1771.5
27.5°	1422.4	1339.1	1345.0	1466.0	1688.2
30°	1424.4	1295.4	1297.4	1424.4	1595.0
32.5°	1410.5	1249.8	1251.7	1372.8	1489.8
35°	1376.8	1196.2	1194.2	1313.3	1347.0
37.5°	1331.1	1138.7	1138.7	1247.8	1190.3
40°	1275.6	1081.1	1087.2	1162.5	1051.4
42.5°	1208.1	1019.6	1027.6	1049.4	948.2
45°	1134.7	960.2	966.1	886.7	868.9
47.5°	1053.3	898.6	900.6	736.0	843.1
50°	956.2	835.1	827.3	630.8	841.2
52.5°	870.8	765.7	742.0	571.3	763.8
55°	787.5	692.4	640.8	525.7	708.2
57.5°	714.2	597.1	547.5	472.1	696.3
60°	646.7	503.8	466.2	414.6	638.8
62.5°	591.2	434.4	426.5	375.0	579.3
65°	531.7	386.8	384.8	341.3	492.0
67.5°	474.2	355.1	353.1	309.5	375.0
70°	412.6	321.3	317.4	275.8	277.8
72.5°	349.1	283.7	279.7	248.0	230.1
75°	285.6	240.0	238.0	216.2	186.5
77.5°	224.2	190.4	194.4	174.6	136.9
80°	160.7	138.8	142.9	125.0	103.1
82.5°	107.1	91.3	95.2	79.4	69.4
85°	59.6	51.6	53.5	41.7	31.7
87.5°	27.8	23.8	23.8	15.9	10.0
90°	13.0	8.3	7.7	5.3	3.0
92.5°	80.4	57.2	52.2	31.9	11.8
95°	197.8	111.4	102.1	65.3	28.4
97.5°	266.4	122.4	114.3	81.7	49.2
100°	291.5	131.5	124.1	94.7	65.2
102.5°	302.9	140.7	133.8	106.3	78.8
105°	311.4	154.3	148.5	125.2	102.0
107.5°	313.0	174.5	169.1	147.3	125.6
110°	310.6	185.8	180.8	161.2	141.6



TEST NUMBER: P933878

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	310.7	199.4	194.7	176.0	157.4
115°	313.5	219.9	215.5	198.3	181.0
117.5°	319.4	239.7	235.8	220.1	204.4
120°	324.1	251.2	247.6	232.8	218.0
122.5°	330.9	264.8	261.1	246.3	231.4
125°	340.2	282.4	279.0	265.4	251.8
127.5°	349.3	299.3	295.8	282.1	268.4
130°	356.0	310.5	306.8	292.1	277.3
132.5°	361.5	319.7	316.0	301.2	286.5
135°	367.4	330.3	327.0	313.5	300.1
137.5°	376.3	343.9	340.6	327.4	314.0
140°	381.7	353.2	350.1	337.8	325.6
142.5°	386.2	360.0	357.1	345.8	334.5
145°	392.1	370.3	367.9	358.0	348.2
147.5°	400.8	383.4	381.0	371.3	361.8
150°	405.3	390.2	388.0	379.3	370.6
152.5°	408.3	394.6	392.9	386.4	379.8
155°	414.8	404.4	403.2	398.2	393.4
157.5°	421.4	414.2	413.0	408.2	403.5
160°	424.4	418.7	417.8	414.0	410.4
162.5°	427.5	423.4	422.7	419.9	417.2
165°	432.1	430.2	429.6	427.0	424.6
167.5°	435.6	434.0	433.7	432.6	431.4
170°	438.6	438.5	438.2	437.0	435.8
172.5°	438.8	438.8	438.7	438.5	438.2
175°	440.5	441.4	441.4	441.4	441.4
177.5°	440.7	441.4	441.4	441.4	441.4
180°	441.4	441.4	441.4	441.4	441.4

TEST NUMBER: P933878

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.63	13.65	13.44	14.48	15.51	15.48	16.50	16.29	17.33	18.37
	3H	13.12	14.03	13.94	14.88	15.94	16.84	17.76	17.67	18.60	19.66
	4H	13.32	14.18	14.16	15.03	16.10	17.30	18.17	18.14	19.02	20.09
	6H	13.44	14.24	14.30	15.10	16.18	17.60	18.40	18.45	19.26	20.34
	8H	13.45	14.21	14.31	15.09	16.17	17.68	18.44	18.54	19.32	20.40
	12H	13.43	14.15	14.29	15.02	16.13	17.73	18.45	18.60	19.32	20.43
4H	2H	13.69	14.55	14.53	15.40	16.47	15.91	16.77	16.75	17.62	18.69
	3H	14.73	15.45	15.59	16.33	17.42	17.43	18.16	18.29	19.04	20.13
	4H	15.01	15.67	15.88	16.55	17.66	17.97	18.63	18.84	19.51	20.62
	6H	15.14	15.71	16.03	16.62	17.73	18.35	18.92	19.24	19.83	20.94
	8H	15.15	15.68	16.04	16.58	17.71	18.47	19.00	19.36	19.90	21.03
	12H	15.13	15.61	16.04	16.52	17.66	18.54	19.01	19.44	19.93	21.07
8H	4H	15.48	16.01	16.37	16.91	18.04	18.11	18.64	19.00	19.54	20.67
	6H	15.75	16.19	16.66	17.13	18.26	18.56	19.00	19.48	19.94	21.07
	8H	15.79	16.18	16.72	17.11	18.26	18.72	19.10	19.64	20.04	21.18
	12H	15.78	16.13	16.71	17.05	18.25	18.83	19.17	19.76	20.09	21.29
12H	4H	15.49	15.97	16.40	16.89	18.03	18.08	18.56	18.99	19.48	20.61
	6H	15.81	16.20	16.74	17.13	18.28	18.56	18.95	19.48	19.88	21.03
	8H	15.89	16.23	16.82	17.15	18.35	18.73	19.07	19.66	20.00	21.20

END OF REPORT