

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P933893

Luminaire Tested: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P933893
REPORT IS A COMBINATION OF REPORTS P933676 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5533.4 lumens
Efficiency: N/A
Efficacy: 125.8 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P933893

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P933893

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66		
1	101	97	93	89	95	91	88	85	81	78	76	71	69	68	62	61	60	55		
2	92	85	78	73	87	80	74	70	71	67	63	63	59	56	55	52	50	46		
3	84	75	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39		
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	43	40	37	34		
5	71	59	50	44	66	56	48	43	50	44	39	44	39	35	39	35	32	29		
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28	26		
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25	23		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18		
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6486	6486	6486	6486
5°	6535	6547	6535	5148
10°	6490	6449	6490	4611
15°	6420	6309	6420	5269
20°	6285	6144	6285	5280
25°	6011	5903	6011	5168
30°	5656	5702	5656	4922
35°	5042	5448	5042	4652
40°	4201	5150	4201	4448
45°	3754	4800	3754	4214
50°	3988	4384	3988	3978
55°	3752	3935	3752	3842
60°	3868	3342	3868	3519
65°	3506	2763	3506	3089
70°	2429	2202	2429	2589
75°	2129	1628	2129	1949
80°	1714	1076	1714	1172
85°	987	570	987	485

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 5753 cd/sqm

TEST NUMBER: P933893

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.2	2.3
10°-20°	358.3	6.5
20°-30°	553.8	10.0
30°-40°	661.2	11.9
40°-50°	665.0	12.0
50°-60°	578.7	10.5
60°-70°	410.3	7.4
70°-80°	217.1	3.9
80°-90°	55.2	1.0
90°-100°	143.4	2.6
100°-110°	377.1	6.8
110°-120°	391.1	7.1
120°-130°	313.7	5.7
130°-140°	246.1	4.4
140°-150°	188.9	3.4
150°-160°	136.0	2.5
160°-170°	83.2	1.5
170°-180°	28.1	0.5
0°-30°	1038.3	18.8
0°-40°	1699.5	30.7
0°-60°	2943.1	53.2
0°-90°	3625.6	65.5
90°-120°	911.7	16.5
90°-150°	1660.4	30.0
90°-180°	1908.0	34.5
0°-180°	5533.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1398	1398	1398	1398	1398	
5°	1405	1448	1405	1139	1405	133
15°	1341	1435	1341	1198	1341	377
25°	1181	1338	1181	1172	1181	542
35°	898	1194	898	1020	898	556
45°	579	984	579	864	579	464
55°	472	726	472	709	472	434
65°	328	438	328	489	328	313
75°	124	208	124	249	124	131
85°	21	53	21	45	21	29
90°	2	8	2	8	2	3
95°	19	87	19	87	19	21
105°	68	590	68	590	68	72
115°	121	760	121	760	121	119
125°	168	606	168	606	168	149
135°	200	470	200	470	200	155
145°	232	381	232	381	232	145
155°	262	328	262	328	262	121
165°	283	306	283	306	283	80
175°	294	296	294	296	294	28
180°	294	294	294	294	294	

TEST NUMBER: P933893

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0
2.5°	1409.8	1409.8	1417.8	1420.4	1420.4	1416.4	1412.4	1416.4	1428.3	1432.3	1431.0
5°	1404.6	1415.1	1429.7	1432.3	1434.9	1433.6	1431.0	1433.6	1446.9	1449.5	1450.8
7.5°	1393.9	1413.8	1432.3	1436.3	1440.3	1436.3	1434.9	1437.6	1450.8	1453.5	1453.5
10°	1380.7	1408.5	1429.7	1432.3	1436.3	1432.3	1432.3	1437.6	1450.8	1453.5	1454.7
12.5°	1362.2	1400.5	1420.4	1423.0	1428.3	1427.0	1425.7	1431.0	1444.2	1446.9	1446.9
15°	1341.1	1386.0	1404.6	1407.1	1416.4	1413.8	1413.8	1419.1	1433.6	1437.6	1436.3
17.5°	1312.0	1367.5	1388.7	1392.6	1399.2	1398.0	1399.2	1404.6	1417.8	1420.4	1421.7
20°	1278.8	1342.3	1367.5	1371.4	1378.0	1378.0	1378.0	1384.6	1398.0	1403.2	1403.2
22.5°	1233.9	1315.9	1342.3	1345.0	1353.0	1353.0	1355.6	1364.8	1376.8	1378.0	1378.0
25°	1181.0	1286.8	1309.3	1317.2	1325.2	1329.1	1333.1	1338.4	1342.3	1341.1	1342.3
27.5°	1125.5	1249.8	1278.8	1284.2	1294.7	1298.8	1304.0	1305.4	1306.6	1310.6	1308.0
30°	1063.3	1198.2	1241.9	1247.2	1264.3	1267.0	1261.7	1264.3	1271.0	1273.6	1276.3
32.5°	993.2	1121.5	1203.5	1215.4	1231.3	1223.3	1222.0	1226.0	1236.5	1236.5	1239.2
35°	898.0	1062.0	1167.8	1178.4	1190.3	1181.0	1186.4	1187.6	1194.2	1198.2	1196.9
37.5°	793.5	1010.5	1130.7	1138.7	1148.0	1136.1	1144.0	1148.0	1153.2	1150.6	1150.6
40°	700.9	929.7	1087.2	1092.4	1100.4	1091.1	1099.0	1101.7	1104.3	1101.7	1100.4
42.5°	632.1	841.2	1040.8	1047.4	1042.1	1048.8	1051.4	1056.7	1052.8	1047.4	1047.4
45°	579.3	817.3	990.5	998.5	990.5	1001.2	1005.1	1005.1	993.2	990.5	989.3
47.5°	562.1	769.7	940.3	940.3	936.3	949.6	956.2	947.0	935.0	931.1	931.1
50°	560.7	716.8	871.5	866.3	884.7	900.6	894.0	884.7	875.5	861.0	861.0
52.5°	509.2	652.0	783.0	802.8	831.9	841.2	830.5	821.3	805.5	798.8	793.5
55°	472.1	584.6	702.2	742.0	772.3	784.3	764.4	755.2	731.3	727.4	724.7
57.5°	464.2	486.7	628.2	678.5	715.4	714.2	702.2	685.1	665.3	661.3	659.9
60°	425.9	351.8	548.8	608.4	646.7	642.8	632.1	616.2	597.8	595.1	592.5
62.5°	386.2	255.3	458.9	526.3	580.6	579.3	570.0	546.2	532.9	526.3	521.1
65°	327.9	214.3	326.7	437.8	515.8	518.4	498.6	481.4	466.9	458.9	457.6
67.5°	250.0	174.6	220.9	365.0	453.7	451.0	425.9	418.0	399.4	395.5	387.5
70°	185.2	116.3	153.4	296.3	392.8	386.2	366.3	357.1	339.9	330.6	325.4
72.5°	153.4	93.9	112.4	230.1	330.6	322.7	305.5	294.9	280.4	272.4	267.1
75°	124.3	99.2	86.0	170.6	268.5	263.2	247.3	236.7	224.8	214.3	215.5
77.5°	91.3	92.6	68.7	125.6	213.0	205.0	195.7	182.5	177.2	166.6	166.6
80°	68.7	72.8	51.6	86.0	153.4	153.4	145.4	136.3	127.0	121.7	121.7
82.5°	46.2	46.2	38.4	54.2	104.5	100.5	95.2	92.6	87.3	84.6	84.6
85°	21.2	26.4	23.8	33.0	56.9	59.6	59.6	56.9	55.5	52.9	54.2
87.5°	6.6	11.9	14.6	18.5	29.1	30.5	31.7	31.7	31.7	33.0	33.0
90°	2.0	3.5	5.1	5.5	8.7	12.9	15.0	13.3	10.0	7.5	7.5
92.5°	7.9	21.3	34.8	38.2	53.6	74.2	84.5	74.0	53.2	37.6	36.1
95°	18.9	43.5	68.1	74.2	131.8	208.6	247.1	220.5	167.3	127.4	122.9
97.5°	32.8	54.5	76.1	81.5	177.6	305.7	369.8	353.0	319.4	294.1	285.5
100°	43.5	63.1	82.7	87.7	194.2	336.3	407.4	408.7	411.2	413.0	402.8
102.5°	52.6	70.9	89.2	93.8	201.9	346.1	418.2	439.6	482.4	514.5	505.7
105°	67.9	83.5	99.1	102.9	207.7	347.2	417.0	465.0	561.0	633.0	628.3
107.5°	83.7	98.2	112.7	116.3	208.6	331.7	393.2	460.2	594.2	694.6	695.8
110°	94.5	107.5	120.6	123.8	207.1	318.0	373.5	448.3	598.1	710.4	715.3

TEST NUMBER: P933893

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	104.9	117.3	129.8	132.9	207.2	306.1	355.6	432.2	585.4	700.4	707.9
115°	120.7	132.1	143.7	146.5	209.0	292.3	334.0	407.8	555.5	666.2	676.7
117.5°	136.3	146.7	157.2	159.8	213.0	283.8	319.2	385.8	519.0	619.0	630.6
120°	145.3	155.2	165.1	167.5	216.1	280.9	313.3	374.1	495.9	587.2	598.4
122.5°	154.2	164.2	174.1	176.6	220.7	279.3	308.7	363.5	473.2	555.4	566.6
125°	167.9	177.0	186.0	188.2	226.8	278.2	303.8	350.3	443.5	513.3	523.6
127.5°	179.0	188.0	197.2	199.5	232.9	277.4	299.6	339.7	419.6	479.6	488.3
130°	184.9	194.7	204.5	207.0	237.3	277.9	298.1	333.7	404.9	458.2	466.2
132.5°	191.0	200.8	210.6	213.1	241.0	278.2	296.7	328.5	392.2	440.1	447.2
135°	200.1	209.0	218.0	220.3	244.9	277.9	294.3	321.0	374.4	414.4	420.5
137.5°	209.3	218.2	227.1	229.3	250.8	279.5	293.9	316.5	361.6	395.4	400.4
140°	217.0	225.2	233.4	235.5	254.5	279.8	292.5	312.1	351.0	380.2	384.9
142.5°	223.0	230.5	238.1	240.0	257.5	280.9	292.5	309.7	343.9	369.6	373.6
145°	232.1	238.7	245.2	246.9	261.5	280.9	290.6	304.6	332.6	353.6	356.6
147.5°	241.2	247.6	254.0	255.6	267.2	282.8	290.6	301.6	323.6	340.1	342.6
150°	247.1	252.9	258.6	260.1	270.3	283.8	290.6	299.8	318.5	332.4	334.5
152.5°	253.2	257.5	262.0	263.1	272.2	284.5	290.6	298.5	314.3	326.3	327.8
155°	262.3	265.5	268.8	269.6	276.6	285.9	290.6	296.9	309.5	319.0	320.0
157.5°	269.0	272.1	275.3	276.1	280.9	287.3	290.6	295.5	305.3	312.7	313.4
160°	273.5	276.0	278.4	279.0	282.9	288.0	290.6	294.8	303.2	309.5	309.9
162.5°	278.1	279.9	281.7	282.2	285.0	288.7	290.6	294.1	301.2	306.5	306.9
165°	283.1	284.8	286.4	286.8	288.1	289.8	290.6	293.1	298.2	302.0	302.4
167.5°	287.6	288.4	289.2	289.4	290.5	291.9	292.5	294.2	297.6	300.0	300.2
170°	290.6	291.4	292.2	292.3	292.4	292.5	292.5	294.2	297.6	300.0	300.0
172.5°	292.2	292.3	292.5	292.5	292.5	292.5	292.5	293.8	296.5	298.5	298.3
175°	294.3	294.3	294.3	294.3	293.7	292.9	292.5	293.3	295.0	296.3	296.3
177.5°	294.3	294.3	294.3	294.3	293.8	293.2	292.9	293.6	294.9	295.9	295.7
180°	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3

TEST NUMBER: P933893

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0
2.5°	1433.6	1429.7	1433.6	1431.0	1432.3	1428.3	1416.4	1412.4	1416.4	1420.4	1420.4
5°	1450.8	1448.1	1450.8	1450.8	1449.5	1446.9	1433.6	1431.0	1433.6	1434.9	1432.3
7.5°	1456.1	1452.2	1456.1	1453.5	1453.5	1450.8	1437.6	1434.9	1436.3	1440.3	1436.3
10°	1456.1	1452.2	1456.1	1454.7	1453.5	1450.8	1437.6	1432.3	1432.3	1436.3	1432.3
12.5°	1449.5	1446.9	1449.5	1446.9	1446.9	1444.2	1431.0	1425.7	1427.0	1428.3	1423.0
15°	1438.9	1434.9	1438.9	1436.3	1437.6	1433.6	1419.1	1413.8	1413.8	1416.4	1407.1
17.5°	1423.0	1417.8	1423.0	1421.7	1420.4	1417.8	1404.6	1399.2	1398.0	1399.2	1392.6
20°	1404.6	1400.5	1404.6	1403.2	1403.2	1398.0	1384.6	1378.0	1378.0	1378.0	1371.4
22.5°	1375.5	1371.4	1375.5	1378.0	1378.0	1376.8	1364.8	1355.6	1353.0	1353.0	1345.0
25°	1342.3	1338.4	1342.3	1342.3	1341.1	1342.3	1338.4	1333.1	1329.1	1325.2	1317.2
27.5°	1310.6	1308.0	1310.6	1308.0	1310.6	1306.6	1305.4	1304.0	1298.8	1294.7	1284.2
30°	1278.8	1276.3	1278.8	1276.3	1273.6	1271.0	1264.3	1261.7	1267.0	1264.3	1247.2
32.5°	1239.2	1236.5	1239.2	1239.2	1236.5	1236.5	1226.0	1222.0	1223.3	1231.3	1215.4
35°	1198.2	1194.2	1198.2	1196.9	1198.2	1194.2	1187.6	1186.4	1181.0	1190.3	1178.4
37.5°	1150.6	1146.6	1150.6	1150.6	1150.6	1153.2	1148.0	1144.0	1136.1	1148.0	1138.7
40°	1101.7	1096.3	1101.7	1100.4	1101.7	1104.3	1101.7	1099.0	1091.1	1100.4	1092.4
42.5°	1046.1	1044.8	1046.1	1047.4	1047.4	1052.8	1056.7	1051.4	1048.8	1042.1	1047.4
45°	986.6	983.9	986.6	989.3	990.5	993.2	1005.1	1005.1	1001.2	990.5	998.5
47.5°	923.1	916.5	923.1	931.1	931.1	935.0	947.0	956.2	949.6	936.3	940.3
50°	855.7	857.0	855.7	861.0	861.0	875.5	884.7	894.0	900.6	884.7	866.3
52.5°	789.6	788.2	789.6	793.5	798.8	805.5	821.3	830.5	841.2	831.9	802.8
55°	723.4	726.1	723.4	724.7	727.4	731.3	755.2	764.4	784.3	772.3	742.0
57.5°	657.3	653.3	657.3	659.9	661.3	665.3	685.1	702.2	714.2	715.4	678.5
60°	580.6	575.3	580.6	592.5	595.1	597.8	616.2	632.1	642.8	646.7	608.4
62.5°	513.1	503.8	513.1	521.1	526.3	532.9	546.2	570.0	579.3	580.6	526.3
65°	441.7	437.8	441.7	457.6	458.9	466.9	481.4	498.6	518.4	515.8	437.8
67.5°	376.9	376.9	376.9	387.5	395.5	399.4	418.0	425.9	451.0	453.7	365.0
70°	317.4	316.1	317.4	325.4	330.6	339.9	357.1	366.3	386.2	392.8	296.3
72.5°	260.5	259.2	260.5	267.1	272.4	280.4	294.9	305.5	322.7	330.6	230.1
75°	210.3	207.7	210.3	215.5	214.3	224.8	236.7	247.3	263.2	268.5	170.6
77.5°	161.3	161.3	161.3	166.6	166.6	177.2	182.5	195.7	205.0	213.0	125.6
80°	120.4	119.0	120.4	121.7	121.7	127.0	136.3	145.4	153.4	153.4	86.0
82.5°	84.6	82.0	84.6	84.6	84.6	87.3	92.6	95.2	100.5	104.5	54.2
85°	52.9	52.9	52.9	54.2	52.9	55.5	56.9	59.6	59.6	56.9	33.0
87.5°	34.4	33.0	34.4	33.0	33.0	31.7	31.7	31.7	30.5	29.1	18.5
90°	7.5	7.5	7.5	7.5	7.5	10.0	13.3	15.0	12.9	8.7	5.5
92.5°	30.1	24.1	30.1	36.1	37.6	53.2	74.0	84.5	74.2	53.6	38.2
95°	104.8	86.7	104.8	122.9	127.4	167.3	220.5	247.1	208.6	131.8	74.2
97.5°	251.0	216.6	251.0	285.5	294.1	319.4	353.0	369.8	305.7	177.6	81.5
100°	361.8	320.7	361.8	402.8	413.0	411.2	408.7	407.4	336.3	194.2	87.7
102.5°	470.6	435.5	470.6	505.7	514.5	482.4	439.6	418.2	346.1	201.9	93.8
105°	609.4	590.5	609.4	628.3	633.0	561.0	465.0	417.0	347.2	207.7	102.9
107.5°	700.4	704.9	700.4	695.8	694.6	594.2	460.2	393.2	331.7	208.6	116.3
110°	735.0	754.7	735.0	715.3	710.4	598.1	448.3	373.5	318.0	207.1	123.8

TEST NUMBER: P933893

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	738.1	768.3	738.1	707.9	700.4	585.4	432.2	355.6	306.1	207.2	132.9
115°	718.6	760.4	718.6	676.7	666.2	555.5	407.8	334.0	292.3	209.0	146.5
117.5°	677.1	723.5	677.1	630.6	619.0	519.0	385.8	319.2	283.8	213.0	159.8
120°	643.6	688.7	643.6	598.4	587.2	495.9	374.1	313.3	280.9	216.1	167.5
122.5°	611.0	655.5	611.0	566.6	555.4	473.2	363.5	308.7	279.3	220.7	176.6
125°	564.6	605.6	564.6	523.6	513.3	443.5	350.3	303.8	278.2	226.8	188.2
127.5°	522.8	557.4	522.8	488.3	479.6	419.6	339.7	299.6	277.4	232.9	199.5
130°	498.1	530.1	498.1	466.2	458.2	404.9	333.7	298.1	277.9	237.3	207.0
132.5°	475.8	504.4	475.8	447.2	440.1	392.2	328.5	296.7	278.2	241.0	213.1
135°	445.2	469.8	445.2	420.5	414.4	374.4	321.0	294.3	277.9	244.9	220.3
137.5°	420.6	440.8	420.6	400.4	395.4	361.6	316.5	293.9	279.5	250.8	229.3
140°	403.8	422.7	403.8	384.9	380.2	351.0	312.1	292.5	279.8	254.5	235.5
142.5°	389.9	406.0	389.9	373.6	369.6	343.9	309.7	292.5	280.9	257.5	240.0
145°	369.0	381.2	369.0	356.6	353.6	332.6	304.6	290.6	280.9	261.5	246.9
147.5°	352.8	363.0	352.8	342.6	340.1	323.6	301.6	290.6	282.8	267.2	255.6
150°	342.7	351.0	342.7	334.5	332.4	318.5	299.8	290.6	283.8	270.3	260.1
152.5°	334.1	340.3	334.1	327.8	326.3	314.3	298.5	290.6	284.5	272.2	263.1
155°	324.1	328.2	324.1	320.0	319.0	309.5	296.9	290.6	285.9	276.6	269.6
157.5°	316.3	319.2	316.3	313.4	312.7	305.3	295.5	290.6	287.3	280.9	276.1
160°	311.6	313.3	311.6	309.9	309.5	303.2	294.8	290.6	288.0	282.9	279.0
162.5°	308.5	310.1	308.5	306.9	306.5	301.2	294.1	290.6	288.7	285.0	282.2
165°	304.1	305.8	304.1	302.4	302.0	298.2	293.1	290.6	289.8	288.1	286.8
167.5°	300.9	301.6	300.9	300.2	300.0	297.6	294.2	292.5	291.9	290.5	289.4
170°	300.0	300.0	300.0	300.0	300.0	297.6	294.2	292.5	292.5	292.4	292.3
172.5°	297.7	297.1	297.7	298.3	298.5	296.5	293.8	292.5	292.5	292.5	292.5
175°	296.3	296.3	296.3	296.3	296.3	295.0	293.3	292.5	292.9	293.7	294.3
177.5°	295.0	294.3	295.0	295.7	295.9	294.9	293.6	292.9	293.2	293.8	294.3
180°	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3

TEST NUMBER: P933893

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0
2.5°	1417.8	1409.8	1409.8	1396.6	1391.3	1387.3	1380.7	1360.9	1355.6	1350.3	1358.2
5°	1429.7	1415.1	1404.6	1380.7	1360.9	1353.0	1327.8	1280.2	1248.5	1224.6	1211.4
7.5°	1432.3	1413.8	1393.9	1356.9	1309.3	1288.1	1211.4	1124.1	1100.4	1079.2	1066.0
10°	1429.7	1408.5	1380.7	1325.2	1212.8	1175.7	1099.0	1042.1	1027.6	1023.7	1027.6
12.5°	1420.4	1400.5	1362.2	1269.7	1112.2	1087.2	1042.1	1009.1	1006.4	1013.0	1048.8
15°	1404.6	1386.0	1341.1	1195.5	1056.7	1038.2	1006.4	994.6	1009.1	1055.4	1162.5
17.5°	1388.7	1367.5	1312.0	1122.9	1014.4	1001.2	978.7	1002.5	1084.5	1146.6	1182.3
20°	1367.5	1342.3	1278.8	1069.9	983.9	972.1	961.4	1068.6	1130.7	1153.2	1173.0
22.5°	1342.3	1315.9	1233.9	1032.9	952.2	943.0	949.6	1105.6	1130.7	1146.6	1163.8
25°	1309.3	1286.8	1181.0	1003.8	927.1	916.5	941.6	1101.7	1116.3	1120.2	1154.6
27.5°	1278.8	1249.8	1125.5	977.3	896.7	892.7	948.2	1084.5	1095.1	1099.0	1136.1
30°	1241.9	1198.2	1063.3	949.6	864.9	863.6	949.6	1063.3	1060.6	1071.3	1108.3
32.5°	1203.5	1121.5	993.2	915.2	834.6	833.2	940.3	1031.6	1028.9	1043.5	1071.3
35°	1167.8	1062.0	898.0	875.5	796.2	797.5	917.9	994.6	995.9	1009.1	1026.3
37.5°	1130.7	1010.5	793.5	831.9	759.1	759.1	887.4	960.2	957.5	961.4	985.3
40°	1087.2	929.7	700.9	775.0	724.7	720.8	850.4	923.1	913.8	912.5	945.6
42.5°	1040.8	841.2	632.1	699.7	685.1	679.7	805.5	878.1	861.0	864.9	907.2
45°	990.5	817.3	579.3	591.2	644.1	640.1	756.5	826.6	814.6	825.3	868.9
47.5°	940.3	769.7	562.1	490.6	600.5	599.1	702.2	776.3	769.7	780.3	826.6
50°	871.5	716.8	560.7	420.5	551.5	556.8	637.4	727.4	727.4	736.6	785.5
52.5°	783.0	652.0	509.2	380.9	494.6	510.5	580.6	685.1	687.7	697.0	740.6
55°	702.2	584.6	472.1	350.4	427.1	461.5	525.0	641.4	646.7	656.0	695.6
57.5°	628.2	486.7	464.2	314.7	365.0	398.0	476.1	599.1	601.8	609.6	648.0
60°	548.8	351.8	425.9	276.4	310.8	335.9	431.2	548.8	558.1	563.4	596.4
62.5°	458.9	255.3	386.2	250.0	284.4	289.6	394.1	501.3	513.1	517.2	537.0
65°	326.7	214.3	327.9	227.5	256.6	257.9	354.5	452.3	462.9	469.5	484.0
67.5°	220.9	174.6	250.0	206.3	235.5	236.7	316.1	395.5	410.0	415.3	424.6
70°	153.4	116.3	185.2	183.8	211.6	214.3	275.1	343.8	357.1	361.1	366.3
72.5°	112.4	93.9	153.4	165.4	186.5	189.1	232.8	285.6	298.9	302.9	305.5
75°	86.0	99.2	124.3	144.2	158.7	160.0	190.4	232.8	242.1	244.6	246.0
77.5°	68.7	92.6	91.3	116.3	129.6	127.0	149.5	179.8	187.8	187.8	187.8
80°	51.6	72.8	68.7	83.3	95.2	92.6	107.1	128.3	130.9	133.6	132.2
82.5°	38.4	46.2	46.2	52.9	63.5	60.8	71.4	83.3	83.3	83.3	86.0
85°	23.8	26.4	21.2	27.8	35.7	34.4	39.6	45.0	46.2	46.2	43.7
87.5°	14.6	11.9	6.6	10.6	15.9	15.9	18.5	19.8	18.5	18.5	18.5
90°	5.1	3.5	2.0	3.5	5.1	5.5	8.7	12.9	15.0	13.3	10.0
92.5°	34.8	21.3	7.9	21.3	34.8	38.2	53.6	74.2	84.5	74.0	53.2
95°	68.1	43.5	18.9	43.5	68.1	74.2	131.8	208.6	247.1	220.5	167.3
97.5°	76.1	54.5	32.8	54.5	76.1	81.5	177.6	305.7	369.8	353.0	319.4
100°	82.7	63.1	43.5	63.1	82.7	87.7	194.2	336.3	407.4	408.7	411.2
102.5°	89.2	70.9	52.6	70.9	89.2	93.8	201.9	346.1	418.2	439.6	482.4
105°	99.1	83.5	67.9	83.5	99.1	102.9	207.7	347.2	417.0	465.0	561.0
107.5°	112.7	98.2	83.7	98.2	112.7	116.3	208.6	331.7	393.2	460.2	594.2
110°	120.6	107.5	94.5	107.5	120.6	123.8	207.1	318.0	373.5	448.3	598.1

TEST NUMBER: P933893

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	129.8	117.3	104.9	117.3	129.8	132.9	207.2	306.1	355.6	432.2	585.4
115°	143.7	132.1	120.7	132.1	143.7	146.5	209.0	292.3	334.0	407.8	555.5
117.5°	157.2	146.7	136.3	146.7	157.2	159.8	213.0	283.8	319.2	385.8	519.0
120°	165.1	155.2	145.3	155.2	165.1	167.5	216.1	280.9	313.3	374.1	495.9
122.5°	174.1	164.2	154.2	164.2	174.1	176.6	220.7	279.3	308.7	363.5	473.2
125°	186.0	177.0	167.9	177.0	186.0	188.2	226.8	278.2	303.8	350.3	443.5
127.5°	197.2	188.0	179.0	188.0	197.2	199.5	232.9	277.4	299.6	339.7	419.6
130°	204.5	194.7	184.9	194.7	204.5	207.0	237.3	277.9	298.1	333.7	404.9
132.5°	210.6	200.8	191.0	200.8	210.6	213.1	241.0	278.2	296.7	328.5	392.2
135°	218.0	209.0	200.1	209.0	218.0	220.3	244.9	277.9	294.3	321.0	374.4
137.5°	227.1	218.2	209.3	218.2	227.1	229.3	250.8	279.5	293.9	316.5	361.6
140°	233.4	225.2	217.0	225.2	233.4	235.5	254.5	279.8	292.5	312.1	351.0
142.5°	238.1	230.5	223.0	230.5	238.1	240.0	257.5	280.9	292.5	309.7	343.9
145°	245.2	238.7	232.1	238.7	245.2	246.9	261.5	280.9	290.6	304.6	332.6
147.5°	254.0	247.6	241.2	247.6	254.0	255.6	267.2	282.8	290.6	301.6	323.6
150°	258.6	252.9	247.1	252.9	258.6	260.1	270.3	283.8	290.6	299.8	318.5
152.5°	262.0	257.5	253.2	257.5	262.0	263.1	272.2	284.5	290.6	298.5	314.3
155°	268.8	265.5	262.3	265.5	268.8	269.6	276.6	285.9	290.6	296.9	309.5
157.5°	275.3	272.1	269.0	272.1	275.3	276.1	280.9	287.3	290.6	295.5	305.3
160°	278.4	276.0	273.5	276.0	278.4	279.0	282.9	288.0	290.6	294.8	303.2
162.5°	281.7	279.9	278.1	279.9	281.7	282.2	285.0	288.7	290.6	294.1	301.2
165°	286.4	284.8	283.1	284.8	286.4	286.8	288.1	289.8	290.6	293.1	298.2
167.5°	289.2	288.4	287.6	288.4	289.2	289.4	290.5	291.9	292.5	294.2	297.6
170°	292.2	291.4	290.6	291.4	292.2	292.3	292.4	292.5	292.5	294.2	297.6
172.5°	292.5	292.3	292.2	292.3	292.5	292.5	292.5	292.5	292.5	293.8	296.5
175°	294.3	294.3	294.3	294.3	294.3	294.3	293.7	292.9	292.5	293.3	295.0
177.5°	294.3	294.3	294.3	294.3	294.3	294.3	293.8	293.2	292.9	293.6	294.9
180°	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3

TEST NUMBER: P933893

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0
2.5°	1348.9	1345.0	1350.3	1335.7	1350.3	1345.0	1348.9	1358.2	1350.3	1355.6	1360.9
5°	1183.7	1177.1	1155.9	1138.7	1155.9	1177.1	1183.7	1211.4	1224.6	1248.5	1280.2
7.5°	1058.0	1052.8	1047.4	1036.9	1047.4	1052.8	1058.0	1066.0	1079.2	1100.4	1124.1
10°	1030.3	1031.6	1039.5	1038.2	1039.5	1031.6	1030.3	1027.6	1023.7	1027.6	1042.1
12.5°	1101.7	1113.6	1157.2	1154.6	1157.2	1113.6	1101.7	1048.8	1013.0	1006.4	1009.1
15°	1183.7	1187.6	1196.9	1198.2	1196.9	1187.6	1183.7	1162.5	1055.4	1009.1	994.6
17.5°	1191.6	1193.0	1199.6	1199.6	1199.6	1193.0	1191.6	1182.3	1146.6	1084.5	1002.5
20°	1185.0	1187.6	1200.8	1203.5	1200.8	1187.6	1185.0	1173.0	1153.2	1130.7	1068.6
22.5°	1182.3	1187.6	1198.2	1196.9	1198.2	1187.6	1182.3	1163.8	1146.6	1130.7	1105.6
25°	1169.1	1169.1	1170.5	1171.8	1170.5	1169.1	1169.1	1154.6	1120.2	1116.3	1101.7
27.5°	1141.3	1144.0	1151.9	1150.6	1151.9	1144.0	1141.3	1136.1	1099.0	1095.1	1084.5
30°	1116.3	1113.6	1107.0	1101.7	1107.0	1113.6	1116.3	1108.3	1071.3	1060.6	1063.3
32.5°	1073.9	1067.2	1060.6	1056.7	1060.6	1067.2	1073.9	1071.3	1043.5	1028.9	1031.6
35°	1023.7	1024.9	1023.7	1019.6	1023.7	1024.9	1023.7	1026.3	1009.1	995.9	994.6
37.5°	988.0	990.5	989.3	983.9	989.3	990.5	988.0	985.3	961.4	957.5	960.2
40°	950.9	952.2	950.9	947.0	950.9	952.2	950.9	945.6	912.5	913.8	923.1
42.5°	915.2	913.8	909.9	907.2	909.9	913.8	915.2	907.2	864.9	861.0	878.1
45°	874.2	875.5	867.6	863.6	867.6	875.5	874.2	868.9	825.3	814.6	826.6
47.5°	833.2	833.2	826.6	822.6	826.6	833.2	833.2	826.6	780.3	769.7	776.3
50°	789.6	788.2	778.9	777.7	778.9	788.2	789.6	785.5	736.6	727.4	727.4
52.5°	739.3	739.3	740.6	743.2	740.6	739.3	739.3	740.6	697.0	687.7	685.1
55°	695.6	697.0	706.3	708.8	706.3	697.0	695.6	695.6	656.0	646.7	641.4
57.5°	650.7	650.7	657.3	657.3	657.3	650.7	650.7	648.0	609.6	601.8	599.1
60°	599.1	601.8	607.1	605.7	607.1	601.8	599.1	596.4	563.4	558.1	548.8
62.5°	544.9	547.5	548.8	546.2	548.8	547.5	544.9	537.0	517.2	513.1	501.3
65°	488.0	490.6	492.0	489.4	492.0	490.6	488.0	484.0	469.5	462.9	452.3
67.5°	429.8	428.5	427.1	432.5	427.1	428.5	429.8	424.6	415.3	410.0	395.5
70°	370.3	370.3	369.0	371.6	369.0	370.3	370.3	366.3	361.1	357.1	343.8
72.5°	306.8	305.5	310.8	306.8	310.8	305.5	306.8	305.5	302.9	298.9	285.6
75°	244.6	247.3	244.6	248.7	244.6	247.3	244.6	246.0	244.6	242.1	232.8
77.5°	186.5	189.1	186.5	186.5	186.5	189.1	186.5	187.8	187.8	187.8	179.8
80°	132.2	130.9	130.9	129.6	130.9	130.9	132.2	132.2	133.6	130.9	128.3
82.5°	84.6	83.3	83.3	86.0	83.3	83.3	84.6	86.0	83.3	83.3	83.3
85°	46.2	47.6	45.0	45.0	45.0	47.6	46.2	43.7	46.2	46.2	45.0
87.5°	17.2	15.9	15.9	15.9	15.9	15.9	17.2	18.5	18.5	18.5	19.8
90°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	10.0	13.3	15.0	12.9
92.5°	37.6	36.1	30.1	24.1	30.1	36.1	37.6	53.2	74.0	84.5	74.2
95°	127.4	122.9	104.8	86.7	104.8	122.9	127.4	167.3	220.5	247.1	208.6
97.5°	294.1	285.5	251.0	216.6	251.0	285.5	294.1	319.4	353.0	369.8	305.7
100°	413.0	402.8	361.8	320.7	361.8	402.8	413.0	411.2	408.7	407.4	336.3
102.5°	514.5	505.7	470.6	435.5	470.6	505.7	514.5	482.4	439.6	418.2	346.1
105°	633.0	628.3	609.4	590.5	609.4	628.3	633.0	561.0	465.0	417.0	347.2
107.5°	694.6	695.8	700.4	704.9	700.4	695.8	694.6	594.2	460.2	393.2	331.7
110°	710.4	715.3	735.0	754.7	735.0	715.3	710.4	598.1	448.3	373.5	318.0

TEST NUMBER: P933893

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	700.4	707.9	738.1	768.3	738.1	707.9	700.4	585.4	432.2	355.6	306.1
115°	666.2	676.7	718.6	760.4	718.6	676.7	666.2	555.5	407.8	334.0	292.3
117.5°	619.0	630.6	677.1	723.5	677.1	630.6	619.0	519.0	385.8	319.2	283.8
120°	587.2	598.4	643.6	688.7	643.6	598.4	587.2	495.9	374.1	313.3	280.9
122.5°	555.4	566.6	611.0	655.5	611.0	566.6	555.4	473.2	363.5	308.7	279.3
125°	513.3	523.6	564.6	605.6	564.6	523.6	513.3	443.5	350.3	303.8	278.2
127.5°	479.6	488.3	522.8	557.4	522.8	488.3	479.6	419.6	339.7	299.6	277.4
130°	458.2	466.2	498.1	530.1	498.1	466.2	458.2	404.9	333.7	298.1	277.9
132.5°	440.1	447.2	475.8	504.4	475.8	447.2	440.1	392.2	328.5	296.7	278.2
135°	414.4	420.5	445.2	469.8	445.2	420.5	414.4	374.4	321.0	294.3	277.9
137.5°	395.4	400.4	420.6	440.8	420.6	400.4	395.4	361.6	316.5	293.9	279.5
140°	380.2	384.9	403.8	422.7	403.8	384.9	380.2	351.0	312.1	292.5	279.8
142.5°	369.6	373.6	389.9	406.0	389.9	373.6	369.6	343.9	309.7	292.5	280.9
145°	353.6	356.6	369.0	381.2	369.0	356.6	353.6	332.6	304.6	290.6	280.9
147.5°	340.1	342.6	352.8	363.0	352.8	342.6	340.1	323.6	301.6	290.6	282.8
150°	332.4	334.5	342.7	351.0	342.7	334.5	332.4	318.5	299.8	290.6	283.8
152.5°	326.3	327.8	334.1	340.3	334.1	327.8	326.3	314.3	298.5	290.6	284.5
155°	319.0	320.0	324.1	328.2	324.1	320.0	319.0	309.5	296.9	290.6	285.9
157.5°	312.7	313.4	316.3	319.2	316.3	313.4	312.7	305.3	295.5	290.6	287.3
160°	309.5	309.9	311.6	313.3	311.6	309.9	309.5	303.2	294.8	290.6	288.0
162.5°	306.5	306.9	308.5	310.1	308.5	306.9	306.5	301.2	294.1	290.6	288.7
165°	302.0	302.4	304.1	305.8	304.1	302.4	302.0	298.2	293.1	290.6	289.8
167.5°	300.0	300.2	300.9	301.6	300.9	300.2	300.0	297.6	294.2	292.5	291.9
170°	300.0	300.0	300.0	300.0	300.0	300.0	300.0	297.6	294.2	292.5	292.5
172.5°	298.5	298.3	297.7	297.1	297.7	298.3	298.5	296.5	293.8	292.5	292.5
175°	296.3	296.3	296.3	296.3	296.3	296.3	296.3	295.0	293.3	292.5	292.9
177.5°	295.9	295.7	295.0	294.3	295.0	295.7	295.9	294.9	293.6	292.9	293.2
180°	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3

TEST NUMBER: P933893

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1398.0	1398.0	1398.0	1398.0	1398.0
2.5°	1380.7	1387.3	1391.3	1396.6	1409.8
5°	1327.8	1353.0	1360.9	1380.7	1404.6
7.5°	1211.4	1288.1	1309.3	1356.9	1393.9
10°	1099.0	1175.7	1212.8	1325.2	1380.7
12.5°	1042.1	1087.2	1112.2	1269.7	1362.2
15°	1006.4	1038.2	1056.7	1195.5	1341.1
17.5°	978.7	1001.2	1014.4	1122.9	1312.0
20°	961.4	972.1	983.9	1069.9	1278.8
22.5°	949.6	943.0	952.2	1032.9	1233.9
25°	941.6	916.5	927.1	1003.8	1181.0
27.5°	948.2	892.7	896.7	977.3	1125.5
30°	949.6	863.6	864.9	949.6	1063.3
32.5°	940.3	833.2	834.6	915.2	993.2
35°	917.9	797.5	796.2	875.5	898.0
37.5°	887.4	759.1	759.1	831.9	793.5
40°	850.4	720.8	724.7	775.0	700.9
42.5°	805.5	679.7	685.1	699.7	632.1
45°	756.5	640.1	644.1	591.2	579.3
47.5°	702.2	599.1	600.5	490.6	562.1
50°	637.4	556.8	551.5	420.5	560.7
52.5°	580.6	510.5	494.6	380.9	509.2
55°	525.0	461.5	427.1	350.4	472.1
57.5°	476.1	398.0	365.0	314.7	464.2
60°	431.2	335.9	310.8	276.4	425.9
62.5°	394.1	289.6	284.4	250.0	386.2
65°	354.5	257.9	256.6	227.5	327.9
67.5°	316.1	236.7	235.5	206.3	250.0
70°	275.1	214.3	211.6	183.8	185.2
72.5°	232.8	189.1	186.5	165.4	153.4
75°	190.4	160.0	158.7	144.2	124.3
77.5°	149.5	127.0	129.6	116.3	91.3
80°	107.1	92.6	95.2	83.3	68.7
82.5°	71.4	60.8	63.5	52.9	46.2
85°	39.6	34.4	35.7	27.8	21.2
87.5°	18.5	15.9	15.9	10.6	6.6
90°	8.7	5.5	5.1	3.5	2.0
92.5°	53.6	38.2	34.8	21.3	7.9
95°	131.8	74.2	68.1	43.5	18.9
97.5°	177.6	81.5	76.1	54.5	32.8
100°	194.2	87.7	82.7	63.1	43.5
102.5°	201.9	93.8	89.2	70.9	52.6
105°	207.7	102.9	99.1	83.5	67.9
107.5°	208.6	116.3	112.7	98.2	83.7
110°	207.1	123.8	120.6	107.5	94.5



TEST NUMBER: P933893

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	207.2	132.9	129.8	117.3	104.9
115°	209.0	146.5	143.7	132.1	120.7
117.5°	213.0	159.8	157.2	146.7	136.3
120°	216.1	167.5	165.1	155.2	145.3
122.5°	220.7	176.6	174.1	164.2	154.2
125°	226.8	188.2	186.0	177.0	167.9
127.5°	232.9	199.5	197.2	188.0	179.0
130°	237.3	207.0	204.5	194.7	184.9
132.5°	241.0	213.1	210.6	200.8	191.0
135°	244.9	220.3	218.0	209.0	200.1
137.5°	250.8	229.3	227.1	218.2	209.3
140°	254.5	235.5	233.4	225.2	217.0
142.5°	257.5	240.0	238.1	230.5	223.0
145°	261.5	246.9	245.2	238.7	232.1
147.5°	267.2	255.6	254.0	247.6	241.2
150°	270.3	260.1	258.6	252.9	247.1
152.5°	272.2	263.1	262.0	257.5	253.2
155°	276.6	269.6	268.8	265.5	262.3
157.5°	280.9	276.1	275.3	272.1	269.0
160°	282.9	279.0	278.4	276.0	273.5
162.5°	285.0	282.2	281.7	279.9	278.1
165°	288.1	286.8	286.4	284.8	283.1
167.5°	290.5	289.4	289.2	288.4	287.6
170°	292.4	292.3	292.2	291.4	290.6
172.5°	292.5	292.5	292.5	292.3	292.2
175°	293.7	294.3	294.3	294.3	294.3
177.5°	293.8	294.3	294.3	294.3	294.3
180°	294.3	294.3	294.3	294.3	294.3

TEST NUMBER: P933893

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-8-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.62	13.64	13.44	14.48	15.51	15.46	16.48	16.27	17.32	18.35
	3H	13.11	14.03	13.94	14.87	15.93	16.82	17.74	17.65	18.58	19.64
	4H	13.31	14.18	14.15	15.03	16.10	17.28	18.14	18.12	18.99	20.06
	6H	13.44	14.24	14.29	15.09	16.18	17.57	18.37	18.42	19.23	20.31
	8H	13.44	14.20	14.31	15.08	16.16	17.65	18.41	18.51	19.29	20.37
	12H	13.42	14.14	14.29	15.02	16.12	17.70	18.42	18.56	19.29	20.40
4H	2H	13.68	14.54	14.52	15.39	16.46	15.89	16.75	16.74	17.61	18.68
	3H	14.72	15.44	15.58	16.32	17.41	17.41	18.13	18.27	19.02	20.10
	4H	15.00	15.66	15.87	16.54	17.65	17.95	18.61	18.82	19.49	20.60
	6H	15.14	15.70	16.02	16.61	17.72	18.33	18.89	19.21	19.80	20.91
	8H	15.15	15.68	16.03	16.58	17.70	18.44	18.97	19.33	19.87	21.00
	12H	15.12	15.60	16.03	16.52	17.65	18.50	18.98	19.41	19.90	21.03
8H	4H	15.47	16.00	16.36	16.90	18.03	18.09	18.62	18.98	19.52	20.64
	6H	15.74	16.18	16.65	17.12	18.25	18.53	18.97	19.45	19.91	21.04
	8H	15.78	16.17	16.71	17.10	18.25	18.69	19.07	19.61	20.01	21.15
	12H	15.77	16.12	16.70	17.04	18.24	18.79	19.14	19.72	20.06	21.26
12H	4H	15.48	15.96	16.39	16.88	18.01	18.06	18.54	18.97	19.45	20.59
	6H	15.80	16.19	16.73	17.12	18.27	18.53	18.92	19.46	19.85	21.00
	8H	15.88	16.22	16.80	17.14	18.34	18.70	19.04	19.63	19.97	21.17

END OF REPORT