

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934593

Luminaire Tested: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934593
REPORT IS A COMBINATION OF REPORTS P933704 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13073.4 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 112
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934593

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P934593

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	65	63
2	93	86	79	74	88	81	76	71	73	68	65	65	62	59	58	56	53
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	52	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27
8	57	44	36	30	54	42	35	29	38	32	28	35	29	26	31	27	24
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21
10	49	37	30	25	47	35	28	24	32	26	22	30	25	21	27	23	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16364	16364	16364	16364
5°	16487	16519	16487	12989
10°	16376	16272	16376	11634
15°	16199	15919	16199	13294
20°	15860	15502	15860	13321
25°	15166	14893	15166	13039
30°	14270	14387	14270	12419
35°	12721	13747	12721	11738
40°	10601	12994	10601	11223
45°	9471	12113	9471	10631
50°	10062	11062	10062	10037
55°	9467	9929	9467	9694
60°	9758	8433	9758	8879
65°	8847	6971	8847	7792
70°	6127	5555	6127	6532
75°	5371	4107	5371	4917
80°	4329	2715	4329	2957
85°	2483	1438	2483	1223

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 14516 cd/sqm

TEST NUMBER: P934593

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	318.4	2.4
10°-20°	904.0	6.9
20°-30°	1397.4	10.7
30°-40°	1668.2	12.8
40°-50°	1678.0	12.8
50°-60°	1460.0	11.2
60°-70°	1035.2	7.9
70°-80°	547.7	4.2
80°-90°	138.7	1.1
90°-100°	295.2	2.3
100°-110°	776.1	5.9
110°-120°	804.7	6.2
120°-130°	645.5	4.9
130°-140°	506.5	3.9
140°-150°	388.8	3.0
150°-160°	280.0	2.1
160°-170°	171.3	1.3
170°-180°	57.9	0.4
0°-30°	2619.7	20.0
0°-40°	4287.9	32.8
0°-60°	7425.9	56.8
0°-90°	9147.5	70.0
90°-120°	1876.0	14.4
90°-150°	3416.8	26.1
90°-180°	3926.0	30.0
0°-180°	13073.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3527	3527	3527	3527	3527	
5°	3544	3654	3544	2873	3544	336
15°	3384	3620	3384	3023	3384	952
25°	2980	3377	2980	2956	2980	1368
35°	2266	3013	2266	2573	2266	1402
45°	1462	2483	1462	2179	1462	1171
55°	1191	1832	1191	1789	1191	1095
65°	828	1104	828	1235	828	791
75°	314	524	314	627	314	330
85°	53	134	53	114	53	72
90°	4	16	4	16	4	6
95°	39	178	39	178	39	43
105°	140	1215	140	1215	140	148
115°	248	1565	248	1565	248	245
125°	346	1246	346	1246	346	307
135°	412	967	412	967	412	319
145°	478	784	478	784	478	299
155°	540	676	540	676	540	248
165°	582	629	582	629	582	164
175°	606	610	606	610	606	57
180°	606	606	606	606	606	

TEST NUMBER: P934593

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1
2.5°	3557.1	3557.1	3577.1	3583.8	3583.8	3573.9	3563.8	3573.9	3603.8	3613.9	3610.5
5°	3543.8	3570.5	3607.2	3613.9	3620.5	3617.2	3610.5	3617.2	3650.6	3657.3	3660.6
7.5°	3517.1	3567.2	3613.9	3623.8	3633.9	3623.8	3620.5	3627.2	3660.6	3667.2	3667.2
10°	3483.7	3553.8	3607.2	3613.9	3623.8	3613.9	3613.9	3627.2	3660.6	3667.2	3670.6
12.5°	3437.0	3533.7	3583.8	3590.5	3603.8	3600.5	3597.2	3610.5	3643.9	3650.6	3650.6
15°	3383.7	3497.0	3543.8	3550.5	3573.9	3567.2	3567.2	3580.5	3617.2	3627.2	3623.8
17.5°	3310.2	3450.3	3503.8	3513.7	3530.5	3527.1	3530.5	3543.8	3577.1	3583.8	3587.2
20°	3226.8	3386.9	3450.3	3460.4	3477.0	3477.0	3477.0	3493.7	3527.1	3540.4	3540.4
22.5°	3113.3	3320.3	3386.9	3393.6	3413.6	3413.6	3420.3	3443.7	3473.7	3477.0	3477.0
25°	2979.9	3246.8	3303.5	3323.5	3343.5	3353.6	3363.6	3377.0	3386.9	3383.7	3386.9
27.5°	2839.7	3153.3	3226.8	3240.1	3266.8	3276.9	3290.2	3293.5	3296.9	3306.8	3300.1
30°	2682.9	3023.3	3133.3	3146.7	3190.1	3196.7	3183.4	3190.1	3206.8	3213.5	3220.1
32.5°	2506.0	2829.7	3036.6	3066.7	3106.7	3086.7	3083.3	3093.3	3120.0	3120.0	3126.7
35°	2265.7	2679.6	2946.5	2973.2	3003.2	2979.9	2993.2	2996.6	3013.2	3023.3	3019.9
37.5°	2002.2	2549.4	2853.1	2873.1	2896.5	2866.4	2886.4	2896.5	2909.8	2903.1	2903.1
40°	1768.6	2345.8	2743.0	2756.3	2776.3	2752.9	2772.9	2779.6	2786.3	2779.6	2776.3
42.5°	1595.1	2122.3	2626.1	2642.8	2629.5	2646.1	2652.8	2666.1	2656.2	2642.8	2642.8
45°	1461.5	2062.2	2499.3	2519.3	2499.3	2526.0	2536.1	2536.1	2506.0	2499.3	2496.0
47.5°	1418.2	1942.0	2372.5	2372.5	2362.6	2395.9	2412.5	2389.2	2359.2	2349.1	2349.1
50°	1414.8	1808.6	2199.0	2185.7	2232.4	2272.4	2255.8	2232.4	2209.0	2172.4	2172.4
52.5°	1284.7	1645.0	1975.5	2025.5	2098.9	2122.3	2095.5	2072.2	2032.1	2015.5	2002.2
55°	1191.3	1475.0	1771.9	1872.0	1948.7	1978.8	1928.7	1905.3	1845.3	1835.3	1828.6
57.5°	1171.3	1228.0	1585.0	1711.8	1805.3	1801.9	1771.9	1728.6	1678.5	1668.4	1665.2
60°	1074.4	887.6	1384.8	1535.0	1631.7	1621.8	1595.1	1555.0	1508.3	1501.6	1495.0
62.5°	974.4	644.1	1157.9	1328.0	1464.9	1461.5	1438.2	1378.1	1344.8	1328.0	1314.7
65°	827.5	540.6	824.2	1104.5	1301.4	1308.0	1258.0	1214.7	1177.9	1157.9	1154.6
67.5°	630.6	440.4	557.3	921.0	1144.5	1137.8	1074.4	1054.4	1007.8	997.7	977.7
70°	467.2	293.6	387.1	747.5	991.0	974.4	924.3	901.0	857.6	834.3	820.8
72.5°	387.1	236.9	283.7	580.7	834.3	814.2	770.9	744.1	707.5	687.4	674.0
75°	313.6	250.2	216.9	430.5	677.4	664.1	624.0	597.3	567.2	540.6	543.9
77.5°	230.2	233.6	173.5	317.0	537.3	517.3	493.9	460.5	447.2	420.4	420.4
80°	173.5	183.5	130.2	216.9	387.1	387.1	367.1	343.7	320.4	307.0	307.0
82.5°	116.7	116.7	96.7	136.9	263.7	253.6	240.3	233.6	220.3	213.6	213.6
85°	53.3	66.8	60.0	83.4	143.5	150.2	150.2	143.5	140.1	133.5	136.9
87.5°	16.7	30.1	36.7	46.7	73.5	76.7	80.1	80.1	80.1	83.4	83.4
90°	4.0	7.3	10.6	11.3	17.8	26.5	30.9	27.4	20.6	15.5	15.5
92.5°	16.3	43.9	71.6	78.5	110.3	152.7	173.9	152.4	109.4	77.2	74.1
95°	39.0	89.6	140.2	152.8	271.3	429.4	508.5	453.8	344.3	262.2	252.9
97.5°	67.4	112.0	156.7	167.8	365.5	629.1	760.9	726.3	657.1	605.2	587.5
100°	89.4	129.9	170.3	180.4	399.8	692.3	838.5	841.1	846.1	849.8	828.7
102.5°	108.2	145.9	183.6	193.1	415.5	712.2	860.5	904.6	992.7	1058.8	1040.7
105°	139.8	171.8	203.8	211.8	427.2	714.5	858.0	956.8	1154.5	1302.7	1292.9
107.5°	172.4	202.1	231.9	239.4	429.3	682.6	809.2	947.1	1222.7	1429.5	1431.9
110°	194.2	221.2	248.2	254.9	426.1	654.4	768.6	922.7	1230.8	1461.9	1472.1

TEST NUMBER: P934593

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	215.8	241.5	267.1	273.5	426.2	629.9	731.6	889.3	1204.7	1441.2	1456.8
115°	248.4	272.0	295.7	301.6	430.2	601.7	687.3	839.3	1143.1	1370.9	1392.4
117.5°	280.4	301.9	323.4	328.8	438.2	583.9	656.8	793.9	1068.1	1273.8	1297.7
120°	299.2	319.4	339.7	344.7	444.7	578.0	644.6	769.9	1020.4	1208.3	1231.5
122.5°	317.4	337.8	358.2	363.3	454.0	574.8	635.3	748.1	973.8	1143.0	1165.8
125°	345.5	364.0	382.7	387.3	466.6	572.3	625.1	721.0	912.6	1056.4	1077.5
127.5°	368.3	387.0	405.7	410.5	479.2	570.8	616.5	698.9	863.4	986.9	1004.6
130°	380.4	400.6	420.9	426.0	488.4	571.7	613.3	686.6	833.1	942.9	959.4
132.5°	393.0	413.2	433.5	438.6	495.9	572.3	610.5	676.1	807.2	905.5	920.2
135°	411.8	430.2	448.5	453.2	503.9	571.7	605.6	660.5	770.4	852.7	865.4
137.5°	430.9	449.1	467.4	471.9	516.2	575.2	604.8	651.3	744.1	813.7	824.1
140°	446.7	463.5	480.3	484.5	523.7	575.8	602.0	642.1	722.2	782.4	792.1
142.5°	458.9	474.4	489.9	493.8	529.9	577.9	602.0	637.2	707.7	760.5	768.9
145°	477.6	491.1	504.7	508.1	538.1	578.0	597.9	626.7	684.4	727.6	733.9
147.5°	496.3	509.5	522.7	525.9	549.9	581.9	597.9	620.6	665.8	699.9	705.1
150°	508.5	520.4	532.3	535.3	556.2	584.0	597.9	617.0	655.4	684.1	688.3
152.5°	521.1	530.2	539.1	541.4	560.2	585.4	597.9	614.3	646.9	671.5	674.7
155°	539.7	546.4	553.1	554.8	569.2	588.3	597.9	610.9	636.9	656.4	658.5
157.5°	553.5	560.0	566.6	568.2	578.1	591.3	597.9	608.0	628.2	643.4	644.8
160°	562.9	568.0	573.1	574.3	582.2	592.7	597.9	606.6	623.8	636.9	637.7
162.5°	572.3	576.1	579.9	580.9	586.6	594.2	597.9	605.2	619.9	630.8	631.6
165°	582.4	585.9	589.2	590.1	592.7	596.1	597.9	603.1	613.6	621.5	622.4
167.5°	591.8	593.4	595.1	595.4	597.6	600.5	602.0	605.4	612.3	617.4	617.8
170°	597.9	599.5	601.2	601.6	601.7	601.9	602.0	605.4	612.3	617.4	617.4
172.5°	601.2	601.6	601.9	602.0	602.0	602.0	602.0	604.7	610.1	614.2	613.9
175°	605.6	605.6	605.6	605.6	604.4	602.7	602.0	603.6	607.1	609.6	609.6
177.5°	605.6	605.6	605.6	605.6	604.6	603.3	602.7	604.1	606.8	608.9	608.5
180°	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6

TEST NUMBER: P934593

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1
2.5°	3617.2	3607.2	3617.2	3610.5	3613.9	3603.8	3573.9	3563.8	3573.9	3583.8	3583.8
5°	3660.6	3653.9	3660.6	3660.6	3657.3	3650.6	3617.2	3610.5	3617.2	3620.5	3613.9
7.5°	3673.9	3663.9	3673.9	3667.2	3667.2	3660.6	3627.2	3620.5	3623.8	3633.9	3623.8
10°	3673.9	3663.9	3673.9	3670.6	3667.2	3660.6	3627.2	3613.9	3613.9	3623.8	3613.9
12.5°	3657.3	3650.6	3657.3	3650.6	3650.6	3643.9	3610.5	3597.2	3600.5	3603.8	3590.5
15°	3630.6	3620.5	3630.6	3623.8	3627.2	3617.2	3580.5	3567.2	3567.2	3573.9	3550.5
17.5°	3590.5	3577.1	3590.5	3587.2	3583.8	3577.1	3543.8	3530.5	3527.1	3530.5	3513.7
20°	3543.8	3533.7	3543.8	3540.4	3540.4	3527.1	3493.7	3477.0	3477.0	3477.0	3460.4
22.5°	3470.3	3460.4	3470.3	3477.0	3477.0	3473.7	3443.7	3420.3	3413.6	3413.6	3393.6
25°	3386.9	3377.0	3386.9	3386.9	3383.7	3386.9	3377.0	3363.6	3353.6	3343.5	3323.5
27.5°	3306.8	3300.1	3306.8	3300.1	3306.8	3296.9	3293.5	3290.2	3276.9	3266.8	3240.1
30°	3226.8	3220.1	3226.8	3220.1	3213.5	3206.8	3190.1	3183.4	3196.7	3190.1	3146.7
32.5°	3126.7	3120.0	3126.7	3126.7	3120.0	3120.0	3093.3	3083.3	3086.7	3106.7	3066.7
35°	3023.3	3013.2	3023.3	3019.9	3023.3	3013.2	2996.6	2993.2	2979.9	3003.2	2973.2
37.5°	2903.1	2893.1	2903.1	2903.1	2903.1	2909.8	2896.5	2886.4	2866.4	2896.5	2873.1
40°	2779.6	2766.3	2779.6	2776.3	2779.6	2786.3	2779.6	2772.9	2752.9	2776.3	2756.3
42.5°	2639.5	2636.2	2639.5	2642.8	2642.8	2656.2	2666.1	2652.8	2646.1	2629.5	2642.8
45°	2489.4	2482.6	2489.4	2496.0	2499.3	2506.0	2536.1	2536.1	2526.0	2499.3	2519.3
47.5°	2329.1	2312.5	2329.1	2349.1	2349.1	2359.2	2389.2	2412.5	2395.9	2362.6	2372.5
50°	2158.9	2162.3	2158.9	2172.4	2172.4	2209.0	2232.4	2255.8	2272.4	2232.4	2185.7
52.5°	1992.1	1988.8	1992.1	2002.2	2015.5	2032.1	2072.2	2095.5	2122.3	2098.9	2025.5
55°	1825.3	1832.0	1825.3	1828.6	1835.3	1845.3	1905.3	1928.7	1978.8	1948.7	1872.0
57.5°	1658.5	1648.4	1658.5	1665.2	1668.4	1678.5	1728.6	1771.9	1801.9	1805.3	1711.8
60°	1464.9	1451.6	1464.9	1495.0	1501.6	1508.3	1555.0	1595.1	1621.8	1631.7	1535.0
62.5°	1294.7	1271.3	1294.7	1314.7	1328.0	1344.8	1378.1	1438.2	1461.5	1464.9	1328.0
65°	1114.5	1104.5	1114.5	1154.6	1157.9	1177.9	1214.7	1258.0	1308.0	1301.4	1104.5
67.5°	951.0	951.0	951.0	977.7	997.7	1007.8	1054.4	1074.4	1137.8	1144.5	921.0
70°	800.8	797.5	800.8	820.8	834.3	857.6	901.0	924.3	974.4	991.0	747.5
72.5°	657.4	654.0	657.4	674.0	687.4	707.5	744.1	770.9	814.2	834.3	580.7
75°	530.6	523.9	530.6	543.9	540.6	567.2	597.3	624.0	664.1	677.4	430.5
77.5°	407.1	407.1	407.1	420.4	420.4	447.2	460.5	493.9	517.3	537.3	317.0
80°	303.7	300.3	303.7	307.0	307.0	320.4	343.7	367.1	387.1	387.1	216.9
82.5°	213.6	206.9	213.6	213.6	213.6	220.3	233.6	240.3	253.6	263.7	136.9
85°	133.5	133.5	133.5	136.9	133.5	140.1	143.5	150.2	150.2	143.5	83.4
87.5°	86.8	83.4	86.8	83.4	83.4	80.1	80.1	80.1	76.7	73.5	46.7
90°	15.5	15.5	15.5	15.5	15.5	20.6	27.4	30.9	26.5	17.8	11.3
92.5°	61.8	49.6	61.8	74.1	77.2	109.4	152.4	173.9	152.7	110.3	78.5
95°	215.6	178.5	215.6	252.9	262.2	344.3	453.8	508.5	429.4	271.3	152.8
97.5°	516.7	445.9	516.7	587.5	605.2	657.1	726.3	760.9	629.1	365.5	167.8
100°	744.4	660.0	744.4	828.7	849.8	846.1	841.1	838.5	692.3	399.8	180.4
102.5°	968.4	896.2	968.4	1040.7	1058.8	992.7	904.6	860.5	712.2	415.5	193.1
105°	1254.1	1215.2	1254.1	1292.9	1302.7	1154.5	956.8	858.0	714.5	427.2	211.8
107.5°	1441.2	1450.6	1441.2	1431.9	1429.5	1222.7	947.1	809.2	682.6	429.3	239.4
110°	1512.5	1553.0	1512.5	1472.1	1461.9	1230.8	922.7	768.6	654.4	426.1	254.9

TEST NUMBER: P934593

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1518.9	1581.1	1518.9	1456.8	1441.2	1204.7	889.3	731.6	629.9	426.2	273.5
115°	1478.6	1564.8	1478.6	1392.4	1370.9	1143.1	839.3	687.3	601.7	430.2	301.6
117.5°	1393.3	1488.9	1393.3	1297.7	1273.8	1068.1	793.9	656.8	583.9	438.2	328.8
120°	1324.4	1417.3	1324.4	1231.5	1208.3	1020.4	769.9	644.6	578.0	444.7	344.7
122.5°	1257.4	1349.0	1257.4	1165.8	1143.0	973.8	748.1	635.3	574.8	454.0	363.3
125°	1161.8	1246.2	1161.8	1077.5	1056.4	912.6	721.0	625.1	572.3	466.6	387.3
127.5°	1075.8	1147.0	1075.8	1004.6	986.9	863.4	698.9	616.5	570.8	479.2	410.5
130°	1025.1	1090.9	1025.1	959.4	942.9	833.1	686.6	613.3	571.7	488.4	426.0
132.5°	979.2	1038.1	979.2	920.2	905.5	807.2	676.1	610.5	572.3	495.9	438.6
135°	916.2	967.0	916.2	865.4	852.7	770.4	660.5	605.6	571.7	503.9	453.2
137.5°	865.7	907.2	865.7	824.1	813.7	744.1	651.3	604.8	575.2	516.2	471.9
140°	830.9	869.8	830.9	792.1	782.4	722.2	642.1	602.0	575.8	523.7	484.5
142.5°	802.2	835.6	802.2	768.9	760.5	707.7	637.2	602.0	577.9	529.9	493.8
145°	759.2	784.5	759.2	733.9	727.6	684.4	626.7	597.9	578.0	538.1	508.1
147.5°	726.1	747.1	726.1	705.1	699.9	665.8	620.6	597.9	581.9	549.9	525.9
150°	705.3	722.2	705.3	688.3	684.1	655.4	617.0	597.9	584.0	556.2	535.3
152.5°	687.5	700.4	687.5	674.7	671.5	646.9	614.3	597.9	585.4	560.2	541.4
155°	667.0	675.5	667.0	658.5	656.4	636.9	610.9	597.9	588.3	569.2	554.8
157.5°	650.9	656.8	650.9	644.8	643.4	628.2	608.0	597.9	591.3	578.1	568.2
160°	641.2	644.6	641.2	637.7	636.9	623.8	606.6	597.9	592.7	582.2	574.3
162.5°	634.9	638.1	634.9	631.6	630.8	619.9	605.2	597.9	594.2	586.6	580.9
165°	625.7	629.2	625.7	622.4	621.5	613.6	603.1	597.9	596.1	592.7	590.1
167.5°	619.2	620.7	619.2	617.8	617.4	612.3	605.4	602.0	600.5	597.6	595.4
170°	617.4	617.4	617.4	617.4	617.4	612.3	605.4	602.0	601.9	601.7	601.6
172.5°	612.6	611.3	612.6	613.9	614.2	610.1	604.7	602.0	602.0	602.0	602.0
175°	609.6	609.6	609.6	609.6	609.6	607.1	603.6	602.0	602.7	604.4	605.6
177.5°	607.1	605.6	607.1	608.5	608.9	606.8	604.1	602.7	603.3	604.6	605.6
180°	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6

TEST NUMBER: P934593

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1
2.5°	3577.1	3557.1	3557.1	3523.8	3510.5	3500.4	3483.7	3433.6	3420.3	3406.9	3427.0
5°	3607.2	3570.5	3543.8	3483.7	3433.6	3413.6	3350.2	3230.1	3150.1	3089.9	3056.6
7.5°	3613.9	3567.2	3517.1	3423.7	3303.5	3250.2	3056.6	2836.3	2776.3	2722.9	2689.5
10°	3607.2	3553.8	3483.7	3343.5	3060.0	2966.5	2772.9	2629.5	2592.8	2582.7	2592.8
12.5°	3583.8	3533.7	3437.0	3203.4	2806.4	2743.0	2629.5	2546.0	2539.3	2556.1	2646.1
15°	3543.8	3497.0	3383.7	3016.6	2666.1	2619.5	2539.3	2509.4	2546.0	2662.9	2933.2
17.5°	3503.8	3450.3	3310.2	2833.1	2559.4	2526.0	2469.3	2529.4	2736.2	2893.1	2983.1
20°	3450.3	3386.9	3226.8	2699.6	2482.6	2452.6	2426.0	2696.2	2853.1	2909.8	2959.9
22.5°	3386.9	3320.3	3113.3	2606.1	2402.6	2379.2	2395.9	2789.7	2853.1	2893.1	2936.5
25°	3303.5	3246.8	2979.9	2532.7	2339.2	2312.5	2375.9	2779.6	2816.3	2826.4	2913.1
27.5°	3226.8	3153.3	2839.7	2466.0	2262.4	2252.4	2392.5	2736.2	2763.0	2772.9	2866.4
30°	3133.3	3023.3	2682.9	2395.9	2182.3	2179.0	2395.9	2682.9	2676.2	2702.9	2796.3
32.5°	3036.6	2829.7	2506.0	2309.1	2105.6	2102.3	2372.5	2602.7	2596.1	2632.8	2702.9
35°	2946.5	2679.6	2265.7	2209.0	2008.8	2012.1	2315.8	2509.4	2512.7	2546.0	2589.4
37.5°	2853.1	2549.4	2002.2	2098.9	1915.4	1915.4	2239.0	2422.6	2415.9	2426.0	2486.0
40°	2743.0	2345.8	1768.6	1955.4	1828.6	1818.6	2145.6	2329.1	2305.8	2302.5	2385.9
42.5°	2626.1	2122.3	1595.1	1765.2	1728.6	1715.1	2032.1	2215.7	2172.4	2182.3	2289.1
45°	2499.3	2062.2	1461.5	1491.6	1625.0	1615.1	1908.7	2085.6	2055.5	2082.2	2192.4
47.5°	2372.5	1942.0	1418.2	1238.0	1515.0	1511.6	1771.9	1958.8	1942.0	1968.7	2085.6
50°	2199.0	1808.6	1414.8	1061.1	1391.4	1404.9	1608.4	1835.3	1835.3	1858.6	1982.2
52.5°	1975.5	1645.0	1284.7	961.1	1248.0	1288.0	1464.9	1728.6	1735.2	1758.5	1868.7
55°	1771.9	1475.0	1191.3	884.2	1077.8	1164.6	1324.8	1618.4	1631.7	1655.1	1755.2
57.5°	1585.0	1228.0	1171.3	794.2	921.0	1004.4	1201.2	1511.6	1518.2	1538.4	1635.1
60°	1384.8	887.6	1074.4	697.4	784.2	847.6	1087.9	1384.8	1408.2	1421.5	1504.9
62.5°	1157.9	644.1	974.4	630.6	717.4	730.8	994.4	1264.6	1294.7	1304.8	1354.8
65°	824.2	540.6	827.5	574.0	647.3	650.7	894.3	1141.2	1167.9	1184.6	1221.3
67.5°	557.3	440.4	630.6	520.5	594.0	597.3	797.5	997.7	1034.4	1047.8	1071.2
70°	387.1	293.6	467.2	463.8	533.9	540.6	694.0	867.6	901.0	911.0	924.3
72.5°	283.7	236.9	387.1	417.1	470.5	477.2	587.3	720.8	754.1	764.2	770.9
75°	216.9	250.2	313.6	363.7	400.4	403.8	480.5	587.3	610.6	617.3	620.7
77.5°	173.5	233.6	230.2	293.6	327.1	320.4	377.0	453.9	473.9	473.9	473.9
80°	130.2	183.5	173.5	210.2	240.3	233.6	270.3	323.7	330.3	337.0	333.7
82.5°	96.7	116.7	116.7	133.5	160.1	153.5	180.2	210.2	210.2	210.2	216.9
85°	60.0	66.8	53.3	70.1	90.1	86.8	100.1	113.5	116.7	116.7	110.1
87.5°	36.7	30.1	16.7	26.7	40.0	40.0	46.7	50.1	46.7	46.7	46.7
90°	10.6	7.3	4.0	7.3	10.6	11.3	17.8	26.5	30.9	27.4	20.6
92.5°	71.6	43.9	16.3	43.9	71.6	78.5	110.3	152.7	173.9	152.4	109.4
95°	140.2	89.6	39.0	89.6	140.2	152.8	271.3	429.4	508.5	453.8	344.3
97.5°	156.7	112.0	67.4	112.0	156.7	167.8	365.5	629.1	760.9	726.3	657.1
100°	170.3	129.9	89.4	129.9	170.3	180.4	399.8	692.3	838.5	841.1	846.1
102.5°	183.6	145.9	108.2	145.9	183.6	193.1	415.5	712.2	860.5	904.6	992.7
105°	203.8	171.8	139.8	171.8	203.8	211.8	427.2	714.5	858.0	956.8	1154.5
107.5°	231.9	202.1	172.4	202.1	231.9	239.4	429.3	682.6	809.2	947.1	1222.7
110°	248.2	221.2	194.2	221.2	248.2	254.9	426.1	654.4	768.6	922.7	1230.8

TEST NUMBER: P934593

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	267.1	241.5	215.8	241.5	267.1	273.5	426.2	629.9	731.6	889.3	1204.7
115°	295.7	272.0	248.4	272.0	295.7	301.6	430.2	601.7	687.3	839.3	1143.1
117.5°	323.4	301.9	280.4	301.9	323.4	328.8	438.2	583.9	656.8	793.9	1068.1
120°	339.7	319.4	299.2	319.4	339.7	344.7	444.7	578.0	644.6	769.9	1020.4
122.5°	358.2	337.8	317.4	337.8	358.2	363.3	454.0	574.8	635.3	748.1	973.8
125°	382.7	364.0	345.5	364.0	382.7	387.3	466.6	572.3	625.1	721.0	912.6
127.5°	405.7	387.0	368.3	387.0	405.7	410.5	479.2	570.8	616.5	698.9	863.4
130°	420.9	400.6	380.4	400.6	420.9	426.0	488.4	571.7	613.3	686.6	833.1
132.5°	433.5	413.2	393.0	413.2	433.5	438.6	495.9	572.3	610.5	676.1	807.2
135°	448.5	430.2	411.8	430.2	448.5	453.2	503.9	571.7	605.6	660.5	770.4
137.5°	467.4	449.1	430.9	449.1	467.4	471.9	516.2	575.2	604.8	651.3	744.1
140°	480.3	463.5	446.7	463.5	480.3	484.5	523.7	575.8	602.0	642.1	722.2
142.5°	489.9	474.4	458.9	474.4	489.9	493.8	529.9	577.9	602.0	637.2	707.7
145°	504.7	491.1	477.6	491.1	504.7	508.1	538.1	578.0	597.9	626.7	684.4
147.5°	522.7	509.5	496.3	509.5	522.7	525.9	549.9	581.9	597.9	620.6	665.8
150°	532.3	520.4	508.5	520.4	532.3	535.3	556.2	584.0	597.9	617.0	655.4
152.5°	539.1	530.2	521.1	530.2	539.1	541.4	560.2	585.4	597.9	614.3	646.9
155°	553.1	546.4	539.7	546.4	553.1	554.8	569.2	588.3	597.9	610.9	636.9
157.5°	566.6	560.0	553.5	560.0	566.6	568.2	578.1	591.3	597.9	608.0	628.2
160°	573.1	568.0	562.9	568.0	573.1	574.3	582.2	592.7	597.9	606.6	623.8
162.5°	579.9	576.1	572.3	576.1	579.9	580.9	586.6	594.2	597.9	605.2	619.9
165°	589.2	585.9	582.4	585.9	589.2	590.1	592.7	596.1	597.9	603.1	613.6
167.5°	595.1	593.4	591.8	593.4	595.1	595.4	597.6	600.5	602.0	605.4	612.3
170°	601.2	599.5	597.9	599.5	601.2	601.6	601.7	601.9	602.0	605.4	612.3
172.5°	601.9	601.6	601.2	601.6	601.9	602.0	602.0	602.0	602.0	604.7	610.1
175°	605.6	605.6	605.6	605.6	605.6	605.6	604.4	602.7	602.0	603.6	607.1
177.5°	605.6	605.6	605.6	605.6	605.6	605.6	604.6	603.3	602.7	604.1	606.8
180°	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6

TEST NUMBER: P934593

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1
2.5°	3403.7	3393.6	3406.9	3370.2	3406.9	3393.6	3403.7	3427.0	3406.9	3420.3	3433.6
5°	2986.5	2969.8	2916.5	2873.1	2916.5	2969.8	2986.5	3056.6	3089.9	3150.1	3230.1
7.5°	2669.5	2656.2	2642.8	2616.2	2642.8	2656.2	2669.5	2689.5	2722.9	2776.3	2836.3
10°	2599.5	2602.7	2622.8	2619.5	2622.8	2602.7	2599.5	2592.8	2582.7	2592.8	2629.5
12.5°	2779.6	2809.7	2919.7	2913.1	2919.7	2809.7	2779.6	2646.1	2556.1	2539.3	2546.0
15°	2986.5	2996.6	3019.9	3023.3	3019.9	2996.6	2986.5	2933.2	2662.9	2546.0	2509.4
17.5°	3006.5	3009.9	3026.5	3026.5	3026.5	3009.9	3006.5	2983.1	2893.1	2736.2	2529.4
20°	2989.8	2996.6	3029.9	3036.6	3029.9	2996.6	2989.8	2959.9	2909.8	2853.1	2696.2
22.5°	2983.1	2996.6	3023.3	3019.9	3023.3	2996.6	2983.1	2936.5	2893.1	2853.1	2789.7
25°	2949.8	2949.8	2953.2	2956.5	2953.2	2949.8	2949.8	2913.1	2826.4	2816.3	2779.6
27.5°	2879.7	2886.4	2906.4	2903.1	2906.4	2886.4	2879.7	2866.4	2772.9	2763.0	2736.2
30°	2816.3	2809.7	2792.9	2779.6	2792.9	2809.7	2816.3	2796.3	2702.9	2676.2	2682.9
32.5°	2709.5	2692.9	2676.2	2666.1	2676.2	2692.9	2709.5	2702.9	2632.8	2596.1	2602.7
35°	2582.7	2586.1	2582.7	2572.8	2582.7	2586.1	2582.7	2589.4	2546.0	2512.7	2509.4
37.5°	2492.7	2499.3	2496.0	2482.6	2496.0	2499.3	2492.7	2486.0	2426.0	2415.9	2422.6
40°	2399.2	2402.6	2399.2	2389.2	2399.2	2402.6	2399.2	2385.9	2302.5	2305.8	2329.1
42.5°	2309.1	2305.8	2295.8	2289.1	2295.8	2305.8	2309.1	2289.1	2182.3	2172.4	2215.7
45°	2205.7	2209.0	2189.0	2179.0	2189.0	2209.0	2205.7	2192.4	2082.2	2055.5	2085.6
47.5°	2102.3	2102.3	2085.6	2075.5	2085.6	2102.3	2102.3	2085.6	1968.7	1942.0	1958.8
50°	1992.1	1988.8	1965.4	1962.1	1965.4	1988.8	1992.1	1982.2	1858.6	1835.3	1835.3
52.5°	1865.3	1865.3	1868.7	1875.4	1868.7	1865.3	1865.3	1868.7	1758.5	1735.2	1728.6
55°	1755.2	1758.5	1781.9	1788.6	1781.9	1758.5	1755.2	1755.2	1655.1	1631.7	1618.4
57.5°	1641.8	1641.8	1658.5	1658.5	1658.5	1641.8	1641.8	1635.1	1538.4	1518.2	1511.6
60°	1511.6	1518.2	1531.7	1528.3	1531.7	1518.2	1511.6	1504.9	1421.5	1408.2	1384.8
62.5°	1374.8	1381.5	1384.8	1378.1	1384.8	1381.5	1374.8	1354.8	1304.8	1294.7	1264.6
65°	1231.3	1238.0	1241.4	1234.7	1241.4	1238.0	1231.3	1221.3	1184.6	1167.9	1141.2
67.5°	1084.5	1081.1	1077.8	1091.2	1077.8	1081.1	1084.5	1071.2	1047.8	1034.4	997.7
70°	934.3	934.3	931.0	937.7	931.0	934.3	934.3	924.3	911.0	901.0	867.6
72.5°	774.2	770.9	784.2	774.2	784.2	770.9	774.2	770.9	764.2	754.1	720.8
75°	617.3	624.0	617.3	627.3	617.3	624.0	617.3	620.7	617.3	610.6	587.3
77.5°	470.5	477.2	470.5	470.5	470.5	477.2	470.5	473.9	473.9	473.9	453.9
80°	333.7	330.3	330.3	327.1	330.3	330.3	333.7	333.7	337.0	330.3	323.7
82.5°	213.6	210.2	210.2	216.9	210.2	210.2	213.6	216.9	210.2	210.2	210.2
85°	116.7	120.1	113.5	113.5	113.5	120.1	116.7	110.1	116.7	116.7	113.5
87.5°	43.4	40.0	40.0	40.0	40.0	40.0	43.4	46.7	46.7	46.7	50.1
90°	15.5	15.5	15.5	15.5	15.5	15.5	15.5	20.6	27.4	30.9	26.5
92.5°	77.2	74.1	61.8	49.6	61.8	74.1	77.2	109.4	152.4	173.9	152.7
95°	262.2	252.9	215.6	178.5	215.6	252.9	262.2	344.3	453.8	508.5	429.4
97.5°	605.2	587.5	516.7	445.9	516.7	587.5	605.2	657.1	726.3	760.9	629.1
100°	849.8	828.7	744.4	660.0	744.4	828.7	849.8	846.1	841.1	838.5	692.3
102.5°	1058.8	1040.7	968.4	896.2	968.4	1040.7	1058.8	992.7	904.6	860.5	712.2
105°	1302.7	1292.9	1254.1	1215.2	1254.1	1292.9	1302.7	1154.5	956.8	858.0	714.5
107.5°	1429.5	1431.9	1441.2	1450.6	1441.2	1431.9	1429.5	1222.7	947.1	809.2	682.6
110°	1461.9	1472.1	1512.5	1553.0	1512.5	1472.1	1461.9	1230.8	922.7	768.6	654.4

TEST NUMBER: P934593

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1441.2	1456.8	1518.9	1581.1	1518.9	1456.8	1441.2	1204.7	889.3	731.6	629.9
115°	1370.9	1392.4	1478.6	1564.8	1478.6	1392.4	1370.9	1143.1	839.3	687.3	601.7
117.5°	1273.8	1297.7	1393.3	1488.9	1393.3	1297.7	1273.8	1068.1	793.9	656.8	583.9
120°	1208.3	1231.5	1324.4	1417.3	1324.4	1231.5	1208.3	1020.4	769.9	644.6	578.0
122.5°	1143.0	1165.8	1257.4	1349.0	1257.4	1165.8	1143.0	973.8	748.1	635.3	574.8
125°	1056.4	1077.5	1161.8	1246.2	1161.8	1077.5	1056.4	912.6	721.0	625.1	572.3
127.5°	986.9	1004.6	1075.8	1147.0	1075.8	1004.6	986.9	863.4	698.9	616.5	570.8
130°	942.9	959.4	1025.1	1090.9	1025.1	959.4	942.9	833.1	686.6	613.3	571.7
132.5°	905.5	920.2	979.2	1038.1	979.2	920.2	905.5	807.2	676.1	610.5	572.3
135°	852.7	865.4	916.2	967.0	916.2	865.4	852.7	770.4	660.5	605.6	571.7
137.5°	813.7	824.1	865.7	907.2	865.7	824.1	813.7	744.1	651.3	604.8	575.2
140°	782.4	792.1	830.9	869.8	830.9	792.1	782.4	722.2	642.1	602.0	575.8
142.5°	760.5	768.9	802.2	835.6	802.2	768.9	760.5	707.7	637.2	602.0	577.9
145°	727.6	733.9	759.2	784.5	759.2	733.9	727.6	684.4	626.7	597.9	578.0
147.5°	699.9	705.1	726.1	747.1	726.1	705.1	699.9	665.8	620.6	597.9	581.9
150°	684.1	688.3	705.3	722.2	705.3	688.3	684.1	655.4	617.0	597.9	584.0
152.5°	671.5	674.7	687.5	700.4	687.5	674.7	671.5	646.9	614.3	597.9	585.4
155°	656.4	658.5	667.0	675.5	667.0	658.5	656.4	636.9	610.9	597.9	588.3
157.5°	643.4	644.8	650.9	656.8	650.9	644.8	643.4	628.2	608.0	597.9	591.3
160°	636.9	637.7	641.2	644.6	641.2	637.7	636.9	623.8	606.6	597.9	592.7
162.5°	630.8	631.6	634.9	638.1	634.9	631.6	630.8	619.9	605.2	597.9	594.2
165°	621.5	622.4	625.7	629.2	625.7	622.4	621.5	613.6	603.1	597.9	596.1
167.5°	617.4	617.8	619.2	620.7	619.2	617.8	617.4	612.3	605.4	602.0	600.5
170°	617.4	617.4	617.4	617.4	617.4	617.4	617.4	612.3	605.4	602.0	601.9
172.5°	614.2	613.9	612.6	611.3	612.6	613.9	614.2	610.1	604.7	602.0	602.0
175°	609.6	609.6	609.6	609.6	609.6	609.6	609.6	607.1	603.6	602.0	602.7
177.5°	608.9	608.5	607.1	605.6	607.1	608.5	608.9	606.8	604.1	602.7	603.3
180°	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6

TEST NUMBER: P934593

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	3527.1	3527.1	3527.1	3527.1	3527.1
2.5°	3483.7	3500.4	3510.5	3523.8	3557.1
5°	3350.2	3413.6	3433.6	3483.7	3543.8
7.5°	3056.6	3250.2	3303.5	3423.7	3517.1
10°	2772.9	2966.5	3060.0	3343.5	3483.7
12.5°	2629.5	2743.0	2806.4	3203.4	3437.0
15°	2539.3	2619.5	2666.1	3016.6	3383.7
17.5°	2469.3	2526.0	2559.4	2833.1	3310.2
20°	2426.0	2452.6	2482.6	2699.6	3226.8
22.5°	2395.9	2379.2	2402.6	2606.1	3113.3
25°	2375.9	2312.5	2339.2	2532.7	2979.9
27.5°	2392.5	2252.4	2262.4	2466.0	2839.7
30°	2395.9	2179.0	2182.3	2395.9	2682.9
32.5°	2372.5	2102.3	2105.6	2309.1	2506.0
35°	2315.8	2012.1	2008.8	2209.0	2265.7
37.5°	2239.0	1915.4	1915.4	2098.9	2002.2
40°	2145.6	1818.6	1828.6	1955.4	1768.6
42.5°	2032.1	1715.1	1728.6	1765.2	1595.1
45°	1908.7	1615.1	1625.0	1491.6	1461.5
47.5°	1771.9	1511.6	1515.0	1238.0	1418.2
50°	1608.4	1404.9	1391.4	1061.1	1414.8
52.5°	1464.9	1288.0	1248.0	961.1	1284.7
55°	1324.8	1164.6	1077.8	884.2	1191.3
57.5°	1201.2	1004.4	921.0	794.2	1171.3
60°	1087.9	847.6	784.2	697.4	1074.4
62.5°	994.4	730.8	717.4	630.6	974.4
65°	894.3	650.7	647.3	574.0	827.5
67.5°	797.5	597.3	594.0	520.5	630.6
70°	694.0	540.6	533.9	463.8	467.2
72.5°	587.3	477.2	470.5	417.1	387.1
75°	480.5	403.8	400.4	363.7	313.6
77.5°	377.0	320.4	327.1	293.6	230.2
80°	270.3	233.6	240.3	210.2	173.5
82.5°	180.2	153.5	160.1	133.5	116.7
85°	100.1	86.8	90.1	70.1	53.3
87.5°	46.7	40.0	40.0	26.7	16.7
90°	17.8	11.3	10.6	7.3	4.0
92.5°	110.3	78.5	71.6	43.9	16.3
95°	271.3	152.8	140.2	89.6	39.0
97.5°	365.5	167.8	156.7	112.0	67.4
100°	399.8	180.4	170.3	129.9	89.4
102.5°	415.5	193.1	183.6	145.9	108.2
105°	427.2	211.8	203.8	171.8	139.8
107.5°	429.3	239.4	231.9	202.1	172.4
110°	426.1	254.9	248.2	221.2	194.2

TEST NUMBER: P934593

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	426.2	273.5	267.1	241.5	215.8
115°	430.2	301.6	295.7	272.0	248.4
117.5°	438.2	328.8	323.4	301.9	280.4
120°	444.7	344.7	339.7	319.4	299.2
122.5°	454.0	363.3	358.2	337.8	317.4
125°	466.6	387.3	382.7	364.0	345.5
127.5°	479.2	410.5	405.7	387.0	368.3
130°	488.4	426.0	420.9	400.6	380.4
132.5°	495.9	438.6	433.5	413.2	393.0
135°	503.9	453.2	448.5	430.2	411.8
137.5°	516.2	471.9	467.4	449.1	430.9
140°	523.7	484.5	480.3	463.5	446.7
142.5°	529.9	493.8	489.9	474.4	458.9
145°	538.1	508.1	504.7	491.1	477.6
147.5°	549.9	525.9	522.7	509.5	496.3
150°	556.2	535.3	532.3	520.4	508.5
152.5°	560.2	541.4	539.1	530.2	521.1
155°	569.2	554.8	553.1	546.4	539.7
157.5°	578.1	568.2	566.6	560.0	553.5
160°	582.2	574.3	573.1	568.0	562.9
162.5°	586.6	580.9	579.9	576.1	572.3
165°	592.7	590.1	589.2	585.9	582.4
167.5°	597.6	595.4	595.1	593.4	591.8
170°	601.7	601.6	601.2	599.5	597.9
172.5°	602.0	602.0	601.9	601.6	601.2
175°	604.4	605.6	605.6	605.6	605.6
177.5°	604.6	605.6	605.6	605.6	605.6
180°	605.6	605.6	605.6	605.6	605.6

TEST NUMBER: P934593

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.19	17.26	16.95	18.05	19.00	19.02	20.10	19.79	20.89	21.84
	3H	16.68	17.64	17.46	18.44	19.42	20.39	21.35	21.17	22.15	23.13
	4H	16.88	17.79	17.67	18.59	19.59	20.84	21.75	21.64	22.56	23.55
	6H	17.01	17.85	17.82	18.66	19.67	21.14	21.98	21.95	22.79	23.80
	8H	17.02	17.82	17.83	18.65	19.66	21.22	22.02	22.04	22.85	23.87
	12H	16.99	17.76	17.82	18.58	19.62	21.27	22.03	22.09	22.86	23.90
4H	2H	17.25	18.16	18.05	18.96	19.96	19.46	20.37	20.26	21.17	22.17
	3H	18.29	19.05	19.10	19.89	20.90	20.99	21.74	21.80	22.58	23.60
	4H	18.58	19.27	19.40	20.11	21.15	21.52	22.21	22.35	23.05	24.09
	6H	18.71	19.31	19.56	20.17	21.22	21.90	22.50	22.75	23.36	24.41
	8H	18.73	19.28	19.57	20.14	21.20	22.02	22.57	22.86	23.43	24.49
	12H	18.70	19.20	19.57	20.08	21.15	22.08	22.59	22.95	23.46	24.53
8H	4H	19.05	19.61	19.90	20.46	21.52	21.67	22.22	22.51	23.08	24.14
	6H	19.32	19.78	20.19	20.68	21.74	22.11	22.57	22.99	23.47	24.53
	8H	19.36	19.77	20.25	20.67	21.74	22.27	22.68	23.15	23.57	24.65
	12H	19.36	19.72	20.25	20.60	21.73	22.38	22.74	23.27	23.62	24.75
12H	4H	19.07	19.57	19.93	20.45	21.51	21.64	22.14	22.51	23.02	24.08
	6H	19.38	19.79	20.27	20.69	21.76	22.11	22.52	23.00	23.42	24.49
	8H	19.46	19.82	20.35	20.71	21.83	22.28	22.65	23.17	23.53	24.66

END OF REPORT