

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934688

Luminaire Tested: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934688
REPORT IS A COMBINATION OF REPORTS P933707 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7149.5 lumens
Efficiency: N/A
Efficacy: 138.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 51.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934688

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P934688

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45			38
1	95	91	87	84	86	83	79	77	67	65	63	53	52	50	40	39	38			32
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32			27
3	79	70	63	57	71	64	57	52	52	47	44	41	38	35	31	29	27			23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	25	24			20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20			17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18			15
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	21	18	16			13
8	52	40	32	27	47	37	30	25	30	25	22	24	21	18	19	16	14			12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13			11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6486	6486	6486	6486
5°	6531	6547	6531	5148
10°	6486	6449	6486	4611
15°	6413	6309	6413	5268
20°	6277	6144	6277	5279
25°	5999	5903	5999	5167
30°	5642	5702	5642	4922
35°	5028	5449	5028	4652
40°	4187	5150	4187	4448
45°	3738	4800	3738	4214
50°	3968	4384	3968	3978
55°	3730	3936	3730	3842
60°	3841	3342	3841	3519
65°	3477	2763	3477	3088
70°	2401	2201	2401	2589
75°	2099	1627	2099	1949
80°	1679	1075	1679	1172
85°	948	569	948	484

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 5734 cd/sqm

TEST NUMBER: P934688

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	1.3
10°-20°	268.7	3.8
20°-30°	415.4	5.8
30°-40°	495.9	6.9
40°-50°	498.8	7.0
50°-60°	434.0	6.1
60°-70°	307.7	4.3
70°-80°	162.8	2.3
80°-90°	43.1	0.6
90°-100°	333.0	4.7
100°-110°	875.5	12.2
110°-120°	907.8	12.7
120°-130°	728.1	10.2
130°-140°	571.3	8.0
140°-150°	438.5	6.1
150°-160°	315.8	4.4
160°-170°	193.2	2.7
170°-180°	65.3	0.9
0°-30°	778.7	10.9
0°-40°	1274.6	17.8
0°-60°	2207.3	30.9
0°-90°	2721.0	38.1
90°-120°	2116.2	29.6
90°-150°	3854.2	53.9
90°-180°	4428.0	61.9
0°-180°	7149.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1048	1048	1048	1048	1048	
5°	1053	1086	1053	854	1053	100
15°	1006	1076	1006	899	1006	283
25°	886	1004	886	879	886	407
35°	674	896	674	765	674	417
45°	434	738	434	648	434	348
55°	354	545	354	532	354	325
65°	246	328	246	367	246	235
75°	93	156	93	186	93	98
85°	16	40	16	34	16	21
90°	4	18	4	18	4	4
95°	44	201	44	201	44	49
105°	158	1371	158	1371	158	167
115°	280	1765	280	1765	280	277
125°	390	1406	390	1406	390	346
135°	464	1091	464	1091	464	359
145°	539	885	539	885	539	338
155°	609	762	609	762	609	280
165°	657	710	657	710	657	185
175°	683	688	683	688	683	65
180°	683	683	683	683	683	

TEST NUMBER: P934688

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4
2.5°	1057.4	1057.4	1063.3	1065.3	1065.3	1062.3	1059.4	1062.3	1071.3	1074.2	1073.3
5°	1053.3	1061.3	1072.3	1074.2	1076.2	1075.2	1073.3	1075.2	1085.1	1087.2	1088.1
7.5°	1045.5	1060.3	1074.2	1077.2	1080.2	1077.2	1076.2	1078.2	1088.1	1090.1	1090.1
10°	1035.5	1056.4	1072.3	1074.2	1077.2	1074.2	1074.2	1078.2	1088.1	1090.1	1091.1
12.5°	1021.7	1050.4	1065.3	1067.2	1071.3	1070.3	1069.2	1073.3	1083.1	1085.1	1085.1
15°	1005.8	1039.5	1053.3	1055.4	1062.3	1060.3	1060.3	1064.3	1075.2	1078.2	1077.2
17.5°	983.9	1025.6	1041.5	1044.5	1049.4	1048.4	1049.4	1053.3	1063.3	1065.3	1066.3
20°	959.2	1006.8	1025.6	1028.6	1033.5	1033.5	1033.5	1038.6	1048.4	1052.4	1052.4
22.5°	925.5	986.9	1006.8	1008.8	1014.7	1014.7	1016.7	1023.7	1032.5	1033.5	1033.5
25°	885.7	965.1	982.0	988.0	993.9	996.8	999.8	1003.8	1006.8	1005.8	1006.8
27.5°	844.1	937.3	959.2	963.1	971.1	974.1	978.0	979.0	980.0	982.9	981.0
30°	797.5	898.6	931.4	935.3	948.2	950.2	946.3	948.2	953.2	955.2	957.2
32.5°	744.9	841.2	902.6	911.6	923.5	917.5	916.5	919.4	927.4	927.4	929.4
35°	673.5	796.5	875.9	883.8	892.7	885.7	889.8	890.8	895.7	898.6	897.7
37.5°	595.1	757.8	848.1	854.0	861.0	852.0	858.0	861.0	864.9	862.9	862.9
40°	525.7	697.3	815.3	819.3	825.3	818.3	824.3	826.3	828.2	826.3	825.3
42.5°	474.2	630.8	780.6	785.5	781.6	786.5	788.6	792.5	789.6	785.5	785.5
45°	434.4	613.0	743.0	748.9	743.0	750.8	753.8	753.8	744.9	743.0	742.0
47.5°	421.5	577.3	705.3	705.3	702.2	712.2	717.1	710.2	701.2	698.3	698.3
50°	420.5	537.6	653.6	649.7	663.6	675.5	670.5	663.6	656.7	645.7	645.7
52.5°	381.9	489.0	587.2	602.1	623.9	630.8	623.0	616.0	604.0	599.1	595.1
55°	354.1	438.4	526.7	556.5	579.3	588.1	573.4	566.4	548.5	545.6	543.6
57.5°	348.2	365.0	471.1	508.9	536.6	535.6	526.7	513.8	498.9	496.0	495.0
60°	319.4	263.9	411.7	456.3	485.0	482.1	474.2	462.2	448.3	446.4	444.4
62.5°	289.6	191.5	344.2	394.8	435.4	434.4	427.5	409.7	399.7	394.8	390.9
65°	246.0	160.7	245.0	328.3	386.8	388.8	374.0	361.1	350.1	344.2	343.2
67.5°	187.4	130.9	165.6	273.8	340.3	338.2	319.4	313.4	299.5	296.6	290.7
70°	138.8	87.3	115.1	222.1	294.6	289.6	274.8	267.8	254.9	248.0	244.0
72.5°	115.1	70.4	84.3	172.6	248.0	242.1	229.1	221.2	210.3	204.3	200.4
75°	93.3	74.3	64.5	128.0	201.3	197.4	185.5	177.6	168.6	160.7	161.7
77.5°	68.4	69.4	51.6	94.3	159.7	153.7	146.8	136.9	132.9	125.0	125.0
80°	51.6	54.5	38.7	64.5	115.1	115.1	109.2	102.1	95.2	91.3	91.3
82.5°	34.7	34.7	28.8	40.6	78.4	75.4	71.4	69.4	65.5	63.5	63.5
85°	15.9	19.8	17.8	24.7	42.7	44.7	44.7	42.7	41.7	39.6	40.6
87.5°	4.9	9.0	10.9	13.9	21.8	22.8	23.8	23.8	23.8	24.7	24.7
90°	4.5	8.2	11.9	12.8	20.1	29.9	34.8	31.0	23.3	17.5	17.5
92.5°	18.3	49.5	80.7	88.4	124.3	172.3	196.2	172.0	123.4	87.1	83.6
95°	44.0	101.1	158.1	172.4	306.1	484.4	573.6	511.8	388.3	295.7	285.2
97.5°	76.1	126.4	176.7	189.3	412.3	709.6	858.3	819.3	741.3	682.7	662.7
100°	100.9	146.5	192.2	203.6	451.0	780.9	945.9	948.7	954.4	958.7	934.9
102.5°	122.0	164.6	207.2	217.8	468.7	803.3	970.6	1020.3	1119.8	1194.3	1173.9
105°	157.8	193.8	229.9	238.9	481.9	805.9	967.9	1079.3	1302.2	1469.4	1458.5
107.5°	194.4	228.1	261.7	270.1	484.3	770.0	912.8	1068.3	1379.3	1612.5	1615.2
110°	219.2	249.6	279.8	287.4	480.6	738.2	867.0	1040.8	1388.5	1649.2	1660.6

TEST NUMBER: P934688

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	243.4	272.3	301.3	308.5	480.8	710.4	825.3	1003.2	1358.9	1625.7	1643.3
115°	280.1	306.8	333.5	340.2	485.2	678.6	775.3	946.7	1289.4	1546.4	1570.7
117.5°	316.3	340.6	364.8	370.9	494.3	658.6	740.9	895.6	1204.9	1436.9	1463.8
120°	337.4	360.3	383.1	388.8	501.6	651.9	727.2	868.5	1151.1	1363.0	1389.3
122.5°	358.1	381.1	404.2	409.9	512.1	648.5	716.6	843.8	1098.3	1289.2	1315.0
125°	389.7	410.7	431.7	436.9	526.3	645.5	705.2	813.3	1029.5	1191.6	1215.3
127.5°	415.4	436.6	457.7	463.0	540.5	643.9	695.5	788.3	974.0	1113.2	1133.3
130°	429.1	452.0	474.8	480.5	551.0	644.9	691.9	774.5	939.8	1063.7	1082.2
132.5°	443.3	466.2	489.0	494.7	559.4	645.5	688.6	762.6	910.6	1021.5	1038.1
135°	464.4	485.2	506.0	511.2	568.5	644.9	683.1	745.0	869.0	961.8	976.1
137.5°	486.0	506.5	527.1	532.2	582.2	648.9	682.2	734.6	839.3	917.9	929.6
140°	503.8	522.8	541.8	546.5	590.7	649.6	679.0	724.2	814.7	882.6	893.5
142.5°	517.6	535.2	552.8	557.1	597.7	651.8	679.0	718.7	798.2	857.8	867.3
145°	538.8	554.0	569.2	573.1	606.9	651.9	674.4	707.0	771.9	820.6	827.7
147.5°	559.8	574.6	589.5	593.3	620.3	656.4	674.4	700.0	751.1	789.5	795.4
150°	573.6	587.0	600.5	603.8	627.4	658.7	674.4	696.0	739.2	771.6	776.5
152.5°	587.8	598.0	608.2	610.7	631.9	660.2	674.4	692.9	729.7	757.4	761.1
155°	608.9	616.3	623.9	625.8	642.0	663.6	674.4	689.1	718.5	740.5	742.9
157.5°	624.4	631.8	639.1	641.0	652.1	667.0	674.4	685.9	708.6	725.8	727.5
160°	635.0	640.7	646.4	647.8	656.7	668.5	674.4	684.2	703.7	718.4	719.4
162.5°	645.5	649.9	654.1	655.2	661.6	670.2	674.4	682.7	699.2	711.6	712.5
165°	657.0	660.9	664.8	665.7	668.6	672.5	674.4	680.3	692.2	701.0	702.0
167.5°	667.5	669.4	671.2	671.7	674.1	677.4	679.0	682.8	690.6	696.4	696.8
170°	674.4	676.3	678.1	678.6	678.7	678.9	679.0	682.8	690.6	696.4	696.4
172.5°	678.1	678.5	678.9	679.0	679.0	679.0	679.0	682.0	688.1	692.8	692.4
175°	683.1	683.1	683.1	683.1	681.7	679.8	679.0	680.9	684.8	687.7	687.7
177.5°	683.1	683.1	683.1	683.1	682.0	680.6	679.9	681.5	684.6	686.8	686.5
180°	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1

TEST NUMBER: P934688

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4
2.5°	1075.2	1072.3	1075.2	1073.3	1074.2	1071.3	1062.3	1059.4	1062.3	1065.3	1065.3
5°	1088.1	1086.1	1088.1	1088.1	1087.2	1085.1	1075.2	1073.3	1075.2	1076.2	1074.2
7.5°	1092.1	1089.1	1092.1	1090.1	1090.1	1088.1	1078.2	1076.2	1077.2	1080.2	1077.2
10°	1092.1	1089.1	1092.1	1091.1	1090.1	1088.1	1078.2	1074.2	1074.2	1077.2	1074.2
12.5°	1087.2	1085.1	1087.2	1085.1	1085.1	1083.1	1073.3	1069.2	1070.3	1071.3	1067.2
15°	1079.2	1076.2	1079.2	1077.2	1078.2	1075.2	1064.3	1060.3	1060.3	1062.3	1055.4
17.5°	1067.2	1063.3	1067.2	1066.3	1065.3	1063.3	1053.3	1049.4	1048.4	1049.4	1044.5
20°	1053.3	1050.4	1053.3	1052.4	1052.4	1048.4	1038.6	1033.5	1033.5	1033.5	1028.6
22.5°	1031.6	1028.6	1031.6	1033.5	1033.5	1032.5	1023.7	1016.7	1014.7	1014.7	1008.8
25°	1006.8	1003.8	1006.8	1006.8	1005.8	1006.8	1003.8	999.8	996.8	993.9	988.0
27.5°	982.9	981.0	982.9	981.0	982.9	980.0	979.0	978.0	974.1	971.1	963.1
30°	959.2	957.2	959.2	957.2	955.2	953.2	948.2	946.3	950.2	948.2	935.3
32.5°	929.4	927.4	929.4	929.4	927.4	927.4	919.4	916.5	917.5	923.5	911.6
35°	898.6	895.7	898.6	897.7	898.6	895.7	890.8	889.8	885.7	892.7	883.8
37.5°	862.9	860.0	862.9	862.9	862.9	864.9	861.0	858.0	852.0	861.0	854.0
40°	826.3	822.3	826.3	825.3	826.3	828.2	826.3	824.3	818.3	825.3	819.3
42.5°	784.6	783.6	784.6	785.5	785.5	789.6	792.5	788.6	786.5	781.6	785.5
45°	740.0	737.9	740.0	742.0	743.0	744.9	753.8	753.8	750.8	743.0	748.9
47.5°	692.4	687.3	692.4	698.3	698.3	701.2	710.2	717.1	712.2	702.2	705.3
50°	641.8	642.8	641.8	645.7	645.7	656.7	663.6	670.5	675.5	663.6	649.7
52.5°	592.2	591.2	592.2	595.1	599.1	604.0	616.0	623.0	630.8	623.9	602.1
55°	542.6	544.6	542.6	543.6	545.6	548.5	566.4	573.4	588.1	579.3	556.5
57.5°	493.0	490.0	493.0	495.0	496.0	498.9	513.8	526.7	535.6	536.6	508.9
60°	435.4	431.5	435.4	444.4	446.4	448.3	462.2	474.2	482.1	485.0	456.3
62.5°	384.8	377.9	384.8	390.9	394.8	399.7	409.7	427.5	434.4	435.4	394.8
65°	331.3	328.3	331.3	343.2	344.2	350.1	361.1	374.0	388.8	386.8	328.3
67.5°	282.7	282.7	282.7	290.7	296.6	299.5	313.4	319.4	338.2	340.3	273.8
70°	238.0	237.0	238.0	244.0	248.0	254.9	267.8	274.8	289.6	294.6	222.1
72.5°	195.4	194.4	195.4	200.4	204.3	210.3	221.2	229.1	242.1	248.0	172.6
75°	157.8	155.7	157.8	161.7	160.7	168.6	177.6	185.5	197.4	201.3	128.0
77.5°	121.0	121.0	121.0	125.0	125.0	132.9	136.9	146.8	153.7	159.7	94.3
80°	90.2	89.2	90.2	91.3	91.3	95.2	102.1	109.2	115.1	115.1	64.5
82.5°	63.5	61.5	63.5	63.5	63.5	65.5	69.4	71.4	75.4	78.4	40.6
85°	39.6	39.6	39.6	40.6	39.6	41.7	42.7	44.7	44.7	42.7	24.7
87.5°	25.8	24.7	25.8	24.7	24.7	23.8	23.8	23.8	22.8	21.8	13.9
90°	17.5	17.5	17.5	17.5	17.5	23.3	31.0	34.8	29.9	20.1	12.8
92.5°	69.7	55.9	69.7	83.6	87.1	123.4	172.0	196.2	172.3	124.3	88.4
95°	243.2	201.2	243.2	285.2	295.7	388.3	511.8	573.6	484.4	306.1	172.4
97.5°	582.8	503.0	582.8	662.7	682.7	741.3	819.3	858.3	709.6	412.3	189.3
100°	839.7	744.5	839.7	934.9	958.7	954.4	948.7	945.9	780.9	451.0	203.6
102.5°	1092.5	1010.9	1092.5	1173.9	1194.3	1119.8	1020.3	970.6	803.3	468.7	217.8
105°	1414.6	1370.8	1414.6	1458.5	1469.4	1302.2	1079.3	967.9	805.9	481.9	238.9
107.5°	1625.7	1636.3	1625.7	1615.2	1612.5	1379.3	1068.3	912.8	770.0	484.3	270.1
110°	1706.2	1751.8	1706.2	1660.6	1649.2	1388.5	1040.8	867.0	738.2	480.6	287.4

TEST NUMBER: P934688

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1713.4	1783.5	1713.4	1643.3	1625.7	1358.9	1003.2	825.3	710.4	480.8	308.5
115°	1667.9	1765.1	1667.9	1570.7	1546.4	1289.4	946.7	775.3	678.6	485.2	340.2
117.5°	1571.6	1679.4	1571.6	1463.8	1436.9	1204.9	895.6	740.9	658.6	494.3	370.9
120°	1494.0	1598.7	1494.0	1389.3	1363.0	1151.1	868.5	727.2	651.9	501.6	388.8
122.5°	1418.4	1521.7	1418.4	1315.0	1289.2	1098.3	843.8	716.6	648.5	512.1	409.9
125°	1310.6	1405.7	1310.6	1215.3	1191.6	1029.5	813.3	705.2	645.5	526.3	436.9
127.5°	1213.6	1293.8	1213.6	1133.3	1113.2	974.0	788.3	695.5	643.9	540.5	463.0
130°	1156.4	1230.5	1156.4	1082.2	1063.7	939.8	774.5	691.9	644.9	551.0	480.5
132.5°	1104.5	1171.0	1104.5	1038.1	1021.5	910.6	762.6	688.6	645.5	559.4	494.7
135°	1033.4	1090.7	1033.4	976.1	961.8	869.0	745.0	683.1	644.9	568.5	511.2
137.5°	976.4	1023.4	976.4	929.6	917.9	839.3	734.6	682.2	648.9	582.2	532.2
140°	937.4	981.2	937.4	893.5	882.6	814.7	724.2	679.0	649.6	590.7	546.5
142.5°	905.0	942.6	905.0	867.3	857.8	798.2	718.7	679.0	651.8	597.7	557.1
145°	856.3	884.8	856.3	827.7	820.6	771.9	707.0	674.4	651.9	606.9	573.1
147.5°	819.0	842.6	819.0	795.4	789.5	751.1	700.0	674.4	656.4	620.3	593.3
150°	795.6	814.7	795.6	776.5	771.6	739.2	696.0	674.4	658.7	627.4	603.8
152.5°	775.5	790.0	775.5	761.1	757.4	729.7	692.9	674.4	660.2	631.9	610.7
155°	752.4	762.0	752.4	742.9	740.5	718.5	689.1	674.4	663.6	642.0	625.8
157.5°	734.2	740.9	734.2	727.5	725.8	708.6	685.9	674.4	667.0	652.1	641.0
160°	723.2	727.2	723.2	719.4	718.4	703.7	684.2	674.4	668.5	656.7	647.8
162.5°	716.1	719.8	716.1	712.5	711.6	699.2	682.7	674.4	670.2	661.6	655.2
165°	705.9	709.7	705.9	702.0	701.0	692.2	680.3	674.4	672.5	668.6	665.7
167.5°	698.5	700.1	698.5	696.8	696.4	690.6	682.8	679.0	677.4	674.1	671.7
170°	696.4	696.4	696.4	696.4	696.4	690.6	682.8	679.0	678.9	678.7	678.6
172.5°	691.0	689.5	691.0	692.4	692.8	688.1	682.0	679.0	679.0	679.0	679.0
175°	687.7	687.7	687.7	687.7	687.7	684.8	680.9	679.0	679.8	681.7	683.1
177.5°	684.8	683.1	684.8	686.5	686.8	684.6	681.5	679.9	680.6	682.0	683.1
180°	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1

TEST NUMBER: P934688

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4
2.5°	1063.3	1057.4	1057.4	1047.4	1043.5	1040.5	1035.5	1020.7	1016.7	1012.7	1018.6
5°	1072.3	1061.3	1053.3	1035.5	1020.7	1014.7	995.9	960.2	936.3	918.5	908.6
7.5°	1074.2	1060.3	1045.5	1017.7	982.0	966.1	908.6	843.1	825.3	809.4	799.4
10°	1072.3	1056.4	1035.5	993.9	909.6	881.8	824.3	781.6	770.7	767.7	770.7
12.5°	1065.3	1050.4	1021.7	952.2	834.2	815.3	781.6	756.9	754.8	759.8	786.5
15°	1053.3	1039.5	1005.8	896.7	792.5	778.6	754.8	745.9	756.9	791.6	871.9
17.5°	1041.5	1025.6	983.9	842.1	760.8	750.8	734.0	751.8	813.4	860.0	886.7
20°	1025.6	1006.8	959.2	802.4	737.9	729.0	721.1	801.4	848.1	864.9	879.8
22.5°	1006.8	986.9	925.5	774.7	714.2	707.3	712.2	829.2	848.1	860.0	872.9
25°	982.0	965.1	885.7	752.8	695.3	687.3	706.3	826.3	837.1	840.2	865.9
27.5°	959.2	937.3	844.1	733.0	672.6	669.5	711.2	813.4	821.3	824.3	852.0
30°	931.4	898.6	797.5	712.2	648.7	647.7	712.2	797.5	795.5	803.4	831.2
32.5°	902.6	841.2	744.9	686.4	625.9	624.9	705.3	773.7	771.7	782.6	803.4
35°	875.9	796.5	673.5	656.7	597.1	598.1	688.3	745.9	746.9	756.9	769.7
37.5°	848.1	757.8	595.1	623.9	569.3	569.3	665.6	720.1	718.1	721.1	739.0
40°	815.3	697.3	525.7	581.2	543.6	540.6	637.7	692.4	685.4	684.4	709.2
42.5°	780.6	630.8	474.2	524.7	513.8	509.9	604.0	658.6	645.7	648.7	680.4
45°	743.0	613.0	434.4	443.4	483.0	480.1	567.3	619.9	611.0	618.9	651.6
47.5°	705.3	577.3	421.5	368.0	450.3	449.3	526.7	582.2	577.3	585.2	619.9
50°	653.6	537.6	420.5	315.4	413.6	417.6	478.1	545.6	545.6	552.5	589.2
52.5°	587.2	489.0	381.9	285.6	370.9	382.9	435.4	513.8	515.8	522.8	555.4
55°	526.7	438.4	354.1	262.9	320.4	346.2	393.8	481.1	485.0	492.0	521.7
57.5°	471.1	365.0	348.2	236.0	273.8	298.6	357.1	449.3	451.3	457.3	486.0
60°	411.7	263.9	319.4	207.3	233.1	251.9	323.3	411.7	418.6	422.5	447.3
62.5°	344.2	191.5	289.6	187.4	213.3	217.2	295.6	376.0	384.8	387.8	402.7
65°	245.0	160.7	246.0	170.6	192.5	193.5	265.8	339.2	347.2	352.1	363.0
67.5°	165.6	130.9	187.4	154.7	176.6	177.6	237.0	296.6	307.5	311.5	318.4
70°	115.1	87.3	138.8	137.8	158.7	160.7	206.3	257.9	267.8	270.8	274.8
72.5°	84.3	70.4	115.1	123.9	139.8	141.9	174.6	214.3	224.2	227.2	229.1
75°	64.5	74.3	93.3	108.2	119.0	120.0	142.9	174.6	181.5	183.5	184.5
77.5°	51.6	69.4	68.4	87.3	97.2	95.2	112.1	134.9	140.8	140.8	140.8
80°	38.7	54.5	51.6	62.5	71.4	69.4	80.4	96.2	98.2	100.2	99.2
82.5°	28.8	34.7	34.7	39.6	47.6	45.7	53.5	62.5	62.5	62.5	64.5
85°	17.8	19.8	15.9	20.8	26.8	25.8	29.8	33.7	34.7	34.7	32.7
87.5°	10.9	9.0	4.9	7.9	11.9	11.9	13.9	14.9	13.9	13.9	13.9
90°	11.9	8.2	4.5	8.2	11.9	12.8	20.1	29.9	34.8	31.0	23.3
92.5°	80.7	49.5	18.3	49.5	80.7	88.4	124.3	172.3	196.2	172.0	123.4
95°	158.1	101.1	44.0	101.1	158.1	172.4	306.1	484.4	573.6	511.8	388.3
97.5°	176.7	126.4	76.1	126.4	176.7	189.3	412.3	709.6	858.3	819.3	741.3
100°	192.2	146.5	100.9	146.5	192.2	203.6	451.0	780.9	945.9	948.7	954.4
102.5°	207.2	164.6	122.0	164.6	207.2	217.8	468.7	803.3	970.6	1020.3	1119.8
105°	229.9	193.8	157.8	193.8	229.9	238.9	481.9	805.9	967.9	1079.3	1302.2
107.5°	261.7	228.1	194.4	228.1	261.7	270.1	484.3	770.0	912.8	1068.3	1379.3
110°	279.8	249.6	219.2	249.6	279.8	287.4	480.6	738.2	867.0	1040.8	1388.5

TEST NUMBER: P934688

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	301.3	272.3	243.4	272.3	301.3	308.5	480.8	710.4	825.3	1003.2	1358.9
115°	333.5	306.8	280.1	306.8	333.5	340.2	485.2	678.6	775.3	946.7	1289.4
117.5°	364.8	340.6	316.3	340.6	364.8	370.9	494.3	658.6	740.9	895.6	1204.9
120°	383.1	360.3	337.4	360.3	383.1	388.8	501.6	651.9	727.2	868.5	1151.1
122.5°	404.2	381.1	358.1	381.1	404.2	409.9	512.1	648.5	716.6	843.8	1098.3
125°	431.7	410.7	389.7	410.7	431.7	436.9	526.3	645.5	705.2	813.3	1029.5
127.5°	457.7	436.6	415.4	436.6	457.7	463.0	540.5	643.9	695.5	788.3	974.0
130°	474.8	452.0	429.1	452.0	474.8	480.5	551.0	644.9	691.9	774.5	939.8
132.5°	489.0	466.2	443.3	466.2	489.0	494.7	559.4	645.5	688.6	762.6	910.6
135°	506.0	485.2	464.4	485.2	506.0	511.2	568.5	644.9	683.1	745.0	869.0
137.5°	527.1	506.5	486.0	506.5	527.1	532.2	582.2	648.9	682.2	734.6	839.3
140°	541.8	522.8	503.8	522.8	541.8	546.5	590.7	649.6	679.0	724.2	814.7
142.5°	552.8	535.2	517.6	535.2	552.8	557.1	597.7	651.8	679.0	718.7	798.2
145°	569.2	554.0	538.8	554.0	569.2	573.1	606.9	651.9	674.4	707.0	771.9
147.5°	589.5	574.6	559.8	574.6	589.5	593.3	620.3	656.4	674.4	700.0	751.1
150°	600.5	587.0	573.6	587.0	600.5	603.8	627.4	658.7	674.4	696.0	739.2
152.5°	608.2	598.0	587.8	598.0	608.2	610.7	631.9	660.2	674.4	692.9	729.7
155°	623.9	616.3	608.9	616.3	623.9	625.8	642.0	663.6	674.4	689.1	718.5
157.5°	639.1	631.8	624.4	631.8	639.1	641.0	652.1	667.0	674.4	685.9	708.6
160°	646.4	640.7	635.0	640.7	646.4	647.8	656.7	668.5	674.4	684.2	703.7
162.5°	654.1	649.9	645.5	649.9	654.1	655.2	661.6	670.2	674.4	682.7	699.2
165°	664.8	660.9	657.0	660.9	664.8	665.7	668.6	672.5	674.4	680.3	692.2
167.5°	671.2	669.4	667.5	669.4	671.2	671.7	674.1	677.4	679.0	682.8	690.6
170°	678.1	676.3	674.4	676.3	678.1	678.6	678.7	678.9	679.0	682.8	690.6
172.5°	678.9	678.5	678.1	678.5	678.9	679.0	679.0	679.0	679.0	682.0	688.1
175°	683.1	683.1	683.1	683.1	683.1	683.1	681.7	679.8	679.0	680.9	684.8
177.5°	683.1	683.1	683.1	683.1	683.1	683.1	682.0	680.6	679.9	681.5	684.6
180°	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1

TEST NUMBER: P934688

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4	1048.4
2.5°	1011.7	1008.8	1012.7	1001.8	1012.7	1008.8	1011.7	1018.6	1012.7	1016.7	1020.7
5°	887.8	882.8	866.9	854.0	866.9	882.8	887.8	908.6	918.5	936.3	960.2
7.5°	793.5	789.6	785.5	777.7	785.5	789.6	793.5	799.4	809.4	825.3	843.1
10°	772.7	773.7	779.6	778.6	779.6	773.7	772.7	770.7	767.7	770.7	781.6
12.5°	826.3	835.1	867.9	865.9	867.9	835.1	826.3	786.5	759.8	754.8	756.9
15°	887.8	890.8	897.7	898.6	897.7	890.8	887.8	871.9	791.6	756.9	745.9
17.5°	893.7	894.7	899.6	899.6	899.6	894.7	893.7	886.7	860.0	813.4	751.8
20°	888.8	890.8	900.6	902.6	900.6	890.8	888.8	879.8	864.9	848.1	801.4
22.5°	886.7	890.8	898.6	897.7	898.6	890.8	886.7	872.9	860.0	848.1	829.2
25°	876.8	876.8	877.8	878.8	877.8	876.8	876.8	865.9	840.2	837.1	826.3
27.5°	856.0	858.0	863.9	862.9	863.9	858.0	856.0	852.0	824.3	821.3	813.4
30°	837.1	835.1	830.2	826.3	830.2	835.1	837.1	831.2	803.4	795.5	797.5
32.5°	805.5	800.4	795.5	792.5	795.5	800.4	805.5	803.4	782.6	771.7	773.7
35°	767.7	768.7	767.7	764.7	767.7	768.7	767.7	769.7	756.9	746.9	745.9
37.5°	741.0	743.0	742.0	737.9	742.0	743.0	741.0	739.0	721.1	718.1	720.1
40°	713.2	714.2	713.2	710.2	713.2	714.2	713.2	709.2	684.4	685.4	692.4
42.5°	686.4	685.4	682.4	680.4	682.4	685.4	686.4	680.4	648.7	645.7	658.6
45°	655.7	656.7	650.7	647.7	650.7	656.7	655.7	651.6	618.9	611.0	619.9
47.5°	624.9	624.9	619.9	616.9	619.9	624.9	624.9	619.9	585.2	577.3	582.2
50°	592.2	591.2	584.2	583.2	584.2	591.2	592.2	589.2	552.5	545.6	545.6
52.5°	554.4	554.4	555.4	557.5	555.4	554.4	554.4	555.4	522.8	515.8	513.8
55°	521.7	522.8	529.7	531.7	529.7	522.8	521.7	521.7	492.0	485.0	481.1
57.5°	488.0	488.0	493.0	493.0	493.0	488.0	488.0	486.0	457.3	451.3	449.3
60°	449.3	451.3	455.2	454.3	455.2	451.3	449.3	447.3	422.5	418.6	411.7
62.5°	408.7	410.7	411.7	409.7	411.7	410.7	408.7	402.7	387.8	384.8	376.0
65°	366.0	368.0	369.0	367.0	369.0	368.0	366.0	363.0	352.1	347.2	339.2
67.5°	322.3	321.3	320.4	324.4	320.4	321.3	322.3	318.4	311.5	307.5	296.6
70°	277.8	277.8	276.8	278.7	276.8	277.8	277.8	274.8	270.8	267.8	257.9
72.5°	230.1	229.1	233.1	230.1	233.1	229.1	230.1	229.1	227.2	224.2	214.3
75°	183.5	185.5	183.5	186.5	183.5	185.5	183.5	184.5	183.5	181.5	174.6
77.5°	139.8	141.9	139.8	139.8	139.8	141.9	139.8	140.8	140.8	140.8	134.9
80°	99.2	98.2	98.2	97.2	98.2	98.2	99.2	99.2	100.2	98.2	96.2
82.5°	63.5	62.5	62.5	64.5	62.5	62.5	63.5	64.5	62.5	62.5	62.5
85°	34.7	35.7	33.7	33.7	33.7	35.7	34.7	32.7	34.7	34.7	33.7
87.5°	12.9	11.9	11.9	11.9	11.9	11.9	12.9	13.9	13.9	13.9	14.9
90°	17.5	17.5	17.5	17.5	17.5	17.5	17.5	23.3	31.0	34.8	29.9
92.5°	87.1	83.6	69.7	55.9	69.7	83.6	87.1	123.4	172.0	196.2	172.3
95°	295.7	285.2	243.2	201.2	243.2	285.2	295.7	388.3	511.8	573.6	484.4
97.5°	682.7	662.7	582.8	503.0	582.8	662.7	682.7	741.3	819.3	858.3	709.6
100°	958.7	934.9	839.7	744.5	839.7	934.9	958.7	954.4	948.7	945.9	780.9
102.5°	1194.3	1173.9	1092.5	1010.9	1092.5	1173.9	1194.3	1119.8	1020.3	970.6	803.3
105°	1469.4	1458.5	1414.6	1370.8	1414.6	1458.5	1469.4	1302.2	1079.3	967.9	805.9
107.5°	1612.5	1615.2	1625.7	1636.3	1625.7	1615.2	1612.5	1379.3	1068.3	912.8	770.0
110°	1649.2	1660.6	1706.2	1751.8	1706.2	1660.6	1649.2	1388.5	1040.8	867.0	738.2

TEST NUMBER: P934688

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1625.7	1643.3	1713.4	1783.5	1713.4	1643.3	1625.7	1358.9	1003.2	825.3	710.4
115°	1546.4	1570.7	1667.9	1765.1	1667.9	1570.7	1546.4	1289.4	946.7	775.3	678.6
117.5°	1436.9	1463.8	1571.6	1679.4	1571.6	1463.8	1436.9	1204.9	895.6	740.9	658.6
120°	1363.0	1389.3	1494.0	1598.7	1494.0	1389.3	1363.0	1151.1	868.5	727.2	651.9
122.5°	1289.2	1315.0	1418.4	1521.7	1418.4	1315.0	1289.2	1098.3	843.8	716.6	648.5
125°	1191.6	1215.3	1310.6	1405.7	1310.6	1215.3	1191.6	1029.5	813.3	705.2	645.5
127.5°	1113.2	1133.3	1213.6	1293.8	1213.6	1133.3	1113.2	974.0	788.3	695.5	643.9
130°	1063.7	1082.2	1156.4	1230.5	1156.4	1082.2	1063.7	939.8	774.5	691.9	644.9
132.5°	1021.5	1038.1	1104.5	1171.0	1104.5	1038.1	1021.5	910.6	762.6	688.6	645.5
135°	961.8	976.1	1033.4	1090.7	1033.4	976.1	961.8	869.0	745.0	683.1	644.9
137.5°	917.9	929.6	976.4	1023.4	976.4	929.6	917.9	839.3	734.6	682.2	648.9
140°	882.6	893.5	937.4	981.2	937.4	893.5	882.6	814.7	724.2	679.0	649.6
142.5°	857.8	867.3	905.0	942.6	905.0	867.3	857.8	798.2	718.7	679.0	651.8
145°	820.6	827.7	856.3	884.8	856.3	827.7	820.6	771.9	707.0	674.4	651.9
147.5°	789.5	795.4	819.0	842.6	819.0	795.4	789.5	751.1	700.0	674.4	656.4
150°	771.6	776.5	795.6	814.7	795.6	776.5	771.6	739.2	696.0	674.4	658.7
152.5°	757.4	761.1	775.5	790.0	775.5	761.1	757.4	729.7	692.9	674.4	660.2
155°	740.5	742.9	752.4	762.0	752.4	742.9	740.5	718.5	689.1	674.4	663.6
157.5°	725.8	727.5	734.2	740.9	734.2	727.5	725.8	708.6	685.9	674.4	667.0
160°	718.4	719.4	723.2	727.2	723.2	719.4	718.4	703.7	684.2	674.4	668.5
162.5°	711.6	712.5	716.1	719.8	716.1	712.5	711.6	699.2	682.7	674.4	670.2
165°	701.0	702.0	705.9	709.7	705.9	702.0	701.0	692.2	680.3	674.4	672.5
167.5°	696.4	696.8	698.5	700.1	698.5	696.8	696.4	690.6	682.8	679.0	677.4
170°	696.4	696.4	696.4	696.4	696.4	696.4	696.4	690.6	682.8	679.0	678.9
172.5°	692.8	692.4	691.0	689.5	691.0	692.4	692.8	688.1	682.0	679.0	679.0
175°	687.7	687.7	687.7	687.7	687.7	687.7	687.7	684.8	680.9	679.0	679.8
177.5°	686.8	686.5	684.8	683.1	684.8	686.5	686.8	684.6	681.5	679.9	680.6
180°	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1	683.1

TEST NUMBER: P934688

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1048.4	1048.4	1048.4	1048.4	1048.4
2.5°	1035.5	1040.5	1043.5	1047.4	1057.4
5°	995.9	1014.7	1020.7	1035.5	1053.3
7.5°	908.6	966.1	982.0	1017.7	1045.5
10°	824.3	881.8	909.6	993.9	1035.5
12.5°	781.6	815.3	834.2	952.2	1021.7
15°	754.8	778.6	792.5	896.7	1005.8
17.5°	734.0	750.8	760.8	842.1	983.9
20°	721.1	729.0	737.9	802.4	959.2
22.5°	712.2	707.3	714.2	774.7	925.5
25°	706.3	687.3	695.3	752.8	885.7
27.5°	711.2	669.5	672.6	733.0	844.1
30°	712.2	647.7	648.7	712.2	797.5
32.5°	705.3	624.9	625.9	686.4	744.9
35°	688.3	598.1	597.1	656.7	673.5
37.5°	665.6	569.3	569.3	623.9	595.1
40°	637.7	540.6	543.6	581.2	525.7
42.5°	604.0	509.9	513.8	524.7	474.2
45°	567.3	480.1	483.0	443.4	434.4
47.5°	526.7	449.3	450.3	368.0	421.5
50°	478.1	417.6	413.6	315.4	420.5
52.5°	435.4	382.9	370.9	285.6	381.9
55°	393.8	346.2	320.4	262.9	354.1
57.5°	357.1	298.6	273.8	236.0	348.2
60°	323.3	251.9	233.1	207.3	319.4
62.5°	295.6	217.2	213.3	187.4	289.6
65°	265.8	193.5	192.5	170.6	246.0
67.5°	237.0	177.6	176.6	154.7	187.4
70°	206.3	160.7	158.7	137.8	138.8
72.5°	174.6	141.9	139.8	123.9	115.1
75°	142.9	120.0	119.0	108.2	93.3
77.5°	112.1	95.2	97.2	87.3	68.4
80°	80.4	69.4	71.4	62.5	51.6
82.5°	53.5	45.7	47.6	39.6	34.7
85°	29.8	25.8	26.8	20.8	15.9
87.5°	13.9	11.9	11.9	7.9	4.9
90°	20.1	12.8	11.9	8.2	4.5
92.5°	124.3	88.4	80.7	49.5	18.3
95°	306.1	172.4	158.1	101.1	44.0
97.5°	412.3	189.3	176.7	126.4	76.1
100°	451.0	203.6	192.2	146.5	100.9
102.5°	468.7	217.8	207.2	164.6	122.0
105°	481.9	238.9	229.9	193.8	157.8
107.5°	484.3	270.1	261.7	228.1	194.4
110°	480.6	287.4	279.8	249.6	219.2



TEST NUMBER: P934688

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	480.8	308.5	301.3	272.3	243.4
115°	485.2	340.2	333.5	306.8	280.1
117.5°	494.3	370.9	364.8	340.6	316.3
120°	501.6	388.8	383.1	360.3	337.4
122.5°	512.1	409.9	404.2	381.1	358.1
125°	526.3	436.9	431.7	410.7	389.7
127.5°	540.5	463.0	457.7	436.6	415.4
130°	551.0	480.5	474.8	452.0	429.1
132.5°	559.4	494.7	489.0	466.2	443.3
135°	568.5	511.2	506.0	485.2	464.4
137.5°	582.2	532.2	527.1	506.5	486.0
140°	590.7	546.5	541.8	522.8	503.8
142.5°	597.7	557.1	552.8	535.2	517.6
145°	606.9	573.1	569.2	554.0	538.8
147.5°	620.3	593.3	589.5	574.6	559.8
150°	627.4	603.8	600.5	587.0	573.6
152.5°	631.9	610.7	608.2	598.0	587.8
155°	642.0	625.8	623.9	616.3	608.9
157.5°	652.1	641.0	639.1	631.8	624.4
160°	656.7	647.8	646.4	640.7	635.0
162.5°	661.6	655.2	654.1	649.9	645.5
165°	668.6	665.7	664.8	660.9	657.0
167.5°	674.1	671.7	671.2	669.4	667.5
170°	678.7	678.6	678.1	676.3	674.4
172.5°	679.0	679.0	678.9	678.5	678.1
175°	681.7	683.1	683.1	683.1	683.1
177.5°	682.0	683.1	683.1	683.1	683.1
180°	683.1	683.1	683.1	683.1	683.1

TEST NUMBER: P934688

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-6-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.08	10.85	11.14	11.90	13.33	12.91	13.67	13.96	14.73	16.16
	3H	10.55	11.23	11.61	12.30	13.75	14.24	14.93	15.31	15.99	17.44
	4H	10.74	11.39	11.81	12.45	13.91	14.68	15.33	15.76	16.40	17.85
	6H	10.85	11.45	11.94	12.52	13.99	14.96	15.56	16.04	16.63	18.10
	8H	10.85	11.42	11.94	12.50	13.97	15.03	15.60	16.12	16.69	18.15
	12H	10.82	11.36	11.91	12.44	13.93	15.06	15.60	16.16	16.68	18.17
4H	2H	11.10	11.75	12.18	12.82	14.27	13.30	13.95	14.39	15.02	16.48
	3H	12.12	12.66	13.21	13.75	15.22	14.80	15.34	15.89	16.43	17.90
	4H	12.39	12.89	13.48	13.97	15.46	15.32	15.82	16.42	16.90	18.39
	6H	12.51	12.94	13.61	14.04	15.53	15.68	16.10	16.78	17.21	18.70
	8H	12.51	12.91	13.62	14.01	15.51	15.78	16.18	16.89	17.28	18.78
	12H	12.48	12.84	13.60	13.95	15.45	15.83	16.19	16.95	17.31	18.81
8H	4H	12.84	13.23	13.94	14.33	15.83	15.44	15.84	16.54	16.94	18.44
	6H	13.09	13.42	14.22	14.56	16.06	15.87	16.20	16.99	17.34	18.84
	8H	13.13	13.42	14.27	14.55	16.06	16.02	16.31	17.15	17.43	18.95
	12H	13.11	13.37	14.25	14.49	16.04	16.11	16.36	17.25	17.48	19.04
12H	4H	12.84	13.20	13.96	14.31	15.82	15.40	15.76	16.52	16.87	18.38
	6H	13.15	13.44	14.28	14.56	16.08	15.87	16.15	17.00	17.28	18.79
	8H	13.21	13.47	14.35	14.59	16.14	16.02	16.27	17.16	17.39	18.95

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

16 of 16