

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P933879

Luminaire Tested: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P933879
REPORT IS A COMBINATION OF REPORTS P933673 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8157.1 lumens
Efficiency: N/A
Efficacy: 123.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 66
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P933879

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P933879

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66		
1	101	97	93	89	95	91	88	85	81	78	76	71	69	68	62	61	60	55		
2	92	85	78	73	87	80	74	70	71	67	63	63	59	56	55	52	50	46		
3	84	75	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39		
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	43	40	37	34		
5	71	59	50	44	66	56	48	43	50	44	39	44	39	35	39	35	32	29		
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28	26		
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25	23		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18		
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6374	6374	6374	6374
5°	6424	6434	6424	5059
10°	6383	6338	6383	4531
15°	6316	6201	6316	5178
20°	6187	6038	6187	5188
25°	5919	5801	5919	5078
30°	5572	5604	5572	4837
35°	4970	5355	4970	4572
40°	4143	5061	4143	4371
45°	3704	4718	3704	4141
50°	3939	4308	3939	3909
55°	3709	3868	3709	3776
60°	3828	3285	3828	3458
65°	3477	2716	3477	3035
70°	2414	2164	2414	2544
75°	2123	1600	2123	1915
80°	1725	1058	1725	1152
85°	1011	560	1011	476

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 5674 cd/sqm

TEST NUMBER: P933879

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.0	2.3
10°-20°	528.1	6.5
20°-30°	816.4	10.0
30°-40°	974.6	11.9
40°-50°	980.4	12.0
50°-60°	853.0	10.5
60°-70°	604.8	7.4
70°-80°	320.0	3.9
80°-90°	81.3	1.0
90°-100°	211.5	2.6
100°-110°	556.0	6.8
110°-120°	576.5	7.1
120°-130°	462.4	5.7
130°-140°	362.8	4.4
140°-150°	278.5	3.4
150°-160°	200.6	2.5
160°-170°	122.7	1.5
170°-180°	41.5	0.5
0°-30°	1530.6	18.8
0°-40°	2505.2	30.7
0°-60°	4338.6	53.2
0°-90°	5344.7	65.5
90°-120°	1343.9	16.5
90°-150°	2447.6	30.0
90°-180°	2812.0	34.5
0°-180°	8157.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2061	2061	2061	2061	2061	
5°	2070	2135	2070	1679	2070	196
15°	1977	2115	1977	1766	1977	556
25°	1741	1973	1741	1727	1741	799
35°	1324	1760	1324	1503	1324	819
45°	854	1450	854	1273	854	684
55°	696	1070	696	1045	696	640
65°	484	645	484	721	484	462
75°	183	306	183	366	183	193
85°	31	78	31	66	31	42
90°	3	11	3	11	3	4
95°	28	128	28	128	28	31
105°	100	870	100	870	100	106
115°	178	1121	178	1121	178	176
125°	248	893	248	893	248	220
135°	295	693	295	693	295	228
145°	342	562	342	562	342	214
155°	387	484	387	484	387	178
165°	417	451	417	451	417	118
175°	434	437	434	437	434	41
180°	434	434	434	434	434	

TEST NUMBER: P933879

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7
2.5°	2078.2	2078.2	2089.9	2093.8	2093.8	2088.0	2082.2	2088.0	2105.5	2111.4	2109.4
5°	2070.5	2086.1	2107.5	2111.4	2115.3	2113.4	2109.4	2113.4	2132.9	2136.7	2138.7
7.5°	2054.9	2084.1	2111.4	2117.3	2123.1	2117.3	2115.3	2119.2	2138.7	2142.6	2142.6
10°	2035.4	2076.3	2107.5	2111.4	2117.3	2111.4	2111.4	2119.2	2138.7	2142.6	2144.6
12.5°	2008.1	2064.6	2093.8	2097.8	2105.5	2103.6	2101.7	2109.4	2129.0	2132.9	2132.9
15°	1976.9	2043.1	2070.5	2074.3	2088.0	2084.1	2084.1	2091.9	2113.4	2119.2	2117.3
17.5°	1934.0	2015.9	2047.1	2052.9	2062.7	2060.7	2062.7	2070.5	2089.9	2093.8	2095.9
20°	1885.3	1978.8	2015.9	2021.7	2031.5	2031.5	2031.5	2041.2	2060.7	2068.5	2068.5
22.5°	1819.0	1939.8	1978.8	1982.8	1994.4	1994.4	1998.4	2011.9	2029.5	2031.5	2031.5
25°	1741.0	1896.9	1930.1	1941.8	1953.5	1959.3	1965.2	1973.0	1978.8	1976.9	1978.8
27.5°	1659.1	1842.4	1885.3	1893.0	1908.6	1914.5	1922.3	1924.2	1926.2	1932.0	1928.1
30°	1567.5	1766.3	1830.6	1838.5	1863.8	1867.7	1859.9	1863.8	1873.6	1877.4	1881.3
32.5°	1464.2	1653.2	1774.1	1791.7	1815.0	1803.4	1801.4	1807.3	1822.9	1822.9	1826.8
35°	1323.8	1565.5	1721.5	1737.1	1754.7	1741.0	1748.8	1750.7	1760.5	1766.3	1764.4
37.5°	1169.8	1489.4	1666.9	1678.6	1692.3	1674.7	1686.4	1692.3	1700.0	1696.1	1696.1
40°	1033.2	1370.6	1602.5	1610.4	1622.0	1608.4	1620.1	1624.0	1627.9	1624.0	1622.0
42.5°	931.9	1239.9	1534.3	1544.1	1536.3	1546.0	1549.9	1557.8	1551.9	1544.1	1544.1
45°	853.9	1204.9	1460.3	1471.9	1460.3	1475.9	1481.7	1481.7	1464.2	1460.3	1458.2
47.5°	828.6	1134.7	1386.2	1386.2	1380.3	1399.8	1409.5	1395.9	1378.4	1372.5	1372.5
50°	826.7	1056.7	1284.8	1276.9	1304.3	1327.6	1317.9	1304.3	1290.6	1269.2	1269.2
52.5°	750.6	961.2	1154.2	1183.4	1226.3	1239.9	1224.3	1210.7	1187.3	1177.5	1169.8
55°	696.0	861.7	1035.2	1093.7	1138.6	1156.1	1126.9	1113.2	1078.1	1072.3	1068.4
57.5°	684.3	717.4	926.1	1000.1	1054.8	1052.8	1035.2	1009.9	980.6	974.8	972.9
60°	627.8	518.6	809.1	896.8	953.3	947.5	931.9	908.5	881.2	877.3	873.5
62.5°	569.3	376.3	676.5	776.0	855.8	853.9	840.3	805.1	785.7	776.0	768.1
65°	483.5	315.8	481.6	645.4	760.4	764.3	735.0	709.7	688.2	676.5	674.5
67.5°	368.5	257.4	325.6	538.1	668.7	664.8	627.8	616.1	588.8	583.0	571.2
70°	273.0	171.6	226.2	436.7	579.1	569.3	540.0	526.4	501.1	487.4	479.6
72.5°	226.2	138.4	165.7	339.2	487.4	475.7	450.4	434.8	413.3	401.7	393.8
75°	183.2	146.2	126.7	251.5	395.7	388.0	364.5	348.9	331.4	315.8	317.7
77.5°	134.5	136.4	101.4	185.2	313.9	302.2	288.6	269.1	261.2	245.6	245.6
80°	101.4	107.3	76.1	126.7	226.2	226.2	214.4	200.8	187.1	179.4	179.4
82.5°	68.2	68.2	56.5	79.9	154.0	148.2	140.4	136.4	128.7	124.8	124.8
85°	31.2	39.0	35.1	48.7	83.8	87.7	87.7	83.8	81.9	78.0	79.9
87.5°	9.8	17.5	21.4	27.3	42.9	44.9	46.8	46.8	46.8	48.7	48.7
90°	2.9	5.2	7.6	8.1	12.8	19.0	22.1	19.7	14.7	11.0	11.0
92.5°	11.6	31.4	51.3	56.2	79.0	109.4	124.6	109.2	78.4	55.3	53.1
95°	27.9	64.1	100.4	109.5	194.4	307.7	364.2	325.0	246.6	187.8	181.1
97.5°	48.4	80.3	112.3	120.3	261.8	450.7	545.1	520.3	470.7	433.5	420.8
100°	64.1	93.0	122.0	129.3	286.4	495.9	600.7	602.5	606.1	608.8	593.7
102.5°	77.4	104.5	131.5	138.3	297.7	510.2	616.4	648.0	711.1	758.4	745.5
105°	100.2	123.1	145.9	151.6	306.0	511.7	614.6	685.4	826.9	933.1	926.2
107.5°	123.5	144.8	166.2	171.5	307.6	489.0	579.7	678.4	875.9	1024.0	1025.7
110°	139.1	158.4	177.7	182.6	305.2	468.8	550.6	661.0	881.7	1047.3	1054.6

TEST NUMBER: P933879

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	154.7	173.0	191.4	195.9	305.3	451.2	524.1	637.1	863.0	1032.5	1043.6
115°	177.9	194.9	211.8	216.1	308.1	430.9	492.3	601.2	818.8	982.1	997.5
117.5°	200.9	216.3	231.7	235.6	313.9	418.3	470.5	568.8	765.2	912.5	929.7
120°	214.2	228.8	243.3	246.9	318.5	414.0	461.7	551.5	731.0	865.6	882.3
122.5°	227.4	242.1	256.6	260.3	325.2	411.7	455.0	535.9	697.5	818.7	835.1
125°	247.5	260.9	274.2	277.5	334.3	410.0	447.8	516.4	653.7	756.7	771.8
127.5°	263.8	277.2	290.7	294.1	343.3	408.9	441.7	500.6	618.5	706.9	719.7
130°	272.5	287.0	301.6	305.1	349.9	409.5	439.3	491.9	596.8	675.5	687.3
132.5°	281.6	296.0	310.6	314.1	355.2	410.0	437.3	484.3	578.3	648.7	659.3
135°	295.0	308.1	321.3	324.6	361.0	409.6	433.8	473.2	551.8	610.9	620.0
137.5°	308.6	321.7	334.7	338.0	369.8	412.1	433.2	466.5	532.9	582.9	590.3
140°	320.0	332.0	344.1	347.1	375.1	412.5	431.2	459.9	517.3	560.5	567.4
142.5°	328.7	339.8	351.0	353.8	379.6	414.0	431.2	456.4	506.9	544.8	550.8
145°	342.2	351.8	361.5	364.0	385.4	414.0	428.3	448.9	490.2	521.1	525.7
147.5°	355.5	364.9	374.4	376.7	393.9	416.9	428.3	444.6	477.0	501.4	505.1
150°	364.2	372.8	381.3	383.4	398.4	418.3	428.3	442.1	469.5	490.0	493.0
152.5°	373.3	379.8	386.1	387.8	401.3	419.3	428.3	440.0	463.5	481.0	483.3
155°	386.6	391.4	396.2	397.4	407.7	421.4	428.3	437.6	456.3	470.3	471.8
157.5°	396.5	401.2	405.9	407.1	414.2	423.5	428.3	435.6	450.0	460.9	461.9
160°	403.3	406.9	410.6	411.4	417.1	424.5	428.3	434.5	446.9	456.2	456.8
162.5°	410.0	412.7	415.4	416.1	420.2	425.6	428.3	433.5	444.0	451.8	452.4
165°	417.3	419.7	422.2	422.8	424.6	427.0	428.3	432.1	439.5	445.2	445.7
167.5°	423.9	425.1	426.3	426.6	428.1	430.1	431.2	433.6	438.6	442.3	442.5
170°	428.3	429.5	430.6	430.9	431.0	431.1	431.2	433.6	438.6	442.3	442.3
172.5°	430.6	430.9	431.1	431.2	431.2	431.2	431.2	433.1	437.0	439.9	439.7
175°	433.8	433.8	433.8	433.8	432.9	431.8	431.2	432.5	434.9	436.7	436.7
177.5°	433.8	433.8	433.8	433.8	433.1	432.3	431.8	432.8	434.7	436.1	435.9
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8

TEST NUMBER: P933879

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7
2.5°	2113.4	2107.5	2113.4	2109.4	2111.4	2105.5	2088.0	2082.2	2088.0	2093.8	2093.8
5°	2138.7	2134.8	2138.7	2138.7	2136.7	2132.9	2113.4	2109.4	2113.4	2115.3	2111.4
7.5°	2146.5	2140.6	2146.5	2142.6	2142.6	2138.7	2119.2	2115.3	2117.3	2123.1	2117.3
10°	2146.5	2140.6	2146.5	2144.6	2142.6	2138.7	2119.2	2111.4	2111.4	2117.3	2111.4
12.5°	2136.7	2132.9	2136.7	2132.9	2132.9	2129.0	2109.4	2101.7	2103.6	2105.5	2097.8
15°	2121.1	2115.3	2121.1	2117.3	2119.2	2113.4	2091.9	2084.1	2084.1	2088.0	2074.3
17.5°	2097.8	2089.9	2097.8	2095.9	2093.8	2089.9	2070.5	2062.7	2060.7	2062.7	2052.9
20°	2070.5	2064.6	2070.5	2068.5	2068.5	2060.7	2041.2	2031.5	2031.5	2031.5	2021.7
22.5°	2027.5	2021.7	2027.5	2031.5	2031.5	2029.5	2011.9	1998.4	1994.4	1994.4	1982.8
25°	1978.8	1973.0	1978.8	1978.8	1976.9	1978.8	1973.0	1965.2	1959.3	1953.5	1941.8
27.5°	1932.0	1928.1	1932.0	1928.1	1932.0	1926.2	1924.2	1922.3	1914.5	1908.6	1893.0
30°	1885.3	1881.3	1885.3	1881.3	1877.4	1873.6	1863.8	1859.9	1867.7	1863.8	1838.5
32.5°	1826.8	1822.9	1826.8	1826.8	1822.9	1822.9	1807.3	1801.4	1803.4	1815.0	1791.7
35°	1766.3	1760.5	1766.3	1764.4	1766.3	1760.5	1750.7	1748.8	1741.0	1754.7	1737.1
37.5°	1696.1	1690.3	1696.1	1696.1	1696.1	1700.0	1692.3	1686.4	1674.7	1692.3	1678.6
40°	1624.0	1616.2	1624.0	1622.0	1624.0	1627.9	1624.0	1620.1	1608.4	1622.0	1610.4
42.5°	1542.2	1540.1	1542.2	1544.1	1544.1	1551.9	1557.8	1549.9	1546.0	1536.3	1544.1
45°	1454.4	1450.5	1454.4	1458.2	1460.3	1464.2	1481.7	1481.7	1475.9	1460.3	1471.9
47.5°	1360.8	1351.1	1360.8	1372.5	1372.5	1378.4	1395.9	1409.5	1399.8	1380.3	1386.2
50°	1261.3	1263.3	1261.3	1269.2	1269.2	1290.6	1304.3	1317.9	1327.6	1304.3	1276.9
52.5°	1163.9	1161.9	1163.9	1169.8	1177.5	1187.3	1210.7	1224.3	1239.9	1226.3	1183.4
55°	1066.4	1070.4	1066.4	1068.4	1072.3	1078.1	1113.2	1126.9	1156.1	1138.6	1093.7
57.5°	968.9	963.1	968.9	972.9	974.8	980.6	1009.9	1035.2	1052.8	1054.8	1000.1
60°	855.8	848.1	855.8	873.5	877.3	881.2	908.5	931.9	947.5	953.3	896.8
62.5°	756.4	742.8	756.4	768.1	776.0	785.7	805.1	840.3	853.9	855.8	776.0
65°	651.2	645.4	651.2	674.5	676.5	688.2	709.7	735.0	764.3	760.4	645.4
67.5°	555.6	555.6	555.6	571.2	583.0	588.8	616.1	627.8	664.8	668.7	538.1
70°	467.9	466.0	467.9	479.6	487.4	501.1	526.4	540.0	569.3	579.1	436.7
72.5°	384.1	382.1	384.1	393.8	401.7	413.3	434.8	450.4	475.7	487.4	339.2
75°	310.0	306.1	310.0	317.7	315.8	331.4	348.9	364.5	388.0	395.7	251.5
77.5°	237.9	237.9	237.9	245.6	245.6	261.2	269.1	288.6	302.2	313.9	185.2
80°	177.4	175.5	177.4	179.4	179.4	187.1	200.8	214.4	226.2	226.2	126.7
82.5°	124.8	120.8	124.8	124.8	124.8	128.7	136.4	140.4	148.2	154.0	79.9
85°	78.0	78.0	78.0	79.9	78.0	81.9	83.8	87.7	87.7	83.8	48.7
87.5°	50.7	48.7	50.7	48.7	48.7	46.8	46.8	46.8	44.9	42.9	27.3
90°	11.0	11.0	11.0	11.0	11.0	14.7	19.7	22.1	19.0	12.8	8.1
92.5°	44.4	35.6	44.4	53.1	55.3	78.4	109.2	124.6	109.4	79.0	56.2
95°	154.5	127.8	154.5	181.1	187.8	246.6	325.0	364.2	307.7	194.4	109.5
97.5°	370.2	319.4	370.2	420.8	433.5	470.7	520.3	545.1	450.7	261.8	120.3
100°	533.3	472.9	533.3	593.7	608.8	606.1	602.5	600.7	495.9	286.4	129.3
102.5°	693.7	642.0	693.7	745.5	758.4	711.1	648.0	616.4	510.2	297.7	138.3
105°	898.4	870.5	898.4	926.2	933.1	826.9	685.4	614.6	511.7	306.0	151.6
107.5°	1032.5	1039.2	1032.5	1025.7	1024.0	875.9	678.4	579.7	489.0	307.6	171.5
110°	1083.5	1112.5	1083.5	1054.6	1047.3	881.7	661.0	550.6	468.8	305.2	182.6

TEST NUMBER: P933879

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1088.1	1132.6	1088.1	1043.6	1032.5	863.0	637.1	524.1	451.2	305.3	195.9
115°	1059.2	1120.9	1059.2	997.5	982.1	818.8	601.2	492.3	430.9	308.1	216.1
117.5°	998.1	1066.5	998.1	929.7	912.5	765.2	568.8	470.5	418.3	313.9	235.6
120°	948.7	1015.2	948.7	882.3	865.6	731.0	551.5	461.7	414.0	318.5	246.9
122.5°	900.8	966.4	900.8	835.1	818.7	697.5	535.9	455.0	411.7	325.2	260.3
125°	832.2	892.6	832.2	771.8	756.7	653.7	516.4	447.8	410.0	334.3	277.5
127.5°	770.6	821.6	770.6	719.7	706.9	618.5	500.6	441.7	408.9	343.3	294.1
130°	734.4	781.5	734.4	687.3	675.5	596.8	491.9	439.3	409.5	349.9	305.1
132.5°	701.5	743.6	701.5	659.3	648.7	578.3	484.3	437.3	410.0	355.2	314.1
135°	656.3	692.6	656.3	620.0	610.9	551.8	473.2	433.8	409.6	361.0	324.6
137.5°	620.1	649.9	620.1	590.3	582.9	532.9	466.5	433.2	412.1	369.8	338.0
140°	595.3	623.1	595.3	567.4	560.5	517.3	459.9	431.2	412.5	375.1	347.1
142.5°	574.7	598.6	574.7	550.8	544.8	506.9	456.4	431.2	414.0	379.6	353.8
145°	543.8	561.9	543.8	525.7	521.1	490.2	448.9	428.3	414.0	385.4	364.0
147.5°	520.2	535.2	520.2	505.1	501.4	477.0	444.6	428.3	416.9	393.9	376.7
150°	505.2	517.3	505.2	493.0	490.0	469.5	442.1	428.3	418.3	398.4	383.4
152.5°	492.4	501.7	492.4	483.3	481.0	463.5	440.0	428.3	419.3	401.3	387.8
155°	477.8	483.9	477.8	471.8	470.3	456.3	437.6	428.3	421.4	407.7	397.4
157.5°	466.3	470.5	466.3	461.9	460.9	450.0	435.6	428.3	423.5	414.2	407.1
160°	459.3	461.7	459.3	456.8	456.2	446.9	434.5	428.3	424.5	417.1	411.4
162.5°	454.8	457.1	454.8	452.4	451.8	444.0	433.5	428.3	425.6	420.2	416.1
165°	448.3	450.7	448.3	445.7	445.2	439.5	432.1	428.3	427.0	424.6	422.8
167.5°	443.5	444.6	443.5	442.5	442.3	438.6	433.6	431.2	430.1	428.1	426.6
170°	442.3	442.3	442.3	442.3	442.3	438.6	433.6	431.2	431.1	431.0	430.9
172.5°	438.8	437.9	438.8	439.7	439.9	437.0	433.1	431.2	431.2	431.2	431.2
175°	436.7	436.7	436.7	436.7	436.7	434.9	432.5	431.2	431.8	432.9	433.8
177.5°	434.9	433.8	434.9	435.9	436.1	434.7	432.8	431.8	432.3	433.1	433.8
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8

TEST NUMBER: P933879

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7
2.5°	2089.9	2078.2	2078.2	2058.7	2051.0	2045.1	2035.4	2006.1	1998.4	1990.5	2002.2
5°	2107.5	2086.1	2070.5	2035.4	2006.1	1994.4	1957.4	1887.2	1840.4	1805.3	1785.9
7.5°	2111.4	2084.1	2054.9	2000.3	1930.1	1898.9	1785.9	1657.2	1622.0	1590.9	1571.3
10°	2107.5	2076.3	2035.4	1953.5	1787.8	1733.2	1620.1	1536.3	1514.8	1509.0	1514.8
12.5°	2093.8	2064.6	2008.1	1871.6	1639.6	1602.5	1536.3	1487.5	1483.6	1493.4	1546.0
15°	2070.5	2043.1	1976.9	1762.4	1557.8	1530.4	1483.6	1466.1	1487.5	1555.7	1713.7
17.5°	2047.1	2015.9	1934.0	1655.2	1495.4	1475.9	1442.6	1477.8	1598.7	1690.3	1742.9
20°	2015.9	1978.8	1885.3	1577.2	1450.5	1433.0	1417.4	1575.3	1666.9	1700.0	1729.3
22.5°	1978.8	1939.8	1819.0	1522.6	1403.7	1390.0	1399.8	1629.9	1666.9	1690.3	1715.6
25°	1930.1	1896.9	1741.0	1479.8	1366.7	1351.1	1388.1	1624.0	1645.5	1651.3	1702.0
27.5°	1885.3	1842.4	1659.1	1440.7	1321.8	1316.0	1397.9	1598.7	1614.3	1620.1	1674.7
30°	1830.6	1766.3	1567.5	1399.8	1275.0	1273.1	1399.8	1567.5	1563.6	1579.2	1633.7
32.5°	1774.1	1653.2	1464.2	1349.1	1230.1	1228.2	1386.2	1520.7	1516.8	1538.2	1579.2
35°	1721.5	1565.5	1323.8	1290.6	1173.7	1175.6	1353.0	1466.1	1468.0	1487.5	1512.9
37.5°	1666.9	1489.4	1169.8	1226.3	1119.1	1119.1	1308.1	1415.4	1411.5	1417.4	1452.4
40°	1602.5	1370.6	1033.2	1142.5	1068.4	1062.5	1253.6	1360.8	1347.2	1345.3	1393.9
42.5°	1534.3	1239.9	931.9	1031.3	1009.9	1002.0	1187.3	1294.5	1269.2	1275.0	1337.4
45°	1460.3	1204.9	853.9	871.4	949.4	943.6	1115.1	1218.5	1201.0	1216.6	1280.9
47.5°	1386.2	1134.7	828.6	723.3	885.1	883.1	1035.2	1144.4	1134.7	1150.3	1218.5
50°	1284.8	1056.7	826.7	620.0	813.0	820.7	939.7	1072.3	1072.3	1086.0	1158.1
52.5°	1154.2	961.2	750.6	561.4	729.2	752.5	855.8	1009.9	1013.8	1027.4	1091.8
55°	1035.2	861.7	696.0	516.7	629.8	680.4	773.9	945.6	953.3	967.0	1025.5
57.5°	926.1	717.4	684.3	464.0	538.1	586.8	701.8	883.1	887.0	898.7	955.3
60°	809.1	518.6	627.8	407.5	458.1	495.2	635.6	809.1	822.7	830.5	879.3
62.5°	676.5	376.3	569.3	368.5	419.2	426.9	581.0	738.9	756.4	762.3	791.6
65°	481.6	315.8	483.5	335.4	378.2	380.1	522.5	666.8	682.4	692.1	713.6
67.5°	325.6	257.4	368.5	304.2	347.0	348.9	466.0	583.0	604.4	612.2	625.8
70°	226.2	171.6	273.0	271.0	311.9	315.8	405.5	506.9	526.4	532.3	540.0
72.5°	165.7	138.4	226.2	243.7	274.9	278.8	343.1	421.1	440.6	446.4	450.4
75°	126.7	146.2	183.2	212.5	233.9	235.9	280.7	343.1	356.8	360.7	362.6
77.5°	101.4	136.4	134.5	171.6	191.1	187.1	220.4	265.1	276.8	276.8	276.8
80°	76.1	107.3	101.4	122.9	140.4	136.4	157.9	189.1	193.0	196.9	195.0
82.5°	56.5	68.2	68.2	78.0	93.6	89.7	105.2	122.9	122.9	122.9	126.7
85°	35.1	39.0	31.2	41.0	52.6	50.7	58.5	66.3	68.2	68.2	64.3
87.5°	21.4	17.5	9.8	15.6	23.4	23.4	27.3	29.3	27.3	27.3	27.3
90°	7.6	5.2	2.9	5.2	7.6	8.1	12.8	19.0	22.1	19.7	14.7
92.5°	51.3	31.4	11.6	31.4	51.3	56.2	79.0	109.4	124.6	109.2	78.4
95°	100.4	64.1	27.9	64.1	100.4	109.5	194.4	307.7	364.2	325.0	246.6
97.5°	112.3	80.3	48.4	80.3	112.3	120.3	261.8	450.7	545.1	520.3	470.7
100°	122.0	93.0	64.1	93.0	122.0	129.3	286.4	495.9	600.7	602.5	606.1
102.5°	131.5	104.5	77.4	104.5	131.5	138.3	297.7	510.2	616.4	648.0	711.1
105°	145.9	123.1	100.2	123.1	145.9	151.6	306.0	511.7	614.6	685.4	826.9
107.5°	166.2	144.8	123.5	144.8	166.2	171.5	307.6	489.0	579.7	678.4	875.9
110°	177.7	158.4	139.1	158.4	177.7	182.6	305.2	468.8	550.6	661.0	881.7

TEST NUMBER: P933879

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	191.4	173.0	154.7	173.0	191.4	195.9	305.3	451.2	524.1	637.1	863.0
115°	211.8	194.9	177.9	194.9	211.8	216.1	308.1	430.9	492.3	601.2	818.8
117.5°	231.7	216.3	200.9	216.3	231.7	235.6	313.9	418.3	470.5	568.8	765.2
120°	243.3	228.8	214.2	228.8	243.3	246.9	318.5	414.0	461.7	551.5	731.0
122.5°	256.6	242.1	227.4	242.1	256.6	260.3	325.2	411.7	455.0	535.9	697.5
125°	274.2	260.9	247.5	260.9	274.2	277.5	334.3	410.0	447.8	516.4	653.7
127.5°	290.7	277.2	263.8	277.2	290.7	294.1	343.3	408.9	441.7	500.6	618.5
130°	301.6	287.0	272.5	287.0	301.6	305.1	349.9	409.5	439.3	491.9	596.8
132.5°	310.6	296.0	281.6	296.0	310.6	314.1	355.2	410.0	437.3	484.3	578.3
135°	321.3	308.1	295.0	308.1	321.3	324.6	361.0	409.6	433.8	473.2	551.8
137.5°	334.7	321.7	308.6	321.7	334.7	338.0	369.8	412.1	433.2	466.5	532.9
140°	344.1	332.0	320.0	332.0	344.1	347.1	375.1	412.5	431.2	459.9	517.3
142.5°	351.0	339.8	328.7	339.8	351.0	353.8	379.6	414.0	431.2	456.4	506.9
145°	361.5	351.8	342.2	351.8	361.5	364.0	385.4	414.0	428.3	448.9	490.2
147.5°	374.4	364.9	355.5	364.9	374.4	376.7	393.9	416.9	428.3	444.6	477.0
150°	381.3	372.8	364.2	372.8	381.3	383.4	398.4	418.3	428.3	442.1	469.5
152.5°	386.1	379.8	373.3	379.8	386.1	387.8	401.3	419.3	428.3	440.0	463.5
155°	396.2	391.4	386.6	391.4	396.2	397.4	407.7	421.4	428.3	437.6	456.3
157.5°	405.9	401.2	396.5	401.2	405.9	407.1	414.2	423.5	428.3	435.6	450.0
160°	410.6	406.9	403.3	406.9	410.6	411.4	417.1	424.5	428.3	434.5	446.9
162.5°	415.4	412.7	410.0	412.7	415.4	416.1	420.2	425.6	428.3	433.5	444.0
165°	422.2	419.7	417.3	419.7	422.2	422.8	424.6	427.0	428.3	432.1	439.5
167.5°	426.3	425.1	423.9	425.1	426.3	426.6	428.1	430.1	431.2	433.6	438.6
170°	430.6	429.5	428.3	429.5	430.6	430.9	431.0	431.1	431.2	433.6	438.6
172.5°	431.1	430.9	430.6	430.9	431.1	431.2	431.2	431.2	431.2	433.1	437.0
175°	433.8	433.8	433.8	433.8	433.8	433.8	432.9	431.8	431.2	432.5	434.9
177.5°	433.8	433.8	433.8	433.8	433.8	433.8	433.1	432.3	431.8	432.8	434.7
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8

TEST NUMBER: P933879

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7	2060.7
2.5°	1988.6	1982.8	1990.5	1969.1	1990.5	1982.8	1988.6	2002.2	1990.5	1998.4	2006.1
5°	1744.9	1735.1	1704.0	1678.6	1704.0	1735.1	1744.9	1785.9	1805.3	1840.4	1887.2
7.5°	1559.7	1551.9	1544.1	1528.5	1544.1	1551.9	1559.7	1571.3	1590.9	1622.0	1657.2
10°	1518.7	1520.7	1532.4	1530.4	1532.4	1520.7	1518.7	1514.8	1509.0	1514.8	1536.3
12.5°	1624.0	1641.6	1705.9	1702.0	1705.9	1641.6	1624.0	1546.0	1493.4	1483.6	1487.5
15°	1744.9	1750.7	1764.4	1766.3	1764.4	1750.7	1744.9	1713.7	1555.7	1487.5	1466.1
17.5°	1756.6	1758.5	1768.2	1768.2	1768.2	1758.5	1756.6	1742.9	1690.3	1598.7	1477.8
20°	1746.8	1750.7	1770.3	1774.1	1770.3	1750.7	1746.8	1729.3	1700.0	1666.9	1575.3
22.5°	1742.9	1750.7	1766.3	1764.4	1766.3	1750.7	1742.9	1715.6	1690.3	1666.9	1629.9
25°	1723.5	1723.5	1725.4	1727.3	1725.4	1723.5	1723.5	1702.0	1651.3	1645.5	1624.0
27.5°	1682.5	1686.4	1698.1	1696.1	1698.1	1686.4	1682.5	1674.7	1620.1	1614.3	1598.7
30°	1645.5	1641.6	1631.8	1624.0	1631.8	1641.6	1645.5	1633.7	1579.2	1563.6	1567.5
32.5°	1583.1	1573.3	1563.6	1557.8	1563.6	1573.3	1583.1	1579.2	1538.2	1516.8	1520.7
35°	1509.0	1511.0	1509.0	1503.1	1509.0	1511.0	1509.0	1512.9	1487.5	1468.0	1466.1
37.5°	1456.3	1460.3	1458.2	1450.5	1458.2	1460.3	1456.3	1452.4	1417.4	1411.5	1415.4
40°	1401.8	1403.7	1401.8	1395.9	1401.8	1403.7	1401.8	1393.9	1345.3	1347.2	1360.8
42.5°	1349.1	1347.2	1341.3	1337.4	1341.3	1347.2	1349.1	1337.4	1275.0	1269.2	1294.5
45°	1288.7	1290.6	1278.9	1273.1	1278.9	1290.6	1288.7	1280.9	1216.6	1201.0	1218.5
47.5°	1228.2	1228.2	1218.5	1212.6	1218.5	1228.2	1228.2	1218.5	1150.3	1134.7	1144.4
50°	1163.9	1161.9	1148.3	1146.3	1148.3	1161.9	1163.9	1158.1	1086.0	1072.3	1072.3
52.5°	1089.8	1089.8	1091.8	1095.6	1091.8	1089.8	1089.8	1091.8	1027.4	1013.8	1009.9
55°	1025.5	1027.4	1041.1	1045.0	1041.1	1027.4	1025.5	1025.5	967.0	953.3	945.6
57.5°	959.2	959.2	968.9	968.9	968.9	959.2	959.2	955.3	898.7	887.0	883.1
60°	883.1	887.0	894.9	892.9	894.9	887.0	883.1	879.3	830.5	822.7	809.1
62.5°	803.2	807.2	809.1	805.1	809.1	807.2	803.2	791.6	762.3	756.4	738.9
65°	719.4	723.3	725.2	721.3	725.2	723.3	719.4	713.6	692.1	682.4	666.8
67.5°	633.6	631.7	629.8	637.5	629.8	631.7	633.6	625.8	612.2	604.4	583.0
70°	545.8	545.8	543.9	547.9	543.9	545.8	545.8	540.0	532.3	526.4	506.9
72.5°	452.3	450.4	458.1	452.3	458.1	450.4	452.3	450.4	446.4	440.6	421.1
75°	360.7	364.5	360.7	366.5	360.7	364.5	360.7	362.6	360.7	356.8	343.1
77.5°	274.9	278.8	274.9	274.9	274.9	278.8	274.9	276.8	276.8	276.8	265.1
80°	195.0	193.0	193.0	191.1	193.0	193.0	195.0	195.0	196.9	193.0	189.1
82.5°	124.8	122.9	122.9	126.7	122.9	122.9	124.8	126.7	122.9	122.9	122.9
85°	68.2	70.2	66.3	66.3	66.3	70.2	68.2	64.3	68.2	68.2	66.3
87.5°	25.4	23.4	23.4	23.4	23.4	23.4	25.4	27.3	27.3	27.3	29.3
90°	11.0	11.0	11.0	11.0	11.0	11.0	11.0	14.7	19.7	22.1	19.0
92.5°	55.3	53.1	44.4	35.6	44.4	53.1	55.3	78.4	109.2	124.6	109.4
95°	187.8	181.1	154.5	127.8	154.5	181.1	187.8	246.6	325.0	364.2	307.7
97.5°	433.5	420.8	370.2	319.4	370.2	420.8	433.5	470.7	520.3	545.1	450.7
100°	608.8	593.7	533.3	472.9	533.3	593.7	608.8	606.1	602.5	600.7	495.9
102.5°	758.4	745.5	693.7	642.0	693.7	745.5	758.4	711.1	648.0	616.4	510.2
105°	933.1	926.2	898.4	870.5	898.4	926.2	933.1	826.9	685.4	614.6	511.7
107.5°	1024.0	1025.7	1032.5	1039.2	1032.5	1025.7	1024.0	875.9	678.4	579.7	489.0
110°	1047.3	1054.6	1083.5	1112.5	1083.5	1054.6	1047.3	881.7	661.0	550.6	468.8

TEST NUMBER: P933879

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1032.5	1043.6	1088.1	1132.6	1088.1	1043.6	1032.5	863.0	637.1	524.1	451.2
115°	982.1	997.5	1059.2	1120.9	1059.2	997.5	982.1	818.8	601.2	492.3	430.9
117.5°	912.5	929.7	998.1	1066.5	998.1	929.7	912.5	765.2	568.8	470.5	418.3
120°	865.6	882.3	948.7	1015.2	948.7	882.3	865.6	731.0	551.5	461.7	414.0
122.5°	818.7	835.1	900.8	966.4	900.8	835.1	818.7	697.5	535.9	455.0	411.7
125°	756.7	771.8	832.2	892.6	832.2	771.8	756.7	653.7	516.4	447.8	410.0
127.5°	706.9	719.7	770.6	821.6	770.6	719.7	706.9	618.5	500.6	441.7	408.9
130°	675.5	687.3	734.4	781.5	734.4	687.3	675.5	596.8	491.9	439.3	409.5
132.5°	648.7	659.3	701.5	743.6	701.5	659.3	648.7	578.3	484.3	437.3	410.0
135°	610.9	620.0	656.3	692.6	656.3	620.0	610.9	551.8	473.2	433.8	409.6
137.5°	582.9	590.3	620.1	649.9	620.1	590.3	582.9	532.9	466.5	433.2	412.1
140°	560.5	567.4	595.3	623.1	595.3	567.4	560.5	517.3	459.9	431.2	412.5
142.5°	544.8	550.8	574.7	598.6	574.7	550.8	544.8	506.9	456.4	431.2	414.0
145°	521.1	525.7	543.8	561.9	543.8	525.7	521.1	490.2	448.9	428.3	414.0
147.5°	501.4	505.1	520.2	535.2	520.2	505.1	501.4	477.0	444.6	428.3	416.9
150°	490.0	493.0	505.2	517.3	505.2	493.0	490.0	469.5	442.1	428.3	418.3
152.5°	481.0	483.3	492.4	501.7	492.4	483.3	481.0	463.5	440.0	428.3	419.3
155°	470.3	471.8	477.8	483.9	477.8	471.8	470.3	456.3	437.6	428.3	421.4
157.5°	460.9	461.9	466.3	470.5	466.3	461.9	460.9	450.0	435.6	428.3	423.5
160°	456.2	456.8	459.3	461.7	459.3	456.8	456.2	446.9	434.5	428.3	424.5
162.5°	451.8	452.4	454.8	457.1	454.8	452.4	451.8	444.0	433.5	428.3	425.6
165°	445.2	445.7	448.3	450.7	448.3	445.7	445.2	439.5	432.1	428.3	427.0
167.5°	442.3	442.5	443.5	444.6	443.5	442.5	442.3	438.6	433.6	431.2	430.1
170°	442.3	442.3	442.3	442.3	442.3	442.3	442.3	438.6	433.6	431.2	431.1
172.5°	439.9	439.7	438.8	437.9	438.8	439.7	439.9	437.0	433.1	431.2	431.2
175°	436.7	436.7	436.7	436.7	436.7	436.7	436.7	434.9	432.5	431.2	431.8
177.5°	436.1	435.9	434.9	433.8	434.9	435.9	436.1	434.7	432.8	431.8	432.3
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8

TEST NUMBER: P933879

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2060.7	2060.7	2060.7	2060.7	2060.7
2.5°	2035.4	2045.1	2051.0	2058.7	2078.2
5°	1957.4	1994.4	2006.1	2035.4	2070.5
7.5°	1785.9	1898.9	1930.1	2000.3	2054.9
10°	1620.1	1733.2	1787.8	1953.5	2035.4
12.5°	1536.3	1602.5	1639.6	1871.6	2008.1
15°	1483.6	1530.4	1557.8	1762.4	1976.9
17.5°	1442.6	1475.9	1495.4	1655.2	1934.0
20°	1417.4	1433.0	1450.5	1577.2	1885.3
22.5°	1399.8	1390.0	1403.7	1522.6	1819.0
25°	1388.1	1351.1	1366.7	1479.8	1741.0
27.5°	1397.9	1316.0	1321.8	1440.7	1659.1
30°	1399.8	1273.1	1275.0	1399.8	1567.5
32.5°	1386.2	1228.2	1230.1	1349.1	1464.2
35°	1353.0	1175.6	1173.7	1290.6	1323.8
37.5°	1308.1	1119.1	1119.1	1226.3	1169.8
40°	1253.6	1062.5	1068.4	1142.5	1033.2
42.5°	1187.3	1002.0	1009.9	1031.3	931.9
45°	1115.1	943.6	949.4	871.4	853.9
47.5°	1035.2	883.1	885.1	723.3	828.6
50°	939.7	820.7	813.0	620.0	826.7
52.5°	855.8	752.5	729.2	561.4	750.6
55°	773.9	680.4	629.8	516.7	696.0
57.5°	701.8	586.8	538.1	464.0	684.3
60°	635.6	495.2	458.1	407.5	627.8
62.5°	581.0	426.9	419.2	368.5	569.3
65°	522.5	380.1	378.2	335.4	483.5
67.5°	466.0	348.9	347.0	304.2	368.5
70°	405.5	315.8	311.9	271.0	273.0
72.5°	343.1	278.8	274.9	243.7	226.2
75°	280.7	235.9	233.9	212.5	183.2
77.5°	220.4	187.1	191.1	171.6	134.5
80°	157.9	136.4	140.4	122.9	101.4
82.5°	105.2	89.7	93.6	78.0	68.2
85°	58.5	50.7	52.6	41.0	31.2
87.5°	27.3	23.4	23.4	15.6	9.8
90°	12.8	8.1	7.6	5.2	2.9
92.5°	79.0	56.2	51.3	31.4	11.6
95°	194.4	109.5	100.4	64.1	27.9
97.5°	261.8	120.3	112.3	80.3	48.4
100°	286.4	129.3	122.0	93.0	64.1
102.5°	297.7	138.3	131.5	104.5	77.4
105°	306.0	151.6	145.9	123.1	100.2
107.5°	307.6	171.5	166.2	144.8	123.5
110°	305.2	182.6	177.7	158.4	139.1

TEST NUMBER: P933879

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	305.3	195.9	191.4	173.0	154.7
115°	308.1	216.1	211.8	194.9	177.9
117.5°	313.9	235.6	231.7	216.3	200.9
120°	318.5	246.9	243.3	228.8	214.2
122.5°	325.2	260.3	256.6	242.1	227.4
125°	334.3	277.5	274.2	260.9	247.5
127.5°	343.3	294.1	290.7	277.2	263.8
130°	349.9	305.1	301.6	287.0	272.5
132.5°	355.2	314.1	310.6	296.0	281.6
135°	361.0	324.6	321.3	308.1	295.0
137.5°	369.8	338.0	334.7	321.7	308.6
140°	375.1	347.1	344.1	332.0	320.0
142.5°	379.6	353.8	351.0	339.8	328.7
145°	385.4	364.0	361.5	351.8	342.2
147.5°	393.9	376.7	374.4	364.9	355.5
150°	398.4	383.4	381.3	372.8	364.2
152.5°	401.3	387.8	386.1	379.8	373.3
155°	407.7	397.4	396.2	391.4	386.6
157.5°	414.2	407.1	405.9	401.2	396.5
160°	417.1	411.4	410.6	406.9	403.3
162.5°	420.2	416.1	415.4	412.7	410.0
165°	424.6	422.8	422.2	419.7	417.3
167.5°	428.1	426.6	426.3	425.1	423.9
170°	431.0	430.9	430.6	429.5	428.3
172.5°	431.2	431.2	431.1	430.9	430.6
175°	432.9	433.8	433.8	433.8	433.8
177.5°	433.1	433.8	433.8	433.8	433.8
180°	433.8	433.8	433.8	433.8	433.8

TEST NUMBER: P933879

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.57	13.59	13.38	14.42	15.45	15.42	16.44	16.23	17.27	18.31
	3H	13.06	13.97	13.88	14.82	15.88	16.78	17.70	17.61	18.54	19.60
	4H	13.26	14.12	14.10	14.97	16.04	17.24	18.10	18.08	18.96	20.03
	6H	13.38	14.18	14.24	15.04	16.12	17.54	18.34	18.39	19.19	20.28
	8H	13.39	14.15	14.25	15.03	16.11	17.62	18.38	18.48	19.26	20.34
	12H	13.37	14.09	14.23	14.96	16.07	17.67	18.39	18.54	19.26	20.37
4H	2H	13.63	14.49	14.47	15.34	16.41	15.85	16.71	16.69	17.56	18.63
	3H	14.67	15.39	15.53	16.27	17.36	17.37	18.10	18.23	18.98	20.06
	4H	14.95	15.61	15.82	16.49	17.60	17.91	18.57	18.78	19.45	20.56
	6H	15.08	15.65	15.97	16.56	17.67	18.29	18.86	19.18	19.77	20.88
	8H	15.09	15.62	15.98	16.52	17.65	18.41	18.94	19.30	19.84	20.97
	12H	15.07	15.55	15.98	16.46	17.60	18.48	18.95	19.38	19.87	21.01
8H	4H	15.42	15.95	16.31	16.85	17.98	18.05	18.58	18.94	19.48	20.61
	6H	15.69	16.13	16.60	17.07	18.20	18.50	18.94	19.42	19.88	21.01
	8H	15.73	16.12	16.66	17.05	18.20	18.66	19.04	19.58	19.98	21.12
	12H	15.72	16.07	16.65	16.99	18.19	18.77	19.11	19.70	20.03	21.23
12H	4H	15.43	15.91	16.34	16.83	17.96	18.02	18.50	18.93	19.42	20.55
	6H	15.75	16.14	16.68	17.07	18.22	18.50	18.89	19.42	19.82	20.97
	8H	15.83	16.17	16.76	17.09	18.29	18.67	19.01	19.60	19.94	21.13

END OF REPORT