

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934094

Luminaire Tested: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934094
REPORT IS A COMBINATION OF REPORTS P933684 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8893.5 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 77.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934094

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P934094

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	73	72	70
2	95	87	81	76	91	84	78	73	77	72	68	70	67	64	65	62	59
3	87	77	69	63	83	74	67	61	68	62	57	62	58	54	57	54	50
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43
5	73	61	52	46	70	58	51	45	54	47	42	50	44	40	46	41	38
6	67	55	46	40	64	53	45	39	49	42	37	45	39	35	42	37	33
7	62	50	41	35	59	48	40	34	44	38	33	41	35	31	38	33	30
8	58	45	37	31	55	44	36	31	40	34	29	38	32	28	35	30	26
9	54	41	33	28	52	40	33	27	37	31	26	35	29	25	32	27	24
10	51	38	30	25	48	37	30	25	34	28	24	32	27	23	30	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12557	12557	12557	12557
5°	12651	12676	12651	9967
10°	12566	12486	12566	8927
15°	12430	12216	12430	10201
20°	12170	11895	12170	10222
25°	11637	11428	11637	10005
30°	10950	11040	10950	9530
35°	9762	10549	9762	9007
40°	8134	9971	8134	8612
45°	7268	9295	7268	8158
50°	7722	8488	7722	7702
55°	7265	7619	7265	7439
60°	7489	6471	7489	6813
65°	6789	5349	6789	5979
70°	4700	4263	4700	5012
75°	4122	3151	4122	3773
80°	3321	2083	3321	2269
85°	1910	1103	1910	937

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 11139 cd/sqm

TEST NUMBER: P934094

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.3	2.7
10°-20°	693.7	7.8
20°-30°	1072.3	12.1
30°-40°	1280.1	14.4
40°-50°	1287.6	14.5
50°-60°	1120.3	12.6
60°-70°	794.3	8.9
70°-80°	420.3	4.7
80°-90°	105.8	1.2
90°-100°	141.0	1.6
100°-110°	370.6	4.2
110°-120°	384.3	4.3
120°-130°	308.3	3.5
130°-140°	241.9	2.7
140°-150°	185.7	2.1
150°-160°	133.7	1.5
160°-170°	81.8	0.9
170°-180°	27.6	0.3
0°-30°	2010.3	22.6
0°-40°	3290.3	37.0
0°-60°	5698.2	64.1
0°-90°	7018.6	78.9
90°-120°	895.9	10.1
90°-150°	1631.8	18.3
90°-180°	1875.0	21.1
0°-180°	8893.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2706	2706	2706	2706	2706	
5°	2719	2804	2719	2205	2719	258
15°	2596	2778	2596	2320	2596	731
25°	2286	2591	2286	2269	2286	1050
35°	1739	2312	1739	1974	1739	1076
45°	1122	1905	1122	1672	1122	898
55°	914	1406	914	1372	914	840
65°	635	848	635	947	635	607
75°	241	402	241	481	241	253
85°	41	102	41	87	41	55
90°	2	7	2	7	2	3
95°	19	85	19	85	19	21
105°	67	580	67	580	67	71
115°	119	747	119	747	119	117
125°	165	595	165	595	165	146
135°	197	462	197	462	197	152
145°	228	375	228	375	228	143
155°	258	323	258	323	258	118
165°	278	300	278	300	278	79
175°	289	291	289	291	289	27
180°	289	289	289	289	289	

TEST NUMBER: P934094

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5
2.5°	2729.6	2729.6	2744.9	2750.0	2750.0	2742.4	2734.7	2742.4	2765.4	2773.1	2770.6
5°	2719.3	2739.8	2767.9	2773.1	2778.2	2775.6	2770.6	2775.6	2801.3	2806.4	2808.9
7.5°	2698.9	2737.2	2773.1	2780.7	2788.5	2780.7	2778.2	2783.4	2808.9	2814.1	2814.1
10°	2673.2	2727.0	2767.9	2773.1	2780.7	2773.1	2773.1	2783.4	2808.9	2814.1	2816.6
12.5°	2637.3	2711.6	2750.0	2755.2	2765.4	2762.8	2760.3	2770.6	2796.1	2801.3	2801.3
15°	2596.4	2683.5	2719.3	2724.4	2742.4	2737.2	2737.2	2747.5	2775.6	2783.4	2780.7
17.5°	2540.0	2647.6	2688.6	2696.2	2709.0	2706.5	2709.0	2719.3	2744.9	2750.0	2752.6
20°	2476.1	2599.0	2647.6	2655.3	2668.1	2668.1	2668.1	2680.9	2706.5	2716.8	2716.8
22.5°	2389.0	2547.8	2599.0	2604.1	2619.4	2619.4	2624.5	2642.5	2665.5	2668.1	2668.1
25°	2286.5	2491.4	2534.9	2550.3	2565.7	2573.4	2581.0	2591.3	2599.0	2596.4	2599.0
27.5°	2179.0	2419.7	2476.1	2486.3	2506.8	2514.5	2524.7	2527.2	2529.9	2537.5	2532.4
30°	2058.6	2319.9	2404.4	2414.7	2447.9	2453.0	2442.8	2447.9	2460.7	2465.8	2471.0
32.5°	1923.0	2171.3	2330.2	2353.1	2383.8	2368.5	2365.9	2373.7	2394.1	2394.1	2399.2
35°	1738.6	2056.1	2261.0	2281.4	2304.5	2286.5	2296.8	2299.3	2312.2	2319.9	2317.3
37.5°	1536.3	1956.2	2189.3	2204.7	2222.6	2199.5	2214.8	2222.6	2232.8	2227.7	2227.7
40°	1357.1	1800.1	2104.8	2115.0	2130.3	2112.4	2127.8	2133.0	2138.1	2133.0	2130.3
42.5°	1223.9	1628.5	2015.1	2027.9	2017.7	2030.5	2035.7	2045.8	2038.2	2027.9	2027.9
45°	1121.5	1582.4	1917.8	1933.3	1917.8	1938.4	1946.0	1946.0	1923.0	1917.8	1915.3
47.5°	1088.3	1490.2	1820.6	1820.6	1812.9	1838.5	1851.3	1833.3	1810.3	1802.6	1802.6
50°	1085.7	1387.8	1687.4	1677.1	1713.0	1743.7	1730.9	1713.0	1695.1	1666.9	1666.9
52.5°	985.9	1262.3	1515.8	1554.3	1610.6	1628.5	1608.1	1590.1	1559.4	1546.6	1536.3
55°	914.2	1131.8	1359.7	1436.4	1495.4	1518.4	1480.0	1462.1	1416.0	1408.3	1403.2
57.5°	898.7	942.3	1216.3	1313.6	1385.3	1382.7	1359.7	1326.4	1288.0	1280.2	1277.7
60°	824.5	681.1	1062.6	1177.8	1252.1	1244.4	1223.9	1193.2	1157.4	1152.2	1147.1
62.5°	747.7	494.2	888.5	1019.1	1124.0	1121.5	1103.6	1057.5	1031.9	1019.1	1008.8
65°	635.0	414.8	632.5	847.6	998.7	1003.7	965.3	932.1	903.9	888.5	886.0
67.5°	483.9	338.0	427.6	706.7	878.3	873.2	824.5	809.1	773.3	765.6	750.2
70°	358.4	225.3	297.0	573.6	760.5	747.7	709.3	691.4	658.0	640.1	629.8
72.5°	297.0	181.8	217.6	445.5	640.1	624.8	591.5	571.0	542.8	527.4	517.3
75°	240.7	192.1	166.5	330.3	519.8	509.6	478.8	458.3	435.3	414.8	417.3
77.5°	176.6	179.3	133.1	243.2	412.2	396.9	379.0	353.4	343.1	322.7	322.7
80°	133.1	140.8	99.9	166.5	297.0	297.0	281.7	263.8	245.8	235.6	235.6
82.5°	89.6	89.6	74.2	104.9	202.3	194.6	184.4	179.3	169.0	163.9	163.9
85°	41.0	51.2	46.1	64.1	110.1	115.2	115.2	110.1	107.6	102.4	104.9
87.5°	12.8	23.1	28.2	35.9	56.3	58.9	61.4	61.4	61.4	64.1	64.1
90°	1.9	3.5	5.0	5.4	8.5	12.7	14.7	13.1	9.8	7.4	7.4
92.5°	7.8	20.9	34.2	37.5	52.7	73.0	83.0	72.8	52.3	36.9	35.5
95°	18.6	42.7	67.0	73.0	129.6	205.0	242.8	216.7	164.4	125.2	120.7
97.5°	32.3	53.6	74.8	80.1	174.5	300.4	363.4	346.9	313.9	289.1	280.6
100°	42.7	62.0	81.3	86.1	190.9	330.5	400.4	401.7	404.1	405.9	395.8
102.5°	51.6	69.7	87.7	92.2	198.5	340.1	411.0	432.0	474.0	505.6	497.0
105°	66.8	82.1	97.4	101.2	204.1	341.2	409.8	457.0	551.4	622.1	617.4
107.5°	82.3	96.5	110.8	114.3	205.0	326.0	386.4	452.2	583.9	682.7	683.8
110°	92.8	105.6	118.5	121.7	203.5	312.5	367.1	440.6	587.8	698.2	703.0

TEST NUMBER: P934094

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	103.1	115.3	127.5	130.6	203.6	300.8	349.4	424.7	575.3	688.3	695.7
115°	118.6	129.8	141.2	144.0	205.4	287.3	328.2	400.8	545.9	654.8	665.0
117.5°	133.9	144.2	154.5	157.1	209.3	278.9	313.7	379.2	510.1	608.3	619.8
120°	142.8	152.5	162.2	164.6	212.4	276.1	307.9	367.6	487.3	577.0	588.1
122.5°	151.6	161.3	171.1	173.5	216.9	274.5	303.4	357.3	465.0	545.8	556.8
125°	165.0	173.9	182.8	185.0	222.9	273.4	298.5	344.3	435.9	504.5	514.5
127.5°	175.9	184.8	193.8	196.0	228.9	272.6	294.5	333.8	412.4	471.3	479.8
130°	181.7	191.4	201.0	203.4	233.2	273.1	292.9	327.9	397.9	450.3	458.1
132.5°	187.7	197.4	207.0	209.4	236.8	273.4	291.6	322.9	385.5	432.5	439.5
135°	196.6	205.4	214.2	216.5	240.7	273.1	289.2	315.5	367.9	407.3	413.3
137.5°	205.7	214.4	223.2	225.4	246.5	274.7	288.9	311.0	355.3	388.6	393.5
140°	213.3	221.3	229.4	231.4	250.1	275.0	287.5	306.7	345.0	373.6	378.3
142.5°	219.2	226.6	234.0	235.9	253.1	276.1	287.5	304.4	338.0	363.2	367.2
145°	228.1	234.6	241.0	242.6	257.0	276.1	285.6	299.3	326.8	347.5	350.5
147.5°	237.0	243.3	249.6	251.2	262.6	277.9	285.6	296.4	318.0	334.2	336.7
150°	242.8	248.5	254.2	255.6	265.6	278.9	285.6	294.7	313.0	326.6	328.7
152.5°	248.8	253.1	257.5	258.5	267.5	279.6	285.6	293.3	308.9	320.6	322.2
155°	257.8	261.0	264.1	264.9	271.8	281.0	285.6	291.8	304.2	313.5	314.4
157.5°	264.3	267.4	270.5	271.3	276.1	282.4	285.6	290.4	300.0	307.3	307.9
160°	268.8	271.2	273.6	274.2	278.0	283.0	285.6	289.7	298.0	304.2	304.6
162.5°	273.3	275.1	276.8	277.3	280.0	283.7	285.6	289.1	296.0	301.3	301.6
165°	278.2	279.8	281.5	281.9	283.1	284.8	285.6	288.1	293.0	296.8	297.2
167.5°	282.7	283.4	284.2	284.4	285.5	286.8	287.5	289.1	292.4	294.9	295.1
170°	285.6	286.3	287.1	287.3	287.4	287.5	287.5	289.1	292.4	294.9	294.9
172.5°	287.1	287.3	287.5	287.5	287.5	287.5	287.5	288.8	291.4	293.3	293.1
175°	289.2	289.2	289.2	289.2	288.7	287.9	287.5	288.3	289.9	291.2	291.2
177.5°	289.2	289.2	289.2	289.2	288.8	288.2	287.9	288.6	289.8	290.8	290.6
180°	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2

TEST NUMBER: P934094

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5
2.5°	2775.6	2767.9	2775.6	2770.6	2773.1	2765.4	2742.4	2734.7	2742.4	2750.0	2750.0
5°	2808.9	2803.8	2808.9	2808.9	2806.4	2801.3	2775.6	2770.6	2775.6	2778.2	2773.1
7.5°	2819.2	2811.5	2819.2	2814.1	2814.1	2808.9	2783.4	2778.2	2780.7	2788.5	2780.7
10°	2819.2	2811.5	2819.2	2816.6	2814.1	2808.9	2783.4	2773.1	2773.1	2780.7	2773.1
12.5°	2806.4	2801.3	2806.4	2801.3	2801.3	2796.1	2770.6	2760.3	2762.8	2765.4	2755.2
15°	2785.9	2778.2	2785.9	2780.7	2783.4	2775.6	2747.5	2737.2	2737.2	2742.4	2724.4
17.5°	2755.2	2744.9	2755.2	2752.6	2750.0	2744.9	2719.3	2709.0	2706.5	2709.0	2696.2
20°	2719.3	2711.6	2719.3	2716.8	2716.8	2706.5	2680.9	2668.1	2668.1	2668.1	2655.3
22.5°	2663.0	2655.3	2663.0	2668.1	2668.1	2665.5	2642.5	2624.5	2619.4	2619.4	2604.1
25°	2599.0	2591.3	2599.0	2599.0	2596.4	2599.0	2591.3	2581.0	2573.4	2565.7	2550.3
27.5°	2537.5	2532.4	2537.5	2532.4	2537.5	2529.9	2527.2	2524.7	2514.5	2506.8	2486.3
30°	2476.1	2471.0	2476.1	2471.0	2465.8	2460.7	2447.9	2442.8	2453.0	2447.9	2414.7
32.5°	2399.2	2394.1	2399.2	2399.2	2394.1	2394.1	2373.7	2365.9	2368.5	2383.8	2353.1
35°	2319.9	2312.2	2319.9	2317.3	2319.9	2312.2	2299.3	2296.8	2286.5	2304.5	2281.4
37.5°	2227.7	2220.0	2227.7	2227.7	2227.7	2232.8	2222.6	2214.8	2199.5	2222.6	2204.7
40°	2133.0	2122.7	2133.0	2130.3	2133.0	2138.1	2133.0	2127.8	2112.4	2130.3	2115.0
42.5°	2025.4	2022.9	2025.4	2027.9	2027.9	2038.2	2045.8	2035.7	2030.5	2017.7	2027.9
45°	1910.2	1905.1	1910.2	1915.3	1917.8	1923.0	1946.0	1946.0	1938.4	1917.8	1933.3
47.5°	1787.2	1774.4	1787.2	1802.6	1802.6	1810.3	1833.3	1851.3	1838.5	1812.9	1820.6
50°	1656.7	1659.2	1656.7	1666.9	1666.9	1695.1	1713.0	1730.9	1743.7	1713.0	1677.1
52.5°	1528.7	1526.1	1528.7	1536.3	1546.6	1559.4	1590.1	1608.1	1628.5	1610.6	1554.3
55°	1400.6	1405.7	1400.6	1403.2	1408.3	1416.0	1462.1	1480.0	1518.4	1495.4	1436.4
57.5°	1272.6	1264.9	1272.6	1277.7	1280.2	1288.0	1326.4	1359.7	1382.7	1385.3	1313.6
60°	1124.0	1113.9	1124.0	1147.1	1152.2	1157.4	1193.2	1223.9	1244.4	1252.1	1177.8
62.5°	993.5	975.6	993.5	1008.8	1019.1	1031.9	1057.5	1103.6	1121.5	1124.0	1019.1
65°	855.2	847.6	855.2	886.0	888.5	903.9	932.1	965.3	1003.7	998.7	847.6
67.5°	729.8	729.8	729.8	750.2	765.6	773.3	809.1	824.5	873.2	878.3	706.7
70°	614.5	612.0	614.5	629.8	640.1	658.0	691.4	709.3	747.7	760.5	573.6
72.5°	504.5	501.8	504.5	517.3	527.4	542.8	571.0	591.5	624.8	640.1	445.5
75°	407.2	402.0	407.2	417.3	414.8	435.3	458.3	478.8	509.6	519.8	330.3
77.5°	312.4	312.4	312.4	322.7	322.7	343.1	353.4	379.0	396.9	412.2	243.2
80°	233.0	230.4	233.0	235.6	235.6	245.8	263.8	281.7	297.0	297.0	166.5
82.5°	163.9	158.7	163.9	163.9	163.9	169.0	179.3	184.4	194.6	202.3	104.9
85°	102.4	102.4	102.4	104.9	102.4	107.6	110.1	115.2	115.2	110.1	64.1
87.5°	66.6	64.1	66.6	64.1	64.1	61.4	61.4	61.4	58.9	56.3	35.9
90°	7.4	7.4	7.4	7.4	7.4	9.8	13.1	14.7	12.7	8.5	5.4
92.5°	29.6	23.6	29.6	35.5	36.9	52.3	72.8	83.0	73.0	52.7	37.5
95°	103.0	85.2	103.0	120.7	125.2	164.4	216.7	242.8	205.0	129.6	73.0
97.5°	246.7	212.9	246.7	280.6	289.1	313.9	346.9	363.4	300.4	174.5	80.1
100°	355.5	315.2	355.5	395.8	405.9	404.1	401.7	400.4	330.5	190.9	86.1
102.5°	462.5	428.0	462.5	497.0	505.6	474.0	432.0	411.0	340.1	198.5	92.2
105°	598.9	580.3	598.9	617.4	622.1	551.4	457.0	409.8	341.2	204.1	101.2
107.5°	688.3	692.7	688.3	683.8	682.7	583.9	452.2	386.4	326.0	205.0	114.3
110°	722.3	741.7	722.3	703.0	698.2	587.8	440.6	367.1	312.5	203.5	121.7

TEST NUMBER: P934094

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	725.4	755.0	725.4	695.7	688.3	575.3	424.7	349.4	300.8	203.6	130.6
115°	706.2	747.3	706.2	665.0	654.8	545.9	400.8	328.2	287.3	205.4	144.0
117.5°	665.4	711.1	665.4	619.8	608.3	510.1	379.2	313.7	278.9	209.3	157.1
120°	632.5	676.8	632.5	588.1	577.0	487.3	367.6	307.9	276.1	212.4	164.6
122.5°	600.5	644.2	600.5	556.8	545.8	465.0	357.3	303.4	274.5	216.9	173.5
125°	554.8	595.2	554.8	514.5	504.5	435.9	344.3	298.5	273.4	222.9	185.0
127.5°	513.8	547.8	513.8	479.8	471.3	412.4	333.8	294.5	272.6	228.9	196.0
130°	489.5	520.9	489.5	458.1	450.3	397.9	327.9	292.9	273.1	233.2	203.4
132.5°	467.6	495.7	467.6	439.5	432.5	385.5	322.9	291.6	273.4	236.8	209.4
135°	437.5	461.7	437.5	413.3	407.3	367.9	315.5	289.2	273.1	240.7	216.5
137.5°	413.4	433.2	413.4	393.5	388.6	355.3	311.0	288.9	274.7	246.5	225.4
140°	396.8	415.4	396.8	378.3	373.6	345.0	306.7	287.5	275.0	250.1	231.4
142.5°	383.1	399.0	383.1	367.2	363.2	338.0	304.4	287.5	276.1	253.1	235.9
145°	362.6	374.6	362.6	350.5	347.5	326.8	299.3	285.6	276.1	257.0	242.6
147.5°	346.7	356.8	346.7	336.7	334.2	318.0	296.4	285.6	277.9	262.6	251.2
150°	336.8	345.0	336.8	328.7	326.6	313.0	294.7	285.6	278.9	265.6	255.6
152.5°	328.3	334.4	328.3	322.2	320.6	308.9	293.3	285.6	279.6	267.5	258.5
155°	318.5	322.6	318.5	314.4	313.5	304.2	291.8	285.6	281.0	271.8	264.9
157.5°	310.9	313.7	310.9	307.9	307.3	300.0	290.4	285.6	282.4	276.1	271.3
160°	306.2	307.9	306.2	304.6	304.2	298.0	289.7	285.6	283.0	278.0	274.2
162.5°	303.2	304.8	303.2	301.6	301.3	296.0	289.1	285.6	283.7	280.0	277.3
165°	298.8	300.5	298.8	297.2	296.8	293.0	288.1	285.6	284.8	283.1	281.9
167.5°	295.7	296.4	295.7	295.1	294.9	292.4	289.1	287.5	286.8	285.5	284.4
170°	294.9	294.9	294.9	294.9	294.9	292.4	289.1	287.5	287.5	287.4	287.3
172.5°	292.5	292.0	292.5	293.1	293.3	291.4	288.8	287.5	287.5	287.5	287.5
175°	291.2	291.2	291.2	291.2	291.2	289.9	288.3	287.5	287.9	288.7	289.2
177.5°	289.9	289.2	289.9	290.6	290.8	289.8	288.6	287.9	288.2	288.8	289.2
180°	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2

TEST NUMBER: P934094

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5
2.5°	2744.9	2729.6	2729.6	2704.0	2693.7	2686.1	2673.2	2634.8	2624.5	2614.4	2629.7
5°	2767.9	2739.8	2719.3	2673.2	2634.8	2619.4	2570.8	2478.6	2417.2	2371.0	2345.5
7.5°	2773.1	2737.2	2698.9	2627.2	2534.9	2494.0	2345.5	2176.5	2130.3	2089.5	2063.8
10°	2767.9	2727.0	2673.2	2565.7	2348.0	2276.4	2127.8	2017.7	1989.6	1981.9	1989.6
12.5°	2750.0	2711.6	2637.3	2458.2	2153.4	2104.8	2017.7	1953.7	1948.6	1961.4	2030.5
15°	2719.3	2683.5	2596.4	2314.7	2045.8	2010.0	1948.6	1925.5	1953.7	2043.3	2250.7
17.5°	2688.6	2647.6	2540.0	2174.0	1964.0	1938.4	1894.8	1940.9	2099.6	2220.0	2289.2
20°	2647.6	2599.0	2476.1	2071.5	1905.1	1882.0	1861.5	2068.9	2189.3	2232.8	2271.2
22.5°	2599.0	2547.8	2389.0	1999.8	1843.6	1825.7	1838.5	2140.6	2189.3	2220.0	2253.3
25°	2534.9	2491.4	2286.5	1943.4	1795.0	1774.4	1823.1	2133.0	2161.1	2168.8	2235.4
27.5°	2476.1	2419.7	2179.0	1892.3	1736.1	1728.4	1836.0	2099.6	2120.2	2127.8	2199.5
30°	2404.4	2319.9	2058.6	1838.5	1674.6	1672.0	1838.5	2058.6	2053.6	2074.0	2145.8
32.5°	2330.2	2171.3	1923.0	1771.9	1615.7	1613.2	1820.6	1997.2	1992.1	2020.3	2074.0
35°	2261.0	2056.1	1738.6	1695.1	1541.5	1544.0	1777.0	1925.5	1928.1	1953.7	1987.0
37.5°	2189.3	1956.2	1536.3	1610.6	1469.8	1469.8	1718.1	1858.9	1853.9	1861.5	1907.6
40°	2104.8	1800.1	1357.1	1500.5	1403.2	1395.5	1646.4	1787.2	1769.3	1766.8	1830.8
42.5°	2015.1	1628.5	1223.9	1354.6	1326.4	1316.1	1559.4	1700.2	1666.9	1674.6	1756.5
45°	1917.8	1582.4	1121.5	1144.6	1247.0	1239.4	1464.6	1600.3	1577.3	1597.8	1682.3
47.5°	1820.6	1490.2	1088.3	950.0	1162.5	1159.9	1359.7	1503.0	1490.2	1510.8	1600.3
50°	1687.4	1387.8	1085.7	814.3	1067.7	1078.0	1234.2	1408.3	1408.3	1426.3	1520.9
52.5°	1515.8	1262.3	985.9	737.4	957.7	988.4	1124.0	1326.4	1331.5	1349.4	1433.9
55°	1359.7	1131.8	914.2	678.6	827.0	893.6	1016.6	1241.9	1252.1	1270.1	1346.8
57.5°	1216.3	942.3	898.7	609.4	706.7	770.7	921.8	1159.9	1165.0	1180.4	1254.7
60°	1062.6	681.1	824.5	535.2	601.7	650.4	834.7	1062.6	1080.5	1090.8	1154.9
62.5°	888.5	494.2	747.7	483.9	550.5	560.8	763.1	970.5	993.5	1001.2	1039.5
65°	632.5	414.8	635.0	440.4	496.7	499.3	686.2	875.7	896.2	909.0	937.1
67.5°	427.6	338.0	483.9	399.4	455.8	458.3	612.0	765.6	793.8	804.0	821.9
70°	297.0	225.3	358.4	355.9	409.7	414.8	532.6	665.7	691.4	699.0	709.3
72.5°	217.6	181.8	297.0	320.1	361.0	366.2	450.7	553.1	578.7	586.3	591.5
75°	166.5	192.1	240.7	279.1	307.3	309.8	368.7	450.7	468.6	473.7	476.3
77.5°	133.1	179.3	176.6	225.3	251.0	245.8	289.3	348.3	363.6	363.6	363.6
80°	99.9	140.8	133.1	161.3	184.4	179.3	207.4	248.4	253.5	258.6	256.0
82.5°	74.2	89.6	89.6	102.4	122.9	117.8	138.3	161.3	161.3	161.3	166.5
85°	46.1	51.2	41.0	53.8	69.1	66.6	76.8	87.0	89.6	89.6	84.5
87.5°	28.2	23.1	12.8	20.4	30.7	30.7	35.9	38.4	35.9	35.9	35.9
90°	5.0	3.5	1.9	3.5	5.0	5.4	8.5	12.7	14.7	13.1	9.8
92.5°	34.2	20.9	7.8	20.9	34.2	37.5	52.7	73.0	83.0	72.8	52.3
95°	67.0	42.7	18.6	42.7	67.0	73.0	129.6	205.0	242.8	216.7	164.4
97.5°	74.8	53.6	32.3	53.6	74.8	80.1	174.5	300.4	363.4	346.9	313.9
100°	81.3	62.0	42.7	62.0	81.3	86.1	190.9	330.5	400.4	401.7	404.1
102.5°	87.7	69.7	51.6	69.7	87.7	92.2	198.5	340.1	411.0	432.0	474.0
105°	97.4	82.1	66.8	82.1	97.4	101.2	204.1	341.2	409.8	457.0	551.4
107.5°	110.8	96.5	82.3	96.5	110.8	114.3	205.0	326.0	386.4	452.2	583.9
110°	118.5	105.6	92.8	105.6	118.5	121.7	203.5	312.5	367.1	440.6	587.8

TEST NUMBER: P934094

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	127.5	115.3	103.1	115.3	127.5	130.6	203.6	300.8	349.4	424.7	575.3
115°	141.2	129.8	118.6	129.8	141.2	144.0	205.4	287.3	328.2	400.8	545.9
117.5°	154.5	144.2	133.9	144.2	154.5	157.1	209.3	278.9	313.7	379.2	510.1
120°	162.2	152.5	142.8	152.5	162.2	164.6	212.4	276.1	307.9	367.6	487.3
122.5°	171.1	161.3	151.6	161.3	171.1	173.5	216.9	274.5	303.4	357.3	465.0
125°	182.8	173.9	165.0	173.9	182.8	185.0	222.9	273.4	298.5	344.3	435.9
127.5°	193.8	184.8	175.9	184.8	193.8	196.0	228.9	272.6	294.5	333.8	412.4
130°	201.0	191.4	181.7	191.4	201.0	203.4	233.2	273.1	292.9	327.9	397.9
132.5°	207.0	197.4	187.7	197.4	207.0	209.4	236.8	273.4	291.6	322.9	385.5
135°	214.2	205.4	196.6	205.4	214.2	216.5	240.7	273.1	289.2	315.5	367.9
137.5°	223.2	214.4	205.7	214.4	223.2	225.4	246.5	274.7	288.9	311.0	355.3
140°	229.4	221.3	213.3	221.3	229.4	231.4	250.1	275.0	287.5	306.7	345.0
142.5°	234.0	226.6	219.2	226.6	234.0	235.9	253.1	276.1	287.5	304.4	338.0
145°	241.0	234.6	228.1	234.6	241.0	242.6	257.0	276.1	285.6	299.3	326.8
147.5°	249.6	243.3	237.0	243.3	249.6	251.2	262.6	277.9	285.6	296.4	318.0
150°	254.2	248.5	242.8	248.5	254.2	255.6	265.6	278.9	285.6	294.7	313.0
152.5°	257.5	253.1	248.8	253.1	257.5	258.5	267.5	279.6	285.6	293.3	308.9
155°	264.1	261.0	257.8	261.0	264.1	264.9	271.8	281.0	285.6	291.8	304.2
157.5°	270.5	267.4	264.3	267.4	270.5	271.3	276.1	282.4	285.6	290.4	300.0
160°	273.6	271.2	268.8	271.2	273.6	274.2	278.0	283.0	285.6	289.7	298.0
162.5°	276.8	275.1	273.3	275.1	276.8	277.3	280.0	283.7	285.6	289.1	296.0
165°	281.5	279.8	278.2	279.8	281.5	281.9	283.1	284.8	285.6	288.1	293.0
167.5°	284.2	283.4	282.7	283.4	284.2	284.4	285.5	286.8	287.5	289.1	292.4
170°	287.1	286.3	285.6	286.3	287.1	287.3	287.4	287.5	287.5	289.1	292.4
172.5°	287.5	287.3	287.1	287.3	287.5	287.5	287.5	287.5	287.5	288.8	291.4
175°	289.2	289.2	289.2	289.2	289.2	289.2	288.7	287.9	287.5	288.3	289.9
177.5°	289.2	289.2	289.2	289.2	289.2	289.2	288.8	288.2	287.9	288.6	289.8
180°	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2

TEST NUMBER: P934094

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5
2.5°	2611.7	2604.1	2614.4	2586.2	2614.4	2604.1	2611.7	2629.7	2614.4	2624.5	2634.8
5°	2291.7	2278.9	2237.9	2204.7	2237.9	2278.9	2291.7	2345.5	2371.0	2417.2	2478.6
7.5°	2048.5	2038.2	2027.9	2007.5	2027.9	2038.2	2048.5	2063.8	2089.5	2130.3	2176.5
10°	1994.7	1997.2	2012.6	2010.0	2012.6	1997.2	1994.7	1989.6	1981.9	1989.6	2017.7
12.5°	2133.0	2156.0	2240.5	2235.4	2240.5	2156.0	2133.0	2030.5	1961.4	1948.6	1953.7
15°	2291.7	2299.3	2317.3	2319.9	2317.3	2299.3	2291.7	2250.7	2043.3	1953.7	1925.5
17.5°	2307.1	2309.6	2322.4	2322.4	2322.4	2309.6	2307.1	2289.2	2220.0	2099.6	1940.9
20°	2294.3	2299.3	2325.0	2330.2	2325.0	2299.3	2294.3	2271.2	2232.8	2189.3	2068.9
22.5°	2289.2	2299.3	2319.9	2317.3	2319.9	2299.3	2289.2	2253.3	2220.0	2189.3	2140.6
25°	2263.5	2263.5	2266.1	2268.6	2266.1	2263.5	2263.5	2235.4	2168.8	2161.1	2133.0
27.5°	2209.8	2214.8	2230.3	2227.7	2230.3	2214.8	2209.8	2199.5	2127.8	2120.2	2099.6
30°	2161.1	2156.0	2143.1	2133.0	2143.1	2156.0	2161.1	2145.8	2074.0	2053.6	2058.6
32.5°	2079.2	2066.4	2053.6	2045.8	2053.6	2066.4	2079.2	2074.0	2020.3	1992.1	1997.2
35°	1981.9	1984.4	1981.9	1974.1	1981.9	1984.4	1981.9	1987.0	1953.7	1928.1	1925.5
37.5°	1912.7	1917.8	1915.3	1905.1	1915.3	1917.8	1912.7	1907.6	1861.5	1853.9	1858.9
40°	1841.0	1843.6	1841.0	1833.3	1841.0	1843.6	1841.0	1830.8	1766.8	1769.3	1787.2
42.5°	1771.9	1769.3	1761.6	1756.5	1761.6	1769.3	1771.9	1756.5	1674.6	1666.9	1700.2
45°	1692.6	1695.1	1679.8	1672.0	1679.8	1695.1	1692.6	1682.3	1597.8	1577.3	1600.3
47.5°	1613.2	1613.2	1600.3	1592.6	1600.3	1613.2	1613.2	1600.3	1510.8	1490.2	1503.0
50°	1528.7	1526.1	1508.2	1505.6	1508.2	1526.1	1528.7	1520.9	1426.3	1408.3	1408.3
52.5°	1431.3	1431.3	1433.9	1439.1	1433.9	1431.3	1431.3	1433.9	1349.4	1331.5	1326.4
55°	1346.8	1349.4	1367.4	1372.5	1367.4	1349.4	1346.8	1346.8	1270.1	1252.1	1241.9
57.5°	1259.8	1259.8	1272.6	1272.6	1272.6	1259.8	1259.8	1254.7	1180.4	1165.0	1159.9
60°	1159.9	1165.0	1175.3	1172.8	1175.3	1165.0	1159.9	1154.9	1090.8	1080.5	1062.6
62.5°	1055.0	1060.1	1062.6	1057.5	1062.6	1060.1	1055.0	1039.5	1001.2	993.5	970.5
65°	944.9	950.0	952.5	947.4	952.5	950.0	944.9	937.1	909.0	896.2	875.7
67.5°	832.2	829.7	827.0	837.3	827.0	829.7	832.2	821.9	804.0	793.8	765.6
70°	717.0	717.0	714.3	719.5	714.3	717.0	717.0	709.3	699.0	691.4	665.7
72.5°	594.1	591.5	601.7	594.1	601.7	591.5	594.1	591.5	586.3	578.7	553.1
75°	473.7	478.8	473.7	481.4	473.7	478.8	473.7	476.3	473.7	468.6	450.7
77.5°	361.0	366.2	361.0	361.0	361.0	366.2	361.0	363.6	363.6	363.6	348.3
80°	256.0	253.5	253.5	251.0	253.5	253.5	256.0	256.0	258.6	253.5	248.4
82.5°	163.9	161.3	161.3	166.5	161.3	161.3	163.9	166.5	161.3	161.3	161.3
85°	89.6	92.2	87.0	87.0	87.0	92.2	89.6	84.5	89.6	89.6	87.0
87.5°	33.3	30.7	30.7	30.7	30.7	30.7	33.3	35.9	35.9	35.9	38.4
90°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	9.8	13.1	14.7	12.7
92.5°	36.9	35.5	29.6	23.6	29.6	35.5	36.9	52.3	72.8	83.0	73.0
95°	125.2	120.7	103.0	85.2	103.0	120.7	125.2	164.4	216.7	242.8	205.0
97.5°	289.1	280.6	246.7	212.9	246.7	280.6	289.1	313.9	346.9	363.4	300.4
100°	405.9	395.8	355.5	315.2	355.5	395.8	405.9	404.1	401.7	400.4	330.5
102.5°	505.6	497.0	462.5	428.0	462.5	497.0	505.6	474.0	432.0	411.0	340.1
105°	622.1	617.4	598.9	580.3	598.9	617.4	622.1	551.4	457.0	409.8	341.2
107.5°	682.7	683.8	688.3	692.7	688.3	683.8	682.7	583.9	452.2	386.4	326.0
110°	698.2	703.0	722.3	741.7	722.3	703.0	698.2	587.8	440.6	367.1	312.5

TEST NUMBER: P934094

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	688.3	695.7	725.4	755.0	725.4	695.7	688.3	575.3	424.7	349.4	300.8
115°	654.8	665.0	706.2	747.3	706.2	665.0	654.8	545.9	400.8	328.2	287.3
117.5°	608.3	619.8	665.4	711.1	665.4	619.8	608.3	510.1	379.2	313.7	278.9
120°	577.0	588.1	632.5	676.8	632.5	588.1	577.0	487.3	367.6	307.9	276.1
122.5°	545.8	556.8	600.5	644.2	600.5	556.8	545.8	465.0	357.3	303.4	274.5
125°	504.5	514.5	554.8	595.2	554.8	514.5	504.5	435.9	344.3	298.5	273.4
127.5°	471.3	479.8	513.8	547.8	513.8	479.8	471.3	412.4	333.8	294.5	272.6
130°	450.3	458.1	489.5	520.9	489.5	458.1	450.3	397.9	327.9	292.9	273.1
132.5°	432.5	439.5	467.6	495.7	467.6	439.5	432.5	385.5	322.9	291.6	273.4
135°	407.3	413.3	437.5	461.7	437.5	413.3	407.3	367.9	315.5	289.2	273.1
137.5°	388.6	393.5	413.4	433.2	413.4	393.5	388.6	355.3	311.0	288.9	274.7
140°	373.6	378.3	396.8	415.4	396.8	378.3	373.6	345.0	306.7	287.5	275.0
142.5°	363.2	367.2	383.1	399.0	383.1	367.2	363.2	338.0	304.4	287.5	276.1
145°	347.5	350.5	362.6	374.6	362.6	350.5	347.5	326.8	299.3	285.6	276.1
147.5°	334.2	336.7	346.7	356.8	346.7	336.7	334.2	318.0	296.4	285.6	277.9
150°	326.6	328.7	336.8	345.0	336.8	328.7	326.6	313.0	294.7	285.6	278.9
152.5°	320.6	322.2	328.3	334.4	328.3	322.2	320.6	308.9	293.3	285.6	279.6
155°	313.5	314.4	318.5	322.6	318.5	314.4	313.5	304.2	291.8	285.6	281.0
157.5°	307.3	307.9	310.9	313.7	310.9	307.9	307.3	300.0	290.4	285.6	282.4
160°	304.2	304.6	306.2	307.9	306.2	304.6	304.2	298.0	289.7	285.6	283.0
162.5°	301.3	301.6	303.2	304.8	303.2	301.6	301.3	296.0	289.1	285.6	283.7
165°	296.8	297.2	298.8	300.5	298.8	297.2	296.8	293.0	288.1	285.6	284.8
167.5°	294.9	295.1	295.7	296.4	295.7	295.1	294.9	292.4	289.1	287.5	286.8
170°	294.9	294.9	294.9	294.9	294.9	294.9	294.9	292.4	289.1	287.5	287.5
172.5°	293.3	293.1	292.5	292.0	292.5	293.1	293.3	291.4	288.8	287.5	287.5
175°	291.2	291.2	291.2	291.2	291.2	291.2	291.2	289.9	288.3	287.5	287.9
177.5°	290.8	290.6	289.9	289.2	289.9	290.6	290.8	289.8	288.6	287.9	288.2
180°	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2

TEST NUMBER: P934094

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2706.5	2706.5	2706.5	2706.5	2706.5
2.5°	2673.2	2686.1	2693.7	2704.0	2729.6
5°	2570.8	2619.4	2634.8	2673.2	2719.3
7.5°	2345.5	2494.0	2534.9	2627.2	2698.9
10°	2127.8	2276.4	2348.0	2565.7	2673.2
12.5°	2017.7	2104.8	2153.4	2458.2	2637.3
15°	1948.6	2010.0	2045.8	2314.7	2596.4
17.5°	1894.8	1938.4	1964.0	2174.0	2540.0
20°	1861.5	1882.0	1905.1	2071.5	2476.1
22.5°	1838.5	1825.7	1843.6	1999.8	2389.0
25°	1823.1	1774.4	1795.0	1943.4	2286.5
27.5°	1836.0	1728.4	1736.1	1892.3	2179.0
30°	1838.5	1672.0	1674.6	1838.5	2058.6
32.5°	1820.6	1613.2	1615.7	1771.9	1923.0
35°	1777.0	1544.0	1541.5	1695.1	1738.6
37.5°	1718.1	1469.8	1469.8	1610.6	1536.3
40°	1646.4	1395.5	1403.2	1500.5	1357.1
42.5°	1559.4	1316.1	1326.4	1354.6	1223.9
45°	1464.6	1239.4	1247.0	1144.6	1121.5
47.5°	1359.7	1159.9	1162.5	950.0	1088.3
50°	1234.2	1078.0	1067.7	814.3	1085.7
52.5°	1124.0	988.4	957.7	737.4	985.9
55°	1016.6	893.6	827.0	678.6	914.2
57.5°	921.8	770.7	706.7	609.4	898.7
60°	834.7	650.4	601.7	535.2	824.5
62.5°	763.1	560.8	550.5	483.9	747.7
65°	686.2	499.3	496.7	440.4	635.0
67.5°	612.0	458.3	455.8	399.4	483.9
70°	532.6	414.8	409.7	355.9	358.4
72.5°	450.7	366.2	361.0	320.1	297.0
75°	368.7	309.8	307.3	279.1	240.7
77.5°	289.3	245.8	251.0	225.3	176.6
80°	207.4	179.3	184.4	161.3	133.1
82.5°	138.3	117.8	122.9	102.4	89.6
85°	76.8	66.6	69.1	53.8	41.0
87.5°	35.9	30.7	30.7	20.4	12.8
90°	8.5	5.4	5.0	3.5	1.9
92.5°	52.7	37.5	34.2	20.9	7.8
95°	129.6	73.0	67.0	42.7	18.6
97.5°	174.5	80.1	74.8	53.6	32.3
100°	190.9	86.1	81.3	62.0	42.7
102.5°	198.5	92.2	87.7	69.7	51.6
105°	204.1	101.2	97.4	82.1	66.8
107.5°	205.0	114.3	110.8	96.5	82.3
110°	203.5	121.7	118.5	105.6	92.8



TEST NUMBER: P934094

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	203.6	130.6	127.5	115.3	103.1
115°	205.4	144.0	141.2	129.8	118.6
117.5°	209.3	157.1	154.5	144.2	133.9
120°	212.4	164.6	162.2	152.5	142.8
122.5°	216.9	173.5	171.1	161.3	151.6
125°	222.9	185.0	182.8	173.9	165.0
127.5°	228.9	196.0	193.8	184.8	175.9
130°	233.2	203.4	201.0	191.4	181.7
132.5°	236.8	209.4	207.0	197.4	187.7
135°	240.7	216.5	214.2	205.4	196.6
137.5°	246.5	225.4	223.2	214.4	205.7
140°	250.1	231.4	229.4	221.3	213.3
142.5°	253.1	235.9	234.0	226.6	219.2
145°	257.0	242.6	241.0	234.6	228.1
147.5°	262.6	251.2	249.6	243.3	237.0
150°	265.6	255.6	254.2	248.5	242.8
152.5°	267.5	258.5	257.5	253.1	248.8
155°	271.8	264.9	264.1	261.0	257.8
157.5°	276.1	271.3	270.5	267.4	264.3
160°	278.0	274.2	273.6	271.2	268.8
162.5°	280.0	277.3	276.8	275.1	273.3
165°	283.1	281.9	281.5	279.8	278.2
167.5°	285.5	284.4	284.2	283.4	282.7
170°	287.4	287.3	287.1	286.3	285.6
172.5°	287.5	287.5	287.5	287.3	287.1
175°	288.7	289.2	289.2	289.2	289.2
177.5°	288.8	289.2	289.2	289.2	289.2
180°	289.2	289.2	289.2	289.2	289.2

TEST NUMBER: P934094

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.93	17.13	16.59	17.81	18.60	18.77	19.97	19.43	20.65	21.44
	3H	16.43	17.51	17.11	18.20	19.02	20.14	21.22	20.82	21.91	22.73
	4H	16.64	17.66	17.34	18.36	19.19	20.60	21.62	21.30	22.32	23.15
	6H	16.78	17.71	17.49	18.42	19.27	20.91	21.85	21.62	22.56	23.41
	8H	16.79	17.68	17.51	18.41	19.26	20.99	21.89	21.71	22.62	23.47
	12H	16.77	17.62	17.50	18.35	19.23	21.04	21.90	21.77	22.62	23.50
4H	2H	17.01	18.02	17.71	18.72	19.56	19.22	20.24	19.92	20.93	21.77
	3H	18.07	18.91	18.78	19.65	20.50	20.76	21.61	21.47	22.34	23.20
	4H	18.36	19.12	19.08	19.86	20.75	21.30	22.07	22.03	22.81	23.69
	6H	18.50	19.17	19.25	19.93	20.82	21.69	22.35	22.43	23.12	24.01
	8H	18.51	19.14	19.26	19.90	20.80	21.80	22.43	22.55	23.19	24.09
	12H	18.50	19.06	19.27	19.84	20.75	21.88	22.44	22.65	23.22	24.13
8H	4H	18.84	19.46	19.59	20.22	21.12	21.45	22.08	22.20	22.84	23.74
	6H	19.11	19.63	19.89	20.43	21.34	21.91	22.42	22.69	23.22	24.13
	8H	19.16	19.62	19.95	20.42	21.34	22.06	22.52	22.85	23.32	24.25
	12H	19.16	19.56	19.95	20.36	21.34	22.18	22.58	22.97	23.38	24.36
12H	4H	18.86	19.42	19.63	20.20	21.11	21.43	21.99	22.20	22.78	23.69
	6H	19.18	19.64	19.97	20.44	21.36	21.91	22.37	22.70	23.17	24.09
	8H	19.26	19.66	20.05	20.46	21.44	22.08	22.49	22.88	23.28	24.26

END OF REPORT