

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934494

Luminaire Tested: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934494
REPORT IS A COMBINATION OF REPORTS P933700 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10878.0 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 90.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934494

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P934494

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	65		
1	101	97	93	89	95	91	88	84	80	78	75	71	69	67	62	60	59	55		
2	92	85	78	73	86	80	74	69	70	66	63	62	59	56	54	52	50	46		
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42	39		
4	77	66	58	52	72	62	55	49	55	49	45	49	44	41	43	39	36	33		
5	71	59	50	44	66	56	48	42	49	43	39	44	39	35	39	35	32	29		
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25		
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25	22		
8	56	43	35	30	52	41	34	29	37	31	27	33	28	24	29	25	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18		
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12557	12557	12557	12557
5°	12651	12676	12651	9967
10°	12566	12486	12566	8927
15°	12430	12216	12430	10201
20°	12170	11895	12170	10222
25°	11637	11428	11637	10005
30°	10950	11040	10950	9530
35°	9762	10549	9762	9007
40°	8134	9971	8134	8612
45°	7268	9295	7268	8158
50°	7722	8488	7722	7702
55°	7265	7619	7265	7439
60°	7489	6471	7489	6813
65°	6789	5349	6789	5979
70°	4700	4263	4700	5012
75°	4122	3151	4122	3773
80°	3321	2083	3321	2269
85°	1910	1103	1910	937

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 11139 cd/sqm

TEST NUMBER: P934494

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.3	2.2
10°-20°	693.7	6.4
20°-30°	1072.3	9.9
30°-40°	1280.1	11.8
40°-50°	1287.6	11.8
50°-60°	1120.3	10.3
60°-70°	794.3	7.3
70°-80°	420.3	3.9
80°-90°	106.9	1.0
90°-100°	290.1	2.7
100°-110°	762.7	7.0
110°-120°	790.9	7.3
120°-130°	634.4	5.8
130°-140°	497.8	4.6
140°-150°	382.1	3.5
150°-160°	275.1	2.5
160°-170°	168.3	1.5
170°-180°	56.9	0.5
0°-30°	2010.3	18.5
0°-40°	3290.3	30.2
0°-60°	5698.2	52.4
0°-90°	7019.8	64.5
90°-120°	1843.7	16.9
90°-150°	3357.9	30.9
90°-180°	3858.0	35.5
0°-180°	10878.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2706	2706	2706	2706	2706	
5°	2719	2804	2719	2205	2719	258
15°	2596	2778	2596	2320	2596	731
25°	2286	2591	2286	2269	2286	1050
35°	1739	2312	1739	1974	1739	1076
45°	1122	1905	1122	1672	1122	898
55°	914	1406	914	1372	914	840
65°	635	848	635	947	635	607
75°	241	402	241	481	241	253
85°	41	102	41	87	41	55
90°	4	15	4	15	4	5
95°	38	175	38	175	38	43
105°	137	1194	137	1194	137	146
115°	244	1538	244	1538	244	241
125°	340	1225	340	1225	340	301
135°	405	950	405	950	405	313
145°	469	771	469	771	469	294
155°	530	664	530	664	530	244
165°	572	618	572	618	572	162
175°	595	599	595	599	595	56
180°	595	595	595	595	595	

TEST NUMBER: P934494

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5
2.5°	2729.6	2729.6	2744.9	2750.0	2750.0	2742.4	2734.7	2742.4	2765.4	2773.1	2770.6
5°	2719.3	2739.8	2767.9	2773.1	2778.2	2775.6	2770.6	2775.6	2801.3	2806.4	2808.9
7.5°	2698.9	2737.2	2773.1	2780.7	2788.5	2780.7	2778.2	2783.4	2808.9	2814.1	2814.1
10°	2673.2	2727.0	2767.9	2773.1	2780.7	2773.1	2773.1	2783.4	2808.9	2814.1	2816.6
12.5°	2637.3	2711.6	2750.0	2755.2	2765.4	2762.8	2760.3	2770.6	2796.1	2801.3	2801.3
15°	2596.4	2683.5	2719.3	2724.4	2742.4	2737.2	2737.2	2747.5	2775.6	2783.4	2780.7
17.5°	2540.0	2647.6	2688.6	2696.2	2709.0	2706.5	2709.0	2719.3	2744.9	2750.0	2752.6
20°	2476.1	2599.0	2647.6	2655.3	2668.1	2668.1	2668.1	2680.9	2706.5	2716.8	2716.8
22.5°	2389.0	2547.8	2599.0	2604.1	2619.4	2619.4	2624.5	2642.5	2665.5	2668.1	2668.1
25°	2286.5	2491.4	2534.9	2550.3	2565.7	2573.4	2581.0	2591.3	2599.0	2596.4	2599.0
27.5°	2179.0	2419.7	2476.1	2486.3	2506.8	2514.5	2524.7	2527.2	2529.9	2537.5	2532.4
30°	2058.6	2319.9	2404.4	2414.7	2447.9	2453.0	2442.8	2447.9	2460.7	2465.8	2471.0
32.5°	1923.0	2171.3	2330.2	2353.1	2383.8	2368.5	2365.9	2373.7	2394.1	2394.1	2399.2
35°	1738.6	2056.1	2261.0	2281.4	2304.5	2286.5	2296.8	2299.3	2312.2	2319.9	2317.3
37.5°	1536.3	1956.2	2189.3	2204.7	2222.6	2199.5	2214.8	2222.6	2232.8	2227.7	2227.7
40°	1357.1	1800.1	2104.8	2115.0	2130.3	2112.4	2127.8	2133.0	2138.1	2133.0	2130.3
42.5°	1223.9	1628.5	2015.1	2027.9	2017.7	2030.5	2035.7	2045.8	2038.2	2027.9	2027.9
45°	1121.5	1582.4	1917.8	1933.3	1917.8	1938.4	1946.0	1946.0	1923.0	1917.8	1915.3
47.5°	1088.3	1490.2	1820.6	1820.6	1812.9	1838.5	1851.3	1833.3	1810.3	1802.6	1802.6
50°	1085.7	1387.8	1687.4	1677.1	1713.0	1743.7	1730.9	1713.0	1695.1	1666.9	1666.9
52.5°	985.9	1262.3	1515.8	1554.3	1610.6	1628.5	1608.1	1590.1	1559.4	1546.6	1536.3
55°	914.2	1131.8	1359.7	1436.4	1495.4	1518.4	1480.0	1462.1	1416.0	1408.3	1403.2
57.5°	898.7	942.3	1216.3	1313.6	1385.3	1382.7	1359.7	1326.4	1288.0	1280.2	1277.7
60°	824.5	681.1	1062.6	1177.8	1252.1	1244.4	1223.9	1193.2	1157.4	1152.2	1147.1
62.5°	747.7	494.2	888.5	1019.1	1124.0	1121.5	1103.6	1057.5	1031.9	1019.1	1008.8
65°	635.0	414.8	632.5	847.6	998.7	1003.7	965.3	932.1	903.9	888.5	886.0
67.5°	483.9	338.0	427.6	706.7	878.3	873.2	824.5	809.1	773.3	765.6	750.2
70°	358.4	225.3	297.0	573.6	760.5	747.7	709.3	691.4	658.0	640.1	629.8
72.5°	297.0	181.8	217.6	445.5	640.1	624.8	591.5	571.0	542.8	527.4	517.3
75°	240.7	192.1	166.5	330.3	519.8	509.6	478.8	458.3	435.3	414.8	417.3
77.5°	176.6	179.3	133.1	243.2	412.2	396.9	379.0	353.4	343.1	322.7	322.7
80°	133.1	140.8	99.9	166.5	297.0	297.0	281.7	263.8	245.8	235.6	235.6
82.5°	89.6	89.6	74.2	104.9	202.3	194.6	184.4	179.3	169.0	163.9	163.9
85°	41.0	51.2	46.1	64.1	110.1	115.2	115.2	110.1	107.6	102.4	104.9
87.5°	12.8	23.1	28.2	35.9	56.3	58.9	61.4	61.4	61.4	64.1	64.1
90°	4.0	7.2	10.4	11.1	17.5	26.1	30.3	26.9	20.3	15.2	15.2
92.5°	16.0	43.1	70.3	77.1	108.4	150.1	170.9	149.8	107.6	75.9	72.9
95°	38.4	88.1	137.8	150.2	266.7	422.0	499.7	445.9	338.4	257.7	248.5
97.5°	66.3	110.1	154.0	164.9	359.2	618.2	747.8	713.8	645.7	594.8	577.3
100°	87.9	127.6	167.3	177.3	392.9	680.3	824.0	826.6	831.5	835.2	814.4
102.5°	106.3	143.4	180.4	189.7	408.3	699.9	845.6	889.0	975.6	1040.5	1022.8
105°	137.4	168.8	200.3	208.1	419.9	702.1	843.2	940.3	1134.6	1280.2	1270.6
107.5°	169.4	198.6	227.9	235.3	421.9	670.8	795.3	930.7	1201.7	1404.9	1407.2
110°	190.9	217.3	243.9	250.5	418.8	643.1	755.3	906.8	1209.6	1436.7	1446.7

TEST NUMBER: P934494

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	212.1	237.3	262.5	268.8	418.9	619.0	719.0	873.9	1183.9	1416.4	1431.7
115°	244.1	267.3	290.6	296.4	422.8	591.3	675.5	824.8	1123.4	1347.3	1368.4
117.5°	275.6	296.7	317.8	323.2	430.6	573.8	645.5	780.2	1049.7	1251.9	1275.3
120°	294.0	313.9	333.8	338.8	437.0	568.0	633.5	756.6	1002.8	1187.5	1210.3
122.5°	311.9	332.0	352.0	357.1	446.1	564.9	624.3	735.2	957.0	1123.3	1145.7
125°	339.5	357.8	376.1	380.6	458.5	562.4	614.3	708.5	896.9	1038.2	1058.9
127.5°	361.9	380.3	398.7	403.4	470.9	561.0	605.9	686.8	848.6	969.9	987.3
130°	373.8	393.7	413.7	418.6	479.9	561.8	602.7	674.7	818.7	926.7	942.8
132.5°	386.2	406.1	426.1	431.0	487.3	562.4	600.0	664.4	793.3	889.9	904.4
135°	404.7	422.8	440.8	445.4	495.3	561.8	595.2	649.1	757.1	838.0	850.5
137.5°	423.5	441.4	459.3	463.8	507.3	565.3	594.4	640.0	731.3	799.7	809.9
140°	439.0	455.5	472.0	476.2	514.6	565.9	591.6	631.0	709.8	768.9	778.4
142.5°	451.0	466.2	481.5	485.3	520.7	567.9	591.6	626.2	695.5	747.4	755.6
145°	469.4	482.7	496.0	499.3	528.8	568.0	587.6	615.9	672.6	715.0	721.2
147.5°	487.7	500.7	513.7	516.9	540.4	571.9	587.6	609.9	654.4	687.8	692.9
150°	499.7	511.4	523.2	526.1	546.6	573.9	587.6	606.4	644.1	672.3	676.5
152.5°	512.1	521.0	529.8	532.1	550.6	575.3	587.6	603.7	635.8	659.9	663.1
155°	530.4	537.0	543.6	545.3	559.4	578.2	587.6	600.4	625.9	645.1	647.2
157.5°	544.0	550.4	556.8	558.4	568.1	581.1	587.6	597.5	617.3	632.3	633.7
160°	553.2	558.2	563.2	564.4	572.2	582.5	587.6	596.1	613.1	625.9	626.7
162.5°	562.4	566.2	569.9	570.8	576.5	583.9	587.6	594.8	609.2	620.0	620.7
165°	572.4	575.8	579.1	579.9	582.5	585.9	587.6	592.7	603.0	610.8	611.6
167.5°	581.6	583.1	584.8	585.2	587.3	590.1	591.6	595.0	601.7	606.8	607.2
170°	587.6	589.2	590.8	591.2	591.3	591.5	591.6	595.0	601.7	606.8	606.8
172.5°	590.8	591.2	591.5	591.6	591.6	591.6	591.6	594.3	599.6	603.6	603.3
175°	595.2	595.2	595.2	595.2	594.0	592.3	591.6	593.2	596.6	599.1	599.1
177.5°	595.2	595.2	595.2	595.2	594.2	592.9	592.3	593.7	596.3	598.4	598.0
180°	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2

TEST NUMBER: P934494

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5
2.5°	2775.6	2767.9	2775.6	2770.6	2773.1	2765.4	2742.4	2734.7	2742.4	2750.0	2750.0
5°	2808.9	2803.8	2808.9	2808.9	2806.4	2801.3	2775.6	2770.6	2775.6	2778.2	2773.1
7.5°	2819.2	2811.5	2819.2	2814.1	2814.1	2808.9	2783.4	2778.2	2780.7	2788.5	2780.7
10°	2819.2	2811.5	2819.2	2816.6	2814.1	2808.9	2783.4	2773.1	2773.1	2780.7	2773.1
12.5°	2806.4	2801.3	2806.4	2801.3	2801.3	2796.1	2770.6	2760.3	2762.8	2765.4	2755.2
15°	2785.9	2778.2	2785.9	2780.7	2783.4	2775.6	2747.5	2737.2	2737.2	2742.4	2724.4
17.5°	2755.2	2744.9	2755.2	2752.6	2750.0	2744.9	2719.3	2709.0	2706.5	2709.0	2696.2
20°	2719.3	2711.6	2719.3	2716.8	2716.8	2706.5	2680.9	2668.1	2668.1	2668.1	2655.3
22.5°	2663.0	2655.3	2663.0	2668.1	2668.1	2665.5	2642.5	2624.5	2619.4	2619.4	2604.1
25°	2599.0	2591.3	2599.0	2599.0	2596.4	2599.0	2591.3	2581.0	2573.4	2565.7	2550.3
27.5°	2537.5	2532.4	2537.5	2532.4	2537.5	2529.9	2527.2	2524.7	2514.5	2506.8	2486.3
30°	2476.1	2471.0	2476.1	2471.0	2465.8	2460.7	2447.9	2442.8	2453.0	2447.9	2414.7
32.5°	2399.2	2394.1	2399.2	2399.2	2394.1	2394.1	2373.7	2365.9	2368.5	2383.8	2353.1
35°	2319.9	2312.2	2319.9	2317.3	2319.9	2312.2	2299.3	2296.8	2286.5	2304.5	2281.4
37.5°	2227.7	2220.0	2227.7	2227.7	2227.7	2232.8	2222.6	2214.8	2199.5	2222.6	2204.7
40°	2133.0	2122.7	2133.0	2130.3	2133.0	2138.1	2133.0	2127.8	2112.4	2130.3	2115.0
42.5°	2025.4	2022.9	2025.4	2027.9	2027.9	2038.2	2045.8	2035.7	2030.5	2017.7	2027.9
45°	1910.2	1905.1	1910.2	1915.3	1917.8	1923.0	1946.0	1946.0	1938.4	1917.8	1933.3
47.5°	1787.2	1774.4	1787.2	1802.6	1802.6	1810.3	1833.3	1851.3	1838.5	1812.9	1820.6
50°	1656.7	1659.2	1656.7	1666.9	1666.9	1695.1	1713.0	1730.9	1743.7	1713.0	1677.1
52.5°	1528.7	1526.1	1528.7	1536.3	1546.6	1559.4	1590.1	1608.1	1628.5	1610.6	1554.3
55°	1400.6	1405.7	1400.6	1403.2	1408.3	1416.0	1462.1	1480.0	1518.4	1495.4	1436.4
57.5°	1272.6	1264.9	1272.6	1277.7	1280.2	1288.0	1326.4	1359.7	1382.7	1385.3	1313.6
60°	1124.0	1113.9	1124.0	1147.1	1152.2	1157.4	1193.2	1223.9	1244.4	1252.1	1177.8
62.5°	993.5	975.6	993.5	1008.8	1019.1	1031.9	1057.5	1103.6	1121.5	1124.0	1019.1
65°	855.2	847.6	855.2	886.0	888.5	903.9	932.1	965.3	1003.7	998.7	847.6
67.5°	729.8	729.8	729.8	750.2	765.6	773.3	809.1	824.5	873.2	878.3	706.7
70°	614.5	612.0	614.5	629.8	640.1	658.0	691.4	709.3	747.7	760.5	573.6
72.5°	504.5	501.8	504.5	517.3	527.4	542.8	571.0	591.5	624.8	640.1	445.5
75°	407.2	402.0	407.2	417.3	414.8	435.3	458.3	478.8	509.6	519.8	330.3
77.5°	312.4	312.4	312.4	322.7	322.7	343.1	353.4	379.0	396.9	412.2	243.2
80°	233.0	230.4	233.0	235.6	235.6	245.8	263.8	281.7	297.0	297.0	166.5
82.5°	163.9	158.7	163.9	163.9	163.9	169.0	179.3	184.4	194.6	202.3	104.9
85°	102.4	102.4	102.4	104.9	102.4	107.6	110.1	115.2	115.2	110.1	64.1
87.5°	66.6	64.1	66.6	64.1	64.1	61.4	61.4	61.4	58.9	56.3	35.9
90°	15.2	15.2	15.2	15.2	15.2	20.3	26.9	30.3	26.1	17.5	11.1
92.5°	60.8	48.7	60.8	72.9	75.9	107.6	149.8	170.9	150.1	108.4	77.1
95°	211.9	175.4	211.9	248.5	257.7	338.4	445.9	499.7	422.0	266.7	150.2
97.5°	507.8	438.2	507.8	577.3	594.8	645.7	713.8	747.8	618.2	359.2	164.9
100°	731.6	648.6	731.6	814.4	835.2	831.5	826.6	824.0	680.3	392.9	177.3
102.5°	951.8	880.7	951.8	1022.8	1040.5	975.6	889.0	845.6	699.9	408.3	189.7
105°	1232.5	1194.3	1232.5	1270.6	1280.2	1134.6	940.3	843.2	702.1	419.9	208.1
107.5°	1416.4	1425.6	1416.4	1407.2	1404.9	1201.7	930.7	795.3	670.8	421.9	235.3
110°	1486.4	1526.3	1486.4	1446.7	1436.7	1209.6	906.8	755.3	643.1	418.8	250.5

TEST NUMBER: P934494

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1492.7	1553.8	1492.7	1431.7	1416.4	1183.9	873.9	719.0	619.0	418.9	268.8
115°	1453.1	1537.8	1453.1	1368.4	1347.3	1123.4	824.8	675.5	591.3	422.8	296.4
117.5°	1369.3	1463.2	1369.3	1275.3	1251.9	1049.7	780.2	645.5	573.8	430.6	323.2
120°	1301.6	1392.8	1301.6	1210.3	1187.5	1002.8	756.6	633.5	568.0	437.0	338.8
122.5°	1235.8	1325.8	1235.8	1145.7	1123.3	957.0	735.2	624.3	564.9	446.1	357.1
125°	1141.8	1224.7	1141.8	1058.9	1038.2	896.9	708.5	614.3	562.4	458.5	380.6
127.5°	1057.3	1127.2	1057.3	987.3	969.9	848.6	686.8	605.9	561.0	470.9	403.4
130°	1007.5	1072.1	1007.5	942.8	926.7	818.7	674.7	602.7	561.8	479.9	418.6
132.5°	962.3	1020.2	962.3	904.4	889.9	793.3	664.4	600.0	562.4	487.3	431.0
135°	900.4	950.3	900.4	850.5	838.0	757.1	649.1	595.2	561.8	495.3	445.4
137.5°	850.8	891.6	850.8	809.9	799.7	731.3	640.0	594.4	565.3	507.3	463.8
140°	816.6	854.8	816.6	778.4	768.9	709.8	631.0	591.6	565.9	514.6	476.2
142.5°	788.4	821.2	788.4	755.6	747.4	695.5	626.2	591.6	567.9	520.7	485.3
145°	746.1	770.9	746.1	721.2	715.0	672.6	615.9	587.6	568.0	528.8	499.3
147.5°	713.6	734.2	713.6	692.9	687.8	654.4	609.9	587.6	571.9	540.4	516.9
150°	693.1	709.8	693.1	676.5	672.3	644.1	606.4	587.6	573.9	546.6	526.1
152.5°	675.7	688.3	675.7	663.1	659.9	635.8	603.7	587.6	575.3	550.6	532.1
155°	655.5	663.9	655.5	647.2	645.1	625.9	600.4	587.6	578.2	559.4	545.3
157.5°	639.6	645.5	639.6	633.7	632.3	617.3	597.5	587.6	581.1	568.1	558.4
160°	630.1	633.5	630.1	626.7	625.9	613.1	596.1	587.6	582.5	572.2	564.4
162.5°	623.9	627.1	623.9	620.7	620.0	609.2	594.8	587.6	583.9	576.5	570.8
165°	614.9	618.3	614.9	611.6	610.8	603.0	592.7	587.6	585.9	582.5	579.9
167.5°	608.5	610.0	608.5	607.2	606.8	601.7	595.0	591.6	590.1	587.3	585.2
170°	606.8	606.8	606.8	606.8	606.8	601.7	595.0	591.6	591.5	591.3	591.2
172.5°	602.0	600.8	602.0	603.3	603.6	599.6	594.3	591.6	591.6	591.6	591.6
175°	599.1	599.1	599.1	599.1	599.1	596.6	593.2	591.6	592.3	594.0	595.2
177.5°	596.6	595.2	596.6	598.0	598.4	596.3	593.7	592.3	592.9	594.2	595.2
180°	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2

TEST NUMBER: P934494

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5
2.5°	2744.9	2729.6	2729.6	2704.0	2693.7	2686.1	2673.2	2634.8	2624.5	2614.4	2629.7
5°	2767.9	2739.8	2719.3	2673.2	2634.8	2619.4	2570.8	2478.6	2417.2	2371.0	2345.5
7.5°	2773.1	2737.2	2698.9	2627.2	2534.9	2494.0	2345.5	2176.5	2130.3	2089.5	2063.8
10°	2767.9	2727.0	2673.2	2565.7	2348.0	2276.4	2127.8	2017.7	1989.6	1981.9	1989.6
12.5°	2750.0	2711.6	2637.3	2458.2	2153.4	2104.8	2017.7	1953.7	1948.6	1961.4	2030.5
15°	2719.3	2683.5	2596.4	2314.7	2045.8	2010.0	1948.6	1925.5	1953.7	2043.3	2250.7
17.5°	2688.6	2647.6	2540.0	2174.0	1964.0	1938.4	1894.8	1940.9	2099.6	2220.0	2289.2
20°	2647.6	2599.0	2476.1	2071.5	1905.1	1882.0	1861.5	2068.9	2189.3	2232.8	2271.2
22.5°	2599.0	2547.8	2389.0	1999.8	1843.6	1825.7	1838.5	2140.6	2189.3	2220.0	2253.3
25°	2534.9	2491.4	2286.5	1943.4	1795.0	1774.4	1823.1	2133.0	2161.1	2168.8	2235.4
27.5°	2476.1	2419.7	2179.0	1892.3	1736.1	1728.4	1836.0	2099.6	2120.2	2127.8	2199.5
30°	2404.4	2319.9	2058.6	1838.5	1674.6	1672.0	1838.5	2058.6	2053.6	2074.0	2145.8
32.5°	2330.2	2171.3	1923.0	1771.9	1615.7	1613.2	1820.6	1997.2	1992.1	2020.3	2074.0
35°	2261.0	2056.1	1738.6	1695.1	1541.5	1544.0	1777.0	1925.5	1928.1	1953.7	1987.0
37.5°	2189.3	1956.2	1536.3	1610.6	1469.8	1469.8	1718.1	1858.9	1853.9	1861.5	1907.6
40°	2104.8	1800.1	1357.1	1500.5	1403.2	1395.5	1646.4	1787.2	1769.3	1766.8	1830.8
42.5°	2015.1	1628.5	1223.9	1354.6	1326.4	1316.1	1559.4	1700.2	1666.9	1674.6	1756.5
45°	1917.8	1582.4	1121.5	1144.6	1247.0	1239.4	1464.6	1600.3	1577.3	1597.8	1682.3
47.5°	1820.6	1490.2	1088.3	950.0	1162.5	1159.9	1359.7	1503.0	1490.2	1510.8	1600.3
50°	1687.4	1387.8	1085.7	814.3	1067.7	1078.0	1234.2	1408.3	1408.3	1426.3	1520.9
52.5°	1515.8	1262.3	985.9	737.4	957.7	988.4	1124.0	1326.4	1331.5	1349.4	1433.9
55°	1359.7	1131.8	914.2	678.6	827.0	893.6	1016.6	1241.9	1252.1	1270.1	1346.8
57.5°	1216.3	942.3	898.7	609.4	706.7	770.7	921.8	1159.9	1165.0	1180.4	1254.7
60°	1062.6	681.1	824.5	535.2	601.7	650.4	834.7	1062.6	1080.5	1090.8	1154.9
62.5°	888.5	494.2	747.7	483.9	550.5	560.8	763.1	970.5	993.5	1001.2	1039.5
65°	632.5	414.8	635.0	440.4	496.7	499.3	686.2	875.7	896.2	909.0	937.1
67.5°	427.6	338.0	483.9	399.4	455.8	458.3	612.0	765.6	793.8	804.0	821.9
70°	297.0	225.3	358.4	355.9	409.7	414.8	532.6	665.7	691.4	699.0	709.3
72.5°	217.6	181.8	297.0	320.1	361.0	366.2	450.7	553.1	578.7	586.3	591.5
75°	166.5	192.1	240.7	279.1	307.3	309.8	368.7	450.7	468.6	473.7	476.3
77.5°	133.1	179.3	176.6	225.3	251.0	245.8	289.3	348.3	363.6	363.6	363.6
80°	99.9	140.8	133.1	161.3	184.4	179.3	207.4	248.4	253.5	258.6	256.0
82.5°	74.2	89.6	89.6	102.4	122.9	117.8	138.3	161.3	161.3	161.3	166.5
85°	46.1	51.2	41.0	53.8	69.1	66.6	76.8	87.0	89.6	89.6	84.5
87.5°	28.2	23.1	12.8	20.4	30.7	30.7	35.9	38.4	35.9	35.9	35.9
90°	10.4	7.2	4.0	7.2	10.4	11.1	17.5	26.1	30.3	26.9	20.3
92.5°	70.3	43.1	16.0	43.1	70.3	77.1	108.4	150.1	170.9	149.8	107.6
95°	137.8	88.1	38.4	88.1	137.8	150.2	266.7	422.0	499.7	445.9	338.4
97.5°	154.0	110.1	66.3	110.1	154.0	164.9	359.2	618.2	747.8	713.8	645.7
100°	167.3	127.6	87.9	127.6	167.3	177.3	392.9	680.3	824.0	826.6	831.5
102.5°	180.4	143.4	106.3	143.4	180.4	189.7	408.3	699.9	845.6	889.0	975.6
105°	200.3	168.8	137.4	168.8	200.3	208.1	419.9	702.1	843.2	940.3	1134.6
107.5°	227.9	198.6	169.4	198.6	227.9	235.3	421.9	670.8	795.3	930.7	1201.7
110°	243.9	217.3	190.9	217.3	243.9	250.5	418.8	643.1	755.3	906.8	1209.6

TEST NUMBER: P934494

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	262.5	237.3	212.1	237.3	262.5	268.8	418.9	619.0	719.0	873.9	1183.9
115°	290.6	267.3	244.1	267.3	290.6	296.4	422.8	591.3	675.5	824.8	1123.4
117.5°	317.8	296.7	275.6	296.7	317.8	323.2	430.6	573.8	645.5	780.2	1049.7
120°	333.8	313.9	294.0	313.9	333.8	338.8	437.0	568.0	633.5	756.6	1002.8
122.5°	352.0	332.0	311.9	332.0	352.0	357.1	446.1	564.9	624.3	735.2	957.0
125°	376.1	357.8	339.5	357.8	376.1	380.6	458.5	562.4	614.3	708.5	896.9
127.5°	398.7	380.3	361.9	380.3	398.7	403.4	470.9	561.0	605.9	686.8	848.6
130°	413.7	393.7	373.8	393.7	413.7	418.6	479.9	561.8	602.7	674.7	818.7
132.5°	426.1	406.1	386.2	406.1	426.1	431.0	487.3	562.4	600.0	664.4	793.3
135°	440.8	422.8	404.7	422.8	440.8	445.4	495.3	561.8	595.2	649.1	757.1
137.5°	459.3	441.4	423.5	441.4	459.3	463.8	507.3	565.3	594.4	640.0	731.3
140°	472.0	455.5	439.0	455.5	472.0	476.2	514.6	565.9	591.6	631.0	709.8
142.5°	481.5	466.2	451.0	466.2	481.5	485.3	520.7	567.9	591.6	626.2	695.5
145°	496.0	482.7	469.4	482.7	496.0	499.3	528.8	568.0	587.6	615.9	672.6
147.5°	513.7	500.7	487.7	500.7	513.7	516.9	540.4	571.9	587.6	609.9	654.4
150°	523.2	511.4	499.7	511.4	523.2	526.1	546.6	573.9	587.6	606.4	644.1
152.5°	529.8	521.0	512.1	521.0	529.8	532.1	550.6	575.3	587.6	603.7	635.8
155°	543.6	537.0	530.4	537.0	543.6	545.3	559.4	578.2	587.6	600.4	625.9
157.5°	556.8	550.4	544.0	550.4	556.8	558.4	568.1	581.1	587.6	597.5	617.3
160°	563.2	558.2	553.2	558.2	563.2	564.4	572.2	582.5	587.6	596.1	613.1
162.5°	569.9	566.2	562.4	566.2	569.9	570.8	576.5	583.9	587.6	594.8	609.2
165°	579.1	575.8	572.4	575.8	579.1	579.9	582.5	585.9	587.6	592.7	603.0
167.5°	584.8	583.1	581.6	583.1	584.8	585.2	587.3	590.1	591.6	595.0	601.7
170°	590.8	589.2	587.6	589.2	590.8	591.2	591.3	591.5	591.6	595.0	601.7
172.5°	591.5	591.2	590.8	591.2	591.5	591.6	591.6	591.6	591.6	594.3	599.6
175°	595.2	595.2	595.2	595.2	595.2	595.2	594.0	592.3	591.6	593.2	596.6
177.5°	595.2	595.2	595.2	595.2	595.2	595.2	594.2	592.9	592.3	593.7	596.3
180°	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2

TEST NUMBER: P934494

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5	2706.5
2.5°	2611.7	2604.1	2614.4	2586.2	2614.4	2604.1	2611.7	2629.7	2614.4	2624.5	2634.8
5°	2291.7	2278.9	2237.9	2204.7	2237.9	2278.9	2291.7	2345.5	2371.0	2417.2	2478.6
7.5°	2048.5	2038.2	2027.9	2007.5	2027.9	2038.2	2048.5	2063.8	2089.5	2130.3	2176.5
10°	1994.7	1997.2	2012.6	2010.0	2012.6	1997.2	1994.7	1989.6	1981.9	1989.6	2017.7
12.5°	2133.0	2156.0	2240.5	2235.4	2240.5	2156.0	2133.0	2030.5	1961.4	1948.6	1953.7
15°	2291.7	2299.3	2317.3	2319.9	2317.3	2299.3	2291.7	2250.7	2043.3	1953.7	1925.5
17.5°	2307.1	2309.6	2322.4	2322.4	2322.4	2309.6	2307.1	2289.2	2220.0	2099.6	1940.9
20°	2294.3	2299.3	2325.0	2330.2	2325.0	2299.3	2294.3	2271.2	2232.8	2189.3	2068.9
22.5°	2289.2	2299.3	2319.9	2317.3	2319.9	2299.3	2289.2	2253.3	2220.0	2189.3	2140.6
25°	2263.5	2263.5	2266.1	2268.6	2266.1	2263.5	2263.5	2235.4	2168.8	2161.1	2133.0
27.5°	2209.8	2214.8	2230.3	2227.7	2230.3	2214.8	2209.8	2199.5	2127.8	2120.2	2099.6
30°	2161.1	2156.0	2143.1	2133.0	2143.1	2156.0	2161.1	2145.8	2074.0	2053.6	2058.6
32.5°	2079.2	2066.4	2053.6	2045.8	2053.6	2066.4	2079.2	2074.0	2020.3	1992.1	1997.2
35°	1981.9	1984.4	1981.9	1974.1	1981.9	1984.4	1981.9	1987.0	1953.7	1928.1	1925.5
37.5°	1912.7	1917.8	1915.3	1905.1	1915.3	1917.8	1912.7	1907.6	1861.5	1853.9	1858.9
40°	1841.0	1843.6	1841.0	1833.3	1841.0	1843.6	1841.0	1830.8	1766.8	1769.3	1787.2
42.5°	1771.9	1769.3	1761.6	1756.5	1761.6	1769.3	1771.9	1756.5	1674.6	1666.9	1700.2
45°	1692.6	1695.1	1679.8	1672.0	1679.8	1695.1	1692.6	1682.3	1597.8	1577.3	1600.3
47.5°	1613.2	1613.2	1600.3	1592.6	1600.3	1613.2	1613.2	1600.3	1510.8	1490.2	1503.0
50°	1528.7	1526.1	1508.2	1505.6	1508.2	1526.1	1528.7	1520.9	1426.3	1408.3	1408.3
52.5°	1431.3	1431.3	1433.9	1439.1	1433.9	1431.3	1431.3	1433.9	1349.4	1331.5	1326.4
55°	1346.8	1349.4	1367.4	1372.5	1367.4	1349.4	1346.8	1346.8	1270.1	1252.1	1241.9
57.5°	1259.8	1259.8	1272.6	1272.6	1272.6	1259.8	1259.8	1254.7	1180.4	1165.0	1159.9
60°	1159.9	1165.0	1175.3	1172.8	1175.3	1165.0	1159.9	1154.9	1090.8	1080.5	1062.6
62.5°	1055.0	1060.1	1062.6	1057.5	1062.6	1060.1	1055.0	1039.5	1001.2	993.5	970.5
65°	944.9	950.0	952.5	947.4	952.5	950.0	944.9	937.1	909.0	896.2	875.7
67.5°	832.2	829.7	827.0	837.3	827.0	829.7	832.2	821.9	804.0	793.8	765.6
70°	717.0	717.0	714.3	719.5	714.3	717.0	717.0	709.3	699.0	691.4	665.7
72.5°	594.1	591.5	601.7	594.1	601.7	591.5	594.1	591.5	586.3	578.7	553.1
75°	473.7	478.8	473.7	481.4	473.7	478.8	473.7	476.3	473.7	468.6	450.7
77.5°	361.0	366.2	361.0	361.0	361.0	366.2	361.0	363.6	363.6	363.6	348.3
80°	256.0	253.5	253.5	251.0	253.5	253.5	256.0	256.0	258.6	253.5	248.4
82.5°	163.9	161.3	161.3	166.5	161.3	161.3	163.9	166.5	161.3	161.3	161.3
85°	89.6	92.2	87.0	87.0	87.0	92.2	89.6	84.5	89.6	89.6	87.0
87.5°	33.3	30.7	30.7	30.7	30.7	30.7	33.3	35.9	35.9	35.9	38.4
90°	15.2	15.2	15.2	15.2	15.2	15.2	15.2	20.3	26.9	30.3	26.1
92.5°	75.9	72.9	60.8	48.7	60.8	72.9	75.9	107.6	149.8	170.9	150.1
95°	257.7	248.5	211.9	175.4	211.9	248.5	257.7	338.4	445.9	499.7	422.0
97.5°	594.8	577.3	507.8	438.2	507.8	577.3	594.8	645.7	713.8	747.8	618.2
100°	835.2	814.4	731.6	648.6	731.6	814.4	835.2	831.5	826.6	824.0	680.3
102.5°	1040.5	1022.8	951.8	880.7	951.8	1022.8	1040.5	975.6	889.0	845.6	699.9
105°	1280.2	1270.6	1232.5	1194.3	1232.5	1270.6	1280.2	1134.6	940.3	843.2	702.1
107.5°	1404.9	1407.2	1416.4	1425.6	1416.4	1407.2	1404.9	1201.7	930.7	795.3	670.8
110°	1436.7	1446.7	1486.4	1526.3	1486.4	1446.7	1436.7	1209.6	906.8	755.3	643.1

TEST NUMBER: P934494

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1416.4	1431.7	1492.7	1553.8	1492.7	1431.7	1416.4	1183.9	873.9	719.0	619.0
115°	1347.3	1368.4	1453.1	1537.8	1453.1	1368.4	1347.3	1123.4	824.8	675.5	591.3
117.5°	1251.9	1275.3	1369.3	1463.2	1369.3	1275.3	1251.9	1049.7	780.2	645.5	573.8
120°	1187.5	1210.3	1301.6	1392.8	1301.6	1210.3	1187.5	1002.8	756.6	633.5	568.0
122.5°	1123.3	1145.7	1235.8	1325.8	1235.8	1145.7	1123.3	957.0	735.2	624.3	564.9
125°	1038.2	1058.9	1141.8	1224.7	1141.8	1058.9	1038.2	896.9	708.5	614.3	562.4
127.5°	969.9	987.3	1057.3	1127.2	1057.3	987.3	969.9	848.6	686.8	605.9	561.0
130°	926.7	942.8	1007.5	1072.1	1007.5	942.8	926.7	818.7	674.7	602.7	561.8
132.5°	889.9	904.4	962.3	1020.2	962.3	904.4	889.9	793.3	664.4	600.0	562.4
135°	838.0	850.5	900.4	950.3	900.4	850.5	838.0	757.1	649.1	595.2	561.8
137.5°	799.7	809.9	850.8	891.6	850.8	809.9	799.7	731.3	640.0	594.4	565.3
140°	768.9	778.4	816.6	854.8	816.6	778.4	768.9	709.8	631.0	591.6	565.9
142.5°	747.4	755.6	788.4	821.2	788.4	755.6	747.4	695.5	626.2	591.6	567.9
145°	715.0	721.2	746.1	770.9	746.1	721.2	715.0	672.6	615.9	587.6	568.0
147.5°	687.8	692.9	713.6	734.2	713.6	692.9	687.8	654.4	609.9	587.6	571.9
150°	672.3	676.5	693.1	709.8	693.1	676.5	672.3	644.1	606.4	587.6	573.9
152.5°	659.9	663.1	675.7	688.3	675.7	663.1	659.9	635.8	603.7	587.6	575.3
155°	645.1	647.2	655.5	663.9	655.5	647.2	645.1	625.9	600.4	587.6	578.2
157.5°	632.3	633.7	639.6	645.5	639.6	633.7	632.3	617.3	597.5	587.6	581.1
160°	625.9	626.7	630.1	633.5	630.1	626.7	625.9	613.1	596.1	587.6	582.5
162.5°	620.0	620.7	623.9	627.1	623.9	620.7	620.0	609.2	594.8	587.6	583.9
165°	610.8	611.6	614.9	618.3	614.9	611.6	610.8	603.0	592.7	587.6	585.9
167.5°	606.8	607.2	608.5	610.0	608.5	607.2	606.8	601.7	595.0	591.6	590.1
170°	606.8	606.8	606.8	606.8	606.8	606.8	606.8	601.7	595.0	591.6	591.5
172.5°	603.6	603.3	602.0	600.8	602.0	603.3	603.6	599.6	594.3	591.6	591.6
175°	599.1	599.1	599.1	599.1	599.1	599.1	599.1	596.6	593.2	591.6	592.3
177.5°	598.4	598.0	596.6	595.2	596.6	598.0	598.4	596.3	593.7	592.3	592.9
180°	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2

TEST NUMBER: P934494

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2706.5	2706.5	2706.5	2706.5	2706.5
2.5°	2673.2	2686.1	2693.7	2704.0	2729.6
5°	2570.8	2619.4	2634.8	2673.2	2719.3
7.5°	2345.5	2494.0	2534.9	2627.2	2698.9
10°	2127.8	2276.4	2348.0	2565.7	2673.2
12.5°	2017.7	2104.8	2153.4	2458.2	2637.3
15°	1948.6	2010.0	2045.8	2314.7	2596.4
17.5°	1894.8	1938.4	1964.0	2174.0	2540.0
20°	1861.5	1882.0	1905.1	2071.5	2476.1
22.5°	1838.5	1825.7	1843.6	1999.8	2389.0
25°	1823.1	1774.4	1795.0	1943.4	2286.5
27.5°	1836.0	1728.4	1736.1	1892.3	2179.0
30°	1838.5	1672.0	1674.6	1838.5	2058.6
32.5°	1820.6	1613.2	1615.7	1771.9	1923.0
35°	1777.0	1544.0	1541.5	1695.1	1738.6
37.5°	1718.1	1469.8	1469.8	1610.6	1536.3
40°	1646.4	1395.5	1403.2	1500.5	1357.1
42.5°	1559.4	1316.1	1326.4	1354.6	1223.9
45°	1464.6	1239.4	1247.0	1144.6	1121.5
47.5°	1359.7	1159.9	1162.5	950.0	1088.3
50°	1234.2	1078.0	1067.7	814.3	1085.7
52.5°	1124.0	988.4	957.7	737.4	985.9
55°	1016.6	893.6	827.0	678.6	914.2
57.5°	921.8	770.7	706.7	609.4	898.7
60°	834.7	650.4	601.7	535.2	824.5
62.5°	763.1	560.8	550.5	483.9	747.7
65°	686.2	499.3	496.7	440.4	635.0
67.5°	612.0	458.3	455.8	399.4	483.9
70°	532.6	414.8	409.7	355.9	358.4
72.5°	450.7	366.2	361.0	320.1	297.0
75°	368.7	309.8	307.3	279.1	240.7
77.5°	289.3	245.8	251.0	225.3	176.6
80°	207.4	179.3	184.4	161.3	133.1
82.5°	138.3	117.8	122.9	102.4	89.6
85°	76.8	66.6	69.1	53.8	41.0
87.5°	35.9	30.7	30.7	20.4	12.8
90°	17.5	11.1	10.4	7.2	4.0
92.5°	108.4	77.1	70.3	43.1	16.0
95°	266.7	150.2	137.8	88.1	38.4
97.5°	359.2	164.9	154.0	110.1	66.3
100°	392.9	177.3	167.3	127.6	87.9
102.5°	408.3	189.7	180.4	143.4	106.3
105°	419.9	208.1	200.3	168.8	137.4
107.5°	421.9	235.3	227.9	198.6	169.4
110°	418.8	250.5	243.9	217.3	190.9



TEST NUMBER: P934494

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	418.9	268.8	262.5	237.3	212.1
115°	422.8	296.4	290.6	267.3	244.1
117.5°	430.6	323.2	317.8	296.7	275.6
120°	437.0	338.8	333.8	313.9	294.0
122.5°	446.1	357.1	352.0	332.0	311.9
125°	458.5	380.6	376.1	357.8	339.5
127.5°	470.9	403.4	398.7	380.3	361.9
130°	479.9	418.6	413.7	393.7	373.8
132.5°	487.3	431.0	426.1	406.1	386.2
135°	495.3	445.4	440.8	422.8	404.7
137.5°	507.3	463.8	459.3	441.4	423.5
140°	514.6	476.2	472.0	455.5	439.0
142.5°	520.7	485.3	481.5	466.2	451.0
145°	528.8	499.3	496.0	482.7	469.4
147.5°	540.4	516.9	513.7	500.7	487.7
150°	546.6	526.1	523.2	511.4	499.7
152.5°	550.6	532.1	529.8	521.0	512.1
155°	559.4	545.3	543.6	537.0	530.4
157.5°	568.1	558.4	556.8	550.4	544.0
160°	572.2	564.4	563.2	558.2	553.2
162.5°	576.5	570.8	569.9	566.2	562.4
165°	582.5	579.9	579.1	575.8	572.4
167.5°	587.3	585.2	584.8	583.1	581.6
170°	591.3	591.2	590.8	589.2	587.6
172.5°	591.6	591.6	591.5	591.2	590.8
175°	594.0	595.2	595.2	595.2	595.2
177.5°	594.2	595.2	595.2	595.2	595.2
180°	595.2	595.2	595.2	595.2	595.2

TEST NUMBER: P934494

CATALOG NUMBER: SQ4-FA-050U-100D-B2750-1D-UNV-W2A-W-8-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.84	15.85	15.66	16.69	17.74	17.68	18.69	18.50	19.53	20.58
	3H	15.33	16.23	16.16	17.09	18.16	19.04	19.94	19.87	20.80	21.87
	4H	15.53	16.38	16.38	17.24	18.33	19.49	20.35	20.34	21.21	22.29
	6H	15.65	16.44	16.52	17.31	18.41	19.79	20.57	20.65	21.44	22.54
	8H	15.66	16.41	16.53	17.30	18.40	19.87	20.62	20.74	21.50	22.60
	12H	15.64	16.35	16.51	17.23	18.36	19.91	20.62	20.79	21.51	22.63
4H	2H	15.89	16.75	16.75	17.61	18.70	18.11	18.96	18.96	19.82	20.91
	3H	16.93	17.65	17.80	18.54	19.64	19.63	20.34	20.50	21.23	22.33
	4H	17.22	17.87	18.10	18.76	19.88	20.16	20.81	21.04	21.70	22.83
	6H	17.35	17.91	18.25	18.82	19.96	20.54	21.10	21.43	22.01	23.14
	8H	17.36	17.88	18.26	18.79	19.94	20.65	21.17	21.55	22.08	23.23
	12H	17.33	17.80	18.25	18.73	19.88	20.72	21.19	21.63	22.11	23.26
8H	4H	17.68	18.21	18.58	19.12	20.26	20.30	20.82	21.20	21.73	22.88
	6H	17.95	18.38	18.88	19.33	20.48	20.74	21.18	21.67	22.13	23.27
	8H	18.00	18.38	18.93	19.32	20.48	20.90	21.28	21.83	22.23	23.39
	12H	17.99	18.32	18.92	19.26	20.47	21.01	21.34	21.94	22.28	23.49
12H	4H	17.70	18.17	18.61	19.10	20.25	20.27	20.74	21.19	21.67	22.82
	6H	18.01	18.40	18.95	19.34	20.50	20.74	21.13	21.68	22.07	23.23
	8H	18.09	18.43	19.03	19.36	20.57	20.91	21.25	21.85	22.18	23.40

END OF REPORT