

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934589

Luminaire Tested: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934589
REPORT IS A COMBINATION OF REPORTS P933703 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9635.7 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934589

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P934589

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	65	63
2	93	86	79	74	88	81	76	71	73	68	65	65	62	59	58	56	53
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	52	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27
8	57	44	36	30	54	42	35	29	38	32	28	35	29	26	31	27	24
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21
10	49	37	30	25	47	35	28	24	32	26	22	30	25	21	27	23	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16082	16082	16082	16082
5°	16196	16233	16196	12765
10°	16082	15991	16082	11432
15°	15901	15645	15901	13063
20°	15562	15234	15562	13091
25°	14875	14636	14875	12813
30°	13990	14139	13990	12205
35°	12466	13510	12466	11535
40°	10381	12770	10381	11030
45°	9269	11904	9269	10448
50°	9840	10870	9840	9864
55°	9249	9757	9249	9526
60°	9524	8287	9524	8726
65°	8621	6851	8621	7658
70°	5955	5459	5955	6419
75°	5202	4035	5202	4833
80°	4163	2667	4163	2905
85°	2343	1413	2343	1201

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 14216 cd/sqm

TEST NUMBER: P934589

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.7	2.4
10°-20°	666.3	6.9
20°-30°	1029.9	10.7
30°-40°	1229.5	12.8
40°-50°	1236.7	12.8
50°-60°	1076.1	11.2
60°-70°	763.0	7.9
70°-80°	403.7	4.2
80°-90°	102.2	1.1
90°-100°	217.6	2.3
100°-110°	572.0	5.9
110°-120°	593.1	6.2
120°-130°	475.8	4.9
130°-140°	373.3	3.9
140°-150°	286.5	3.0
150°-160°	206.4	2.1
160°-170°	126.3	1.3
170°-180°	42.7	0.4
0°-30°	1930.9	20.0
0°-40°	3160.4	32.8
0°-60°	5473.2	56.8
0°-90°	6742.1	70.0
90°-120°	1382.8	14.4
90°-150°	2518.4	26.1
90°-180°	2894.0	30.0
0°-180°	9635.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2600	2600	2600	2600	2600	
5°	2612	2693	2612	2118	2612	248
15°	2494	2668	2494	2228	2494	702
25°	2196	2489	2196	2179	2196	1008
35°	1670	2221	1670	1896	1670	1033
45°	1077	1830	1077	1606	1077	863
55°	878	1350	878	1318	878	807
65°	610	814	610	910	610	583
75°	231	386	231	462	231	243
85°	39	98	39	84	39	53
90°	3	11	3	11	3	4
95°	29	132	29	132	29	32
105°	103	896	103	896	103	109
115°	183	1153	183	1153	183	181
125°	255	918	255	918	255	226
135°	304	713	304	713	304	235
145°	352	578	352	578	352	221
155°	398	498	398	498	398	183
165°	429	464	429	464	429	121
175°	446	449	446	449	446	42
180°	446	446	446	446	446	

TEST NUMBER: P934589

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6
2.5°	2621.7	2621.7	2636.6	2641.4	2641.4	2634.0	2626.7	2634.0	2656.2	2663.6	2661.1
5°	2611.9	2631.6	2658.6	2663.6	2668.5	2666.0	2661.1	2666.0	2690.6	2695.6	2698.0
7.5°	2592.3	2629.1	2663.6	2671.0	2678.3	2671.0	2668.5	2673.4	2698.0	2702.9	2702.9
10°	2567.7	2619.3	2658.6	2663.6	2671.0	2663.6	2663.6	2673.4	2698.0	2702.9	2705.4
12.5°	2533.3	2604.6	2641.4	2646.3	2656.2	2653.7	2651.3	2661.1	2685.7	2690.6	2690.6
15°	2493.9	2577.4	2611.9	2616.9	2634.0	2629.1	2629.1	2639.0	2666.0	2673.4	2671.0
17.5°	2439.7	2543.0	2582.4	2589.7	2602.1	2599.6	2602.1	2611.9	2636.6	2641.4	2643.9
20°	2378.3	2496.3	2543.0	2550.4	2562.7	2562.7	2562.7	2575.0	2599.6	2609.4	2609.4
22.5°	2294.7	2447.1	2496.3	2501.3	2516.0	2516.0	2521.0	2538.1	2560.3	2562.7	2562.7
25°	2196.2	2393.0	2434.8	2449.6	2464.4	2471.7	2479.1	2489.0	2496.3	2493.9	2496.3
27.5°	2092.9	2324.1	2378.3	2388.1	2407.8	2415.1	2425.0	2427.4	2430.0	2437.3	2432.4
30°	1977.3	2228.2	2309.4	2319.2	2351.2	2356.1	2346.3	2351.2	2363.5	2368.4	2373.4
32.5°	1847.0	2085.6	2238.1	2260.2	2289.7	2275.0	2272.5	2279.9	2299.5	2299.5	2304.5
35°	1670.0	1974.9	2171.7	2191.4	2213.5	2196.2	2206.1	2208.5	2220.9	2228.2	2225.8
37.5°	1475.7	1879.0	2102.8	2117.6	2134.8	2112.6	2127.4	2134.8	2144.6	2139.7	2139.7
40°	1303.5	1729.0	2021.6	2031.5	2046.2	2029.0	2043.8	2048.8	2053.6	2048.8	2046.2
42.5°	1175.6	1564.2	1935.6	1947.9	1938.0	1950.3	1955.2	1965.1	1957.7	1947.9	1947.9
45°	1077.2	1520.0	1842.1	1856.9	1842.1	1861.8	1869.2	1869.2	1847.0	1842.1	1839.6
47.5°	1045.3	1431.4	1748.7	1748.7	1741.3	1765.9	1778.2	1761.0	1738.8	1731.4	1731.4
50°	1042.8	1333.1	1620.7	1611.0	1645.4	1674.9	1662.6	1645.4	1628.1	1601.1	1601.1
52.5°	946.9	1212.5	1456.0	1492.8	1547.0	1564.2	1544.5	1527.3	1497.8	1485.5	1475.7
55°	878.0	1087.0	1305.9	1379.8	1436.3	1458.4	1421.5	1404.4	1360.1	1352.7	1347.8
57.5°	863.3	905.0	1168.2	1261.7	1330.5	1328.1	1305.9	1273.9	1237.1	1229.8	1227.2
60°	792.0	654.2	1020.6	1131.3	1202.6	1195.3	1175.6	1146.1	1111.6	1106.8	1101.8
62.5°	718.1	474.7	853.4	978.9	1079.7	1077.2	1060.0	1015.7	991.2	978.9	969.0
65°	610.0	398.5	607.5	814.1	959.2	964.1	927.2	895.3	868.2	853.4	851.0
67.5°	464.8	324.6	410.8	678.8	843.6	838.7	792.0	777.1	742.7	735.4	720.6
70°	344.3	216.5	285.3	550.9	730.4	718.1	681.3	664.1	632.1	614.8	605.0
72.5°	285.3	174.6	209.0	427.9	614.8	600.1	568.1	548.5	521.4	506.7	496.8
75°	231.2	184.5	159.9	317.3	499.2	489.4	459.9	440.2	418.1	398.5	400.9
77.5°	169.7	172.2	127.9	233.6	395.9	381.2	364.0	339.4	329.6	309.9	309.9
80°	127.9	135.3	95.9	159.9	285.3	285.3	270.5	253.3	236.1	226.3	226.3
82.5°	86.0	86.0	71.3	100.9	194.3	186.9	177.0	172.2	162.3	157.4	157.4
85°	39.3	49.2	44.3	61.5	105.7	110.7	110.7	105.7	103.3	98.4	100.9
87.5°	12.3	22.1	27.0	34.4	54.1	56.6	59.0	59.0	59.0	61.5	61.5
90°	3.0	5.4	7.8	8.4	13.2	19.6	22.8	20.3	15.1	11.3	11.3
92.5°	12.0	32.4	52.7	57.8	81.3	112.6	128.2	112.3	80.6	56.9	54.7
95°	28.8	66.0	103.3	112.6	200.0	316.6	374.8	334.5	253.8	193.2	186.3
97.5°	49.7	82.7	115.5	123.7	269.5	463.8	560.9	535.4	484.3	446.0	432.9
100°	65.9	95.7	125.6	133.0	294.7	510.3	618.0	619.9	623.6	626.5	611.0
102.5°	79.7	107.6	135.4	142.3	306.3	524.9	634.2	666.7	731.7	780.4	767.2
105°	103.1	126.6	150.2	156.1	314.8	526.6	632.4	705.2	850.9	960.2	953.0
107.5°	127.0	149.0	170.9	176.5	316.5	503.1	596.4	698.0	901.2	1053.6	1055.3
110°	143.2	163.0	182.9	187.8	314.1	482.4	566.5	680.0	907.3	1077.6	1085.1

TEST NUMBER: P934589

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	159.1	178.0	196.9	201.6	314.1	464.2	539.2	655.5	888.0	1062.3	1073.7
115°	183.0	200.5	217.9	222.3	317.1	443.4	506.6	618.6	842.5	1010.5	1026.4
117.5°	206.7	222.6	238.4	242.3	323.0	430.4	484.1	585.2	787.3	938.9	956.5
120°	220.4	235.4	250.3	254.1	327.7	426.0	475.1	567.4	752.1	890.6	907.8
122.5°	234.0	249.0	264.1	267.8	334.6	423.6	468.2	551.4	717.7	842.4	859.3
125°	254.7	268.3	282.1	285.5	343.9	421.8	460.8	531.4	672.7	778.6	794.1
127.5°	271.4	285.3	299.1	302.6	353.2	420.7	454.5	515.1	636.3	727.3	740.4
130°	280.4	295.4	310.3	314.0	360.0	421.3	452.0	506.0	614.1	695.1	707.2
132.5°	289.7	304.7	319.6	323.3	365.5	421.8	450.0	498.4	595.0	667.4	678.3
135°	303.5	317.1	330.6	334.0	371.5	421.4	446.4	486.9	567.8	628.5	637.9
137.5°	317.5	331.0	344.4	347.8	380.4	423.9	445.7	479.9	548.4	599.7	607.4
140°	329.3	341.7	354.0	357.1	386.0	424.4	443.7	473.3	532.4	576.7	583.8
142.5°	338.2	349.6	361.0	364.0	390.5	426.0	443.7	469.7	521.5	560.5	566.7
145°	352.0	362.0	372.0	374.5	396.6	426.0	440.7	461.9	504.4	536.2	540.9
147.5°	365.8	375.5	385.3	387.7	405.3	428.9	440.7	457.4	490.8	515.9	519.8
150°	374.8	383.6	392.3	394.6	410.0	430.4	440.7	454.8	483.0	504.2	507.3
152.5°	384.0	390.7	397.4	399.0	412.9	431.4	440.7	452.7	476.8	494.9	497.2
155°	397.9	402.8	407.7	408.9	419.5	433.6	440.7	450.3	469.5	483.8	485.4
157.5°	408.0	412.8	417.6	418.8	426.1	435.9	440.7	448.2	463.1	474.2	475.3
160°	414.9	418.6	422.3	423.3	429.1	436.8	440.7	447.1	459.9	469.5	470.1
162.5°	421.8	424.6	427.4	428.1	432.3	437.9	440.7	446.1	456.9	464.9	465.5
165°	429.3	431.8	434.3	435.0	436.9	439.4	440.7	444.6	452.2	458.0	458.7
167.5°	436.1	437.3	438.6	438.9	440.5	442.6	443.7	446.2	451.3	455.0	455.3
170°	440.7	441.9	443.1	443.4	443.5	443.6	443.7	446.2	451.3	455.0	455.0
172.5°	443.1	443.4	443.6	443.7	443.7	443.7	443.7	445.6	449.6	452.6	452.4
175°	446.4	446.4	446.4	446.4	445.5	444.3	443.7	445.0	447.5	449.3	449.3
177.5°	446.4	446.4	446.4	446.4	445.7	444.8	444.3	445.3	447.3	448.7	448.5
180°	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4

TEST NUMBER: P934589

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6
2.5°	2666.0	2658.6	2666.0	2661.1	2663.6	2656.2	2634.0	2626.7	2634.0	2641.4	2641.4
5°	2698.0	2693.0	2698.0	2698.0	2695.6	2690.6	2666.0	2661.1	2666.0	2668.5	2663.6
7.5°	2707.9	2700.5	2707.9	2702.9	2702.9	2698.0	2673.4	2668.5	2671.0	2678.3	2671.0
10°	2707.9	2700.5	2707.9	2705.4	2702.9	2698.0	2673.4	2663.6	2663.6	2671.0	2663.6
12.5°	2695.6	2690.6	2695.6	2690.6	2690.6	2685.7	2661.1	2651.3	2653.7	2656.2	2646.3
15°	2675.9	2668.5	2675.9	2671.0	2673.4	2666.0	2639.0	2629.1	2629.1	2634.0	2616.9
17.5°	2646.3	2636.6	2646.3	2643.9	2641.4	2636.6	2611.9	2602.1	2599.6	2602.1	2589.7
20°	2611.9	2604.6	2611.9	2609.4	2609.4	2599.6	2575.0	2562.7	2562.7	2562.7	2550.4
22.5°	2557.8	2550.4	2557.8	2562.7	2562.7	2560.3	2538.1	2521.0	2516.0	2516.0	2501.3
25°	2496.3	2489.0	2496.3	2496.3	2493.9	2496.3	2489.0	2479.1	2471.7	2464.4	2449.6
27.5°	2437.3	2432.4	2437.3	2432.4	2437.3	2430.0	2427.4	2425.0	2415.1	2407.8	2388.1
30°	2378.3	2373.4	2378.3	2373.4	2368.4	2363.5	2351.2	2346.3	2356.1	2351.2	2319.2
32.5°	2304.5	2299.5	2304.5	2304.5	2299.5	2299.5	2279.9	2272.5	2275.0	2289.7	2260.2
35°	2228.2	2220.9	2228.2	2225.8	2228.2	2220.9	2208.5	2206.1	2196.2	2213.5	2191.4
37.5°	2139.7	2132.3	2139.7	2139.7	2139.7	2144.6	2134.8	2127.4	2112.6	2134.8	2117.6
40°	2048.8	2038.9	2048.8	2046.2	2048.8	2053.6	2048.8	2043.8	2029.0	2046.2	2031.5
42.5°	1945.5	1942.9	1945.5	1947.9	1947.9	1957.7	1965.1	1955.2	1950.3	1938.0	1947.9
45°	1834.7	1829.9	1834.7	1839.6	1842.1	1847.0	1869.2	1869.2	1861.8	1842.1	1856.9
47.5°	1716.7	1704.4	1716.7	1731.4	1731.4	1738.8	1761.0	1778.2	1765.9	1741.3	1748.7
50°	1591.3	1593.7	1591.3	1601.1	1601.1	1628.1	1645.4	1662.6	1674.9	1645.4	1611.0
52.5°	1468.3	1465.8	1468.3	1475.7	1485.5	1497.8	1527.3	1544.5	1564.2	1547.0	1492.8
55°	1345.3	1350.2	1345.3	1347.8	1352.7	1360.1	1404.4	1421.5	1458.4	1436.3	1379.8
57.5°	1222.3	1214.9	1222.3	1227.2	1229.8	1237.1	1273.9	1305.9	1328.1	1330.5	1261.7
60°	1079.7	1069.9	1079.7	1101.8	1106.8	1111.6	1146.1	1175.6	1195.3	1202.6	1131.3
62.5°	954.3	937.0	954.3	969.0	978.9	991.2	1015.7	1060.0	1077.2	1079.7	978.9
65°	821.4	814.1	821.4	851.0	853.4	868.2	895.3	927.2	964.1	959.2	814.1
67.5°	701.0	701.0	701.0	720.6	735.4	742.7	777.1	792.0	838.7	843.6	678.8
70°	590.2	587.8	590.2	605.0	614.8	632.1	664.1	681.3	718.1	730.4	550.9
72.5°	484.5	482.1	484.5	496.8	506.7	521.4	548.5	568.1	600.1	614.8	427.9
75°	391.1	386.1	391.1	400.9	398.5	418.1	440.2	459.9	489.4	499.2	317.3
77.5°	300.1	300.1	300.1	309.9	309.9	329.6	339.4	364.0	381.2	395.9	233.6
80°	223.8	221.3	223.8	226.3	226.3	236.1	253.3	270.5	285.3	285.3	159.9
82.5°	157.4	152.5	157.4	157.4	157.4	162.3	172.2	177.0	186.9	194.3	100.9
85°	98.4	98.4	98.4	100.9	98.4	103.3	105.7	110.7	110.7	105.7	61.5
87.5°	64.0	61.5	64.0	61.5	61.5	59.0	59.0	59.0	56.6	54.1	34.4
90°	11.3	11.3	11.3	11.3	11.3	15.1	20.3	22.8	19.6	13.2	8.4
92.5°	45.5	36.5	45.5	54.7	56.9	80.6	112.3	128.2	112.6	81.3	57.8
95°	158.9	131.5	158.9	186.3	193.2	253.8	334.5	374.8	316.6	200.0	112.6
97.5°	380.8	328.7	380.8	432.9	446.0	484.3	535.4	560.9	463.8	269.5	123.7
100°	548.7	486.5	548.7	611.0	626.5	623.6	619.9	618.0	510.3	294.7	133.0
102.5°	713.9	660.6	713.9	767.2	780.4	731.7	666.7	634.2	524.9	306.3	142.3
105°	924.4	895.7	924.4	953.0	960.2	850.9	705.2	632.4	526.6	314.8	156.1
107.5°	1062.2	1069.2	1062.2	1055.3	1053.6	901.2	698.0	596.4	503.1	316.5	176.5
110°	1114.8	1144.7	1114.8	1085.1	1077.6	907.3	680.0	566.5	482.4	314.1	187.8

TEST NUMBER: P934589

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1119.6	1165.3	1119.6	1073.7	1062.3	888.0	655.5	539.2	464.2	314.1	201.6
115°	1089.8	1153.4	1089.8	1026.4	1010.5	842.5	618.6	506.6	443.4	317.1	222.3
117.5°	1026.9	1097.4	1026.9	956.5	938.9	787.3	585.2	484.1	430.4	323.0	242.3
120°	976.2	1044.7	976.2	907.8	890.6	752.1	567.4	475.1	426.0	327.7	254.1
122.5°	926.8	994.3	926.8	859.3	842.4	717.7	551.4	468.2	423.6	334.6	267.8
125°	856.3	918.5	856.3	794.1	778.6	672.7	531.4	460.8	421.8	343.9	285.5
127.5°	792.9	845.5	792.9	740.4	727.3	636.3	515.1	454.5	420.7	353.2	302.6
130°	755.6	804.1	755.6	707.2	695.1	614.1	506.0	452.0	421.3	360.0	314.0
132.5°	721.7	765.1	721.7	678.3	667.4	595.0	498.4	450.0	421.8	365.5	323.3
135°	675.3	712.7	675.3	637.9	628.5	567.8	486.9	446.4	421.4	371.5	334.0
137.5°	638.1	668.7	638.1	607.4	599.7	548.4	479.9	445.7	423.9	380.4	347.8
140°	612.4	641.1	612.4	583.8	576.7	532.4	473.3	443.7	424.4	386.0	357.1
142.5°	591.3	615.9	591.3	566.7	560.5	521.5	469.7	443.7	426.0	390.5	364.0
145°	559.6	578.2	559.6	540.9	536.2	504.4	461.9	440.7	426.0	396.6	374.5
147.5°	535.2	550.6	535.2	519.8	515.9	490.8	457.4	440.7	428.9	405.3	387.7
150°	519.9	532.4	519.9	507.3	504.2	483.0	454.8	440.7	430.4	410.0	394.6
152.5°	506.7	516.2	506.7	497.2	494.9	476.8	452.7	440.7	431.4	412.9	399.0
155°	491.7	497.9	491.7	485.4	483.8	469.5	450.3	440.7	433.6	419.5	408.9
157.5°	479.8	484.1	479.8	475.3	474.2	463.1	448.2	440.7	435.9	426.1	418.8
160°	472.6	475.1	472.6	470.1	469.5	459.9	447.1	440.7	436.8	429.1	423.3
162.5°	467.9	470.4	467.9	465.5	464.9	456.9	446.1	440.7	437.9	432.3	428.1
165°	461.2	463.8	461.2	458.7	458.0	452.2	444.6	440.7	439.4	436.9	435.0
167.5°	456.4	457.5	456.4	455.3	455.0	451.3	446.2	443.7	442.6	440.5	438.9
170°	455.0	455.0	455.0	455.0	455.0	451.3	446.2	443.7	443.6	443.5	443.4
172.5°	451.5	450.6	451.5	452.4	452.6	449.6	445.6	443.7	443.7	443.7	443.7
175°	449.3	449.3	449.3	449.3	449.3	447.5	445.0	443.7	444.3	445.5	446.4
177.5°	447.5	446.4	447.5	448.5	448.7	447.3	445.3	444.3	444.8	445.7	446.4
180°	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4

TEST NUMBER: P934589

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6
2.5°	2636.6	2621.7	2621.7	2597.2	2587.3	2580.0	2567.7	2530.7	2521.0	2511.1	2525.8
5°	2658.6	2631.6	2611.9	2567.7	2530.7	2516.0	2469.3	2380.7	2321.7	2277.4	2252.8
7.5°	2663.6	2629.1	2592.3	2523.4	2434.8	2395.5	2252.8	2090.5	2046.2	2006.9	1982.3
10°	2658.6	2619.3	2567.7	2464.4	2255.3	2186.5	2043.8	1938.0	1911.0	1903.6	1911.0
12.5°	2641.4	2604.6	2533.3	2361.1	2068.4	2021.6	1938.0	1876.6	1871.6	1883.9	1950.3
15°	2611.9	2577.4	2493.9	2223.4	1965.1	1930.6	1871.6	1849.5	1876.6	1962.6	2161.8
17.5°	2582.4	2543.0	2439.7	2088.1	1886.4	1861.8	1820.0	1864.3	2016.8	2132.3	2198.8
20°	2543.0	2496.3	2378.3	1989.6	1829.9	1807.7	1788.0	1987.2	2102.8	2144.6	2181.5
22.5°	2496.3	2447.1	2294.7	1920.8	1770.8	1753.6	1765.9	2056.1	2102.8	2132.3	2164.3
25°	2434.8	2393.0	2196.2	1866.7	1724.0	1704.4	1751.1	2048.8	2075.8	2083.2	2147.1
27.5°	2378.3	2324.1	2092.9	1817.6	1667.5	1660.1	1763.4	2016.8	2036.5	2043.8	2112.6
30°	2309.4	2228.2	1977.3	1765.9	1608.4	1606.0	1765.9	1977.3	1972.5	1992.2	2061.0
32.5°	2238.1	2085.6	1847.0	1702.0	1552.0	1549.4	1748.7	1918.3	1913.5	1940.5	1992.2
35°	2171.7	1974.9	1670.0	1628.1	1480.5	1483.1	1706.9	1849.5	1852.0	1876.6	1908.5
37.5°	2102.8	1879.0	1475.7	1547.0	1411.7	1411.7	1650.3	1785.6	1780.6	1788.0	1832.3
40°	2021.6	1729.0	1303.5	1441.2	1347.8	1340.4	1581.4	1716.7	1699.4	1697.0	1758.5
42.5°	1935.6	1564.2	1175.6	1301.1	1273.9	1264.2	1497.8	1633.1	1601.1	1608.4	1687.1
45°	1842.1	1520.0	1077.2	1099.3	1197.8	1190.3	1406.8	1537.1	1515.0	1534.7	1615.8
47.5°	1748.7	1431.4	1045.3	912.4	1116.6	1114.2	1305.9	1443.7	1431.4	1451.1	1537.1
50°	1620.7	1333.1	1042.8	782.1	1025.6	1035.4	1185.5	1352.7	1352.7	1369.9	1460.9
52.5°	1456.0	1212.5	946.9	708.3	919.9	949.3	1079.7	1273.9	1278.9	1296.1	1377.2
55°	1305.9	1087.0	878.0	651.7	794.4	858.3	976.4	1192.8	1202.6	1219.9	1293.6
57.5°	1168.2	905.0	863.3	585.4	678.8	740.3	885.4	1114.2	1119.0	1133.8	1205.1
60°	1020.6	654.2	792.0	514.1	578.0	624.7	801.8	1020.6	1037.9	1047.7	1109.2
62.5°	853.4	474.7	718.1	464.8	528.8	538.6	733.0	932.1	954.3	961.6	998.6
65°	607.5	398.5	610.0	423.1	477.1	479.6	659.1	841.1	860.8	873.1	900.2
67.5°	410.8	324.6	464.8	383.6	437.8	440.2	587.8	735.4	762.4	772.3	789.4
70°	285.3	216.5	344.3	341.9	393.5	398.5	511.5	639.4	664.1	671.4	681.3
72.5°	209.0	174.6	285.3	307.5	346.8	351.7	432.9	531.2	555.8	563.2	568.1
75°	159.9	184.5	231.2	268.1	295.2	297.6	354.2	432.9	450.1	455.0	457.5
77.5°	127.9	172.2	169.7	216.5	241.0	236.1	277.9	334.5	349.2	349.2	349.2
80°	95.9	135.3	127.9	154.9	177.0	172.2	199.2	238.6	243.5	248.4	245.9
82.5°	71.3	86.0	86.0	98.4	118.0	113.2	132.8	154.9	154.9	154.9	159.9
85°	44.3	49.2	39.3	51.6	66.4	64.0	73.7	83.6	86.0	86.0	81.2
87.5°	27.0	22.1	12.3	19.7	29.6	29.6	34.4	36.9	34.4	34.4	34.4
90°	7.8	5.4	3.0	5.4	7.8	8.4	13.2	19.6	22.8	20.3	15.1
92.5°	52.7	32.4	12.0	32.4	52.7	57.8	81.3	112.6	128.2	112.3	80.6
95°	103.3	66.0	28.8	66.0	103.3	112.6	200.0	316.6	374.8	334.5	253.8
97.5°	115.5	82.7	49.7	82.7	115.5	123.7	269.5	463.8	560.9	535.4	484.3
100°	125.6	95.7	65.9	95.7	125.6	133.0	294.7	510.3	618.0	619.9	623.6
102.5°	135.4	107.6	79.7	107.6	135.4	142.3	306.3	524.9	634.2	666.7	731.7
105°	150.2	126.6	103.1	126.6	150.2	156.1	314.8	526.6	632.4	705.2	850.9
107.5°	170.9	149.0	127.0	149.0	170.9	176.5	316.5	503.1	596.4	698.0	901.2
110°	182.9	163.0	143.2	163.0	182.9	187.8	314.1	482.4	566.5	680.0	907.3

TEST NUMBER: P934589

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	196.9	178.0	159.1	178.0	196.9	201.6	314.1	464.2	539.2	655.5	888.0
115°	217.9	200.5	183.0	200.5	217.9	222.3	317.1	443.4	506.6	618.6	842.5
117.5°	238.4	222.6	206.7	222.6	238.4	242.3	323.0	430.4	484.1	585.2	787.3
120°	250.3	235.4	220.4	235.4	250.3	254.1	327.7	426.0	475.1	567.4	752.1
122.5°	264.1	249.0	234.0	249.0	264.1	267.8	334.6	423.6	468.2	551.4	717.7
125°	282.1	268.3	254.7	268.3	282.1	285.5	343.9	421.8	460.8	531.4	672.7
127.5°	299.1	285.3	271.4	285.3	299.1	302.6	353.2	420.7	454.5	515.1	636.3
130°	310.3	295.4	280.4	295.4	310.3	314.0	360.0	421.3	452.0	506.0	614.1
132.5°	319.6	304.7	289.7	304.7	319.6	323.3	365.5	421.8	450.0	498.4	595.0
135°	330.6	317.1	303.5	317.1	330.6	334.0	371.5	421.4	446.4	486.9	567.8
137.5°	344.4	331.0	317.5	331.0	344.4	347.8	380.4	423.9	445.7	479.9	548.4
140°	354.0	341.7	329.3	341.7	354.0	357.1	386.0	424.4	443.7	473.3	532.4
142.5°	361.0	349.6	338.2	349.6	361.0	364.0	390.5	426.0	443.7	469.7	521.5
145°	372.0	362.0	352.0	362.0	372.0	374.5	396.6	426.0	440.7	461.9	504.4
147.5°	385.3	375.5	365.8	375.5	385.3	387.7	405.3	428.9	440.7	457.4	490.8
150°	392.3	383.6	374.8	383.6	392.3	394.6	410.0	430.4	440.7	454.8	483.0
152.5°	397.4	390.7	384.0	390.7	397.4	399.0	412.9	431.4	440.7	452.7	476.8
155°	407.7	402.8	397.9	402.8	407.7	408.9	419.5	433.6	440.7	450.3	469.5
157.5°	417.6	412.8	408.0	412.8	417.6	418.8	426.1	435.9	440.7	448.2	463.1
160°	422.3	418.6	414.9	418.6	422.3	423.3	429.1	436.8	440.7	447.1	459.9
162.5°	427.4	424.6	421.8	424.6	427.4	428.1	432.3	437.9	440.7	446.1	456.9
165°	434.3	431.8	429.3	431.8	434.3	435.0	436.9	439.4	440.7	444.6	452.2
167.5°	438.6	437.3	436.1	437.3	438.6	438.9	440.5	442.6	443.7	446.2	451.3
170°	443.1	441.9	440.7	441.9	443.1	443.4	443.5	443.6	443.7	446.2	451.3
172.5°	443.6	443.4	443.1	443.4	443.6	443.7	443.7	443.7	443.7	445.6	449.6
175°	446.4	446.4	446.4	446.4	446.4	446.4	445.5	444.3	443.7	445.0	447.5
177.5°	446.4	446.4	446.4	446.4	446.4	446.4	445.7	444.8	444.3	445.3	447.3
180°	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4

TEST NUMBER: P934589

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6
2.5°	2508.6	2501.3	2511.1	2484.0	2511.1	2501.3	2508.6	2525.8	2511.1	2521.0	2530.7
5°	2201.2	2188.9	2149.5	2117.6	2149.5	2188.9	2201.2	2252.8	2277.4	2321.7	2380.7
7.5°	1967.6	1957.7	1947.9	1928.2	1947.9	1957.7	1967.6	1982.3	2006.9	2046.2	2090.5
10°	1915.9	1918.3	1933.2	1930.6	1933.2	1918.3	1915.9	1911.0	1903.6	1911.0	1938.0
12.5°	2048.8	2070.8	2152.1	2147.1	2152.1	2070.8	2048.8	1950.3	1883.9	1871.6	1876.6
15°	2201.2	2208.5	2225.8	2228.2	2225.8	2208.5	2201.2	2161.8	1962.6	1876.6	1849.5
17.5°	2215.9	2218.4	2230.7	2230.7	2230.7	2218.4	2215.9	2198.8	2132.3	2016.8	1864.3
20°	2203.7	2208.5	2233.2	2238.1	2233.2	2208.5	2203.7	2181.5	2144.6	2102.8	1987.2
22.5°	2198.8	2208.5	2228.2	2225.8	2228.2	2208.5	2198.8	2164.3	2132.3	2102.8	2056.1
25°	2174.1	2174.1	2176.6	2179.1	2176.6	2174.1	2174.1	2147.1	2083.2	2075.8	2048.8
27.5°	2122.5	2127.4	2142.2	2139.7	2142.2	2127.4	2122.5	2112.6	2043.8	2036.5	2016.8
30°	2075.8	2070.8	2058.5	2048.8	2058.5	2070.8	2075.8	2061.0	1992.2	1972.5	1977.3
32.5°	1997.1	1984.8	1972.5	1965.1	1972.5	1984.8	1997.1	1992.2	1940.5	1913.5	1918.3
35°	1903.6	1906.0	1903.6	1896.2	1903.6	1906.0	1903.6	1908.5	1876.6	1852.0	1849.5
37.5°	1837.2	1842.1	1839.6	1829.9	1839.6	1842.1	1837.2	1832.3	1788.0	1780.6	1785.6
40°	1768.3	1770.8	1768.3	1761.0	1768.3	1770.8	1768.3	1758.5	1697.0	1699.4	1716.7
42.5°	1702.0	1699.4	1692.1	1687.1	1692.1	1699.4	1702.0	1687.1	1608.4	1601.1	1633.1
45°	1625.7	1628.1	1613.4	1606.0	1613.4	1628.1	1625.7	1615.8	1534.7	1515.0	1537.1
47.5°	1549.4	1549.4	1537.1	1529.8	1537.1	1549.4	1549.4	1537.1	1451.1	1431.4	1443.7
50°	1468.3	1465.8	1448.7	1446.1	1448.7	1465.8	1468.3	1460.9	1369.9	1352.7	1352.7
52.5°	1374.8	1374.8	1377.2	1382.2	1377.2	1374.8	1374.8	1377.2	1296.1	1278.9	1273.9
55°	1293.6	1296.1	1313.4	1318.2	1313.4	1296.1	1293.6	1293.6	1219.9	1202.6	1192.8
57.5°	1210.1	1210.1	1222.3	1222.3	1222.3	1210.1	1210.1	1205.1	1133.8	1119.0	1114.2
60°	1114.2	1119.0	1128.9	1126.5	1128.9	1119.0	1114.2	1109.2	1047.7	1037.9	1020.6
62.5°	1013.3	1018.2	1020.6	1015.7	1020.6	1018.2	1013.3	998.6	961.6	954.3	932.1
65°	907.6	912.4	914.9	910.0	914.9	912.4	907.6	900.2	873.1	860.8	841.1
67.5°	799.3	796.8	794.4	804.3	794.4	796.8	799.3	789.4	772.3	762.4	735.4
70°	688.7	688.7	686.1	691.1	686.1	688.7	688.7	681.3	671.4	664.1	639.4
72.5°	570.5	568.1	578.0	570.5	578.0	568.1	570.5	568.1	563.2	555.8	531.2
75°	455.0	459.9	455.0	462.4	455.0	459.9	455.0	457.5	455.0	450.1	432.9
77.5°	346.8	351.7	346.8	346.8	346.8	351.7	346.8	349.2	349.2	349.2	334.5
80°	245.9	243.5	243.5	241.0	243.5	243.5	245.9	245.9	248.4	243.5	238.6
82.5°	157.4	154.9	154.9	159.9	154.9	154.9	157.4	159.9	154.9	154.9	154.9
85°	86.0	88.6	83.6	83.6	83.6	88.6	86.0	81.2	86.0	86.0	83.6
87.5°	32.0	29.6	29.6	29.6	29.6	29.6	32.0	34.4	34.4	34.4	36.9
90°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	15.1	20.3	22.8	19.6
92.5°	56.9	54.7	45.5	36.5	45.5	54.7	56.9	80.6	112.3	128.2	112.6
95°	193.2	186.3	158.9	131.5	158.9	186.3	193.2	253.8	334.5	374.8	316.6
97.5°	446.0	432.9	380.8	328.7	380.8	432.9	446.0	484.3	535.4	560.9	463.8
100°	626.5	611.0	548.7	486.5	548.7	611.0	626.5	623.6	619.9	618.0	510.3
102.5°	780.4	767.2	713.9	660.6	713.9	767.2	780.4	731.7	666.7	634.2	524.9
105°	960.2	953.0	924.4	895.7	924.4	953.0	960.2	850.9	705.2	632.4	526.6
107.5°	1053.6	1055.3	1062.2	1069.2	1062.2	1055.3	1053.6	901.2	698.0	596.4	503.1
110°	1077.6	1085.1	1114.8	1144.7	1114.8	1085.1	1077.6	907.3	680.0	566.5	482.4

TEST NUMBER: P934589

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1062.3	1073.7	1119.6	1165.3	1119.6	1073.7	1062.3	888.0	655.5	539.2	464.2
115°	1010.5	1026.4	1089.8	1153.4	1089.8	1026.4	1010.5	842.5	618.6	506.6	443.4
117.5°	938.9	956.5	1026.9	1097.4	1026.9	956.5	938.9	787.3	585.2	484.1	430.4
120°	890.6	907.8	976.2	1044.7	976.2	907.8	890.6	752.1	567.4	475.1	426.0
122.5°	842.4	859.3	926.8	994.3	926.8	859.3	842.4	717.7	551.4	468.2	423.6
125°	778.6	794.1	856.3	918.5	856.3	794.1	778.6	672.7	531.4	460.8	421.8
127.5°	727.3	740.4	792.9	845.5	792.9	740.4	727.3	636.3	515.1	454.5	420.7
130°	695.1	707.2	755.6	804.1	755.6	707.2	695.1	614.1	506.0	452.0	421.3
132.5°	667.4	678.3	721.7	765.1	721.7	678.3	667.4	595.0	498.4	450.0	421.8
135°	628.5	637.9	675.3	712.7	675.3	637.9	628.5	567.8	486.9	446.4	421.4
137.5°	599.7	607.4	638.1	668.7	638.1	607.4	599.7	548.4	479.9	445.7	423.9
140°	576.7	583.8	612.4	641.1	612.4	583.8	576.7	532.4	473.3	443.7	424.4
142.5°	560.5	566.7	591.3	615.9	591.3	566.7	560.5	521.5	469.7	443.7	426.0
145°	536.2	540.9	559.6	578.2	559.6	540.9	536.2	504.4	461.9	440.7	426.0
147.5°	515.9	519.8	535.2	550.6	535.2	519.8	515.9	490.8	457.4	440.7	428.9
150°	504.2	507.3	519.9	532.4	519.9	507.3	504.2	483.0	454.8	440.7	430.4
152.5°	494.9	497.2	506.7	516.2	506.7	497.2	494.9	476.8	452.7	440.7	431.4
155°	483.8	485.4	491.7	497.9	491.7	485.4	483.8	469.5	450.3	440.7	433.6
157.5°	474.2	475.3	479.8	484.1	479.8	475.3	474.2	463.1	448.2	440.7	435.9
160°	469.5	470.1	472.6	475.1	472.6	470.1	469.5	459.9	447.1	440.7	436.8
162.5°	464.9	465.5	467.9	470.4	467.9	465.5	464.9	456.9	446.1	440.7	437.9
165°	458.0	458.7	461.2	463.8	461.2	458.7	458.0	452.2	444.6	440.7	439.4
167.5°	455.0	455.3	456.4	457.5	456.4	455.3	455.0	451.3	446.2	443.7	442.6
170°	455.0	455.0	455.0	455.0	455.0	455.0	455.0	451.3	446.2	443.7	443.6
172.5°	452.6	452.4	451.5	450.6	451.5	452.4	452.6	449.6	445.6	443.7	443.7
175°	449.3	449.3	449.3	449.3	449.3	449.3	449.3	447.5	445.0	443.7	444.3
177.5°	448.7	448.5	447.5	446.4	447.5	448.5	448.7	447.3	445.3	444.3	444.8
180°	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4	446.4

TEST NUMBER: P934589

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2599.6	2599.6	2599.6	2599.6	2599.6
2.5°	2567.7	2580.0	2587.3	2597.2	2621.7
5°	2469.3	2516.0	2530.7	2567.7	2611.9
7.5°	2252.8	2395.5	2434.8	2523.4	2592.3
10°	2043.8	2186.5	2255.3	2464.4	2567.7
12.5°	1938.0	2021.6	2068.4	2361.1	2533.3
15°	1871.6	1930.6	1965.1	2223.4	2493.9
17.5°	1820.0	1861.8	1886.4	2088.1	2439.7
20°	1788.0	1807.7	1829.9	1989.6	2378.3
22.5°	1765.9	1753.6	1770.8	1920.8	2294.7
25°	1751.1	1704.4	1724.0	1866.7	2196.2
27.5°	1763.4	1660.1	1667.5	1817.6	2092.9
30°	1765.9	1606.0	1608.4	1765.9	1977.3
32.5°	1748.7	1549.4	1552.0	1702.0	1847.0
35°	1706.9	1483.1	1480.5	1628.1	1670.0
37.5°	1650.3	1411.7	1411.7	1547.0	1475.7
40°	1581.4	1340.4	1347.8	1441.2	1303.5
42.5°	1497.8	1264.2	1273.9	1301.1	1175.6
45°	1406.8	1190.3	1197.8	1099.3	1077.2
47.5°	1305.9	1114.2	1116.6	912.4	1045.3
50°	1185.5	1035.4	1025.6	782.1	1042.8
52.5°	1079.7	949.3	919.9	708.3	946.9
55°	976.4	858.3	794.4	651.7	878.0
57.5°	885.4	740.3	678.8	585.4	863.3
60°	801.8	624.7	578.0	514.1	792.0
62.5°	733.0	538.6	528.8	464.8	718.1
65°	659.1	479.6	477.1	423.1	610.0
67.5°	587.8	440.2	437.8	383.6	464.8
70°	511.5	398.5	393.5	341.9	344.3
72.5°	432.9	351.7	346.8	307.5	285.3
75°	354.2	297.6	295.2	268.1	231.2
77.5°	277.9	236.1	241.0	216.5	169.7
80°	199.2	172.2	177.0	154.9	127.9
82.5°	132.8	113.2	118.0	98.4	86.0
85°	73.7	64.0	66.4	51.6	39.3
87.5°	34.4	29.6	29.6	19.7	12.3
90°	13.2	8.4	7.8	5.4	3.0
92.5°	81.3	57.8	52.7	32.4	12.0
95°	200.0	112.6	103.3	66.0	28.8
97.5°	269.5	123.7	115.5	82.7	49.7
100°	294.7	133.0	125.6	95.7	65.9
102.5°	306.3	142.3	135.4	107.6	79.7
105°	314.8	156.1	150.2	126.6	103.1
107.5°	316.5	176.5	170.9	149.0	127.0
110°	314.1	187.8	182.9	163.0	143.2



TEST NUMBER: P934589

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	314.1	201.6	196.9	178.0	159.1
115°	317.1	222.3	217.9	200.5	183.0
117.5°	323.0	242.3	238.4	222.6	206.7
120°	327.7	254.1	250.3	235.4	220.4
122.5°	334.6	267.8	264.1	249.0	234.0
125°	343.9	285.5	282.1	268.3	254.7
127.5°	353.2	302.6	299.1	285.3	271.4
130°	360.0	314.0	310.3	295.4	280.4
132.5°	365.5	323.3	319.6	304.7	289.7
135°	371.5	334.0	330.6	317.1	303.5
137.5°	380.4	347.8	344.4	331.0	317.5
140°	386.0	357.1	354.0	341.7	329.3
142.5°	390.5	364.0	361.0	349.6	338.2
145°	396.6	374.5	372.0	362.0	352.0
147.5°	405.3	387.7	385.3	375.5	365.8
150°	410.0	394.6	392.3	383.6	374.8
152.5°	412.9	399.0	397.4	390.7	384.0
155°	419.5	408.9	407.7	402.8	397.9
157.5°	426.1	418.8	417.6	412.8	408.0
160°	429.1	423.3	422.3	418.6	414.9
162.5°	432.3	428.1	427.4	424.6	421.8
165°	436.9	435.0	434.3	431.8	429.3
167.5°	440.5	438.9	438.6	437.3	436.1
170°	443.5	443.4	443.1	441.9	440.7
172.5°	443.7	443.7	443.6	443.4	443.1
175°	445.5	446.4	446.4	446.4	446.4
177.5°	445.7	446.4	446.4	446.4	446.4
180°	446.4	446.4	446.4	446.4	446.4

TEST NUMBER: P934589

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.12	17.19	16.88	17.98	18.94	18.94	20.02	19.71	20.81	21.76
	3H	16.61	17.58	17.39	18.37	19.36	20.30	21.27	21.08	22.07	23.05
	4H	16.81	17.72	17.61	18.53	19.53	20.76	21.67	21.55	22.47	23.47
	6H	16.94	17.78	17.75	18.60	19.61	21.05	21.89	21.86	22.70	23.71
	8H	16.95	17.75	17.77	18.58	19.59	21.13	21.93	21.95	22.76	23.77
	12H	16.93	17.69	17.75	18.52	19.56	21.18	21.94	22.00	22.77	23.80
4H	2H	17.18	18.09	17.98	18.89	19.89	19.38	20.29	20.18	21.10	22.09
	3H	18.22	18.98	19.04	19.82	20.83	20.90	21.66	21.72	22.50	23.51
	4H	18.51	19.20	19.33	20.04	21.08	21.44	22.13	22.27	22.97	24.01
	6H	18.65	19.24	19.49	20.11	21.15	21.82	22.41	22.66	23.27	24.32
	8H	18.66	19.21	19.50	20.07	21.13	21.93	22.48	22.77	23.34	24.40
	12H	18.63	19.14	19.50	20.01	21.08	21.99	22.49	22.86	23.37	24.44
8H	4H	18.98	19.54	19.82	20.39	21.45	21.58	22.14	22.43	23.00	24.05
	6H	19.25	19.71	20.12	20.61	21.67	22.02	22.49	22.90	23.39	24.44
	8H	19.29	19.70	20.18	20.60	21.67	22.18	22.59	23.06	23.48	24.56
	12H	19.29	19.65	20.18	20.53	21.66	22.29	22.65	23.17	23.53	24.66
12H	4H	18.99	19.50	19.86	20.37	21.44	21.56	22.06	22.42	22.94	24.00
	6H	19.31	19.72	20.20	20.62	21.69	22.02	22.43	22.91	23.33	24.40
	8H	19.39	19.75	20.28	20.63	21.76	22.19	22.56	23.08	23.44	24.57

END OF REPORT