

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934989

Luminaire Tested: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934989
REPORT IS A COMBINATION OF REPORTS P933719 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11095.0 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 93
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934989

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P934989

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	56	56	51
2	91	84	78	72	85	79	73	68	69	65	61	60	57	54	52	49	47	47	47	43
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	40	40	36
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35	35	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	30	30	27
6	65	52	44	38	60	49	42	36	44	37	33	38	33	30	33	29	26	26	26	24
7	60	47	39	33	56	45	37	32	39	33	29	35	30	26	30	26	23	23	23	21
8	55	43	35	29	52	40	33	28	36	30	26	32	27	23	28	24	21	21	21	19
9	52	39	31	26	48	37	30	25	33	27	23	29	24	21	26	22	19	19	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16082	16082	16082	16082
5°	16196	16233	16196	12765
10°	16082	15991	16082	11432
15°	15901	15645	15901	13063
20°	15562	15234	15562	13091
25°	14875	14636	14875	12813
30°	13990	14139	13990	12205
35°	12466	13510	12466	11535
40°	10381	12770	10381	11030
45°	9269	11904	9269	10448
50°	9840	10870	9840	9864
55°	9249	9757	9249	9526
60°	9524	8287	9524	8726
65°	8621	6851	8621	7658
70°	5955	5459	5955	6419
75°	5202	4035	5202	4833
80°	4163	2667	4163	2905
85°	2343	1413	2343	1201

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 14216 cd/sqm

TEST NUMBER: P934989

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.7	2.1
10°-20°	666.3	6.0
20°-30°	1029.9	9.3
30°-40°	1229.5	11.1
40°-50°	1236.7	11.1
50°-60°	1076.1	9.7
60°-70°	763.0	6.9
70°-80°	403.7	3.6
80°-90°	103.1	0.9
90°-100°	327.2	2.9
100°-110°	860.4	7.8
110°-120°	892.1	8.0
120°-130°	715.6	6.4
130°-140°	561.5	5.1
140°-150°	431.0	3.9
150°-160°	310.4	2.8
160°-170°	189.9	1.7
170°-180°	64.2	0.6
0°-30°	1930.9	17.4
0°-40°	3160.4	28.5
0°-60°	5473.2	49.3
0°-90°	6742.9	60.8
90°-120°	2079.7	18.7
90°-150°	3787.7	34.1
90°-180°	4352.0	39.2
0°-180°	11095.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2600	2600	2600	2600	2600	
5°	2612	2693	2612	2118	2612	248
15°	2494	2668	2494	2228	2494	702
25°	2196	2489	2196	2179	2196	1008
35°	1670	2221	1670	1896	1670	1033
45°	1077	1830	1077	1606	1077	863
55°	878	1350	878	1318	878	807
65°	610	814	610	910	610	583
75°	231	386	231	462	231	243
85°	39	98	39	84	39	53
90°	4	17	4	17	4	5
95°	43	198	43	198	43	48
105°	155	1347	155	1347	155	164
115°	275	1735	275	1735	275	272
125°	383	1382	383	1382	383	340
135°	456	1072	456	1072	456	353
145°	530	870	530	870	530	332
155°	598	749	598	749	598	275
165°	646	698	646	698	646	182
175°	671	676	671	676	671	64
180°	671	671	671	671	671	

TEST NUMBER: P934989

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6
2.5°	2621.7	2621.7	2636.6	2641.4	2641.4	2634.0	2626.7	2634.0	2656.2	2663.6	2661.1
5°	2611.9	2631.6	2658.6	2663.6	2668.5	2666.0	2661.1	2666.0	2690.6	2695.6	2698.0
7.5°	2592.3	2629.1	2663.6	2671.0	2678.3	2671.0	2668.5	2673.4	2698.0	2702.9	2702.9
10°	2567.7	2619.3	2658.6	2663.6	2671.0	2663.6	2663.6	2673.4	2698.0	2702.9	2705.4
12.5°	2533.3	2604.6	2641.4	2646.3	2656.2	2653.7	2651.3	2661.1	2685.7	2690.6	2690.6
15°	2493.9	2577.4	2611.9	2616.9	2634.0	2629.1	2629.1	2639.0	2666.0	2673.4	2671.0
17.5°	2439.7	2543.0	2582.4	2589.7	2602.1	2599.6	2602.1	2611.9	2636.6	2641.4	2643.9
20°	2378.3	2496.3	2543.0	2550.4	2562.7	2562.7	2562.7	2575.0	2599.6	2609.4	2609.4
22.5°	2294.7	2447.1	2496.3	2501.3	2516.0	2516.0	2521.0	2538.1	2560.3	2562.7	2562.7
25°	2196.2	2393.0	2434.8	2449.6	2464.4	2471.7	2479.1	2489.0	2496.3	2493.9	2496.3
27.5°	2092.9	2324.1	2378.3	2388.1	2407.8	2415.1	2425.0	2427.4	2430.0	2437.3	2432.4
30°	1977.3	2228.2	2309.4	2319.2	2351.2	2356.1	2346.3	2351.2	2363.5	2368.4	2373.4
32.5°	1847.0	2085.6	2238.1	2260.2	2289.7	2275.0	2272.5	2279.9	2299.5	2299.5	2304.5
35°	1670.0	1974.9	2171.7	2191.4	2213.5	2196.2	2206.1	2208.5	2220.9	2228.2	2225.8
37.5°	1475.7	1879.0	2102.8	2117.6	2134.8	2112.6	2127.4	2134.8	2144.6	2139.7	2139.7
40°	1303.5	1729.0	2021.6	2031.5	2046.2	2029.0	2043.8	2048.8	2053.6	2048.8	2046.2
42.5°	1175.6	1564.2	1935.6	1947.9	1938.0	1950.3	1955.2	1965.1	1957.7	1947.9	1947.9
45°	1077.2	1520.0	1842.1	1856.9	1842.1	1861.8	1869.2	1869.2	1847.0	1842.1	1839.6
47.5°	1045.3	1431.4	1748.7	1748.7	1741.3	1765.9	1778.2	1761.0	1738.8	1731.4	1731.4
50°	1042.8	1333.1	1620.7	1611.0	1645.4	1674.9	1662.6	1645.4	1628.1	1601.1	1601.1
52.5°	946.9	1212.5	1456.0	1492.8	1547.0	1564.2	1544.5	1527.3	1497.8	1485.5	1475.7
55°	878.0	1087.0	1305.9	1379.8	1436.3	1458.4	1421.5	1404.4	1360.1	1352.7	1347.8
57.5°	863.3	905.0	1168.2	1261.7	1330.5	1328.1	1305.9	1273.9	1237.1	1229.8	1227.2
60°	792.0	654.2	1020.6	1131.3	1202.6	1195.3	1175.6	1146.1	1111.6	1106.8	1101.8
62.5°	718.1	474.7	853.4	978.9	1079.7	1077.2	1060.0	1015.7	991.2	978.9	969.0
65°	610.0	398.5	607.5	814.1	959.2	964.1	927.2	895.3	868.2	853.4	851.0
67.5°	464.8	324.6	410.8	678.8	843.6	838.7	792.0	777.1	742.7	735.4	720.6
70°	344.3	216.5	285.3	550.9	730.4	718.1	681.3	664.1	632.1	614.8	605.0
72.5°	285.3	174.6	209.0	427.9	614.8	600.1	568.1	548.5	521.4	506.7	496.8
75°	231.2	184.5	159.9	317.3	499.2	489.4	459.9	440.2	418.1	398.5	400.9
77.5°	169.7	172.2	127.9	233.6	395.9	381.2	364.0	339.4	329.6	309.9	309.9
80°	127.9	135.3	95.9	159.9	285.3	285.3	270.5	253.3	236.1	226.3	226.3
82.5°	86.0	86.0	71.3	100.9	194.3	186.9	177.0	172.2	162.3	157.4	157.4
85°	39.3	49.2	44.3	61.5	105.7	110.7	110.7	105.7	103.3	98.4	100.9
87.5°	12.3	22.1	27.0	34.4	54.1	56.6	59.0	59.0	59.0	61.5	61.5
90°	4.5	8.0	11.7	12.6	19.8	29.4	34.2	30.4	22.9	17.2	17.2
92.5°	18.0	48.6	79.3	86.9	122.2	169.3	192.8	169.0	121.3	85.6	82.2
95°	43.2	99.3	155.3	169.4	300.8	476.1	563.7	503.0	381.6	290.6	280.3
97.5°	74.8	124.2	173.6	186.0	405.2	697.4	843.5	805.1	728.5	670.9	651.3
100°	99.1	144.0	188.9	200.1	443.2	767.4	929.6	932.4	938.0	942.2	918.8
102.5°	119.9	161.7	203.6	214.1	460.7	789.4	953.9	1002.7	1100.5	1173.7	1153.7
105°	155.0	190.5	226.0	234.8	473.6	792.0	951.2	1060.7	1279.8	1444.1	1433.3
107.5°	191.1	224.1	257.2	265.4	476.0	756.7	897.1	1049.9	1355.5	1584.7	1587.3
110°	215.4	245.3	275.0	282.5	472.3	725.5	852.0	1022.9	1364.5	1620.7	1632.0

TEST NUMBER: P934989

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	239.2	267.6	296.1	303.2	472.5	698.2	811.1	985.9	1335.5	1597.7	1614.9
115°	275.3	301.6	327.7	334.3	476.8	666.9	761.9	930.3	1267.2	1519.8	1543.6
117.5°	310.9	334.7	358.5	364.5	485.8	647.3	728.1	880.1	1184.1	1412.1	1438.6
120°	331.6	354.1	376.5	382.1	492.9	640.7	714.6	853.5	1131.2	1339.5	1365.3
122.5°	351.9	374.5	397.2	402.8	503.3	637.3	704.3	829.3	1079.4	1267.0	1292.4
125°	382.9	403.6	424.2	429.4	517.3	634.4	693.0	799.2	1011.7	1171.0	1194.4
127.5°	408.2	429.1	449.8	455.0	531.2	632.8	683.5	774.7	957.2	1094.0	1113.8
130°	421.7	444.2	466.6	472.2	541.5	633.8	679.9	761.1	923.6	1045.4	1063.6
132.5°	435.7	458.1	480.5	486.1	549.7	634.4	676.7	749.4	894.9	1003.9	1020.2
135°	456.4	476.8	497.3	502.4	558.7	633.8	671.3	732.2	854.0	945.3	959.3
137.5°	477.6	497.8	518.0	523.1	572.2	637.7	670.5	721.9	824.8	902.0	913.6
140°	495.2	513.8	532.5	537.1	580.5	638.4	667.3	711.7	800.7	867.4	878.1
142.5°	508.7	526.0	543.2	547.5	587.4	640.6	667.3	706.3	784.4	843.0	852.3
145°	529.5	544.5	559.4	563.2	596.4	640.7	662.8	694.8	758.6	806.5	813.5
147.5°	550.1	564.7	579.4	583.0	609.6	645.1	662.8	687.9	738.2	775.9	781.7
150°	563.7	576.8	590.1	593.4	616.6	647.4	662.8	684.0	726.5	758.3	763.1
152.5°	577.6	587.7	597.7	600.2	621.0	648.8	662.8	680.9	717.2	744.4	748.0
155°	598.4	605.7	613.2	615.0	630.9	652.1	662.8	677.2	706.1	727.7	730.0
157.5°	613.7	620.9	628.1	629.9	640.9	655.5	662.8	674.0	696.4	713.3	714.9
160°	624.0	629.7	635.3	636.6	645.4	657.0	662.8	672.4	691.6	706.0	707.0
162.5°	634.4	638.7	642.8	643.9	650.2	658.6	662.8	670.9	687.1	699.3	700.2
165°	645.6	649.5	653.3	654.3	657.1	660.9	662.8	668.6	680.2	689.0	689.9
167.5°	656.0	657.9	659.6	660.1	662.5	665.7	667.3	671.0	678.7	684.4	684.8
170°	662.8	664.6	666.4	666.9	667.0	667.2	667.3	671.0	678.7	684.4	684.4
172.5°	666.4	666.8	667.2	667.3	667.3	667.3	667.3	670.3	676.3	680.8	680.4
175°	671.3	671.3	671.3	671.3	670.0	668.1	667.3	669.2	673.0	675.9	675.9
177.5°	671.3	671.3	671.3	671.3	670.3	668.9	668.2	669.8	672.8	675.0	674.6
180°	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3

TEST NUMBER: P934989

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6
2.5°	2666.0	2658.6	2666.0	2661.1	2663.6	2656.2	2634.0	2626.7	2634.0	2641.4	2641.4
5°	2698.0	2693.0	2698.0	2698.0	2695.6	2690.6	2666.0	2661.1	2666.0	2668.5	2663.6
7.5°	2707.9	2700.5	2707.9	2702.9	2702.9	2698.0	2673.4	2668.5	2671.0	2678.3	2671.0
10°	2707.9	2700.5	2707.9	2705.4	2702.9	2698.0	2673.4	2663.6	2663.6	2671.0	2663.6
12.5°	2695.6	2690.6	2695.6	2690.6	2690.6	2685.7	2661.1	2651.3	2653.7	2656.2	2646.3
15°	2675.9	2668.5	2675.9	2671.0	2673.4	2666.0	2639.0	2629.1	2629.1	2634.0	2616.9
17.5°	2646.3	2636.6	2646.3	2643.9	2641.4	2636.6	2611.9	2602.1	2599.6	2602.1	2589.7
20°	2611.9	2604.6	2611.9	2609.4	2609.4	2599.6	2575.0	2562.7	2562.7	2562.7	2550.4
22.5°	2557.8	2550.4	2557.8	2562.7	2562.7	2560.3	2538.1	2521.0	2516.0	2516.0	2501.3
25°	2496.3	2489.0	2496.3	2496.3	2493.9	2496.3	2489.0	2479.1	2471.7	2464.4	2449.6
27.5°	2437.3	2432.4	2437.3	2432.4	2437.3	2430.0	2427.4	2425.0	2415.1	2407.8	2388.1
30°	2378.3	2373.4	2378.3	2373.4	2368.4	2363.5	2351.2	2346.3	2356.1	2351.2	2319.2
32.5°	2304.5	2299.5	2304.5	2304.5	2299.5	2299.5	2279.9	2272.5	2275.0	2289.7	2260.2
35°	2228.2	2220.9	2228.2	2225.8	2228.2	2220.9	2208.5	2206.1	2196.2	2213.5	2191.4
37.5°	2139.7	2132.3	2139.7	2139.7	2139.7	2144.6	2134.8	2127.4	2112.6	2134.8	2117.6
40°	2048.8	2038.9	2048.8	2046.2	2048.8	2053.6	2048.8	2043.8	2029.0	2046.2	2031.5
42.5°	1945.5	1942.9	1945.5	1947.9	1947.9	1957.7	1965.1	1955.2	1950.3	1938.0	1947.9
45°	1834.7	1829.9	1834.7	1839.6	1842.1	1847.0	1869.2	1869.2	1861.8	1842.1	1856.9
47.5°	1716.7	1704.4	1716.7	1731.4	1731.4	1738.8	1761.0	1778.2	1765.9	1741.3	1748.7
50°	1591.3	1593.7	1591.3	1601.1	1601.1	1628.1	1645.4	1662.6	1674.9	1645.4	1611.0
52.5°	1468.3	1465.8	1468.3	1475.7	1485.5	1497.8	1527.3	1544.5	1564.2	1547.0	1492.8
55°	1345.3	1350.2	1345.3	1347.8	1352.7	1360.1	1404.4	1421.5	1458.4	1436.3	1379.8
57.5°	1222.3	1214.9	1222.3	1227.2	1229.8	1237.1	1273.9	1305.9	1328.1	1330.5	1261.7
60°	1079.7	1069.9	1079.7	1101.8	1106.8	1111.6	1146.1	1175.6	1195.3	1202.6	1131.3
62.5°	954.3	937.0	954.3	969.0	978.9	991.2	1015.7	1060.0	1077.2	1079.7	978.9
65°	821.4	814.1	821.4	851.0	853.4	868.2	895.3	927.2	964.1	959.2	814.1
67.5°	701.0	701.0	701.0	720.6	735.4	742.7	777.1	792.0	838.7	843.6	678.8
70°	590.2	587.8	590.2	605.0	614.8	632.1	664.1	681.3	718.1	730.4	550.9
72.5°	484.5	482.1	484.5	496.8	506.7	521.4	548.5	568.1	600.1	614.8	427.9
75°	391.1	386.1	391.1	400.9	398.5	418.1	440.2	459.9	489.4	499.2	317.3
77.5°	300.1	300.1	300.1	309.9	309.9	329.6	339.4	364.0	381.2	395.9	233.6
80°	223.8	221.3	223.8	226.3	226.3	236.1	253.3	270.5	285.3	285.3	159.9
82.5°	157.4	152.5	157.4	157.4	157.4	162.3	172.2	177.0	186.9	194.3	100.9
85°	98.4	98.4	98.4	100.9	98.4	103.3	105.7	110.7	110.7	105.7	61.5
87.5°	64.0	61.5	64.0	61.5	61.5	59.0	59.0	59.0	56.6	54.1	34.4
90°	17.2	17.2	17.2	17.2	17.2	22.9	30.4	34.2	29.4	19.8	12.6
92.5°	68.5	54.9	68.5	82.2	85.6	121.3	169.0	192.8	169.3	122.2	86.9
95°	239.1	197.8	239.1	280.3	290.6	381.6	503.0	563.7	476.1	300.8	169.4
97.5°	572.8	494.3	572.8	651.3	670.9	728.5	805.1	843.5	697.4	405.2	186.0
100°	825.2	731.7	825.2	918.8	942.2	938.0	932.4	929.6	767.4	443.2	200.1
102.5°	1073.7	993.5	1073.7	1153.7	1173.7	1100.5	1002.7	953.9	789.4	460.7	214.1
105°	1390.2	1347.2	1390.2	1433.3	1444.1	1279.8	1060.7	951.2	792.0	473.6	234.8
107.5°	1597.7	1608.1	1597.7	1587.3	1584.7	1355.5	1049.9	897.1	756.7	476.0	265.4
110°	1676.8	1721.6	1676.8	1632.0	1620.7	1364.5	1022.9	852.0	725.5	472.3	282.5

TEST NUMBER: P934989

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1683.8	1752.7	1683.8	1614.9	1597.7	1335.5	985.9	811.1	698.2	472.5	303.2
115°	1639.2	1734.7	1639.2	1543.6	1519.8	1267.2	930.3	761.9	666.9	476.8	334.3
117.5°	1544.5	1650.4	1544.5	1438.6	1412.1	1184.1	880.1	728.1	647.3	485.8	364.5
120°	1468.2	1571.1	1468.2	1365.3	1339.5	1131.2	853.5	714.6	640.7	492.9	382.1
122.5°	1393.9	1495.5	1393.9	1292.4	1267.0	1079.4	829.3	704.3	637.3	503.3	402.8
125°	1288.0	1381.5	1288.0	1194.4	1171.0	1011.7	799.2	693.0	634.4	517.3	429.4
127.5°	1192.6	1271.5	1192.6	1113.8	1094.0	957.2	774.7	683.5	632.8	531.2	455.0
130°	1136.4	1209.3	1136.4	1063.6	1045.4	923.6	761.1	679.9	633.8	541.5	472.2
132.5°	1085.5	1150.8	1085.5	1020.2	1003.9	894.9	749.4	676.7	634.4	549.7	486.1
135°	1015.6	1071.9	1015.6	959.3	945.3	854.0	732.2	671.3	633.8	558.7	502.4
137.5°	959.6	1005.7	959.6	913.6	902.0	824.8	721.9	670.5	637.7	572.2	523.1
140°	921.2	964.3	921.2	878.1	867.4	800.7	711.7	667.3	638.4	580.5	537.1
142.5°	889.3	926.4	889.3	852.3	843.0	784.4	706.3	667.3	640.6	587.4	547.5
145°	841.6	869.6	841.6	813.5	806.5	758.6	694.8	662.8	640.7	596.4	563.2
147.5°	804.9	828.1	804.9	781.7	775.9	738.2	687.9	662.8	645.1	609.6	583.0
150°	781.9	800.7	781.9	763.1	758.3	726.5	684.0	662.8	647.4	616.6	593.4
152.5°	762.1	776.4	762.1	748.0	744.4	717.2	680.9	662.8	648.8	621.0	600.2
155°	739.4	748.8	739.4	730.0	727.7	706.1	677.2	662.8	652.1	630.9	615.0
157.5°	721.5	728.1	721.5	714.9	713.3	696.4	674.0	662.8	655.5	640.9	629.9
160°	710.8	714.6	710.8	707.0	706.0	691.6	672.4	662.8	657.0	645.4	636.6
162.5°	703.8	707.4	703.8	700.2	699.3	687.1	670.9	662.8	658.6	650.2	643.9
165°	693.7	697.5	693.7	689.9	689.0	680.2	668.6	662.8	660.9	657.1	654.3
167.5°	686.4	688.0	686.4	684.8	684.4	678.7	671.0	667.3	665.7	662.5	660.1
170°	684.4	684.4	684.4	684.4	684.4	678.7	671.0	667.3	667.2	667.0	666.9
172.5°	679.1	677.6	679.1	680.4	680.8	676.3	670.3	667.3	667.3	667.3	667.3
175°	675.9	675.9	675.9	675.9	675.9	673.0	669.2	667.3	668.1	670.0	671.3
177.5°	673.0	671.3	673.0	674.6	675.0	672.8	669.8	668.2	668.9	670.3	671.3
180°	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3

TEST NUMBER: P934989

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6
2.5°	2636.6	2621.7	2621.7	2597.2	2587.3	2580.0	2567.7	2530.7	2521.0	2511.1	2525.8
5°	2658.6	2631.6	2611.9	2567.7	2530.7	2516.0	2469.3	2380.7	2321.7	2277.4	2252.8
7.5°	2663.6	2629.1	2592.3	2523.4	2434.8	2395.5	2252.8	2090.5	2046.2	2006.9	1982.3
10°	2658.6	2619.3	2567.7	2464.4	2255.3	2186.5	2043.8	1938.0	1911.0	1903.6	1911.0
12.5°	2641.4	2604.6	2533.3	2361.1	2068.4	2021.6	1938.0	1876.6	1871.6	1883.9	1950.3
15°	2611.9	2577.4	2493.9	2223.4	1965.1	1930.6	1871.6	1849.5	1876.6	1962.6	2161.8
17.5°	2582.4	2543.0	2439.7	2088.1	1886.4	1861.8	1820.0	1864.3	2016.8	2132.3	2198.8
20°	2543.0	2496.3	2378.3	1989.6	1829.9	1807.7	1788.0	1987.2	2102.8	2144.6	2181.5
22.5°	2496.3	2447.1	2294.7	1920.8	1770.8	1753.6	1765.9	2056.1	2102.8	2132.3	2164.3
25°	2434.8	2393.0	2196.2	1866.7	1724.0	1704.4	1751.1	2048.8	2075.8	2083.2	2147.1
27.5°	2378.3	2324.1	2092.9	1817.6	1667.5	1660.1	1763.4	2016.8	2036.5	2043.8	2112.6
30°	2309.4	2228.2	1977.3	1765.9	1608.4	1606.0	1765.9	1977.3	1972.5	1992.2	2061.0
32.5°	2238.1	2085.6	1847.0	1702.0	1552.0	1549.4	1748.7	1918.3	1913.5	1940.5	1992.2
35°	2171.7	1974.9	1670.0	1628.1	1480.5	1483.1	1706.9	1849.5	1852.0	1876.6	1908.5
37.5°	2102.8	1879.0	1475.7	1547.0	1411.7	1411.7	1650.3	1785.6	1780.6	1788.0	1832.3
40°	2021.6	1729.0	1303.5	1441.2	1347.8	1340.4	1581.4	1716.7	1699.4	1697.0	1758.5
42.5°	1935.6	1564.2	1175.6	1301.1	1273.9	1264.2	1497.8	1633.1	1601.1	1608.4	1687.1
45°	1842.1	1520.0	1077.2	1099.3	1197.8	1190.3	1406.8	1537.1	1515.0	1534.7	1615.8
47.5°	1748.7	1431.4	1045.3	912.4	1116.6	1114.2	1305.9	1443.7	1431.4	1451.1	1537.1
50°	1620.7	1333.1	1042.8	782.1	1025.6	1035.4	1185.5	1352.7	1352.7	1369.9	1460.9
52.5°	1456.0	1212.5	946.9	708.3	919.9	949.3	1079.7	1273.9	1278.9	1296.1	1377.2
55°	1305.9	1087.0	878.0	651.7	794.4	858.3	976.4	1192.8	1202.6	1219.9	1293.6
57.5°	1168.2	905.0	863.3	585.4	678.8	740.3	885.4	1114.2	1119.0	1133.8	1205.1
60°	1020.6	654.2	792.0	514.1	578.0	624.7	801.8	1020.6	1037.9	1047.7	1109.2
62.5°	853.4	474.7	718.1	464.8	528.8	538.6	733.0	932.1	954.3	961.6	998.6
65°	607.5	398.5	610.0	423.1	477.1	479.6	659.1	841.1	860.8	873.1	900.2
67.5°	410.8	324.6	464.8	383.6	437.8	440.2	587.8	735.4	762.4	772.3	789.4
70°	285.3	216.5	344.3	341.9	393.5	398.5	511.5	639.4	664.1	671.4	681.3
72.5°	209.0	174.6	285.3	307.5	346.8	351.7	432.9	531.2	555.8	563.2	568.1
75°	159.9	184.5	231.2	268.1	295.2	297.6	354.2	432.9	450.1	455.0	457.5
77.5°	127.9	172.2	169.7	216.5	241.0	236.1	277.9	334.5	349.2	349.2	349.2
80°	95.9	135.3	127.9	154.9	177.0	172.2	199.2	238.6	243.5	248.4	245.9
82.5°	71.3	86.0	86.0	98.4	118.0	113.2	132.8	154.9	154.9	154.9	159.9
85°	44.3	49.2	39.3	51.6	66.4	64.0	73.7	83.6	86.0	86.0	81.2
87.5°	27.0	22.1	12.3	19.7	29.6	29.6	34.4	36.9	34.4	34.4	34.4
90°	11.7	8.0	4.5	8.0	11.7	12.6	19.8	29.4	34.2	30.4	22.9
92.5°	79.3	48.6	18.0	48.6	79.3	86.9	122.2	169.3	192.8	169.0	121.3
95°	155.3	99.3	43.2	99.3	155.3	169.4	300.8	476.1	563.7	503.0	381.6
97.5°	173.6	124.2	74.8	124.2	173.6	186.0	405.2	697.4	843.5	805.1	728.5
100°	188.9	144.0	99.1	144.0	188.9	200.1	443.2	767.4	929.6	932.4	938.0
102.5°	203.6	161.7	119.9	161.7	203.6	214.1	460.7	789.4	953.9	1002.7	1100.5
105°	226.0	190.5	155.0	190.5	226.0	234.8	473.6	792.0	951.2	1060.7	1279.8
107.5°	257.2	224.1	191.1	224.1	257.2	265.4	476.0	756.7	897.1	1049.9	1355.5
110°	275.0	245.3	215.4	245.3	275.0	282.5	472.3	725.5	852.0	1022.9	1364.5

TEST NUMBER: P934989

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	296.1	267.6	239.2	267.6	296.1	303.2	472.5	698.2	811.1	985.9	1335.5
115°	327.7	301.6	275.3	301.6	327.7	334.3	476.8	666.9	761.9	930.3	1267.2
117.5°	358.5	334.7	310.9	334.7	358.5	364.5	485.8	647.3	728.1	880.1	1184.1
120°	376.5	354.1	331.6	354.1	376.5	382.1	492.9	640.7	714.6	853.5	1131.2
122.5°	397.2	374.5	351.9	374.5	397.2	402.8	503.3	637.3	704.3	829.3	1079.4
125°	424.2	403.6	382.9	403.6	424.2	429.4	517.3	634.4	693.0	799.2	1011.7
127.5°	449.8	429.1	408.2	429.1	449.8	455.0	531.2	632.8	683.5	774.7	957.2
130°	466.6	444.2	421.7	444.2	466.6	472.2	541.5	633.8	679.9	761.1	923.6
132.5°	480.5	458.1	435.7	458.1	480.5	486.1	549.7	634.4	676.7	749.4	894.9
135°	497.3	476.8	456.4	476.8	497.3	502.4	558.7	633.8	671.3	732.2	854.0
137.5°	518.0	497.8	477.6	497.8	518.0	523.1	572.2	637.7	670.5	721.9	824.8
140°	532.5	513.8	495.2	513.8	532.5	537.1	580.5	638.4	667.3	711.7	800.7
142.5°	543.2	526.0	508.7	526.0	543.2	547.5	587.4	640.6	667.3	706.3	784.4
145°	559.4	544.5	529.5	544.5	559.4	563.2	596.4	640.7	662.8	694.8	758.6
147.5°	579.4	564.7	550.1	564.7	579.4	583.0	609.6	645.1	662.8	687.9	738.2
150°	590.1	576.8	563.7	576.8	590.1	593.4	616.6	647.4	662.8	684.0	726.5
152.5°	597.7	587.7	577.6	587.7	597.7	600.2	621.0	648.8	662.8	680.9	717.2
155°	613.2	605.7	598.4	605.7	613.2	615.0	630.9	652.1	662.8	677.2	706.1
157.5°	628.1	620.9	613.7	620.9	628.1	629.9	640.9	655.5	662.8	674.0	696.4
160°	635.3	629.7	624.0	629.7	635.3	636.6	645.4	657.0	662.8	672.4	691.6
162.5°	642.8	638.7	634.4	638.7	642.8	643.9	650.2	658.6	662.8	670.9	687.1
165°	653.3	649.5	645.6	649.5	653.3	654.3	657.1	660.9	662.8	668.6	680.2
167.5°	659.6	657.9	656.0	657.9	659.6	660.1	662.5	665.7	667.3	671.0	678.7
170°	666.4	664.6	662.8	664.6	666.4	666.9	667.0	667.2	667.3	671.0	678.7
172.5°	667.2	666.8	666.4	666.8	667.2	667.3	667.3	667.3	667.3	670.3	676.3
175°	671.3	671.3	671.3	671.3	671.3	671.3	670.0	668.1	667.3	669.2	673.0
177.5°	671.3	671.3	671.3	671.3	671.3	671.3	670.3	668.9	668.2	669.8	672.8
180°	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3

TEST NUMBER: P934989

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6	2599.6
2.5°	2508.6	2501.3	2511.1	2484.0	2511.1	2501.3	2508.6	2525.8	2511.1	2521.0	2530.7
5°	2201.2	2188.9	2149.5	2117.6	2149.5	2188.9	2201.2	2252.8	2277.4	2321.7	2380.7
7.5°	1967.6	1957.7	1947.9	1928.2	1947.9	1957.7	1967.6	1982.3	2006.9	2046.2	2090.5
10°	1915.9	1918.3	1933.2	1930.6	1933.2	1918.3	1915.9	1911.0	1903.6	1911.0	1938.0
12.5°	2048.8	2070.8	2152.1	2147.1	2152.1	2070.8	2048.8	1950.3	1883.9	1871.6	1876.6
15°	2201.2	2208.5	2225.8	2228.2	2225.8	2208.5	2201.2	2161.8	1962.6	1876.6	1849.5
17.5°	2215.9	2218.4	2230.7	2230.7	2230.7	2218.4	2215.9	2198.8	2132.3	2016.8	1864.3
20°	2203.7	2208.5	2233.2	2238.1	2233.2	2208.5	2203.7	2181.5	2144.6	2102.8	1987.2
22.5°	2198.8	2208.5	2228.2	2225.8	2228.2	2208.5	2198.8	2164.3	2132.3	2102.8	2056.1
25°	2174.1	2174.1	2176.6	2179.1	2176.6	2174.1	2174.1	2147.1	2083.2	2075.8	2048.8
27.5°	2122.5	2127.4	2142.2	2139.7	2142.2	2127.4	2122.5	2112.6	2043.8	2036.5	2016.8
30°	2075.8	2070.8	2058.5	2048.8	2058.5	2070.8	2075.8	2061.0	1992.2	1972.5	1977.3
32.5°	1997.1	1984.8	1972.5	1965.1	1972.5	1984.8	1997.1	1992.2	1940.5	1913.5	1918.3
35°	1903.6	1906.0	1903.6	1896.2	1903.6	1906.0	1903.6	1908.5	1876.6	1852.0	1849.5
37.5°	1837.2	1842.1	1839.6	1829.9	1839.6	1842.1	1837.2	1832.3	1788.0	1780.6	1785.6
40°	1768.3	1770.8	1768.3	1761.0	1768.3	1770.8	1768.3	1758.5	1697.0	1699.4	1716.7
42.5°	1702.0	1699.4	1692.1	1687.1	1692.1	1699.4	1702.0	1687.1	1608.4	1601.1	1633.1
45°	1625.7	1628.1	1613.4	1606.0	1613.4	1628.1	1625.7	1615.8	1534.7	1515.0	1537.1
47.5°	1549.4	1549.4	1537.1	1529.8	1537.1	1549.4	1549.4	1537.1	1451.1	1431.4	1443.7
50°	1468.3	1465.8	1448.7	1446.1	1448.7	1465.8	1468.3	1460.9	1369.9	1352.7	1352.7
52.5°	1374.8	1374.8	1377.2	1382.2	1377.2	1374.8	1374.8	1377.2	1296.1	1278.9	1273.9
55°	1293.6	1296.1	1313.4	1318.2	1313.4	1296.1	1293.6	1293.6	1219.9	1202.6	1192.8
57.5°	1210.1	1210.1	1222.3	1222.3	1222.3	1210.1	1210.1	1205.1	1133.8	1119.0	1114.2
60°	1114.2	1119.0	1128.9	1126.5	1128.9	1119.0	1114.2	1109.2	1047.7	1037.9	1020.6
62.5°	1013.3	1018.2	1020.6	1015.7	1020.6	1018.2	1013.3	998.6	961.6	954.3	932.1
65°	907.6	912.4	914.9	910.0	914.9	912.4	907.6	900.2	873.1	860.8	841.1
67.5°	799.3	796.8	794.4	804.3	794.4	796.8	799.3	789.4	772.3	762.4	735.4
70°	688.7	688.7	686.1	691.1	686.1	688.7	688.7	681.3	671.4	664.1	639.4
72.5°	570.5	568.1	578.0	570.5	578.0	568.1	570.5	568.1	563.2	555.8	531.2
75°	455.0	459.9	455.0	462.4	455.0	459.9	455.0	457.5	455.0	450.1	432.9
77.5°	346.8	351.7	346.8	346.8	346.8	351.7	346.8	349.2	349.2	349.2	334.5
80°	245.9	243.5	243.5	241.0	243.5	243.5	245.9	245.9	248.4	243.5	238.6
82.5°	157.4	154.9	154.9	159.9	154.9	154.9	157.4	159.9	154.9	154.9	154.9
85°	86.0	88.6	83.6	83.6	83.6	88.6	86.0	81.2	86.0	86.0	83.6
87.5°	32.0	29.6	29.6	29.6	29.6	29.6	32.0	34.4	34.4	34.4	36.9
90°	17.2	17.2	17.2	17.2	17.2	17.2	17.2	22.9	30.4	34.2	29.4
92.5°	85.6	82.2	68.5	54.9	68.5	82.2	85.6	121.3	169.0	192.8	169.3
95°	290.6	280.3	239.1	197.8	239.1	280.3	290.6	381.6	503.0	563.7	476.1
97.5°	670.9	651.3	572.8	494.3	572.8	651.3	670.9	728.5	805.1	843.5	697.4
100°	942.2	918.8	825.2	731.7	825.2	918.8	942.2	938.0	932.4	929.6	767.4
102.5°	1173.7	1153.7	1073.7	993.5	1073.7	1153.7	1173.7	1100.5	1002.7	953.9	789.4
105°	1444.1	1433.3	1390.2	1347.2	1390.2	1433.3	1444.1	1279.8	1060.7	951.2	792.0
107.5°	1584.7	1587.3	1597.7	1608.1	1597.7	1587.3	1584.7	1355.5	1049.9	897.1	756.7
110°	1620.7	1632.0	1676.8	1721.6	1676.8	1632.0	1620.7	1364.5	1022.9	852.0	725.5

TEST NUMBER: P934989

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1597.7	1614.9	1683.8	1752.7	1683.8	1614.9	1597.7	1335.5	985.9	811.1	698.2
115°	1519.8	1543.6	1639.2	1734.7	1639.2	1543.6	1519.8	1267.2	930.3	761.9	666.9
117.5°	1412.1	1438.6	1544.5	1650.4	1544.5	1438.6	1412.1	1184.1	880.1	728.1	647.3
120°	1339.5	1365.3	1468.2	1571.1	1468.2	1365.3	1339.5	1131.2	853.5	714.6	640.7
122.5°	1267.0	1292.4	1393.9	1495.5	1393.9	1292.4	1267.0	1079.4	829.3	704.3	637.3
125°	1171.0	1194.4	1288.0	1381.5	1288.0	1194.4	1171.0	1011.7	799.2	693.0	634.4
127.5°	1094.0	1113.8	1192.6	1271.5	1192.6	1113.8	1094.0	957.2	774.7	683.5	632.8
130°	1045.4	1063.6	1136.4	1209.3	1136.4	1063.6	1045.4	923.6	761.1	679.9	633.8
132.5°	1003.9	1020.2	1085.5	1150.8	1085.5	1020.2	1003.9	894.9	749.4	676.7	634.4
135°	945.3	959.3	1015.6	1071.9	1015.6	959.3	945.3	854.0	732.2	671.3	633.8
137.5°	902.0	913.6	959.6	1005.7	959.6	913.6	902.0	824.8	721.9	670.5	637.7
140°	867.4	878.1	921.2	964.3	921.2	878.1	867.4	800.7	711.7	667.3	638.4
142.5°	843.0	852.3	889.3	926.4	889.3	852.3	843.0	784.4	706.3	667.3	640.6
145°	806.5	813.5	841.6	869.6	841.6	813.5	806.5	758.6	694.8	662.8	640.7
147.5°	775.9	781.7	804.9	828.1	804.9	781.7	775.9	738.2	687.9	662.8	645.1
150°	758.3	763.1	781.9	800.7	781.9	763.1	758.3	726.5	684.0	662.8	647.4
152.5°	744.4	748.0	762.1	776.4	762.1	748.0	744.4	717.2	680.9	662.8	648.8
155°	727.7	730.0	739.4	748.8	739.4	730.0	727.7	706.1	677.2	662.8	652.1
157.5°	713.3	714.9	721.5	728.1	721.5	714.9	713.3	696.4	674.0	662.8	655.5
160°	706.0	707.0	710.8	714.6	710.8	707.0	706.0	691.6	672.4	662.8	657.0
162.5°	699.3	700.2	703.8	707.4	703.8	700.2	699.3	687.1	670.9	662.8	658.6
165°	689.0	689.9	693.7	697.5	693.7	689.9	689.0	680.2	668.6	662.8	660.9
167.5°	684.4	684.8	686.4	688.0	686.4	684.8	684.4	678.7	671.0	667.3	665.7
170°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	678.7	671.0	667.3	667.2
172.5°	680.8	680.4	679.1	677.6	679.1	680.4	680.8	676.3	670.3	667.3	667.3
175°	675.9	675.9	675.9	675.9	675.9	675.9	675.9	673.0	669.2	667.3	668.1
177.5°	675.0	674.6	673.0	671.3	673.0	674.6	675.0	672.8	669.8	668.2	668.9
180°	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3

TEST NUMBER: P934989

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2599.6	2599.6	2599.6	2599.6	2599.6
2.5°	2567.7	2580.0	2587.3	2597.2	2621.7
5°	2469.3	2516.0	2530.7	2567.7	2611.9
7.5°	2252.8	2395.5	2434.8	2523.4	2592.3
10°	2043.8	2186.5	2255.3	2464.4	2567.7
12.5°	1938.0	2021.6	2068.4	2361.1	2533.3
15°	1871.6	1930.6	1965.1	2223.4	2493.9
17.5°	1820.0	1861.8	1886.4	2088.1	2439.7
20°	1788.0	1807.7	1829.9	1989.6	2378.3
22.5°	1765.9	1753.6	1770.8	1920.8	2294.7
25°	1751.1	1704.4	1724.0	1866.7	2196.2
27.5°	1763.4	1660.1	1667.5	1817.6	2092.9
30°	1765.9	1606.0	1608.4	1765.9	1977.3
32.5°	1748.7	1549.4	1552.0	1702.0	1847.0
35°	1706.9	1483.1	1480.5	1628.1	1670.0
37.5°	1650.3	1411.7	1411.7	1547.0	1475.7
40°	1581.4	1340.4	1347.8	1441.2	1303.5
42.5°	1497.8	1264.2	1273.9	1301.1	1175.6
45°	1406.8	1190.3	1197.8	1099.3	1077.2
47.5°	1305.9	1114.2	1116.6	912.4	1045.3
50°	1185.5	1035.4	1025.6	782.1	1042.8
52.5°	1079.7	949.3	919.9	708.3	946.9
55°	976.4	858.3	794.4	651.7	878.0
57.5°	885.4	740.3	678.8	585.4	863.3
60°	801.8	624.7	578.0	514.1	792.0
62.5°	733.0	538.6	528.8	464.8	718.1
65°	659.1	479.6	477.1	423.1	610.0
67.5°	587.8	440.2	437.8	383.6	464.8
70°	511.5	398.5	393.5	341.9	344.3
72.5°	432.9	351.7	346.8	307.5	285.3
75°	354.2	297.6	295.2	268.1	231.2
77.5°	277.9	236.1	241.0	216.5	169.7
80°	199.2	172.2	177.0	154.9	127.9
82.5°	132.8	113.2	118.0	98.4	86.0
85°	73.7	64.0	66.4	51.6	39.3
87.5°	34.4	29.6	29.6	19.7	12.3
90°	19.8	12.6	11.7	8.0	4.5
92.5°	122.2	86.9	79.3	48.6	18.0
95°	300.8	169.4	155.3	99.3	43.2
97.5°	405.2	186.0	173.6	124.2	74.8
100°	443.2	200.1	188.9	144.0	99.1
102.5°	460.7	214.1	203.6	161.7	119.9
105°	473.6	234.8	226.0	190.5	155.0
107.5°	476.0	265.4	257.2	224.1	191.1
110°	472.3	282.5	275.0	245.3	215.4



TEST NUMBER: P934989

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	472.5	303.2	296.1	267.6	239.2
115°	476.8	334.3	327.7	301.6	275.3
117.5°	485.8	364.5	358.5	334.7	310.9
120°	492.9	382.1	376.5	354.1	331.6
122.5°	503.3	402.8	397.2	374.5	351.9
125°	517.3	429.4	424.2	403.6	382.9
127.5°	531.2	455.0	449.8	429.1	408.2
130°	541.5	472.2	466.6	444.2	421.7
132.5°	549.7	486.1	480.5	458.1	435.7
135°	558.7	502.4	497.3	476.8	456.4
137.5°	572.2	523.1	518.0	497.8	477.6
140°	580.5	537.1	532.5	513.8	495.2
142.5°	587.4	547.5	543.2	526.0	508.7
145°	596.4	563.2	559.4	544.5	529.5
147.5°	609.6	583.0	579.4	564.7	550.1
150°	616.6	593.4	590.1	576.8	563.7
152.5°	621.0	600.2	597.7	587.7	577.6
155°	630.9	615.0	613.2	605.7	598.4
157.5°	640.9	629.9	628.1	620.9	613.7
160°	645.4	636.6	635.3	629.7	624.0
162.5°	650.2	643.9	642.8	638.7	634.4
165°	657.1	654.3	653.3	649.5	645.6
167.5°	662.5	660.1	659.6	657.9	656.0
170°	667.0	666.9	666.4	664.6	662.8
172.5°	667.3	667.3	667.2	666.8	666.4
175°	670.0	671.3	671.3	671.3	671.3
177.5°	670.3	671.3	671.3	671.3	671.3
180°	671.3	671.3	671.3	671.3	671.3

TEST NUMBER: P934989

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-6-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.39	16.36	16.25	17.24	18.35	18.22	19.18	19.07	20.06	21.17
	3H	15.88	16.74	16.75	17.63	18.77	19.57	20.44	20.44	21.33	22.46
	4H	16.07	16.89	16.96	17.79	18.93	20.02	20.84	20.90	21.73	22.88
	6H	16.20	16.95	17.10	17.86	19.01	20.31	21.06	21.20	21.96	23.12
	8H	16.20	16.92	17.11	17.84	19.00	20.38	21.10	21.29	22.02	23.18
	12H	16.18	16.86	17.09	17.78	18.96	20.42	21.11	21.34	22.02	23.21
4H	2H	16.44	17.26	17.33	18.15	19.30	18.64	19.46	19.53	20.35	21.50
	3H	17.47	18.16	18.38	19.08	20.24	20.15	20.84	21.06	21.76	22.92
	4H	17.75	18.38	18.67	19.30	20.49	20.68	21.31	21.60	22.23	23.42
	6H	17.88	18.42	18.81	19.37	20.56	21.05	21.59	21.98	22.54	23.73
	8H	17.89	18.39	18.82	19.34	20.54	21.16	21.66	22.09	22.61	23.81
	12H	17.87	18.32	18.82	19.28	20.48	21.22	21.68	22.17	22.63	23.84
8H	4H	18.21	18.72	19.15	19.66	20.86	20.82	21.32	21.75	22.26	23.46
	6H	18.48	18.90	19.44	19.88	21.08	21.26	21.67	22.21	22.65	23.85
	8H	18.52	18.89	19.49	19.86	21.08	21.41	21.78	22.38	22.75	23.97
	12H	18.51	18.84	19.48	19.80	21.07	21.51	21.83	22.48	22.80	24.07
12H	4H	18.23	18.68	19.18	19.64	20.84	20.79	21.24	21.74	22.20	23.40
	6H	18.54	18.91	19.51	19.88	21.10	21.25	21.62	22.22	22.60	23.81
	8H	18.61	18.94	19.58	19.90	21.17	21.42	21.74	22.39	22.71	23.98

END OF REPORT