

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P935484

Luminaire Tested: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P935484
REPORT IS A COMBINATION OF REPORTS P933754 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6630.0 lumens
Efficiency: N/A
Efficacy: 139.3 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 47.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P935484

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P935484

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	88	85	81	83	79	76	73	62	60	58	46	44	43	31	30	29
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	48	43	40	35	33	30	24	22	21
4	70	60	52	47	62	54	47	42	42	38	34	31	28	26	21	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14
7	55	43	35	30	49	38	32	27	30	26	22	23	20	17	16	14	12
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	15	12	11
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	13	11	10
10	44	32	25	20	39	29	23	19	23	19	15	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6374	6374	6374	6374
5°	6414	6434	6414	5059
10°	6365	6338	6365	4532
15°	6288	6201	6288	5178
20°	6149	6038	6149	5189
25°	5873	5801	5873	5079
30°	5519	5604	5519	4838
35°	4913	5354	4913	4572
40°	4086	5062	4086	4371
45°	3644	4718	3644	4140
50°	3863	4308	3863	3909
55°	3624	3868	3624	3777
60°	3723	3285	3723	3459
65°	3357	2715	3357	3034
70°	2310	2164	2310	2545
75°	2000	1599	2000	1916
80°	1582	1058	1582	1152
85°	861	560	861	476

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 5596 cd/sqm

TEST NUMBER: P935484

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.0	0.9
10°-20°	176.0	2.7
20°-30°	272.1	4.1
30°-40°	324.9	4.9
40°-50°	326.8	4.9
50°-60°	284.3	4.3
60°-70°	201.6	3.0
70°-80°	106.7	1.6
80°-90°	29.4	0.4
90°-100°	364.4	5.5
100°-110°	958.0	14.4
110°-120°	993.4	15.0
120°-130°	796.8	12.0
130°-140°	625.2	9.4
140°-150°	479.9	7.2
150°-160°	345.6	5.2
160°-170°	211.4	3.2
170°-180°	71.4	1.1
0°-30°	510.2	7.7
0°-40°	835.1	12.6
0°-60°	1446.2	21.8
0°-90°	1783.9	26.9
90°-120°	2315.8	34.9
90°-150°	4217.6	63.6
90°-180°	4846.0	73.1
0°-180°	6630.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	687	687	687	687	687	
5°	690	712	690	560	690	65
15°	659	705	659	589	659	185
25°	580	658	580	576	580	266
35°	441	587	441	501	441	273
45°	285	484	285	424	285	228
55°	232	357	232	348	232	213
65°	161	215	161	240	161	154
75°	61	102	61	122	61	64
85°	10	26	10	22	10	14
90°	5	19	5	19	5	5
95°	48	220	48	220	48	53
105°	173	1500	173	1500	173	183
115°	306	1932	306	1932	306	303
125°	426	1538	426	1538	426	379
135°	508	1194	508	1194	508	393
145°	590	968	590	968	590	369
155°	666	834	666	834	666	306
165°	719	777	719	777	719	203
175°	748	752	748	752	748	71
180°	748	748	748	748	748	

TEST NUMBER: P935484

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
2.5°	692.7	692.7	696.6	698.0	698.0	696.0	694.1	696.0	701.8	703.8	703.1
5°	690.1	695.4	702.5	703.8	705.1	704.5	703.1	704.5	711.0	712.2	712.9
7.5°	685.0	694.7	703.8	705.7	707.7	705.7	705.1	706.4	712.9	714.2	714.2
10°	678.5	692.1	702.5	703.8	705.7	703.8	703.8	706.4	712.9	714.2	714.8
12.5°	669.4	688.2	698.0	699.2	701.8	701.2	700.6	703.1	709.7	711.0	711.0
15°	658.9	681.0	690.1	691.5	696.0	694.7	694.7	697.3	704.5	706.4	705.7
17.5°	644.7	672.0	682.4	684.3	687.6	686.9	687.6	690.1	696.6	698.0	698.6
20°	628.4	659.6	672.0	673.9	677.1	677.1	677.1	680.4	686.9	689.5	689.5
22.5°	606.3	646.6	659.6	661.0	664.8	664.8	666.1	670.6	676.5	677.1	677.1
25°	580.3	632.3	643.3	647.3	651.2	653.1	655.0	657.7	659.6	658.9	659.6
27.5°	553.0	614.2	628.4	631.0	636.2	638.2	640.8	641.4	642.1	644.0	642.7
30°	522.5	588.8	610.2	612.8	621.2	622.6	620.0	621.2	624.5	625.8	627.1
32.5°	488.1	551.1	591.4	597.2	605.0	601.2	600.5	602.4	607.7	607.7	608.9
35°	441.3	521.8	573.8	579.1	584.9	580.3	583.0	583.5	586.8	588.8	588.1
37.5°	389.9	496.5	555.6	559.5	564.1	558.2	562.1	564.1	566.7	565.4	565.4
40°	344.4	456.9	534.2	536.8	540.7	536.1	540.0	541.4	542.6	541.4	540.7
42.5°	310.7	413.3	511.4	514.7	512.1	515.3	516.7	519.3	517.3	514.7	514.7
45°	284.6	401.7	486.7	490.6	486.7	492.0	493.9	493.9	488.1	486.7	486.1
47.5°	276.2	378.2	462.0	462.0	460.1	466.6	469.9	465.3	459.5	457.5	457.5
50°	275.6	352.2	428.3	425.7	434.8	442.5	439.3	434.8	430.2	423.1	423.1
52.5°	250.2	320.4	384.7	394.5	408.7	413.3	408.1	403.6	395.7	392.5	389.9
55°	232.0	287.2	345.1	364.5	379.6	385.4	375.6	371.0	359.4	357.5	356.1
57.5°	228.1	239.1	308.7	333.3	351.6	351.0	345.1	336.6	326.8	324.9	324.3
60°	209.3	172.9	269.7	298.9	317.7	315.8	310.7	302.8	293.7	292.4	291.2
62.5°	189.7	125.4	225.5	258.6	285.3	284.6	280.1	268.4	261.9	258.6	256.0
65°	161.1	105.2	160.6	215.1	253.5	254.8	245.0	236.5	229.4	225.5	224.8
67.5°	122.9	85.8	108.5	179.4	222.9	221.6	209.3	205.3	196.2	194.3	190.4
70°	91.0	57.2	75.4	145.5	193.0	189.7	180.0	175.5	167.1	162.5	159.9
72.5°	75.4	46.1	55.2	113.1	162.5	158.5	150.1	145.0	137.8	133.9	131.3
75°	61.0	48.7	42.2	83.8	131.9	129.4	121.5	116.3	110.5	105.2	105.9
77.5°	44.9	45.4	33.8	61.7	104.7	100.8	96.2	89.7	87.1	81.9	81.9
80°	33.8	35.8	25.4	42.2	75.4	75.4	71.5	67.0	62.4	59.8	59.8
82.5°	22.8	22.8	18.8	26.6	51.4	49.4	46.8	45.4	42.9	41.6	41.6
85°	10.4	13.0	11.7	16.3	27.9	29.3	29.3	27.9	27.3	26.0	26.6
87.5°	3.3	5.8	7.2	9.1	14.3	14.9	15.6	15.6	15.6	16.3	16.3
90°	5.0	9.0	13.1	14.1	22.1	32.8	38.1	33.8	25.4	19.1	19.1
92.5°	20.1	54.2	88.3	96.8	136.1	188.6	214.7	188.2	135.2	95.3	91.6
95°	48.2	110.6	173.1	188.7	335.0	530.0	627.6	560.1	425.0	323.6	312.1
97.5°	83.2	138.3	193.4	207.2	451.2	776.5	939.2	896.4	811.1	747.0	725.2
100°	110.4	160.4	210.3	222.8	493.5	854.5	1035.0	1038.1	1044.4	1049.0	1023.0
102.5°	133.4	180.0	226.6	238.3	512.9	879.1	1062.1	1116.6	1225.4	1307.0	1284.7
105°	172.6	212.1	251.6	261.4	527.3	881.9	1059.1	1181.1	1425.0	1608.0	1595.9
107.5°	212.7	249.5	286.3	295.5	530.0	842.6	998.9	1169.1	1509.3	1764.5	1767.4
110°	239.8	273.1	306.2	314.5	526.0	807.9	948.7	1139.0	1519.4	1804.7	1817.2

TEST NUMBER: P935484

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	266.4	298.1	329.7	337.6	526.1	777.4	903.1	1097.8	1487.1	1779.1	1798.3
115°	306.5	335.8	365.0	372.3	531.0	742.5	848.4	1035.9	1411.0	1692.3	1718.8
117.5°	346.2	372.8	399.3	405.9	540.9	720.8	810.8	979.9	1318.4	1572.3	1601.8
120°	369.3	394.3	419.3	425.5	548.9	713.5	795.7	950.4	1259.6	1491.6	1520.3
122.5°	391.9	417.1	442.3	448.6	560.5	709.6	784.2	923.5	1201.9	1410.8	1439.1
125°	426.5	449.4	472.4	478.1	576.0	706.4	771.6	889.9	1126.5	1303.9	1330.0
127.5°	454.6	477.7	500.9	506.7	591.5	704.6	761.1	862.6	1065.8	1218.1	1240.1
130°	469.6	494.6	519.6	525.8	602.9	705.7	757.1	847.5	1028.3	1164.0	1184.2
132.5°	485.2	510.2	535.2	541.4	612.1	706.4	753.6	834.5	996.4	1117.8	1136.0
135°	508.2	531.0	553.7	559.4	622.1	705.7	747.6	815.4	951.0	1052.6	1068.3
137.5°	531.8	554.3	576.8	582.5	637.1	710.1	746.5	803.8	918.4	1004.4	1017.2
140°	551.4	572.1	592.8	598.1	646.4	710.9	743.0	792.5	891.6	965.8	977.8
142.5°	566.4	585.6	604.8	609.6	654.1	713.4	743.0	786.5	873.5	938.7	948.9
145°	589.5	606.2	623.0	627.1	664.1	713.4	738.0	773.6	844.7	898.1	905.9
147.5°	612.6	628.9	645.2	649.2	678.8	718.2	738.0	766.0	822.0	864.0	870.5
150°	627.6	642.4	657.1	660.8	686.5	720.8	738.0	761.6	808.9	844.4	849.6
152.5°	643.2	654.4	665.5	668.3	691.6	722.5	738.0	758.1	798.6	828.8	832.8
155°	666.3	674.5	682.8	684.8	702.5	726.2	738.0	754.1	786.1	810.3	812.9
157.5°	683.3	691.4	699.3	701.4	713.6	729.9	738.0	750.5	775.5	794.2	796.0
160°	694.9	701.1	707.4	708.9	718.6	731.5	738.0	748.6	770.1	786.1	787.2
162.5°	706.4	711.1	715.8	717.0	723.9	733.3	738.0	747.0	765.1	778.7	779.7
165°	718.9	723.2	727.4	728.5	731.7	735.9	738.0	744.5	757.4	767.1	768.1
167.5°	730.5	732.5	734.5	735.0	737.7	741.3	743.0	747.3	755.7	762.1	762.6
170°	738.0	740.0	742.1	742.5	742.7	742.9	743.0	747.3	755.7	762.1	762.1
172.5°	742.1	742.4	742.9	743.0	743.0	743.0	743.0	746.3	753.0	758.0	757.7
175°	747.6	747.6	747.6	747.6	746.0	744.0	743.0	745.2	749.3	752.5	752.5
177.5°	747.6	747.6	747.6	747.6	746.4	744.8	744.0	745.6	749.0	751.6	751.1
180°	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6

TEST NUMBER: P935484

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
2.5°	704.5	702.5	704.5	703.1	703.8	701.8	696.0	694.1	696.0	698.0	698.0
5°	712.9	711.6	712.9	712.9	712.2	711.0	704.5	703.1	704.5	705.1	703.8
7.5°	715.5	713.6	715.5	714.2	714.2	712.9	706.4	705.1	705.7	707.7	705.7
10°	715.5	713.6	715.5	714.8	714.2	712.9	706.4	703.8	703.8	705.7	703.8
12.5°	712.2	711.0	712.2	711.0	711.0	709.7	703.1	700.6	701.2	701.8	699.2
15°	707.1	705.1	707.1	705.7	706.4	704.5	697.3	694.7	694.7	696.0	691.5
17.5°	699.2	696.6	699.2	698.6	698.0	696.6	690.1	687.6	686.9	687.6	684.3
20°	690.1	688.2	690.1	689.5	689.5	686.9	680.4	677.1	677.1	677.1	673.9
22.5°	675.9	673.9	675.9	677.1	677.1	676.5	670.6	666.1	664.8	664.8	661.0
25°	659.6	657.7	659.6	659.6	658.9	659.6	657.7	655.0	653.1	651.2	647.3
27.5°	644.0	642.7	644.0	642.7	644.0	642.1	641.4	640.8	638.2	636.2	631.0
30°	628.4	627.1	628.4	627.1	625.8	624.5	621.2	620.0	622.6	621.2	612.8
32.5°	608.9	607.7	608.9	608.9	607.7	607.7	602.4	600.5	601.2	605.0	597.2
35°	588.8	586.8	588.8	588.1	588.8	586.8	583.5	583.0	580.3	584.9	579.1
37.5°	565.4	563.5	565.4	565.4	565.4	566.7	564.1	562.1	558.2	564.1	559.5
40°	541.4	538.8	541.4	540.7	541.4	542.6	541.4	540.0	536.1	540.7	536.8
42.5°	514.1	513.4	514.1	514.7	514.7	517.3	519.3	516.7	515.3	512.1	514.7
45°	484.8	483.5	484.8	486.1	486.7	488.1	493.9	493.9	492.0	486.7	490.6
47.5°	453.6	450.4	453.6	457.5	457.5	459.5	465.3	469.9	466.6	460.1	462.0
50°	420.4	421.1	420.4	423.1	423.1	430.2	434.8	439.3	442.5	434.8	425.7
52.5°	388.0	387.3	388.0	389.9	392.5	395.7	403.6	408.1	413.3	408.7	394.5
55°	355.4	356.8	355.4	356.1	357.5	359.4	371.0	375.6	385.4	379.6	364.5
57.5°	323.0	321.0	323.0	324.3	324.9	326.8	336.6	345.1	351.0	351.6	333.3
60°	285.3	282.7	285.3	291.2	292.4	293.7	302.8	310.7	315.8	317.7	298.9
62.5°	252.1	247.6	252.1	256.0	258.6	261.9	268.4	280.1	284.6	285.3	258.6
65°	217.1	215.1	217.1	224.8	225.5	229.4	236.5	245.0	254.8	253.5	215.1
67.5°	185.2	185.2	185.2	190.4	194.3	196.2	205.3	209.3	221.6	222.9	179.4
70°	156.0	155.3	156.0	159.9	162.5	167.1	175.5	180.0	189.7	193.0	145.5
72.5°	128.0	127.3	128.0	131.3	133.9	137.8	145.0	150.1	158.5	162.5	113.1
75°	103.3	102.0	103.3	105.9	105.2	110.5	116.3	121.5	129.4	131.9	83.8
77.5°	79.3	79.3	79.3	81.9	81.9	87.1	89.7	96.2	100.8	104.7	61.7
80°	59.1	58.5	59.1	59.8	59.8	62.4	67.0	71.5	75.4	75.4	42.2
82.5°	41.6	40.3	41.6	41.6	41.6	42.9	45.4	46.8	49.4	51.4	26.6
85°	26.0	26.0	26.0	26.6	26.0	27.3	27.9	29.3	29.3	27.9	16.3
87.5°	16.9	16.3	16.9	16.3	16.3	15.6	15.6	15.6	14.9	14.3	9.1
90°	19.1	19.1	19.1	19.1	19.1	25.4	33.8	38.1	32.8	22.1	14.1
92.5°	76.4	61.2	76.4	91.6	95.3	135.2	188.2	214.7	188.6	136.1	96.8
95°	266.2	220.3	266.2	312.1	323.6	425.0	560.1	627.6	530.0	335.0	188.7
97.5°	637.8	550.4	637.8	725.2	747.0	811.1	896.4	939.2	776.5	451.2	207.2
100°	918.9	814.7	918.9	1023.0	1049.0	1044.4	1038.1	1035.0	854.5	493.5	222.8
102.5°	1195.5	1106.3	1195.5	1284.7	1307.0	1225.4	1116.6	1062.1	879.1	512.9	238.3
105°	1548.1	1500.1	1548.1	1595.9	1608.0	1425.0	1181.1	1059.1	881.9	527.3	261.4
107.5°	1779.0	1790.6	1779.0	1767.4	1764.5	1509.3	1169.1	998.9	842.6	530.0	295.5
110°	1867.1	1917.0	1867.1	1817.2	1804.7	1519.4	1139.0	948.7	807.9	526.0	314.5

TEST NUMBER: P935484

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1874.9	1951.7	1874.9	1798.3	1779.1	1487.1	1097.8	903.1	777.4	526.1	337.6
115°	1825.2	1931.6	1825.2	1718.8	1692.3	1411.0	1035.9	848.4	742.5	531.0	372.3
117.5°	1719.8	1837.7	1719.8	1601.8	1572.3	1318.4	979.9	810.8	720.8	540.9	405.9
120°	1634.8	1749.4	1634.8	1520.3	1491.6	1259.6	950.4	795.7	713.5	548.9	425.5
122.5°	1552.0	1665.1	1552.0	1439.1	1410.8	1201.9	923.5	784.2	709.6	560.5	448.6
125°	1434.0	1538.2	1434.0	1330.0	1303.9	1126.5	889.9	771.6	706.4	576.0	478.1
127.5°	1327.9	1415.8	1327.9	1240.1	1218.1	1065.8	862.6	761.1	704.6	591.5	506.7
130°	1265.4	1346.6	1265.4	1184.2	1164.0	1028.3	847.5	757.1	705.7	602.9	525.8
132.5°	1208.6	1281.3	1208.6	1136.0	1117.8	996.4	834.5	753.6	706.4	612.1	541.4
135°	1130.9	1193.5	1130.9	1068.3	1052.6	951.0	815.4	747.6	705.7	622.1	559.4
137.5°	1068.5	1119.8	1068.5	1017.2	1004.4	918.4	803.8	746.5	710.1	637.1	582.5
140°	1025.7	1073.7	1025.7	977.8	965.8	891.6	792.5	743.0	710.9	646.4	598.1
142.5°	990.2	1031.5	990.2	948.9	938.7	873.5	786.5	743.0	713.4	654.1	609.6
145°	937.1	968.3	937.1	905.9	898.1	844.7	773.6	738.0	713.4	664.1	627.1
147.5°	896.2	922.1	896.2	870.5	864.0	822.0	766.0	738.0	718.2	678.8	649.2
150°	870.6	891.6	870.6	849.6	844.4	808.9	761.6	738.0	720.8	686.5	660.8
152.5°	848.6	864.4	848.6	832.8	828.8	798.6	758.1	738.0	722.5	691.6	668.3
155°	823.4	833.8	823.4	812.9	810.3	786.1	754.1	738.0	726.2	702.5	684.8
157.5°	803.4	810.8	803.4	796.0	794.2	775.5	750.5	738.0	729.9	713.6	701.4
160°	791.5	795.7	791.5	787.2	786.1	770.1	748.6	738.0	731.5	718.6	708.9
162.5°	783.7	787.7	783.7	779.7	778.7	765.1	747.0	738.0	733.3	723.9	717.0
165°	772.4	776.7	772.4	768.1	767.1	757.4	744.5	738.0	735.9	731.7	728.5
167.5°	764.3	766.1	764.3	762.6	762.1	755.7	747.3	743.0	741.3	737.7	735.0
170°	762.1	762.1	762.1	762.1	762.1	755.7	747.3	743.0	742.9	742.7	742.5
172.5°	756.1	754.6	756.1	757.7	758.0	753.0	746.3	743.0	743.0	743.0	743.0
175°	752.5	752.5	752.5	752.5	752.5	749.3	745.2	743.0	744.0	746.0	747.6
177.5°	749.3	747.6	749.3	751.1	751.6	749.0	745.6	744.0	744.8	746.4	747.6
180°	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6

TEST NUMBER: P935484

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
2.5°	696.6	692.7	692.7	686.2	683.6	681.7	678.5	668.7	666.1	663.5	667.4
5°	702.5	695.4	690.1	678.5	668.7	664.8	652.4	629.1	613.5	601.7	595.3
7.5°	703.8	694.7	685.0	666.8	643.3	633.0	595.3	552.4	540.7	530.3	523.7
10°	702.5	692.1	678.5	651.2	595.9	577.7	540.0	512.1	504.9	503.0	504.9
12.5°	698.0	688.2	669.4	623.8	546.5	534.2	512.1	495.8	494.6	497.8	515.3
15°	690.1	681.0	658.9	587.5	519.3	510.2	494.6	488.7	495.8	518.6	571.2
17.5°	682.4	672.0	644.7	551.7	498.5	492.0	480.9	492.6	532.9	563.5	581.0
20°	672.0	659.6	628.4	525.8	483.5	477.6	472.5	525.1	555.6	566.7	576.5
22.5°	659.6	646.6	606.3	507.6	467.9	463.4	466.6	543.3	555.6	563.5	571.9
25°	643.3	632.3	580.3	493.2	455.5	450.4	462.7	541.4	548.5	550.4	567.3
27.5°	628.4	614.2	553.0	480.2	440.6	438.7	466.0	532.9	538.1	540.0	558.2
30°	610.2	588.8	522.5	466.6	425.0	424.3	466.6	522.5	521.2	526.4	544.6
32.5°	591.4	551.1	488.1	449.7	410.1	409.4	462.0	506.9	505.6	512.7	526.4
35°	573.8	521.8	441.3	430.2	391.2	391.9	451.0	488.7	489.3	495.8	504.3
37.5°	555.6	496.5	389.9	408.7	373.1	373.1	436.0	471.8	470.5	472.5	484.1
40°	534.2	456.9	344.4	380.8	356.1	354.2	417.8	453.6	449.0	448.5	464.6
42.5°	511.4	413.3	310.7	343.8	336.6	334.0	395.7	431.5	423.1	425.0	445.8
45°	486.7	401.7	284.6	290.5	316.5	314.5	371.7	406.2	400.3	405.5	426.9
47.5°	462.0	378.2	276.2	241.1	295.1	294.4	345.1	381.5	378.2	383.4	406.2
50°	428.3	352.2	275.6	206.7	271.0	273.5	313.3	357.5	357.5	362.0	386.0
52.5°	384.7	320.4	250.2	187.1	243.0	250.9	285.3	336.6	337.9	342.4	364.0
55°	345.1	287.2	232.0	172.2	209.9	226.8	257.9	315.2	317.7	322.3	341.9
57.5°	308.7	239.1	228.1	154.7	179.4	195.6	233.9	294.4	295.6	299.6	318.4
60°	269.7	172.9	209.3	135.9	152.7	165.0	211.8	269.7	274.2	276.8	293.1
62.5°	225.5	125.4	189.7	122.9	139.7	142.3	193.7	246.3	252.1	254.1	263.9
65°	160.6	105.2	161.1	111.8	126.1	126.7	174.1	222.3	227.4	230.7	237.9
67.5°	108.5	85.8	122.9	101.4	115.7	116.3	155.3	194.3	201.5	204.1	208.6
70°	75.4	57.2	91.0	90.3	104.0	105.2	135.2	169.0	175.5	177.4	180.0
72.5°	55.2	46.1	75.4	81.2	91.7	92.9	114.3	140.4	146.9	148.8	150.1
75°	42.2	48.7	61.0	70.8	78.0	78.6	93.6	114.3	118.9	120.3	120.8
77.5°	33.8	45.4	44.9	57.2	63.7	62.4	73.5	88.4	92.2	92.2	92.2
80°	25.4	35.8	33.8	41.0	46.8	45.4	52.6	63.1	64.3	65.6	65.0
82.5°	18.8	22.8	22.8	26.0	31.2	29.9	35.1	41.0	41.0	41.0	42.2
85°	11.7	13.0	10.4	13.7	17.5	16.9	19.5	22.1	22.8	22.8	21.4
87.5°	7.2	5.8	3.3	5.2	7.8	7.8	9.1	9.8	9.1	9.1	9.1
90°	13.1	9.0	5.0	9.0	13.1	14.1	22.1	32.8	38.1	33.8	25.4
92.5°	88.3	54.2	20.1	54.2	88.3	96.8	136.1	188.6	214.7	188.2	135.2
95°	173.1	110.6	48.2	110.6	173.1	188.7	335.0	530.0	627.6	560.1	425.0
97.5°	193.4	138.3	83.2	138.3	193.4	207.2	451.2	776.5	939.2	896.4	811.1
100°	210.3	160.4	110.4	160.4	210.3	222.8	493.5	854.5	1035.0	1038.1	1044.4
102.5°	226.6	180.0	133.4	180.0	226.6	238.3	512.9	879.1	1062.1	1116.6	1225.4
105°	251.6	212.1	172.6	212.1	251.6	261.4	527.3	881.9	1059.1	1181.1	1425.0
107.5°	286.3	249.5	212.7	249.5	286.3	295.5	530.0	842.6	998.9	1169.1	1509.3
110°	306.2	273.1	239.8	273.1	306.2	314.5	526.0	807.9	948.7	1139.0	1519.4

TEST NUMBER: P935484

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	329.7	298.1	266.4	298.1	329.7	337.6	526.1	777.4	903.1	1097.8	1487.1
115°	365.0	335.8	306.5	335.8	365.0	372.3	531.0	742.5	848.4	1035.9	1411.0
117.5°	399.3	372.8	346.2	372.8	399.3	405.9	540.9	720.8	810.8	979.9	1318.4
120°	419.3	394.3	369.3	394.3	419.3	425.5	548.9	713.5	795.7	950.4	1259.6
122.5°	442.3	417.1	391.9	417.1	442.3	448.6	560.5	709.6	784.2	923.5	1201.9
125°	472.4	449.4	426.5	449.4	472.4	478.1	576.0	706.4	771.6	889.9	1126.5
127.5°	500.9	477.7	454.6	477.7	500.9	506.7	591.5	704.6	761.1	862.6	1065.8
130°	519.6	494.6	469.6	494.6	519.6	525.8	602.9	705.7	757.1	847.5	1028.3
132.5°	535.2	510.2	485.2	510.2	535.2	541.4	612.1	706.4	753.6	834.5	996.4
135°	553.7	531.0	508.2	531.0	553.7	559.4	622.1	705.7	747.6	815.4	951.0
137.5°	576.8	554.3	531.8	554.3	576.8	582.5	637.1	710.1	746.5	803.8	918.4
140°	592.8	572.1	551.4	572.1	592.8	598.1	646.4	710.9	743.0	792.5	891.6
142.5°	604.8	585.6	566.4	585.6	604.8	609.6	654.1	713.4	743.0	786.5	873.5
145°	623.0	606.2	589.5	606.2	623.0	627.1	664.1	713.4	738.0	773.6	844.7
147.5°	645.2	628.9	612.6	628.9	645.2	649.2	678.8	718.2	738.0	766.0	822.0
150°	657.1	642.4	627.6	642.4	657.1	660.8	686.5	720.8	738.0	761.6	808.9
152.5°	665.5	654.4	643.2	654.4	665.5	668.3	691.6	722.5	738.0	758.1	798.6
155°	682.8	674.5	666.3	674.5	682.8	684.8	702.5	726.2	738.0	754.1	786.1
157.5°	699.3	691.4	683.3	691.4	699.3	701.4	713.6	729.9	738.0	750.5	775.5
160°	707.4	701.1	694.9	701.1	707.4	708.9	718.6	731.5	738.0	748.6	770.1
162.5°	715.8	711.1	706.4	711.1	715.8	717.0	723.9	733.3	738.0	747.0	765.1
165°	727.4	723.2	718.9	723.2	727.4	728.5	731.7	735.9	738.0	744.5	757.4
167.5°	734.5	732.5	730.5	732.5	734.5	735.0	737.7	741.3	743.0	747.3	755.7
170°	742.1	740.0	738.0	740.0	742.1	742.5	742.7	742.9	743.0	747.3	755.7
172.5°	742.9	742.4	742.1	742.4	742.9	743.0	743.0	743.0	743.0	746.3	753.0
175°	747.6	747.6	747.6	747.6	747.6	747.6	746.0	744.0	743.0	745.2	749.3
177.5°	747.6	747.6	747.6	747.6	747.6	747.6	746.4	744.8	744.0	745.6	749.0
180°	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6

TEST NUMBER: P935484

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
2.5°	662.9	661.0	663.5	656.4	663.5	661.0	662.9	667.4	663.5	666.1	668.7
5°	581.6	578.4	568.0	559.5	568.0	578.4	581.6	595.3	601.7	613.5	629.1
7.5°	519.9	517.3	514.7	509.5	514.7	517.3	519.9	523.7	530.3	540.7	552.4
10°	506.2	506.9	510.8	510.2	510.8	506.9	506.2	504.9	503.0	504.9	512.1
12.5°	541.4	547.2	568.6	567.3	568.6	547.2	541.4	515.3	497.8	494.6	495.8
15°	581.6	583.5	588.1	588.8	588.1	583.5	581.6	571.2	518.6	495.8	488.7
17.5°	585.6	586.1	589.4	589.4	589.4	586.1	585.6	581.0	563.5	532.9	492.6
20°	582.3	583.5	590.1	591.4	590.1	583.5	582.3	576.5	566.7	555.6	525.1
22.5°	581.0	583.5	588.8	588.1	588.8	583.5	581.0	571.9	563.5	555.6	543.3
25°	574.5	574.5	575.1	575.8	575.1	574.5	574.5	567.3	550.4	548.5	541.4
27.5°	560.9	562.1	566.0	565.4	566.0	562.1	560.9	558.2	540.0	538.1	532.9
30°	548.5	547.2	543.9	541.4	543.9	547.2	548.5	544.6	526.4	521.2	522.5
32.5°	527.7	524.4	521.2	519.3	521.2	524.4	527.7	526.4	512.7	505.6	506.9
35°	503.0	503.7	503.0	501.1	503.0	503.7	503.0	504.3	495.8	489.3	488.7
37.5°	485.5	486.7	486.1	483.5	486.1	486.7	485.5	484.1	472.5	470.5	471.8
40°	467.3	467.9	467.3	465.3	467.3	467.9	467.3	464.6	448.5	449.0	453.6
42.5°	449.7	449.0	447.1	445.8	447.1	449.0	449.7	445.8	425.0	423.1	431.5
45°	429.6	430.2	426.3	424.3	426.3	430.2	429.6	426.9	405.5	400.3	406.2
47.5°	409.4	409.4	406.2	404.2	406.2	409.4	409.4	406.2	383.4	378.2	381.5
50°	388.0	387.3	382.8	382.1	382.8	387.3	388.0	386.0	362.0	357.5	357.5
52.5°	363.3	363.3	364.0	365.2	364.0	363.3	363.3	364.0	342.4	337.9	336.6
55°	341.9	342.4	347.0	348.4	347.0	342.4	341.9	341.9	322.3	317.7	315.2
57.5°	319.8	319.8	323.0	323.0	323.0	319.8	319.8	318.4	299.6	295.6	294.4
60°	294.4	295.6	298.3	297.7	298.3	295.6	294.4	293.1	276.8	274.2	269.7
62.5°	267.7	269.1	269.7	268.4	269.7	269.1	267.7	263.9	254.1	252.1	246.3
65°	239.8	241.1	241.8	240.4	241.8	241.1	239.8	237.9	230.7	227.4	222.3
67.5°	211.2	210.6	209.9	212.5	209.9	210.6	211.2	208.6	204.1	201.5	194.3
70°	182.0	182.0	181.3	182.7	181.3	182.0	182.0	180.0	177.4	175.5	169.0
72.5°	150.8	150.1	152.7	150.8	152.7	150.1	150.8	150.1	148.8	146.9	140.4
75°	120.3	121.5	120.3	122.2	120.3	121.5	120.3	120.8	120.3	118.9	114.3
77.5°	91.7	92.9	91.7	91.7	91.7	92.9	91.7	92.2	92.2	92.2	88.4
80°	65.0	64.3	64.3	63.7	64.3	64.3	65.0	65.0	65.6	64.3	63.1
82.5°	41.6	41.0	41.0	42.2	41.0	41.0	41.6	42.2	41.0	41.0	41.0
85°	22.8	23.4	22.1	22.1	22.1	23.4	22.8	21.4	22.8	22.8	22.1
87.5°	8.4	7.8	7.8	7.8	7.8	7.8	8.4	9.1	9.1	9.1	9.8
90°	19.1	19.1	19.1	19.1	19.1	19.1	19.1	25.4	33.8	38.1	32.8
92.5°	95.3	91.6	76.4	61.2	76.4	91.6	95.3	135.2	188.2	214.7	188.6
95°	323.6	312.1	266.2	220.3	266.2	312.1	323.6	425.0	560.1	627.6	530.0
97.5°	747.0	725.2	637.8	550.4	637.8	725.2	747.0	811.1	896.4	939.2	776.5
100°	1049.0	1023.0	918.9	814.7	918.9	1023.0	1049.0	1044.4	1038.1	1035.0	854.5
102.5°	1307.0	1284.7	1195.5	1106.3	1195.5	1284.7	1307.0	1225.4	1116.6	1062.1	879.1
105°	1608.0	1595.9	1548.1	1500.1	1548.1	1595.9	1608.0	1425.0	1181.1	1059.1	881.9
107.5°	1764.5	1767.4	1779.0	1790.6	1779.0	1767.4	1764.5	1509.3	1169.1	998.9	842.6
110°	1804.7	1817.2	1867.1	1917.0	1867.1	1817.2	1804.7	1519.4	1139.0	948.7	807.9

TEST NUMBER: P935484

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1779.1	1798.3	1874.9	1951.7	1874.9	1798.3	1779.1	1487.1	1097.8	903.1	777.4
115°	1692.3	1718.8	1825.2	1931.6	1825.2	1718.8	1692.3	1411.0	1035.9	848.4	742.5
117.5°	1572.3	1601.8	1719.8	1837.7	1719.8	1601.8	1572.3	1318.4	979.9	810.8	720.8
120°	1491.6	1520.3	1634.8	1749.4	1634.8	1520.3	1491.6	1259.6	950.4	795.7	713.5
122.5°	1410.8	1439.1	1552.0	1665.1	1552.0	1439.1	1410.8	1201.9	923.5	784.2	709.6
125°	1303.9	1330.0	1434.0	1538.2	1434.0	1330.0	1303.9	1126.5	889.9	771.6	706.4
127.5°	1218.1	1240.1	1327.9	1415.8	1327.9	1240.1	1218.1	1065.8	862.6	761.1	704.6
130°	1164.0	1184.2	1265.4	1346.6	1265.4	1184.2	1164.0	1028.3	847.5	757.1	705.7
132.5°	1117.8	1136.0	1208.6	1281.3	1208.6	1136.0	1117.8	996.4	834.5	753.6	706.4
135°	1052.6	1068.3	1130.9	1193.5	1130.9	1068.3	1052.6	951.0	815.4	747.6	705.7
137.5°	1004.4	1017.2	1068.5	1119.8	1068.5	1017.2	1004.4	918.4	803.8	746.5	710.1
140°	965.8	977.8	1025.7	1073.7	1025.7	977.8	965.8	891.6	792.5	743.0	710.9
142.5°	938.7	948.9	990.2	1031.5	990.2	948.9	938.7	873.5	786.5	743.0	713.4
145°	898.1	905.9	937.1	968.3	937.1	905.9	898.1	844.7	773.6	738.0	713.4
147.5°	864.0	870.5	896.2	922.1	896.2	870.5	864.0	822.0	766.0	738.0	718.2
150°	844.4	849.6	870.6	891.6	870.6	849.6	844.4	808.9	761.6	738.0	720.8
152.5°	828.8	832.8	848.6	864.4	848.6	832.8	828.8	798.6	758.1	738.0	722.5
155°	810.3	812.9	823.4	833.8	823.4	812.9	810.3	786.1	754.1	738.0	726.2
157.5°	794.2	796.0	803.4	810.8	803.4	796.0	794.2	775.5	750.5	738.0	729.9
160°	786.1	787.2	791.5	795.7	791.5	787.2	786.1	770.1	748.6	738.0	731.5
162.5°	778.7	779.7	783.7	787.7	783.7	779.7	778.7	765.1	747.0	738.0	733.3
165°	767.1	768.1	772.4	776.7	772.4	768.1	767.1	757.4	744.5	738.0	735.9
167.5°	762.1	762.6	764.3	766.1	764.3	762.6	762.1	755.7	747.3	743.0	741.3
170°	762.1	762.1	762.1	762.1	762.1	762.1	762.1	755.7	747.3	743.0	742.9
172.5°	758.0	757.7	756.1	754.6	756.1	757.7	758.0	753.0	746.3	743.0	743.0
175°	752.5	752.5	752.5	752.5	752.5	752.5	752.5	749.3	745.2	743.0	744.0
177.5°	751.6	751.1	749.3	747.6	749.3	751.1	751.6	749.0	745.6	744.0	744.8
180°	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6

TEST NUMBER: P935484

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	686.9	686.9	686.9	686.9	686.9
2.5°	678.5	681.7	683.6	686.2	692.7
5°	652.4	664.8	668.7	678.5	690.1
7.5°	595.3	633.0	643.3	666.8	685.0
10°	540.0	577.7	595.9	651.2	678.5
12.5°	512.1	534.2	546.5	623.8	669.4
15°	494.6	510.2	519.3	587.5	658.9
17.5°	480.9	492.0	498.5	551.7	644.7
20°	472.5	477.6	483.5	525.8	628.4
22.5°	466.6	463.4	467.9	507.6	606.3
25°	462.7	450.4	455.5	493.2	580.3
27.5°	466.0	438.7	440.6	480.2	553.0
30°	466.6	424.3	425.0	466.6	522.5
32.5°	462.0	409.4	410.1	449.7	488.1
35°	451.0	391.9	391.2	430.2	441.3
37.5°	436.0	373.1	373.1	408.7	389.9
40°	417.8	354.2	356.1	380.8	344.4
42.5°	395.7	334.0	336.6	343.8	310.7
45°	371.7	314.5	316.5	290.5	284.6
47.5°	345.1	294.4	295.1	241.1	276.2
50°	313.3	273.5	271.0	206.7	275.6
52.5°	285.3	250.9	243.0	187.1	250.2
55°	257.9	226.8	209.9	172.2	232.0
57.5°	233.9	195.6	179.4	154.7	228.1
60°	211.8	165.0	152.7	135.9	209.3
62.5°	193.7	142.3	139.7	122.9	189.7
65°	174.1	126.7	126.1	111.8	161.1
67.5°	155.3	116.3	115.7	101.4	122.9
70°	135.2	105.2	104.0	90.3	91.0
72.5°	114.3	92.9	91.7	81.2	75.4
75°	93.6	78.6	78.0	70.8	61.0
77.5°	73.5	62.4	63.7	57.2	44.9
80°	52.6	45.4	46.8	41.0	33.8
82.5°	35.1	29.9	31.2	26.0	22.8
85°	19.5	16.9	17.5	13.7	10.4
87.5°	9.1	7.8	7.8	5.2	3.3
90°	22.1	14.1	13.1	9.0	5.0
92.5°	136.1	96.8	88.3	54.2	20.1
95°	335.0	188.7	173.1	110.6	48.2
97.5°	451.2	207.2	193.4	138.3	83.2
100°	493.5	222.8	210.3	160.4	110.4
102.5°	512.9	238.3	226.6	180.0	133.4
105°	527.3	261.4	251.6	212.1	172.6
107.5°	530.0	295.5	286.3	249.5	212.7
110°	526.0	314.5	306.2	273.1	239.8

TEST NUMBER: P935484

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	526.1	337.6	329.7	298.1	266.4
115°	531.0	372.3	365.0	335.8	306.5
117.5°	540.9	405.9	399.3	372.8	346.2
120°	548.9	425.5	419.3	394.3	369.3
122.5°	560.5	448.6	442.3	417.1	391.9
125°	576.0	478.1	472.4	449.4	426.5
127.5°	591.5	506.7	500.9	477.7	454.6
130°	602.9	525.8	519.6	494.6	469.6
132.5°	612.1	541.4	535.2	510.2	485.2
135°	622.1	559.4	553.7	531.0	508.2
137.5°	637.1	582.5	576.8	554.3	531.8
140°	646.4	598.1	592.8	572.1	551.4
142.5°	654.1	609.6	604.8	585.6	566.4
145°	664.1	627.1	623.0	606.2	589.5
147.5°	678.8	649.2	645.2	628.9	612.6
150°	686.5	660.8	657.1	642.4	627.6
152.5°	691.6	668.3	665.5	654.4	643.2
155°	702.5	684.8	682.8	674.5	666.3
157.5°	713.6	701.4	699.3	691.4	683.3
160°	718.6	708.9	707.4	701.1	694.9
162.5°	723.9	717.0	715.8	711.1	706.4
165°	731.7	728.5	727.4	723.2	718.9
167.5°	737.7	735.0	734.5	732.5	730.5
170°	742.7	742.5	742.1	740.0	738.0
172.5°	743.0	743.0	742.9	742.4	742.1
175°	746.0	747.6	747.6	747.6	747.6
177.5°	746.4	747.6	747.6	747.6	747.6
180°	747.6	747.6	747.6	747.6	747.6

TEST NUMBER: P935484

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.57	9.26	9.71	10.38	11.95	11.37	12.06	12.50	13.18	14.75
	3H	9.04	9.65	10.18	10.78	12.37	12.69	13.31	13.83	14.44	16.02
	4H	9.22	9.80	10.37	10.94	12.52	13.12	13.71	14.27	14.84	16.43
	6H	9.33	9.87	10.49	11.00	12.60	13.39	13.93	14.55	15.06	16.66
	8H	9.33	9.84	10.49	10.99	12.58	13.45	13.97	14.62	15.12	16.71
	12H	9.29	9.78	10.46	10.92	12.53	13.48	13.97	14.65	15.11	16.73
4H	2H	9.58	10.16	10.73	11.29	12.88	11.76	12.34	12.92	13.48	15.06
	3H	10.59	11.07	11.75	12.23	13.83	13.24	13.73	14.40	14.88	16.48
	4H	10.85	11.30	12.02	12.45	14.07	13.75	14.20	14.92	15.35	16.97
	6H	10.97	11.35	12.14	12.52	14.13	14.10	14.48	15.27	15.65	17.26
	8H	10.97	11.33	12.14	12.49	14.12	14.20	14.56	15.37	15.72	17.34
	12H	10.93	11.26	12.12	12.43	14.06	14.24	14.57	15.43	15.74	17.37
8H	4H	11.29	11.65	12.46	12.81	14.43	13.86	14.22	15.03	15.38	17.01
	6H	11.54	11.84	12.73	13.04	14.66	14.29	14.58	15.47	15.78	17.41
	8H	11.58	11.84	12.78	13.02	14.67	14.43	14.69	15.63	15.87	17.51
	12H	11.56	11.79	12.76	12.97	14.64	14.52	14.74	15.71	15.92	17.59
12H	4H	11.29	11.61	12.47	12.78	14.41	13.82	14.14	15.01	15.32	16.95
	6H	11.60	11.86	12.80	13.04	14.68	14.28	14.54	15.48	15.72	17.36
	8H	11.66	11.89	12.86	13.06	14.74	14.43	14.65	15.63	15.83	17.51