

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P933885

Luminaire Tested: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P933885
REPORT IS A COMBINATION OF REPORTS P933674 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2679.7 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P933885

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K

Luminous Intensity Polar Plot



TEST NUMBER: P933885

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66		
1	101	97	93	89	95	91	88	85	81	78	76	71	69	68	62	61	60	55		
2	92	85	78	73	87	80	74	70	71	67	63	63	59	56	55	52	50	46		
3	84	75	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39		
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	43	40	37	34		
5	71	59	50	44	66	56	48	43	50	44	39	44	39	35	39	35	32	29		
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28	26		
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25	23		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18		
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6282	6282	6282	6282
5°	6322	6342	6322	4986
10°	6273	6247	6273	4466
15°	6197	6112	6197	5103
20°	6060	5950	6060	5113
25°	5788	5717	5788	5005
30°	5439	5523	5439	4768
35°	4842	5277	4842	4506
40°	4027	4989	4027	4308
45°	3591	4650	3591	4081
50°	3807	4246	3807	3853
55°	3571	3811	3571	3721
60°	3670	3237	3670	3409
65°	3309	2676	3309	2990
70°	2277	2133	2277	2508
75°	1974	1577	1974	1888
80°	1558	1043	1558	1134
85°	845	552	845	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 5515 cd/sqm

TEST NUMBER: P933885

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.1	2.3
10°-20°	173.5	6.5
20°-30°	268.2	10.0
30°-40°	320.2	11.9
40°-50°	322.1	12.0
50°-60°	280.2	10.5
60°-70°	198.7	7.4
70°-80°	105.1	3.9
80°-90°	26.7	1.0
90°-100°	69.5	2.6
100°-110°	182.7	6.8
110°-120°	189.4	7.1
120°-130°	151.9	5.7
130°-140°	119.2	4.4
140°-150°	91.5	3.4
150°-160°	65.9	2.5
160°-170°	40.3	1.5
170°-180°	13.6	0.5
0°-30°	502.8	18.8
0°-40°	823.0	30.7
0°-60°	1425.3	53.2
0°-90°	1755.8	65.5
90°-120°	441.5	16.5
90°-150°	804.1	30.0
90°-180°	924.0	34.5
0°-180°	2679.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	677	677	677	677	677	
5°	680	701	680	551	680	65
15°	649	695	649	580	649	183
25°	572	648	572	568	572	263
35°	435	578	435	494	435	269
45°	280	476	280	418	280	225
55°	229	352	229	343	229	210
65°	159	212	159	237	159	152
75°	60	101	60	120	60	63
85°	10	26	10	22	10	14
90°	1	4	1	4	1	1
95°	9	42	9	42	9	10
105°	33	286	33	286	33	35
115°	58	368	58	368	58	58
125°	81	293	81	293	81	72
135°	97	228	97	228	97	75
145°	112	185	112	185	112	70
155°	127	159	127	159	127	58
165°	137	148	137	148	137	39
175°	142	143	142	143	142	14
180°	142	142	142	142	142	

TEST NUMBER: P933885

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0
2.5°	682.7	682.7	686.5	687.9	687.9	686.0	684.1	686.0	691.7	693.6	692.9
5°	680.2	685.3	692.4	693.6	695.0	694.3	692.9	694.3	700.7	701.9	702.6
7.5°	675.1	684.6	693.6	695.5	697.4	695.5	695.0	696.2	702.6	703.8	703.8
10°	668.7	682.1	692.4	693.6	695.5	693.6	693.6	696.2	702.6	703.8	704.5
12.5°	659.7	678.2	687.9	689.1	691.7	691.0	690.5	692.9	699.4	700.7	700.7
15°	649.4	671.2	680.2	681.5	686.0	684.6	684.6	687.2	694.3	696.2	695.5
17.5°	635.4	662.3	672.5	674.4	677.7	677.0	677.7	680.2	686.5	687.9	688.6
20°	619.3	650.1	662.3	664.2	667.4	667.4	667.4	670.6	677.0	679.6	679.6
22.5°	597.5	637.3	650.1	651.4	655.2	655.2	656.5	661.0	666.7	667.4	667.4
25°	571.9	623.1	634.0	637.9	641.8	643.7	645.6	648.2	650.1	649.4	650.1
27.5°	545.0	605.3	619.3	621.9	627.1	629.0	631.5	632.1	632.8	634.7	633.5
30°	514.9	580.3	601.4	603.9	612.3	613.6	611.0	612.3	615.5	616.7	618.1
32.5°	481.0	543.1	582.8	588.6	596.3	592.5	591.8	593.7	598.9	598.9	600.1
35°	434.9	514.3	565.6	570.7	576.4	571.9	574.5	575.1	578.3	580.3	579.6
37.5°	384.3	489.3	547.6	551.4	555.9	550.2	554.0	555.9	558.5	557.2	557.2
40°	339.4	450.3	526.5	529.1	532.9	528.4	532.2	533.6	534.8	533.6	532.9
42.5°	306.2	407.3	504.0	507.3	504.7	507.9	509.2	511.8	509.8	507.3	507.3
45°	280.5	395.8	479.7	483.5	479.7	484.9	486.8	486.8	481.0	479.7	479.0
47.5°	272.2	372.7	455.3	455.3	453.4	459.8	463.1	458.6	452.9	450.9	450.9
50°	271.6	347.1	422.1	419.5	428.5	436.1	433.0	428.5	424.0	417.0	417.0
52.5°	246.6	315.7	379.1	388.8	402.8	407.3	402.2	397.8	390.0	386.9	384.3
55°	228.6	283.1	340.1	359.3	374.1	379.8	370.2	365.7	354.2	352.3	351.0
57.5°	224.8	235.7	304.3	328.5	346.5	345.9	340.1	331.8	322.1	320.2	319.6
60°	206.3	170.4	265.8	294.6	313.1	311.2	306.2	298.4	289.5	288.2	287.0
62.5°	187.0	123.6	222.2	254.9	281.2	280.5	276.1	264.5	258.1	254.9	252.3
65°	158.8	103.7	158.2	212.0	249.8	251.1	241.4	233.1	226.0	222.2	221.6
67.5°	121.1	84.5	107.0	176.8	219.6	218.4	206.3	202.4	193.4	191.5	187.7
70°	89.7	56.3	74.3	143.4	190.2	187.0	177.4	173.0	164.6	160.2	157.6
72.5°	74.3	45.5	54.4	111.4	160.2	156.2	147.9	142.9	135.8	132.0	129.4
75°	60.2	48.0	41.6	82.6	130.0	127.5	119.8	114.6	108.9	103.7	104.4
77.5°	44.2	44.8	33.3	60.8	103.1	99.3	94.8	88.4	85.9	80.7	80.7
80°	33.3	35.2	25.0	41.6	74.3	74.3	70.5	66.0	61.5	58.9	58.9
82.5°	22.4	22.4	18.5	26.3	50.6	48.7	46.1	44.8	42.3	41.0	41.0
85°	10.2	12.8	11.6	16.0	27.5	28.8	28.8	27.5	26.9	25.6	26.3
87.5°	3.2	5.7	7.1	9.0	14.1	14.7	15.4	15.4	15.4	16.0	16.0
90°	1.0	1.7	2.5	2.7	4.2	6.2	7.3	6.5	4.9	3.6	3.6
92.5°	3.8	10.3	16.8	18.4	26.0	36.0	41.0	35.9	25.8	18.1	17.4
95°	9.2	21.1	33.0	36.0	63.9	101.0	119.7	106.8	81.0	61.7	59.5
97.5°	15.9	26.4	36.9	39.5	86.0	148.0	179.1	170.9	154.6	142.4	138.2
100°	21.0	30.6	40.1	42.5	94.1	162.9	197.3	197.9	199.1	200.0	195.0
102.5°	25.4	34.3	43.3	45.5	97.8	167.6	202.5	212.9	233.6	249.2	244.9
105°	32.9	40.5	47.9	49.9	100.6	168.1	201.9	225.2	271.7	306.6	304.3
107.5°	40.6	47.6	54.6	56.3	101.0	160.6	190.4	222.9	287.7	336.4	337.0
110°	45.7	52.0	58.4	60.0	100.3	154.0	180.9	217.2	289.7	344.1	346.5

TEST NUMBER: P933885

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	50.8	56.8	62.8	64.4	100.3	148.2	172.2	209.3	283.5	339.2	342.8
115°	58.4	64.0	69.5	71.0	101.2	141.6	161.8	197.5	269.0	322.6	327.7
117.5°	66.0	71.1	76.1	77.4	103.1	137.4	154.6	186.9	251.4	299.8	305.4
120°	70.4	75.2	79.9	81.1	104.6	136.0	151.7	181.2	240.2	284.4	289.8
122.5°	74.7	79.5	84.2	85.5	106.8	135.2	149.5	176.0	229.1	268.9	274.3
125°	81.3	85.7	90.1	91.2	109.8	134.7	147.1	169.6	214.8	248.6	253.6
127.5°	86.6	91.1	95.5	96.6	112.8	134.3	145.1	164.5	203.2	232.3	236.5
130°	89.5	94.3	99.0	100.3	115.0	134.6	144.3	161.6	196.1	221.9	225.8
132.5°	92.5	97.3	102.1	103.2	116.7	134.7	143.6	159.1	189.9	213.2	216.6
135°	96.9	101.2	105.6	106.7	118.6	134.6	142.5	155.4	181.3	200.6	203.6
137.5°	101.4	105.7	110.0	111.1	121.5	135.3	142.3	153.2	175.1	191.5	194.0
140°	105.1	109.1	113.1	114.0	123.2	135.5	141.6	151.1	170.0	184.1	186.4
142.5°	108.0	111.6	115.3	116.2	124.7	136.0	141.6	149.9	166.6	179.0	181.0
145°	112.4	115.6	118.8	119.6	126.6	136.0	140.7	147.5	161.0	171.2	172.8
147.5°	116.8	119.9	123.0	123.8	129.4	136.9	140.7	146.0	156.7	164.7	166.0
150°	119.7	122.4	125.3	126.0	130.8	137.4	140.7	145.2	154.2	161.0	162.0
152.5°	122.6	124.7	126.8	127.4	131.8	137.7	140.7	144.5	152.2	158.1	158.8
155°	127.0	128.5	130.2	130.5	133.9	138.4	140.7	143.7	149.9	154.5	155.0
157.5°	130.3	131.8	133.3	133.7	136.0	139.1	140.7	143.1	147.8	151.4	151.7
160°	132.5	133.6	134.8	135.1	136.9	139.4	140.7	142.7	146.8	149.8	150.0
162.5°	134.7	135.5	136.5	136.7	138.0	139.8	140.7	142.4	145.8	148.4	148.6
165°	137.0	137.8	138.7	138.9	139.4	140.3	140.7	141.9	144.4	146.2	146.4
167.5°	139.2	139.6	140.0	140.1	140.6	141.2	141.6	142.4	144.0	145.3	145.4
170°	140.7	141.1	141.4	141.5	141.5	141.6	141.6	142.4	144.0	145.3	145.3
172.5°	141.4	141.5	141.6	141.6	141.6	141.6	141.6	142.3	143.5	144.5	144.4
175°	142.5	142.5	142.5	142.5	142.2	141.8	141.6	142.0	142.9	143.4	143.4
177.5°	142.5	142.5	142.5	142.5	142.3	142.0	141.8	142.1	142.8	143.2	143.2
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5

TEST NUMBER: P933885

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0
2.5°	694.3	692.4	694.3	692.9	693.6	691.7	686.0	684.1	686.0	687.9	687.9
5°	702.6	701.4	702.6	702.6	701.9	700.7	694.3	692.9	694.3	695.0	693.6
7.5°	705.2	703.3	705.2	703.8	703.8	702.6	696.2	695.0	695.5	697.4	695.5
10°	705.2	703.3	705.2	704.5	703.8	702.6	696.2	693.6	693.6	695.5	693.6
12.5°	701.9	700.7	701.9	700.7	700.7	699.4	692.9	690.5	691.0	691.7	689.1
15°	696.9	695.0	696.9	695.5	696.2	694.3	687.2	684.6	684.6	686.0	681.5
17.5°	689.1	686.5	689.1	688.6	687.9	686.5	680.2	677.7	677.0	677.7	674.4
20°	680.2	678.2	680.2	679.6	679.6	677.0	670.6	667.4	667.4	667.4	664.2
22.5°	666.1	664.2	666.1	667.4	667.4	666.7	661.0	656.5	655.2	655.2	651.4
25°	650.1	648.2	650.1	650.1	649.4	650.1	648.2	645.6	643.7	641.8	637.9
27.5°	634.7	633.5	634.7	633.5	634.7	632.8	632.1	631.5	629.0	627.1	621.9
30°	619.3	618.1	619.3	618.1	616.7	615.5	612.3	611.0	613.6	612.3	603.9
32.5°	600.1	598.9	600.1	600.1	598.9	598.9	593.7	591.8	592.5	596.3	588.6
35°	580.3	578.3	580.3	579.6	580.3	578.3	575.1	574.5	571.9	576.4	570.7
37.5°	557.2	555.3	557.2	557.2	557.2	558.5	555.9	554.0	550.2	555.9	551.4
40°	533.6	531.0	533.6	532.9	533.6	534.8	533.6	532.2	528.4	532.9	529.1
42.5°	506.6	506.0	506.6	507.3	507.3	509.8	511.8	509.2	507.9	504.7	507.3
45°	477.8	476.5	477.8	479.0	479.7	481.0	486.8	486.8	484.9	479.7	483.5
47.5°	447.0	443.9	447.0	450.9	450.9	452.9	458.6	463.1	459.8	453.4	455.3
50°	414.4	415.0	414.4	417.0	417.0	424.0	428.5	433.0	436.1	428.5	419.5
52.5°	382.4	381.7	382.4	384.3	386.9	390.0	397.8	402.2	407.3	402.8	388.8
55°	350.3	351.6	350.3	351.0	352.3	354.2	365.7	370.2	379.8	374.1	359.3
57.5°	318.3	316.4	318.3	319.6	320.2	322.1	331.8	340.1	345.9	346.5	328.5
60°	281.2	278.6	281.2	287.0	288.2	289.5	298.4	306.2	311.2	313.1	294.6
62.5°	248.5	244.0	248.5	252.3	254.9	258.1	264.5	276.1	280.5	281.2	254.9
65°	213.9	212.0	213.9	221.6	222.2	226.0	233.1	241.4	251.1	249.8	212.0
67.5°	182.5	182.5	182.5	187.7	191.5	193.4	202.4	206.3	218.4	219.6	176.8
70°	153.8	153.1	153.8	157.6	160.2	164.6	173.0	177.4	187.0	190.2	143.4
72.5°	126.2	125.5	126.2	129.4	132.0	135.8	142.9	147.9	156.2	160.2	111.4
75°	101.8	100.6	101.8	104.4	103.7	108.9	114.6	119.8	127.5	130.0	82.6
77.5°	78.1	78.1	78.1	80.7	80.7	85.9	88.4	94.8	99.3	103.1	60.8
80°	58.3	57.7	58.3	58.9	58.9	61.5	66.0	70.5	74.3	74.3	41.6
82.5°	41.0	39.7	41.0	41.0	41.0	42.3	44.8	46.1	48.7	50.6	26.3
85°	25.6	25.6	25.6	26.3	25.6	26.9	27.5	28.8	28.8	27.5	16.0
87.5°	16.6	16.0	16.6	16.0	16.0	15.4	15.4	15.4	14.7	14.1	9.0
90°	3.6	3.6	3.6	3.6	3.6	4.9	6.5	7.3	6.2	4.2	2.7
92.5°	14.5	11.7	14.5	17.4	18.1	25.8	35.9	41.0	36.0	26.0	18.4
95°	50.8	42.0	50.8	59.5	61.7	81.0	106.8	119.7	101.0	63.9	36.0
97.5°	121.6	105.0	121.6	138.2	142.4	154.6	170.9	179.1	148.0	86.0	39.5
100°	175.2	155.4	175.2	195.0	200.0	199.1	197.9	197.3	162.9	94.1	42.5
102.5°	227.9	210.9	227.9	244.9	249.2	233.6	212.9	202.5	167.6	97.8	45.5
105°	295.2	286.0	295.2	304.3	306.6	271.7	225.2	201.9	168.1	100.6	49.9
107.5°	339.2	341.4	339.2	337.0	336.4	287.7	222.9	190.4	160.6	101.0	56.3
110°	355.9	365.5	355.9	346.5	344.1	289.7	217.2	180.9	154.0	100.3	60.0

TEST NUMBER: P933885

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	357.5	372.1	357.5	342.8	339.2	283.5	209.3	172.2	148.2	100.3	64.4
115°	348.0	368.2	348.0	327.7	322.6	269.0	197.5	161.8	141.6	101.2	71.0
117.5°	327.9	350.4	327.9	305.4	299.8	251.4	186.9	154.6	137.4	103.1	77.4
120°	311.7	333.5	311.7	289.8	284.4	240.2	181.2	151.7	136.0	104.6	81.1
122.5°	295.9	317.4	295.9	274.3	268.9	229.1	176.0	149.5	135.2	106.8	85.5
125°	273.4	293.3	273.4	253.6	248.6	214.8	169.6	147.1	134.7	109.8	91.2
127.5°	253.2	269.9	253.2	236.5	232.3	203.2	164.5	145.1	134.3	112.8	96.6
130°	241.2	256.7	241.2	225.8	221.9	196.1	161.6	144.3	134.6	115.0	100.3
132.5°	230.4	244.3	230.4	216.6	213.2	189.9	159.1	143.6	134.7	116.7	103.2
135°	215.6	227.6	215.6	203.6	200.6	181.3	155.4	142.5	134.6	118.6	106.7
137.5°	203.7	213.5	203.7	194.0	191.5	175.1	153.2	142.3	135.3	121.5	111.1
140°	195.5	204.7	195.5	186.4	184.1	170.0	151.1	141.6	135.5	123.2	114.0
142.5°	188.8	196.6	188.8	181.0	179.0	166.6	149.9	141.6	136.0	124.7	116.2
145°	178.7	184.6	178.7	172.8	171.2	161.0	147.5	140.7	136.0	126.6	119.6
147.5°	170.8	175.8	170.8	166.0	164.7	156.7	146.0	140.7	136.9	129.4	123.8
150°	166.0	170.0	166.0	162.0	161.0	154.2	145.2	140.7	137.4	130.8	126.0
152.5°	161.8	164.8	161.8	158.8	158.1	152.2	144.5	140.7	137.7	131.8	127.4
155°	157.0	159.0	157.0	155.0	154.5	149.9	143.7	140.7	138.4	133.9	130.5
157.5°	153.2	154.6	153.2	151.7	151.4	147.8	143.1	140.7	139.1	136.0	133.7
160°	150.9	151.7	150.9	150.0	149.8	146.8	142.7	140.7	139.4	136.9	135.1
162.5°	149.4	150.1	149.4	148.6	148.4	145.8	142.4	140.7	139.8	138.0	136.7
165°	147.3	148.0	147.3	146.4	146.2	144.4	141.9	140.7	140.3	139.4	138.9
167.5°	145.6	146.0	145.6	145.4	145.3	144.0	142.4	141.6	141.2	140.6	140.1
170°	145.3	145.3	145.3	145.3	145.3	144.0	142.4	141.6	141.6	141.5	141.5
172.5°	144.1	143.8	144.1	144.4	144.5	143.5	142.3	141.6	141.6	141.6	141.6
175°	143.4	143.4	143.4	143.4	143.4	142.9	142.0	141.6	141.8	142.2	142.5
177.5°	142.9	142.5	142.9	143.2	143.2	142.8	142.1	141.8	142.0	142.3	142.5
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5

TEST NUMBER: P933885

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0
2.5°	686.5	682.7	682.7	676.3	673.8	671.8	668.7	659.0	656.5	653.9	657.8
5°	692.4	685.3	680.2	668.7	659.0	655.2	643.0	620.0	604.6	593.1	586.7
7.5°	693.6	684.6	675.1	657.1	634.0	623.8	586.7	544.4	532.9	522.7	516.2
10°	692.4	682.1	668.7	641.8	587.3	569.4	532.2	504.7	497.7	495.7	497.7
12.5°	687.9	678.2	659.7	614.8	538.6	526.5	504.7	488.7	487.4	490.6	507.9
15°	680.2	671.2	649.4	579.0	511.8	502.8	487.4	481.6	488.7	511.1	563.0
17.5°	672.5	662.3	635.4	543.8	491.3	484.9	474.0	485.5	525.2	555.3	572.6
20°	662.3	650.1	619.3	518.2	476.5	470.7	465.7	517.5	547.6	558.5	568.1
22.5°	650.1	637.3	597.5	500.2	461.2	456.7	459.8	535.5	547.6	555.3	563.6
25°	634.0	623.1	571.9	486.1	448.9	443.9	456.0	533.6	540.5	542.4	559.2
27.5°	619.3	605.3	545.0	473.3	434.2	432.3	459.3	525.2	530.3	532.2	550.2
30°	601.4	580.3	514.9	459.8	418.9	418.2	459.8	514.9	513.7	518.8	536.7
32.5°	582.8	543.1	481.0	443.2	404.2	403.5	455.3	499.6	498.3	505.3	518.8
35°	565.6	514.3	434.9	424.0	385.5	386.2	444.5	481.6	482.3	488.7	497.0
37.5°	547.6	489.3	384.3	402.8	367.7	367.7	429.8	465.0	463.7	465.7	477.1
40°	526.5	450.3	339.4	375.3	351.0	349.1	411.8	447.0	442.5	442.0	457.9
42.5°	504.0	407.3	306.2	338.8	331.8	329.2	390.0	425.3	417.0	418.9	439.4
45°	479.7	395.8	280.5	286.3	311.9	310.0	366.3	400.3	394.5	399.7	420.8
47.5°	455.3	372.7	272.2	237.6	290.8	290.1	340.1	376.0	372.7	377.9	400.3
50°	422.1	347.1	271.6	203.7	267.1	269.6	308.8	352.3	352.3	356.8	380.5
52.5°	379.1	315.7	246.6	184.4	239.5	247.2	281.2	331.8	333.0	337.5	358.7
55°	340.1	283.1	228.6	169.7	206.9	223.6	254.2	310.7	313.1	317.6	336.9
57.5°	304.3	235.7	224.8	152.4	176.8	192.8	230.5	290.1	291.4	295.3	313.8
60°	265.8	170.4	206.3	133.9	150.5	162.6	208.8	265.8	270.3	272.8	288.9
62.5°	222.2	123.6	187.0	121.1	137.7	140.3	190.9	242.8	248.5	250.4	260.0
65°	158.2	103.7	158.8	110.2	124.2	124.9	171.6	219.1	224.1	227.4	234.5
67.5°	107.0	84.5	121.1	99.9	114.0	114.6	153.1	191.5	198.5	201.1	205.6
70°	74.3	56.3	89.7	89.0	102.5	103.7	133.2	166.6	173.0	174.9	177.4
72.5°	54.4	45.5	74.3	80.0	90.3	91.6	112.7	138.4	144.8	146.7	147.9
75°	41.6	48.0	60.2	69.8	76.9	77.5	92.3	112.7	117.2	118.5	119.1
77.5°	33.3	44.8	44.2	56.3	62.7	61.5	72.4	87.1	90.9	90.9	90.9
80°	25.0	35.2	33.3	40.4	46.1	44.8	51.9	62.2	63.4	64.7	64.1
82.5°	18.5	22.4	22.4	25.6	30.8	29.5	34.6	40.4	40.4	40.4	41.6
85°	11.6	12.8	10.2	13.5	17.3	16.6	19.2	21.8	22.4	22.4	21.1
87.5°	7.1	5.7	3.2	5.2	7.6	7.6	9.0	9.6	9.0	9.0	9.0
90°	2.5	1.7	1.0	1.7	2.5	2.7	4.2	6.2	7.3	6.5	4.9
92.5°	16.8	10.3	3.8	10.3	16.8	18.4	26.0	36.0	41.0	35.9	25.8
95°	33.0	21.1	9.2	21.1	33.0	36.0	63.9	101.0	119.7	106.8	81.0
97.5°	36.9	26.4	15.9	26.4	36.9	39.5	86.0	148.0	179.1	170.9	154.6
100°	40.1	30.6	21.0	30.6	40.1	42.5	94.1	162.9	197.3	197.9	199.1
102.5°	43.3	34.3	25.4	34.3	43.3	45.5	97.8	167.6	202.5	212.9	233.6
105°	47.9	40.5	32.9	40.5	47.9	49.9	100.6	168.1	201.9	225.2	271.7
107.5°	54.6	47.6	40.6	47.6	54.6	56.3	101.0	160.6	190.4	222.9	287.7
110°	58.4	52.0	45.7	52.0	58.4	60.0	100.3	154.0	180.9	217.2	289.7

TEST NUMBER: P933885

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	62.8	56.8	50.8	56.8	62.8	64.4	100.3	148.2	172.2	209.3	283.5
115°	69.5	64.0	58.4	64.0	69.5	71.0	101.2	141.6	161.8	197.5	269.0
117.5°	76.1	71.1	66.0	71.1	76.1	77.4	103.1	137.4	154.6	186.9	251.4
120°	79.9	75.2	70.4	75.2	79.9	81.1	104.6	136.0	151.7	181.2	240.2
122.5°	84.2	79.5	74.7	79.5	84.2	85.5	106.8	135.2	149.5	176.0	229.1
125°	90.1	85.7	81.3	85.7	90.1	91.2	109.8	134.7	147.1	169.6	214.8
127.5°	95.5	91.1	86.6	91.1	95.5	96.6	112.8	134.3	145.1	164.5	203.2
130°	99.0	94.3	89.5	94.3	99.0	100.3	115.0	134.6	144.3	161.6	196.1
132.5°	102.1	97.3	92.5	97.3	102.1	103.2	116.7	134.7	143.6	159.1	189.9
135°	105.6	101.2	96.9	101.2	105.6	106.7	118.6	134.6	142.5	155.4	181.3
137.5°	110.0	105.7	101.4	105.7	110.0	111.1	121.5	135.3	142.3	153.2	175.1
140°	113.1	109.1	105.1	109.1	113.1	114.0	123.2	135.5	141.6	151.1	170.0
142.5°	115.3	111.6	108.0	111.6	115.3	116.2	124.7	136.0	141.6	149.9	166.6
145°	118.8	115.6	112.4	115.6	118.8	119.6	126.6	136.0	140.7	147.5	161.0
147.5°	123.0	119.9	116.8	119.9	123.0	123.8	129.4	136.9	140.7	146.0	156.7
150°	125.3	122.4	119.7	122.4	125.3	126.0	130.8	137.4	140.7	145.2	154.2
152.5°	126.8	124.7	122.6	124.7	126.8	127.4	131.8	137.7	140.7	144.5	152.2
155°	130.2	128.5	127.0	128.5	130.2	130.5	133.9	138.4	140.7	143.7	149.9
157.5°	133.3	131.8	130.3	131.8	133.3	133.7	136.0	139.1	140.7	143.1	147.8
160°	134.8	133.6	132.5	133.6	134.8	135.1	136.9	139.4	140.7	142.7	146.8
162.5°	136.5	135.5	134.7	135.5	136.5	136.7	138.0	139.8	140.7	142.4	145.8
165°	138.7	137.8	137.0	137.8	138.7	138.9	139.4	140.3	140.7	141.9	144.4
167.5°	140.0	139.6	139.2	139.6	140.0	140.1	140.6	141.2	141.6	142.4	144.0
170°	141.4	141.1	140.7	141.1	141.4	141.5	141.5	141.6	141.6	142.4	144.0
172.5°	141.6	141.5	141.4	141.5	141.6	141.6	141.6	141.6	141.6	142.3	143.5
175°	142.5	142.5	142.5	142.5	142.5	142.5	142.2	141.8	141.6	142.0	142.9
177.5°	142.5	142.5	142.5	142.5	142.5	142.5	142.3	142.0	141.8	142.1	142.8
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5

TEST NUMBER: P933885

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0
2.5°	653.3	651.4	653.9	646.9	653.9	651.4	653.3	657.8	653.9	656.5	659.0
5°	573.2	570.0	559.8	551.4	559.8	570.0	573.2	586.7	593.1	604.6	620.0
7.5°	512.4	509.8	507.3	502.1	507.3	509.8	512.4	516.2	522.7	532.9	544.4
10°	498.9	499.6	503.4	502.8	503.4	499.6	498.9	497.7	495.7	497.7	504.7
12.5°	533.6	539.3	560.4	559.2	560.4	539.3	533.6	507.9	490.6	487.4	488.7
15°	573.2	575.1	579.6	580.3	579.6	575.1	573.2	563.0	511.1	488.7	481.6
17.5°	577.1	577.7	580.9	580.9	580.9	577.7	577.1	572.6	555.3	525.2	485.5
20°	573.9	575.1	581.6	582.8	581.6	575.1	573.9	568.1	558.5	547.6	517.5
22.5°	572.6	575.1	580.3	579.6	580.3	575.1	572.6	563.6	555.3	547.6	535.5
25°	566.2	566.2	566.8	567.5	566.8	566.2	566.2	559.2	542.4	540.5	533.6
27.5°	552.8	554.0	557.8	557.2	557.8	554.0	552.8	550.2	532.2	530.3	525.2
30°	540.5	539.3	536.0	533.6	536.0	539.3	540.5	536.7	518.8	513.7	514.9
32.5°	520.1	516.8	513.7	511.8	513.7	516.8	520.1	518.8	505.3	498.3	499.6
35°	495.7	496.4	495.7	493.8	495.7	496.4	495.7	497.0	488.7	482.3	481.6
37.5°	478.5	479.7	479.0	476.5	479.0	479.7	478.5	477.1	465.7	463.7	465.0
40°	460.5	461.2	460.5	458.6	460.5	461.2	460.5	457.9	442.0	442.5	447.0
42.5°	443.2	442.5	440.6	439.4	440.6	442.5	443.2	439.4	418.9	417.0	425.3
45°	423.4	424.0	420.1	418.2	420.1	424.0	423.4	420.8	399.7	394.5	400.3
47.5°	403.5	403.5	400.3	398.3	400.3	403.5	403.5	400.3	377.9	372.7	376.0
50°	382.4	381.7	377.2	376.6	377.2	381.7	382.4	380.5	356.8	352.3	352.3
52.5°	358.0	358.0	358.7	359.9	358.7	358.0	358.0	358.7	337.5	333.0	331.8
55°	336.9	337.5	342.0	343.3	342.0	337.5	336.9	336.9	317.6	313.1	310.7
57.5°	315.2	315.2	318.3	318.3	318.3	315.2	315.2	313.8	295.3	291.4	290.1
60°	290.1	291.4	293.9	293.4	293.9	291.4	290.1	288.9	272.8	270.3	265.8
62.5°	263.9	265.2	265.8	264.5	265.8	265.2	263.9	260.0	250.4	248.5	242.8
65°	236.4	237.6	238.3	236.9	238.3	237.6	236.4	234.5	227.4	224.1	219.1
67.5°	208.2	207.5	206.9	209.4	206.9	207.5	208.2	205.6	201.1	198.5	191.5
70°	179.3	179.3	178.7	180.0	178.7	179.3	179.3	177.4	174.9	173.0	166.6
72.5°	148.6	147.9	150.5	148.6	150.5	147.9	148.6	147.9	146.7	144.8	138.4
75°	118.5	119.8	118.5	120.4	118.5	119.8	118.5	119.1	118.5	117.2	112.7
77.5°	90.3	91.6	90.3	90.3	90.3	91.6	90.3	90.9	90.9	90.9	87.1
80°	64.1	63.4	63.4	62.7	63.4	63.4	64.1	64.1	64.7	63.4	62.2
82.5°	41.0	40.4	40.4	41.6	40.4	40.4	41.0	41.6	40.4	40.4	40.4
85°	22.4	23.0	21.8	21.8	21.8	23.0	22.4	21.1	22.4	22.4	21.8
87.5°	8.3	7.6	7.6	7.6	7.6	7.6	8.3	9.0	9.0	9.0	9.6
90°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.9	6.5	7.3	6.2
92.5°	18.1	17.4	14.5	11.7	14.5	17.4	18.1	25.8	35.9	41.0	36.0
95°	61.7	59.5	50.8	42.0	50.8	59.5	61.7	81.0	106.8	119.7	101.0
97.5°	142.4	138.2	121.6	105.0	121.6	138.2	142.4	154.6	170.9	179.1	148.0
100°	200.0	195.0	175.2	155.4	175.2	195.0	200.0	199.1	197.9	197.3	162.9
102.5°	249.2	244.9	227.9	210.9	227.9	244.9	249.2	233.6	212.9	202.5	167.6
105°	306.6	304.3	295.2	286.0	295.2	304.3	306.6	271.7	225.2	201.9	168.1
107.5°	336.4	337.0	339.2	341.4	339.2	337.0	336.4	287.7	222.9	190.4	160.6
110°	344.1	346.5	355.9	365.5	355.9	346.5	344.1	289.7	217.2	180.9	154.0

TEST NUMBER: P933885

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	339.2	342.8	357.5	372.1	357.5	342.8	339.2	283.5	209.3	172.2	148.2
115°	322.6	327.7	348.0	368.2	348.0	327.7	322.6	269.0	197.5	161.8	141.6
117.5°	299.8	305.4	327.9	350.4	327.9	305.4	299.8	251.4	186.9	154.6	137.4
120°	284.4	289.8	311.7	333.5	311.7	289.8	284.4	240.2	181.2	151.7	136.0
122.5°	268.9	274.3	295.9	317.4	295.9	274.3	268.9	229.1	176.0	149.5	135.2
125°	248.6	253.6	273.4	293.3	273.4	253.6	248.6	214.8	169.6	147.1	134.7
127.5°	232.3	236.5	253.2	269.9	253.2	236.5	232.3	203.2	164.5	145.1	134.3
130°	221.9	225.8	241.2	256.7	241.2	225.8	221.9	196.1	161.6	144.3	134.6
132.5°	213.2	216.6	230.4	244.3	230.4	216.6	213.2	189.9	159.1	143.6	134.7
135°	200.6	203.6	215.6	227.6	215.6	203.6	200.6	181.3	155.4	142.5	134.6
137.5°	191.5	194.0	203.7	213.5	203.7	194.0	191.5	175.1	153.2	142.3	135.3
140°	184.1	186.4	195.5	204.7	195.5	186.4	184.1	170.0	151.1	141.6	135.5
142.5°	179.0	181.0	188.8	196.6	188.8	181.0	179.0	166.6	149.9	141.6	136.0
145°	171.2	172.8	178.7	184.6	178.7	172.8	171.2	161.0	147.5	140.7	136.0
147.5°	164.7	166.0	170.8	175.8	170.8	166.0	164.7	156.7	146.0	140.7	136.9
150°	161.0	162.0	166.0	170.0	166.0	162.0	161.0	154.2	145.2	140.7	137.4
152.5°	158.1	158.8	161.8	164.8	161.8	158.8	158.1	152.2	144.5	140.7	137.7
155°	154.5	155.0	157.0	159.0	157.0	155.0	154.5	149.9	143.7	140.7	138.4
157.5°	151.4	151.7	153.2	154.6	153.2	151.7	151.4	147.8	143.1	140.7	139.1
160°	149.8	150.0	150.9	151.7	150.9	150.0	149.8	146.8	142.7	140.7	139.4
162.5°	148.4	148.6	149.4	150.1	149.4	148.6	148.4	145.8	142.4	140.7	139.8
165°	146.2	146.4	147.3	148.0	147.3	146.4	146.2	144.4	141.9	140.7	140.3
167.5°	145.3	145.4	145.6	146.0	145.6	145.4	145.3	144.0	142.4	141.6	141.2
170°	145.3	145.3	145.3	145.3	145.3	145.3	145.3	144.0	142.4	141.6	141.6
172.5°	144.5	144.4	144.1	143.8	144.1	144.4	144.5	143.5	142.3	141.6	141.6
175°	143.4	143.4	143.4	143.4	143.4	143.4	143.4	142.9	142.0	141.6	141.8
177.5°	143.2	143.2	142.9	142.5	142.9	143.2	143.2	142.8	142.1	141.8	142.0
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5

TEST NUMBER: P933885

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	677.0	677.0	677.0	677.0	677.0
2.5°	668.7	671.8	673.8	676.3	682.7
5°	643.0	655.2	659.0	668.7	680.2
7.5°	586.7	623.8	634.0	657.1	675.1
10°	532.2	569.4	587.3	641.8	668.7
12.5°	504.7	526.5	538.6	614.8	659.7
15°	487.4	502.8	511.8	579.0	649.4
17.5°	474.0	484.9	491.3	543.8	635.4
20°	465.7	470.7	476.5	518.2	619.3
22.5°	459.8	456.7	461.2	500.2	597.5
25°	456.0	443.9	448.9	486.1	571.9
27.5°	459.3	432.3	434.2	473.3	545.0
30°	459.8	418.2	418.9	459.8	514.9
32.5°	455.3	403.5	404.2	443.2	481.0
35°	444.5	386.2	385.5	424.0	434.9
37.5°	429.8	367.7	367.7	402.8	384.3
40°	411.8	349.1	351.0	375.3	339.4
42.5°	390.0	329.2	331.8	338.8	306.2
45°	366.3	310.0	311.9	286.3	280.5
47.5°	340.1	290.1	290.8	237.6	272.2
50°	308.8	269.6	267.1	203.7	271.6
52.5°	281.2	247.2	239.5	184.4	246.6
55°	254.2	223.6	206.9	169.7	228.6
57.5°	230.5	192.8	176.8	152.4	224.8
60°	208.8	162.6	150.5	133.9	206.3
62.5°	190.9	140.3	137.7	121.1	187.0
65°	171.6	124.9	124.2	110.2	158.8
67.5°	153.1	114.6	114.0	99.9	121.1
70°	133.2	103.7	102.5	89.0	89.7
72.5°	112.7	91.6	90.3	80.0	74.3
75°	92.3	77.5	76.9	69.8	60.2
77.5°	72.4	61.5	62.7	56.3	44.2
80°	51.9	44.8	46.1	40.4	33.3
82.5°	34.6	29.5	30.8	25.6	22.4
85°	19.2	16.6	17.3	13.5	10.2
87.5°	9.0	7.6	7.6	5.2	3.2
90°	4.2	2.7	2.5	1.7	1.0
92.5°	26.0	18.4	16.8	10.3	3.8
95°	63.9	36.0	33.0	21.1	9.2
97.5°	86.0	39.5	36.9	26.4	15.9
100°	94.1	42.5	40.1	30.6	21.0
102.5°	97.8	45.5	43.3	34.3	25.4
105°	100.6	49.9	47.9	40.5	32.9
107.5°	101.0	56.3	54.6	47.6	40.6
110°	100.3	60.0	58.4	52.0	45.7



TEST NUMBER: P933885

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	100.3	64.4	62.8	56.8	50.8
115°	101.2	71.0	69.5	64.0	58.4
117.5°	103.1	77.4	76.1	71.1	66.0
120°	104.6	81.1	79.9	75.2	70.4
122.5°	106.8	85.5	84.2	79.5	74.7
125°	109.8	91.2	90.1	85.7	81.3
127.5°	112.8	96.6	95.5	91.1	86.6
130°	115.0	100.3	99.0	94.3	89.5
132.5°	116.7	103.2	102.1	97.3	92.5
135°	118.6	106.7	105.6	101.2	96.9
137.5°	121.5	111.1	110.0	105.7	101.4
140°	123.2	114.0	113.1	109.1	105.1
142.5°	124.7	116.2	115.3	111.6	108.0
145°	126.6	119.6	118.8	115.6	112.4
147.5°	129.4	123.8	123.0	119.9	116.8
150°	130.8	126.0	125.3	122.4	119.7
152.5°	131.8	127.4	126.8	124.7	122.6
155°	133.9	130.5	130.2	128.5	127.0
157.5°	136.0	133.7	133.3	131.8	130.3
160°	136.9	135.1	134.8	133.6	132.5
162.5°	138.0	136.7	136.5	135.5	134.7
165°	139.4	138.9	138.7	137.8	137.0
167.5°	140.6	140.1	140.0	139.6	139.2
170°	141.5	141.5	141.4	141.1	140.7
172.5°	141.6	141.6	141.6	141.5	141.4
175°	142.2	142.5	142.5	142.5	142.5
177.5°	142.3	142.5	142.5	142.5	142.5
180°	142.5	142.5	142.5	142.5	142.5

TEST NUMBER: P933885

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-4-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.50	13.52	13.31	14.36	15.39	15.30	16.32	16.11	17.15	18.18
	3H	12.99	13.91	13.81	14.75	15.81	16.64	17.56	17.47	18.40	19.46
	4H	13.19	14.05	14.03	14.90	15.97	17.09	17.95	17.93	18.81	19.88
	6H	13.32	14.11	14.17	14.97	16.05	17.38	18.17	18.23	19.03	20.11
	8H	13.32	14.08	14.18	14.96	16.04	17.45	18.21	18.31	19.09	20.17
	12H	13.30	14.02	14.17	14.89	16.00	17.49	18.21	18.36	19.08	20.19
4H	2H	13.54	14.41	14.39	15.26	16.33	15.73	16.59	16.57	17.44	18.51
	3H	14.59	15.31	15.44	16.19	17.28	17.24	17.96	18.10	18.84	19.93
	4H	14.87	15.52	15.74	16.41	17.52	17.77	18.42	18.64	19.30	20.42
	6H	15.00	15.57	15.89	16.47	17.59	18.13	18.70	19.02	19.60	20.72
	8H	15.01	15.54	15.90	16.44	17.57	18.24	18.77	19.13	19.67	20.80
	12H	14.99	15.46	15.90	16.38	17.52	18.30	18.77	19.21	19.69	20.83
8H	4H	15.33	15.86	16.22	16.76	17.89	17.90	18.43	18.79	19.33	20.46
	6H	15.60	16.04	16.51	16.98	18.11	18.34	18.78	19.26	19.72	20.85
	8H	15.64	16.03	16.57	16.96	18.11	18.49	18.88	19.41	19.81	20.96
	12H	15.63	15.98	16.56	16.90	18.10	18.59	18.93	19.52	19.86	21.05
12H	4H	15.34	15.82	16.25	16.74	17.87	17.88	18.35	18.79	19.27	20.41
	6H	15.66	16.05	16.58	16.98	18.13	18.34	18.73	19.26	19.66	20.81
	8H	15.73	16.07	16.66	17.00	18.20	18.50	18.84	19.43	19.77	20.97

END OF REPORT