

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934395

Luminaire Tested: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934395
REPORT IS A COMBINATION OF REPORTS P933696 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9039.1 lumens
Efficiency: N/A
Efficacy: 124.2 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934395

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K

Luminous Intensity Polar Plot



TEST NUMBER: P934395

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	95	91	88	93	89	86	83	77	75	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	57	60	55	50	51	48	44	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9366	9366	9366	9366
5°	9436	9455	9436	7434
10°	9373	9314	9373	6659
15°	9271	9112	9271	7609
20°	9078	8873	9078	7624
25°	8680	8524	8680	7463
30°	8167	8235	8167	7108
35°	7281	7868	7281	6718
40°	6067	7437	6067	6424
45°	5422	6933	5422	6085
50°	5759	6331	5759	5745
55°	5419	5683	5419	5549
60°	5586	4827	5586	5082
65°	5065	3990	5065	4460
70°	3507	3180	3507	3739
75°	3074	2351	3074	2815
80°	2478	1554	2478	1692
85°	1425	823	1425	699

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 8309 cd/sqm

TEST NUMBER: P934395

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.2	2.0
10°-20°	517.4	5.7
20°-30°	799.8	8.8
30°-40°	954.8	10.6
40°-50°	960.4	10.6
50°-60°	835.7	9.2
60°-70°	592.5	6.6
70°-80°	313.5	3.5
80°-90°	80.3	0.9
90°-100°	285.9	3.2
100°-110°	751.7	8.3
110°-120°	779.4	8.6
120°-130°	625.2	6.9
130°-140°	490.6	5.4
140°-150°	376.5	4.2
150°-160°	271.2	3.0
160°-170°	165.9	1.8
170°-180°	56.1	0.6
0°-30°	1499.4	16.6
0°-40°	2454.2	27.2
0°-60°	4250.3	47.0
0°-90°	5236.6	57.9
90°-120°	1817.1	20.1
90°-150°	3309.4	36.6
90°-180°	3802.0	42.1
0°-180°	9039.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2019	2019	2019	2019	2019	
5°	2028	2091	2028	1644	2028	192
15°	1937	2072	1937	1730	1937	545
25°	1706	1933	1706	1692	1706	783
35°	1297	1725	1297	1472	1297	802
45°	837	1421	837	1247	837	670
55°	682	1049	682	1024	682	627
65°	474	632	474	707	474	453
75°	180	300	180	359	180	189
85°	31	76	31	65	31	41
90°	4	15	4	15	4	5
95°	38	173	38	173	38	42
105°	135	1177	135	1177	135	144
115°	241	1516	241	1516	241	238
125°	335	1207	335	1207	335	297
135°	399	937	399	937	399	309
145°	463	760	463	760	463	290
155°	523	654	523	654	523	240
165°	564	609	564	609	564	159
175°	587	590	587	590	587	56
180°	587	587	587	587	587	

TEST NUMBER: P934395

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8
2.5°	2036.0	2036.0	2047.4	2051.2	2051.2	2045.5	2039.8	2045.5	2062.7	2068.4	2066.5
5°	2028.3	2043.6	2064.6	2068.4	2072.3	2070.3	2066.5	2070.3	2089.4	2093.3	2095.2
7.5°	2013.0	2041.7	2068.4	2074.2	2079.9	2074.2	2072.3	2076.1	2095.2	2099.0	2099.0
10°	1993.9	2034.1	2064.6	2068.4	2074.2	2068.4	2068.4	2076.1	2095.2	2099.0	2100.9
12.5°	1967.2	2022.6	2051.2	2055.1	2062.7	2060.8	2058.9	2066.5	2085.6	2089.4	2089.4
15°	1936.6	2001.6	2028.3	2032.1	2045.5	2041.7	2041.7	2049.3	2070.3	2076.1	2074.2
17.5°	1894.6	1974.8	2005.4	2011.1	2020.7	2018.8	2020.7	2028.3	2047.4	2051.2	2053.2
20°	1846.9	1938.6	1974.8	1980.6	1990.1	1990.1	1990.1	1999.7	2018.8	2026.4	2026.4
22.5°	1781.9	1900.4	1938.6	1942.4	1953.8	1953.8	1957.7	1971.0	1988.2	1990.1	1990.1
25°	1705.5	1858.3	1890.8	1902.3	1913.7	1919.5	1925.2	1932.8	1938.6	1936.6	1938.6
27.5°	1625.3	1804.9	1846.9	1854.5	1869.8	1875.5	1883.2	1885.1	1887.0	1892.7	1888.9
30°	1535.5	1730.4	1793.4	1801.0	1825.9	1829.7	1822.0	1825.9	1835.4	1839.2	1843.1
32.5°	1434.3	1619.6	1738.0	1755.2	1778.1	1766.7	1764.7	1770.5	1785.8	1785.8	1789.6
35°	1296.8	1533.6	1686.4	1701.7	1718.9	1705.5	1713.2	1715.1	1724.6	1730.4	1728.5
37.5°	1145.9	1459.1	1633.0	1644.4	1657.8	1640.6	1652.1	1657.8	1665.4	1661.6	1661.6
40°	1012.3	1342.6	1569.9	1577.6	1589.0	1575.7	1587.1	1590.9	1594.8	1590.9	1589.0
42.5°	913.0	1214.7	1503.1	1512.6	1505.0	1514.5	1518.4	1526.0	1520.3	1512.6	1512.6
45°	836.6	1180.3	1430.5	1442.0	1430.5	1445.8	1451.5	1451.5	1434.3	1430.5	1428.6
47.5°	811.8	1111.6	1357.9	1357.9	1352.2	1371.3	1380.8	1367.5	1350.3	1344.5	1344.5
50°	809.8	1035.2	1258.6	1251.0	1277.7	1300.6	1291.1	1277.7	1264.3	1243.3	1243.3
52.5°	735.4	941.6	1130.7	1159.3	1201.3	1214.7	1199.4	1186.0	1163.1	1153.5	1145.9
55°	681.9	844.2	1014.2	1071.5	1115.4	1132.6	1104.0	1090.6	1056.2	1050.5	1046.7
57.5°	670.4	702.9	907.2	979.8	1033.3	1031.4	1014.2	989.4	960.7	955.0	953.1
60°	615.0	508.1	792.6	878.6	934.0	928.3	913.0	890.1	863.3	859.5	855.7
62.5°	557.7	368.6	662.8	760.2	838.5	836.6	823.2	788.8	769.7	760.2	752.5
65°	473.7	309.4	471.8	632.2	744.9	748.7	720.1	695.2	674.2	662.8	660.9
67.5°	361.0	252.1	319.0	527.2	655.1	651.3	615.0	603.6	576.8	571.1	559.6
70°	267.4	168.1	221.6	427.8	567.3	557.7	529.1	515.7	490.9	477.5	469.9
72.5°	221.6	135.6	162.4	332.3	477.5	466.0	441.2	425.9	404.9	393.5	385.8
75°	179.5	143.2	124.2	246.4	387.7	380.1	357.2	341.9	324.7	309.4	311.3
77.5°	131.8	133.7	99.3	181.4	307.5	296.0	282.7	263.6	255.9	240.7	240.7
80°	99.3	105.0	74.5	124.2	221.6	221.6	210.1	196.7	183.4	175.7	175.7
82.5°	66.8	66.8	55.4	78.3	150.9	145.2	137.5	133.7	126.1	122.2	122.2
85°	30.6	38.2	34.4	47.8	82.1	86.0	86.0	82.1	80.2	76.4	78.3
87.5°	9.5	17.2	21.0	26.7	42.0	43.9	45.8	45.8	45.8	47.8	47.8
90°	3.9	7.1	10.2	11.0	17.3	25.7	29.9	26.5	20.0	15.0	15.0
92.5°	15.8	42.5	69.3	76.0	106.9	147.9	168.5	147.6	106.0	74.8	71.8
95°	37.8	86.8	135.8	148.0	262.8	415.9	492.5	439.5	333.5	253.9	245.0
97.5°	65.3	108.5	151.7	162.5	354.0	609.3	737.0	703.5	636.4	586.2	569.0
100°	86.6	125.8	164.9	174.8	387.3	670.5	812.1	814.6	819.5	823.1	802.7
102.5°	104.8	141.3	177.8	187.0	402.4	689.8	833.4	876.1	961.5	1025.5	1008.0
105°	135.4	166.4	197.4	205.1	413.8	692.0	831.0	926.7	1118.2	1261.7	1252.3
107.5°	166.9	195.8	224.6	231.9	415.8	661.1	783.8	917.3	1184.3	1384.6	1386.9
110°	188.1	214.2	240.4	246.9	412.8	633.8	744.4	893.7	1192.1	1416.0	1425.8

TEST NUMBER: P934395

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	209.0	233.9	258.7	264.9	412.8	610.1	708.6	861.3	1166.8	1395.9	1411.0
115°	240.6	263.5	286.4	292.1	416.7	582.7	665.7	812.9	1107.1	1327.8	1348.7
117.5°	271.6	292.4	313.2	318.5	424.4	565.6	636.1	769.0	1034.6	1233.8	1256.9
120°	289.7	309.3	329.0	333.9	430.7	559.8	624.4	745.7	988.3	1170.4	1192.8
122.5°	307.4	327.2	347.0	351.9	439.7	556.8	615.3	724.6	943.2	1107.0	1129.2
125°	334.6	352.6	370.6	375.1	451.9	554.3	605.5	698.3	883.9	1023.2	1043.6
127.5°	356.7	374.8	393.0	397.6	464.1	552.8	597.2	676.9	836.3	955.9	973.0
130°	368.4	388.0	407.7	412.6	473.0	553.7	594.0	665.0	806.9	913.3	929.2
132.5°	380.7	400.2	419.9	424.8	480.3	554.3	591.3	654.8	781.9	877.1	891.3
135°	398.8	416.7	434.4	438.9	488.1	553.7	586.6	639.8	746.1	825.9	838.2
137.5°	417.3	435.0	452.7	457.1	499.9	557.1	585.8	630.8	720.7	788.2	798.2
140°	432.6	448.9	465.2	469.3	507.2	557.7	583.0	621.9	699.5	757.8	767.2
142.5°	444.5	459.5	474.5	478.3	513.2	559.7	583.0	617.1	685.4	736.6	744.7
145°	462.6	475.7	488.9	492.1	521.1	559.8	579.1	607.0	662.9	704.7	710.8
147.5°	480.7	493.4	506.2	509.4	532.6	563.6	579.1	601.1	644.9	677.9	682.9
150°	492.5	504.0	515.6	518.5	538.7	565.6	579.1	597.6	634.8	662.6	666.7
152.5°	504.7	513.5	522.2	524.4	542.6	567.0	579.1	595.0	626.6	650.4	653.5
155°	522.8	529.3	535.8	537.4	551.3	569.8	579.1	591.7	616.8	635.7	637.8
157.5°	536.1	542.4	548.7	550.4	559.9	572.7	579.1	588.9	608.4	623.1	624.6
160°	545.2	550.2	555.0	556.3	563.9	574.1	579.1	587.5	604.2	616.8	617.7
162.5°	554.3	558.0	561.6	562.6	568.1	575.5	579.1	586.2	600.4	611.0	611.8
165°	564.1	567.5	570.7	571.6	574.1	577.4	579.1	584.2	594.3	601.9	602.8
167.5°	573.2	574.7	576.3	576.7	578.8	581.6	583.0	586.4	593.1	598.0	598.4
170°	579.1	580.6	582.3	582.6	582.7	582.9	583.0	586.4	593.1	598.0	598.0
172.5°	582.3	582.6	582.9	583.0	583.0	583.0	583.0	585.7	591.0	594.9	594.6
175°	586.6	586.6	586.6	586.6	585.4	583.8	583.0	584.7	588.0	590.5	590.5
177.5°	586.6	586.6	586.6	586.6	585.6	584.4	583.8	585.1	587.7	589.7	589.3
180°	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6

TEST NUMBER: P934395

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8
2.5°	2070.3	2064.6	2070.3	2066.5	2068.4	2062.7	2045.5	2039.8	2045.5	2051.2	2051.2
5°	2095.2	2091.4	2095.2	2095.2	2093.3	2089.4	2070.3	2066.5	2070.3	2072.3	2068.4
7.5°	2102.8	2097.1	2102.8	2099.0	2099.0	2095.2	2076.1	2072.3	2074.2	2079.9	2074.2
10°	2102.8	2097.1	2102.8	2100.9	2099.0	2095.2	2076.1	2068.4	2068.4	2074.2	2068.4
12.5°	2093.3	2089.4	2093.3	2089.4	2089.4	2085.6	2066.5	2058.9	2060.8	2062.7	2055.1
15°	2078.0	2072.3	2078.0	2074.2	2076.1	2070.3	2049.3	2041.7	2041.7	2045.5	2032.1
17.5°	2055.1	2047.4	2055.1	2053.2	2051.2	2047.4	2028.3	2020.7	2018.8	2020.7	2011.1
20°	2028.3	2022.6	2028.3	2026.4	2026.4	2018.8	1999.7	1990.1	1990.1	1990.1	1980.6
22.5°	1986.3	1980.6	1986.3	1990.1	1990.1	1988.2	1971.0	1957.7	1953.8	1953.8	1942.4
25°	1938.6	1932.8	1938.6	1938.6	1936.6	1938.6	1932.8	1925.2	1919.5	1913.7	1902.3
27.5°	1892.7	1888.9	1892.7	1888.9	1892.7	1887.0	1885.1	1883.2	1875.5	1869.8	1854.5
30°	1846.9	1843.1	1846.9	1843.1	1839.2	1835.4	1825.9	1822.0	1829.7	1825.9	1801.0
32.5°	1789.6	1785.8	1789.6	1789.6	1785.8	1785.8	1770.5	1764.7	1766.7	1778.1	1755.2
35°	1730.4	1724.6	1730.4	1728.5	1730.4	1724.6	1715.1	1713.2	1705.5	1718.9	1701.7
37.5°	1661.6	1655.9	1661.6	1661.6	1661.6	1665.4	1657.8	1652.1	1640.6	1657.8	1644.4
40°	1590.9	1583.3	1590.9	1589.0	1590.9	1594.8	1590.9	1587.1	1575.7	1589.0	1577.6
42.5°	1510.7	1508.8	1510.7	1512.6	1512.6	1520.3	1526.0	1518.4	1514.5	1505.0	1512.6
45°	1424.8	1420.9	1424.8	1428.6	1430.5	1434.3	1451.5	1451.5	1445.8	1430.5	1442.0
47.5°	1333.1	1323.5	1333.1	1344.5	1344.5	1350.3	1367.5	1380.8	1371.3	1352.2	1357.9
50°	1235.7	1237.6	1235.7	1243.3	1243.3	1264.3	1277.7	1291.1	1300.6	1277.7	1251.0
52.5°	1140.2	1138.4	1140.2	1145.9	1153.5	1163.1	1186.0	1199.4	1214.7	1201.3	1159.3
55°	1044.8	1048.6	1044.8	1046.7	1050.5	1056.2	1090.6	1104.0	1132.6	1115.4	1071.5
57.5°	949.3	943.5	949.3	953.1	955.0	960.7	989.4	1014.2	1031.4	1033.3	979.8
60°	838.5	830.8	838.5	855.7	859.5	863.3	890.1	913.0	928.3	934.0	878.6
62.5°	741.1	727.7	741.1	752.5	760.2	769.7	788.8	823.2	836.6	838.5	760.2
65°	637.9	632.2	637.9	660.9	662.8	674.2	695.2	720.1	748.7	744.9	632.2
67.5°	544.4	544.4	544.4	559.6	571.1	576.8	603.6	615.0	651.3	655.1	527.2
70°	458.4	456.5	458.4	469.9	477.5	490.9	515.7	529.1	557.7	567.3	427.8
72.5°	376.3	374.4	376.3	385.8	393.5	404.9	425.9	441.2	466.0	477.5	332.3
75°	303.7	299.9	303.7	311.3	309.4	324.7	341.9	357.2	380.1	387.7	246.4
77.5°	233.0	233.0	233.0	240.7	240.7	255.9	263.6	282.7	296.0	307.5	181.4
80°	173.8	171.9	173.8	175.7	175.7	183.4	196.7	210.1	221.6	221.6	124.2
82.5°	122.2	118.4	122.2	122.2	122.2	126.1	133.7	137.5	145.2	150.9	78.3
85°	76.4	76.4	76.4	78.3	76.4	80.2	82.1	86.0	86.0	82.1	47.8
87.5°	49.7	47.8	49.7	47.8	47.8	45.8	45.8	45.8	43.9	42.0	26.7
90°	15.0	15.0	15.0	15.0	15.0	20.0	26.5	29.9	25.7	17.3	11.0
92.5°	59.9	48.0	59.9	71.8	74.8	106.0	147.6	168.5	147.9	106.9	76.0
95°	208.9	172.9	208.9	245.0	253.9	333.5	439.5	492.5	415.9	262.8	148.0
97.5°	500.4	431.9	500.4	569.0	586.2	636.4	703.5	737.0	609.3	354.0	162.5
100°	721.0	639.3	721.0	802.7	823.1	819.5	814.6	812.1	670.5	387.3	174.8
102.5°	938.0	868.0	938.0	1008.0	1025.5	961.5	876.1	833.4	689.8	402.4	187.0
105°	1214.7	1177.0	1214.7	1252.3	1261.7	1118.2	926.7	831.0	692.0	413.8	205.1
107.5°	1395.9	1405.0	1395.9	1386.9	1384.6	1184.3	917.3	783.8	661.1	415.8	231.9
110°	1465.0	1504.2	1465.0	1425.8	1416.0	1192.1	893.7	744.4	633.8	412.8	246.9

TEST NUMBER: P934395

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1471.2	1531.3	1471.2	1411.0	1395.9	1166.8	861.3	708.6	610.1	412.8	264.9
115°	1432.1	1515.6	1432.1	1348.7	1327.8	1107.1	812.9	665.7	582.7	416.7	292.1
117.5°	1349.5	1442.0	1349.5	1256.9	1233.8	1034.6	769.0	636.1	565.6	424.4	318.5
120°	1282.8	1372.7	1282.8	1192.8	1170.4	988.3	745.7	624.4	559.8	430.7	333.9
122.5°	1217.9	1306.6	1217.9	1129.2	1107.0	943.2	724.6	615.3	556.8	439.7	351.9
125°	1125.3	1207.0	1125.3	1043.6	1023.2	883.9	698.3	605.5	554.3	451.9	375.1
127.5°	1042.0	1111.0	1042.0	973.0	955.9	836.3	676.9	597.2	552.8	464.1	397.6
130°	992.9	1056.6	992.9	929.2	913.3	806.9	665.0	594.0	553.7	473.0	412.6
132.5°	948.4	1005.4	948.4	891.3	877.1	781.9	654.8	591.3	554.3	480.3	424.8
135°	887.4	936.6	887.4	838.2	825.9	746.1	639.8	586.6	553.7	488.1	438.9
137.5°	838.5	878.7	838.5	798.2	788.2	720.7	630.8	585.8	557.1	499.9	457.1
140°	804.8	842.4	804.8	767.2	757.8	699.5	621.9	583.0	557.7	507.2	469.3
142.5°	777.0	809.4	777.0	744.7	736.6	685.4	617.1	583.0	559.7	513.2	478.3
145°	735.4	759.8	735.4	710.8	704.7	662.9	607.0	579.1	559.8	521.1	492.1
147.5°	703.3	723.6	703.3	682.9	677.9	644.9	601.1	579.1	563.6	532.6	509.4
150°	683.1	699.5	683.1	666.7	662.6	634.8	597.6	579.1	565.6	538.7	518.5
152.5°	665.9	678.3	665.9	653.5	650.4	626.6	595.0	579.1	567.0	542.6	524.4
155°	646.1	654.3	646.1	637.8	635.7	616.8	591.7	579.1	569.8	551.3	537.4
157.5°	630.4	636.1	630.4	624.6	623.1	608.4	588.9	579.1	572.7	559.9	550.4
160°	621.0	624.4	621.0	617.7	616.8	604.2	587.5	579.1	574.1	563.9	556.3
162.5°	614.9	618.1	614.9	611.8	611.0	600.4	586.2	579.1	575.5	568.1	562.6
165°	606.0	609.4	606.0	602.8	601.9	594.3	584.2	579.1	577.4	574.1	571.6
167.5°	599.7	601.2	599.7	598.4	598.0	593.1	586.4	583.0	581.6	578.8	576.7
170°	598.0	598.0	598.0	598.0	598.0	593.1	586.4	583.0	582.9	582.7	582.6
172.5°	593.3	592.1	593.3	594.6	594.9	591.0	585.7	583.0	583.0	583.0	583.0
175°	590.5	590.5	590.5	590.5	590.5	588.0	584.7	583.0	583.8	585.4	586.6
177.5°	588.0	586.6	588.0	589.3	589.7	587.7	585.1	583.8	584.4	585.6	586.6
180°	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6

TEST NUMBER: P934395

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8
2.5°	2047.4	2036.0	2036.0	2016.9	2009.2	2003.5	1993.9	1965.3	1957.7	1950.0	1961.5
5°	2064.6	2043.6	2028.3	1993.9	1965.3	1953.8	1917.5	1848.8	1802.9	1768.6	1749.5
7.5°	2068.4	2041.7	2013.0	1959.6	1890.8	1860.2	1749.5	1623.4	1589.0	1558.5	1539.4
10°	2064.6	2034.1	1993.9	1913.7	1751.4	1697.9	1587.1	1505.0	1484.0	1478.2	1484.0
12.5°	2051.2	2022.6	1967.2	1833.5	1606.2	1569.9	1505.0	1457.2	1453.4	1463.0	1514.5
15°	2028.3	2001.6	1936.6	1726.5	1526.0	1499.3	1453.4	1436.2	1457.2	1524.1	1678.8
17.5°	2005.4	1974.8	1894.6	1621.5	1464.9	1445.8	1413.3	1447.7	1566.1	1655.9	1707.4
20°	1974.8	1938.6	1846.9	1545.1	1420.9	1403.8	1388.5	1543.2	1633.0	1665.4	1694.1
22.5°	1938.6	1900.4	1781.9	1491.6	1375.1	1361.7	1371.3	1596.7	1633.0	1655.9	1680.7
25°	1890.8	1858.3	1705.5	1449.6	1338.8	1323.5	1359.8	1590.9	1611.9	1617.7	1667.3
27.5°	1846.9	1804.9	1625.3	1411.4	1294.9	1289.2	1369.4	1566.1	1581.4	1587.1	1640.6
30°	1793.4	1730.4	1535.5	1371.3	1249.0	1247.1	1371.3	1535.5	1531.7	1547.0	1600.5
32.5°	1738.0	1619.6	1434.3	1321.6	1205.1	1203.2	1357.9	1489.7	1485.9	1506.9	1547.0
35°	1686.4	1533.6	1296.8	1264.3	1149.7	1151.6	1325.4	1436.2	1438.1	1457.2	1482.1
37.5°	1633.0	1459.1	1145.9	1201.3	1096.3	1096.3	1281.5	1386.6	1382.7	1388.5	1422.9
40°	1569.9	1342.6	1012.3	1119.3	1046.7	1041.0	1228.0	1333.1	1319.7	1317.8	1365.6
42.5°	1503.1	1214.7	913.0	1010.4	989.4	981.7	1163.1	1268.1	1243.3	1249.0	1310.2
45°	1430.5	1180.3	836.6	853.8	930.2	924.4	1092.5	1193.7	1176.5	1191.7	1254.8
47.5°	1357.9	1111.6	811.8	708.6	867.1	865.2	1014.2	1121.2	1111.6	1126.9	1193.7
50°	1258.6	1035.2	809.8	607.4	796.5	804.1	920.6	1050.5	1050.5	1063.9	1134.5
52.5°	1130.7	941.6	735.4	550.1	714.3	737.3	838.5	989.4	993.2	1006.6	1069.6
55°	1014.2	844.2	681.9	506.2	616.9	666.6	758.3	926.4	934.0	947.4	1004.7
57.5°	907.2	702.9	670.4	454.6	527.2	574.9	687.6	865.2	869.0	880.5	935.9
60°	792.6	508.1	615.0	399.2	448.8	485.1	622.7	792.6	806.0	813.7	861.4
62.5°	662.8	368.6	557.7	361.0	410.6	418.3	569.2	723.9	741.1	746.8	775.5
65°	471.8	309.4	473.7	328.5	370.5	372.4	511.9	653.2	668.5	678.0	699.1
67.5°	319.0	252.1	361.0	298.0	340.0	341.9	456.5	571.1	592.1	599.7	613.1
70°	221.6	168.1	267.4	265.5	305.6	309.4	397.3	496.6	515.7	521.4	529.1
72.5°	162.4	135.6	221.6	238.8	269.3	273.1	336.2	412.6	431.7	437.4	441.2
75°	124.2	143.2	179.5	208.2	229.2	231.1	275.0	336.2	349.5	353.3	355.3
77.5°	99.3	133.7	131.8	168.1	187.2	183.4	215.8	259.8	271.2	271.2	271.2
80°	74.5	105.0	99.3	120.3	137.5	133.7	154.7	185.3	189.1	192.9	191.0
82.5°	55.4	66.8	66.8	76.4	91.7	87.9	103.1	120.3	120.3	120.3	124.2
85°	34.4	38.2	30.6	40.1	51.6	49.7	57.3	64.9	66.8	66.8	63.0
87.5°	21.0	17.2	9.5	15.3	22.9	22.9	26.7	28.6	26.7	26.7	26.7
90°	10.2	7.1	3.9	7.1	10.2	11.0	17.3	25.7	29.9	26.5	20.0
92.5°	69.3	42.5	15.8	42.5	69.3	76.0	106.9	147.9	168.5	147.6	106.0
95°	135.8	86.8	37.8	86.8	135.8	148.0	262.8	415.9	492.5	439.5	333.5
97.5°	151.7	108.5	65.3	108.5	151.7	162.5	354.0	609.3	737.0	703.5	636.4
100°	164.9	125.8	86.6	125.8	164.9	174.8	387.3	670.5	812.1	814.6	819.5
102.5°	177.8	141.3	104.8	141.3	177.8	187.0	402.4	689.8	833.4	876.1	961.5
105°	197.4	166.4	135.4	166.4	197.4	205.1	413.8	692.0	831.0	926.7	1118.2
107.5°	224.6	195.8	166.9	195.8	224.6	231.9	415.8	661.1	783.8	917.3	1184.3
110°	240.4	214.2	188.1	214.2	240.4	246.9	412.8	633.8	744.4	893.7	1192.1

TEST NUMBER: P934395

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	258.7	233.9	209.0	233.9	258.7	264.9	412.8	610.1	708.6	861.3	1166.8
115°	286.4	263.5	240.6	263.5	286.4	292.1	416.7	582.7	665.7	812.9	1107.1
117.5°	313.2	292.4	271.6	292.4	313.2	318.5	424.4	565.6	636.1	769.0	1034.6
120°	329.0	309.3	289.7	309.3	329.0	333.9	430.7	559.8	624.4	745.7	988.3
122.5°	347.0	327.2	307.4	327.2	347.0	351.9	439.7	556.8	615.3	724.6	943.2
125°	370.6	352.6	334.6	352.6	370.6	375.1	451.9	554.3	605.5	698.3	883.9
127.5°	393.0	374.8	356.7	374.8	393.0	397.6	464.1	552.8	597.2	676.9	836.3
130°	407.7	388.0	368.4	388.0	407.7	412.6	473.0	553.7	594.0	665.0	806.9
132.5°	419.9	400.2	380.7	400.2	419.9	424.8	480.3	554.3	591.3	654.8	781.9
135°	434.4	416.7	398.8	416.7	434.4	438.9	488.1	553.7	586.6	639.8	746.1
137.5°	452.7	435.0	417.3	435.0	452.7	457.1	499.9	557.1	585.8	630.8	720.7
140°	465.2	448.9	432.6	448.9	465.2	469.3	507.2	557.7	583.0	621.9	699.5
142.5°	474.5	459.5	444.5	459.5	474.5	478.3	513.2	559.7	583.0	617.1	685.4
145°	488.9	475.7	462.6	475.7	488.9	492.1	521.1	559.8	579.1	607.0	662.9
147.5°	506.2	493.4	480.7	493.4	506.2	509.4	532.6	563.6	579.1	601.1	644.9
150°	515.6	504.0	492.5	504.0	515.6	518.5	538.7	565.6	579.1	597.6	634.8
152.5°	522.2	513.5	504.7	513.5	522.2	524.4	542.6	567.0	579.1	595.0	626.6
155°	535.8	529.3	522.8	529.3	535.8	537.4	551.3	569.8	579.1	591.7	616.8
157.5°	548.7	542.4	536.1	542.4	548.7	550.4	559.9	572.7	579.1	588.9	608.4
160°	555.0	550.2	545.2	550.2	555.0	556.3	563.9	574.1	579.1	587.5	604.2
162.5°	561.6	558.0	554.3	558.0	561.6	562.6	568.1	575.5	579.1	586.2	600.4
165°	570.7	567.5	564.1	567.5	570.7	571.6	574.1	577.4	579.1	584.2	594.3
167.5°	576.3	574.7	573.2	574.7	576.3	576.7	578.8	581.6	583.0	586.4	593.1
170°	582.3	580.6	579.1	580.6	582.3	582.6	582.7	582.9	583.0	586.4	593.1
172.5°	582.9	582.6	582.3	582.6	582.9	583.0	583.0	583.0	583.0	585.7	591.0
175°	586.6	586.6	586.6	586.6	586.6	586.6	585.4	583.8	583.0	584.7	588.0
177.5°	586.6	586.6	586.6	586.6	586.6	586.6	585.6	584.4	583.8	585.1	587.7
180°	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6

TEST NUMBER: P934395

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8	2018.8
2.5°	1948.1	1942.4	1950.0	1929.0	1950.0	1942.4	1948.1	1961.5	1950.0	1957.7	1965.3
5°	1709.4	1699.8	1669.2	1644.4	1669.2	1699.8	1709.4	1749.5	1768.6	1802.9	1848.8
7.5°	1527.9	1520.3	1512.6	1497.3	1512.6	1520.3	1527.9	1539.4	1558.5	1589.0	1623.4
10°	1487.8	1489.7	1501.2	1499.3	1501.2	1489.7	1487.8	1484.0	1478.2	1484.0	1505.0
12.5°	1590.9	1608.1	1671.2	1667.3	1671.2	1608.1	1590.9	1514.5	1463.0	1453.4	1457.2
15°	1709.4	1715.1	1728.5	1730.4	1728.5	1715.1	1709.4	1678.8	1524.1	1457.2	1436.2
17.5°	1720.8	1722.7	1732.3	1732.3	1732.3	1722.7	1720.8	1707.4	1655.9	1566.1	1447.7
20°	1711.3	1715.1	1734.2	1738.0	1734.2	1715.1	1711.3	1694.1	1665.4	1633.0	1543.2
22.5°	1707.4	1715.1	1730.4	1728.5	1730.4	1715.1	1707.4	1680.7	1655.9	1633.0	1596.7
25°	1688.3	1688.3	1690.3	1692.2	1690.3	1688.3	1688.3	1667.3	1617.7	1611.9	1590.9
27.5°	1648.2	1652.1	1663.5	1661.6	1663.5	1652.1	1648.2	1640.6	1587.1	1581.4	1566.1
30°	1611.9	1608.1	1598.6	1590.9	1598.6	1608.1	1611.9	1600.5	1547.0	1531.7	1535.5
32.5°	1550.8	1541.3	1531.7	1526.0	1531.7	1541.3	1550.8	1547.0	1506.9	1485.9	1489.7
35°	1478.2	1480.2	1478.2	1472.5	1478.2	1480.2	1478.2	1482.1	1457.2	1438.1	1436.2
37.5°	1426.7	1430.5	1428.6	1420.9	1428.6	1430.5	1426.7	1422.9	1388.5	1382.7	1386.6
40°	1373.2	1375.1	1373.2	1367.5	1373.2	1375.1	1373.2	1365.6	1317.8	1319.7	1333.1
42.5°	1321.6	1319.7	1314.0	1310.2	1314.0	1319.7	1321.6	1310.2	1249.0	1243.3	1268.1
45°	1262.4	1264.3	1252.9	1247.1	1252.9	1264.3	1262.4	1254.8	1191.7	1176.5	1193.7
47.5°	1203.2	1203.2	1193.7	1187.9	1193.7	1203.2	1203.2	1193.7	1126.9	1111.6	1121.2
50°	1140.2	1138.4	1125.0	1123.1	1125.0	1138.4	1140.2	1134.5	1063.9	1050.5	1050.5
52.5°	1067.7	1067.7	1069.6	1073.4	1069.6	1067.7	1067.7	1069.6	1006.6	993.2	989.4
55°	1004.7	1006.6	1019.9	1023.8	1019.9	1006.6	1004.7	1004.7	947.4	934.0	926.4
57.5°	939.7	939.7	949.3	949.3	949.3	939.7	939.7	935.9	880.5	869.0	865.2
60°	865.2	869.0	876.7	874.8	876.7	869.0	865.2	861.4	813.7	806.0	792.6
62.5°	786.9	790.7	792.6	788.8	792.6	790.7	786.9	775.5	746.8	741.1	723.9
65°	704.8	708.6	710.5	706.7	710.5	708.6	704.8	699.1	678.0	668.5	653.2
67.5°	620.8	618.8	616.9	624.6	616.9	618.8	620.8	613.1	599.7	592.1	571.1
70°	534.8	534.8	532.9	536.7	532.9	534.8	534.8	529.1	521.4	515.7	496.6
72.5°	443.1	441.2	448.8	443.1	448.8	441.2	443.1	441.2	437.4	431.7	412.6
75°	353.3	357.2	353.3	359.1	353.3	357.2	353.3	355.3	353.3	349.5	336.2
77.5°	269.3	273.1	269.3	269.3	269.3	273.1	269.3	271.2	271.2	271.2	259.8
80°	191.0	189.1	189.1	187.2	189.1	189.1	191.0	191.0	192.9	189.1	185.3
82.5°	122.2	120.3	120.3	124.2	120.3	120.3	122.2	124.2	120.3	120.3	120.3
85°	66.8	68.8	64.9	64.9	64.9	68.8	66.8	63.0	66.8	66.8	64.9
87.5°	24.8	22.9	22.9	22.9	22.9	22.9	24.8	26.7	26.7	26.7	28.6
90°	15.0	15.0	15.0	15.0	15.0	15.0	15.0	20.0	26.5	29.9	25.7
92.5°	74.8	71.8	59.9	48.0	59.9	71.8	74.8	106.0	147.6	168.5	147.9
95°	253.9	245.0	208.9	172.9	208.9	245.0	253.9	333.5	439.5	492.5	415.9
97.5°	586.2	569.0	500.4	431.9	500.4	569.0	586.2	636.4	703.5	737.0	609.3
100°	823.1	802.7	721.0	639.3	721.0	802.7	823.1	819.5	814.6	812.1	670.5
102.5°	1025.5	1008.0	938.0	868.0	938.0	1008.0	1025.5	961.5	876.1	833.4	689.8
105°	1261.7	1252.3	1214.7	1177.0	1214.7	1252.3	1261.7	1118.2	926.7	831.0	692.0
107.5°	1384.6	1386.9	1395.9	1405.0	1395.9	1386.9	1384.6	1184.3	917.3	783.8	661.1
110°	1416.0	1425.8	1465.0	1504.2	1465.0	1425.8	1416.0	1192.1	893.7	744.4	633.8

TEST NUMBER: P934395

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1395.9	1411.0	1471.2	1531.3	1471.2	1411.0	1395.9	1166.8	861.3	708.6	610.1
115°	1327.8	1348.7	1432.1	1515.6	1432.1	1348.7	1327.8	1107.1	812.9	665.7	582.7
117.5°	1233.8	1256.9	1349.5	1442.0	1349.5	1256.9	1233.8	1034.6	769.0	636.1	565.6
120°	1170.4	1192.8	1282.8	1372.7	1282.8	1192.8	1170.4	988.3	745.7	624.4	559.8
122.5°	1107.0	1129.2	1217.9	1306.6	1217.9	1129.2	1107.0	943.2	724.6	615.3	556.8
125°	1023.2	1043.6	1125.3	1207.0	1125.3	1043.6	1023.2	883.9	698.3	605.5	554.3
127.5°	955.9	973.0	1042.0	1111.0	1042.0	973.0	955.9	836.3	676.9	597.2	552.8
130°	913.3	929.2	992.9	1056.6	992.9	929.2	913.3	806.9	665.0	594.0	553.7
132.5°	877.1	891.3	948.4	1005.4	948.4	891.3	877.1	781.9	654.8	591.3	554.3
135°	825.9	838.2	887.4	936.6	887.4	838.2	825.9	746.1	639.8	586.6	553.7
137.5°	788.2	798.2	838.5	878.7	838.5	798.2	788.2	720.7	630.8	585.8	557.1
140°	757.8	767.2	804.8	842.4	804.8	767.2	757.8	699.5	621.9	583.0	557.7
142.5°	736.6	744.7	777.0	809.4	777.0	744.7	736.6	685.4	617.1	583.0	559.7
145°	704.7	710.8	735.4	759.8	735.4	710.8	704.7	662.9	607.0	579.1	559.8
147.5°	677.9	682.9	703.3	723.6	703.3	682.9	677.9	644.9	601.1	579.1	563.6
150°	662.6	666.7	683.1	699.5	683.1	666.7	662.6	634.8	597.6	579.1	565.6
152.5°	650.4	653.5	665.9	678.3	665.9	653.5	650.4	626.6	595.0	579.1	567.0
155°	635.7	637.8	646.1	654.3	646.1	637.8	635.7	616.8	591.7	579.1	569.8
157.5°	623.1	624.6	630.4	636.1	630.4	624.6	623.1	608.4	588.9	579.1	572.7
160°	616.8	617.7	621.0	624.4	621.0	617.7	616.8	604.2	587.5	579.1	574.1
162.5°	611.0	611.8	614.9	618.1	614.9	611.8	611.0	600.4	586.2	579.1	575.5
165°	601.9	602.8	606.0	609.4	606.0	602.8	601.9	594.3	584.2	579.1	577.4
167.5°	598.0	598.4	599.7	601.2	599.7	598.4	598.0	593.1	586.4	583.0	581.6
170°	598.0	598.0	598.0	598.0	598.0	598.0	598.0	593.1	586.4	583.0	582.9
172.5°	594.9	594.6	593.3	592.1	593.3	594.6	594.9	591.0	585.7	583.0	583.0
175°	590.5	590.5	590.5	590.5	590.5	590.5	590.5	588.0	584.7	583.0	583.8
177.5°	589.7	589.3	588.0	586.6	588.0	589.3	589.7	587.7	585.1	583.8	584.4
180°	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6

TEST NUMBER: P934395

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2018.8	2018.8	2018.8	2018.8	2018.8
2.5°	1993.9	2003.5	2009.2	2016.9	2036.0
5°	1917.5	1953.8	1965.3	1993.9	2028.3
7.5°	1749.5	1860.2	1890.8	1959.6	2013.0
10°	1587.1	1697.9	1751.4	1913.7	1993.9
12.5°	1505.0	1569.9	1606.2	1833.5	1967.2
15°	1453.4	1499.3	1526.0	1726.5	1936.6
17.5°	1413.3	1445.8	1464.9	1621.5	1894.6
20°	1388.5	1403.8	1420.9	1545.1	1846.9
22.5°	1371.3	1361.7	1375.1	1491.6	1781.9
25°	1359.8	1323.5	1338.8	1449.6	1705.5
27.5°	1369.4	1289.2	1294.9	1411.4	1625.3
30°	1371.3	1247.1	1249.0	1371.3	1535.5
32.5°	1357.9	1203.2	1205.1	1321.6	1434.3
35°	1325.4	1151.6	1149.7	1264.3	1296.8
37.5°	1281.5	1096.3	1096.3	1201.3	1145.9
40°	1228.0	1041.0	1046.7	1119.3	1012.3
42.5°	1163.1	981.7	989.4	1010.4	913.0
45°	1092.5	924.4	930.2	853.8	836.6
47.5°	1014.2	865.2	867.1	708.6	811.8
50°	920.6	804.1	796.5	607.4	809.8
52.5°	838.5	737.3	714.3	550.1	735.4
55°	758.3	666.6	616.9	506.2	681.9
57.5°	687.6	574.9	527.2	454.6	670.4
60°	622.7	485.1	448.8	399.2	615.0
62.5°	569.2	418.3	410.6	361.0	557.7
65°	511.9	372.4	370.5	328.5	473.7
67.5°	456.5	341.9	340.0	298.0	361.0
70°	397.3	309.4	305.6	265.5	267.4
72.5°	336.2	273.1	269.3	238.8	221.6
75°	275.0	231.1	229.2	208.2	179.5
77.5°	215.8	183.4	187.2	168.1	131.8
80°	154.7	133.7	137.5	120.3	99.3
82.5°	103.1	87.9	91.7	76.4	66.8
85°	57.3	49.7	51.6	40.1	30.6
87.5°	26.7	22.9	22.9	15.3	9.5
90°	17.3	11.0	10.2	7.1	3.9
92.5°	106.9	76.0	69.3	42.5	15.8
95°	262.8	148.0	135.8	86.8	37.8
97.5°	354.0	162.5	151.7	108.5	65.3
100°	387.3	174.8	164.9	125.8	86.6
102.5°	402.4	187.0	177.8	141.3	104.8
105°	413.8	205.1	197.4	166.4	135.4
107.5°	415.8	231.9	224.6	195.8	166.9
110°	412.8	246.9	240.4	214.2	188.1



TEST NUMBER: P934395

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	412.8	264.9	258.7	233.9	209.0
115°	416.7	292.1	286.4	263.5	240.6
117.5°	424.4	318.5	313.2	292.4	271.6
120°	430.7	333.9	329.0	309.3	289.7
122.5°	439.7	351.9	347.0	327.2	307.4
125°	451.9	375.1	370.6	352.6	334.6
127.5°	464.1	397.6	393.0	374.8	356.7
130°	473.0	412.6	407.7	388.0	368.4
132.5°	480.3	424.8	419.9	400.2	380.7
135°	488.1	438.9	434.4	416.7	398.8
137.5°	499.9	457.1	452.7	435.0	417.3
140°	507.2	469.3	465.2	448.9	432.6
142.5°	513.2	478.3	474.5	459.5	444.5
145°	521.1	492.1	488.9	475.7	462.6
147.5°	532.6	509.4	506.2	493.4	480.7
150°	538.7	518.5	515.6	504.0	492.5
152.5°	542.6	524.4	522.2	513.5	504.7
155°	551.3	537.4	535.8	529.3	522.8
157.5°	559.9	550.4	548.7	542.4	536.1
160°	563.9	556.3	555.0	550.2	545.2
162.5°	568.1	562.6	561.6	558.0	554.3
165°	574.1	571.6	570.7	567.5	564.1
167.5°	578.8	576.7	576.3	574.7	573.2
170°	582.7	582.6	582.3	580.6	579.1
172.5°	583.0	583.0	582.9	582.6	582.3
175°	585.4	586.6	586.6	586.6	586.6
177.5°	585.6	586.6	586.6	586.6	586.6
180°	586.6	586.6	586.6	586.6	586.6

TEST NUMBER: P934395

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.28	14.22	14.17	15.13	16.28	16.12	17.06	17.01	17.96	19.12
	3H	13.76	14.61	14.66	15.52	16.70	17.47	18.31	18.37	19.23	20.41
	4H	13.96	14.75	14.87	15.68	16.86	17.92	18.72	18.84	19.64	20.83
	6H	14.08	14.81	15.01	15.74	16.94	18.21	18.95	19.14	19.87	21.07
	8H	14.09	14.78	15.02	15.73	16.93	18.29	18.99	19.22	19.93	21.13
	12H	14.06	14.72	15.00	15.66	16.89	18.33	19.00	19.27	19.94	21.16
4H	2H	14.33	15.12	15.24	16.04	17.23	16.54	17.33	17.46	18.25	19.44
	3H	15.36	16.02	16.29	16.97	18.18	18.05	18.72	18.98	19.67	20.87
	4H	15.64	16.24	16.58	17.19	18.42	18.59	19.19	19.53	20.14	21.37
	6H	15.77	16.29	16.72	17.26	18.49	18.96	19.48	19.91	20.45	21.68
	8H	15.78	16.26	16.73	17.23	18.47	19.07	19.55	20.02	20.52	21.76
	12H	15.75	16.19	16.72	17.17	18.41	19.13	19.57	20.10	20.55	21.80
8H	4H	16.10	16.59	17.06	17.55	18.79	18.72	19.20	19.67	20.17	21.41
	6H	16.37	16.77	17.35	17.77	19.01	19.16	19.56	20.14	20.57	21.81
	8H	16.41	16.76	17.40	17.76	19.02	19.31	19.67	20.30	20.66	21.92
	12H	16.40	16.71	17.39	17.70	19.00	19.42	19.73	20.41	20.72	22.02
12H	4H	16.11	16.55	17.09	17.53	18.78	18.68	19.12	19.66	20.11	21.35
	6H	16.43	16.78	17.42	17.78	19.04	19.16	19.51	20.15	20.51	21.77
	8H	16.50	16.81	17.49	17.80	19.10	19.32	19.63	20.32	20.62	21.93

END OF REPORT