

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934580

Luminaire Tested: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934580
REPORT IS A COMBINATION OF REPORTS P933701 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18994.0 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 168
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934580

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K

Luminous Intensity Polar Plot



TEST NUMBER: P934580

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	65	63
2	93	86	79	74	88	81	76	71	73	68	65	65	62	59	58	56	53
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	52	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27
8	57	44	36	30	54	42	35	29	38	32	28	35	30	26	31	27	24
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21
10	49	37	30	25	47	35	28	24	32	26	22	30	25	21	27	23	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15850	15850	15850	15850
5°	15975	16000	15975	12581
10°	15874	15761	15874	11268
15°	15707	15419	15707	12876
20°	15385	15015	15385	12902
25°	14718	14425	14718	12629
30°	13855	13935	13855	12029
35°	12358	13316	12358	11369
40°	10303	12586	10303	10870
45°	9212	11732	9212	10297
50°	9794	10714	9794	9722
55°	9223	9617	9223	9390
60°	9520	8168	9520	8600
65°	8645	6752	8645	7547
70°	6000	5381	6000	6326
75°	5282	3977	5282	4763
80°	4288	2629	4288	2863
85°	2511	1393	2511	1184

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 14110 cd/sqm

TEST NUMBER: P934580

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	462.6	2.4
10°-20°	1313.4	6.9
20°-30°	2030.3	10.7
30°-40°	2423.7	12.8
40°-50°	2437.9	12.8
50°-60°	2121.3	11.2
60°-70°	1504.0	7.9
70°-80°	795.7	4.2
80°-90°	201.5	1.1
90°-100°	428.9	2.3
100°-110°	1127.5	5.9
110°-120°	1169.1	6.2
120°-130°	937.8	4.9
130°-140°	735.9	3.9
140°-150°	564.8	3.0
150°-160°	406.7	2.1
160°-170°	248.9	1.3
170°-180°	84.1	0.4
0°-30°	3806.2	20.0
0°-40°	6229.9	32.8
0°-60°	10789.0	56.8
0°-90°	13290.3	70.0
90°-120°	2725.5	14.3
90°-150°	4964.0	26.1
90°-180°	5704.0	30.0
0°-180°	18994.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	5124	5124	5124	5124	5124	
5°	5149	5309	5149	4174	5149	488
15°	4916	5260	4916	4392	4916	1383
25°	4329	4906	4329	4296	4329	1988
35°	3292	4378	3292	3738	3292	2037
45°	2123	3607	2123	3166	2123	1701
55°	1731	2662	1731	2599	1731	1590
65°	1202	1605	1202	1794	1202	1149
75°	456	761	456	912	456	479
85°	78	194	78	165	78	105
90°	6	22	6	22	6	8
95°	57	259	57	259	57	63
105°	203	1766	203	1766	203	215
115°	361	2274	361	2274	361	356
125°	502	1810	502	1810	502	446
135°	598	1405	598	1405	598	463
145°	694	1140	694	1140	694	435
155°	784	982	784	982	784	360
165°	846	914	846	914	846	239
175°	880	886	880	886	880	84
180°	880	880	880	880	880	

TEST NUMBER: P934580

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5
2.5°	5168.2	5168.2	5197.2	5206.9	5206.9	5192.3	5177.8	5192.3	5236.0	5250.6	5245.7
5°	5148.7	5187.6	5240.8	5250.6	5260.2	5255.4	5245.7	5255.4	5303.9	5313.6	5318.4
7.5°	5109.9	5182.7	5250.6	5265.1	5279.6	5265.1	5260.2	5270.0	5318.4	5328.1	5328.1
10°	5061.5	5163.3	5240.8	5250.6	5265.1	5250.6	5250.6	5270.0	5318.4	5328.1	5333.0
12.5°	4993.6	5134.2	5206.9	5216.6	5236.0	5231.1	5226.3	5245.7	5294.1	5303.9	5303.9
15°	4916.1	5080.9	5148.7	5158.4	5192.3	5182.7	5182.7	5202.1	5255.4	5270.0	5265.1
17.5°	4809.4	5013.0	5090.5	5105.1	5129.3	5124.5	5129.3	5148.7	5197.2	5206.9	5211.7
20°	4688.2	4920.8	5013.0	5027.5	5051.8	5051.8	5051.8	5076.0	5124.5	5143.9	5143.9
22.5°	4523.4	4823.9	4920.8	4930.6	4959.7	4959.7	4969.3	5003.2	5046.9	5051.8	5051.8
25°	4329.4	4717.2	4799.6	4828.8	4857.9	4872.4	4886.9	4906.3	4920.8	4916.1	4920.8
27.5°	4125.8	4581.5	4688.2	4707.6	4746.3	4760.9	4780.3	4785.1	4790.0	4804.5	4794.9
30°	3897.9	4392.4	4552.4	4571.8	4634.8	4644.5	4625.2	4634.8	4659.1	4668.8	4678.4
32.5°	3640.9	4111.3	4411.8	4455.5	4513.6	4484.6	4479.7	4494.2	4533.0	4533.0	4542.7
35°	3291.9	3893.1	4280.9	4319.7	4363.3	4329.4	4348.8	4353.7	4377.9	4392.4	4387.6
37.5°	2908.9	3704.0	4145.2	4174.3	4208.2	4164.6	4193.7	4208.2	4227.6	4217.9	4217.9
40°	2569.5	3408.2	3985.2	4004.6	4033.6	3999.7	4028.9	4038.5	4048.2	4038.5	4033.6
42.5°	2317.4	3083.4	3815.5	3839.8	3820.4	3844.5	3854.3	3873.7	3859.2	3839.8	3839.8
45°	2123.4	2996.1	3631.3	3660.3	3631.3	3670.1	3684.6	3684.6	3640.9	3631.3	3626.4
47.5°	2060.5	2821.6	3447.1	3447.1	3432.5	3481.0	3505.2	3471.2	3427.7	3413.1	3413.1
50°	2055.6	2627.7	3195.0	3175.6	3243.4	3301.6	3277.4	3243.4	3209.5	3156.2	3156.2
52.5°	1866.5	2390.2	2870.1	2942.8	3049.5	3083.4	3044.6	3010.7	2952.5	2928.3	2908.9
55°	1730.7	2142.9	2574.4	2719.8	2831.3	2874.9	2802.3	2768.3	2681.1	2666.5	2656.8
57.5°	1701.7	1784.1	2302.9	2487.1	2622.8	2618.0	2574.4	2511.4	2438.6	2424.1	2419.2
60°	1561.1	1289.6	2012.0	2230.1	2370.8	2356.2	2317.4	2259.2	2191.3	2181.7	2172.0
62.5°	1415.7	935.7	1682.3	1929.6	2128.3	2123.4	2089.5	2002.3	1953.8	1929.6	1910.2
65°	1202.3	785.4	1197.5	1604.8	1890.8	1900.4	1827.8	1764.7	1711.4	1682.3	1677.5
67.5°	916.3	639.9	809.6	1338.1	1662.9	1653.2	1561.1	1532.0	1464.1	1449.6	1420.5
70°	678.7	426.6	562.4	1086.0	1439.9	1415.7	1342.9	1309.0	1246.0	1212.0	1192.6
72.5°	562.4	344.2	412.1	843.6	1212.0	1183.0	1119.9	1081.2	1027.8	998.7	979.4
75°	455.7	363.6	315.2	625.4	984.1	964.7	906.6	867.8	824.2	785.4	790.3
77.5°	334.5	339.4	252.1	460.6	780.5	751.5	717.5	669.1	649.7	610.9	610.9
80°	252.1	266.6	189.1	315.2	562.4	562.4	533.3	499.4	465.5	446.0	446.0
82.5°	169.7	169.7	140.6	198.7	383.1	368.4	349.1	339.4	320.0	310.3	310.3
85°	77.5	96.9	87.3	121.2	208.5	218.1	218.1	208.5	203.6	194.0	198.7
87.5°	24.3	43.6	53.3	67.9	106.7	111.5	116.3	116.3	116.3	121.2	121.2
90°	5.9	10.6	15.4	16.5	26.0	38.6	44.9	39.9	29.9	22.4	22.4
92.5°	23.6	63.7	103.9	113.9	160.2	221.8	252.7	221.5	159.0	112.2	107.7
95°	56.7	130.2	203.7	222.0	394.2	623.9	738.7	659.1	500.1	380.9	367.3
97.5°	98.0	162.8	227.7	243.9	531.1	913.9	1105.4	1055.2	954.6	879.3	853.6
100°	129.9	188.7	247.4	262.1	580.8	1005.7	1218.2	1221.8	1229.2	1234.7	1204.1
102.5°	157.1	211.9	266.7	280.5	603.7	1034.6	1250.1	1314.1	1442.1	1538.2	1512.0
105°	203.1	249.5	296.0	307.6	620.6	1037.9	1246.6	1390.1	1677.2	1892.5	1878.4
107.5°	250.4	293.7	337.0	347.8	623.8	991.8	1175.7	1376.0	1776.5	2076.8	2080.3
110°	282.3	321.4	360.5	370.3	619.0	950.8	1116.7	1340.5	1788.2	2124.0	2138.7

TEST NUMBER: P934580

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	313.5	350.8	388.0	397.4	619.2	915.0	1062.9	1292.0	1750.2	2093.9	2116.5
115°	360.8	395.2	429.6	438.2	625.0	874.0	998.5	1219.2	1660.6	1991.7	2023.1
117.5°	407.4	438.6	469.9	477.7	636.5	848.3	954.2	1153.4	1551.8	1850.6	1885.3
120°	434.6	464.0	493.4	500.7	646.0	839.7	936.6	1118.6	1482.5	1755.6	1789.3
122.5°	461.2	490.9	520.5	527.9	659.6	835.1	922.9	1086.8	1414.6	1660.5	1693.7
125°	501.9	529.0	556.0	562.8	678.0	831.4	908.2	1047.4	1325.8	1534.7	1565.3
127.5°	535.0	562.3	589.6	596.4	696.2	829.2	895.8	1015.4	1254.4	1433.7	1459.6
130°	552.8	582.2	611.5	618.8	709.6	830.6	891.1	997.5	1210.4	1369.9	1393.8
132.5°	571.0	600.4	629.8	637.2	720.5	831.4	886.9	982.2	1172.7	1315.6	1337.0
135°	598.2	625.0	651.7	658.4	732.2	830.7	879.8	959.7	1119.3	1238.9	1257.4
137.5°	625.9	652.5	679.0	685.6	750.0	835.8	878.7	946.1	1081.1	1182.2	1197.3
140°	648.9	673.4	697.7	703.8	760.8	836.6	874.5	932.7	1049.4	1136.7	1150.9
142.5°	666.7	689.2	711.9	717.5	769.8	839.6	874.5	925.7	1028.1	1104.8	1117.0
145°	693.8	713.5	733.2	738.1	781.7	839.6	868.7	910.5	994.3	1057.0	1066.2
147.5°	721.0	740.1	759.3	764.1	799.0	845.5	868.7	901.6	967.5	1016.9	1024.5
150°	738.7	756.0	773.4	777.7	808.0	848.4	868.7	896.5	952.0	993.8	1000.0
152.5°	757.0	770.1	783.3	786.5	813.9	850.4	868.7	892.4	939.9	975.5	980.2
155°	784.2	793.9	803.6	806.0	826.9	854.7	868.7	887.6	925.3	953.7	956.7
157.5°	804.3	813.8	823.1	825.5	839.9	859.1	868.7	883.4	912.7	934.8	937.0
160°	817.9	825.2	832.6	834.4	845.8	861.0	868.7	881.3	906.4	925.3	926.5
162.5°	831.4	837.0	842.5	843.8	852.1	863.1	868.7	879.3	900.5	916.4	917.6
165°	846.2	851.2	856.2	857.4	861.1	866.2	868.7	876.3	891.5	902.9	904.1
167.5°	859.8	862.1	864.5	865.0	868.2	872.4	874.5	879.5	889.5	896.9	897.5
170°	868.7	871.0	873.3	873.9	874.1	874.4	874.5	879.5	889.5	896.9	896.9
172.5°	873.3	873.8	874.4	874.5	874.5	874.5	874.5	878.4	886.3	892.3	891.8
175°	879.8	879.8	879.8	879.8	878.0	875.6	874.5	877.0	882.0	885.8	885.8
177.5°	879.8	879.8	879.8	879.8	878.5	876.7	875.7	877.7	881.7	884.6	884.0
180°	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8

TEST NUMBER: P934580

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5
2.5°	5255.4	5240.8	5255.4	5245.7	5250.6	5236.0	5192.3	5177.8	5192.3	5206.9	5206.9
5°	5318.4	5308.7	5318.4	5318.4	5313.6	5303.9	5255.4	5245.7	5255.4	5260.2	5250.6
7.5°	5337.8	5323.3	5337.8	5328.1	5328.1	5318.4	5270.0	5260.2	5265.1	5279.6	5265.1
10°	5337.8	5323.3	5337.8	5333.0	5328.1	5318.4	5270.0	5250.6	5250.6	5265.1	5250.6
12.5°	5313.6	5303.9	5313.6	5303.9	5303.9	5294.1	5245.7	5226.3	5231.1	5236.0	5216.6
15°	5274.8	5260.2	5274.8	5265.1	5270.0	5255.4	5202.1	5182.7	5182.7	5192.3	5158.4
17.5°	5216.6	5197.2	5216.6	5211.7	5206.9	5197.2	5148.7	5129.3	5124.5	5129.3	5105.1
20°	5148.7	5134.2	5148.7	5143.9	5143.9	5124.5	5076.0	5051.8	5051.8	5051.8	5027.5
22.5°	5042.1	5027.5	5042.1	5051.8	5051.8	5046.9	5003.2	4969.3	4959.7	4959.7	4930.6
25°	4920.8	4906.3	4920.8	4920.8	4916.1	4920.8	4906.3	4886.9	4872.4	4857.9	4828.8
27.5°	4804.5	4794.9	4804.5	4794.9	4804.5	4790.0	4785.1	4780.3	4760.9	4746.3	4707.6
30°	4688.2	4678.4	4688.2	4678.4	4668.8	4659.1	4634.8	4625.2	4644.5	4634.8	4571.8
32.5°	4542.7	4533.0	4542.7	4542.7	4533.0	4533.0	4494.2	4479.7	4484.6	4513.6	4455.5
35°	4392.4	4377.9	4392.4	4387.6	4392.4	4377.9	4353.7	4348.8	4329.4	4363.3	4319.7
37.5°	4217.9	4203.3	4217.9	4217.9	4217.9	4227.6	4208.2	4193.7	4164.6	4208.2	4174.3
40°	4038.5	4019.1	4038.5	4033.6	4038.5	4048.2	4038.5	4028.9	3999.7	4033.6	4004.6
42.5°	3834.9	3830.0	3834.9	3839.8	3839.8	3859.2	3873.7	3854.3	3844.5	3820.4	3839.8
45°	3616.7	3607.0	3616.7	3626.4	3631.3	3640.9	3684.6	3684.6	3670.1	3631.3	3660.3
47.5°	3384.0	3359.8	3384.0	3413.1	3413.1	3427.7	3471.2	3505.2	3481.0	3432.5	3447.1
50°	3136.8	3141.6	3136.8	3156.2	3156.2	3209.5	3243.4	3277.4	3301.6	3243.4	3175.6
52.5°	2894.3	2889.5	2894.3	2908.9	2928.3	2952.5	3010.7	3044.6	3083.4	3049.5	2942.8
55°	2651.9	2661.7	2651.9	2656.8	2666.5	2681.1	2768.3	2802.3	2874.9	2831.3	2719.8
57.5°	2409.6	2394.9	2409.6	2419.2	2424.1	2438.6	2511.4	2574.4	2618.0	2622.8	2487.1
60°	2128.3	2108.9	2128.3	2172.0	2181.7	2191.3	2259.2	2317.4	2356.2	2370.8	2230.1
62.5°	1881.1	1847.2	1881.1	1910.2	1929.6	1953.8	2002.3	2089.5	2123.4	2128.3	1929.6
65°	1619.3	1604.8	1619.3	1677.5	1682.3	1711.4	1764.7	1827.8	1900.4	1890.8	1604.8
67.5°	1381.7	1381.7	1381.7	1420.5	1449.6	1464.1	1532.0	1561.1	1653.2	1662.9	1338.1
70°	1163.6	1158.7	1163.6	1192.6	1212.0	1246.0	1309.0	1342.9	1415.7	1439.9	1086.0
72.5°	955.1	950.2	955.1	979.4	998.7	1027.8	1081.2	1119.9	1183.0	1212.0	843.6
75°	770.9	761.1	770.9	790.3	785.4	824.2	867.8	906.6	964.7	984.1	625.4
77.5°	591.4	591.4	591.4	610.9	610.9	649.7	669.1	717.5	751.5	780.5	460.6
80°	441.2	436.3	441.2	446.0	446.0	465.5	499.4	533.3	562.4	562.4	315.2
82.5°	310.3	300.5	310.3	310.3	310.3	320.0	339.4	349.1	368.4	383.1	198.7
85°	194.0	194.0	194.0	198.7	194.0	203.6	208.5	218.1	218.1	208.5	121.2
87.5°	126.1	121.2	126.1	121.2	121.2	116.3	116.3	116.3	111.5	106.7	67.9
90°	22.4	22.4	22.4	22.4	22.4	29.9	39.9	44.9	38.6	26.0	16.5
92.5°	89.9	72.0	89.9	107.7	112.2	159.0	221.5	252.7	221.8	160.2	113.9
95°	313.2	259.2	313.2	367.3	380.9	500.1	659.1	738.7	623.9	394.2	222.0
97.5°	750.6	647.8	750.6	853.6	879.3	954.6	1055.2	1105.4	913.9	531.1	243.9
100°	1081.5	959.0	1081.5	1204.1	1234.7	1229.2	1221.8	1218.2	1005.7	580.8	262.1
102.5°	1407.0	1302.0	1407.0	1512.0	1538.2	1442.1	1314.1	1250.1	1034.6	603.7	280.5
105°	1822.0	1765.6	1822.0	1878.4	1892.5	1677.2	1390.1	1246.6	1037.9	620.6	307.6
107.5°	2093.8	2107.5	2093.8	2080.3	2076.8	1776.5	1376.0	1175.7	991.8	623.8	347.8
110°	2197.5	2256.3	2197.5	2138.7	2124.0	1788.2	1340.5	1116.7	950.8	619.0	370.3

TEST NUMBER: P934580

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	2206.8	2297.1	2206.8	2116.5	2093.9	1750.2	1292.0	1062.9	915.0	619.2	397.4
115°	2148.3	2273.5	2148.3	2023.1	1991.7	1660.6	1219.2	998.5	874.0	625.0	438.2
117.5°	2024.1	2163.0	2024.1	1885.3	1850.6	1551.8	1153.4	954.2	848.3	636.5	477.7
120°	1924.2	2059.1	1924.2	1789.3	1755.6	1482.5	1118.6	936.6	839.7	646.0	500.7
122.5°	1826.8	1959.9	1826.8	1693.7	1660.5	1414.6	1086.8	922.9	835.1	659.6	527.9
125°	1687.9	1810.5	1687.9	1565.3	1534.7	1325.8	1047.4	908.2	831.4	678.0	562.8
127.5°	1563.0	1666.4	1563.0	1459.6	1433.7	1254.4	1015.4	895.8	829.2	696.2	596.4
130°	1489.4	1584.9	1489.4	1393.8	1369.9	1210.4	997.5	891.1	830.6	709.6	618.8
132.5°	1422.6	1508.1	1422.6	1337.0	1315.6	1172.7	982.2	886.9	831.4	720.5	637.2
135°	1331.1	1404.8	1331.1	1257.4	1238.9	1119.3	959.7	879.8	830.7	732.2	658.4
137.5°	1257.6	1318.0	1257.6	1197.3	1182.2	1081.1	946.1	878.7	835.8	750.0	685.6
140°	1207.2	1263.7	1207.2	1150.9	1136.7	1049.4	932.7	874.5	836.6	760.8	703.8
142.5°	1165.6	1214.1	1165.6	1117.0	1104.8	1028.1	925.7	874.5	839.6	769.8	717.5
145°	1102.9	1139.7	1102.9	1066.2	1057.0	994.3	910.5	868.7	839.6	781.7	738.1
147.5°	1054.9	1085.4	1054.9	1024.5	1016.9	967.5	901.6	868.7	845.5	799.0	764.1
150°	1024.6	1049.4	1024.6	1000.0	993.8	952.0	896.5	868.7	848.4	808.0	777.7
152.5°	998.8	1017.5	998.8	980.2	975.5	939.9	892.4	868.7	850.4	813.9	786.5
155°	969.1	981.5	969.1	956.7	953.7	925.3	887.6	868.7	854.7	826.9	806.0
157.5°	945.5	954.2	945.5	937.0	934.8	912.7	883.4	868.7	859.1	839.9	825.5
160°	931.6	936.6	931.6	926.5	925.3	906.4	881.3	868.7	861.0	845.8	834.4
162.5°	922.3	927.1	922.3	917.6	916.4	900.5	879.3	868.7	863.1	852.1	843.8
165°	909.2	914.1	909.2	904.1	902.9	891.5	876.3	868.7	866.2	861.1	857.4
167.5°	899.6	901.7	899.6	897.5	896.9	889.5	879.5	874.5	872.4	868.2	865.0
170°	896.9	896.9	896.9	896.9	896.9	889.5	879.5	874.5	874.4	874.1	873.9
172.5°	890.0	888.2	890.0	891.8	892.3	886.3	878.4	874.5	874.5	874.5	874.5
175°	885.8	885.8	885.8	885.8	885.8	882.0	877.0	874.5	875.6	878.0	879.8
177.5°	881.9	879.8	881.9	884.0	884.6	881.7	877.7	875.7	876.7	878.5	879.8
180°	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8

TEST NUMBER: P934580

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5
2.5°	5197.2	5168.2	5168.2	5119.7	5100.3	5085.8	5061.5	4988.7	4969.3	4950.0	4979.1
5°	5240.8	5187.6	5148.7	5061.5	4988.7	4959.7	4867.5	4693.0	4576.6	4489.4	4440.9
7.5°	5250.6	5182.7	5109.9	4974.2	4799.6	4722.1	4440.9	4120.9	4033.6	3956.1	3907.6
10°	5240.8	5163.3	5061.5	4857.9	4445.7	4310.0	4028.9	3820.4	3767.0	3752.5	3767.0
12.5°	5206.9	5134.2	4993.6	4654.2	4077.3	3985.2	3820.4	3699.1	3689.5	3713.7	3844.5
15°	5148.7	5080.9	4916.1	4382.7	3873.7	3805.8	3689.5	3645.8	3699.1	3868.8	4261.5
17.5°	5090.5	5013.0	4809.4	4116.0	3718.6	3670.1	3587.6	3674.9	3975.5	4203.3	4334.3
20°	5013.0	4920.8	4688.2	3922.2	3607.0	3563.4	3524.6	3917.3	4145.2	4227.6	4300.3
22.5°	4920.8	4823.9	4523.4	3786.4	3490.7	3456.7	3481.0	4053.0	4145.2	4203.3	4266.4
25°	4799.6	4717.2	4329.4	3679.7	3398.6	3359.8	3451.8	4038.5	4091.8	4106.4	4232.5
27.5°	4688.2	4581.5	4125.8	3582.8	3287.0	3272.5	3476.1	3975.5	4014.2	4028.9	4164.6
30°	4552.4	4392.4	3897.9	3481.0	3170.7	3165.8	3481.0	3897.9	3888.2	3927.0	4062.8
32.5°	4411.8	4111.3	3640.9	3354.9	3059.2	3054.4	3447.1	3781.5	3771.9	3825.2	3927.0
35°	4280.9	3893.1	3291.9	3209.5	2918.6	2923.4	3364.7	3645.8	3650.7	3699.1	3762.1
37.5°	4145.2	3704.0	2908.9	3049.5	2782.9	2782.9	3253.1	3519.7	3510.1	3524.6	3611.9
40°	3985.2	3408.2	2569.5	2841.0	2656.8	2642.2	3117.4	3384.0	3350.0	3345.3	3466.5
42.5°	3815.5	3083.4	2317.4	2564.7	2511.4	2492.0	2952.5	3219.2	3156.2	3170.7	3325.8
45°	3631.3	2996.1	2123.4	2167.1	2361.0	2346.5	2773.1	3030.1	2986.5	3025.2	3185.2
47.5°	3447.1	2821.6	2060.5	1798.6	2201.1	2196.2	2574.4	2845.9	2821.6	2860.4	3030.1
50°	3195.0	2627.7	2055.6	1541.8	2021.6	2041.0	2336.8	2666.5	2666.5	2700.5	2879.8
52.5°	2870.1	2390.2	1866.5	1396.3	1813.2	1871.4	2128.3	2511.4	2521.0	2555.0	2715.0
55°	2574.4	2142.9	1730.7	1284.8	1565.9	1692.0	1924.7	2351.3	2370.8	2404.7	2550.1
57.5°	2302.9	1784.1	1701.7	1153.8	1338.1	1459.3	1745.4	2196.2	2206.0	2235.0	2375.6
60°	2012.0	1289.6	1561.1	1013.3	1139.3	1231.5	1580.5	2012.0	2045.9	2065.3	2186.5
62.5°	1682.3	935.7	1415.7	916.3	1042.4	1061.8	1444.7	1837.4	1881.1	1895.6	1968.4
65°	1197.5	785.4	1202.3	833.9	940.6	945.4	1299.3	1658.1	1696.8	1721.1	1774.4
67.5°	809.6	639.9	916.3	756.3	862.9	867.8	1158.7	1449.6	1502.9	1522.4	1556.3
70°	562.4	426.6	678.7	673.8	775.7	785.4	1008.4	1260.5	1309.0	1323.5	1342.9
72.5°	412.1	344.2	562.4	606.0	683.6	693.3	853.3	1047.2	1095.7	1110.2	1119.9
75°	315.2	363.6	455.7	528.4	581.8	586.7	698.1	853.3	887.2	896.9	901.7
77.5°	252.1	339.4	334.5	426.6	475.1	465.5	547.9	659.3	688.5	688.5	688.5
80°	189.1	266.6	252.1	305.4	349.1	339.4	392.7	470.2	480.0	489.6	484.9
82.5°	140.6	169.7	169.7	194.0	232.7	223.0	261.8	305.4	305.4	305.4	315.2
85°	87.3	96.9	77.5	101.8	130.9	126.1	145.4	164.8	169.7	169.7	160.0
87.5°	53.3	43.6	24.3	38.8	58.2	58.2	67.9	72.7	67.9	67.9	67.9
90°	15.4	10.6	5.9	10.6	15.4	16.5	26.0	38.6	44.9	39.9	29.9
92.5°	103.9	63.7	23.6	63.7	103.9	113.9	160.2	221.8	252.7	221.5	159.0
95°	203.7	130.2	56.7	130.2	203.7	222.0	394.2	623.9	738.7	659.1	500.1
97.5°	227.7	162.8	98.0	162.8	227.7	243.9	531.1	913.9	1105.4	1055.2	954.6
100°	247.4	188.7	129.9	188.7	247.4	262.1	580.8	1005.7	1218.2	1221.8	1229.2
102.5°	266.7	211.9	157.1	211.9	266.7	280.5	603.7	1034.6	1250.1	1314.1	1442.1
105°	296.0	249.5	203.1	249.5	296.0	307.6	620.6	1037.9	1246.6	1390.1	1677.2
107.5°	337.0	293.7	250.4	293.7	337.0	347.8	623.8	991.8	1175.7	1376.0	1776.5
110°	360.5	321.4	282.3	321.4	360.5	370.3	619.0	950.8	1116.7	1340.5	1788.2

TEST NUMBER: P934580

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	388.0	350.8	313.5	350.8	388.0	397.4	619.2	915.0	1062.9	1292.0	1750.2
115°	429.6	395.2	360.8	395.2	429.6	438.2	625.0	874.0	998.5	1219.2	1660.6
117.5°	469.9	438.6	407.4	438.6	469.9	477.7	636.5	848.3	954.2	1153.4	1551.8
120°	493.4	464.0	434.6	464.0	493.4	500.7	646.0	839.7	936.6	1118.6	1482.5
122.5°	520.5	490.9	461.2	490.9	520.5	527.9	659.6	835.1	922.9	1086.8	1414.6
125°	556.0	529.0	501.9	529.0	556.0	562.8	678.0	831.4	908.2	1047.4	1325.8
127.5°	589.6	562.3	535.0	562.3	589.6	596.4	696.2	829.2	895.8	1015.4	1254.4
130°	611.5	582.2	552.8	582.2	611.5	618.8	709.6	830.6	891.1	997.5	1210.4
132.5°	629.8	600.4	571.0	600.4	629.8	637.2	720.5	831.4	886.9	982.2	1172.7
135°	651.7	625.0	598.2	625.0	651.7	658.4	732.2	830.7	879.8	959.7	1119.3
137.5°	679.0	652.5	625.9	652.5	679.0	685.6	750.0	835.8	878.7	946.1	1081.1
140°	697.7	673.4	648.9	673.4	697.7	703.8	760.8	836.6	874.5	932.7	1049.4
142.5°	711.9	689.2	666.7	689.2	711.9	717.5	769.8	839.6	874.5	925.7	1028.1
145°	733.2	713.5	693.8	713.5	733.2	738.1	781.7	839.6	868.7	910.5	994.3
147.5°	759.3	740.1	721.0	740.1	759.3	764.1	799.0	845.5	868.7	901.6	967.5
150°	773.4	756.0	738.7	756.0	773.4	777.7	808.0	848.4	868.7	896.5	952.0
152.5°	783.3	770.1	757.0	770.1	783.3	786.5	813.9	850.4	868.7	892.4	939.9
155°	803.6	793.9	784.2	793.9	803.6	806.0	826.9	854.7	868.7	887.6	925.3
157.5°	823.1	813.8	804.3	813.8	823.1	825.5	839.9	859.1	868.7	883.4	912.7
160°	832.6	825.2	817.9	825.2	832.6	834.4	845.8	861.0	868.7	881.3	906.4
162.5°	842.5	837.0	831.4	837.0	842.5	843.8	852.1	863.1	868.7	879.3	900.5
165°	856.2	851.2	846.2	851.2	856.2	857.4	861.1	866.2	868.7	876.3	891.5
167.5°	864.5	862.1	859.8	862.1	864.5	865.0	868.2	872.4	874.5	879.5	889.5
170°	873.3	871.0	868.7	871.0	873.3	873.9	874.1	874.4	874.5	879.5	889.5
172.5°	874.4	873.8	873.3	873.8	874.4	874.5	874.5	874.5	874.5	878.4	886.3
175°	879.8	879.8	879.8	879.8	879.8	879.8	878.0	875.6	874.5	877.0	882.0
177.5°	879.8	879.8	879.8	879.8	879.8	879.8	878.5	876.7	875.7	877.7	881.7
180°	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8

TEST NUMBER: P934580

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5
2.5°	4945.1	4930.6	4950.0	4896.7	4950.0	4930.6	4945.1	4979.1	4950.0	4969.3	4988.7
5°	4339.1	4314.9	4237.2	4174.3	4237.2	4314.9	4339.1	4440.9	4489.4	4576.6	4693.0
7.5°	3878.5	3859.2	3839.8	3801.0	3839.8	3859.2	3878.5	3907.6	3956.1	4033.6	4120.9
10°	3776.7	3781.5	3810.6	3805.8	3810.6	3781.5	3776.7	3767.0	3752.5	3767.0	3820.4
12.5°	4038.5	4082.1	4242.1	4232.5	4242.1	4082.1	4038.5	3844.5	3713.7	3689.5	3699.1
15°	4339.1	4353.7	4387.6	4392.4	4387.6	4353.7	4339.1	4261.5	3868.8	3699.1	3645.8
17.5°	4368.2	4373.0	4397.3	4397.3	4397.3	4373.0	4368.2	4334.3	4203.3	3975.5	3674.9
20°	4343.9	4353.7	4402.2	4411.8	4402.2	4353.7	4343.9	4300.3	4227.6	4145.2	3917.3
22.5°	4334.3	4353.7	4392.4	4387.6	4392.4	4353.7	4334.3	4266.4	4203.3	4145.2	4053.0
25°	4285.8	4285.8	4290.6	4295.5	4290.6	4285.8	4285.8	4232.5	4106.4	4091.8	4038.5
27.5°	4184.0	4193.7	4222.7	4217.9	4222.7	4193.7	4184.0	4164.6	4028.9	4014.2	3975.5
30°	4091.8	4082.1	4057.9	4038.5	4057.9	4082.1	4091.8	4062.8	3927.0	3888.2	3897.9
32.5°	3936.7	3912.4	3888.2	3873.7	3888.2	3912.4	3936.7	3927.0	3825.2	3771.9	3781.5
35°	3752.5	3757.4	3752.5	3738.0	3752.5	3757.4	3752.5	3762.1	3699.1	3650.7	3645.8
37.5°	3621.6	3631.3	3626.4	3607.0	3626.4	3631.3	3621.6	3611.9	3524.6	3510.1	3519.7
40°	3485.8	3490.7	3485.8	3471.2	3485.8	3490.7	3485.8	3466.5	3345.3	3350.0	3384.0
42.5°	3354.9	3350.0	3335.5	3325.8	3335.5	3350.0	3354.9	3325.8	3170.7	3156.2	3219.2
45°	3204.6	3209.5	3180.3	3165.8	3180.3	3209.5	3204.6	3185.2	3025.2	2986.5	3030.1
47.5°	3054.4	3054.4	3030.1	3015.5	3030.1	3054.4	3054.4	3030.1	2860.4	2821.6	2845.9
50°	2894.3	2889.5	2855.5	2850.7	2855.5	2889.5	2894.3	2879.8	2700.5	2666.5	2666.5
52.5°	2710.1	2710.1	2715.0	2724.6	2715.0	2710.1	2710.1	2715.0	2555.0	2521.0	2511.4
55°	2550.1	2555.0	2588.9	2598.7	2588.9	2555.0	2550.1	2550.1	2404.7	2370.8	2351.3
57.5°	2385.3	2385.3	2409.6	2409.6	2409.6	2385.3	2385.3	2375.6	2235.0	2206.0	2196.2
60°	2196.2	2206.0	2225.3	2220.5	2225.3	2206.0	2196.2	2186.5	2065.3	2045.9	2012.0
62.5°	1997.5	2007.1	2012.0	2002.3	2012.0	2007.1	1997.5	1968.4	1895.6	1881.1	1837.4
65°	1789.0	1798.6	1803.5	1793.8	1803.5	1798.6	1789.0	1774.4	1721.1	1696.8	1658.1
67.5°	1575.7	1570.8	1565.9	1585.3	1565.9	1570.8	1575.7	1556.3	1522.4	1502.9	1449.6
70°	1357.4	1357.4	1352.7	1362.3	1352.7	1357.4	1357.4	1342.9	1323.5	1309.0	1260.5
72.5°	1124.8	1119.9	1139.3	1124.8	1139.3	1119.9	1124.8	1119.9	1110.2	1095.7	1047.2
75°	896.9	906.6	896.9	911.5	896.9	906.6	896.9	901.7	896.9	887.2	853.3
77.5°	683.6	693.3	683.6	683.6	683.6	693.3	683.6	688.5	688.5	688.5	659.3
80°	484.9	480.0	480.0	475.1	480.0	480.0	484.9	484.9	489.6	480.0	470.2
82.5°	310.3	305.4	305.4	315.2	305.4	305.4	310.3	315.2	305.4	305.4	305.4
85°	169.7	174.6	164.8	164.8	164.8	174.6	169.7	160.0	169.7	169.7	164.8
87.5°	63.0	58.2	58.2	58.2	58.2	58.2	63.0	67.9	67.9	67.9	72.7
90°	22.4	22.4	22.4	22.4	22.4	22.4	22.4	29.9	39.9	44.9	38.6
92.5°	112.2	107.7	89.9	72.0	89.9	107.7	112.2	159.0	221.5	252.7	221.8
95°	380.9	367.3	313.2	259.2	313.2	367.3	380.9	500.1	659.1	738.7	623.9
97.5°	879.3	853.6	750.6	647.8	750.6	853.6	879.3	954.6	1055.2	1105.4	913.9
100°	1234.7	1204.1	1081.5	959.0	1081.5	1204.1	1234.7	1229.2	1221.8	1218.2	1005.7
102.5°	1538.2	1512.0	1407.0	1302.0	1407.0	1512.0	1538.2	1442.1	1314.1	1250.1	1034.6
105°	1892.5	1878.4	1822.0	1765.6	1822.0	1878.4	1892.5	1677.2	1390.1	1246.6	1037.9
107.5°	2076.8	2080.3	2093.8	2107.5	2093.8	2080.3	2076.8	1776.5	1376.0	1175.7	991.8
110°	2124.0	2138.7	2197.5	2256.3	2197.5	2138.7	2124.0	1788.2	1340.5	1116.7	950.8

TEST NUMBER: P934580

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	2093.9	2116.5	2206.8	2297.1	2206.8	2116.5	2093.9	1750.2	1292.0	1062.9	915.0
115°	1991.7	2023.1	2148.3	2273.5	2148.3	2023.1	1991.7	1660.6	1219.2	998.5	874.0
117.5°	1850.6	1885.3	2024.1	2163.0	2024.1	1885.3	1850.6	1551.8	1153.4	954.2	848.3
120°	1755.6	1789.3	1924.2	2059.1	1924.2	1789.3	1755.6	1482.5	1118.6	936.6	839.7
122.5°	1660.5	1693.7	1826.8	1959.9	1826.8	1693.7	1660.5	1414.6	1086.8	922.9	835.1
125°	1534.7	1565.3	1687.9	1810.5	1687.9	1565.3	1534.7	1325.8	1047.4	908.2	831.4
127.5°	1433.7	1459.6	1563.0	1666.4	1563.0	1459.6	1433.7	1254.4	1015.4	895.8	829.2
130°	1369.9	1393.8	1489.4	1584.9	1489.4	1393.8	1369.9	1210.4	997.5	891.1	830.6
132.5°	1315.6	1337.0	1422.6	1508.1	1422.6	1337.0	1315.6	1172.7	982.2	886.9	831.4
135°	1238.9	1257.4	1331.1	1404.8	1331.1	1257.4	1238.9	1119.3	959.7	879.8	830.7
137.5°	1182.2	1197.3	1257.6	1318.0	1257.6	1197.3	1182.2	1081.1	946.1	878.7	835.8
140°	1136.7	1150.9	1207.2	1263.7	1207.2	1150.9	1136.7	1049.4	932.7	874.5	836.6
142.5°	1104.8	1117.0	1165.6	1214.1	1165.6	1117.0	1104.8	1028.1	925.7	874.5	839.6
145°	1057.0	1066.2	1102.9	1139.7	1102.9	1066.2	1057.0	994.3	910.5	868.7	839.6
147.5°	1016.9	1024.5	1054.9	1085.4	1054.9	1024.5	1016.9	967.5	901.6	868.7	845.5
150°	993.8	1000.0	1024.6	1049.4	1024.6	1000.0	993.8	952.0	896.5	868.7	848.4
152.5°	975.5	980.2	998.8	1017.5	998.8	980.2	975.5	939.9	892.4	868.7	850.4
155°	953.7	956.7	969.1	981.5	969.1	956.7	953.7	925.3	887.6	868.7	854.7
157.5°	934.8	937.0	945.5	954.2	945.5	937.0	934.8	912.7	883.4	868.7	859.1
160°	925.3	926.5	931.6	936.6	931.6	926.5	925.3	906.4	881.3	868.7	861.0
162.5°	916.4	917.6	922.3	927.1	922.3	917.6	916.4	900.5	879.3	868.7	863.1
165°	902.9	904.1	909.2	914.1	909.2	904.1	902.9	891.5	876.3	868.7	866.2
167.5°	896.9	897.5	899.6	901.7	899.6	897.5	896.9	889.5	879.5	874.5	872.4
170°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	889.5	879.5	874.5	874.4
172.5°	892.3	891.8	890.0	888.2	890.0	891.8	892.3	886.3	878.4	874.5	874.5
175°	885.8	885.8	885.8	885.8	885.8	885.8	885.8	882.0	877.0	874.5	875.6
177.5°	884.6	884.0	881.9	879.8	881.9	884.0	884.6	881.7	877.7	875.7	876.7
180°	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8

TEST NUMBER: P934580

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	5124.5	5124.5	5124.5	5124.5	5124.5
2.5°	5061.5	5085.8	5100.3	5119.7	5168.2
5°	4867.5	4959.7	4988.7	5061.5	5148.7
7.5°	4440.9	4722.1	4799.6	4974.2	5109.9
10°	4028.9	4310.0	4445.7	4857.9	5061.5
12.5°	3820.4	3985.2	4077.3	4654.2	4993.6
15°	3689.5	3805.8	3873.7	4382.7	4916.1
17.5°	3587.6	3670.1	3718.6	4116.0	4809.4
20°	3524.6	3563.4	3607.0	3922.2	4688.2
22.5°	3481.0	3456.7	3490.7	3786.4	4523.4
25°	3451.8	3359.8	3398.6	3679.7	4329.4
27.5°	3476.1	3272.5	3287.0	3582.8	4125.8
30°	3481.0	3165.8	3170.7	3481.0	3897.9
32.5°	3447.1	3054.4	3059.2	3354.9	3640.9
35°	3364.7	2923.4	2918.6	3209.5	3291.9
37.5°	3253.1	2782.9	2782.9	3049.5	2908.9
40°	3117.4	2642.2	2656.8	2841.0	2569.5
42.5°	2952.5	2492.0	2511.4	2564.7	2317.4
45°	2773.1	2346.5	2361.0	2167.1	2123.4
47.5°	2574.4	2196.2	2201.1	1798.6	2060.5
50°	2336.8	2041.0	2021.6	1541.8	2055.6
52.5°	2128.3	1871.4	1813.2	1396.3	1866.5
55°	1924.7	1692.0	1565.9	1284.8	1730.7
57.5°	1745.4	1459.3	1338.1	1153.8	1701.7
60°	1580.5	1231.5	1139.3	1013.3	1561.1
62.5°	1444.7	1061.8	1042.4	916.3	1415.7
65°	1299.3	945.4	940.6	833.9	1202.3
67.5°	1158.7	867.8	862.9	756.3	916.3
70°	1008.4	785.4	775.7	673.8	678.7
72.5°	853.3	693.3	683.6	606.0	562.4
75°	698.1	586.7	581.8	528.4	455.7
77.5°	547.9	465.5	475.1	426.6	334.5
80°	392.7	339.4	349.1	305.4	252.1
82.5°	261.8	223.0	232.7	194.0	169.7
85°	145.4	126.1	130.9	101.8	77.5
87.5°	67.9	58.2	58.2	38.8	24.3
90°	26.0	16.5	15.4	10.6	5.9
92.5°	160.2	113.9	103.9	63.7	23.6
95°	394.2	222.0	203.7	130.2	56.7
97.5°	531.1	243.9	227.7	162.8	98.0
100°	580.8	262.1	247.4	188.7	129.9
102.5°	603.7	280.5	266.7	211.9	157.1
105°	620.6	307.6	296.0	249.5	203.1
107.5°	623.8	347.8	337.0	293.7	250.4
110°	619.0	370.3	360.5	321.4	282.3



TEST NUMBER: P934580

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	619.2	397.4	388.0	350.8	313.5
115°	625.0	438.2	429.6	395.2	360.8
117.5°	636.5	477.7	469.9	438.6	407.4
120°	646.0	500.7	493.4	464.0	434.6
122.5°	659.6	527.9	520.5	490.9	461.2
125°	678.0	562.8	556.0	529.0	501.9
127.5°	696.2	596.4	589.6	562.3	535.0
130°	709.6	618.8	611.5	582.2	552.8
132.5°	720.5	637.2	629.8	600.4	571.0
135°	732.2	658.4	651.7	625.0	598.2
137.5°	750.0	685.6	679.0	652.5	625.9
140°	760.8	703.8	697.7	673.4	648.9
142.5°	769.8	717.5	711.9	689.2	666.7
145°	781.7	738.1	733.2	713.5	693.8
147.5°	799.0	764.1	759.3	740.1	721.0
150°	808.0	777.7	773.4	756.0	738.7
152.5°	813.9	786.5	783.3	770.1	757.0
155°	826.9	806.0	803.6	793.9	784.2
157.5°	839.9	825.5	823.1	813.8	804.3
160°	845.8	834.4	832.6	825.2	817.9
162.5°	852.1	843.8	842.5	837.0	831.4
165°	861.1	857.4	856.2	851.2	846.2
167.5°	868.2	865.0	864.5	862.1	859.8
170°	874.1	873.9	873.3	871.0	868.7
172.5°	874.5	874.5	874.4	873.8	873.3
175°	878.0	879.8	879.8	879.8	879.8
177.5°	878.5	879.8	879.8	879.8	879.8
180°	879.8	879.8	879.8	879.8	879.8

TEST NUMBER: P934580

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.08	17.15	16.84	17.94	18.90	18.93	20.01	19.69	20.79	21.75
	3H	16.57	17.54	17.35	18.33	19.32	20.30	21.26	21.08	22.06	23.04
	4H	16.77	17.68	17.57	18.49	19.48	20.76	21.67	21.55	22.47	23.47
	6H	16.90	17.74	17.71	18.56	19.57	21.06	21.90	21.87	22.71	23.72
	8H	16.91	17.71	17.73	18.54	19.55	21.14	21.94	21.96	22.77	23.79
	12H	16.89	17.65	17.71	18.48	19.51	21.19	21.95	22.02	22.78	23.82
4H	2H	17.14	18.05	17.94	18.86	19.85	19.36	20.28	20.16	21.08	22.08
	3H	18.19	18.95	19.00	19.79	20.80	20.90	21.66	21.71	22.49	23.51
	4H	18.47	19.16	19.30	20.00	21.04	21.44	22.13	22.26	22.97	24.01
	6H	18.61	19.21	19.45	20.07	21.12	21.82	22.42	22.66	23.28	24.32
	8H	18.62	19.18	19.47	20.04	21.10	21.94	22.49	22.78	23.35	24.41
	12H	18.60	19.10	19.47	19.98	21.04	22.01	22.51	22.87	23.39	24.45
8H	4H	18.95	19.51	19.79	20.36	21.42	21.58	22.14	22.43	22.99	24.05
	6H	19.22	19.68	20.09	20.58	21.64	22.03	22.49	22.90	23.39	24.45
	8H	19.26	19.67	20.15	20.57	21.64	22.19	22.60	23.07	23.49	24.57
	12H	19.26	19.62	20.15	20.50	21.63	22.30	22.66	23.19	23.55	24.68
12H	4H	18.97	19.47	19.83	20.35	21.41	21.55	22.06	22.42	22.93	24.00
	6H	19.28	19.69	20.17	20.59	21.66	22.03	22.44	22.91	23.33	24.41
	8H	19.36	19.72	20.25	20.61	21.73	22.20	22.56	23.09	23.45	24.58

END OF REPORT