

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934595

Luminaire Tested: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934595
REPORT IS A COMBINATION OF REPORTS P933704 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12662.4 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 112
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934595

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K

Luminous Intensity Polar Plot



TEST NUMBER: P934595

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	65	63
2	93	86	79	74	88	81	76	71	73	68	65	65	62	59	58	56	53
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	52	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27
8	57	44	36	30	54	42	35	29	38	32	28	35	29	26	31	27	24
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21
10	49	37	30	25	47	35	28	24	32	26	22	30	25	21	27	23	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15850	15850	15850	15850
5°	15968	16000	15968	12581
10°	15862	15760	15862	11268
15°	15689	15419	15689	12875
20°	15361	15014	15361	12902
25°	14690	14425	14690	12629
30°	13822	13934	13822	12028
35°	12322	13315	12322	11369
40°	10267	12586	10267	10870
45°	9174	11732	9174	10297
50°	9746	10714	9746	9722
55°	9169	9617	9169	9389
60°	9452	8168	9452	8599
65°	8569	6752	8569	7548
70°	5935	5380	5935	6326
75°	5203	3977	5203	4763
80°	4194	2630	4194	2864
85°	2408	1393	2408	1184

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 14060 cd/sqm

TEST NUMBER: P934595

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	308.4	2.4
10°-20°	875.6	6.9
20°-30°	1353.5	10.7
30°-40°	1615.7	12.8
40°-50°	1625.2	12.8
50°-60°	1414.1	11.2
60°-70°	1002.6	7.9
70°-80°	530.5	4.2
80°-90°	134.4	1.1
90°-100°	285.9	2.3
100°-110°	751.7	5.9
110°-120°	779.4	6.2
120°-130°	625.2	4.9
130°-140°	490.6	3.9
140°-150°	376.5	3.0
150°-160°	271.2	2.1
160°-170°	165.9	1.3
170°-180°	56.1	0.4
0°-30°	2537.4	20.0
0°-40°	4153.1	32.8
0°-60°	7192.4	56.8
0°-90°	8859.9	70.0
90°-120°	1817.1	14.4
90°-150°	3309.4	26.1
90°-180°	3802.0	30.0
0°-180°	12662.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3416	3416	3416	3416	3416	
5°	3432	3539	3432	2783	3432	326
15°	3277	3507	3277	2928	3277	922
25°	2886	3271	2886	2864	2886	1325
35°	2194	2918	2194	2492	2194	1358
45°	1416	2405	1416	2110	1416	1134
55°	1154	1774	1154	1732	1154	1060
65°	802	1070	802	1196	802	766
75°	304	507	304	608	304	319
85°	52	129	52	110	52	70
90°	4	15	4	15	4	5
95°	38	173	38	173	38	42
105°	135	1177	135	1177	135	144
115°	241	1516	241	1516	241	238
125°	335	1207	335	1207	335	297
135°	399	937	399	937	399	309
145°	463	760	463	760	463	290
155°	523	654	523	654	523	240
165°	564	609	564	609	564	159
175°	587	590	587	590	587	56
180°	587	587	587	587	587	

TEST NUMBER: P934595

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2
2.5°	3445.3	3445.3	3464.6	3471.1	3471.1	3461.5	3451.8	3461.5	3490.5	3500.3	3497.0
5°	3432.4	3458.2	3493.8	3500.3	3506.7	3503.5	3497.0	3503.5	3535.8	3542.3	3545.5
7.5°	3406.5	3455.0	3500.3	3509.9	3519.7	3509.9	3506.7	3513.2	3545.5	3551.9	3551.9
10°	3374.2	3442.1	3493.8	3500.3	3509.9	3500.3	3500.3	3513.2	3545.5	3551.9	3555.2
12.5°	3328.9	3422.6	3471.1	3477.6	3490.5	3487.3	3484.1	3497.0	3529.3	3535.8	3535.8
15°	3277.3	3387.1	3432.4	3438.9	3461.5	3455.0	3455.0	3467.9	3503.5	3513.2	3509.9
17.5°	3206.1	3341.8	3393.6	3403.2	3419.5	3416.2	3419.5	3432.4	3464.6	3471.1	3474.4
20°	3125.3	3280.4	3341.8	3351.6	3367.7	3367.7	3367.7	3383.9	3416.2	3429.1	3429.1
22.5°	3015.4	3215.9	3280.4	3286.9	3306.3	3306.3	3312.8	3335.4	3364.5	3367.7	3367.7
25°	2886.2	3144.7	3199.6	3219.0	3238.4	3248.1	3257.9	3270.8	3280.4	3277.3	3280.4
27.5°	2750.4	3054.2	3125.3	3138.2	3164.1	3173.8	3186.7	3190.0	3193.2	3202.9	3196.4
30°	2598.6	2928.2	3034.8	3047.8	3089.8	3096.2	3083.3	3089.8	3105.9	3112.4	3118.8
32.5°	2427.2	2740.8	2941.1	2970.2	3009.0	2989.6	2986.4	2996.0	3021.9	3021.9	3028.4
35°	2194.5	2595.3	2853.8	2879.7	2908.7	2886.2	2899.1	2902.3	2918.5	2928.2	2925.0
37.5°	1939.2	2469.2	2763.4	2782.8	2805.4	2776.3	2795.7	2805.4	2818.3	2811.8	2811.8
40°	1713.0	2272.0	2656.7	2669.6	2689.0	2666.4	2685.7	2692.2	2698.7	2692.2	2689.0
42.5°	1544.9	2055.5	2543.5	2559.7	2546.8	2562.9	2569.4	2582.3	2572.7	2559.7	2559.7
45°	1415.6	1997.4	2420.7	2440.1	2420.7	2446.6	2456.4	2456.4	2427.2	2420.7	2417.5
47.5°	1373.6	1881.0	2297.9	2297.9	2288.3	2320.6	2336.7	2314.1	2285.0	2275.3	2275.3
50°	1370.3	1751.8	2129.8	2116.9	2162.2	2201.0	2184.8	2162.2	2139.6	2104.1	2104.1
52.5°	1244.3	1593.3	1913.3	1961.9	2032.9	2055.5	2029.7	2007.0	1968.3	1952.1	1939.2
55°	1153.8	1428.6	1716.2	1813.2	1887.5	1916.6	1868.1	1845.4	1787.3	1777.6	1771.1
57.5°	1134.4	1189.4	1535.2	1658.0	1748.5	1745.3	1716.2	1674.2	1625.7	1616.0	1612.8
60°	1040.7	859.7	1341.3	1486.7	1580.4	1570.8	1544.9	1506.1	1460.9	1454.4	1448.0
62.5°	943.7	623.8	1121.5	1286.3	1418.8	1415.6	1393.0	1334.8	1302.5	1286.3	1273.4
65°	801.5	523.6	798.3	1069.8	1260.5	1266.9	1218.5	1176.5	1140.8	1121.5	1118.3
67.5°	610.8	426.6	539.8	892.1	1108.6	1102.1	1040.7	1021.3	976.1	966.4	947.0
70°	452.5	284.4	374.9	724.0	959.9	943.7	895.2	872.7	830.7	808.0	795.0
72.5°	374.9	229.5	274.8	562.4	808.0	788.6	746.6	720.7	685.2	665.8	652.8
75°	303.8	242.4	210.1	417.0	656.1	643.2	604.4	578.5	549.4	523.6	526.8
77.5°	223.0	226.2	168.1	307.0	520.4	501.0	478.4	446.0	433.1	407.2	407.2
80°	168.1	177.7	126.1	210.1	374.9	374.9	355.5	332.9	310.3	297.4	297.4
82.5°	113.1	113.1	93.7	132.6	255.4	245.6	232.7	226.2	213.3	206.9	206.9
85°	51.7	64.7	58.2	80.8	139.0	145.4	145.4	139.0	135.7	129.3	132.6
87.5°	16.1	29.1	35.5	45.3	71.1	74.3	77.5	77.5	77.5	80.8	80.8
90°	3.9	7.1	10.2	11.0	17.3	25.7	29.9	26.5	20.0	15.0	15.0
92.5°	15.8	42.5	69.3	76.0	106.9	147.9	168.5	147.6	106.0	74.8	71.8
95°	37.8	86.8	135.8	148.0	262.8	415.9	492.5	439.5	333.5	253.9	245.0
97.5°	65.3	108.5	151.7	162.5	354.0	609.3	737.0	703.5	636.4	586.2	569.0
100°	86.6	125.8	164.9	174.8	387.3	670.5	812.1	814.6	819.5	823.1	802.7
102.5°	104.8	141.3	177.8	187.0	402.4	689.8	833.4	876.1	961.5	1025.5	1008.0
105°	135.4	166.4	197.4	205.1	413.8	692.0	831.0	926.7	1118.2	1261.7	1252.3
107.5°	166.9	195.8	224.6	231.9	415.8	661.1	783.8	917.3	1184.3	1384.6	1386.9
110°	188.1	214.2	240.4	246.9	412.8	633.8	744.4	893.7	1192.1	1416.0	1425.8

TEST NUMBER: P934595

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	209.0	233.9	258.7	264.9	412.8	610.1	708.6	861.3	1166.8	1395.9	1411.0
115°	240.6	263.5	286.4	292.1	416.7	582.7	665.7	812.9	1107.1	1327.8	1348.7
117.5°	271.6	292.4	313.2	318.5	424.4	565.6	636.1	769.0	1034.6	1233.8	1256.9
120°	289.7	309.3	329.0	333.9	430.7	559.8	624.4	745.7	988.3	1170.4	1192.8
122.5°	307.4	327.2	347.0	351.9	439.7	556.8	615.3	724.6	943.2	1107.0	1129.2
125°	334.6	352.6	370.6	375.1	451.9	554.3	605.5	698.3	883.9	1023.2	1043.6
127.5°	356.7	374.8	393.0	397.6	464.1	552.8	597.2	676.9	836.3	955.9	973.0
130°	368.4	388.0	407.7	412.6	473.0	553.7	594.0	665.0	806.9	913.3	929.2
132.5°	380.7	400.2	419.9	424.8	480.3	554.3	591.3	654.8	781.9	877.1	891.3
135°	398.8	416.7	434.4	438.9	488.1	553.7	586.6	639.8	746.1	825.9	838.2
137.5°	417.3	435.0	452.7	457.1	499.9	557.1	585.8	630.8	720.7	788.2	798.2
140°	432.6	448.9	465.2	469.3	507.2	557.7	583.0	621.9	699.5	757.8	767.2
142.5°	444.5	459.5	474.5	478.3	513.2	559.7	583.0	617.1	685.4	736.6	744.7
145°	462.6	475.7	488.9	492.1	521.1	559.8	579.1	607.0	662.9	704.7	710.8
147.5°	480.7	493.4	506.2	509.4	532.6	563.6	579.1	601.1	644.9	677.9	682.9
150°	492.5	504.0	515.6	518.5	538.7	565.6	579.1	597.6	634.8	662.6	666.7
152.5°	504.7	513.5	522.2	524.4	542.6	567.0	579.1	595.0	626.6	650.4	653.5
155°	522.8	529.3	535.8	537.4	551.3	569.8	579.1	591.7	616.8	635.7	637.8
157.5°	536.1	542.4	548.7	550.4	559.9	572.7	579.1	588.9	608.4	623.1	624.6
160°	545.2	550.2	555.0	556.3	563.9	574.1	579.1	587.5	604.2	616.8	617.7
162.5°	554.3	558.0	561.6	562.6	568.1	575.5	579.1	586.2	600.4	611.0	611.8
165°	564.1	567.5	570.7	571.6	574.1	577.4	579.1	584.2	594.3	601.9	602.8
167.5°	573.2	574.7	576.3	576.7	578.8	581.6	583.0	586.4	593.1	598.0	598.4
170°	579.1	580.6	582.3	582.6	582.7	582.9	583.0	586.4	593.1	598.0	598.0
172.5°	582.3	582.6	582.9	583.0	583.0	583.0	583.0	585.7	591.0	594.9	594.6
175°	586.6	586.6	586.6	586.6	585.4	583.8	583.0	584.7	588.0	590.5	590.5
177.5°	586.6	586.6	586.6	586.6	585.6	584.4	583.8	585.1	587.7	589.7	589.3
180°	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6

TEST NUMBER: P934595

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2
2.5°	3503.5	3493.8	3503.5	3497.0	3500.3	3490.5	3461.5	3451.8	3461.5	3471.1	3471.1
5°	3545.5	3539.0	3545.5	3545.5	3542.3	3535.8	3503.5	3497.0	3503.5	3506.7	3500.3
7.5°	3558.4	3548.7	3558.4	3551.9	3551.9	3545.5	3513.2	3506.7	3509.9	3519.7	3509.9
10°	3558.4	3548.7	3558.4	3555.2	3551.9	3545.5	3513.2	3500.3	3500.3	3509.9	3500.3
12.5°	3542.3	3535.8	3542.3	3535.8	3535.8	3529.3	3497.0	3484.1	3487.3	3490.5	3477.6
15°	3516.4	3506.7	3516.4	3509.9	3513.2	3503.5	3467.9	3455.0	3455.0	3461.5	3438.9
17.5°	3477.6	3464.6	3477.6	3474.4	3471.1	3464.6	3432.4	3419.5	3416.2	3419.5	3403.2
20°	3432.4	3422.6	3432.4	3429.1	3429.1	3416.2	3383.9	3367.7	3367.7	3367.7	3351.6
22.5°	3361.2	3351.6	3361.2	3367.7	3367.7	3364.5	3335.4	3312.8	3306.3	3306.3	3286.9
25°	3280.4	3270.8	3280.4	3280.4	3277.3	3280.4	3270.8	3257.9	3248.1	3238.4	3219.0
27.5°	3202.9	3196.4	3202.9	3196.4	3202.9	3193.2	3190.0	3186.7	3173.8	3164.1	3138.2
30°	3125.3	3118.8	3125.3	3118.8	3112.4	3105.9	3089.8	3083.3	3096.2	3089.8	3047.8
32.5°	3028.4	3021.9	3028.4	3028.4	3021.9	3021.9	2996.0	2986.4	2989.6	3009.0	2970.2
35°	2928.2	2918.5	2928.2	2925.0	2928.2	2918.5	2902.3	2899.1	2886.2	2908.7	2879.7
37.5°	2811.8	2802.2	2811.8	2811.8	2811.8	2818.3	2805.4	2795.7	2776.3	2805.4	2782.8
40°	2692.2	2679.3	2692.2	2689.0	2692.2	2698.7	2692.2	2685.7	2666.4	2689.0	2669.6
42.5°	2556.5	2553.3	2556.5	2559.7	2559.7	2572.7	2582.3	2569.4	2562.9	2546.8	2559.7
45°	2411.1	2404.6	2411.1	2417.5	2420.7	2427.2	2456.4	2456.4	2446.6	2420.7	2440.1
47.5°	2255.9	2239.8	2255.9	2275.3	2275.3	2285.0	2314.1	2336.7	2320.6	2288.3	2297.9
50°	2091.1	2094.3	2091.1	2104.1	2104.1	2139.6	2162.2	2184.8	2201.0	2162.2	2116.9
52.5°	1929.5	1926.2	1929.5	1939.2	1952.1	1968.3	2007.0	2029.7	2055.5	2032.9	1961.9
55°	1767.9	1774.4	1767.9	1771.1	1777.6	1787.3	1845.4	1868.1	1916.6	1887.5	1813.2
57.5°	1606.3	1596.6	1606.3	1612.8	1616.0	1625.7	1674.2	1716.2	1745.3	1748.5	1658.0
60°	1418.8	1406.0	1418.8	1448.0	1454.4	1460.9	1506.1	1544.9	1570.8	1580.4	1486.7
62.5°	1254.0	1231.4	1254.0	1273.4	1286.3	1302.5	1334.8	1393.0	1415.6	1418.8	1286.3
65°	1079.4	1069.8	1079.4	1118.3	1121.5	1140.8	1176.5	1218.5	1266.9	1260.5	1069.8
67.5°	921.1	921.1	921.1	947.0	966.4	976.1	1021.3	1040.7	1102.1	1108.6	892.1
70°	775.7	772.4	775.7	795.0	808.0	830.7	872.7	895.2	943.7	959.9	724.0
72.5°	636.7	633.5	636.7	652.8	665.8	685.2	720.7	746.6	788.6	808.0	562.4
75°	513.9	507.4	513.9	526.8	523.6	549.4	578.5	604.4	643.2	656.1	417.0
77.5°	394.3	394.3	394.3	407.2	407.2	433.1	446.0	478.4	501.0	520.4	307.0
80°	294.1	290.9	294.1	297.4	297.4	310.3	332.9	355.5	374.9	374.9	210.1
82.5°	206.9	200.4	206.9	206.9	206.9	213.3	226.2	232.7	245.6	255.4	132.6
85°	129.3	129.3	129.3	132.6	129.3	135.7	139.0	145.4	145.4	139.0	80.8
87.5°	84.0	80.8	84.0	80.8	80.8	77.5	77.5	77.5	74.3	71.1	45.3
90°	15.0	15.0	15.0	15.0	15.0	20.0	26.5	29.9	25.7	17.3	11.0
92.5°	59.9	48.0	59.9	71.8	74.8	106.0	147.6	168.5	147.9	106.9	76.0
95°	208.9	172.9	208.9	245.0	253.9	333.5	439.5	492.5	415.9	262.8	148.0
97.5°	500.4	431.9	500.4	569.0	586.2	636.4	703.5	737.0	609.3	354.0	162.5
100°	721.0	639.3	721.0	802.7	823.1	819.5	814.6	812.1	670.5	387.3	174.8
102.5°	938.0	868.0	938.0	1008.0	1025.5	961.5	876.1	833.4	689.8	402.4	187.0
105°	1214.7	1177.0	1214.7	1252.3	1261.7	1118.2	926.7	831.0	692.0	413.8	205.1
107.5°	1395.9	1405.0	1395.9	1386.9	1384.6	1184.3	917.3	783.8	661.1	415.8	231.9
110°	1465.0	1504.2	1465.0	1425.8	1416.0	1192.1	893.7	744.4	633.8	412.8	246.9



TEST NUMBER: P934595

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1471.2	1531.3	1471.2	1411.0	1395.9	1166.8	861.3	708.6	610.1	412.8	264.9
115°	1432.1	1515.6	1432.1	1348.7	1327.8	1107.1	812.9	665.7	582.7	416.7	292.1
117.5°	1349.5	1442.0	1349.5	1256.9	1233.8	1034.6	769.0	636.1	565.6	424.4	318.5
120°	1282.8	1372.7	1282.8	1192.8	1170.4	988.3	745.7	624.4	559.8	430.7	333.9
122.5°	1217.9	1306.6	1217.9	1129.2	1107.0	943.2	724.6	615.3	556.8	439.7	351.9
125°	1125.3	1207.0	1125.3	1043.6	1023.2	883.9	698.3	605.5	554.3	451.9	375.1
127.5°	1042.0	1111.0	1042.0	973.0	955.9	836.3	676.9	597.2	552.8	464.1	397.6
130°	992.9	1056.6	992.9	929.2	913.3	806.9	665.0	594.0	553.7	473.0	412.6
132.5°	948.4	1005.4	948.4	891.3	877.1	781.9	654.8	591.3	554.3	480.3	424.8
135°	887.4	936.6	887.4	838.2	825.9	746.1	639.8	586.6	553.7	488.1	438.9
137.5°	838.5	878.7	838.5	798.2	788.2	720.7	630.8	585.8	557.1	499.9	457.1
140°	804.8	842.4	804.8	767.2	757.8	699.5	621.9	583.0	557.7	507.2	469.3
142.5°	777.0	809.4	777.0	744.7	736.6	685.4	617.1	583.0	559.7	513.2	478.3
145°	735.4	759.8	735.4	710.8	704.7	662.9	607.0	579.1	559.8	521.1	492.1
147.5°	703.3	723.6	703.3	682.9	677.9	644.9	601.1	579.1	563.6	532.6	509.4
150°	683.1	699.5	683.1	666.7	662.6	634.8	597.6	579.1	565.6	538.7	518.5
152.5°	665.9	678.3	665.9	653.5	650.4	626.6	595.0	579.1	567.0	542.6	524.4
155°	646.1	654.3	646.1	637.8	635.7	616.8	591.7	579.1	569.8	551.3	537.4
157.5°	630.4	636.1	630.4	624.6	623.1	608.4	588.9	579.1	572.7	559.9	550.4
160°	621.0	624.4	621.0	617.7	616.8	604.2	587.5	579.1	574.1	563.9	556.3
162.5°	614.9	618.1	614.9	611.8	611.0	600.4	586.2	579.1	575.5	568.1	562.6
165°	606.0	609.4	606.0	602.8	601.9	594.3	584.2	579.1	577.4	574.1	571.6
167.5°	599.7	601.2	599.7	598.4	598.0	593.1	586.4	583.0	581.6	578.8	576.7
170°	598.0	598.0	598.0	598.0	598.0	593.1	586.4	583.0	582.9	582.7	582.6
172.5°	593.3	592.1	593.3	594.6	594.9	591.0	585.7	583.0	583.0	583.0	583.0
175°	590.5	590.5	590.5	590.5	590.5	588.0	584.7	583.0	583.8	585.4	586.6
177.5°	588.0	586.6	588.0	589.3	589.7	587.7	585.1	583.8	584.4	585.6	586.6
180°	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6

TEST NUMBER: P934595

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2
2.5°	3464.6	3445.3	3445.3	3413.0	3400.1	3390.3	3374.2	3325.7	3312.8	3299.8	3319.3
5°	3493.8	3458.2	3432.4	3374.2	3325.7	3306.3	3244.9	3128.6	3051.0	2992.8	2960.5
7.5°	3500.3	3455.0	3406.5	3316.0	3199.6	3148.0	2960.5	2747.2	2689.0	2637.3	2605.0
10°	3493.8	3442.1	3374.2	3238.4	2963.7	2873.2	2685.7	2546.8	2511.3	2501.5	2511.3
12.5°	3471.1	3422.6	3328.9	3102.7	2718.1	2656.7	2546.8	2466.0	2459.5	2475.7	2562.9
15°	3432.4	3387.1	3277.3	2921.7	2582.3	2537.1	2459.5	2430.5	2466.0	2579.2	2840.9
17.5°	3393.6	3341.8	3206.1	2744.0	2478.9	2446.6	2391.7	2449.9	2650.2	2802.2	2889.4
20°	3341.8	3280.4	3125.3	2614.7	2404.6	2375.5	2349.7	2611.4	2763.4	2818.3	2866.8
22.5°	3280.4	3215.9	3015.4	2524.2	2327.0	2304.4	2320.6	2702.0	2763.4	2802.2	2844.2
25°	3199.6	3144.7	2886.2	2453.1	2265.6	2239.8	2301.2	2692.2	2727.8	2737.5	2821.5
27.5°	3125.3	3054.2	2750.4	2388.5	2191.2	2181.6	2317.3	2650.2	2676.1	2685.7	2776.3
30°	3034.8	2928.2	2598.6	2320.6	2113.7	2110.5	2320.6	2598.6	2592.1	2617.9	2708.4
32.5°	2941.1	2740.8	2427.2	2236.5	2039.4	2036.2	2297.9	2520.9	2514.5	2550.0	2617.9
35°	2853.8	2595.3	2194.5	2139.6	1945.6	1948.9	2243.0	2430.5	2433.7	2466.0	2508.0
37.5°	2763.4	2469.2	1939.2	2032.9	1855.2	1855.2	2168.6	2346.4	2339.9	2349.7	2407.8
40°	2656.7	2272.0	1713.0	1894.0	1771.1	1761.4	2078.2	2255.9	2233.3	2230.1	2310.9
42.5°	2543.5	2055.5	1544.9	1709.7	1674.2	1661.2	1968.3	2146.1	2104.1	2113.7	2217.1
45°	2420.7	1997.4	1415.6	1444.7	1573.9	1564.3	1848.7	2020.0	1990.9	2016.8	2123.4
47.5°	2297.9	1881.0	1373.6	1199.1	1467.4	1464.1	1716.2	1897.2	1881.0	1906.8	2020.0
50°	2129.8	1751.8	1370.3	1027.8	1347.7	1360.7	1557.8	1777.6	1777.6	1800.2	1919.8
52.5°	1913.3	1593.3	1244.3	930.8	1208.7	1247.5	1418.8	1674.2	1680.6	1703.2	1809.9
55°	1716.2	1428.6	1153.8	856.4	1043.9	1128.0	1283.1	1567.5	1580.4	1603.1	1700.0
57.5°	1535.2	1189.4	1134.4	769.3	892.1	972.9	1163.5	1464.1	1470.5	1490.0	1583.7
60°	1341.3	859.7	1040.7	675.5	759.5	820.9	1053.7	1341.3	1363.9	1376.8	1457.6
62.5°	1121.5	623.8	943.7	610.8	694.9	707.8	963.1	1224.9	1254.0	1263.8	1312.2
65°	798.3	523.6	801.5	555.9	627.0	630.2	866.2	1105.3	1131.2	1147.3	1182.9
67.5°	539.8	426.6	610.8	504.1	575.3	578.5	772.4	966.4	1001.9	1014.9	1037.5
70°	374.9	284.4	452.5	449.2	517.1	523.6	672.2	840.3	872.7	882.3	895.2
72.5°	274.8	229.5	374.9	404.0	455.7	462.2	568.8	698.1	730.4	740.1	746.6
75°	210.1	242.4	303.8	352.3	387.8	391.1	465.4	568.8	591.4	597.9	601.2
77.5°	168.1	226.2	223.0	284.4	316.8	310.3	365.2	439.6	459.0	459.0	459.0
80°	126.1	177.7	168.1	203.6	232.7	226.2	261.8	313.5	319.9	326.4	323.2
82.5°	93.7	113.1	113.1	129.3	155.1	148.7	174.6	203.6	203.6	203.6	210.1
85°	58.2	64.7	51.7	67.9	87.3	84.0	96.9	109.9	113.1	113.1	106.7
87.5°	35.5	29.1	16.1	25.9	38.8	38.8	45.3	48.5	45.3	45.3	45.3
90°	10.2	7.1	3.9	7.1	10.2	11.0	17.3	25.7	29.9	26.5	20.0
92.5°	69.3	42.5	15.8	42.5	69.3	76.0	106.9	147.9	168.5	147.6	106.0
95°	135.8	86.8	37.8	86.8	135.8	148.0	262.8	415.9	492.5	439.5	333.5
97.5°	151.7	108.5	65.3	108.5	151.7	162.5	354.0	609.3	737.0	703.5	636.4
100°	164.9	125.8	86.6	125.8	164.9	174.8	387.3	670.5	812.1	814.6	819.5
102.5°	177.8	141.3	104.8	141.3	177.8	187.0	402.4	689.8	833.4	876.1	961.5
105°	197.4	166.4	135.4	166.4	197.4	205.1	413.8	692.0	831.0	926.7	1118.2
107.5°	224.6	195.8	166.9	195.8	224.6	231.9	415.8	661.1	783.8	917.3	1184.3
110°	240.4	214.2	188.1	214.2	240.4	246.9	412.8	633.8	744.4	893.7	1192.1

TEST NUMBER: P934595

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	258.7	233.9	209.0	233.9	258.7	264.9	412.8	610.1	708.6	861.3	1166.8
115°	286.4	263.5	240.6	263.5	286.4	292.1	416.7	582.7	665.7	812.9	1107.1
117.5°	313.2	292.4	271.6	292.4	313.2	318.5	424.4	565.6	636.1	769.0	1034.6
120°	329.0	309.3	289.7	309.3	329.0	333.9	430.7	559.8	624.4	745.7	988.3
122.5°	347.0	327.2	307.4	327.2	347.0	351.9	439.7	556.8	615.3	724.6	943.2
125°	370.6	352.6	334.6	352.6	370.6	375.1	451.9	554.3	605.5	698.3	883.9
127.5°	393.0	374.8	356.7	374.8	393.0	397.6	464.1	552.8	597.2	676.9	836.3
130°	407.7	388.0	368.4	388.0	407.7	412.6	473.0	553.7	594.0	665.0	806.9
132.5°	419.9	400.2	380.7	400.2	419.9	424.8	480.3	554.3	591.3	654.8	781.9
135°	434.4	416.7	398.8	416.7	434.4	438.9	488.1	553.7	586.6	639.8	746.1
137.5°	452.7	435.0	417.3	435.0	452.7	457.1	499.9	557.1	585.8	630.8	720.7
140°	465.2	448.9	432.6	448.9	465.2	469.3	507.2	557.7	583.0	621.9	699.5
142.5°	474.5	459.5	444.5	459.5	474.5	478.3	513.2	559.7	583.0	617.1	685.4
145°	488.9	475.7	462.6	475.7	488.9	492.1	521.1	559.8	579.1	607.0	662.9
147.5°	506.2	493.4	480.7	493.4	506.2	509.4	532.6	563.6	579.1	601.1	644.9
150°	515.6	504.0	492.5	504.0	515.6	518.5	538.7	565.6	579.1	597.6	634.8
152.5°	522.2	513.5	504.7	513.5	522.2	524.4	542.6	567.0	579.1	595.0	626.6
155°	535.8	529.3	522.8	529.3	535.8	537.4	551.3	569.8	579.1	591.7	616.8
157.5°	548.7	542.4	536.1	542.4	548.7	550.4	559.9	572.7	579.1	588.9	608.4
160°	555.0	550.2	545.2	550.2	555.0	556.3	563.9	574.1	579.1	587.5	604.2
162.5°	561.6	558.0	554.3	558.0	561.6	562.6	568.1	575.5	579.1	586.2	600.4
165°	570.7	567.5	564.1	567.5	570.7	571.6	574.1	577.4	579.1	584.2	594.3
167.5°	576.3	574.7	573.2	574.7	576.3	576.7	578.8	581.6	583.0	586.4	593.1
170°	582.3	580.6	579.1	580.6	582.3	582.6	582.7	582.9	583.0	586.4	593.1
172.5°	582.9	582.6	582.3	582.6	582.9	583.0	583.0	583.0	583.0	585.7	591.0
175°	586.6	586.6	586.6	586.6	586.6	586.6	585.4	583.8	583.0	584.7	588.0
177.5°	586.6	586.6	586.6	586.6	586.6	586.6	585.6	584.4	583.8	585.1	587.7
180°	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6

TEST NUMBER: P934595

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2	3416.2
2.5°	3296.7	3286.9	3299.8	3264.3	3299.8	3286.9	3296.7	3319.3	3299.8	3312.8	3325.7
5°	2892.6	2876.5	2824.8	2782.8	2824.8	2876.5	2892.6	2960.5	2992.8	3051.0	3128.6
7.5°	2585.6	2572.7	2559.7	2533.9	2559.7	2572.7	2585.6	2605.0	2637.3	2689.0	2747.2
10°	2517.8	2520.9	2540.3	2537.1	2540.3	2520.9	2517.8	2511.3	2501.5	2511.3	2546.8
12.5°	2692.2	2721.4	2827.9	2821.5	2827.9	2721.4	2692.2	2562.9	2475.7	2459.5	2466.0
15°	2892.6	2902.3	2925.0	2928.2	2925.0	2902.3	2892.6	2840.9	2579.2	2466.0	2430.5
17.5°	2912.0	2915.2	2931.4	2931.4	2931.4	2915.2	2912.0	2889.4	2802.2	2650.2	2449.9
20°	2895.8	2902.3	2934.6	2941.1	2934.6	2902.3	2895.8	2866.8	2818.3	2763.4	2611.4
22.5°	2889.4	2902.3	2928.2	2925.0	2928.2	2902.3	2889.4	2844.2	2802.2	2763.4	2702.0
25°	2857.1	2857.1	2860.3	2863.6	2860.3	2857.1	2857.1	2821.5	2737.5	2727.8	2692.2
27.5°	2789.2	2795.7	2815.1	2811.8	2815.1	2795.7	2789.2	2776.3	2685.7	2676.1	2650.2
30°	2727.8	2721.4	2705.1	2692.2	2705.1	2721.4	2727.8	2708.4	2617.9	2592.1	2598.6
32.5°	2624.3	2608.2	2592.1	2582.3	2592.1	2608.2	2624.3	2617.9	2550.0	2514.5	2520.9
35°	2501.5	2504.8	2501.5	2491.9	2501.5	2504.8	2501.5	2508.0	2466.0	2433.7	2430.5
37.5°	2414.3	2420.7	2417.5	2404.6	2417.5	2420.7	2414.3	2407.8	2349.7	2339.9	2346.4
40°	2323.8	2327.0	2323.8	2314.1	2323.8	2327.0	2323.8	2310.9	2230.1	2233.3	2255.9
42.5°	2236.5	2233.3	2223.6	2217.1	2223.6	2233.3	2236.5	2217.1	2113.7	2104.1	2146.1
45°	2136.3	2139.6	2120.2	2110.5	2120.2	2139.6	2136.3	2123.4	2016.8	1990.9	2020.0
47.5°	2036.2	2036.2	2020.0	2010.3	2020.0	2036.2	2036.2	2020.0	1906.8	1881.0	1897.2
50°	1929.5	1926.2	1903.6	1900.4	1903.6	1926.2	1929.5	1919.8	1800.2	1777.6	1777.6
52.5°	1806.7	1806.7	1809.9	1816.4	1809.9	1806.7	1806.7	1809.9	1703.2	1680.6	1674.2
55°	1700.0	1703.2	1725.9	1732.4	1725.9	1703.2	1700.0	1700.0	1603.1	1580.4	1567.5
57.5°	1590.2	1590.2	1606.3	1606.3	1606.3	1590.2	1590.2	1583.7	1490.0	1470.5	1464.1
60°	1464.1	1470.5	1483.5	1480.2	1483.5	1470.5	1464.1	1457.6	1376.8	1363.9	1341.3
62.5°	1331.6	1338.1	1341.3	1334.8	1341.3	1338.1	1331.6	1312.2	1263.8	1254.0	1224.9
65°	1192.6	1199.1	1202.3	1195.9	1202.3	1199.1	1192.6	1182.9	1147.3	1131.2	1105.3
67.5°	1050.4	1047.2	1043.9	1056.9	1043.9	1047.2	1050.4	1037.5	1014.9	1001.9	966.4
70°	905.0	905.0	901.7	908.2	901.7	905.0	905.0	895.2	882.3	872.7	840.3
72.5°	749.9	746.6	759.5	749.9	759.5	746.6	749.9	746.6	740.1	730.4	698.1
75°	597.9	604.4	597.9	607.6	597.9	604.4	597.9	601.2	597.9	591.4	568.8
77.5°	455.7	462.2	455.7	455.7	455.7	462.2	455.7	459.0	459.0	459.0	439.6
80°	323.2	319.9	319.9	316.8	319.9	319.9	323.2	323.2	326.4	319.9	313.5
82.5°	206.9	203.6	203.6	210.1	203.6	203.6	206.9	210.1	203.6	203.6	203.6
85°	113.1	116.3	109.9	109.9	109.9	116.3	113.1	106.7	113.1	113.1	109.9
87.5°	42.0	38.8	38.8	38.8	38.8	38.8	42.0	45.3	45.3	45.3	48.5
90°	15.0	15.0	15.0	15.0	15.0	15.0	15.0	20.0	26.5	29.9	25.7
92.5°	74.8	71.8	59.9	48.0	59.9	71.8	74.8	106.0	147.6	168.5	147.9
95°	253.9	245.0	208.9	172.9	208.9	245.0	253.9	333.5	439.5	492.5	415.9
97.5°	586.2	569.0	500.4	431.9	500.4	569.0	586.2	636.4	703.5	737.0	609.3
100°	823.1	802.7	721.0	639.3	721.0	802.7	823.1	819.5	814.6	812.1	670.5
102.5°	1025.5	1008.0	938.0	868.0	938.0	1008.0	1025.5	961.5	876.1	833.4	689.8
105°	1261.7	1252.3	1214.7	1177.0	1214.7	1252.3	1261.7	1118.2	926.7	831.0	692.0
107.5°	1384.6	1386.9	1395.9	1405.0	1395.9	1386.9	1384.6	1184.3	917.3	783.8	661.1
110°	1416.0	1425.8	1465.0	1504.2	1465.0	1425.8	1416.0	1192.1	893.7	744.4	633.8

TEST NUMBER: P934595

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1395.9	1411.0	1471.2	1531.3	1471.2	1411.0	1395.9	1166.8	861.3	708.6	610.1
115°	1327.8	1348.7	1432.1	1515.6	1432.1	1348.7	1327.8	1107.1	812.9	665.7	582.7
117.5°	1233.8	1256.9	1349.5	1442.0	1349.5	1256.9	1233.8	1034.6	769.0	636.1	565.6
120°	1170.4	1192.8	1282.8	1372.7	1282.8	1192.8	1170.4	988.3	745.7	624.4	559.8
122.5°	1107.0	1129.2	1217.9	1306.6	1217.9	1129.2	1107.0	943.2	724.6	615.3	556.8
125°	1023.2	1043.6	1125.3	1207.0	1125.3	1043.6	1023.2	883.9	698.3	605.5	554.3
127.5°	955.9	973.0	1042.0	1111.0	1042.0	973.0	955.9	836.3	676.9	597.2	552.8
130°	913.3	929.2	992.9	1056.6	992.9	929.2	913.3	806.9	665.0	594.0	553.7
132.5°	877.1	891.3	948.4	1005.4	948.4	891.3	877.1	781.9	654.8	591.3	554.3
135°	825.9	838.2	887.4	936.6	887.4	838.2	825.9	746.1	639.8	586.6	553.7
137.5°	788.2	798.2	838.5	878.7	838.5	798.2	788.2	720.7	630.8	585.8	557.1
140°	757.8	767.2	804.8	842.4	804.8	767.2	757.8	699.5	621.9	583.0	557.7
142.5°	736.6	744.7	777.0	809.4	777.0	744.7	736.6	685.4	617.1	583.0	559.7
145°	704.7	710.8	735.4	759.8	735.4	710.8	704.7	662.9	607.0	579.1	559.8
147.5°	677.9	682.9	703.3	723.6	703.3	682.9	677.9	644.9	601.1	579.1	563.6
150°	662.6	666.7	683.1	699.5	683.1	666.7	662.6	634.8	597.6	579.1	565.6
152.5°	650.4	653.5	665.9	678.3	665.9	653.5	650.4	626.6	595.0	579.1	567.0
155°	635.7	637.8	646.1	654.3	646.1	637.8	635.7	616.8	591.7	579.1	569.8
157.5°	623.1	624.6	630.4	636.1	630.4	624.6	623.1	608.4	588.9	579.1	572.7
160°	616.8	617.7	621.0	624.4	621.0	617.7	616.8	604.2	587.5	579.1	574.1
162.5°	611.0	611.8	614.9	618.1	614.9	611.8	611.0	600.4	586.2	579.1	575.5
165°	601.9	602.8	606.0	609.4	606.0	602.8	601.9	594.3	584.2	579.1	577.4
167.5°	598.0	598.4	599.7	601.2	599.7	598.4	598.0	593.1	586.4	583.0	581.6
170°	598.0	598.0	598.0	598.0	598.0	598.0	598.0	593.1	586.4	583.0	582.9
172.5°	594.9	594.6	593.3	592.1	593.3	594.6	594.9	591.0	585.7	583.0	583.0
175°	590.5	590.5	590.5	590.5	590.5	590.5	590.5	588.0	584.7	583.0	583.8
177.5°	589.7	589.3	588.0	586.6	588.0	589.3	589.7	587.7	585.1	583.8	584.4
180°	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6

TEST NUMBER: P934595

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	3416.2	3416.2	3416.2	3416.2	3416.2
2.5°	3374.2	3390.3	3400.1	3413.0	3445.3
5°	3244.9	3306.3	3325.7	3374.2	3432.4
7.5°	2960.5	3148.0	3199.6	3316.0	3406.5
10°	2685.7	2873.2	2963.7	3238.4	3374.2
12.5°	2546.8	2656.7	2718.1	3102.7	3328.9
15°	2459.5	2537.1	2582.3	2921.7	3277.3
17.5°	2391.7	2446.6	2478.9	2744.0	3206.1
20°	2349.7	2375.5	2404.6	2614.7	3125.3
22.5°	2320.6	2304.4	2327.0	2524.2	3015.4
25°	2301.2	2239.8	2265.6	2453.1	2886.2
27.5°	2317.3	2181.6	2191.2	2388.5	2750.4
30°	2320.6	2110.5	2113.7	2320.6	2598.6
32.5°	2297.9	2036.2	2039.4	2236.5	2427.2
35°	2243.0	1948.9	1945.6	2139.6	2194.5
37.5°	2168.6	1855.2	1855.2	2032.9	1939.2
40°	2078.2	1761.4	1771.1	1894.0	1713.0
42.5°	1968.3	1661.2	1674.2	1709.7	1544.9
45°	1848.7	1564.3	1573.9	1444.7	1415.6
47.5°	1716.2	1464.1	1467.4	1199.1	1373.6
50°	1557.8	1360.7	1347.7	1027.8	1370.3
52.5°	1418.8	1247.5	1208.7	930.8	1244.3
55°	1283.1	1128.0	1043.9	856.4	1153.8
57.5°	1163.5	972.9	892.1	769.3	1134.4
60°	1053.7	820.9	759.5	675.5	1040.7
62.5°	963.1	707.8	694.9	610.8	943.7
65°	866.2	630.2	627.0	555.9	801.5
67.5°	772.4	578.5	575.3	504.1	610.8
70°	672.2	523.6	517.1	449.2	452.5
72.5°	568.8	462.2	455.7	404.0	374.9
75°	465.4	391.1	387.8	352.3	303.8
77.5°	365.2	310.3	316.8	284.4	223.0
80°	261.8	226.2	232.7	203.6	168.1
82.5°	174.6	148.7	155.1	129.3	113.1
85°	96.9	84.0	87.3	67.9	51.7
87.5°	45.3	38.8	38.8	25.9	16.1
90°	17.3	11.0	10.2	7.1	3.9
92.5°	106.9	76.0	69.3	42.5	15.8
95°	262.8	148.0	135.8	86.8	37.8
97.5°	354.0	162.5	151.7	108.5	65.3
100°	387.3	174.8	164.9	125.8	86.6
102.5°	402.4	187.0	177.8	141.3	104.8
105°	413.8	205.1	197.4	166.4	135.4
107.5°	415.8	231.9	224.6	195.8	166.9
110°	412.8	246.9	240.4	214.2	188.1

TEST NUMBER: P934595

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	412.8	264.9	258.7	233.9	209.0
115°	416.7	292.1	286.4	263.5	240.6
117.5°	424.4	318.5	313.2	292.4	271.6
120°	430.7	333.9	329.0	309.3	289.7
122.5°	439.7	351.9	347.0	327.2	307.4
125°	451.9	375.1	370.6	352.6	334.6
127.5°	464.1	397.6	393.0	374.8	356.7
130°	473.0	412.6	407.7	388.0	368.4
132.5°	480.3	424.8	419.9	400.2	380.7
135°	488.1	438.9	434.4	416.7	398.8
137.5°	499.9	457.1	452.7	435.0	417.3
140°	507.2	469.3	465.2	448.9	432.6
142.5°	513.2	478.3	474.5	459.5	444.5
145°	521.1	492.1	488.9	475.7	462.6
147.5°	532.6	509.4	506.2	493.4	480.7
150°	538.7	518.5	515.6	504.0	492.5
152.5°	542.6	524.4	522.2	513.5	504.7
155°	551.3	537.4	535.8	529.3	522.8
157.5°	559.9	550.4	548.7	542.4	536.1
160°	563.9	556.3	555.0	550.2	545.2
162.5°	568.1	562.6	561.6	558.0	554.3
165°	574.1	571.6	570.7	567.5	564.1
167.5°	578.8	576.7	576.3	574.7	573.2
170°	582.7	582.6	582.3	580.6	579.1
172.5°	583.0	583.0	582.9	582.6	582.3
175°	585.4	586.6	586.6	586.6	586.6
177.5°	585.6	586.6	586.6	586.6	586.6
180°	586.6	586.6	586.6	586.6	586.6

TEST NUMBER: P934595

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-8-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.07	17.15	16.84	17.94	18.89	18.91	19.99	19.68	20.77	21.73
	3H	16.57	17.53	17.35	18.33	19.31	20.28	21.24	21.05	22.04	23.02
	4H	16.77	17.68	17.56	18.48	19.48	20.73	21.64	21.53	22.45	23.44
	6H	16.90	17.74	17.71	18.55	19.56	21.03	21.87	21.84	22.68	23.69
	8H	16.91	17.71	17.72	18.54	19.55	21.11	21.91	21.93	22.74	23.75
	12H	16.88	17.65	17.71	18.47	19.51	21.16	21.92	21.98	22.75	23.78
4H	2H	17.13	18.05	17.93	18.85	19.85	19.35	20.26	20.15	21.06	22.06
	3H	18.18	18.94	18.99	19.78	20.79	20.87	21.63	21.69	22.47	23.49
	4H	18.47	19.16	19.29	19.99	21.03	21.41	22.10	22.24	22.94	23.98
	6H	18.60	19.20	19.45	20.06	21.11	21.79	22.39	22.64	23.25	24.30
	8H	18.61	19.17	19.46	20.03	21.09	21.91	22.46	22.75	23.32	24.38
	12H	18.59	19.09	19.46	19.97	21.03	21.97	22.48	22.84	23.35	24.42
8H	4H	18.94	19.50	19.78	20.35	21.41	21.55	22.11	22.40	22.97	24.03
	6H	19.21	19.67	20.08	20.57	21.63	22.00	22.46	22.88	23.36	24.42
	8H	19.25	19.66	20.14	20.56	21.63	22.16	22.57	23.04	23.46	24.54
	12H	19.25	19.61	20.13	20.49	21.62	22.27	22.63	23.15	23.51	24.64
12H	4H	18.96	19.46	19.82	20.34	21.40	21.53	22.03	22.40	22.91	23.97
	6H	19.27	19.68	20.16	20.58	21.65	22.00	22.41	22.89	23.31	24.38
	8H	19.35	19.71	20.24	20.60	21.72	22.17	22.53	23.06	23.42	24.55

END OF REPORT