

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P935685

Luminaire Tested: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P935685
REPORT IS A COMBINATION OF REPORTS P933762 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8236.9 lumens
Efficiency: N/A
Efficacy: 127.9 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P935685

CATALOG NUMBER: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K

Luminous Intensity Polar Plot



TEST NUMBER: P935685

CATALOG NUMBER: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35
3	80	70	63	57	72	65	58	53	53	49	45	43	40	37	34	31	30
4	73	62	54	49	66	57	50	45	47	42	38	38	35	32	30	28	25
5	67	55	47	41	61	51	44	39	42	37	33	34	31	27	27	24	22
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	24	22	19
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15
9	49	37	30	25	45	34	27	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12376	12376	12376	12376
5°	12455	12493	12455	9823
10°	12358	12306	12358	8798
15°	12209	12039	12209	10052
20°	11940	11723	11940	10074
25°	11404	11263	11404	9860
30°	10715	10880	10715	9392
35°	9538	10397	9538	8877
40°	7935	9827	7935	8487
45°	7076	9161	7076	8041
50°	7500	8366	7500	7591
55°	7037	7510	7037	7331
60°	7227	6376	7227	6715
65°	6523	5271	6523	5893
70°	4486	4202	4486	4940
75°	3889	3106	3889	3719
80°	3070	2052	3070	2236
85°	1673	1086	1673	924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 10866 cd/sqm

TEST NUMBER: P935685

CATALOG NUMBER: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.4	1.5
10°-20°	341.8	4.1
20°-30°	528.4	6.4
30°-40°	630.8	7.7
40°-50°	634.5	7.7
50°-60°	552.1	6.7
60°-70°	391.4	4.8
70°-80°	207.1	2.5
80°-90°	54.4	0.7
90°-100°	359.1	4.4
100°-110°	944.2	11.5
110°-120°	979.0	11.9
120°-130°	785.3	9.5
130°-140°	616.2	7.5
140°-150°	472.9	5.7
150°-160°	340.6	4.1
160°-170°	208.4	2.5
170°-180°	70.4	0.9
0°-30°	990.6	12.0
0°-40°	1621.4	19.7
0°-60°	2808.0	34.1
0°-90°	3460.9	42.0
90°-120°	2282.3	27.7
90°-150°	4156.6	50.5
90°-180°	4776.0	58.0
0°-180°	8236.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1334	1334	1334	1334	1334	
5°	1340	1382	1340	1086	1340	127
15°	1279	1369	1279	1143	1279	360
25°	1127	1277	1127	1118	1127	517
35°	857	1139	857	973	857	530
45°	553	939	553	824	553	443
55°	450	693	450	676	450	414
65°	313	418	313	467	313	299
75°	119	198	119	237	119	125
85°	20	50	20	43	20	27
90°	5	19	5	19	5	5
95°	48	217	48	217	48	53
105°	170	1478	170	1478	170	180
115°	302	1904	302	1904	302	298
125°	420	1516	420	1516	420	373
135°	501	1176	501	1176	501	388
145°	581	954	581	954	581	364
155°	657	822	657	822	657	302
165°	708	765	708	765	708	200
175°	737	742	737	742	737	70
180°	737	737	737	737	737	

TEST NUMBER: P935685

CATALOG NUMBER: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7
2.5°	1345.0	1345.0	1352.7	1355.1	1355.1	1351.3	1347.6	1351.3	1362.7	1366.5	1365.3
5°	1340.1	1350.1	1364.0	1366.5	1369.0	1367.8	1365.3	1367.8	1380.4	1382.9	1384.2
7.5°	1329.9	1348.8	1366.5	1370.3	1374.1	1370.3	1369.0	1371.6	1384.2	1386.7	1386.7
10°	1317.3	1343.8	1364.0	1366.5	1370.3	1366.5	1366.5	1371.6	1384.2	1386.7	1388.0
12.5°	1299.7	1336.2	1355.1	1357.7	1362.7	1361.4	1360.2	1365.3	1377.9	1380.4	1380.4
15°	1279.4	1322.4	1340.1	1342.5	1351.3	1348.8	1348.8	1353.9	1367.8	1371.6	1370.3
17.5°	1251.7	1304.7	1324.9	1328.7	1335.0	1333.7	1335.0	1340.1	1352.7	1355.1	1356.4
20°	1220.1	1280.8	1304.7	1308.4	1314.7	1314.7	1314.7	1321.1	1333.7	1338.7	1338.7
22.5°	1177.2	1255.4	1280.8	1283.2	1290.8	1290.8	1293.4	1302.1	1313.5	1314.7	1314.7
25°	1126.8	1227.7	1249.1	1256.8	1264.3	1268.0	1271.9	1276.9	1280.8	1279.4	1280.8
27.5°	1073.8	1192.4	1220.1	1225.2	1235.3	1239.1	1244.1	1245.4	1246.7	1250.4	1247.9
30°	1014.5	1143.1	1184.8	1189.8	1206.3	1208.7	1203.8	1206.3	1212.6	1215.1	1217.6
32.5°	947.6	1070.0	1148.2	1159.6	1174.7	1167.1	1165.9	1169.7	1179.8	1179.8	1182.3
35°	856.7	1013.3	1114.2	1124.2	1135.6	1126.8	1131.8	1133.1	1139.4	1143.1	1141.9
37.5°	757.0	964.0	1078.9	1086.4	1095.2	1083.8	1091.5	1095.2	1100.3	1097.8	1097.8
40°	668.8	887.0	1037.2	1042.2	1049.8	1041.0	1048.5	1051.1	1053.6	1051.1	1049.8
42.5°	603.2	802.5	993.0	999.3	994.3	1000.6	1003.1	1008.2	1004.4	999.3	999.3
45°	552.7	779.8	945.1	952.6	945.1	955.2	958.9	958.9	947.6	945.1	943.8
47.5°	536.2	734.4	897.1	897.1	893.3	905.9	912.3	903.4	892.1	888.3	888.3
50°	535.0	683.9	831.5	826.5	844.1	859.3	853.0	844.1	835.3	821.4	821.4
52.5°	485.8	622.1	747.0	765.9	793.7	802.5	792.4	783.6	768.4	762.1	757.0
55°	450.5	557.7	670.0	707.8	736.9	748.2	729.3	720.5	697.7	694.0	691.4
57.5°	442.9	464.3	599.4	647.3	682.6	681.4	670.0	653.6	634.7	630.9	629.6
60°	406.3	335.6	523.6	580.4	617.0	613.2	603.2	588.0	570.3	567.8	565.3
62.5°	368.4	243.5	437.9	502.2	553.9	552.7	543.9	521.1	508.5	502.2	497.2
65°	313.0	204.4	311.6	417.6	492.1	494.6	475.7	459.3	445.4	437.9	436.5
67.5°	238.5	166.6	210.7	348.3	432.8	430.2	406.3	398.7	381.0	377.2	369.7
70°	176.7	111.1	146.4	282.7	374.7	368.4	349.5	340.6	324.3	315.4	310.4
72.5°	146.4	89.6	107.2	219.6	315.4	307.9	291.5	281.3	267.5	260.0	254.9
75°	118.6	94.6	82.0	162.7	256.1	251.1	236.0	225.9	214.5	204.4	205.7
77.5°	87.1	88.3	65.6	119.9	203.1	195.6	186.7	174.1	169.0	159.0	159.0
80°	65.6	69.4	49.2	82.0	146.4	146.4	138.8	130.0	121.1	116.1	116.1
82.5°	44.1	44.1	36.6	51.8	99.7	95.9	90.8	88.3	83.3	80.8	80.8
85°	20.2	25.2	22.7	31.5	54.2	56.8	56.8	54.2	53.0	50.4	51.8
87.5°	6.3	11.4	13.8	17.7	27.8	29.0	30.3	30.3	30.3	31.5	31.5
90°	5.0	8.9	12.9	13.8	21.8	32.3	37.5	33.3	25.0	18.8	18.8
92.5°	19.8	53.4	87.0	95.4	134.2	185.8	211.6	185.5	133.2	94.0	90.2
95°	47.5	109.0	170.6	185.9	330.1	522.4	618.6	552.0	418.9	319.0	307.6
97.5°	82.0	136.3	190.6	204.2	444.6	765.2	925.6	883.5	799.3	736.2	714.7
100°	108.8	158.1	207.2	219.6	486.4	842.1	1020.0	1023.1	1029.3	1033.9	1008.2
102.5°	131.5	177.4	223.4	234.8	505.5	866.4	1046.8	1100.4	1207.7	1288.1	1266.1
105°	170.1	209.0	247.9	257.7	519.7	869.1	1043.8	1164.0	1404.4	1584.7	1572.9
107.5°	209.6	245.9	282.2	291.3	522.4	830.5	984.5	1152.2	1487.5	1739.0	1741.8
110°	236.4	269.1	301.8	310.0	518.4	796.2	935.0	1122.5	1497.4	1778.6	1790.9

TEST NUMBER: P935685

CATALOG NUMBER: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	262.5	293.8	324.9	332.7	518.5	766.2	890.1	1081.9	1465.6	1753.4	1772.3
115°	302.1	330.9	359.7	366.9	523.3	731.8	836.1	1020.9	1390.6	1667.8	1694.0
117.5°	341.2	367.4	393.6	400.0	533.1	710.4	799.0	965.8	1299.4	1549.6	1578.6
120°	364.0	388.6	413.2	419.3	541.0	703.2	784.2	936.7	1241.4	1470.0	1498.3
122.5°	386.2	411.0	435.9	442.1	552.4	699.3	772.9	910.1	1184.6	1390.4	1418.3
125°	420.3	442.9	465.6	471.2	567.7	696.2	760.5	877.1	1110.2	1285.0	1310.7
127.5°	448.0	470.8	493.6	499.4	582.9	694.4	750.1	850.1	1050.4	1200.5	1222.2
130°	462.8	487.4	512.1	518.2	594.2	695.5	746.1	835.2	1013.4	1147.1	1167.1
132.5°	478.2	502.8	527.4	533.6	603.3	696.2	742.7	822.4	982.0	1101.7	1119.5
135°	500.9	523.3	545.7	551.3	613.1	695.5	736.8	803.6	937.2	1037.4	1052.9
137.5°	524.1	546.3	568.5	574.1	627.9	699.8	735.7	792.2	905.1	989.9	1002.5
140°	543.4	563.8	584.3	589.4	637.1	700.6	732.3	781.1	878.7	951.8	963.7
142.5°	558.2	577.1	596.0	600.8	644.6	703.1	732.3	775.2	860.8	925.1	935.2
145°	581.0	597.4	614.0	618.1	654.5	703.1	727.3	762.4	832.5	885.1	892.8
147.5°	603.8	619.8	635.8	639.8	669.0	707.8	727.3	754.9	810.1	851.5	857.9
150°	618.6	633.1	647.6	651.2	676.6	710.4	727.3	750.6	797.2	832.2	837.3
152.5°	633.9	644.9	655.9	658.7	681.6	712.0	727.3	747.2	787.0	816.8	820.7
155°	656.7	664.8	672.9	674.9	692.4	715.7	727.3	743.2	774.8	798.6	801.1
157.5°	673.5	681.4	689.2	691.2	703.3	719.3	727.3	739.6	764.3	782.7	784.5
160°	684.8	690.9	697.2	698.7	708.2	720.9	727.3	737.8	758.9	774.8	775.8
162.5°	696.2	700.8	705.5	706.6	713.5	722.7	727.3	736.2	754.1	767.4	768.4
165°	708.5	712.7	716.9	718.0	721.1	725.2	727.3	733.7	746.4	756.0	757.0
167.5°	720.0	721.9	723.9	724.4	727.0	730.6	732.3	736.5	744.8	751.1	751.6
170°	727.3	729.3	731.3	731.8	732.0	732.2	732.3	736.5	744.8	751.1	751.1
172.5°	731.3	731.7	732.2	732.3	732.3	732.3	732.3	735.5	742.1	747.1	746.7
175°	736.8	736.8	736.8	736.8	735.3	733.2	732.3	734.4	738.5	741.7	741.7
177.5°	736.8	736.8	736.8	736.8	735.6	734.0	733.2	734.9	738.2	740.7	740.2
180°	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8

TEST NUMBER: P935685

CATALOG NUMBER: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7
2.5°	1367.8	1364.0	1367.8	1365.3	1366.5	1362.7	1351.3	1347.6	1351.3	1355.1	1355.1
5°	1384.2	1381.7	1384.2	1384.2	1382.9	1380.4	1367.8	1365.3	1367.8	1369.0	1366.5
7.5°	1389.2	1385.4	1389.2	1386.7	1386.7	1384.2	1371.6	1369.0	1370.3	1374.1	1370.3
10°	1389.2	1385.4	1389.2	1388.0	1386.7	1384.2	1371.6	1366.5	1366.5	1370.3	1366.5
12.5°	1382.9	1380.4	1382.9	1380.4	1380.4	1377.9	1365.3	1360.2	1361.4	1362.7	1357.7
15°	1372.8	1369.0	1372.8	1370.3	1371.6	1367.8	1353.9	1348.8	1348.8	1351.3	1342.5
17.5°	1357.7	1352.7	1357.7	1356.4	1355.1	1352.7	1340.1	1335.0	1333.7	1335.0	1328.7
20°	1340.1	1336.2	1340.1	1338.7	1338.7	1333.7	1321.1	1314.7	1314.7	1314.7	1308.4
22.5°	1312.3	1308.4	1312.3	1314.7	1314.7	1313.5	1302.1	1293.4	1290.8	1290.8	1283.2
25°	1280.8	1276.9	1280.8	1280.8	1279.4	1280.8	1276.9	1271.9	1268.0	1264.3	1256.8
27.5°	1250.4	1247.9	1250.4	1247.9	1250.4	1246.7	1245.4	1244.1	1239.1	1235.3	1225.2
30°	1220.1	1217.6	1220.1	1217.6	1215.1	1212.6	1206.3	1203.8	1208.7	1206.3	1189.8
32.5°	1182.3	1179.8	1182.3	1182.3	1179.8	1179.8	1169.7	1165.9	1167.1	1174.7	1159.6
35°	1143.1	1139.4	1143.1	1141.9	1143.1	1139.4	1133.1	1131.8	1126.8	1135.6	1124.2
37.5°	1097.8	1094.0	1097.8	1097.8	1097.8	1100.3	1095.2	1091.5	1083.8	1095.2	1086.4
40°	1051.1	1046.0	1051.1	1049.8	1051.1	1053.6	1051.1	1048.5	1041.0	1049.8	1042.2
42.5°	998.1	996.8	998.1	999.3	999.3	1004.4	1008.2	1003.1	1000.6	994.3	999.3
45°	941.2	938.8	941.2	943.8	945.1	947.6	958.9	958.9	955.2	945.1	952.6
47.5°	880.7	874.4	880.7	888.3	888.3	892.1	903.4	912.3	905.9	893.3	897.1
50°	816.3	817.7	816.3	821.4	821.4	835.3	844.1	853.0	859.3	844.1	826.5
52.5°	753.3	752.1	753.3	757.0	762.1	768.4	783.6	792.4	802.5	793.7	765.9
55°	690.2	692.8	690.2	691.4	694.0	697.7	720.5	729.3	748.2	736.9	707.8
57.5°	627.1	623.3	627.1	629.6	630.9	634.7	653.6	670.0	681.4	682.6	647.3
60°	553.9	548.8	553.9	565.3	567.8	570.3	588.0	603.2	613.2	617.0	580.4
62.5°	489.5	480.7	489.5	497.2	502.2	508.5	521.1	543.9	552.7	553.9	502.2
65°	421.4	417.6	421.4	436.5	437.9	445.4	459.3	475.7	494.6	492.1	417.6
67.5°	359.7	359.7	359.7	369.7	377.2	381.0	398.7	406.3	430.2	432.8	348.3
70°	302.8	301.6	302.8	310.4	315.4	324.3	340.6	349.5	368.4	374.7	282.7
72.5°	248.6	247.3	248.6	254.9	260.0	267.5	281.3	291.5	307.9	315.4	219.6
75°	200.6	198.1	200.6	205.7	204.4	214.5	225.9	236.0	251.1	256.1	162.7
77.5°	153.9	153.9	153.9	159.0	159.0	169.0	174.1	186.7	195.6	203.1	119.9
80°	114.8	113.5	114.8	116.1	116.1	121.1	130.0	138.8	146.4	146.4	82.0
82.5°	80.8	78.2	80.8	80.8	80.8	83.3	88.3	90.8	95.9	99.7	51.8
85°	50.4	50.4	50.4	51.8	50.4	53.0	54.2	56.8	56.8	54.2	31.5
87.5°	32.9	31.5	32.9	31.5	31.5	30.3	30.3	30.3	29.0	27.8	17.7
90°	18.8	18.8	18.8	18.8	18.8	25.0	33.3	37.5	32.3	21.8	13.8
92.5°	75.3	60.4	75.3	90.2	94.0	133.2	185.5	211.6	185.8	134.2	95.4
95°	262.3	217.1	262.3	307.6	319.0	418.9	552.0	618.6	522.4	330.1	185.9
97.5°	628.6	542.4	628.6	714.7	736.2	799.3	883.5	925.6	765.2	444.6	204.2
100°	905.6	803.0	905.6	1008.2	1033.9	1029.3	1023.1	1020.0	842.1	486.4	219.6
102.5°	1178.2	1090.3	1178.2	1266.1	1288.1	1207.7	1100.4	1046.8	866.4	505.5	234.8
105°	1525.7	1478.4	1525.7	1572.9	1584.7	1404.4	1164.0	1043.8	869.1	519.7	257.7
107.5°	1753.3	1764.7	1753.3	1741.8	1739.0	1487.5	1152.2	984.5	830.5	522.4	291.3
110°	1840.1	1889.3	1840.1	1790.9	1778.6	1497.4	1122.5	935.0	796.2	518.4	310.0

TEST NUMBER: P935685

CATALOG NUMBER: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1847.8	1923.5	1847.8	1772.3	1753.4	1465.6	1081.9	890.1	766.2	518.5	332.7
115°	1798.8	1903.7	1798.8	1694.0	1667.8	1390.6	1020.9	836.1	731.8	523.3	366.9
117.5°	1694.9	1811.2	1694.9	1578.6	1549.6	1299.4	965.8	799.0	710.4	533.1	400.0
120°	1611.2	1724.2	1611.2	1498.3	1470.0	1241.4	936.7	784.2	703.2	541.0	419.3
122.5°	1529.6	1641.1	1529.6	1418.3	1390.4	1184.6	910.1	772.9	699.3	552.4	442.1
125°	1413.3	1516.0	1413.3	1310.7	1285.0	1110.2	877.1	760.5	696.2	567.7	471.2
127.5°	1308.7	1395.4	1308.7	1222.2	1200.5	1050.4	850.1	750.1	694.4	582.9	499.4
130°	1247.1	1327.2	1247.1	1167.1	1147.1	1013.4	835.2	746.1	695.5	594.2	518.2
132.5°	1191.2	1262.8	1191.2	1119.5	1101.7	982.0	822.4	742.7	696.2	603.3	533.6
135°	1114.6	1176.3	1114.6	1052.9	1037.4	937.2	803.6	736.8	695.5	613.1	551.3
137.5°	1053.1	1103.6	1053.1	1002.5	989.9	905.1	792.2	735.7	699.8	627.9	574.1
140°	1010.9	1058.1	1010.9	963.7	951.8	878.7	781.1	732.3	700.6	637.1	589.4
142.5°	975.9	1016.6	975.9	935.2	925.1	860.8	775.2	732.3	703.1	644.6	600.8
145°	923.6	954.3	923.6	892.8	885.1	832.5	762.4	727.3	703.1	654.5	618.1
147.5°	883.3	908.8	883.3	857.9	851.5	810.1	754.9	727.3	707.8	669.0	639.8
150°	858.1	878.7	858.1	837.3	832.2	797.2	750.6	727.3	710.4	676.6	651.2
152.5°	836.3	852.0	836.3	820.7	816.8	787.0	747.2	727.3	712.0	681.6	658.7
155°	811.5	821.8	811.5	801.1	798.6	774.8	743.2	727.3	715.7	692.4	674.9
157.5°	791.8	799.0	791.8	784.5	782.7	764.3	739.6	727.3	719.3	703.3	691.2
160°	780.0	784.2	780.0	775.8	774.8	758.9	737.8	727.3	720.9	708.2	698.7
162.5°	772.4	776.3	772.4	768.4	767.4	754.1	736.2	727.3	722.7	713.5	706.6
165°	761.2	765.4	761.2	757.0	756.0	746.4	733.7	727.3	725.2	721.1	718.0
167.5°	753.3	755.0	753.3	751.6	751.1	744.8	736.5	732.3	730.6	727.0	724.4
170°	751.1	751.1	751.1	751.1	751.1	744.8	736.5	732.3	732.2	732.0	731.8
172.5°	745.2	743.7	745.2	746.7	747.1	742.1	735.5	732.3	732.3	732.3	732.3
175°	741.7	741.7	741.7	741.7	741.7	738.5	734.4	732.3	733.2	735.3	736.8
177.5°	738.5	736.8	738.5	740.2	740.7	738.2	734.9	733.2	734.0	735.6	736.8
180°	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8

TEST NUMBER: P935685

CATALOG NUMBER: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7
2.5°	1352.7	1345.0	1345.0	1332.4	1327.4	1323.6	1317.3	1298.4	1293.4	1288.3	1295.8
5°	1364.0	1350.1	1340.1	1317.3	1298.4	1290.8	1266.8	1221.4	1191.1	1168.4	1155.8
7.5°	1366.5	1348.8	1329.9	1294.6	1249.1	1229.0	1155.8	1072.6	1049.8	1029.6	1017.0
10°	1364.0	1343.8	1317.3	1264.3	1157.1	1121.7	1048.5	994.3	980.4	976.6	980.4
12.5°	1355.1	1336.2	1299.7	1211.3	1061.2	1037.2	994.3	962.7	960.3	966.6	1000.6
15°	1340.1	1322.4	1279.4	1140.7	1008.2	990.5	960.3	948.9	962.7	1006.9	1109.1
17.5°	1324.9	1304.7	1251.7	1071.2	967.8	955.2	933.7	956.4	1034.6	1094.0	1128.0
20°	1304.7	1280.8	1220.1	1020.8	938.8	927.4	917.3	1019.6	1078.9	1100.3	1119.2
22.5°	1280.8	1255.4	1177.2	985.5	908.5	899.6	905.9	1054.9	1078.9	1094.0	1110.4
25°	1249.1	1227.7	1126.8	957.7	884.5	874.4	898.4	1051.1	1064.9	1068.7	1101.5
27.5°	1220.1	1192.4	1073.8	932.5	855.5	851.7	904.7	1034.6	1044.8	1048.5	1083.8
30°	1184.8	1143.1	1014.5	905.9	825.2	824.0	905.9	1014.5	1011.9	1022.0	1057.4
32.5°	1148.2	1070.0	947.6	873.2	796.2	794.9	897.1	984.2	981.6	995.6	1022.0
35°	1114.2	1013.3	856.7	835.3	759.6	760.8	875.6	948.9	950.1	962.7	979.2
37.5°	1078.9	964.0	757.0	793.7	724.3	724.3	846.6	916.0	913.6	917.3	940.0
40°	1037.2	887.0	668.8	739.4	691.4	687.7	811.4	880.7	871.9	870.7	902.2
42.5°	993.0	802.5	603.2	667.4	653.6	648.5	768.4	837.8	821.4	825.2	865.6
45°	945.1	779.8	552.7	564.0	614.4	610.7	721.7	788.6	777.3	787.4	829.0
47.5°	897.1	734.4	536.2	468.1	572.8	571.6	670.0	740.7	734.4	744.4	788.6
50°	831.5	683.9	535.0	401.3	526.2	531.2	608.1	694.0	694.0	702.8	749.5
52.5°	747.0	622.1	485.8	363.4	471.9	487.0	553.9	653.6	656.1	665.0	706.6
55°	670.0	557.7	450.5	334.3	407.6	440.4	500.9	612.0	617.0	625.8	663.7
57.5°	599.4	464.3	442.9	300.3	348.3	379.8	454.2	571.6	574.1	581.7	618.3
60°	523.6	335.6	406.3	263.7	296.5	320.5	411.3	523.6	532.5	537.5	569.1
62.5°	437.9	243.5	368.4	238.5	271.3	276.4	376.0	478.2	489.5	493.4	512.3
65°	311.6	204.4	313.0	217.1	244.8	246.0	338.2	431.6	441.6	447.9	461.8
67.5°	210.7	166.6	238.5	196.8	224.6	225.9	301.6	377.2	391.2	396.2	405.0
70°	146.4	111.1	176.7	175.4	201.9	204.4	262.4	328.0	340.6	344.5	349.5
72.5°	107.2	89.6	146.4	157.8	177.9	180.4	222.0	272.6	285.2	289.0	291.5
75°	82.0	94.6	118.6	137.5	151.4	152.7	181.7	222.0	230.9	233.4	234.6
77.5°	65.6	88.3	87.1	111.1	123.7	121.1	142.6	171.6	179.2	179.2	179.2
80°	49.2	69.4	65.6	79.5	90.8	88.3	102.2	122.4	124.9	127.4	126.2
82.5°	36.6	44.1	44.1	50.4	60.5	58.1	68.1	79.5	79.5	79.5	82.0
85°	22.7	25.2	20.2	26.5	34.1	32.9	37.8	42.9	44.1	44.1	41.6
87.5°	13.8	11.4	6.3	10.1	15.2	15.2	17.7	18.9	17.7	17.7	17.7
90°	12.9	8.9	5.0	8.9	12.9	13.8	21.8	32.3	37.5	33.3	25.0
92.5°	87.0	53.4	19.8	53.4	87.0	95.4	134.2	185.8	211.6	185.5	133.2
95°	170.6	109.0	47.5	109.0	170.6	185.9	330.1	522.4	618.6	552.0	418.9
97.5°	190.6	136.3	82.0	136.3	190.6	204.2	444.6	765.2	925.6	883.5	799.3
100°	207.2	158.1	108.8	158.1	207.2	219.6	486.4	842.1	1020.0	1023.1	1029.3
102.5°	223.4	177.4	131.5	177.4	223.4	234.8	505.5	866.4	1046.8	1100.4	1207.7
105°	247.9	209.0	170.1	209.0	247.9	257.7	519.7	869.1	1043.8	1164.0	1404.4
107.5°	282.2	245.9	209.6	245.9	282.2	291.3	522.4	830.5	984.5	1152.2	1487.5
110°	301.8	269.1	236.4	269.1	301.8	310.0	518.4	796.2	935.0	1122.5	1497.4

TEST NUMBER: P935685

CATALOG NUMBER: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	324.9	293.8	262.5	293.8	324.9	332.7	518.5	766.2	890.1	1081.9	1465.6
115°	359.7	330.9	302.1	330.9	359.7	366.9	523.3	731.8	836.1	1020.9	1390.6
117.5°	393.6	367.4	341.2	367.4	393.6	400.0	533.1	710.4	799.0	965.8	1299.4
120°	413.2	388.6	364.0	388.6	413.2	419.3	541.0	703.2	784.2	936.7	1241.4
122.5°	435.9	411.0	386.2	411.0	435.9	442.1	552.4	699.3	772.9	910.1	1184.6
125°	465.6	442.9	420.3	442.9	465.6	471.2	567.7	696.2	760.5	877.1	1110.2
127.5°	493.6	470.8	448.0	470.8	493.6	499.4	582.9	694.4	750.1	850.1	1050.4
130°	512.1	487.4	462.8	487.4	512.1	518.2	594.2	695.5	746.1	835.2	1013.4
132.5°	527.4	502.8	478.2	502.8	527.4	533.6	603.3	696.2	742.7	822.4	982.0
135°	545.7	523.3	500.9	523.3	545.7	551.3	613.1	695.5	736.8	803.6	937.2
137.5°	568.5	546.3	524.1	546.3	568.5	574.1	627.9	699.8	735.7	792.2	905.1
140°	584.3	563.8	543.4	563.8	584.3	589.4	637.1	700.6	732.3	781.1	878.7
142.5°	596.0	577.1	558.2	577.1	596.0	600.8	644.6	703.1	732.3	775.2	860.8
145°	614.0	597.4	581.0	597.4	614.0	618.1	654.5	703.1	727.3	762.4	832.5
147.5°	635.8	619.8	603.8	619.8	635.8	639.8	669.0	707.8	727.3	754.9	810.1
150°	647.6	633.1	618.6	633.1	647.6	651.2	676.6	710.4	727.3	750.6	797.2
152.5°	655.9	644.9	633.9	644.9	655.9	658.7	681.6	712.0	727.3	747.2	787.0
155°	672.9	664.8	656.7	664.8	672.9	674.9	692.4	715.7	727.3	743.2	774.8
157.5°	689.2	681.4	673.5	681.4	689.2	691.2	703.3	719.3	727.3	739.6	764.3
160°	697.2	690.9	684.8	690.9	697.2	698.7	708.2	720.9	727.3	737.8	758.9
162.5°	705.5	700.8	696.2	700.8	705.5	706.6	713.5	722.7	727.3	736.2	754.1
165°	716.9	712.7	708.5	712.7	716.9	718.0	721.1	725.2	727.3	733.7	746.4
167.5°	723.9	721.9	720.0	721.9	723.9	724.4	727.0	730.6	732.3	736.5	744.8
170°	731.3	729.3	727.3	729.3	731.3	731.8	732.0	732.2	732.3	736.5	744.8
172.5°	732.2	731.7	731.3	731.7	732.2	732.3	732.3	732.3	732.3	735.5	742.1
175°	736.8	736.8	736.8	736.8	736.8	736.8	735.3	733.2	732.3	734.4	738.5
177.5°	736.8	736.8	736.8	736.8	736.8	736.8	735.6	734.0	733.2	734.9	738.2
180°	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8

TEST NUMBER: P935685

CATALOG NUMBER: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7	1333.7
2.5°	1287.1	1283.2	1288.3	1274.4	1288.3	1283.2	1287.1	1295.8	1288.3	1293.4	1298.4
5°	1129.3	1123.0	1102.8	1086.4	1102.8	1123.0	1129.3	1155.8	1168.4	1191.1	1221.4
7.5°	1009.4	1004.4	999.3	989.2	999.3	1004.4	1009.4	1017.0	1029.6	1049.8	1072.6
10°	982.9	984.2	991.8	990.5	991.8	984.2	982.9	980.4	976.6	980.4	994.3
12.5°	1051.1	1062.4	1104.1	1101.5	1104.1	1062.4	1051.1	1000.6	966.6	960.3	962.7
15°	1129.3	1133.1	1141.9	1143.1	1141.9	1133.1	1129.3	1109.1	1006.9	962.7	948.9
17.5°	1136.8	1138.2	1144.5	1144.5	1144.5	1138.2	1136.8	1128.0	1094.0	1034.6	956.4
20°	1130.5	1133.1	1145.7	1148.2	1145.7	1133.1	1130.5	1119.2	1100.3	1078.9	1019.6
22.5°	1128.0	1133.1	1143.1	1141.9	1143.1	1133.1	1128.0	1110.4	1094.0	1078.9	1054.9
25°	1115.4	1115.4	1116.7	1117.9	1116.7	1115.4	1115.4	1101.5	1068.7	1064.9	1051.1
27.5°	1088.9	1091.5	1099.0	1097.8	1099.0	1091.5	1088.9	1083.8	1048.5	1044.8	1034.6
30°	1064.9	1062.4	1056.1	1051.1	1056.1	1062.4	1064.9	1057.4	1022.0	1011.9	1014.5
32.5°	1024.5	1018.2	1011.9	1008.2	1011.9	1018.2	1024.5	1022.0	995.6	981.6	984.2
35°	976.6	977.9	976.6	972.9	976.6	977.9	976.6	979.2	962.7	950.1	948.9
37.5°	942.6	945.1	943.8	938.8	943.8	945.1	942.6	940.0	917.3	913.6	916.0
40°	907.2	908.5	907.2	903.4	907.2	908.5	907.2	902.2	870.7	871.9	880.7
42.5°	873.2	871.9	868.1	865.6	868.1	871.9	873.2	865.6	825.2	821.4	837.8
45°	834.0	835.3	827.7	824.0	827.7	835.3	834.0	829.0	787.4	777.3	788.6
47.5°	794.9	794.9	788.6	784.8	788.6	794.9	794.9	788.6	744.4	734.4	740.7
50°	753.3	752.1	743.2	741.9	743.2	752.1	753.3	749.5	702.8	694.0	694.0
52.5°	705.4	705.4	706.6	709.1	706.6	705.4	705.4	706.6	665.0	656.1	653.6
55°	663.7	665.0	673.8	676.3	673.8	665.0	663.7	663.7	625.8	617.0	612.0
57.5°	620.8	620.8	627.1	627.1	627.1	620.8	620.8	618.3	581.7	574.1	571.6
60°	571.6	574.1	579.1	577.9	579.1	574.1	571.6	569.1	537.5	532.5	523.6
62.5°	519.8	522.4	523.6	521.1	523.6	522.4	519.8	512.3	493.4	489.5	478.2
65°	465.6	468.1	469.4	466.9	469.4	468.1	465.6	461.8	447.9	441.6	431.6
67.5°	410.1	408.8	407.6	412.6	407.6	408.8	410.1	405.0	396.2	391.2	377.2
70°	353.3	353.3	352.0	354.6	352.0	353.3	353.3	349.5	344.5	340.6	328.0
72.5°	292.7	291.5	296.5	292.7	296.5	291.5	292.7	291.5	289.0	285.2	272.6
75°	233.4	236.0	233.4	237.2	233.4	236.0	233.4	234.6	233.4	230.9	222.0
77.5°	177.9	180.4	177.9	177.9	177.9	180.4	177.9	179.2	179.2	179.2	171.6
80°	126.2	124.9	124.9	123.7	124.9	124.9	126.2	126.2	127.4	124.9	122.4
82.5°	80.8	79.5	79.5	82.0	79.5	79.5	80.8	82.0	79.5	79.5	79.5
85°	44.1	45.5	42.9	42.9	42.9	45.5	44.1	41.6	44.1	44.1	42.9
87.5°	16.4	15.2	15.2	15.2	15.2	15.2	16.4	17.7	17.7	17.7	18.9
90°	18.8	18.8	18.8	18.8	18.8	18.8	18.8	25.0	33.3	37.5	32.3
92.5°	94.0	90.2	75.3	60.4	75.3	90.2	94.0	133.2	185.5	211.6	185.8
95°	319.0	307.6	262.3	217.1	262.3	307.6	319.0	418.9	552.0	618.6	522.4
97.5°	736.2	714.7	628.6	542.4	628.6	714.7	736.2	799.3	883.5	925.6	765.2
100°	1033.9	1008.2	905.6	803.0	905.6	1008.2	1033.9	1029.3	1023.1	1020.0	842.1
102.5°	1288.1	1266.1	1178.2	1090.3	1178.2	1266.1	1288.1	1207.7	1100.4	1046.8	866.4
105°	1584.7	1572.9	1525.7	1478.4	1525.7	1572.9	1584.7	1404.4	1164.0	1043.8	869.1
107.5°	1739.0	1741.8	1753.3	1764.7	1753.3	1741.8	1739.0	1487.5	1152.2	984.5	830.5
110°	1778.6	1790.9	1840.1	1889.3	1840.1	1790.9	1778.6	1497.4	1122.5	935.0	796.2

TEST NUMBER: P935685

CATALOG NUMBER: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1753.4	1772.3	1847.8	1923.5	1847.8	1772.3	1753.4	1465.6	1081.9	890.1	766.2
115°	1667.8	1694.0	1798.8	1903.7	1798.8	1694.0	1667.8	1390.6	1020.9	836.1	731.8
117.5°	1549.6	1578.6	1694.9	1811.2	1694.9	1578.6	1549.6	1299.4	965.8	799.0	710.4
120°	1470.0	1498.3	1611.2	1724.2	1611.2	1498.3	1470.0	1241.4	936.7	784.2	703.2
122.5°	1390.4	1418.3	1529.6	1641.1	1529.6	1418.3	1390.4	1184.6	910.1	772.9	699.3
125°	1285.0	1310.7	1413.3	1516.0	1413.3	1310.7	1285.0	1110.2	877.1	760.5	696.2
127.5°	1200.5	1222.2	1308.7	1395.4	1308.7	1222.2	1200.5	1050.4	850.1	750.1	694.4
130°	1147.1	1167.1	1247.1	1327.2	1247.1	1167.1	1147.1	1013.4	835.2	746.1	695.5
132.5°	1101.7	1119.5	1191.2	1262.8	1191.2	1119.5	1101.7	982.0	822.4	742.7	696.2
135°	1037.4	1052.9	1114.6	1176.3	1114.6	1052.9	1037.4	937.2	803.6	736.8	695.5
137.5°	989.9	1002.5	1053.1	1103.6	1053.1	1002.5	989.9	905.1	792.2	735.7	699.8
140°	951.8	963.7	1010.9	1058.1	1010.9	963.7	951.8	878.7	781.1	732.3	700.6
142.5°	925.1	935.2	975.9	1016.6	975.9	935.2	925.1	860.8	775.2	732.3	703.1
145°	885.1	892.8	923.6	954.3	923.6	892.8	885.1	832.5	762.4	727.3	703.1
147.5°	851.5	857.9	883.3	908.8	883.3	857.9	851.5	810.1	754.9	727.3	707.8
150°	832.2	837.3	858.1	878.7	858.1	837.3	832.2	797.2	750.6	727.3	710.4
152.5°	816.8	820.7	836.3	852.0	836.3	820.7	816.8	787.0	747.2	727.3	712.0
155°	798.6	801.1	811.5	821.8	811.5	801.1	798.6	774.8	743.2	727.3	715.7
157.5°	782.7	784.5	791.8	799.0	791.8	784.5	782.7	764.3	739.6	727.3	719.3
160°	774.8	775.8	780.0	784.2	780.0	775.8	774.8	758.9	737.8	727.3	720.9
162.5°	767.4	768.4	772.4	776.3	772.4	768.4	767.4	754.1	736.2	727.3	722.7
165°	756.0	757.0	761.2	765.4	761.2	757.0	756.0	746.4	733.7	727.3	725.2
167.5°	751.1	751.6	753.3	755.0	753.3	751.6	751.1	744.8	736.5	732.3	730.6
170°	751.1	751.1	751.1	751.1	751.1	751.1	751.1	744.8	736.5	732.3	732.2
172.5°	747.1	746.7	745.2	743.7	745.2	746.7	747.1	742.1	735.5	732.3	732.3
175°	741.7	741.7	741.7	741.7	741.7	741.7	741.7	738.5	734.4	732.3	733.2
177.5°	740.7	740.2	738.5	736.8	738.5	740.2	740.7	738.2	734.9	733.2	734.0
180°	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8

TEST NUMBER: P935685

CATALOG NUMBER: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1333.7	1333.7	1333.7	1333.7	1333.7
2.5°	1317.3	1323.6	1327.4	1332.4	1345.0
5°	1266.8	1290.8	1298.4	1317.3	1340.1
7.5°	1155.8	1229.0	1249.1	1294.6	1329.9
10°	1048.5	1121.7	1157.1	1264.3	1317.3
12.5°	994.3	1037.2	1061.2	1211.3	1299.7
15°	960.3	990.5	1008.2	1140.7	1279.4
17.5°	933.7	955.2	967.8	1071.2	1251.7
20°	917.3	927.4	938.8	1020.8	1220.1
22.5°	905.9	899.6	908.5	985.5	1177.2
25°	898.4	874.4	884.5	957.7	1126.8
27.5°	904.7	851.7	855.5	932.5	1073.8
30°	905.9	824.0	825.2	905.9	1014.5
32.5°	897.1	794.9	796.2	873.2	947.6
35°	875.6	760.8	759.6	835.3	856.7
37.5°	846.6	724.3	724.3	793.7	757.0
40°	811.4	687.7	691.4	739.4	668.8
42.5°	768.4	648.5	653.6	667.4	603.2
45°	721.7	610.7	614.4	564.0	552.7
47.5°	670.0	571.6	572.8	468.1	536.2
50°	608.1	531.2	526.2	401.3	535.0
52.5°	553.9	487.0	471.9	363.4	485.8
55°	500.9	440.4	407.6	334.3	450.5
57.5°	454.2	379.8	348.3	300.3	442.9
60°	411.3	320.5	296.5	263.7	406.3
62.5°	376.0	276.4	271.3	238.5	368.4
65°	338.2	246.0	244.8	217.1	313.0
67.5°	301.6	225.9	224.6	196.8	238.5
70°	262.4	204.4	201.9	175.4	176.7
72.5°	222.0	180.4	177.9	157.8	146.4
75°	181.7	152.7	151.4	137.5	118.6
77.5°	142.6	121.1	123.7	111.1	87.1
80°	102.2	88.3	90.8	79.5	65.6
82.5°	68.1	58.1	60.5	50.4	44.1
85°	37.8	32.9	34.1	26.5	20.2
87.5°	17.7	15.2	15.2	10.1	6.3
90°	21.8	13.8	12.9	8.9	5.0
92.5°	134.2	95.4	87.0	53.4	19.8
95°	330.1	185.9	170.6	109.0	47.5
97.5°	444.6	204.2	190.6	136.3	82.0
100°	486.4	219.6	207.2	158.1	108.8
102.5°	505.5	234.8	223.4	177.4	131.5
105°	519.7	257.7	247.9	209.0	170.1
107.5°	522.4	291.3	282.2	245.9	209.6
110°	518.4	310.0	301.8	269.1	236.4

TEST NUMBER: P935685

CATALOG NUMBER: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	518.5	332.7	324.9	293.8	262.5
115°	523.3	366.9	359.7	330.9	302.1
117.5°	533.1	400.0	393.6	367.4	341.2
120°	541.0	419.3	413.2	388.6	364.0
122.5°	552.4	442.1	435.9	411.0	386.2
125°	567.7	471.2	465.6	442.9	420.3
127.5°	582.9	499.4	493.6	470.8	448.0
130°	594.2	518.2	512.1	487.4	462.8
132.5°	603.3	533.6	527.4	502.8	478.2
135°	613.1	551.3	545.7	523.3	500.9
137.5°	627.9	574.1	568.5	546.3	524.1
140°	637.1	589.4	584.3	563.8	543.4
142.5°	644.6	600.8	596.0	577.1	558.2
145°	654.5	618.1	614.0	597.4	581.0
147.5°	669.0	639.8	635.8	619.8	603.8
150°	676.6	651.2	647.6	633.1	618.6
152.5°	681.6	658.7	655.9	644.9	633.9
155°	692.4	674.9	672.9	664.8	656.7
157.5°	703.3	691.2	689.2	681.4	673.5
160°	708.2	698.7	697.2	690.9	684.8
162.5°	713.5	706.6	705.5	700.8	696.2
165°	721.1	718.0	716.9	712.7	708.5
167.5°	727.0	724.4	723.9	721.9	720.0
170°	732.0	731.8	731.3	729.3	727.3
172.5°	732.3	732.3	732.2	731.7	731.3
175°	735.3	736.8	736.8	736.8	736.8
177.5°	735.6	736.8	736.8	736.8	736.8
180°	736.8	736.8	736.8	736.8	736.8

TEST NUMBER: P935685

CATALOG NUMBER: SQ4-FA-125U-100D-B2750-1D-UNV-W2A-W-4-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.75	13.54	13.77	14.57	15.95	15.55	16.34	16.57	17.37	18.75
	3H	13.22	13.93	14.25	14.97	16.37	16.88	17.59	17.91	18.63	20.03
	4H	13.41	14.08	14.45	15.12	16.53	17.31	17.98	18.36	19.03	20.43
	6H	13.52	14.14	14.58	15.19	16.61	17.58	18.20	18.64	19.25	20.67
	8H	13.52	14.11	14.58	15.18	16.59	17.65	18.24	18.71	19.31	20.72
	12H	13.49	14.05	14.56	15.11	16.55	17.68	18.25	18.75	19.30	20.74
4H	2H	13.77	14.44	14.82	15.48	16.89	15.95	16.62	17.00	17.66	19.07
	3H	14.79	15.35	15.84	16.42	17.84	17.44	18.00	18.50	19.07	20.49
	4H	15.06	15.57	16.12	16.63	18.08	17.96	18.47	19.02	19.53	20.98
	6H	15.18	15.62	16.26	16.71	18.14	18.31	18.75	19.39	19.84	21.27
	8H	15.18	15.60	16.26	16.67	18.13	18.41	18.82	19.49	19.90	21.35
	12H	15.15	15.52	16.24	16.61	18.07	18.46	18.83	19.55	19.92	21.38
8H	4H	15.50	15.91	16.58	16.99	18.44	18.08	18.49	19.15	19.57	21.02
	6H	15.76	16.10	16.86	17.22	18.67	18.50	18.84	19.60	19.96	21.41
	8H	15.80	16.10	16.91	17.20	18.67	18.65	18.95	19.75	20.05	21.52
	12H	15.78	16.05	16.89	17.14	18.65	18.74	19.00	19.85	20.10	21.61
12H	4H	15.50	15.88	16.60	16.97	18.43	18.04	18.41	19.13	19.50	20.96
	6H	15.82	16.12	16.92	17.22	18.69	18.50	18.80	19.60	19.90	21.37
	8H	15.88	16.15	16.99	17.24	18.75	18.65	18.91	19.76	20.01	21.52

END OF REPORT