

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934387

Luminaire Tested: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934387
REPORT IS A COMBINATION OF REPORTS P933695 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7070.5 lumens
Efficiency: N/A
Efficacy: 129.5 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 54.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934387

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K

Luminous Intensity Polar Plot



TEST NUMBER: P934387

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	95	91	88	93	89	86	83	77	75	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	57	60	55	50	51	48	44	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9769	9769	9769	9769
5°	9838	9861	9838	7754
10°	9769	9714	9769	6945
15°	9659	9503	9659	7936
20°	9453	9254	9453	7952
25°	9036	8890	9036	7784
30°	8499	8588	8499	7414
35°	7572	8207	7572	7007
40°	6306	7757	6306	6700
45°	5631	7231	5631	6347
50°	5978	6603	5978	5992
55°	5619	5927	5619	5787
60°	5785	5034	5785	5301
65°	5236	4161	5236	4652
70°	3618	3317	3618	3899
75°	3159	2452	3159	2936
80°	2529	1621	2529	1765
85°	1425	859	1425	730

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 8636 cd/sqm

TEST NUMBER: P934387

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.5	2.0
10°-20°	404.7	5.7
20°-30°	625.6	8.8
30°-40°	746.9	10.6
40°-50°	751.3	10.6
50°-60°	653.7	9.2
60°-70°	463.5	6.6
70°-80°	245.2	3.5
80°-90°	62.8	0.9
90°-100°	223.7	3.2
100°-110°	588.0	8.3
110°-120°	609.7	8.6
120°-130°	489.0	6.9
130°-140°	383.7	5.4
140°-150°	294.5	4.2
150°-160°	212.1	3.0
160°-170°	129.8	1.8
170°-180°	43.8	0.6
0°-30°	1172.9	16.6
0°-40°	1919.8	27.2
0°-60°	3324.7	47.0
0°-90°	4096.2	57.9
90°-120°	1421.3	20.1
90°-150°	2588.6	36.6
90°-180°	2974.0	42.1
0°-180°	7070.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1579	1579	1579	1579	1579	
5°	1587	1636	1587	1286	1587	151
15°	1515	1621	1515	1354	1515	426
25°	1334	1512	1334	1324	1334	613
35°	1014	1349	1014	1152	1014	628
45°	654	1112	654	976	654	524
55°	533	820	533	801	533	490
65°	370	494	370	553	370	354
75°	140	235	140	281	140	148
85°	24	60	24	51	24	32
90°	3	12	3	12	3	4
95°	30	135	30	135	30	33
105°	106	921	106	921	106	112
115°	188	1186	188	1186	188	186
125°	262	944	262	944	262	232
135°	312	733	312	733	312	241
145°	362	594	362	594	362	227
155°	409	512	409	512	409	188
165°	441	477	441	477	441	125
175°	459	462	459	462	459	44
180°	459	459	459	459	459	

TEST NUMBER: P934387

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2
2.5°	1592.6	1592.6	1601.6	1604.6	1604.6	1600.1	1595.6	1600.1	1613.5	1618.0	1616.5
5°	1586.6	1598.6	1615.0	1618.0	1621.0	1619.5	1616.5	1619.5	1634.4	1637.4	1638.9
7.5°	1574.7	1597.1	1618.0	1622.5	1627.0	1622.5	1621.0	1624.0	1638.9	1641.9	1641.9
10°	1559.7	1591.1	1615.0	1618.0	1622.5	1618.0	1618.0	1624.0	1638.9	1641.9	1643.4
12.5°	1538.8	1582.1	1604.6	1607.5	1613.5	1612.0	1610.5	1616.5	1631.4	1634.4	1634.4
15°	1514.9	1565.7	1586.6	1589.6	1600.1	1597.1	1597.1	1603.1	1619.5	1624.0	1622.5
17.5°	1482.0	1544.8	1568.7	1573.2	1580.7	1579.2	1580.7	1586.6	1601.6	1604.6	1606.0
20°	1444.7	1516.4	1544.8	1549.3	1556.7	1556.7	1556.7	1564.2	1579.2	1585.1	1585.1
22.5°	1393.9	1486.5	1516.4	1519.4	1528.4	1528.4	1531.4	1541.8	1555.3	1556.7	1556.7
25°	1334.1	1453.7	1479.1	1488.0	1497.0	1501.5	1506.0	1511.9	1516.4	1514.9	1516.4
27.5°	1271.4	1411.8	1444.7	1450.7	1462.6	1467.1	1473.1	1474.6	1476.1	1480.6	1477.6
30°	1201.2	1353.6	1402.9	1408.8	1428.3	1431.3	1425.3	1428.3	1435.7	1438.7	1441.7
32.5°	1122.0	1266.9	1359.5	1373.0	1390.9	1382.0	1380.5	1384.9	1396.9	1396.9	1399.9
35°	1014.4	1199.7	1319.2	1331.2	1344.6	1334.1	1340.1	1341.6	1349.1	1353.6	1352.1
37.5°	896.4	1141.4	1277.4	1286.3	1296.8	1283.3	1292.3	1296.8	1302.8	1299.8	1299.8
40°	791.8	1050.3	1228.1	1234.0	1243.0	1232.6	1241.5	1244.5	1247.5	1244.5	1243.0
42.5°	714.1	950.2	1175.8	1183.2	1177.3	1184.7	1187.7	1193.7	1189.2	1183.2	1183.2
45°	654.4	923.3	1119.0	1128.0	1119.0	1131.0	1135.4	1135.4	1122.0	1119.0	1117.5
47.5°	635.0	869.5	1062.2	1062.2	1057.8	1072.7	1080.2	1069.7	1056.3	1051.8	1051.8
50°	633.5	809.7	984.5	978.6	999.5	1017.4	1009.9	999.5	989.0	972.6	972.6
52.5°	575.2	736.5	884.4	906.9	939.7	950.2	938.2	927.8	909.8	902.4	896.4
55°	533.4	660.3	793.3	838.1	872.5	885.9	863.5	853.1	826.2	821.7	818.7
57.5°	524.4	549.8	709.6	766.4	808.3	806.8	793.3	773.9	751.5	747.0	745.5
60°	481.1	397.4	620.0	687.2	730.6	726.1	714.1	696.2	675.3	672.3	669.3
62.5°	436.2	288.3	518.4	594.6	655.9	654.4	643.9	617.0	602.1	594.6	588.6
65°	370.5	242.0	369.0	494.5	582.7	585.6	563.2	543.8	527.4	518.4	516.9
67.5°	282.4	197.2	249.5	412.3	512.4	509.5	481.1	472.1	451.2	446.7	437.7
70°	209.2	131.5	173.3	334.7	443.7	436.2	413.8	403.4	384.0	373.5	367.5
72.5°	173.3	106.1	127.0	260.0	373.5	364.5	345.1	333.2	316.7	307.8	301.8
75°	140.4	112.0	97.1	192.7	303.3	297.3	279.4	267.4	254.0	242.0	243.5
77.5°	103.1	104.6	77.7	141.9	240.5	231.6	221.1	206.2	200.2	188.2	188.2
80°	77.7	82.2	58.3	97.1	173.3	173.3	164.3	153.9	143.4	137.4	137.4
82.5°	52.3	52.3	43.3	61.3	118.0	113.5	107.6	104.6	98.6	95.6	95.6
85°	23.9	29.9	26.9	37.4	64.2	67.2	67.2	64.2	62.7	59.8	61.3
87.5°	7.5	13.4	16.4	20.9	32.9	34.4	35.9	35.9	35.9	37.4	37.4
90°	3.1	5.6	8.1	8.7	13.5	20.1	23.4	20.8	15.5	11.7	11.7
92.5°	12.4	33.3	54.2	59.5	83.6	115.7	131.8	115.4	82.9	58.5	56.2
95°	29.6	67.8	106.2	115.7	205.6	325.4	385.3	343.8	260.9	198.6	191.5
97.5°	51.1	85.0	118.7	127.2	277.0	476.7	576.5	550.3	497.8	458.5	445.0
100°	67.7	98.4	129.1	136.8	302.9	524.5	635.2	637.1	641.0	643.9	628.0
102.5°	81.9	110.6	139.1	146.3	314.8	539.5	651.9	685.2	752.1	802.2	788.5
105°	106.0	130.2	154.4	160.5	323.6	541.2	650.0	724.9	874.6	986.9	979.6
107.5°	130.6	153.2	175.7	181.4	325.3	517.1	613.0	717.4	926.3	1083.0	1084.7
110°	147.2	167.5	187.9	193.0	322.8	495.8	582.3	699.0	932.6	1107.7	1115.3

TEST NUMBER: P934387

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	163.5	183.0	202.4	207.3	322.9	477.2	554.3	673.8	912.7	1091.9	1103.7
115°	188.1	206.1	224.0	228.5	325.9	455.8	520.7	635.8	866.0	1038.6	1055.0
117.5°	212.4	228.8	245.0	249.1	332.0	442.4	497.6	601.5	809.2	965.0	983.2
120°	226.6	241.9	257.3	261.2	336.8	437.8	488.3	583.3	773.1	915.4	933.1
122.5°	240.5	256.0	271.4	275.3	343.9	435.5	481.3	566.7	737.7	865.9	883.3
125°	261.7	275.8	289.9	293.4	353.5	433.6	473.6	546.2	691.4	800.3	816.2
127.5°	279.0	293.2	307.5	311.1	363.0	432.5	467.1	529.5	654.1	747.6	761.0
130°	288.2	303.6	318.9	322.7	370.0	433.1	464.6	520.1	631.2	714.4	726.9
132.5°	297.8	313.1	328.5	332.3	375.7	433.6	462.5	512.2	611.5	686.0	697.2
135°	311.9	325.9	339.8	343.3	381.9	433.2	458.9	500.5	583.7	646.0	655.7
137.5°	326.4	340.2	354.0	357.5	391.0	435.8	458.2	493.3	563.6	616.4	624.3
140°	338.4	351.2	363.8	367.0	396.7	436.2	456.1	486.4	547.2	592.7	600.1
142.5°	347.6	359.4	371.1	374.1	401.4	437.8	456.1	482.8	536.0	576.1	582.5
145°	361.8	372.1	382.4	385.0	407.7	437.8	453.0	474.8	518.4	551.2	556.0
147.5°	376.0	386.0	396.0	398.5	416.6	440.8	453.0	470.1	504.5	530.3	534.3
150°	385.3	394.3	403.3	405.6	421.4	442.4	453.0	467.5	496.5	518.2	521.4
152.5°	394.7	401.6	408.5	410.2	424.4	443.4	453.0	465.3	490.1	508.7	511.0
155°	409.0	414.0	419.0	420.3	431.2	445.7	453.0	462.8	482.6	497.3	498.9
157.5°	419.4	424.3	429.3	430.5	437.9	448.0	453.0	460.6	476.0	487.4	488.5
160°	426.5	430.3	434.1	435.1	441.0	449.0	453.0	459.6	472.7	482.6	483.2
162.5°	433.6	436.4	439.3	440.0	444.3	450.1	453.0	458.6	469.6	477.9	478.5
165°	441.2	443.8	446.4	447.1	449.1	451.7	453.0	457.0	464.8	470.8	471.5
167.5°	448.3	449.5	450.8	451.1	452.8	455.0	456.1	458.7	463.8	467.7	468.0
170°	453.0	454.2	455.5	455.8	455.9	456.0	456.1	458.7	463.8	467.7	467.7
172.5°	455.5	455.8	456.0	456.1	456.1	456.1	456.1	458.1	462.1	465.2	465.0
175°	458.9	458.9	458.9	458.9	458.0	456.7	456.1	457.4	460.0	461.8	461.8
177.5°	458.9	458.9	458.9	458.9	458.2	457.2	456.7	457.7	459.8	461.2	460.9
180°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9

TEST NUMBER: P934387

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2
2.5°	1619.5	1615.0	1619.5	1616.5	1618.0	1613.5	1600.1	1595.6	1600.1	1604.6	1604.6
5°	1638.9	1635.9	1638.9	1638.9	1637.4	1634.4	1619.5	1616.5	1619.5	1621.0	1618.0
7.5°	1644.9	1640.4	1644.9	1641.9	1641.9	1638.9	1624.0	1621.0	1622.5	1627.0	1622.5
10°	1644.9	1640.4	1644.9	1643.4	1641.9	1638.9	1624.0	1618.0	1618.0	1622.5	1618.0
12.5°	1637.4	1634.4	1637.4	1634.4	1634.4	1631.4	1616.5	1610.5	1612.0	1613.5	1607.5
15°	1625.5	1621.0	1625.5	1622.5	1624.0	1619.5	1603.1	1597.1	1597.1	1600.1	1589.6
17.5°	1607.5	1601.6	1607.5	1606.0	1604.6	1601.6	1586.6	1580.7	1579.2	1580.7	1573.2
20°	1586.6	1582.1	1586.6	1585.1	1585.1	1579.2	1564.2	1556.7	1556.7	1556.7	1549.3
22.5°	1553.8	1549.3	1553.8	1556.7	1556.7	1555.3	1541.8	1531.4	1528.4	1528.4	1519.4
25°	1516.4	1511.9	1516.4	1516.4	1514.9	1516.4	1511.9	1506.0	1501.5	1497.0	1488.0
27.5°	1480.6	1477.6	1480.6	1477.6	1480.6	1476.1	1474.6	1473.1	1467.1	1462.6	1450.7
30°	1444.7	1441.7	1444.7	1441.7	1438.7	1435.7	1428.3	1425.3	1431.3	1428.3	1408.8
32.5°	1399.9	1396.9	1399.9	1399.9	1396.9	1396.9	1384.9	1380.5	1382.0	1390.9	1373.0
35°	1353.6	1349.1	1353.6	1352.1	1353.6	1349.1	1341.6	1340.1	1334.1	1344.6	1331.2
37.5°	1299.8	1295.3	1299.8	1299.8	1299.8	1302.8	1296.8	1292.3	1283.3	1296.8	1286.3
40°	1244.5	1238.5	1244.5	1243.0	1244.5	1247.5	1244.5	1241.5	1232.6	1243.0	1234.0
42.5°	1181.8	1180.3	1181.8	1183.2	1183.2	1189.2	1193.7	1187.7	1184.7	1177.3	1183.2
45°	1114.5	1111.5	1114.5	1117.5	1119.0	1122.0	1135.4	1135.4	1131.0	1119.0	1128.0
47.5°	1042.8	1035.3	1042.8	1051.8	1051.8	1056.3	1069.7	1080.2	1072.7	1057.8	1062.2
50°	966.6	968.1	966.6	972.6	972.6	989.0	999.5	1009.9	1017.4	999.5	978.6
52.5°	891.9	890.4	891.9	896.4	902.4	909.8	927.8	938.2	950.2	939.7	906.9
55°	817.2	820.2	817.2	818.7	821.7	826.2	853.1	863.5	885.9	872.5	838.1
57.5°	742.5	738.0	742.5	745.5	747.0	751.5	773.9	793.3	806.8	808.3	766.4
60°	655.9	649.9	655.9	669.3	672.3	675.3	696.2	714.1	726.1	730.6	687.2
62.5°	579.7	569.2	579.7	588.6	594.6	602.1	617.0	643.9	654.4	655.9	594.6
65°	499.0	494.5	499.0	516.9	518.4	527.4	543.8	563.2	585.6	582.7	494.5
67.5°	425.8	425.8	425.8	437.7	446.7	451.2	472.1	481.1	509.5	512.4	412.3
70°	358.6	357.1	358.6	367.5	373.5	384.0	403.4	413.8	436.2	443.7	334.7
72.5°	294.3	292.8	294.3	301.8	307.8	316.7	333.2	345.1	364.5	373.5	260.0
75°	237.5	234.6	237.5	243.5	242.0	254.0	267.4	279.4	297.3	303.3	192.7
77.5°	182.3	182.3	182.3	188.2	188.2	200.2	206.2	221.1	231.6	240.5	141.9
80°	136.0	134.5	136.0	137.4	137.4	143.4	153.9	164.3	173.3	173.3	97.1
82.5°	95.6	92.6	95.6	95.6	95.6	98.6	104.6	107.6	113.5	118.0	61.3
85°	59.8	59.8	59.8	61.3	59.8	62.7	64.2	67.2	67.2	64.2	37.4
87.5°	38.8	37.4	38.8	37.4	37.4	35.9	35.9	35.9	34.4	32.9	20.9
90°	11.7	11.7	11.7	11.7	11.7	15.5	20.8	23.4	20.1	13.5	8.7
92.5°	46.8	37.5	46.8	56.2	58.5	82.9	115.4	131.8	115.7	83.6	59.5
95°	163.3	135.2	163.3	191.5	198.6	260.9	343.8	385.3	325.4	205.6	115.7
97.5°	391.4	337.8	391.4	445.0	458.5	497.8	550.3	576.5	476.7	277.0	127.2
100°	564.0	500.1	564.0	628.0	643.9	641.0	637.1	635.2	524.5	302.9	136.8
102.5°	733.8	679.0	733.8	788.5	802.2	752.1	685.2	651.9	539.5	314.8	146.3
105°	950.2	920.7	950.2	979.6	986.9	874.6	724.9	650.0	541.2	323.6	160.5
107.5°	1091.8	1099.0	1091.8	1084.7	1083.0	926.3	717.4	613.0	517.1	325.3	181.4
110°	1145.9	1176.6	1145.9	1115.3	1107.7	932.6	699.0	582.3	495.8	322.8	193.0

TEST NUMBER: P934387

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1150.8	1197.8	1150.8	1103.7	1091.9	912.7	673.8	554.3	477.2	322.9	207.3
115°	1120.2	1185.5	1120.2	1055.0	1038.6	866.0	635.8	520.7	455.8	325.9	228.5
117.5°	1055.6	1128.0	1055.6	983.2	965.0	809.2	601.5	497.6	442.4	332.0	249.1
120°	1003.4	1073.8	1003.4	933.1	915.4	773.1	583.3	488.3	437.8	336.8	261.2
122.5°	952.7	1022.0	952.7	883.3	865.9	737.7	566.7	481.3	435.5	343.9	275.3
125°	880.2	944.1	880.2	816.2	800.3	691.4	546.2	473.6	433.6	353.5	293.4
127.5°	815.0	869.0	815.0	761.0	747.6	654.1	529.5	467.1	432.5	363.0	311.1
130°	776.7	826.5	776.7	726.9	714.4	631.2	520.1	464.6	433.1	370.0	322.7
132.5°	741.8	786.4	741.8	697.2	686.0	611.5	512.2	462.5	433.6	375.7	332.3
135°	694.1	732.6	694.1	655.7	646.0	583.7	500.5	458.9	433.2	381.9	343.3
137.5°	655.9	687.3	655.9	624.3	616.4	563.6	493.3	458.2	435.8	391.0	357.5
140°	629.5	659.0	629.5	600.1	592.7	547.2	486.4	456.1	436.2	396.7	367.0
142.5°	607.8	633.1	607.8	582.5	576.1	536.0	482.8	456.1	437.8	401.4	374.1
145°	575.2	594.3	575.2	556.0	551.2	518.4	474.8	453.0	437.8	407.7	385.0
147.5°	550.1	565.9	550.1	534.3	530.3	504.5	470.1	453.0	440.8	416.6	398.5
150°	534.4	547.2	534.4	521.4	518.2	496.5	467.5	453.0	442.4	421.4	405.6
152.5°	520.8	530.6	520.8	511.0	508.7	490.1	465.3	453.0	443.4	424.4	410.2
155°	505.4	511.7	505.4	498.9	497.3	482.6	462.8	453.0	445.7	431.2	420.3
157.5°	493.1	497.6	493.1	488.5	487.4	476.0	460.6	453.0	448.0	437.9	430.5
160°	485.7	488.3	485.7	483.2	482.6	472.7	459.6	453.0	449.0	441.0	435.1
162.5°	481.0	483.5	481.0	478.5	477.9	469.6	458.6	453.0	450.1	444.3	440.0
165°	474.1	476.7	474.1	471.5	470.8	464.8	457.0	453.0	451.7	449.1	447.1
167.5°	469.1	470.2	469.1	468.0	467.7	463.8	458.7	456.1	455.0	452.8	451.1
170°	467.7	467.7	467.7	467.7	467.7	463.8	458.7	456.1	456.0	455.9	455.8
172.5°	464.0	463.1	464.0	465.0	465.2	462.1	458.1	456.1	456.1	456.1	456.1
175°	461.8	461.8	461.8	461.8	461.8	460.0	457.4	456.1	456.7	458.0	458.9
177.5°	460.0	458.9	460.0	460.9	461.2	459.8	457.7	456.7	457.2	458.2	458.9
180°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9

TEST NUMBER: P934387

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2
2.5°	1601.6	1592.6	1592.6	1577.7	1571.7	1567.2	1559.7	1537.3	1531.4	1525.4	1534.3
5°	1615.0	1598.6	1586.6	1559.7	1537.3	1528.4	1500.0	1446.2	1410.3	1383.4	1368.5
7.5°	1618.0	1597.1	1574.7	1532.8	1479.1	1455.2	1368.5	1269.9	1243.0	1219.1	1204.2
10°	1615.0	1591.1	1559.7	1497.0	1370.0	1328.2	1241.5	1177.3	1160.8	1156.4	1160.8
12.5°	1604.6	1582.1	1538.8	1434.2	1256.5	1228.1	1177.3	1139.9	1136.9	1144.4	1184.7
15°	1586.6	1565.7	1514.9	1350.6	1193.7	1172.8	1136.9	1123.5	1139.9	1192.2	1313.2
17.5°	1568.7	1544.8	1482.0	1268.4	1145.9	1131.0	1105.6	1132.5	1225.1	1295.3	1335.6
20°	1544.8	1516.4	1444.7	1208.6	1111.5	1098.1	1086.1	1207.2	1277.4	1302.8	1325.2
22.5°	1516.4	1486.5	1393.9	1166.8	1075.7	1065.2	1072.7	1249.0	1277.4	1295.3	1314.7
25°	1479.1	1453.7	1334.1	1133.9	1047.3	1035.3	1063.7	1244.5	1260.9	1265.4	1304.3
27.5°	1444.7	1411.8	1271.4	1104.1	1012.9	1008.4	1071.2	1225.1	1237.0	1241.5	1283.3
30°	1402.9	1353.6	1201.2	1072.7	977.1	975.6	1072.7	1201.2	1198.2	1210.1	1252.0
32.5°	1359.5	1266.9	1122.0	1033.8	942.7	941.2	1062.2	1165.3	1162.3	1178.8	1210.1
35°	1319.2	1199.7	1014.4	989.0	899.4	900.9	1036.8	1123.5	1125.0	1139.9	1159.3
37.5°	1277.4	1141.4	896.4	939.7	857.6	857.6	1002.5	1084.6	1081.7	1086.1	1113.0
40°	1228.1	1050.3	791.8	875.5	818.7	814.2	960.6	1042.8	1032.4	1030.9	1068.2
42.5°	1175.8	950.2	714.1	790.3	773.9	767.9	909.8	992.0	972.6	977.1	1024.9
45°	1119.0	923.3	654.4	667.8	727.6	723.1	854.6	933.8	920.3	932.3	981.6
47.5°	1062.2	869.5	635.0	554.3	678.3	676.8	793.3	877.0	869.5	881.5	933.8
50°	984.5	809.7	633.5	475.1	623.0	629.0	720.1	821.7	821.7	832.2	887.4
52.5°	884.4	736.5	575.2	430.3	558.8	576.7	655.9	773.9	776.9	787.3	836.6
55°	793.3	660.3	533.4	395.9	482.6	521.4	593.1	724.6	730.6	741.0	785.8
57.5°	709.6	549.8	524.4	355.6	412.3	449.7	537.8	676.8	679.8	688.7	732.1
60°	620.0	397.4	481.1	312.2	351.1	379.5	487.0	620.0	630.5	636.4	673.8
62.5°	518.4	288.3	436.2	282.4	321.2	327.2	445.2	566.2	579.7	584.2	606.6
65°	369.0	242.0	370.5	257.0	289.8	291.3	400.4	510.9	522.9	530.4	546.8
67.5°	249.5	197.2	282.4	233.1	265.9	267.4	357.1	446.7	463.1	469.1	479.6
70°	173.3	131.5	209.2	207.7	239.0	242.0	310.8	388.4	403.4	407.9	413.8
72.5°	127.0	106.1	173.3	186.8	210.7	213.6	262.9	322.7	337.6	342.1	345.1
75°	97.1	112.0	140.4	162.8	179.3	180.8	215.1	262.9	273.4	276.4	277.9
77.5°	77.7	104.6	103.1	131.5	146.4	143.4	168.8	203.2	212.1	212.1	212.1
80°	58.3	82.2	77.7	94.1	107.6	104.6	121.0	144.9	147.9	150.9	149.4
82.5°	43.3	52.3	52.3	59.8	71.7	68.7	80.7	94.1	94.1	94.1	97.1
85°	26.9	29.9	23.9	31.4	40.3	38.8	44.8	50.8	52.3	52.3	49.3
87.5°	16.4	13.4	7.5	12.0	17.9	17.9	20.9	22.4	20.9	20.9	20.9
90°	8.1	5.6	3.1	5.6	8.1	8.7	13.5	20.1	23.4	20.8	15.5
92.5°	54.2	33.3	12.4	33.3	54.2	59.5	83.6	115.7	131.8	115.4	82.9
95°	106.2	67.8	29.6	67.8	106.2	115.7	205.6	325.4	385.3	343.8	260.9
97.5°	118.7	85.0	51.1	85.0	118.7	127.2	277.0	476.7	576.5	550.3	497.8
100°	129.1	98.4	67.7	98.4	129.1	136.8	302.9	524.5	635.2	637.1	641.0
102.5°	139.1	110.6	81.9	110.6	139.1	146.3	314.8	539.5	651.9	685.2	752.1
105°	154.4	130.2	106.0	130.2	154.4	160.5	323.6	541.2	650.0	724.9	874.6
107.5°	175.7	153.2	130.6	153.2	175.7	181.4	325.3	517.1	613.0	717.4	926.3
110°	187.9	167.5	147.2	167.5	187.9	193.0	322.8	495.8	582.3	699.0	932.6

TEST NUMBER: P934387

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	202.4	183.0	163.5	183.0	202.4	207.3	322.9	477.2	554.3	673.8	912.7
115°	224.0	206.1	188.1	206.1	224.0	228.5	325.9	455.8	520.7	635.8	866.0
117.5°	245.0	228.8	212.4	228.8	245.0	249.1	332.0	442.4	497.6	601.5	809.2
120°	257.3	241.9	226.6	241.9	257.3	261.2	336.8	437.8	488.3	583.3	773.1
122.5°	271.4	256.0	240.5	256.0	271.4	275.3	343.9	435.5	481.3	566.7	737.7
125°	289.9	275.8	261.7	275.8	289.9	293.4	353.5	433.6	473.6	546.2	691.4
127.5°	307.5	293.2	279.0	293.2	307.5	311.1	363.0	432.5	467.1	529.5	654.1
130°	318.9	303.6	288.2	303.6	318.9	322.7	370.0	433.1	464.6	520.1	631.2
132.5°	328.5	313.1	297.8	313.1	328.5	332.3	375.7	433.6	462.5	512.2	611.5
135°	339.8	325.9	311.9	325.9	339.8	343.3	381.9	433.2	458.9	500.5	583.7
137.5°	354.0	340.2	326.4	340.2	354.0	357.5	391.0	435.8	458.2	493.3	563.6
140°	363.8	351.2	338.4	351.2	363.8	367.0	396.7	436.2	456.1	486.4	547.2
142.5°	371.1	359.4	347.6	359.4	371.1	374.1	401.4	437.8	456.1	482.8	536.0
145°	382.4	372.1	361.8	372.1	382.4	385.0	407.7	437.8	453.0	474.8	518.4
147.5°	396.0	386.0	376.0	386.0	396.0	398.5	416.6	440.8	453.0	470.1	504.5
150°	403.3	394.3	385.3	394.3	403.3	405.6	421.4	442.4	453.0	467.5	496.5
152.5°	408.5	401.6	394.7	401.6	408.5	410.2	424.4	443.4	453.0	465.3	490.1
155°	419.0	414.0	409.0	414.0	419.0	420.3	431.2	445.7	453.0	462.8	482.6
157.5°	429.3	424.3	419.4	424.3	429.3	430.5	437.9	448.0	453.0	460.6	476.0
160°	434.1	430.3	426.5	430.3	434.1	435.1	441.0	449.0	453.0	459.6	472.7
162.5°	439.3	436.4	433.6	436.4	439.3	440.0	444.3	450.1	453.0	458.6	469.6
165°	446.4	443.8	441.2	443.8	446.4	447.1	449.1	451.7	453.0	457.0	464.8
167.5°	450.8	449.5	448.3	449.5	450.8	451.1	452.8	455.0	456.1	458.7	463.8
170°	455.5	454.2	453.0	454.2	455.5	455.8	455.9	456.0	456.1	458.7	463.8
172.5°	456.0	455.8	455.5	455.8	456.0	456.1	456.1	456.1	456.1	458.1	462.1
175°	458.9	458.9	458.9	458.9	458.9	458.9	458.0	456.7	456.1	457.4	460.0
177.5°	458.9	458.9	458.9	458.9	458.9	458.9	458.2	457.2	456.7	457.7	459.8
180°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9

TEST NUMBER: P934387

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2
2.5°	1523.9	1519.4	1525.4	1508.9	1525.4	1519.4	1523.9	1534.3	1525.4	1531.4	1537.3
5°	1337.1	1329.7	1305.8	1286.3	1305.8	1329.7	1337.1	1368.5	1383.4	1410.3	1446.2
7.5°	1195.2	1189.2	1183.2	1171.3	1183.2	1189.2	1195.2	1204.2	1219.1	1243.0	1269.9
10°	1163.8	1165.3	1174.3	1172.8	1174.3	1165.3	1163.8	1160.8	1156.4	1160.8	1177.3
12.5°	1244.5	1257.9	1307.2	1304.3	1307.2	1257.9	1244.5	1184.7	1144.4	1136.9	1139.9
15°	1337.1	1341.6	1352.1	1353.6	1352.1	1341.6	1337.1	1313.2	1192.2	1139.9	1123.5
17.5°	1346.1	1347.6	1355.1	1355.1	1355.1	1347.6	1346.1	1335.6	1295.3	1225.1	1132.5
20°	1338.6	1341.6	1356.6	1359.5	1356.6	1341.6	1338.6	1325.2	1302.8	1277.4	1207.2
22.5°	1335.6	1341.6	1353.6	1352.1	1353.6	1341.6	1335.6	1314.7	1295.3	1277.4	1249.0
25°	1320.7	1320.7	1322.2	1323.7	1322.2	1320.7	1320.7	1304.3	1265.4	1260.9	1244.5
27.5°	1289.3	1292.3	1301.3	1299.8	1301.3	1292.3	1289.3	1283.3	1241.5	1237.0	1225.1
30°	1260.9	1257.9	1250.5	1244.5	1250.5	1257.9	1260.9	1252.0	1210.1	1198.2	1201.2
32.5°	1213.1	1205.7	1198.2	1193.7	1198.2	1205.7	1213.1	1210.1	1178.8	1162.3	1165.3
35°	1156.4	1157.8	1156.4	1151.9	1156.4	1157.8	1156.4	1159.3	1139.9	1125.0	1123.5
37.5°	1116.0	1119.0	1117.5	1111.5	1117.5	1119.0	1116.0	1113.0	1086.1	1081.7	1084.6
40°	1074.2	1075.7	1074.2	1069.7	1074.2	1075.7	1074.2	1068.2	1030.9	1032.4	1042.8
42.5°	1033.8	1032.4	1027.9	1024.9	1027.9	1032.4	1033.8	1024.9	977.1	972.6	992.0
45°	987.5	989.0	980.1	975.6	980.1	989.0	987.5	981.6	932.3	920.3	933.8
47.5°	941.2	941.2	933.8	929.3	933.8	941.2	941.2	933.8	881.5	869.5	877.0
50°	891.9	890.4	880.0	878.5	880.0	890.4	891.9	887.4	832.2	821.7	821.7
52.5°	835.1	835.1	836.6	839.6	836.6	835.1	835.1	836.6	787.3	776.9	773.9
55°	785.8	787.3	797.8	800.8	797.8	787.3	785.8	785.8	741.0	730.6	724.6
57.5°	735.0	735.0	742.5	742.5	742.5	735.0	735.0	732.1	688.7	679.8	676.8
60°	676.8	679.8	685.7	684.3	685.7	679.8	676.8	673.8	636.4	630.5	620.0
62.5°	615.5	618.5	620.0	617.0	620.0	618.5	615.5	606.6	584.2	579.7	566.2
65°	551.3	554.3	555.8	552.8	555.8	554.3	551.3	546.8	530.4	522.9	510.9
67.5°	485.6	484.1	482.6	488.5	482.6	484.1	485.6	479.6	469.1	463.1	446.7
70°	418.3	418.3	416.8	419.8	416.8	418.3	418.3	413.8	407.9	403.4	388.4
72.5°	346.6	345.1	351.1	346.6	351.1	345.1	346.6	345.1	342.1	337.6	322.7
75°	276.4	279.4	276.4	280.9	276.4	279.4	276.4	277.9	276.4	273.4	262.9
77.5°	210.7	213.6	210.7	210.7	210.7	213.6	210.7	212.1	212.1	212.1	203.2
80°	149.4	147.9	147.9	146.4	147.9	147.9	149.4	149.4	150.9	147.9	144.9
82.5°	95.6	94.1	94.1	97.1	94.1	94.1	95.6	97.1	94.1	94.1	94.1
85°	52.3	53.8	50.8	50.8	50.8	53.8	52.3	49.3	52.3	52.3	50.8
87.5°	19.4	17.9	17.9	17.9	17.9	17.9	19.4	20.9	20.9	20.9	22.4
90°	11.7	11.7	11.7	11.7	11.7	11.7	11.7	15.5	20.8	23.4	20.1
92.5°	58.5	56.2	46.8	37.5	46.8	56.2	58.5	82.9	115.4	131.8	115.7
95°	198.6	191.5	163.3	135.2	163.3	191.5	198.6	260.9	343.8	385.3	325.4
97.5°	458.5	445.0	391.4	337.8	391.4	445.0	458.5	497.8	550.3	576.5	476.7
100°	643.9	628.0	564.0	500.1	564.0	628.0	643.9	641.0	637.1	635.2	524.5
102.5°	802.2	788.5	733.8	679.0	733.8	788.5	802.2	752.1	685.2	651.9	539.5
105°	986.9	979.6	950.2	920.7	950.2	979.6	986.9	874.6	724.9	650.0	541.2
107.5°	1083.0	1084.7	1091.8	1099.0	1091.8	1084.7	1083.0	926.3	717.4	613.0	517.1
110°	1107.7	1115.3	1145.9	1176.6	1145.9	1115.3	1107.7	932.6	699.0	582.3	495.8

TEST NUMBER: P934387

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1091.9	1103.7	1150.8	1197.8	1150.8	1103.7	1091.9	912.7	673.8	554.3	477.2
115°	1038.6	1055.0	1120.2	1185.5	1120.2	1055.0	1038.6	866.0	635.8	520.7	455.8
117.5°	965.0	983.2	1055.6	1128.0	1055.6	983.2	965.0	809.2	601.5	497.6	442.4
120°	915.4	933.1	1003.4	1073.8	1003.4	933.1	915.4	773.1	583.3	488.3	437.8
122.5°	865.9	883.3	952.7	1022.0	952.7	883.3	865.9	737.7	566.7	481.3	435.5
125°	800.3	816.2	880.2	944.1	880.2	816.2	800.3	691.4	546.2	473.6	433.6
127.5°	747.6	761.0	815.0	869.0	815.0	761.0	747.6	654.1	529.5	467.1	432.5
130°	714.4	726.9	776.7	826.5	776.7	726.9	714.4	631.2	520.1	464.6	433.1
132.5°	686.0	697.2	741.8	786.4	741.8	697.2	686.0	611.5	512.2	462.5	433.6
135°	646.0	655.7	694.1	732.6	694.1	655.7	646.0	583.7	500.5	458.9	433.2
137.5°	616.4	624.3	655.9	687.3	655.9	624.3	616.4	563.6	493.3	458.2	435.8
140°	592.7	600.1	629.5	659.0	629.5	600.1	592.7	547.2	486.4	456.1	436.2
142.5°	576.1	582.5	607.8	633.1	607.8	582.5	576.1	536.0	482.8	456.1	437.8
145°	551.2	556.0	575.2	594.3	575.2	556.0	551.2	518.4	474.8	453.0	437.8
147.5°	530.3	534.3	550.1	565.9	550.1	534.3	530.3	504.5	470.1	453.0	440.8
150°	518.2	521.4	534.4	547.2	534.4	521.4	518.2	496.5	467.5	453.0	442.4
152.5°	508.7	511.0	520.8	530.6	520.8	511.0	508.7	490.1	465.3	453.0	443.4
155°	497.3	498.9	505.4	511.7	505.4	498.9	497.3	482.6	462.8	453.0	445.7
157.5°	487.4	488.5	493.1	497.6	493.1	488.5	487.4	476.0	460.6	453.0	448.0
160°	482.6	483.2	485.7	488.3	485.7	483.2	482.6	472.7	459.6	453.0	449.0
162.5°	477.9	478.5	481.0	483.5	481.0	478.5	477.9	469.6	458.6	453.0	450.1
165°	470.8	471.5	474.1	476.7	474.1	471.5	470.8	464.8	457.0	453.0	451.7
167.5°	467.7	468.0	469.1	470.2	469.1	468.0	467.7	463.8	458.7	456.1	455.0
170°	467.7	467.7	467.7	467.7	467.7	467.7	467.7	463.8	458.7	456.1	456.0
172.5°	465.2	465.0	464.0	463.1	464.0	465.0	465.2	462.1	458.1	456.1	456.1
175°	461.8	461.8	461.8	461.8	461.8	461.8	461.8	460.0	457.4	456.1	456.7
177.5°	461.2	460.9	460.0	458.9	460.0	460.9	461.2	459.8	457.7	456.7	457.2
180°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9

TEST NUMBER: P934387

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1579.2	1579.2	1579.2	1579.2	1579.2
2.5°	1559.7	1567.2	1571.7	1577.7	1592.6
5°	1500.0	1528.4	1537.3	1559.7	1586.6
7.5°	1368.5	1455.2	1479.1	1532.8	1574.7
10°	1241.5	1328.2	1370.0	1497.0	1559.7
12.5°	1177.3	1228.1	1256.5	1434.2	1538.8
15°	1136.9	1172.8	1193.7	1350.6	1514.9
17.5°	1105.6	1131.0	1145.9	1268.4	1482.0
20°	1086.1	1098.1	1111.5	1208.6	1444.7
22.5°	1072.7	1065.2	1075.7	1166.8	1393.9
25°	1063.7	1035.3	1047.3	1133.9	1334.1
27.5°	1071.2	1008.4	1012.9	1104.1	1271.4
30°	1072.7	975.6	977.1	1072.7	1201.2
32.5°	1062.2	941.2	942.7	1033.8	1122.0
35°	1036.8	900.9	899.4	989.0	1014.4
37.5°	1002.5	857.6	857.6	939.7	896.4
40°	960.6	814.2	818.7	875.5	791.8
42.5°	909.8	767.9	773.9	790.3	714.1
45°	854.6	723.1	727.6	667.8	654.4
47.5°	793.3	676.8	678.3	554.3	635.0
50°	720.1	629.0	623.0	475.1	633.5
52.5°	655.9	576.7	558.8	430.3	575.2
55°	593.1	521.4	482.6	395.9	533.4
57.5°	537.8	449.7	412.3	355.6	524.4
60°	487.0	379.5	351.1	312.2	481.1
62.5°	445.2	327.2	321.2	282.4	436.2
65°	400.4	291.3	289.8	257.0	370.5
67.5°	357.1	267.4	265.9	233.1	282.4
70°	310.8	242.0	239.0	207.7	209.2
72.5°	262.9	213.6	210.7	186.8	173.3
75°	215.1	180.8	179.3	162.8	140.4
77.5°	168.8	143.4	146.4	131.5	103.1
80°	121.0	104.6	107.6	94.1	77.7
82.5°	80.7	68.7	71.7	59.8	52.3
85°	44.8	38.8	40.3	31.4	23.9
87.5°	20.9	17.9	17.9	12.0	7.5
90°	13.5	8.7	8.1	5.6	3.1
92.5°	83.6	59.5	54.2	33.3	12.4
95°	205.6	115.7	106.2	67.8	29.6
97.5°	277.0	127.2	118.7	85.0	51.1
100°	302.9	136.8	129.1	98.4	67.7
102.5°	314.8	146.3	139.1	110.6	81.9
105°	323.6	160.5	154.4	130.2	106.0
107.5°	325.3	181.4	175.7	153.2	130.6
110°	322.8	193.0	187.9	167.5	147.2



TEST NUMBER: P934387

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	322.9	207.3	202.4	183.0	163.5
115°	325.9	228.5	224.0	206.1	188.1
117.5°	332.0	249.1	245.0	228.8	212.4
120°	336.8	261.2	257.3	241.9	226.6
122.5°	343.9	275.3	271.4	256.0	240.5
125°	353.5	293.4	289.9	275.8	261.7
127.5°	363.0	311.1	307.5	293.2	279.0
130°	370.0	322.7	318.9	303.6	288.2
132.5°	375.7	332.3	328.5	313.1	297.8
135°	381.9	343.3	339.8	325.9	311.9
137.5°	391.0	357.5	354.0	340.2	326.4
140°	396.7	367.0	363.8	351.2	338.4
142.5°	401.4	374.1	371.1	359.4	347.6
145°	407.7	385.0	382.4	372.1	361.8
147.5°	416.6	398.5	396.0	386.0	376.0
150°	421.4	405.6	403.3	394.3	385.3
152.5°	424.4	410.2	408.5	401.6	394.7
155°	431.2	420.3	419.0	414.0	409.0
157.5°	437.9	430.5	429.3	424.3	419.4
160°	441.0	435.1	434.1	430.3	426.5
162.5°	444.3	440.0	439.3	436.4	433.6
165°	449.1	447.1	446.4	443.8	441.2
167.5°	452.8	451.1	450.8	449.5	448.3
170°	455.9	455.8	455.5	454.2	453.0
172.5°	456.1	456.1	456.0	455.8	455.5
175°	458.0	458.9	458.9	458.9	458.9
177.5°	458.2	458.9	458.9	458.9	458.9
180°	458.9	458.9	458.9	458.9	458.9

TEST NUMBER: P934387

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.42	14.36	14.31	15.27	16.42	16.25	17.18	17.13	18.09	19.24
	3H	13.91	14.75	14.80	15.66	16.84	17.60	18.44	18.50	19.35	20.53
	4H	14.10	14.90	15.01	15.82	17.00	18.04	18.84	18.96	19.76	20.95
	6H	14.22	14.96	15.15	15.88	17.08	18.33	19.06	19.26	19.99	21.19
	8H	14.23	14.92	15.16	15.87	17.07	18.41	19.10	19.34	20.05	21.25
	12H	14.20	14.86	15.14	15.80	17.03	18.45	19.11	19.39	20.05	21.28
4H	2H	14.46	15.26	15.38	16.18	17.37	16.67	17.46	17.59	18.38	19.57
	3H	15.50	16.16	16.43	17.11	18.31	18.18	18.84	19.11	19.79	20.99
	4H	15.78	16.38	16.72	17.33	18.56	18.71	19.31	19.65	20.26	21.49
	6H	15.91	16.43	16.86	17.40	18.63	19.08	19.60	20.03	20.57	21.80
	8H	15.91	16.40	16.87	17.37	18.61	19.18	19.67	20.14	20.63	21.88
	12H	15.89	16.32	16.86	17.31	18.55	19.24	19.68	20.22	20.66	21.91
8H	4H	16.24	16.72	17.19	17.69	18.93	18.84	19.32	19.79	20.29	21.53
	6H	16.50	16.90	17.48	17.91	19.15	19.28	19.68	20.26	20.69	21.93
	8H	16.54	16.90	17.53	17.89	19.15	19.43	19.78	20.42	20.78	22.04
	12H	16.53	16.84	17.53	17.83	19.14	19.53	19.84	20.52	20.83	22.14
12H	4H	16.25	16.68	17.22	17.67	18.91	18.81	19.25	19.78	20.23	21.47
	6H	16.56	16.92	17.55	17.91	19.17	19.27	19.63	20.26	20.63	21.88
	8H	16.63	16.94	17.63	17.93	19.24	19.44	19.75	20.43	20.74	22.05

END OF REPORT