

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934392

Luminaire Tested: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934392
REPORT IS A COMBINATION OF REPORTS P933696 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9427.2 lumens
Efficiency: N/A
Efficacy: 129.5 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934392

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K

Luminous Intensity Polar Plot



TEST NUMBER: P934392

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	95	91	88	93	89	86	83	77	75	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	57	60	55	50	51	48	44	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9768	9768	9768	9768
5°	9841	9861	9841	7753
10°	9775	9713	9775	6944
15°	9669	9503	9669	7935
20°	9467	9254	9467	7952
25°	9053	8890	9053	7783
30°	8518	8588	8518	7413
35°	7594	8206	7594	7006
40°	6328	7757	6328	6699
45°	5654	7230	5654	6346
50°	6007	6603	6007	5992
55°	5651	5927	5651	5787
60°	5826	5034	5826	5300
65°	5282	4162	5282	4651
70°	3658	3316	3658	3899
75°	3206	2451	3206	2936
80°	2585	1621	2585	1765
85°	1486	859	1486	729

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 8665 cd/sqm

TEST NUMBER: P934392

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.1	2.0
10°-20°	539.6	5.7
20°-30°	834.1	8.8
30°-40°	995.8	10.6
40°-50°	1001.6	10.6
50°-60°	871.6	9.2
60°-70°	618.0	6.6
70°-80°	326.9	3.5
80°-90°	83.8	0.9
90°-100°	298.2	3.2
100°-110°	784.0	8.3
110°-120°	812.9	8.6
120°-130°	652.0	6.9
130°-140°	511.6	5.4
140°-150°	392.7	4.2
150°-160°	282.8	3.0
160°-170°	173.0	1.8
170°-180°	58.5	0.6
0°-30°	1563.8	16.6
0°-40°	2559.6	27.2
0°-60°	4432.8	47.0
0°-90°	5461.4	57.9
90°-120°	1895.1	20.1
90°-150°	3451.4	36.6
90°-180°	3966.0	42.1
0°-180°	9427.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2105	2105	2105	2105	2105	
5°	2115	2181	2115	1715	2115	201
15°	2020	2161	2020	1805	2020	568
25°	1779	2016	1779	1765	1779	817
35°	1352	1799	1352	1536	1352	837
45°	872	1482	872	1301	872	699
55°	711	1094	711	1068	711	653
65°	494	659	494	737	494	472
75°	187	313	187	374	187	197
85°	32	80	32	68	32	43
90°	4	16	4	16	4	5
95°	39	180	39	180	39	44
105°	141	1228	141	1228	141	150
115°	251	1581	251	1581	251	248
125°	349	1259	349	1259	349	310
135°	416	977	416	977	416	322
145°	482	792	482	792	482	302
155°	545	682	545	682	545	251
165°	588	636	588	636	588	166
175°	612	616	612	616	612	58
180°	612	612	612	612	612	

TEST NUMBER: P934392

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4
2.5°	2123.4	2123.4	2135.3	2139.3	2139.3	2133.3	2127.4	2133.3	2151.3	2157.2	2155.2
5°	2115.4	2131.3	2153.3	2157.2	2161.2	2159.2	2155.2	2159.2	2179.1	2183.1	2185.1
7.5°	2099.5	2129.3	2157.2	2163.2	2169.2	2163.2	2161.2	2165.2	2185.1	2189.1	2189.1
10°	2079.5	2121.4	2153.3	2157.2	2163.2	2157.2	2157.2	2165.2	2185.1	2189.1	2191.1
12.5°	2051.7	2109.4	2139.3	2143.3	2151.3	2149.3	2147.3	2155.2	2175.2	2179.1	2179.1
15°	2019.8	2087.5	2115.4	2119.4	2133.3	2129.3	2129.3	2137.3	2159.2	2165.2	2163.2
17.5°	1976.0	2059.6	2091.5	2097.5	2107.4	2105.4	2107.4	2115.4	2135.3	2139.3	2141.3
20°	1926.2	2021.8	2059.6	2065.6	2075.6	2075.6	2075.6	2085.5	2105.4	2113.4	2113.4
22.5°	1858.4	1981.9	2021.8	2025.8	2037.7	2037.7	2041.7	2055.6	2073.6	2075.6	2075.6
25°	1778.8	1938.1	1972.0	1983.9	1995.9	2001.9	2007.8	2015.8	2021.8	2019.8	2021.8
27.5°	1695.1	1882.3	1926.2	1934.1	1950.1	1956.0	1964.0	1966.0	1968.0	1974.0	1970.0
30°	1601.5	1804.7	1870.4	1878.4	1904.3	1908.2	1900.3	1904.3	1914.2	1918.2	1922.2
32.5°	1495.9	1689.1	1812.6	1830.5	1854.5	1842.5	1840.5	1846.5	1862.4	1862.4	1866.4
35°	1352.5	1599.5	1758.8	1774.8	1792.7	1778.8	1786.7	1788.7	1798.7	1804.7	1802.7
37.5°	1195.1	1521.8	1703.1	1715.0	1729.0	1711.0	1723.0	1729.0	1736.9	1732.9	1732.9
40°	1055.8	1400.3	1637.3	1645.3	1657.2	1643.3	1655.3	1659.2	1663.2	1659.2	1657.2
42.5°	952.2	1266.8	1567.6	1577.6	1569.6	1579.6	1583.5	1591.5	1585.5	1577.6	1577.6
45°	872.5	1231.0	1491.9	1503.9	1491.9	1507.8	1513.8	1513.8	1495.9	1491.9	1489.9
47.5°	846.6	1159.3	1416.2	1416.2	1410.2	1430.2	1440.1	1426.2	1408.2	1402.3	1402.3
50°	844.6	1079.7	1312.6	1304.7	1332.5	1356.5	1346.5	1332.5	1318.6	1296.7	1296.7
52.5°	766.9	982.1	1179.3	1209.0	1252.9	1266.8	1250.9	1236.9	1213.0	1203.1	1195.1
55°	711.1	880.5	1057.8	1117.5	1163.3	1181.3	1151.4	1137.4	1101.6	1095.6	1091.6
57.5°	699.2	733.1	946.2	1021.9	1077.7	1075.7	1057.8	1031.9	1002.0	996.0	994.0
60°	641.4	529.9	826.7	916.3	974.1	968.1	952.2	928.3	900.4	896.4	892.4
62.5°	581.7	384.5	691.2	792.8	874.5	872.5	858.6	822.7	802.8	792.8	784.8
65°	494.0	322.7	492.0	659.4	776.9	780.9	751.0	725.1	703.2	691.2	689.2
67.5°	376.5	262.9	332.7	549.8	683.3	679.3	641.4	629.5	601.6	595.6	583.7
70°	278.9	175.3	231.1	446.2	591.6	581.7	551.8	537.8	511.9	498.0	490.0
72.5°	231.1	141.4	169.3	346.6	498.0	486.0	460.2	444.2	422.3	410.4	402.4
75°	187.2	149.4	129.5	257.0	404.4	396.4	372.5	356.6	338.6	322.7	324.7
77.5°	137.4	139.4	103.6	189.2	320.7	308.8	294.8	274.9	266.9	251.0	251.0
80°	103.6	109.6	77.7	129.5	231.1	231.1	219.1	205.2	191.2	183.3	183.3
82.5°	69.7	69.7	57.8	81.7	157.4	151.4	143.4	139.4	131.5	127.5	127.5
85°	31.9	39.8	35.9	49.8	85.7	89.6	89.6	85.7	83.7	79.7	81.7
87.5°	10.0	17.9	21.9	27.9	43.8	45.8	47.8	47.8	47.8	49.8	49.8
90°	4.1	7.4	10.7	11.5	18.0	26.8	31.2	27.7	20.8	15.6	15.6
92.5°	16.4	44.3	72.3	79.3	111.5	154.3	175.7	154.0	110.6	78.0	74.9
95°	39.4	90.5	141.6	154.4	274.1	433.8	513.6	458.4	347.8	264.8	255.5
97.5°	68.1	113.1	158.3	169.5	369.2	635.4	768.6	733.7	663.7	611.3	593.4
100°	90.3	131.2	172.0	182.3	403.9	699.3	847.0	849.6	854.7	858.5	837.1
102.5°	109.3	147.4	185.5	195.0	419.7	719.4	869.2	913.7	1002.8	1069.5	1051.3
105°	141.2	173.5	205.9	213.9	431.6	721.7	866.7	966.5	1166.2	1315.9	1306.1
107.5°	174.1	204.2	234.3	241.8	433.7	689.5	817.4	956.7	1235.1	1444.0	1446.4
110°	196.2	223.4	250.7	257.5	430.5	661.0	776.4	932.1	1243.3	1476.8	1487.0

TEST NUMBER: P934392

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	218.0	243.9	269.8	276.3	430.6	636.2	739.0	898.3	1216.9	1455.9	1471.6
115°	250.9	274.8	298.7	304.7	434.6	607.8	694.3	847.8	1154.7	1384.8	1406.6
117.5°	283.3	305.0	326.7	332.2	442.6	589.8	663.4	802.0	1079.0	1286.7	1310.8
120°	302.2	322.6	343.1	348.2	449.2	583.9	651.2	777.7	1030.8	1220.6	1244.0
122.5°	320.6	341.2	361.8	367.0	458.6	580.7	641.7	755.7	983.6	1154.6	1177.7
125°	349.0	367.7	386.5	391.2	471.3	578.1	631.5	728.3	921.9	1067.1	1088.4
127.5°	372.0	390.9	409.9	414.6	484.1	576.6	622.8	706.0	872.2	996.9	1014.8
130°	384.3	404.7	425.2	430.3	493.3	577.5	619.5	693.5	841.5	952.5	969.1
132.5°	397.0	417.4	437.9	443.0	500.9	578.1	616.7	683.0	815.4	914.7	929.6
135°	415.9	434.6	453.1	457.8	509.1	577.5	611.7	667.2	778.2	861.3	874.2
137.5°	435.3	453.7	472.1	476.7	521.4	581.1	610.9	657.9	751.7	822.0	832.5
140°	451.2	468.2	485.2	489.4	529.0	581.7	608.1	648.6	729.6	790.3	800.1
142.5°	463.5	479.2	494.9	498.8	535.3	583.8	608.1	643.6	714.8	768.2	776.7
145°	482.5	496.1	509.9	513.2	543.5	583.9	604.0	633.1	691.3	734.9	741.3
147.5°	501.3	514.6	528.0	531.3	555.5	587.8	604.0	626.9	672.6	707.0	712.2
150°	513.6	525.7	537.7	540.7	561.8	589.9	604.0	623.3	662.0	691.0	695.3
152.5°	526.4	535.5	544.6	546.9	565.9	591.3	604.0	620.5	653.5	678.3	681.6
155°	545.2	552.0	558.8	560.4	575.0	594.3	604.0	617.1	643.3	663.0	665.2
157.5°	559.2	565.7	572.3	574.0	584.0	597.3	604.0	614.1	634.6	649.9	651.4
160°	568.6	573.8	578.9	580.2	588.1	598.7	604.0	612.7	630.2	643.3	644.2
162.5°	578.1	582.0	585.7	586.7	592.5	600.2	604.0	611.3	626.2	637.2	638.0
165°	588.3	591.8	595.2	596.1	598.7	602.2	604.0	609.3	619.8	627.8	628.7
167.5°	597.8	599.4	601.1	601.5	603.7	606.6	608.1	611.5	618.5	623.7	624.1
170°	604.0	605.6	607.3	607.7	607.8	608.0	608.1	611.5	618.5	623.7	623.7
172.5°	607.3	607.7	608.0	608.1	608.1	608.1	608.1	610.8	616.3	620.4	620.1
175°	611.7	611.7	611.7	611.7	610.5	608.9	608.1	609.8	613.2	615.8	615.8
177.5°	611.7	611.7	611.7	611.7	610.7	609.5	608.9	610.2	612.9	615.0	614.6
180°	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7

TEST NUMBER: P934392

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4
2.5°	2159.2	2153.3	2159.2	2155.2	2157.2	2151.3	2133.3	2127.4	2133.3	2139.3	2139.3
5°	2185.1	2181.1	2185.1	2185.1	2183.1	2179.1	2159.2	2155.2	2159.2	2161.2	2157.2
7.5°	2193.1	2187.1	2193.1	2189.1	2189.1	2185.1	2165.2	2161.2	2163.2	2169.2	2163.2
10°	2193.1	2187.1	2193.1	2191.1	2189.1	2185.1	2165.2	2157.2	2157.2	2163.2	2157.2
12.5°	2183.1	2179.1	2183.1	2179.1	2179.1	2175.2	2155.2	2147.3	2149.3	2151.3	2143.3
15°	2167.2	2161.2	2167.2	2163.2	2165.2	2159.2	2137.3	2129.3	2129.3	2133.3	2119.4
17.5°	2143.3	2135.3	2143.3	2141.3	2139.3	2135.3	2115.4	2107.4	2105.4	2107.4	2097.5
20°	2115.4	2109.4	2115.4	2113.4	2113.4	2105.4	2085.5	2075.6	2075.6	2075.6	2065.6
22.5°	2071.6	2065.6	2071.6	2075.6	2075.6	2073.6	2055.6	2041.7	2037.7	2037.7	2025.8
25°	2021.8	2015.8	2021.8	2021.8	2019.8	2021.8	2015.8	2007.8	2001.9	1995.9	1983.9
27.5°	1974.0	1970.0	1974.0	1970.0	1974.0	1968.0	1966.0	1964.0	1956.0	1950.1	1934.1
30°	1926.2	1922.2	1926.2	1922.2	1918.2	1914.2	1904.3	1900.3	1908.2	1904.3	1878.4
32.5°	1866.4	1862.4	1866.4	1866.4	1862.4	1862.4	1846.5	1840.5	1842.5	1854.5	1830.5
35°	1804.7	1798.7	1804.7	1802.7	1804.7	1798.7	1788.7	1786.7	1778.8	1792.7	1774.8
37.5°	1732.9	1727.0	1732.9	1732.9	1732.9	1736.9	1729.0	1723.0	1711.0	1729.0	1715.0
40°	1659.2	1651.3	1659.2	1657.2	1659.2	1663.2	1659.2	1655.3	1643.3	1657.2	1645.3
42.5°	1575.6	1573.6	1575.6	1577.6	1577.6	1585.5	1591.5	1583.5	1579.6	1569.6	1577.6
45°	1485.9	1481.9	1485.9	1489.9	1491.9	1495.9	1513.8	1513.8	1507.8	1491.9	1503.9
47.5°	1390.3	1380.4	1390.3	1402.3	1402.3	1408.2	1426.2	1440.1	1430.2	1410.2	1416.2
50°	1288.7	1290.7	1288.7	1296.7	1296.7	1318.6	1332.5	1346.5	1356.5	1332.5	1304.7
52.5°	1189.1	1187.2	1189.1	1195.1	1203.1	1213.0	1236.9	1250.9	1266.8	1252.9	1209.0
55°	1089.6	1093.6	1089.6	1091.6	1095.6	1101.6	1137.4	1151.4	1181.3	1163.3	1117.5
57.5°	990.0	984.0	990.0	994.0	996.0	1002.0	1031.9	1057.8	1075.7	1077.7	1021.9
60°	874.5	866.5	874.5	892.4	896.4	900.4	928.3	952.2	968.1	974.1	916.3
62.5°	772.9	759.0	772.9	784.8	792.8	802.8	822.7	858.6	872.5	874.5	792.8
65°	665.3	659.4	665.3	689.2	691.2	703.2	725.1	751.0	780.9	776.9	659.4
67.5°	567.7	567.7	567.7	583.7	595.6	601.6	629.5	641.4	679.3	683.3	549.8
70°	478.1	476.1	478.1	490.0	498.0	511.9	537.8	551.8	581.7	591.6	446.2
72.5°	392.4	390.4	392.4	402.4	410.4	422.3	444.2	460.2	486.0	498.0	346.6
75°	316.7	312.7	316.7	324.7	322.7	338.6	356.6	372.5	396.4	404.4	257.0
77.5°	243.0	243.0	243.0	251.0	251.0	266.9	274.9	294.8	308.8	320.7	189.2
80°	181.3	179.3	181.3	183.3	183.3	191.2	205.2	219.1	231.1	231.1	129.5
82.5°	127.5	123.5	127.5	127.5	127.5	131.5	139.4	143.4	151.4	157.4	81.7
85°	79.7	79.7	79.7	81.7	79.7	83.7	85.7	89.6	89.6	85.7	49.8
87.5°	51.8	49.8	51.8	49.8	49.8	47.8	47.8	47.8	45.8	43.8	27.9
90°	15.6	15.6	15.6	15.6	15.6	20.8	27.7	31.2	26.8	18.0	11.5
92.5°	62.4	50.1	62.4	74.9	78.0	110.6	154.0	175.7	154.3	111.5	79.3
95°	217.8	180.3	217.8	255.5	264.8	347.8	458.4	513.6	433.8	274.1	154.4
97.5°	521.9	450.4	521.9	593.4	611.3	663.7	733.7	768.6	635.4	369.2	169.5
100°	752.0	666.7	752.0	837.1	858.5	854.7	849.6	847.0	699.3	403.9	182.3
102.5°	978.3	905.3	978.3	1051.3	1069.5	1002.8	913.7	869.2	719.4	419.7	195.0
105°	1266.8	1227.6	1266.8	1306.1	1315.9	1166.2	966.5	866.7	721.7	431.6	213.9
107.5°	1455.9	1465.3	1455.9	1446.4	1444.0	1235.1	956.7	817.4	689.5	433.7	241.8
110°	1527.9	1568.8	1527.9	1487.0	1476.8	1243.3	932.1	776.4	661.0	430.5	257.5

TEST NUMBER: P934392

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1534.3	1597.1	1534.3	1471.6	1455.9	1216.9	898.3	739.0	636.2	430.6	276.3
115°	1493.6	1580.7	1493.6	1406.6	1384.8	1154.7	847.8	694.3	607.8	434.6	304.7
117.5°	1407.4	1504.0	1407.4	1310.8	1286.7	1079.0	802.0	663.4	589.8	442.6	332.2
120°	1337.8	1431.7	1337.8	1244.0	1220.6	1030.8	777.7	651.2	583.9	449.2	348.2
122.5°	1270.2	1362.7	1270.2	1177.7	1154.6	983.6	755.7	641.7	580.7	458.6	367.0
125°	1173.6	1258.8	1173.6	1088.4	1067.1	921.9	728.3	631.5	578.1	471.3	391.2
127.5°	1086.7	1158.6	1086.7	1014.8	996.9	872.2	706.0	622.8	576.6	484.1	414.6
130°	1035.5	1102.0	1035.5	969.1	952.5	841.5	693.5	619.5	577.5	493.3	430.3
132.5°	989.1	1048.6	989.1	929.6	914.7	815.4	683.0	616.7	578.1	500.9	443.0
135°	925.5	976.8	925.5	874.2	861.3	778.2	667.2	611.7	577.5	509.1	457.8
137.5°	874.5	916.4	874.5	832.5	822.0	751.7	657.9	610.9	581.1	521.4	476.7
140°	839.3	878.6	839.3	800.1	790.3	729.6	648.6	608.1	581.7	529.0	489.4
142.5°	810.3	844.1	810.3	776.7	768.2	714.8	643.6	608.1	583.8	535.3	498.8
145°	766.9	792.4	766.9	741.3	734.9	691.3	633.1	604.0	583.9	543.5	513.2
147.5°	733.5	754.7	733.5	712.2	707.0	672.6	626.9	604.0	587.8	555.5	531.3
150°	712.4	729.6	712.4	695.3	691.0	662.0	623.3	604.0	589.9	561.8	540.7
152.5°	694.5	707.5	694.5	681.6	678.3	653.5	620.5	604.0	591.3	565.9	546.9
155°	673.8	682.4	673.8	665.2	663.0	643.3	617.1	604.0	594.3	575.0	560.4
157.5°	657.5	663.4	657.5	651.4	649.9	634.6	614.1	604.0	597.3	584.0	574.0
160°	647.7	651.2	647.7	644.2	643.3	630.2	612.7	604.0	598.7	588.1	580.2
162.5°	641.3	644.6	641.3	638.0	637.2	626.2	611.3	604.0	600.2	592.5	586.7
165°	632.1	635.5	632.1	628.7	627.8	619.8	609.3	604.0	602.2	598.7	596.1
167.5°	625.5	627.0	625.5	624.1	623.7	618.5	611.5	608.1	606.6	603.7	601.5
170°	623.7	623.7	623.7	623.7	623.7	618.5	611.5	608.1	608.0	607.8	607.7
172.5°	618.8	617.5	618.8	620.1	620.4	616.3	610.8	608.1	608.1	608.1	608.1
175°	615.8	615.8	615.8	615.8	615.8	613.2	609.8	608.1	608.9	610.5	611.7
177.5°	613.2	611.7	613.2	614.6	615.0	612.9	610.2	608.9	609.5	610.7	611.7
180°	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7

TEST NUMBER: P934392

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4
2.5°	2135.3	2123.4	2123.4	2103.5	2095.5	2089.5	2079.5	2049.7	2041.7	2033.7	2045.7
5°	2153.3	2131.3	2115.4	2079.5	2049.7	2037.7	1999.9	1928.2	1880.3	1844.5	1824.6
7.5°	2157.2	2129.3	2099.5	2043.7	1972.0	1940.1	1824.6	1693.1	1657.2	1625.4	1605.5
10°	2153.3	2121.4	2079.5	1995.9	1826.6	1770.8	1655.3	1569.6	1547.7	1541.7	1547.7
12.5°	2139.3	2109.4	2051.7	1912.2	1675.2	1637.3	1569.6	1519.8	1515.8	1525.8	1579.6
15°	2115.4	2087.5	2019.8	1800.7	1591.5	1563.6	1515.8	1497.9	1519.8	1589.5	1750.9
17.5°	2091.5	2059.6	1976.0	1691.1	1527.8	1507.8	1474.0	1509.8	1633.3	1727.0	1780.7
20°	2059.6	2021.8	1926.2	1611.4	1481.9	1464.0	1448.1	1609.4	1703.1	1736.9	1766.8
22.5°	2021.8	1981.9	1858.4	1555.7	1434.1	1420.2	1430.2	1665.2	1703.1	1727.0	1752.9
25°	1972.0	1938.1	1778.8	1511.8	1396.3	1380.4	1418.2	1659.2	1681.1	1687.1	1738.9
27.5°	1926.2	1882.3	1695.1	1472.0	1350.5	1344.5	1428.2	1633.3	1649.3	1655.3	1711.0
30°	1870.4	1804.7	1601.5	1430.2	1302.7	1300.7	1430.2	1601.5	1597.5	1613.4	1669.2
32.5°	1812.6	1689.1	1495.9	1378.4	1256.9	1254.9	1416.2	1553.7	1549.7	1571.6	1613.4
35°	1758.8	1599.5	1352.5	1318.6	1199.1	1201.1	1382.3	1497.9	1499.9	1519.8	1545.7
37.5°	1703.1	1521.8	1195.1	1252.9	1143.4	1143.4	1336.5	1446.1	1442.1	1448.1	1483.9
40°	1637.3	1400.3	1055.8	1167.3	1091.6	1085.6	1280.8	1390.3	1376.4	1374.4	1424.2
42.5°	1567.6	1266.8	952.2	1053.8	1031.9	1023.9	1213.0	1322.6	1296.7	1302.7	1366.4
45°	1491.9	1231.0	872.5	890.4	970.1	964.1	1139.4	1244.9	1227.0	1242.9	1308.6
47.5°	1416.2	1159.3	846.6	739.0	904.4	902.4	1057.8	1169.3	1159.3	1175.3	1244.9
50°	1312.6	1079.7	844.6	633.5	830.7	838.6	960.1	1095.6	1095.6	1109.5	1183.2
52.5°	1179.3	982.1	766.9	573.7	745.0	768.9	874.5	1031.9	1035.8	1049.8	1115.5
55°	1057.8	880.5	711.1	527.9	643.4	695.2	790.8	966.1	974.1	988.0	1047.8
57.5°	946.2	733.1	699.2	474.1	549.8	599.6	717.1	902.4	906.4	918.3	976.1
60°	826.7	529.9	641.4	416.3	468.1	506.0	649.4	826.7	840.6	848.6	898.4
62.5°	691.2	384.5	581.7	376.5	428.3	436.2	593.6	755.0	772.9	778.9	808.8
65°	492.0	322.7	494.0	342.6	386.4	388.4	533.9	681.3	697.2	707.2	729.1
67.5°	332.7	262.9	376.5	310.8	354.6	356.6	476.1	595.6	617.5	625.5	639.4
70°	231.1	175.3	278.9	276.9	318.7	322.7	414.3	517.9	537.8	543.8	551.8
72.5°	169.3	141.4	231.1	249.0	280.9	284.9	350.6	430.3	450.2	456.2	460.2
75°	129.5	149.4	187.2	217.1	239.0	241.0	286.8	350.6	364.5	368.5	370.5
77.5°	103.6	139.4	137.4	175.3	195.2	191.2	225.1	270.9	282.9	282.9	282.9
80°	77.7	109.6	103.6	125.5	143.4	139.4	161.4	193.2	197.2	201.2	199.2
82.5°	57.8	69.7	69.7	79.7	95.6	91.6	107.6	125.5	125.5	125.5	129.5
85°	35.9	39.8	31.9	41.8	53.8	51.8	59.8	67.7	69.7	69.7	65.7
87.5°	21.9	17.9	10.0	15.9	23.9	23.9	27.9	29.9	27.9	27.9	27.9
90°	10.7	7.4	4.1	7.4	10.7	11.5	18.0	26.8	31.2	27.7	20.8
92.5°	72.3	44.3	16.4	44.3	72.3	79.3	111.5	154.3	175.7	154.0	110.6
95°	141.6	90.5	39.4	90.5	141.6	154.4	274.1	433.8	513.6	458.4	347.8
97.5°	158.3	113.1	68.1	113.1	158.3	169.5	369.2	635.4	768.6	733.7	663.7
100°	172.0	131.2	90.3	131.2	172.0	182.3	403.9	699.3	847.0	849.6	854.7
102.5°	185.5	147.4	109.3	147.4	185.5	195.0	419.7	719.4	869.2	913.7	1002.8
105°	205.9	173.5	141.2	173.5	205.9	213.9	431.6	721.7	866.7	966.5	1166.2
107.5°	234.3	204.2	174.1	204.2	234.3	241.8	433.7	689.5	817.4	956.7	1235.1
110°	250.7	223.4	196.2	223.4	250.7	257.5	430.5	661.0	776.4	932.1	1243.3

TEST NUMBER: P934392

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	269.8	243.9	218.0	243.9	269.8	276.3	430.6	636.2	739.0	898.3	1216.9
115°	298.7	274.8	250.9	274.8	298.7	304.7	434.6	607.8	694.3	847.8	1154.7
117.5°	326.7	305.0	283.3	305.0	326.7	332.2	442.6	589.8	663.4	802.0	1079.0
120°	343.1	322.6	302.2	322.6	343.1	348.2	449.2	583.9	651.2	777.7	1030.8
122.5°	361.8	341.2	320.6	341.2	361.8	367.0	458.6	580.7	641.7	755.7	983.6
125°	386.5	367.7	349.0	367.7	386.5	391.2	471.3	578.1	631.5	728.3	921.9
127.5°	409.9	390.9	372.0	390.9	409.9	414.6	484.1	576.6	622.8	706.0	872.2
130°	425.2	404.7	384.3	404.7	425.2	430.3	493.3	577.5	619.5	693.5	841.5
132.5°	437.9	417.4	397.0	417.4	437.9	443.0	500.9	578.1	616.7	683.0	815.4
135°	453.1	434.6	415.9	434.6	453.1	457.8	509.1	577.5	611.7	667.2	778.2
137.5°	472.1	453.7	435.3	453.7	472.1	476.7	521.4	581.1	610.9	657.9	751.7
140°	485.2	468.2	451.2	468.2	485.2	489.4	529.0	581.7	608.1	648.6	729.6
142.5°	494.9	479.2	463.5	479.2	494.9	498.8	535.3	583.8	608.1	643.6	714.8
145°	509.9	496.1	482.5	496.1	509.9	513.2	543.5	583.9	604.0	633.1	691.3
147.5°	528.0	514.6	501.3	514.6	528.0	531.3	555.5	587.8	604.0	626.9	672.6
150°	537.7	525.7	513.6	525.7	537.7	540.7	561.8	589.9	604.0	623.3	662.0
152.5°	544.6	535.5	526.4	535.5	544.6	546.9	565.9	591.3	604.0	620.5	653.5
155°	558.8	552.0	545.2	552.0	558.8	560.4	575.0	594.3	604.0	617.1	643.3
157.5°	572.3	565.7	559.2	565.7	572.3	574.0	584.0	597.3	604.0	614.1	634.6
160°	578.9	573.8	568.6	573.8	578.9	580.2	588.1	598.7	604.0	612.7	630.2
162.5°	585.7	582.0	578.1	582.0	585.7	586.7	592.5	600.2	604.0	611.3	626.2
165°	595.2	591.8	588.3	591.8	595.2	596.1	598.7	602.2	604.0	609.3	619.8
167.5°	601.1	599.4	597.8	599.4	601.1	601.5	603.7	606.6	608.1	611.5	618.5
170°	607.3	605.6	604.0	605.6	607.3	607.7	607.8	608.0	608.1	611.5	618.5
172.5°	608.0	607.7	607.3	607.7	608.0	608.1	608.1	608.1	608.1	610.8	616.3
175°	611.7	611.7	611.7	611.7	611.7	611.7	610.5	608.9	608.1	609.8	613.2
177.5°	611.7	611.7	611.7	611.7	611.7	611.7	610.7	609.5	608.9	610.2	612.9
180°	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7

TEST NUMBER: P934392

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4	2105.4
2.5°	2031.7	2025.8	2033.7	2011.8	2033.7	2025.8	2031.7	2045.7	2033.7	2041.7	2049.7
5°	1782.7	1772.8	1740.9	1715.0	1740.9	1772.8	1782.7	1824.6	1844.5	1880.3	1928.2
7.5°	1593.5	1585.5	1577.6	1561.6	1577.6	1585.5	1593.5	1605.5	1625.4	1657.2	1693.1
10°	1551.7	1553.7	1565.6	1563.6	1565.6	1553.7	1551.7	1547.7	1541.7	1547.7	1569.6
12.5°	1659.2	1677.2	1742.9	1738.9	1742.9	1677.2	1659.2	1579.6	1525.8	1515.8	1519.8
15°	1782.7	1788.7	1802.7	1804.7	1802.7	1788.7	1782.7	1750.9	1589.5	1519.8	1497.9
17.5°	1794.7	1796.7	1806.6	1806.6	1806.6	1796.7	1794.7	1780.7	1727.0	1633.3	1509.8
20°	1784.7	1788.7	1808.6	1812.6	1808.6	1788.7	1784.7	1766.8	1736.9	1703.1	1609.4
22.5°	1780.7	1788.7	1804.7	1802.7	1804.7	1788.7	1780.7	1752.9	1727.0	1703.1	1665.2
25°	1760.8	1760.8	1762.8	1764.8	1762.8	1760.8	1760.8	1738.9	1687.1	1681.1	1659.2
27.5°	1719.0	1723.0	1734.9	1732.9	1734.9	1723.0	1719.0	1711.0	1655.3	1649.3	1633.3
30°	1681.1	1677.2	1667.2	1659.2	1667.2	1677.2	1681.1	1669.2	1613.4	1597.5	1601.5
32.5°	1617.4	1607.4	1597.5	1591.5	1597.5	1607.4	1617.4	1613.4	1571.6	1549.7	1553.7
35°	1541.7	1543.7	1541.7	1535.7	1541.7	1543.7	1541.7	1545.7	1519.8	1499.9	1497.9
37.5°	1487.9	1491.9	1489.9	1481.9	1489.9	1491.9	1487.9	1483.9	1448.1	1442.1	1446.1
40°	1432.1	1434.1	1432.1	1426.2	1432.1	1434.1	1432.1	1424.2	1374.4	1376.4	1390.3
42.5°	1378.4	1376.4	1370.4	1366.4	1370.4	1376.4	1378.4	1366.4	1302.7	1296.7	1322.6
45°	1316.6	1318.6	1306.7	1300.7	1306.7	1318.6	1316.6	1308.6	1242.9	1227.0	1244.9
47.5°	1254.9	1254.9	1244.9	1238.9	1244.9	1254.9	1254.9	1244.9	1175.3	1159.3	1169.3
50°	1189.1	1187.2	1173.3	1171.3	1173.3	1187.2	1189.1	1183.2	1109.5	1095.6	1095.6
52.5°	1113.5	1113.5	1115.5	1119.5	1115.5	1113.5	1113.5	1115.5	1049.8	1035.8	1031.9
55°	1047.8	1049.8	1063.7	1067.7	1063.7	1049.8	1047.8	1047.8	988.0	974.1	966.1
57.5°	980.1	980.1	990.0	990.0	990.0	980.1	980.1	976.1	918.3	906.4	902.4
60°	902.4	906.4	914.3	912.3	914.3	906.4	902.4	898.4	848.6	840.6	826.7
62.5°	820.7	824.7	826.7	822.7	826.7	824.7	820.7	808.8	778.9	772.9	755.0
65°	735.0	739.0	741.0	737.0	741.0	739.0	735.0	729.1	707.2	697.2	681.3
67.5°	647.4	645.4	643.4	651.4	643.4	645.4	647.4	639.4	625.5	617.5	595.6
70°	557.8	557.8	555.8	559.8	555.8	557.8	557.8	551.8	543.8	537.8	517.9
72.5°	462.1	460.2	468.1	462.1	468.1	460.2	462.1	460.2	456.2	450.2	430.3
75°	368.5	372.5	368.5	374.5	368.5	372.5	368.5	370.5	368.5	364.5	350.6
77.5°	280.9	284.9	280.9	280.9	280.9	284.9	280.9	282.9	282.9	282.9	270.9
80°	199.2	197.2	197.2	195.2	197.2	197.2	199.2	199.2	201.2	197.2	193.2
82.5°	127.5	125.5	125.5	129.5	125.5	125.5	127.5	129.5	125.5	125.5	125.5
85°	69.7	71.7	67.7	67.7	67.7	71.7	69.7	65.7	69.7	69.7	67.7
87.5°	25.9	23.9	23.9	23.9	23.9	23.9	25.9	27.9	27.9	27.9	29.9
90°	15.6	15.6	15.6	15.6	15.6	15.6	15.6	20.8	27.7	31.2	26.8
92.5°	78.0	74.9	62.4	50.1	62.4	74.9	78.0	110.6	154.0	175.7	154.3
95°	264.8	255.5	217.8	180.3	217.8	255.5	264.8	347.8	458.4	513.6	433.8
97.5°	611.3	593.4	521.9	450.4	521.9	593.4	611.3	663.7	733.7	768.6	635.4
100°	858.5	837.1	752.0	666.7	752.0	837.1	858.5	854.7	849.6	847.0	699.3
102.5°	1069.5	1051.3	978.3	905.3	978.3	1051.3	1069.5	1002.8	913.7	869.2	719.4
105°	1315.9	1306.1	1266.8	1227.6	1266.8	1306.1	1315.9	1166.2	966.5	866.7	721.7
107.5°	1444.0	1446.4	1455.9	1465.3	1455.9	1446.4	1444.0	1235.1	956.7	817.4	689.5
110°	1476.8	1487.0	1527.9	1568.8	1527.9	1487.0	1476.8	1243.3	932.1	776.4	661.0

TEST NUMBER: P934392

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1455.9	1471.6	1534.3	1597.1	1534.3	1471.6	1455.9	1216.9	898.3	739.0	636.2
115°	1384.8	1406.6	1493.6	1580.7	1493.6	1406.6	1384.8	1154.7	847.8	694.3	607.8
117.5°	1286.7	1310.8	1407.4	1504.0	1407.4	1310.8	1286.7	1079.0	802.0	663.4	589.8
120°	1220.6	1244.0	1337.8	1431.7	1337.8	1244.0	1220.6	1030.8	777.7	651.2	583.9
122.5°	1154.6	1177.7	1270.2	1362.7	1270.2	1177.7	1154.6	983.6	755.7	641.7	580.7
125°	1067.1	1088.4	1173.6	1258.8	1173.6	1088.4	1067.1	921.9	728.3	631.5	578.1
127.5°	996.9	1014.8	1086.7	1158.6	1086.7	1014.8	996.9	872.2	706.0	622.8	576.6
130°	952.5	969.1	1035.5	1102.0	1035.5	969.1	952.5	841.5	693.5	619.5	577.5
132.5°	914.7	929.6	989.1	1048.6	989.1	929.6	914.7	815.4	683.0	616.7	578.1
135°	861.3	874.2	925.5	976.8	925.5	874.2	861.3	778.2	667.2	611.7	577.5
137.5°	822.0	832.5	874.5	916.4	874.5	832.5	822.0	751.7	657.9	610.9	581.1
140°	790.3	800.1	839.3	878.6	839.3	800.1	790.3	729.6	648.6	608.1	581.7
142.5°	768.2	776.7	810.3	844.1	810.3	776.7	768.2	714.8	643.6	608.1	583.8
145°	734.9	741.3	766.9	792.4	766.9	741.3	734.9	691.3	633.1	604.0	583.9
147.5°	707.0	712.2	733.5	754.7	733.5	712.2	707.0	672.6	626.9	604.0	587.8
150°	691.0	695.3	712.4	729.6	712.4	695.3	691.0	662.0	623.3	604.0	589.9
152.5°	678.3	681.6	694.5	707.5	694.5	681.6	678.3	653.5	620.5	604.0	591.3
155°	663.0	665.2	673.8	682.4	673.8	665.2	663.0	643.3	617.1	604.0	594.3
157.5°	649.9	651.4	657.5	663.4	657.5	651.4	649.9	634.6	614.1	604.0	597.3
160°	643.3	644.2	647.7	651.2	647.7	644.2	643.3	630.2	612.7	604.0	598.7
162.5°	637.2	638.0	641.3	644.6	641.3	638.0	637.2	626.2	611.3	604.0	600.2
165°	627.8	628.7	632.1	635.5	632.1	628.7	627.8	619.8	609.3	604.0	602.2
167.5°	623.7	624.1	625.5	627.0	625.5	624.1	623.7	618.5	611.5	608.1	606.6
170°	623.7	623.7	623.7	623.7	623.7	623.7	623.7	618.5	611.5	608.1	608.0
172.5°	620.4	620.1	618.8	617.5	618.8	620.1	620.4	616.3	610.8	608.1	608.1
175°	615.8	615.8	615.8	615.8	615.8	615.8	615.8	613.2	609.8	608.1	608.9
177.5°	615.0	614.6	613.2	611.7	613.2	614.6	615.0	612.9	610.2	608.9	609.5
180°	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7	611.7

TEST NUMBER: P934392

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2105.4	2105.4	2105.4	2105.4	2105.4
2.5°	2079.5	2089.5	2095.5	2103.5	2123.4
5°	1999.9	2037.7	2049.7	2079.5	2115.4
7.5°	1824.6	1940.1	1972.0	2043.7	2099.5
10°	1655.3	1770.8	1826.6	1995.9	2079.5
12.5°	1569.6	1637.3	1675.2	1912.2	2051.7
15°	1515.8	1563.6	1591.5	1800.7	2019.8
17.5°	1474.0	1507.8	1527.8	1691.1	1976.0
20°	1448.1	1464.0	1481.9	1611.4	1926.2
22.5°	1430.2	1420.2	1434.1	1555.7	1858.4
25°	1418.2	1380.4	1396.3	1511.8	1778.8
27.5°	1428.2	1344.5	1350.5	1472.0	1695.1
30°	1430.2	1300.7	1302.7	1430.2	1601.5
32.5°	1416.2	1254.9	1256.9	1378.4	1495.9
35°	1382.3	1201.1	1199.1	1318.6	1352.5
37.5°	1336.5	1143.4	1143.4	1252.9	1195.1
40°	1280.8	1085.6	1091.6	1167.3	1055.8
42.5°	1213.0	1023.9	1031.9	1053.8	952.2
45°	1139.4	964.1	970.1	890.4	872.5
47.5°	1057.8	902.4	904.4	739.0	846.6
50°	960.1	838.6	830.7	633.5	844.6
52.5°	874.5	768.9	745.0	573.7	766.9
55°	790.8	695.2	643.4	527.9	711.1
57.5°	717.1	599.6	549.8	474.1	699.2
60°	649.4	506.0	468.1	416.3	641.4
62.5°	593.6	436.2	428.3	376.5	581.7
65°	533.9	388.4	386.4	342.6	494.0
67.5°	476.1	356.6	354.6	310.8	376.5
70°	414.3	322.7	318.7	276.9	278.9
72.5°	350.6	284.9	280.9	249.0	231.1
75°	286.8	241.0	239.0	217.1	187.2
77.5°	225.1	191.2	195.2	175.3	137.4
80°	161.4	139.4	143.4	125.5	103.6
82.5°	107.6	91.6	95.6	79.7	69.7
85°	59.8	51.8	53.8	41.8	31.9
87.5°	27.9	23.9	23.9	15.9	10.0
90°	18.0	11.5	10.7	7.4	4.1
92.5°	111.5	79.3	72.3	44.3	16.4
95°	274.1	154.4	141.6	90.5	39.4
97.5°	369.2	169.5	158.3	113.1	68.1
100°	403.9	182.3	172.0	131.2	90.3
102.5°	419.7	195.0	185.5	147.4	109.3
105°	431.6	213.9	205.9	173.5	141.2
107.5°	433.7	241.8	234.3	204.2	174.1
110°	430.5	257.5	250.7	223.4	196.2



TEST NUMBER: P934392

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	430.6	276.3	269.8	243.9	218.0
115°	434.6	304.7	298.7	274.8	250.9
117.5°	442.6	332.2	326.7	305.0	283.3
120°	449.2	348.2	343.1	322.6	302.2
122.5°	458.6	367.0	361.8	341.2	320.6
125°	471.3	391.2	386.5	367.7	349.0
127.5°	484.1	414.6	409.9	390.9	372.0
130°	493.3	430.3	425.2	404.7	384.3
132.5°	500.9	443.0	437.9	417.4	397.0
135°	509.1	457.8	453.1	434.6	415.9
137.5°	521.4	476.7	472.1	453.7	435.3
140°	529.0	489.4	485.2	468.2	451.2
142.5°	535.3	498.8	494.9	479.2	463.5
145°	543.5	513.2	509.9	496.1	482.5
147.5°	555.5	531.3	528.0	514.6	501.3
150°	561.8	540.7	537.7	525.7	513.6
152.5°	565.9	546.9	544.6	535.5	526.4
155°	575.0	560.4	558.8	552.0	545.2
157.5°	584.0	574.0	572.3	565.7	559.2
160°	588.1	580.2	578.9	573.8	568.6
162.5°	592.5	586.7	585.7	582.0	578.1
165°	598.7	596.1	595.2	591.8	588.3
167.5°	603.7	601.5	601.1	599.4	597.8
170°	607.8	607.7	607.3	605.6	604.0
172.5°	608.1	608.1	608.0	607.7	607.3
175°	610.5	611.7	611.7	611.7	611.7
177.5°	610.7	611.7	611.7	611.7	611.7
180°	611.7	611.7	611.7	611.7	611.7

TEST NUMBER: P934392

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.43	14.37	14.31	15.27	16.43	16.27	17.20	17.15	18.11	19.26
	3H	13.91	14.75	14.81	15.67	16.85	17.62	18.46	18.52	19.38	20.55
	4H	14.11	14.90	15.02	15.82	17.01	18.07	18.86	18.98	19.78	20.97
	6H	14.23	14.96	15.15	15.89	17.09	18.36	19.09	19.28	20.02	21.22
	8H	14.23	14.93	15.16	15.87	17.07	18.44	19.13	19.37	20.08	21.28
	12H	14.21	14.87	15.14	15.81	17.03	18.48	19.14	19.42	20.08	21.31
4H	2H	14.47	15.27	15.39	16.19	17.38	16.68	17.48	17.60	18.40	19.59
	3H	15.51	16.17	16.44	17.12	18.32	18.20	18.86	19.13	19.81	21.02
	4H	15.79	16.39	16.73	17.34	18.56	18.73	19.34	19.67	20.28	21.51
	6H	15.91	16.44	16.87	17.41	18.63	19.10	19.62	20.06	20.60	21.82
	8H	15.92	16.41	16.88	17.37	18.62	19.21	19.70	20.17	20.66	21.91
	12H	15.89	16.33	16.87	17.31	18.56	19.27	19.71	20.25	20.70	21.94
8H	4H	16.25	16.73	17.20	17.70	18.94	18.86	19.35	19.82	20.31	21.56
	6H	16.51	16.91	17.49	17.92	19.16	19.30	19.71	20.29	20.71	21.95
	8H	16.55	16.91	17.54	17.90	19.16	19.46	19.81	20.45	20.81	22.07
	12H	16.54	16.85	17.54	17.84	19.15	19.56	19.87	20.56	20.86	22.17
12H	4H	16.26	16.69	17.23	17.68	18.92	18.83	19.27	19.81	20.25	21.50
	6H	16.57	16.93	17.56	17.92	19.18	19.30	19.66	20.29	20.65	21.91
	8H	16.64	16.96	17.64	17.94	19.25	19.47	19.78	20.46	20.77	22.08

END OF REPORT