

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934577

Luminaire Tested: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934577
REPORT IS A COMBINATION OF REPORTS P933701 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19809.4 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 168
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934577

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K

Luminous Intensity Polar Plot



TEST NUMBER: P934577

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	65	63
2	93	86	79	74	88	81	76	71	73	68	65	65	62	59	58	56	53
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	52	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27
8	57	44	36	30	54	42	35	29	38	32	28	35	30	26	31	27	24
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21
10	49	37	30	25	47	35	28	24	32	26	22	30	25	21	27	23	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16531	16531	16531	16531
5°	16660	16687	16660	13121
10°	16555	16438	16555	11752
15°	16381	16082	16381	13428
20°	16046	15660	16046	13456
25°	15350	15044	15350	13171
30°	14450	14533	14450	12546
35°	12888	13887	12888	11857
40°	10745	13127	10745	11337
45°	9607	12236	9607	10739
50°	10215	11174	10215	10140
55°	9620	10030	9620	9793
60°	9929	8519	9929	8969
65°	9017	7042	9017	7871
70°	6259	5612	6259	6598
75°	5509	4148	5509	4968
80°	4472	2743	4472	2986
85°	2621	1453	2621	1235

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 14716 cd/sqm

TEST NUMBER: P934577

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	482.4	2.4
10°-20°	1369.8	6.9
20°-30°	2117.4	10.7
30°-40°	2527.7	12.8
40°-50°	2542.6	12.8
50°-60°	2212.3	11.2
60°-70°	1568.6	7.9
70°-80°	829.9	4.2
80°-90°	210.2	1.1
90°-100°	447.3	2.3
100°-110°	1176.0	5.9
110°-120°	1219.3	6.2
120°-130°	978.1	4.9
130°-140°	767.4	3.9
140°-150°	589.0	3.0
150°-160°	424.2	2.1
160°-170°	259.6	1.3
170°-180°	87.7	0.4
0°-30°	3969.6	20.0
0°-40°	6497.3	32.8
0°-60°	11252.2	56.8
0°-90°	13860.9	70.0
90°-120°	2842.6	14.3
90°-150°	5177.1	26.1
90°-180°	5949.0	30.0
0°-180°	19809.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	5344	5344	5344	5344	5344	
5°	5370	5537	5370	4354	5370	509
15°	5127	5486	5127	4581	5127	1443
25°	4515	5117	4515	4480	4515	2073
35°	3433	4566	3433	3898	3433	2124
45°	2215	3762	2215	3302	2215	1774
55°	1805	2776	1805	2710	1805	1659
65°	1254	1674	1254	1871	1254	1199
75°	475	794	475	951	475	500
85°	81	202	81	172	81	109
90°	6	23	6	23	6	9
95°	59	270	59	270	59	66
105°	212	1841	212	1841	212	225
115°	376	2371	376	2371	376	372
125°	524	1888	524	1888	524	465
135°	624	1465	624	1465	624	483
145°	724	1189	724	1189	724	453
155°	818	1024	818	1024	818	376
165°	883	953	883	953	883	249
175°	918	924	918	924	918	87
180°	918	918	918	918	918	

TEST NUMBER: P934577

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5
2.5°	5390.1	5390.1	5420.3	5430.5	5430.5	5415.3	5400.1	5415.3	5460.8	5476.0	5470.9
5°	5369.7	5410.3	5465.8	5476.0	5486.1	5481.0	5470.9	5481.0	5531.6	5541.7	5546.7
7.5°	5329.3	5405.2	5476.0	5491.1	5506.3	5491.1	5486.1	5496.2	5546.7	5556.9	5556.9
10°	5278.8	5385.0	5465.8	5476.0	5491.1	5476.0	5476.0	5496.2	5546.7	5556.9	5562.0
12.5°	5208.0	5354.6	5430.5	5440.6	5460.8	5455.7	5450.7	5470.9	5521.4	5531.6	5531.6
15°	5127.1	5299.0	5369.7	5379.9	5415.3	5405.2	5405.2	5425.4	5481.0	5496.2	5491.1
17.5°	5015.9	5228.2	5309.1	5324.3	5349.5	5344.5	5349.5	5369.7	5420.3	5430.5	5435.5
20°	4889.5	5132.1	5228.2	5243.3	5268.6	5268.6	5268.6	5293.9	5344.5	5364.8	5364.8
22.5°	4717.6	5031.0	5132.1	5142.2	5172.6	5172.6	5182.7	5218.0	5263.6	5268.6	5268.6
25°	4515.3	4919.7	5005.7	5036.1	5066.5	5081.6	5096.7	5117.0	5132.1	5127.1	5132.1
27.5°	4302.9	4778.2	4889.5	4909.7	4950.1	4965.3	4985.5	4990.6	4995.6	5010.8	5000.7
30°	4065.3	4581.0	4747.8	4768.1	4833.8	4843.9	4823.7	4833.8	4859.1	4869.2	4879.3
32.5°	3797.2	4287.8	4601.2	4646.7	4707.4	4677.1	4672.0	4687.2	4727.6	4727.6	4737.8
35°	3433.2	4060.2	4464.7	4505.1	4550.6	4515.3	4535.5	4540.6	4565.9	4581.0	4575.9
37.5°	3033.8	3863.0	4323.1	4353.5	4388.9	4343.4	4373.7	4388.9	4409.1	4398.9	4398.9
40°	2679.8	3554.5	4156.3	4176.5	4206.8	4171.4	4201.8	4211.9	4222.0	4211.9	4206.8
42.5°	2416.9	3215.8	3979.3	4004.6	3984.4	4009.6	4019.8	4040.0	4024.8	4004.6	4004.6
45°	2214.6	3124.8	3787.2	3817.5	3787.2	3827.6	3842.8	3842.8	3797.2	3787.2	3782.1
47.5°	2149.0	2942.8	3595.1	3595.1	3579.8	3630.4	3655.7	3620.3	3574.8	3559.6	3559.6
50°	2143.9	2740.5	3332.1	3311.9	3382.6	3443.4	3418.1	3382.6	3347.3	3291.7	3291.7
52.5°	1946.7	2492.8	2993.3	3069.2	3180.4	3215.8	3175.3	3140.0	3079.2	3054.0	3033.8
55°	1805.1	2234.9	2684.9	2836.6	2952.8	2998.4	2922.6	2887.1	2796.2	2780.9	2770.9
57.5°	1774.8	1860.7	2401.8	2593.9	2735.4	2730.4	2684.9	2619.2	2543.3	2528.1	2523.1
60°	1628.2	1345.0	2098.4	2325.9	2472.6	2457.3	2416.9	2356.2	2285.4	2275.4	2265.2
62.5°	1476.5	975.9	1754.6	2012.4	2219.7	2214.6	2179.2	2088.2	2037.7	2012.4	1992.2
65°	1254.0	819.1	1248.9	1673.7	1972.0	1982.0	1906.2	1840.5	1784.8	1754.6	1749.5
67.5°	955.7	667.4	844.4	1395.5	1734.3	1724.2	1628.2	1597.8	1527.0	1511.8	1481.5
70°	707.9	444.9	586.5	1132.7	1501.7	1476.5	1400.6	1365.2	1299.5	1264.0	1243.8
72.5°	586.5	359.0	429.8	879.8	1264.0	1233.7	1168.0	1127.6	1071.9	1041.6	1021.4
75°	475.3	379.2	328.7	652.3	1026.4	1006.2	945.5	905.1	859.5	819.1	824.2
77.5°	348.9	354.0	262.9	480.4	814.0	783.8	748.3	697.8	677.6	637.1	637.1
80°	262.9	278.1	197.2	328.7	586.5	586.5	556.2	520.8	485.5	465.1	465.1
82.5°	177.0	177.0	146.6	207.3	399.5	384.3	364.0	354.0	333.8	323.6	323.6
85°	80.9	101.1	91.0	126.4	217.4	227.5	227.5	217.4	212.3	202.3	207.3
87.5°	25.3	45.5	55.6	70.8	111.3	116.3	121.3	121.3	121.3	126.4	126.4
90°	6.2	11.1	16.0	17.2	27.1	40.2	46.8	41.6	31.2	23.4	23.4
92.5°	24.6	66.4	108.4	118.8	167.0	231.4	263.5	231.0	165.8	117.0	112.3
95°	59.2	135.8	212.4	231.6	411.1	650.7	770.4	687.4	521.6	397.2	383.1
97.5°	102.2	169.8	237.4	254.4	553.9	953.2	1152.9	1100.5	995.6	917.0	890.2
100°	135.5	196.8	258.1	273.4	605.8	1048.9	1270.5	1274.3	1282.0	1287.7	1255.8
102.5°	163.8	221.0	278.2	292.5	629.6	1079.1	1303.8	1370.5	1504.1	1604.3	1576.9
105°	211.8	260.3	308.7	320.8	647.2	1082.5	1300.1	1449.8	1749.2	1973.8	1959.0
107.5°	261.2	306.3	351.5	362.7	650.6	1034.3	1226.2	1435.0	1852.8	2166.0	2169.6
110°	294.4	335.2	376.0	386.1	645.6	991.6	1164.6	1398.1	1865.0	2215.2	2230.5

TEST NUMBER: P934577

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	327.0	365.8	404.7	414.4	645.8	954.3	1108.5	1347.5	1825.4	2183.8	2207.3
115°	376.3	412.1	448.0	457.0	651.8	911.5	1041.4	1271.6	1731.9	2077.3	2109.9
117.5°	424.9	457.5	490.0	498.2	663.8	884.7	995.2	1203.0	1618.4	1930.0	1966.2
120°	453.3	484.0	514.5	522.2	673.7	875.8	976.8	1166.6	1546.2	1830.9	1866.1
122.5°	481.0	511.9	542.8	550.6	687.9	871.0	962.5	1133.4	1475.4	1731.7	1766.4
125°	523.5	551.7	579.9	586.9	707.1	867.1	947.2	1092.4	1382.7	1600.6	1632.5
127.5°	558.0	586.4	614.9	622.0	726.1	864.8	934.2	1058.9	1308.2	1495.3	1522.3
130°	576.5	607.2	637.7	645.4	740.0	866.2	929.4	1040.3	1262.3	1428.8	1453.7
132.5°	595.5	626.2	656.9	664.5	751.4	867.1	925.0	1024.4	1223.1	1372.1	1394.4
135°	623.9	651.8	679.7	686.6	763.6	866.3	917.6	1000.9	1167.3	1292.1	1311.3
137.5°	652.8	680.5	708.2	715.0	782.2	871.7	916.4	986.7	1127.5	1232.9	1248.7
140°	676.8	702.3	727.7	734.1	793.4	872.5	912.0	972.8	1094.4	1185.5	1200.3
142.5°	695.3	718.8	742.4	748.3	802.9	875.7	912.0	965.4	1072.2	1152.3	1164.9
145°	723.6	744.1	764.6	769.8	815.2	875.7	906.0	949.6	1036.9	1102.4	1111.9
147.5°	752.0	771.9	791.9	796.9	833.3	881.8	906.0	940.3	1009.0	1060.5	1068.5
150°	770.4	788.4	806.6	811.0	842.7	884.8	906.0	934.9	992.9	1036.4	1042.9
152.5°	789.5	803.2	816.9	820.3	848.9	886.9	906.0	930.8	980.3	1017.4	1022.3
155°	817.8	828.0	838.1	840.6	862.4	891.4	906.0	925.7	965.0	994.6	997.8
157.5°	838.8	848.7	858.5	860.9	876.0	896.0	906.0	921.3	951.9	974.9	977.2
160°	853.0	860.6	868.3	870.2	882.2	898.0	906.0	919.1	945.3	965.0	966.3
162.5°	867.1	872.9	878.7	880.1	888.7	900.2	906.0	917.0	939.1	955.8	957.0
165°	882.6	887.7	892.9	894.2	898.1	903.4	906.0	913.9	929.8	941.6	942.9
167.5°	896.7	899.1	901.6	902.2	905.5	909.8	912.0	917.2	927.7	935.4	936.0
170°	906.0	908.4	910.8	911.4	911.6	911.9	912.0	917.2	927.7	935.4	935.4
172.5°	910.8	911.3	911.9	912.0	912.0	912.0	912.0	916.1	924.4	930.6	930.1
175°	917.6	917.6	917.6	917.6	915.7	913.2	912.0	914.6	919.9	923.8	923.8
177.5°	917.6	917.6	917.6	917.6	916.2	914.3	913.3	915.4	919.5	922.6	922.0
180°	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6

TEST NUMBER: P934577

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5
2.5°	5481.0	5465.8	5481.0	5470.9	5476.0	5460.8	5415.3	5400.1	5415.3	5430.5	5430.5
5°	5546.7	5536.7	5546.7	5546.7	5541.7	5531.6	5481.0	5470.9	5481.0	5486.1	5476.0
7.5°	5566.9	5551.8	5566.9	5556.9	5556.9	5546.7	5496.2	5486.1	5491.1	5506.3	5491.1
10°	5566.9	5551.8	5566.9	5562.0	5556.9	5546.7	5496.2	5476.0	5476.0	5491.1	5476.0
12.5°	5541.7	5531.6	5541.7	5531.6	5531.6	5521.4	5470.9	5450.7	5455.7	5460.8	5440.6
15°	5501.2	5486.1	5501.2	5491.1	5496.2	5481.0	5425.4	5405.2	5405.2	5415.3	5379.9
17.5°	5440.6	5420.3	5440.6	5435.5	5430.5	5420.3	5369.7	5349.5	5344.5	5349.5	5324.3
20°	5369.7	5354.6	5369.7	5364.8	5364.8	5344.5	5293.9	5268.6	5268.6	5268.6	5243.3
22.5°	5258.6	5243.3	5258.6	5268.6	5268.6	5263.6	5218.0	5182.7	5172.6	5172.6	5142.2
25°	5132.1	5117.0	5132.1	5132.1	5127.1	5132.1	5117.0	5096.7	5081.6	5066.5	5036.1
27.5°	5010.8	5000.7	5010.8	5000.7	5010.8	4995.6	4990.6	4985.5	4965.3	4950.1	4909.7
30°	4889.5	4879.3	4889.5	4879.3	4869.2	4859.1	4833.8	4823.7	4843.9	4833.8	4768.1
32.5°	4737.8	4727.6	4737.8	4737.8	4727.6	4727.6	4687.2	4672.0	4677.1	4707.4	4646.7
35°	4581.0	4565.9	4581.0	4575.9	4581.0	4565.9	4540.6	4535.5	4515.3	4550.6	4505.1
37.5°	4398.9	4383.8	4398.9	4398.9	4398.9	4409.1	4388.9	4373.7	4343.4	4388.9	4353.5
40°	4211.9	4191.7	4211.9	4206.8	4211.9	4222.0	4211.9	4201.8	4171.4	4206.8	4176.5
42.5°	3999.5	3994.5	3999.5	4004.6	4004.6	4024.8	4040.0	4019.8	4009.6	3984.4	4004.6
45°	3772.0	3761.9	3772.0	3782.1	3787.2	3797.2	3842.8	3842.8	3827.6	3787.2	3817.5
47.5°	3529.3	3504.0	3529.3	3559.6	3559.6	3574.8	3620.3	3655.7	3630.4	3579.8	3595.1
50°	3271.5	3276.4	3271.5	3291.7	3291.7	3347.3	3382.6	3418.1	3443.4	3382.6	3311.9
52.5°	3018.6	3013.6	3018.6	3033.8	3054.0	3079.2	3140.0	3175.3	3215.8	3180.4	3069.2
55°	2765.8	2776.0	2765.8	2770.9	2780.9	2796.2	2887.1	2922.6	2998.4	2952.8	2836.6
57.5°	2513.0	2497.8	2513.0	2523.1	2528.1	2543.3	2619.2	2684.9	2730.4	2735.4	2593.9
60°	2219.7	2199.5	2219.7	2265.2	2275.4	2285.4	2356.2	2416.9	2457.3	2472.6	2325.9
62.5°	1961.8	1926.5	1961.8	1992.2	2012.4	2037.7	2088.2	2179.2	2214.6	2219.7	2012.4
65°	1688.8	1673.7	1688.8	1749.5	1754.6	1784.8	1840.5	1906.2	1982.0	1972.0	1673.7
67.5°	1441.0	1441.0	1441.0	1481.5	1511.8	1527.0	1597.8	1628.2	1724.2	1734.3	1395.5
70°	1213.5	1208.4	1213.5	1243.8	1264.0	1299.5	1365.2	1400.6	1476.5	1501.7	1132.7
72.5°	996.1	991.0	996.1	1021.4	1041.6	1071.9	1127.6	1168.0	1233.7	1264.0	879.8
75°	804.0	793.8	804.0	824.2	819.1	859.5	905.1	945.5	1006.2	1026.4	652.3
77.5°	616.8	616.8	616.8	637.1	637.1	677.6	697.8	748.3	783.8	814.0	480.4
80°	460.2	455.1	460.2	465.1	465.1	485.5	520.8	556.2	586.5	586.5	328.7
82.5°	323.6	313.4	323.6	323.6	323.6	333.8	354.0	364.0	384.3	399.5	207.3
85°	202.3	202.3	202.3	207.3	202.3	212.3	217.4	227.5	227.5	217.4	126.4
87.5°	131.5	126.4	131.5	126.4	126.4	121.3	121.3	121.3	116.3	111.3	70.8
90°	23.4	23.4	23.4	23.4	23.4	31.2	41.6	46.8	40.2	27.1	17.2
92.5°	93.7	75.1	93.7	112.3	117.0	165.8	231.0	263.5	231.4	167.0	118.8
95°	326.7	270.3	326.7	383.1	397.2	521.6	687.4	770.4	650.7	411.1	231.6
97.5°	782.9	675.6	782.9	890.2	917.0	995.6	1100.5	1152.9	953.2	553.9	254.4
100°	1128.0	1000.2	1128.0	1255.8	1287.7	1282.0	1274.3	1270.5	1048.9	605.8	273.4
102.5°	1467.4	1357.9	1467.4	1576.9	1604.3	1504.1	1370.5	1303.8	1079.1	629.6	292.5
105°	1900.3	1841.4	1900.3	1959.0	1973.8	1749.2	1449.8	1300.1	1082.5	647.2	320.8
107.5°	2183.7	2198.0	2183.7	2169.6	2166.0	1852.8	1435.0	1226.2	1034.3	650.6	362.7
110°	2291.8	2353.1	2291.8	2230.5	2215.2	1865.0	1398.1	1164.6	991.6	645.6	386.1

TEST NUMBER: P934577

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	2301.6	2395.7	2301.6	2207.3	2183.8	1825.4	1347.5	1108.5	954.3	645.8	414.4
115°	2240.5	2371.1	2240.5	2109.9	2077.3	1731.9	1271.6	1041.4	911.5	651.8	457.0
117.5°	2111.0	2255.8	2111.0	1966.2	1930.0	1618.4	1203.0	995.2	884.7	663.8	498.2
120°	2006.8	2147.5	2006.8	1866.1	1830.9	1546.2	1166.6	976.8	875.8	673.7	522.2
122.5°	1905.2	2044.0	1905.2	1766.4	1731.7	1475.4	1133.4	962.5	871.0	687.9	550.6
125°	1760.3	1888.2	1760.3	1632.5	1600.6	1382.7	1092.4	947.2	867.1	707.1	586.9
127.5°	1630.1	1737.9	1630.1	1522.3	1495.3	1308.2	1058.9	934.2	864.8	726.1	622.0
130°	1553.4	1653.0	1553.4	1453.7	1428.8	1262.3	1040.3	929.4	866.2	740.0	645.4
132.5°	1483.6	1572.9	1483.6	1394.4	1372.1	1223.1	1024.4	925.0	867.1	751.4	664.5
135°	1388.2	1465.1	1388.2	1311.3	1292.1	1167.3	1000.9	917.6	866.3	763.6	686.6
137.5°	1311.6	1374.6	1311.6	1248.7	1232.9	1127.5	986.7	916.4	871.7	782.2	715.0
140°	1259.0	1317.9	1259.0	1200.3	1185.5	1094.4	972.8	912.0	872.5	793.4	734.1
142.5°	1215.6	1266.2	1215.6	1164.9	1152.3	1072.2	965.4	912.0	875.7	802.9	748.3
145°	1150.3	1188.6	1150.3	1111.9	1102.4	1036.9	949.6	906.0	875.7	815.2	769.8
147.5°	1100.2	1132.0	1100.2	1068.5	1060.5	1009.0	940.3	906.0	881.8	833.3	796.9
150°	1068.6	1094.4	1068.6	1042.9	1036.4	992.9	934.9	906.0	884.8	842.7	811.0
152.5°	1041.7	1061.1	1041.7	1022.3	1017.4	980.3	930.8	906.0	886.9	848.9	820.3
155°	1010.7	1023.6	1010.7	997.8	994.6	965.0	925.7	906.0	891.4	862.4	840.6
157.5°	986.1	995.2	986.1	977.2	974.9	951.9	921.3	906.0	896.0	876.0	860.9
160°	971.6	976.8	971.6	966.3	965.0	945.3	919.1	906.0	898.0	882.2	870.2
162.5°	961.9	966.9	961.9	957.0	955.8	939.1	917.0	906.0	900.2	888.7	880.1
165°	948.2	953.4	948.2	942.9	941.6	929.8	913.9	906.0	903.4	898.1	894.2
167.5°	938.2	940.4	938.2	936.0	935.4	927.7	917.2	912.0	909.8	905.5	902.2
170°	935.4	935.4	935.4	935.4	935.4	927.7	917.2	912.0	911.9	911.6	911.4
172.5°	928.2	926.3	928.2	930.1	930.6	924.4	916.1	912.0	912.0	912.0	912.0
175°	923.8	923.8	923.8	923.8	923.8	919.9	914.6	912.0	913.2	915.7	917.6
177.5°	919.8	917.6	919.8	922.0	922.6	919.5	915.4	913.3	914.3	916.2	917.6
180°	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6

TEST NUMBER: P934577

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5
2.5°	5420.3	5390.1	5390.1	5339.5	5319.2	5304.1	5278.8	5202.9	5182.7	5162.5	5192.8
5°	5465.8	5410.3	5369.7	5278.8	5202.9	5172.6	5076.5	4894.4	4773.1	4682.1	4631.6
7.5°	5476.0	5405.2	5329.3	5187.8	5005.7	4924.8	4631.6	4297.8	4206.8	4125.9	4075.3
10°	5465.8	5385.0	5278.8	5066.5	4636.6	4495.0	4201.8	3984.4	3928.7	3913.6	3928.7
12.5°	5430.5	5354.6	5208.0	4854.0	4252.3	4156.3	3984.4	3857.9	3847.8	3873.1	4009.6
15°	5369.7	5299.0	5127.1	4570.8	4040.0	3969.2	3847.8	3802.3	3857.9	4034.9	4444.5
17.5°	5309.1	5228.2	5015.9	4292.8	3878.2	3827.6	3741.7	3832.7	4146.1	4383.8	4520.3
20°	5228.2	5132.1	4889.5	4090.6	3761.9	3716.4	3675.9	4085.5	4323.1	4409.1	4484.9
22.5°	5132.1	5031.0	4717.6	3948.9	3640.6	3605.1	3630.4	4227.0	4323.1	4383.8	4449.5
25°	5005.7	4919.7	4515.3	3837.7	3544.5	3504.0	3600.0	4211.9	4267.5	4282.7	4414.2
27.5°	4889.5	4778.2	4302.9	3736.6	3428.1	3413.0	3625.3	4146.1	4186.6	4201.8	4343.4
30°	4747.8	4581.0	4065.3	3630.4	3306.8	3301.7	3630.4	4065.3	4055.1	4095.6	4237.2
32.5°	4601.2	4287.8	3797.2	3498.9	3190.5	3185.5	3595.1	3943.9	3933.8	3989.4	4095.6
35°	4464.7	4060.2	3433.2	3347.3	3043.9	3049.0	3509.1	3802.3	3807.4	3857.9	3923.6
37.5°	4323.1	3863.0	3033.8	3180.4	2902.3	2902.3	3392.8	3670.9	3660.8	3675.9	3767.0
40°	4156.3	3554.5	2679.8	2963.0	2770.9	2755.6	3251.2	3529.3	3493.9	3488.9	3615.3
42.5°	3979.3	3215.8	2416.9	2674.8	2619.2	2599.0	3079.2	3357.4	3291.7	3306.8	3468.6
45°	3787.2	3124.8	2214.6	2260.1	2462.4	2447.3	2892.2	3160.2	3114.7	3155.1	3322.0
47.5°	3595.1	2942.8	2149.0	1875.9	2295.6	2290.5	2684.9	2968.1	2942.8	2983.2	3160.2
50°	3332.1	2740.5	2143.9	1607.9	2108.4	2128.7	2437.1	2780.9	2780.9	2816.4	3003.4
52.5°	2993.3	2492.8	1946.7	1456.3	1891.0	1951.8	2219.7	2619.2	2629.2	2664.7	2831.5
55°	2684.9	2234.9	1805.1	1339.9	1633.1	1764.6	2007.3	2452.3	2472.6	2507.9	2659.6
57.5°	2401.8	1860.7	1774.8	1203.4	1395.5	1522.0	1820.3	2290.5	2300.7	2330.9	2477.6
60°	2098.4	1345.0	1628.2	1056.8	1188.2	1284.3	1648.4	2098.4	2133.7	2153.9	2280.3
62.5°	1754.6	975.9	1476.5	955.7	1087.1	1107.4	1506.7	1916.3	1961.8	1977.0	2052.9
65°	1248.9	819.1	1254.0	869.7	981.0	985.9	1355.1	1729.3	1769.7	1795.0	1850.6
67.5°	844.4	667.4	955.7	788.7	900.0	905.1	1208.4	1511.8	1567.4	1587.7	1623.1
70°	586.5	444.9	707.9	702.8	809.1	819.1	1051.7	1314.6	1365.2	1380.4	1400.6
72.5°	429.8	359.0	586.5	632.1	712.9	723.1	889.9	1092.1	1142.7	1157.8	1168.0
75°	328.7	379.2	475.3	551.1	606.8	611.8	728.1	889.9	925.3	935.4	940.4
77.5°	262.9	354.0	348.9	444.9	495.5	485.5	571.4	687.6	718.0	718.0	718.0
80°	197.2	278.1	262.9	318.5	364.0	354.0	409.6	490.4	500.6	510.6	505.7
82.5°	146.6	177.0	177.0	202.3	242.7	232.6	273.0	318.5	318.5	318.5	328.7
85°	91.0	101.1	80.9	106.2	136.6	131.5	151.7	171.9	177.0	177.0	166.8
87.5°	55.6	45.5	25.3	40.4	60.7	60.7	70.8	75.8	70.8	70.8	70.8
90°	16.0	11.1	6.2	11.1	16.0	17.2	27.1	40.2	46.8	41.6	31.2
92.5°	108.4	66.4	24.6	66.4	108.4	118.8	167.0	231.4	263.5	231.0	165.8
95°	212.4	135.8	59.2	135.8	212.4	231.6	411.1	650.7	770.4	687.4	521.6
97.5°	237.4	169.8	102.2	169.8	237.4	254.4	553.9	953.2	1152.9	1100.5	995.6
100°	258.1	196.8	135.5	196.8	258.1	273.4	605.8	1048.9	1270.5	1274.3	1282.0
102.5°	278.2	221.0	163.8	221.0	278.2	292.5	629.6	1079.1	1303.8	1370.5	1504.1
105°	308.7	260.3	211.8	260.3	308.7	320.8	647.2	1082.5	1300.1	1449.8	1749.2
107.5°	351.5	306.3	261.2	306.3	351.5	362.7	650.6	1034.3	1226.2	1435.0	1852.8
110°	376.0	335.2	294.4	335.2	376.0	386.1	645.6	991.6	1164.6	1398.1	1865.0

TEST NUMBER: P934577

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	404.7	365.8	327.0	365.8	404.7	414.4	645.8	954.3	1108.5	1347.5	1825.4
115°	448.0	412.1	376.3	412.1	448.0	457.0	651.8	911.5	1041.4	1271.6	1731.9
117.5°	490.0	457.5	424.9	457.5	490.0	498.2	663.8	884.7	995.2	1203.0	1618.4
120°	514.5	484.0	453.3	484.0	514.5	522.2	673.7	875.8	976.8	1166.6	1546.2
122.5°	542.8	511.9	481.0	511.9	542.8	550.6	687.9	871.0	962.5	1133.4	1475.4
125°	579.9	551.7	523.5	551.7	579.9	586.9	707.1	867.1	947.2	1092.4	1382.7
127.5°	614.9	586.4	558.0	586.4	614.9	622.0	726.1	864.8	934.2	1058.9	1308.2
130°	637.7	607.2	576.5	607.2	637.7	645.4	740.0	866.2	929.4	1040.3	1262.3
132.5°	656.9	626.2	595.5	626.2	656.9	664.5	751.4	867.1	925.0	1024.4	1223.1
135°	679.7	651.8	623.9	651.8	679.7	686.6	763.6	866.3	917.6	1000.9	1167.3
137.5°	708.2	680.5	652.8	680.5	708.2	715.0	782.2	871.7	916.4	986.7	1127.5
140°	727.7	702.3	676.8	702.3	727.7	734.1	793.4	872.5	912.0	972.8	1094.4
142.5°	742.4	718.8	695.3	718.8	742.4	748.3	802.9	875.7	912.0	965.4	1072.2
145°	764.6	744.1	723.6	744.1	764.6	769.8	815.2	875.7	906.0	949.6	1036.9
147.5°	791.9	771.9	752.0	771.9	791.9	796.9	833.3	881.8	906.0	940.3	1009.0
150°	806.6	788.4	770.4	788.4	806.6	811.0	842.7	884.8	906.0	934.9	992.9
152.5°	816.9	803.2	789.5	803.2	816.9	820.3	848.9	886.9	906.0	930.8	980.3
155°	838.1	828.0	817.8	828.0	838.1	840.6	862.4	891.4	906.0	925.7	965.0
157.5°	858.5	848.7	838.8	848.7	858.5	860.9	876.0	896.0	906.0	921.3	951.9
160°	868.3	860.6	853.0	860.6	868.3	870.2	882.2	898.0	906.0	919.1	945.3
162.5°	878.7	872.9	867.1	872.9	878.7	880.1	888.7	900.2	906.0	917.0	939.1
165°	892.9	887.7	882.6	887.7	892.9	894.2	898.1	903.4	906.0	913.9	929.8
167.5°	901.6	899.1	896.7	899.1	901.6	902.2	905.5	909.8	912.0	917.2	927.7
170°	910.8	908.4	906.0	908.4	910.8	911.4	911.6	911.9	912.0	917.2	927.7
172.5°	911.9	911.3	910.8	911.3	911.9	912.0	912.0	912.0	912.0	916.1	924.4
175°	917.6	917.6	917.6	917.6	917.6	917.6	915.7	913.2	912.0	914.6	919.9
177.5°	917.6	917.6	917.6	917.6	917.6	917.6	916.2	914.3	913.3	915.4	919.5
180°	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6

TEST NUMBER: P934577

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5	5344.5
2.5°	5157.4	5142.2	5162.5	5106.9	5162.5	5142.2	5157.4	5192.8	5162.5	5182.7	5202.9
5°	4525.4	4500.1	4419.2	4353.5	4419.2	4500.1	4525.4	4631.6	4682.1	4773.1	4894.4
7.5°	4045.1	4024.8	4004.6	3964.2	4004.6	4024.8	4045.1	4075.3	4125.9	4206.8	4297.8
10°	3938.9	3943.9	3974.2	3969.2	3974.2	3943.9	3938.9	3928.7	3913.6	3928.7	3984.4
12.5°	4211.9	4257.4	4424.2	4414.2	4424.2	4257.4	4211.9	4009.6	3873.1	3847.8	3857.9
15°	4525.4	4540.6	4575.9	4581.0	4575.9	4540.6	4525.4	4444.5	4034.9	3857.9	3802.3
17.5°	4555.7	4560.8	4586.1	4586.1	4586.1	4560.8	4555.7	4520.3	4383.8	4146.1	3832.7
20°	4530.4	4540.6	4591.2	4601.2	4591.2	4540.6	4530.4	4484.9	4409.1	4323.1	4085.5
22.5°	4520.3	4540.6	4581.0	4575.9	4581.0	4540.6	4520.3	4449.5	4383.8	4323.1	4227.0
25°	4469.7	4469.7	4474.8	4479.9	4474.8	4469.7	4469.7	4414.2	4282.7	4267.5	4211.9
27.5°	4363.6	4373.7	4404.0	4398.9	4404.0	4373.7	4363.6	4343.4	4201.8	4186.6	4146.1
30°	4267.5	4257.4	4232.1	4211.9	4232.1	4257.4	4267.5	4237.2	4095.6	4055.1	4065.3
32.5°	4105.7	4080.4	4055.1	4040.0	4055.1	4080.4	4105.7	4095.6	3989.4	3933.8	3943.9
35°	3913.6	3918.7	3913.6	3898.4	3913.6	3918.7	3913.6	3923.6	3857.9	3807.4	3802.3
37.5°	3777.0	3787.2	3782.1	3761.9	3782.1	3787.2	3777.0	3767.0	3675.9	3660.8	3670.9
40°	3635.5	3640.6	3635.5	3620.3	3635.5	3640.6	3635.5	3615.3	3488.9	3493.9	3529.3
42.5°	3498.9	3493.9	3478.7	3468.6	3478.7	3493.9	3498.9	3468.6	3306.8	3291.7	3357.4
45°	3342.2	3347.3	3316.9	3301.7	3316.9	3347.3	3342.2	3322.0	3155.1	3114.7	3160.2
47.5°	3185.5	3185.5	3160.2	3145.0	3160.2	3185.5	3185.5	3160.2	2983.2	2942.8	2968.1
50°	3018.6	3013.6	2978.1	2973.1	2978.1	3013.6	3018.6	3003.4	2816.4	2780.9	2780.9
52.5°	2826.4	2826.4	2831.5	2841.6	2831.5	2826.4	2826.4	2831.5	2664.7	2629.2	2619.2
55°	2659.6	2664.7	2700.1	2710.2	2700.1	2664.7	2659.6	2659.6	2507.9	2472.6	2452.3
57.5°	2487.7	2487.7	2513.0	2513.0	2513.0	2487.7	2487.7	2477.6	2330.9	2300.7	2290.5
60°	2290.5	2300.7	2320.9	2315.8	2320.9	2300.7	2290.5	2280.3	2153.9	2133.7	2098.4
62.5°	2083.2	2093.3	2098.4	2088.2	2098.4	2093.3	2083.2	2052.9	1977.0	1961.8	1916.3
65°	1865.8	1875.9	1880.9	1870.8	1880.9	1875.9	1865.8	1850.6	1795.0	1769.7	1729.3
67.5°	1643.3	1638.2	1633.1	1653.4	1633.1	1638.2	1643.3	1623.1	1587.7	1567.4	1511.8
70°	1415.7	1415.7	1410.7	1420.8	1410.7	1415.7	1415.7	1400.6	1380.4	1365.2	1314.6
72.5°	1173.1	1168.0	1188.2	1173.1	1188.2	1168.0	1173.1	1168.0	1157.8	1142.7	1092.1
75°	935.4	945.5	935.4	950.6	935.4	945.5	935.4	940.4	935.4	925.3	889.9
77.5°	712.9	723.1	712.9	712.9	712.9	723.1	712.9	718.0	718.0	718.0	687.6
80°	505.7	500.6	500.6	495.5	500.6	500.6	505.7	505.7	510.6	500.6	490.4
82.5°	323.6	318.5	318.5	328.7	318.5	318.5	323.6	328.7	318.5	318.5	318.5
85°	177.0	182.1	171.9	171.9	171.9	182.1	177.0	166.8	177.0	177.0	171.9
87.5°	65.7	60.7	60.7	60.7	60.7	60.7	65.7	70.8	70.8	70.8	75.8
90°	23.4	23.4	23.4	23.4	23.4	23.4	23.4	31.2	41.6	46.8	40.2
92.5°	117.0	112.3	93.7	75.1	93.7	112.3	117.0	165.8	231.0	263.5	231.4
95°	397.2	383.1	326.7	270.3	326.7	383.1	397.2	521.6	687.4	770.4	650.7
97.5°	917.0	890.2	782.9	675.6	782.9	890.2	917.0	995.6	1100.5	1152.9	953.2
100°	1287.7	1255.8	1128.0	1000.2	1128.0	1255.8	1287.7	1282.0	1274.3	1270.5	1048.9
102.5°	1604.3	1576.9	1467.4	1357.9	1467.4	1576.9	1604.3	1504.1	1370.5	1303.8	1079.1
105°	1973.8	1959.0	1900.3	1841.4	1900.3	1959.0	1973.8	1749.2	1449.8	1300.1	1082.5
107.5°	2166.0	2169.6	2183.7	2198.0	2183.7	2169.6	2166.0	1852.8	1435.0	1226.2	1034.3
110°	2215.2	2230.5	2291.8	2353.1	2291.8	2230.5	2215.2	1865.0	1398.1	1164.6	991.6

TEST NUMBER: P934577

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	2183.8	2207.3	2301.6	2395.7	2301.6	2207.3	2183.8	1825.4	1347.5	1108.5	954.3
115°	2077.3	2109.9	2240.5	2371.1	2240.5	2109.9	2077.3	1731.9	1271.6	1041.4	911.5
117.5°	1930.0	1966.2	2111.0	2255.8	2111.0	1966.2	1930.0	1618.4	1203.0	995.2	884.7
120°	1830.9	1866.1	2006.8	2147.5	2006.8	1866.1	1830.9	1546.2	1166.6	976.8	875.8
122.5°	1731.7	1766.4	1905.2	2044.0	1905.2	1766.4	1731.7	1475.4	1133.4	962.5	871.0
125°	1600.6	1632.5	1760.3	1888.2	1760.3	1632.5	1600.6	1382.7	1092.4	947.2	867.1
127.5°	1495.3	1522.3	1630.1	1737.9	1630.1	1522.3	1495.3	1308.2	1058.9	934.2	864.8
130°	1428.8	1453.7	1553.4	1653.0	1553.4	1453.7	1428.8	1262.3	1040.3	929.4	866.2
132.5°	1372.1	1394.4	1483.6	1572.9	1483.6	1394.4	1372.1	1223.1	1024.4	925.0	867.1
135°	1292.1	1311.3	1388.2	1465.1	1388.2	1311.3	1292.1	1167.3	1000.9	917.6	866.3
137.5°	1232.9	1248.7	1311.6	1374.6	1311.6	1248.7	1232.9	1127.5	986.7	916.4	871.7
140°	1185.5	1200.3	1259.0	1317.9	1259.0	1200.3	1185.5	1094.4	972.8	912.0	872.5
142.5°	1152.3	1164.9	1215.6	1266.2	1215.6	1164.9	1152.3	1072.2	965.4	912.0	875.7
145°	1102.4	1111.9	1150.3	1188.6	1150.3	1111.9	1102.4	1036.9	949.6	906.0	875.7
147.5°	1060.5	1068.5	1100.2	1132.0	1100.2	1068.5	1060.5	1009.0	940.3	906.0	881.8
150°	1036.4	1042.9	1068.6	1094.4	1068.6	1042.9	1036.4	992.9	934.9	906.0	884.8
152.5°	1017.4	1022.3	1041.7	1061.1	1041.7	1022.3	1017.4	980.3	930.8	906.0	886.9
155°	994.6	997.8	1010.7	1023.6	1010.7	997.8	994.6	965.0	925.7	906.0	891.4
157.5°	974.9	977.2	986.1	995.2	986.1	977.2	974.9	951.9	921.3	906.0	896.0
160°	965.0	966.3	971.6	976.8	971.6	966.3	965.0	945.3	919.1	906.0	898.0
162.5°	955.8	957.0	961.9	966.9	961.9	957.0	955.8	939.1	917.0	906.0	900.2
165°	941.6	942.9	948.2	953.4	948.2	942.9	941.6	929.8	913.9	906.0	903.4
167.5°	935.4	936.0	938.2	940.4	938.2	936.0	935.4	927.7	917.2	912.0	909.8
170°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	927.7	917.2	912.0	911.9
172.5°	930.6	930.1	928.2	926.3	928.2	930.1	930.6	924.4	916.1	912.0	912.0
175°	923.8	923.8	923.8	923.8	923.8	923.8	923.8	919.9	914.6	912.0	913.2
177.5°	922.6	922.0	919.8	917.6	919.8	922.0	922.6	919.5	915.4	913.3	914.3
180°	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6	917.6

TEST NUMBER: P934577

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	5344.5	5344.5	5344.5	5344.5	5344.5
2.5°	5278.8	5304.1	5319.2	5339.5	5390.1
5°	5076.5	5172.6	5202.9	5278.8	5369.7
7.5°	4631.6	4924.8	5005.7	5187.8	5329.3
10°	4201.8	4495.0	4636.6	5066.5	5278.8
12.5°	3984.4	4156.3	4252.3	4854.0	5208.0
15°	3847.8	3969.2	4040.0	4570.8	5127.1
17.5°	3741.7	3827.6	3878.2	4292.8	5015.9
20°	3675.9	3716.4	3761.9	4090.6	4889.5
22.5°	3630.4	3605.1	3640.6	3948.9	4717.6
25°	3600.0	3504.0	3544.5	3837.7	4515.3
27.5°	3625.3	3413.0	3428.1	3736.6	4302.9
30°	3630.4	3301.7	3306.8	3630.4	4065.3
32.5°	3595.1	3185.5	3190.5	3498.9	3797.2
35°	3509.1	3049.0	3043.9	3347.3	3433.2
37.5°	3392.8	2902.3	2902.3	3180.4	3033.8
40°	3251.2	2755.6	2770.9	2963.0	2679.8
42.5°	3079.2	2599.0	2619.2	2674.8	2416.9
45°	2892.2	2447.3	2462.4	2260.1	2214.6
47.5°	2684.9	2290.5	2295.6	1875.9	2149.0
50°	2437.1	2128.7	2108.4	1607.9	2143.9
52.5°	2219.7	1951.8	1891.0	1456.3	1946.7
55°	2007.3	1764.6	1633.1	1339.9	1805.1
57.5°	1820.3	1522.0	1395.5	1203.4	1774.8
60°	1648.4	1284.3	1188.2	1056.8	1628.2
62.5°	1506.7	1107.4	1087.1	955.7	1476.5
65°	1355.1	985.9	981.0	869.7	1254.0
67.5°	1208.4	905.1	900.0	788.7	955.7
70°	1051.7	819.1	809.1	702.8	707.9
72.5°	889.9	723.1	712.9	632.1	586.5
75°	728.1	611.8	606.8	551.1	475.3
77.5°	571.4	485.5	495.5	444.9	348.9
80°	409.6	354.0	364.0	318.5	262.9
82.5°	273.0	232.6	242.7	202.3	177.0
85°	151.7	131.5	136.6	106.2	80.9
87.5°	70.8	60.7	60.7	40.4	25.3
90°	27.1	17.2	16.0	11.1	6.2
92.5°	167.0	118.8	108.4	66.4	24.6
95°	411.1	231.6	212.4	135.8	59.2
97.5°	553.9	254.4	237.4	169.8	102.2
100°	605.8	273.4	258.1	196.8	135.5
102.5°	629.6	292.5	278.2	221.0	163.8
105°	647.2	320.8	308.7	260.3	211.8
107.5°	650.6	362.7	351.5	306.3	261.2
110°	645.6	386.1	376.0	335.2	294.4



TEST NUMBER: P934577

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	645.8	414.4	404.7	365.8	327.0
115°	651.8	457.0	448.0	412.1	376.3
117.5°	663.8	498.2	490.0	457.5	424.9
120°	673.7	522.2	514.5	484.0	453.3
122.5°	687.9	550.6	542.8	511.9	481.0
125°	707.1	586.9	579.9	551.7	523.5
127.5°	726.1	622.0	614.9	586.4	558.0
130°	740.0	645.4	637.7	607.2	576.5
132.5°	751.4	664.5	656.9	626.2	595.5
135°	763.6	686.6	679.7	651.8	623.9
137.5°	782.2	715.0	708.2	680.5	652.8
140°	793.4	734.1	727.7	702.3	676.8
142.5°	802.9	748.3	742.4	718.8	695.3
145°	815.2	769.8	764.6	744.1	723.6
147.5°	833.3	796.9	791.9	771.9	752.0
150°	842.7	811.0	806.6	788.4	770.4
152.5°	848.9	820.3	816.9	803.2	789.5
155°	862.4	840.6	838.1	828.0	817.8
157.5°	876.0	860.9	858.5	848.7	838.8
160°	882.2	870.2	868.3	860.6	853.0
162.5°	888.7	880.1	878.7	872.9	867.1
165°	898.1	894.2	892.9	887.7	882.6
167.5°	905.5	902.2	901.6	899.1	896.7
170°	911.6	911.4	910.8	908.4	906.0
172.5°	912.0	912.0	911.9	911.3	910.8
175°	915.7	917.6	917.6	917.6	917.6
177.5°	916.2	917.6	917.6	917.6	917.6
180°	917.6	917.6	917.6	917.6	917.6

TEST NUMBER: P934577

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.23	17.30	16.99	18.09	19.04	19.08	20.15	19.84	20.94	21.89
	3H	16.72	17.68	17.50	18.48	19.46	20.45	21.41	21.22	22.21	23.19
	4H	16.92	17.83	17.71	18.63	19.63	20.90	21.81	21.70	22.62	23.61
	6H	17.05	17.89	17.86	18.70	19.71	21.20	22.04	22.01	22.86	23.87
	8H	17.06	17.86	17.87	18.69	19.70	21.29	22.09	22.11	22.92	23.93
	12H	17.03	17.80	17.86	18.62	19.66	21.34	22.10	22.16	22.93	23.96
4H	2H	17.29	18.20	18.09	19.00	20.00	19.51	20.42	20.31	21.23	22.22
	3H	18.34	19.09	19.15	19.93	20.95	21.04	21.80	21.85	22.64	23.65
	4H	18.62	19.31	19.45	20.15	21.19	21.58	22.27	22.41	23.11	24.15
	6H	18.76	19.35	19.60	20.22	21.26	21.97	22.56	22.81	23.43	24.47
	8H	18.77	19.33	19.61	20.18	21.24	22.08	22.64	22.93	23.50	24.55
	12H	18.75	19.25	19.61	20.13	21.19	22.15	22.65	23.02	23.53	24.60
8H	4H	19.09	19.65	19.94	20.51	21.57	21.73	22.28	22.57	23.14	24.20
	6H	19.37	19.83	20.24	20.73	21.78	22.18	22.64	23.05	23.54	24.60
	8H	19.41	19.82	20.29	20.71	21.79	22.33	22.74	23.22	23.64	24.71
	12H	19.40	19.76	20.29	20.65	21.78	22.45	22.81	23.33	23.69	24.82
12H	4H	19.11	19.61	19.98	20.49	21.55	21.70	22.20	22.57	23.08	24.14
	6H	19.43	19.84	20.31	20.73	21.81	22.17	22.59	23.06	23.48	24.55
	8H	19.51	19.87	20.39	20.75	21.88	22.35	22.71	23.24	23.60	24.72

END OF REPORT