

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P933881

Luminaire Tested: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P933881
REPORT IS A COMBINATION OF REPORTS P933673 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7862.4 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 66
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P933881

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K

Luminous Intensity Polar Plot



TEST NUMBER: P933881

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66		
1	101	97	93	89	95	91	88	85	81	78	76	71	69	68	62	61	60	55		
2	92	85	78	73	87	80	74	70	71	67	63	63	59	56	55	52	50	46		
3	84	75	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39		
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	43	40	37	34		
5	71	59	50	44	66	56	48	43	50	44	39	44	39	35	39	35	32	29		
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28	26		
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25	23		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18		
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6143	6143	6143	6143
5°	6192	6202	6192	4877
10°	6153	6109	6153	4368
15°	6088	5977	6088	4991
20°	5963	5820	5963	5001
25°	5705	5591	5705	4895
30°	5370	5401	5370	4663
35°	4790	5161	4790	4407
40°	3993	4878	3993	4214
45°	3570	4548	3570	3991
50°	3796	4153	3796	3768
55°	3575	3728	3575	3639
60°	3690	3166	3690	3333
65°	3351	2617	3351	2925
70°	2326	2086	2326	2452
75°	2047	1542	2047	1846
80°	1662	1019	1662	1110
85°	975	540	975	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 5469 cd/sqm

TEST NUMBER: P933881

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.3	2.3
10°-20°	509.1	6.5
20°-30°	786.9	10.0
30°-40°	939.4	11.9
40°-50°	944.9	12.0
50°-60°	822.2	10.5
60°-70°	583.0	7.4
70°-80°	308.4	3.9
80°-90°	78.4	1.0
90°-100°	203.8	2.6
100°-110°	535.9	6.8
110°-120°	555.7	7.1
120°-130°	445.7	5.7
130°-140°	349.7	4.4
140°-150°	268.4	3.4
150°-160°	193.3	2.5
160°-170°	118.3	1.5
170°-180°	40.0	0.5
0°-30°	1475.3	18.8
0°-40°	2414.7	30.7
0°-60°	4181.9	53.2
0°-90°	5151.7	65.5
90°-120°	1295.4	16.5
90°-150°	2359.2	30.0
90°-180°	2711.0	34.5
0°-180°	7862.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1986	1986	1986	1986	1986	
5°	1996	2058	1996	1618	1996	189
15°	1906	2039	1906	1702	1906	536
25°	1678	1902	1678	1665	1678	771
35°	1276	1697	1276	1449	1276	789
45°	823	1398	823	1227	823	659
55°	671	1032	671	1007	671	616
65°	466	622	466	695	466	445
75°	177	295	177	353	177	186
85°	30	75	30	64	30	41
90°	3	11	3	11	3	4
95°	27	123	27	123	27	30
105°	97	839	97	839	97	102
115°	172	1080	172	1080	172	169
125°	238	860	238	860	238	212
135°	284	668	284	668	284	220
145°	330	542	330	542	330	207
155°	373	466	373	466	373	171
165°	402	434	402	434	402	114
175°	418	421	418	421	418	40
180°	418	418	418	418	418	

TEST NUMBER: P933881

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2
2.5°	2003.1	2003.1	2014.5	2018.2	2018.2	2012.6	2007.0	2012.6	2029.5	2035.1	2033.2
5°	1995.7	2010.7	2031.4	2035.1	2038.9	2037.1	2033.2	2037.1	2055.8	2059.6	2061.4
7.5°	1980.6	2008.8	2035.1	2040.8	2046.4	2040.8	2038.9	2042.7	2061.4	2065.2	2065.2
10°	1961.9	2001.3	2031.4	2035.1	2040.8	2035.1	2035.1	2042.7	2061.4	2065.2	2067.1
12.5°	1935.5	1990.1	2018.2	2022.0	2029.5	2027.6	2025.8	2033.2	2052.1	2055.8	2055.8
15°	1905.5	1969.3	1995.7	1999.4	2012.6	2008.8	2008.8	2016.3	2037.1	2042.7	2040.8
17.5°	1864.2	1943.1	1973.2	1978.8	1988.2	1986.2	1988.2	1995.7	2014.5	2018.2	2020.1
20°	1817.2	1907.3	1943.1	1948.7	1958.1	1958.1	1958.1	1967.5	1986.2	1993.8	1993.8
22.5°	1753.3	1869.8	1907.3	1911.2	1922.4	1922.4	1926.2	1939.3	1956.2	1958.1	1958.1
25°	1678.1	1828.4	1860.3	1871.6	1882.9	1888.5	1894.2	1901.7	1907.3	1905.5	1907.3
27.5°	1599.2	1775.8	1817.2	1824.7	1839.7	1845.3	1852.9	1854.7	1856.6	1862.2	1858.5
30°	1510.8	1702.5	1764.5	1772.1	1796.5	1800.3	1792.7	1796.5	1805.9	1809.6	1813.4
32.5°	1411.3	1593.5	1710.1	1727.0	1749.5	1738.3	1736.3	1742.0	1757.0	1757.0	1760.8
35°	1275.9	1509.0	1659.3	1674.4	1691.3	1678.1	1685.6	1687.5	1696.9	1702.5	1700.6
37.5°	1127.5	1435.7	1606.7	1618.0	1631.1	1614.2	1625.4	1631.1	1638.6	1634.9	1634.9
40°	995.9	1321.0	1544.6	1552.2	1563.4	1550.3	1561.6	1565.4	1569.1	1565.4	1563.4
42.5°	898.2	1195.1	1478.9	1488.3	1480.8	1490.2	1493.9	1501.5	1495.8	1488.3	1488.3
45°	823.0	1161.3	1407.5	1418.7	1407.5	1422.6	1428.2	1428.2	1411.3	1407.5	1405.6
47.5°	798.7	1093.7	1336.1	1336.1	1330.5	1349.3	1358.6	1345.5	1328.6	1322.9	1322.9
50°	796.8	1018.5	1238.4	1230.8	1257.2	1279.7	1270.3	1257.2	1244.0	1223.4	1223.4
52.5°	723.5	926.4	1112.5	1140.7	1182.0	1195.1	1180.1	1166.9	1144.4	1135.0	1127.5
55°	670.9	830.6	997.8	1054.2	1097.4	1114.4	1086.1	1073.0	1039.2	1033.6	1029.8
57.5°	659.6	691.5	892.6	964.0	1016.7	1014.8	997.8	973.4	945.2	939.6	937.7
60°	605.1	499.9	779.9	864.4	918.9	913.3	898.2	875.7	849.4	845.6	841.9
62.5°	548.7	362.7	652.0	747.9	824.9	823.0	810.0	776.1	757.3	747.9	740.4
65°	466.1	304.4	464.2	622.0	732.9	736.6	708.4	684.1	663.3	652.0	650.2
67.5°	355.2	248.1	313.8	518.7	644.6	640.8	605.1	593.8	567.5	561.9	550.6
70°	263.1	165.4	218.0	421.0	558.2	548.7	520.5	507.3	483.0	469.8	462.2
72.5°	218.0	133.4	159.7	327.0	469.8	458.5	434.1	419.1	398.4	387.1	379.6
75°	176.6	140.9	122.2	242.4	381.4	374.0	351.4	336.3	319.4	304.4	306.3
77.5°	129.6	131.5	97.7	178.5	302.5	291.3	278.1	259.4	251.8	236.8	236.8
80°	97.7	103.4	73.3	122.2	218.0	218.0	206.7	193.5	180.4	172.9	172.9
82.5°	65.8	65.8	54.5	77.1	148.4	142.8	135.3	131.5	124.0	120.3	120.3
85°	30.1	37.5	33.8	47.0	80.8	84.5	84.5	80.8	78.9	75.2	77.1
87.5°	9.4	16.9	20.6	26.3	41.4	43.2	45.1	45.1	45.1	47.0	47.0
90°	2.8	5.0	7.3	7.8	12.3	18.3	21.3	19.0	14.2	10.6	10.6
92.5°	11.2	30.3	49.4	54.2	76.1	105.4	120.1	105.3	75.6	53.3	51.2
95°	26.9	61.8	96.8	105.5	187.4	296.5	351.1	313.3	237.7	181.0	174.6
97.5°	46.6	77.4	108.3	115.9	252.4	434.4	525.4	501.5	453.7	417.9	405.6
100°	61.7	89.7	117.6	124.6	276.1	478.0	579.0	580.8	584.2	586.8	572.3
102.5°	74.6	100.7	126.7	133.3	286.9	491.8	594.1	624.6	685.4	731.0	718.5
105°	96.6	118.6	140.7	146.2	295.0	493.2	592.4	660.6	797.1	899.4	892.7
107.5°	119.0	139.5	160.2	165.3	296.5	471.3	558.7	653.9	844.2	987.1	988.6
110°	134.1	152.7	171.3	176.0	294.2	451.9	530.7	637.1	849.8	1009.5	1016.5

TEST NUMBER: P933881

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	149.1	166.7	184.5	188.9	294.3	434.9	505.2	614.1	831.8	995.2	1005.9
115°	171.5	187.8	204.2	208.3	297.0	415.3	474.6	579.5	789.2	946.6	961.5
117.5°	193.6	208.5	223.3	227.1	302.5	403.2	453.6	548.3	737.6	879.5	896.1
120°	206.5	220.5	234.5	238.0	307.0	399.0	445.1	531.5	704.6	834.3	850.4
122.5°	219.2	233.3	247.3	250.9	313.5	396.9	438.6	516.5	672.3	789.1	804.9
125°	238.5	251.4	264.3	267.5	322.2	395.2	431.6	497.7	630.1	729.4	743.9
127.5°	254.2	267.2	280.2	283.5	330.9	394.1	425.7	482.5	596.2	681.4	693.7
130°	262.6	276.7	290.7	294.1	337.3	394.7	423.5	474.1	575.3	651.1	662.5
132.5°	271.4	285.3	299.3	302.8	342.4	395.2	421.5	466.8	557.4	625.3	635.5
135°	284.3	297.0	309.7	312.9	348.0	394.8	418.2	456.1	531.9	588.8	597.6
137.5°	297.5	310.1	322.6	325.8	356.4	397.2	417.6	449.6	513.7	561.8	569.0
140°	308.4	320.0	331.7	334.6	361.6	397.6	415.6	443.3	498.7	540.2	547.0
142.5°	316.8	327.6	338.3	341.0	365.8	399.0	415.6	439.9	488.6	525.1	530.9
145°	329.8	339.1	348.5	350.8	371.5	399.0	412.8	432.7	472.5	502.3	506.7
147.5°	342.7	351.7	360.9	363.1	379.7	401.8	412.8	428.5	459.8	483.3	486.9
150°	351.1	359.3	367.5	369.6	384.0	403.2	412.8	426.1	452.5	472.3	475.2
152.5°	359.8	366.0	372.2	373.8	386.8	404.1	412.8	424.1	446.7	463.6	465.9
155°	372.7	377.2	381.9	383.0	392.9	406.2	412.8	421.8	439.8	453.3	454.8
157.5°	382.2	386.7	391.3	392.4	399.2	408.3	412.8	419.8	433.7	444.2	445.2
160°	388.7	392.2	395.7	396.6	402.0	409.2	412.8	418.8	430.8	439.7	440.3
162.5°	395.2	397.8	400.4	401.1	405.0	410.2	412.8	417.9	428.0	435.5	436.1
165°	402.2	404.5	406.9	407.5	409.3	411.6	412.8	416.5	423.7	429.1	429.6
167.5°	408.6	409.7	410.9	411.1	412.6	414.6	415.6	418.0	422.7	426.3	426.6
170°	412.8	413.9	415.1	415.3	415.4	415.5	415.6	418.0	422.7	426.3	426.3
172.5°	415.1	415.3	415.5	415.6	415.6	415.6	415.6	417.5	421.2	424.0	423.8
175°	418.2	418.2	418.2	418.2	417.3	416.2	415.6	416.8	419.2	421.0	421.0
177.5°	418.2	418.2	418.2	418.2	417.5	416.7	416.2	417.1	419.0	420.4	420.1
180°	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2

TEST NUMBER: P933881

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2
2.5°	2037.1	2031.4	2037.1	2033.2	2035.1	2029.5	2012.6	2007.0	2012.6	2018.2	2018.2
5°	2061.4	2057.7	2061.4	2061.4	2059.6	2055.8	2037.1	2033.2	2037.1	2038.9	2035.1
7.5°	2069.0	2063.3	2069.0	2065.2	2065.2	2061.4	2042.7	2038.9	2040.8	2046.4	2040.8
10°	2069.0	2063.3	2069.0	2067.1	2065.2	2061.4	2042.7	2035.1	2035.1	2040.8	2035.1
12.5°	2059.6	2055.8	2059.6	2055.8	2055.8	2052.1	2033.2	2025.8	2027.6	2029.5	2022.0
15°	2044.5	2038.9	2044.5	2040.8	2042.7	2037.1	2016.3	2008.8	2008.8	2012.6	1999.4
17.5°	2022.0	2014.5	2022.0	2020.1	2018.2	2014.5	1995.7	1988.2	1986.2	1988.2	1978.8
20°	1995.7	1990.1	1995.7	1993.8	1993.8	1986.2	1967.5	1958.1	1958.1	1958.1	1948.7
22.5°	1954.3	1948.7	1954.3	1958.1	1958.1	1956.2	1939.3	1926.2	1922.4	1922.4	1911.2
25°	1907.3	1901.7	1907.3	1907.3	1905.5	1907.3	1901.7	1894.2	1888.5	1882.9	1871.6
27.5°	1862.2	1858.5	1862.2	1858.5	1862.2	1856.6	1854.7	1852.9	1845.3	1839.7	1824.7
30°	1817.2	1813.4	1817.2	1813.4	1809.6	1805.9	1796.5	1792.7	1800.3	1796.5	1772.1
32.5°	1760.8	1757.0	1760.8	1760.8	1757.0	1757.0	1742.0	1736.3	1738.3	1749.5	1727.0
35°	1702.5	1696.9	1702.5	1700.6	1702.5	1696.9	1687.5	1685.6	1678.1	1691.3	1674.4
37.5°	1634.9	1629.3	1634.9	1634.9	1634.9	1638.6	1631.1	1625.4	1614.2	1631.1	1618.0
40°	1565.4	1557.8	1565.4	1563.4	1565.4	1569.1	1565.4	1561.6	1550.3	1563.4	1552.2
42.5°	1486.5	1484.5	1486.5	1488.3	1488.3	1495.8	1501.5	1493.9	1490.2	1480.8	1488.3
45°	1401.8	1398.1	1401.8	1405.6	1407.5	1411.3	1428.2	1428.2	1422.6	1407.5	1418.7
47.5°	1311.6	1302.3	1311.6	1322.9	1322.9	1328.6	1345.5	1358.6	1349.3	1330.5	1336.1
50°	1215.8	1217.7	1215.8	1223.4	1223.4	1244.0	1257.2	1270.3	1279.7	1257.2	1230.8
52.5°	1121.8	1120.0	1121.8	1127.5	1135.0	1144.4	1166.9	1180.1	1195.1	1182.0	1140.7
55°	1027.9	1031.7	1027.9	1029.8	1033.6	1039.2	1073.0	1086.1	1114.4	1097.4	1054.2
57.5°	933.9	928.3	933.9	937.7	939.6	945.2	973.4	997.8	1014.8	1016.7	964.0
60°	824.9	817.4	824.9	841.9	845.6	849.4	875.7	898.2	913.3	918.9	864.4
62.5°	729.1	716.0	729.1	740.4	747.9	757.3	776.1	810.0	823.0	824.9	747.9
65°	627.6	622.0	627.6	650.2	652.0	663.3	684.1	708.4	736.6	732.9	622.0
67.5°	535.6	535.6	535.6	550.6	561.9	567.5	593.8	605.1	640.8	644.6	518.7
70°	451.0	449.2	451.0	462.2	469.8	483.0	507.3	520.5	548.7	558.2	421.0
72.5°	370.2	368.3	370.2	379.6	387.1	398.4	419.1	434.1	458.5	469.8	327.0
75°	298.8	295.1	298.8	306.3	304.4	319.4	336.3	351.4	374.0	381.4	242.4
77.5°	229.3	229.3	229.3	236.8	236.8	251.8	259.4	278.1	291.3	302.5	178.5
80°	171.0	169.1	171.0	172.9	172.9	180.4	193.5	206.7	218.0	218.0	122.2
82.5°	120.3	116.5	120.3	120.3	120.3	124.0	131.5	135.3	142.8	148.4	77.1
85°	75.2	75.2	75.2	77.1	75.2	78.9	80.8	84.5	84.5	80.8	47.0
87.5°	48.8	47.0	48.8	47.0	47.0	45.1	45.1	45.1	43.2	41.4	26.3
90°	10.6	10.6	10.6	10.6	10.6	14.2	19.0	21.3	18.3	12.3	7.8
92.5°	42.8	34.3	42.8	51.2	53.3	75.6	105.3	120.1	105.4	76.1	54.2
95°	148.9	123.2	148.9	174.6	181.0	237.7	313.3	351.1	296.5	187.4	105.5
97.5°	356.8	307.8	356.8	405.6	417.9	453.7	501.5	525.4	434.4	252.4	115.9
100°	514.1	455.8	514.1	572.3	586.8	584.2	580.8	579.0	478.0	276.1	124.6
102.5°	668.7	618.8	668.7	718.5	731.0	685.4	624.6	594.1	491.8	286.9	133.3
105°	865.9	839.1	865.9	892.7	899.4	797.1	660.6	592.4	493.2	295.0	146.2
107.5°	995.2	1001.6	995.2	988.6	987.1	844.2	653.9	558.7	471.3	296.5	165.3
110°	1044.4	1072.3	1044.4	1016.5	1009.5	849.8	637.1	530.7	451.9	294.2	176.0

TEST NUMBER: P933881

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1048.8	1091.7	1048.8	1005.9	995.2	831.8	614.1	505.2	434.9	294.3	188.9
115°	1021.0	1080.5	1021.0	961.5	946.6	789.2	579.5	474.6	415.3	297.0	208.3
117.5°	962.0	1028.0	962.0	896.1	879.5	737.6	548.3	453.6	403.2	302.5	227.1
120°	914.5	978.6	914.5	850.4	834.3	704.6	531.5	445.1	399.0	307.0	238.0
122.5°	868.2	931.5	868.2	804.9	789.1	672.3	516.5	438.6	396.9	313.5	250.9
125°	802.1	860.4	802.1	743.9	729.4	630.1	497.7	431.6	395.2	322.2	267.5
127.5°	742.8	791.9	742.8	693.7	681.4	596.2	482.5	425.7	394.1	330.9	283.5
130°	707.9	753.3	707.9	662.5	651.1	575.3	474.1	423.5	394.7	337.3	294.1
132.5°	676.1	716.8	676.1	635.5	625.3	557.4	466.8	421.5	395.2	342.4	302.8
135°	632.6	667.6	632.6	597.6	588.8	531.9	456.1	418.2	394.8	348.0	312.9
137.5°	597.7	626.4	597.7	569.0	561.8	513.7	449.6	417.6	397.2	356.4	325.8
140°	573.8	600.6	573.8	547.0	540.2	498.7	443.3	415.6	397.6	361.6	334.6
142.5°	554.0	577.0	554.0	530.9	525.1	488.6	439.9	415.6	399.0	365.8	341.0
145°	524.2	541.6	524.2	506.7	502.3	472.5	432.7	412.8	399.0	371.5	350.8
147.5°	501.4	515.8	501.4	486.9	483.3	459.8	428.5	412.8	401.8	379.7	363.1
150°	487.0	498.7	487.0	475.2	472.3	452.5	426.1	412.8	403.2	384.0	369.6
152.5°	474.7	483.5	474.7	465.9	463.6	446.7	424.1	412.8	404.1	386.8	373.8
155°	460.6	466.4	460.6	454.8	453.3	439.8	421.8	412.8	406.2	392.9	383.0
157.5°	449.4	453.6	449.4	445.2	444.2	433.7	419.8	412.8	408.3	399.2	392.4
160°	442.7	445.1	442.7	440.3	439.7	430.8	418.8	412.8	409.2	402.0	396.6
162.5°	438.3	440.6	438.3	436.1	435.5	428.0	417.9	412.8	410.2	405.0	401.1
165°	432.1	434.4	432.1	429.6	429.1	423.7	416.5	412.8	411.6	409.3	407.5
167.5°	427.5	428.5	427.5	426.6	426.3	422.7	418.0	415.6	414.6	412.6	411.1
170°	426.3	426.3	426.3	426.3	426.3	422.7	418.0	415.6	415.5	415.4	415.3
172.5°	422.9	422.1	422.9	423.8	424.0	421.2	417.5	415.6	415.6	415.6	415.6
175°	421.0	421.0	421.0	421.0	421.0	419.2	416.8	415.6	416.2	417.3	418.2
177.5°	419.2	418.2	419.2	420.1	420.4	419.0	417.1	416.2	416.7	417.5	418.2
180°	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2

TEST NUMBER: P933881

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2
2.5°	2014.5	2003.1	2003.1	1984.4	1976.9	1971.2	1961.9	1933.7	1926.2	1918.6	1929.9
5°	2031.4	2010.7	1995.7	1961.9	1933.7	1922.4	1886.7	1819.1	1773.9	1740.1	1721.4
7.5°	2035.1	2008.8	1980.6	1928.1	1860.3	1830.3	1721.4	1597.3	1563.4	1533.4	1514.6
10°	2031.4	2001.3	1961.9	1882.9	1723.2	1670.6	1561.6	1480.8	1460.1	1454.5	1460.1
12.5°	2018.2	1990.1	1935.5	1804.0	1580.4	1544.6	1480.8	1433.8	1430.0	1439.5	1490.2
15°	1995.7	1969.3	1905.5	1698.8	1501.5	1475.2	1430.0	1413.1	1433.8	1499.5	1651.8
17.5°	1973.2	1943.1	1864.2	1595.5	1441.3	1422.6	1390.5	1424.4	1540.9	1629.3	1680.0
20°	1943.1	1907.3	1817.2	1520.3	1398.1	1381.2	1366.2	1518.4	1606.7	1638.6	1666.8
22.5°	1907.3	1869.8	1753.3	1467.6	1353.0	1339.8	1349.3	1571.0	1606.7	1629.3	1653.6
25°	1860.3	1828.4	1678.1	1426.3	1317.3	1302.3	1338.0	1565.4	1586.0	1591.6	1640.5
27.5°	1817.2	1775.8	1599.2	1388.7	1274.1	1268.5	1347.4	1540.9	1556.0	1561.6	1614.2
30°	1764.5	1702.5	1510.8	1349.3	1229.0	1227.1	1349.3	1510.8	1507.1	1522.1	1574.7
32.5°	1710.1	1593.5	1411.3	1300.4	1185.7	1183.8	1336.1	1465.7	1462.0	1482.6	1522.1
35°	1659.3	1509.0	1275.9	1244.0	1131.3	1133.1	1304.1	1413.1	1415.0	1433.8	1458.3
37.5°	1606.7	1435.7	1127.5	1182.0	1078.7	1078.7	1260.9	1364.3	1360.6	1366.2	1400.0
40°	1544.6	1321.0	995.9	1101.2	1029.8	1024.1	1208.3	1311.6	1298.5	1296.7	1343.6
42.5°	1478.9	1195.1	898.2	994.1	973.4	965.8	1144.4	1247.7	1223.4	1229.0	1289.1
45°	1407.5	1161.3	823.0	839.9	915.1	909.5	1074.8	1174.5	1157.6	1172.6	1234.7
47.5°	1336.1	1093.7	798.7	697.1	853.1	851.2	997.8	1103.1	1093.7	1108.8	1174.5
50°	1238.4	1018.5	796.8	597.6	783.6	791.1	905.8	1033.6	1033.6	1046.7	1116.2
52.5°	1112.5	926.4	723.5	541.2	702.8	725.3	824.9	973.4	977.2	990.3	1052.3
55°	997.8	830.6	670.9	498.0	607.0	655.9	746.0	911.4	918.9	932.0	988.5
57.5°	892.6	691.5	659.6	447.2	518.7	565.6	676.5	851.2	855.0	866.3	920.8
60°	779.9	499.9	605.1	392.7	441.6	477.3	612.6	779.9	793.0	800.5	847.5
62.5°	652.0	362.7	548.7	355.2	404.0	411.5	560.0	712.2	729.1	734.8	763.0
65°	464.2	304.4	466.1	323.3	364.5	366.4	503.6	642.7	657.7	667.1	687.8
67.5°	313.8	248.1	355.2	293.2	334.5	336.3	449.2	561.9	582.5	590.1	603.2
70°	218.0	165.4	263.1	261.2	300.7	304.4	390.9	488.6	507.3	513.0	520.5
72.5°	159.7	133.4	218.0	234.9	265.0	268.7	330.7	405.9	424.7	430.3	434.1
75°	122.2	140.9	176.6	204.8	225.5	227.3	270.6	330.7	343.9	347.6	349.5
77.5°	97.7	131.5	129.6	165.4	184.2	180.4	212.4	255.5	266.8	266.8	266.8
80°	73.3	103.4	97.7	118.4	135.3	131.5	152.2	182.3	186.1	189.8	187.9
82.5°	54.5	65.8	65.8	75.2	90.2	86.5	101.4	118.4	118.4	118.4	122.2
85°	33.8	37.5	30.1	39.5	50.7	48.8	56.4	63.9	65.8	65.8	62.0
87.5°	20.6	16.9	9.4	15.0	22.5	22.5	26.3	28.2	26.3	26.3	26.3
90°	7.3	5.0	2.8	5.0	7.3	7.8	12.3	18.3	21.3	19.0	14.2
92.5°	49.4	30.3	11.2	30.3	49.4	54.2	76.1	105.4	120.1	105.3	75.6
95°	96.8	61.8	26.9	61.8	96.8	105.5	187.4	296.5	351.1	313.3	237.7
97.5°	108.3	77.4	46.6	77.4	108.3	115.9	252.4	434.4	525.4	501.5	453.7
100°	117.6	89.7	61.7	89.7	117.6	124.6	276.1	478.0	579.0	580.8	584.2
102.5°	126.7	100.7	74.6	100.7	126.7	133.3	286.9	491.8	594.1	624.6	685.4
105°	140.7	118.6	96.6	118.6	140.7	146.2	295.0	493.2	592.4	660.6	797.1
107.5°	160.2	139.5	119.0	139.5	160.2	165.3	296.5	471.3	558.7	653.9	844.2
110°	171.3	152.7	134.1	152.7	171.3	176.0	294.2	451.9	530.7	637.1	849.8

TEST NUMBER: P933881

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	184.5	166.7	149.1	166.7	184.5	188.9	294.3	434.9	505.2	614.1	831.8
115°	204.2	187.8	171.5	187.8	204.2	208.3	297.0	415.3	474.6	579.5	789.2
117.5°	223.3	208.5	193.6	208.5	223.3	227.1	302.5	403.2	453.6	548.3	737.6
120°	234.5	220.5	206.5	220.5	234.5	238.0	307.0	399.0	445.1	531.5	704.6
122.5°	247.3	233.3	219.2	233.3	247.3	250.9	313.5	396.9	438.6	516.5	672.3
125°	264.3	251.4	238.5	251.4	264.3	267.5	322.2	395.2	431.6	497.7	630.1
127.5°	280.2	267.2	254.2	267.2	280.2	283.5	330.9	394.1	425.7	482.5	596.2
130°	290.7	276.7	262.6	276.7	290.7	294.1	337.3	394.7	423.5	474.1	575.3
132.5°	299.3	285.3	271.4	285.3	299.3	302.8	342.4	395.2	421.5	466.8	557.4
135°	309.7	297.0	284.3	297.0	309.7	312.9	348.0	394.8	418.2	456.1	531.9
137.5°	322.6	310.1	297.5	310.1	322.6	325.8	356.4	397.2	417.6	449.6	513.7
140°	331.7	320.0	308.4	320.0	331.7	334.6	361.6	397.6	415.6	443.3	498.7
142.5°	338.3	327.6	316.8	327.6	338.3	341.0	365.8	399.0	415.6	439.9	488.6
145°	348.5	339.1	329.8	339.1	348.5	350.8	371.5	399.0	412.8	432.7	472.5
147.5°	360.9	351.7	342.7	351.7	360.9	363.1	379.7	401.8	412.8	428.5	459.8
150°	367.5	359.3	351.1	359.3	367.5	369.6	384.0	403.2	412.8	426.1	452.5
152.5°	372.2	366.0	359.8	366.0	372.2	373.8	386.8	404.1	412.8	424.1	446.7
155°	381.9	377.2	372.7	377.2	381.9	383.0	392.9	406.2	412.8	421.8	439.8
157.5°	391.3	386.7	382.2	386.7	391.3	392.4	399.2	408.3	412.8	419.8	433.7
160°	395.7	392.2	388.7	392.2	395.7	396.6	402.0	409.2	412.8	418.8	430.8
162.5°	400.4	397.8	395.2	397.8	400.4	401.1	405.0	410.2	412.8	417.9	428.0
165°	406.9	404.5	402.2	404.5	406.9	407.5	409.3	411.6	412.8	416.5	423.7
167.5°	410.9	409.7	408.6	409.7	410.9	411.1	412.6	414.6	415.6	418.0	422.7
170°	415.1	413.9	412.8	413.9	415.1	415.3	415.4	415.5	415.6	418.0	422.7
172.5°	415.5	415.3	415.1	415.3	415.5	415.6	415.6	415.6	415.6	417.5	421.2
175°	418.2	418.2	418.2	418.2	418.2	418.2	417.3	416.2	415.6	416.8	419.2
177.5°	418.2	418.2	418.2	418.2	418.2	418.2	417.5	416.7	416.2	417.1	419.0
180°	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2

TEST NUMBER: P933881

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2	1986.2
2.5°	1916.8	1911.2	1918.6	1898.0	1918.6	1911.2	1916.8	1929.9	1918.6	1926.2	1933.7
5°	1681.9	1672.4	1642.4	1618.0	1642.4	1672.4	1681.9	1721.4	1740.1	1773.9	1819.1
7.5°	1503.4	1495.8	1488.3	1473.3	1488.3	1495.8	1503.4	1514.6	1533.4	1563.4	1597.3
10°	1463.9	1465.7	1477.0	1475.2	1477.0	1465.7	1463.9	1460.1	1454.5	1460.1	1480.8
12.5°	1565.4	1582.3	1644.3	1640.5	1644.3	1582.3	1565.4	1490.2	1439.5	1430.0	1433.8
15°	1681.9	1687.5	1700.6	1702.5	1700.6	1687.5	1681.9	1651.8	1499.5	1433.8	1413.1
17.5°	1693.2	1695.0	1704.4	1704.4	1704.4	1695.0	1693.2	1680.0	1629.3	1540.9	1424.4
20°	1683.7	1687.5	1706.3	1710.1	1706.3	1687.5	1683.7	1666.8	1638.6	1606.7	1518.4
22.5°	1680.0	1687.5	1702.5	1700.6	1702.5	1687.5	1680.0	1653.6	1629.3	1606.7	1571.0
25°	1661.2	1661.2	1663.1	1664.9	1663.1	1661.2	1661.2	1640.5	1591.6	1586.0	1565.4
27.5°	1621.7	1625.4	1636.7	1634.9	1636.7	1625.4	1621.7	1614.2	1561.6	1556.0	1540.9
30°	1586.0	1582.3	1572.9	1565.4	1572.9	1582.3	1586.0	1574.7	1522.1	1507.1	1510.8
32.5°	1525.9	1516.4	1507.1	1501.5	1507.1	1516.4	1525.9	1522.1	1482.6	1462.0	1465.7
35°	1454.5	1456.4	1454.5	1448.8	1454.5	1456.4	1454.5	1458.3	1433.8	1415.0	1413.1
37.5°	1403.7	1407.5	1405.6	1398.1	1405.6	1407.5	1403.7	1400.0	1366.2	1360.6	1364.3
40°	1351.1	1353.0	1351.1	1345.5	1351.1	1353.0	1351.1	1343.6	1296.7	1298.5	1311.6
42.5°	1300.4	1298.5	1292.8	1289.1	1292.8	1298.5	1300.4	1289.1	1229.0	1223.4	1247.7
45°	1242.1	1244.0	1232.7	1227.1	1232.7	1244.0	1242.1	1234.7	1172.6	1157.6	1174.5
47.5°	1183.8	1183.8	1174.5	1168.8	1174.5	1183.8	1183.8	1174.5	1108.8	1093.7	1103.1
50°	1121.8	1120.0	1106.8	1104.9	1106.8	1120.0	1121.8	1116.2	1046.7	1033.6	1033.6
52.5°	1050.5	1050.5	1052.3	1056.1	1052.3	1050.5	1050.5	1052.3	990.3	977.2	973.4
55°	988.5	990.3	1003.5	1007.2	1003.5	990.3	988.5	988.5	932.0	918.9	911.4
57.5°	924.6	924.6	933.9	933.9	933.9	924.6	924.6	920.8	866.3	855.0	851.2
60°	851.2	855.0	862.5	860.7	862.5	855.0	851.2	847.5	800.5	793.0	779.9
62.5°	774.2	778.0	779.9	776.1	779.9	778.0	774.2	763.0	734.8	729.1	712.2
65°	693.4	697.1	699.0	695.3	699.0	697.1	693.4	687.8	667.1	657.7	642.7
67.5°	610.7	608.9	607.0	614.5	607.0	608.9	610.7	603.2	590.1	582.5	561.9
70°	526.1	526.1	524.3	528.1	524.3	526.1	526.1	520.5	513.0	507.3	488.6
72.5°	436.0	434.1	441.6	436.0	441.6	434.1	436.0	434.1	430.3	424.7	405.9
75°	347.6	351.4	347.6	353.2	347.6	351.4	347.6	349.5	347.6	343.9	330.7
77.5°	265.0	268.7	265.0	265.0	265.0	268.7	265.0	266.8	266.8	266.8	255.5
80°	187.9	186.1	186.1	184.2	186.1	186.1	187.9	187.9	189.8	186.1	182.3
82.5°	120.3	118.4	118.4	122.2	118.4	118.4	120.3	122.2	118.4	118.4	118.4
85°	65.8	67.6	63.9	63.9	63.9	67.6	65.8	62.0	65.8	65.8	63.9
87.5°	24.5	22.5	22.5	22.5	22.5	22.5	24.5	26.3	26.3	26.3	28.2
90°	10.6	10.6	10.6	10.6	10.6	10.6	10.6	14.2	19.0	21.3	18.3
92.5°	53.3	51.2	42.8	34.3	42.8	51.2	53.3	75.6	105.3	120.1	105.4
95°	181.0	174.6	148.9	123.2	148.9	174.6	181.0	237.7	313.3	351.1	296.5
97.5°	417.9	405.6	356.8	307.8	356.8	405.6	417.9	453.7	501.5	525.4	434.4
100°	586.8	572.3	514.1	455.8	514.1	572.3	586.8	584.2	580.8	579.0	478.0
102.5°	731.0	718.5	668.7	618.8	668.7	718.5	731.0	685.4	624.6	594.1	491.8
105°	899.4	892.7	865.9	839.1	865.9	892.7	899.4	797.1	660.6	592.4	493.2
107.5°	987.1	988.6	995.2	1001.6	995.2	988.6	987.1	844.2	653.9	558.7	471.3
110°	1009.5	1016.5	1044.4	1072.3	1044.4	1016.5	1009.5	849.8	637.1	530.7	451.9

TEST NUMBER: P933881

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	995.2	1005.9	1048.8	1091.7	1048.8	1005.9	995.2	831.8	614.1	505.2	434.9
115°	946.6	961.5	1021.0	1080.5	1021.0	961.5	946.6	789.2	579.5	474.6	415.3
117.5°	879.5	896.1	962.0	1028.0	962.0	896.1	879.5	737.6	548.3	453.6	403.2
120°	834.3	850.4	914.5	978.6	914.5	850.4	834.3	704.6	531.5	445.1	399.0
122.5°	789.1	804.9	868.2	931.5	868.2	804.9	789.1	672.3	516.5	438.6	396.9
125°	729.4	743.9	802.1	860.4	802.1	743.9	729.4	630.1	497.7	431.6	395.2
127.5°	681.4	693.7	742.8	791.9	742.8	693.7	681.4	596.2	482.5	425.7	394.1
130°	651.1	662.5	707.9	753.3	707.9	662.5	651.1	575.3	474.1	423.5	394.7
132.5°	625.3	635.5	676.1	716.8	676.1	635.5	625.3	557.4	466.8	421.5	395.2
135°	588.8	597.6	632.6	667.6	632.6	597.6	588.8	531.9	456.1	418.2	394.8
137.5°	561.8	569.0	597.7	626.4	597.7	569.0	561.8	513.7	449.6	417.6	397.2
140°	540.2	547.0	573.8	600.6	573.8	547.0	540.2	498.7	443.3	415.6	397.6
142.5°	525.1	530.9	554.0	577.0	554.0	530.9	525.1	488.6	439.9	415.6	399.0
145°	502.3	506.7	524.2	541.6	524.2	506.7	502.3	472.5	432.7	412.8	399.0
147.5°	483.3	486.9	501.4	515.8	501.4	486.9	483.3	459.8	428.5	412.8	401.8
150°	472.3	475.2	487.0	498.7	487.0	475.2	472.3	452.5	426.1	412.8	403.2
152.5°	463.6	465.9	474.7	483.5	474.7	465.9	463.6	446.7	424.1	412.8	404.1
155°	453.3	454.8	460.6	466.4	460.6	454.8	453.3	439.8	421.8	412.8	406.2
157.5°	444.2	445.2	449.4	453.6	449.4	445.2	444.2	433.7	419.8	412.8	408.3
160°	439.7	440.3	442.7	445.1	442.7	440.3	439.7	430.8	418.8	412.8	409.2
162.5°	435.5	436.1	438.3	440.6	438.3	436.1	435.5	428.0	417.9	412.8	410.2
165°	429.1	429.6	432.1	434.4	432.1	429.6	429.1	423.7	416.5	412.8	411.6
167.5°	426.3	426.6	427.5	428.5	427.5	426.6	426.3	422.7	418.0	415.6	414.6
170°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	422.7	418.0	415.6	415.5
172.5°	424.0	423.8	422.9	422.1	422.9	423.8	424.0	421.2	417.5	415.6	415.6
175°	421.0	421.0	421.0	421.0	421.0	421.0	421.0	419.2	416.8	415.6	416.2
177.5°	420.4	420.1	419.2	418.2	419.2	420.1	420.4	419.0	417.1	416.2	416.7
180°	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2

TEST NUMBER: P933881

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1986.2	1986.2	1986.2	1986.2	1986.2
2.5°	1961.9	1971.2	1976.9	1984.4	2003.1
5°	1886.7	1922.4	1933.7	1961.9	1995.7
7.5°	1721.4	1830.3	1860.3	1928.1	1980.6
10°	1561.6	1670.6	1723.2	1882.9	1961.9
12.5°	1480.8	1544.6	1580.4	1804.0	1935.5
15°	1430.0	1475.2	1501.5	1698.8	1905.5
17.5°	1390.5	1422.6	1441.3	1595.5	1864.2
20°	1366.2	1381.2	1398.1	1520.3	1817.2
22.5°	1349.3	1339.8	1353.0	1467.6	1753.3
25°	1338.0	1302.3	1317.3	1426.3	1678.1
27.5°	1347.4	1268.5	1274.1	1388.7	1599.2
30°	1349.3	1227.1	1229.0	1349.3	1510.8
32.5°	1336.1	1183.8	1185.7	1300.4	1411.3
35°	1304.1	1133.1	1131.3	1244.0	1275.9
37.5°	1260.9	1078.7	1078.7	1182.0	1127.5
40°	1208.3	1024.1	1029.8	1101.2	995.9
42.5°	1144.4	965.8	973.4	994.1	898.2
45°	1074.8	909.5	915.1	839.9	823.0
47.5°	997.8	851.2	853.1	697.1	798.7
50°	905.8	791.1	783.6	597.6	796.8
52.5°	824.9	725.3	702.8	541.2	723.5
55°	746.0	655.9	607.0	498.0	670.9
57.5°	676.5	565.6	518.7	447.2	659.6
60°	612.6	477.3	441.6	392.7	605.1
62.5°	560.0	411.5	404.0	355.2	548.7
65°	503.6	366.4	364.5	323.3	466.1
67.5°	449.2	336.3	334.5	293.2	355.2
70°	390.9	304.4	300.7	261.2	263.1
72.5°	330.7	268.7	265.0	234.9	218.0
75°	270.6	227.3	225.5	204.8	176.6
77.5°	212.4	180.4	184.2	165.4	129.6
80°	152.2	131.5	135.3	118.4	97.7
82.5°	101.4	86.5	90.2	75.2	65.8
85°	56.4	48.8	50.7	39.5	30.1
87.5°	26.3	22.5	22.5	15.0	9.4
90°	12.3	7.8	7.3	5.0	2.8
92.5°	76.1	54.2	49.4	30.3	11.2
95°	187.4	105.5	96.8	61.8	26.9
97.5°	252.4	115.9	108.3	77.4	46.6
100°	276.1	124.6	117.6	89.7	61.7
102.5°	286.9	133.3	126.7	100.7	74.6
105°	295.0	146.2	140.7	118.6	96.6
107.5°	296.5	165.3	160.2	139.5	119.0
110°	294.2	176.0	171.3	152.7	134.1

TEST NUMBER: P933881

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	294.3	188.9	184.5	166.7	149.1
115°	297.0	208.3	204.2	187.8	171.5
117.5°	302.5	227.1	223.3	208.5	193.6
120°	307.0	238.0	234.5	220.5	206.5
122.5°	313.5	250.9	247.3	233.3	219.2
125°	322.2	267.5	264.3	251.4	238.5
127.5°	330.9	283.5	280.2	267.2	254.2
130°	337.3	294.1	290.7	276.7	262.6
132.5°	342.4	302.8	299.3	285.3	271.4
135°	348.0	312.9	309.7	297.0	284.3
137.5°	356.4	325.8	322.6	310.1	297.5
140°	361.6	334.6	331.7	320.0	308.4
142.5°	365.8	341.0	338.3	327.6	316.8
145°	371.5	350.8	348.5	339.1	329.8
147.5°	379.7	363.1	360.9	351.7	342.7
150°	384.0	369.6	367.5	359.3	351.1
152.5°	386.8	373.8	372.2	366.0	359.8
155°	392.9	383.0	381.9	377.2	372.7
157.5°	399.2	392.4	391.3	386.7	382.2
160°	402.0	396.6	395.7	392.2	388.7
162.5°	405.0	401.1	400.4	397.8	395.2
165°	409.3	407.5	406.9	404.5	402.2
167.5°	412.6	411.1	410.9	409.7	408.6
170°	415.4	415.3	415.1	413.9	412.8
172.5°	415.6	415.6	415.5	415.3	415.1
175°	417.3	418.2	418.2	418.2	418.2
177.5°	417.5	418.2	418.2	418.2	418.2
180°	418.2	418.2	418.2	418.2	418.2

TEST NUMBER: P933881

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-12-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.44	13.46	13.25	14.30	15.33	15.29	16.31	16.10	17.15	18.18
	3H	12.93	13.85	13.75	14.69	15.75	16.66	17.57	17.48	18.42	19.47
	4H	13.13	13.99	13.97	14.84	15.91	17.11	17.98	17.95	18.83	19.90
	6H	13.26	14.05	14.11	14.91	15.99	17.41	18.21	18.26	19.07	20.15
	8H	13.26	14.02	14.12	14.90	15.98	17.49	18.25	18.36	19.13	20.21
	12H	13.24	13.96	14.11	14.83	15.94	17.54	18.26	18.41	19.13	20.24
4H	2H	13.50	14.36	14.34	15.21	16.28	15.72	16.58	16.57	17.44	18.51
	3H	14.54	15.26	15.40	16.14	17.23	17.25	17.97	18.10	18.85	19.94
	4H	14.82	15.48	15.69	16.36	17.47	17.79	18.44	18.66	19.32	20.44
	6H	14.96	15.52	15.84	16.43	17.54	18.17	18.73	19.05	19.64	20.75
	8H	14.97	15.50	15.85	16.40	17.52	18.28	18.81	19.17	19.71	20.84
	12H	14.94	15.42	15.85	16.34	17.47	18.35	18.82	19.26	19.74	20.88
8H	4H	15.29	15.82	16.18	16.72	17.85	17.92	18.45	18.81	19.35	20.48
	6H	15.56	16.00	16.48	16.94	18.07	18.37	18.81	19.29	19.75	20.88
	8H	15.60	15.99	16.53	16.93	18.07	18.53	18.92	19.45	19.85	21.00
	12H	15.60	15.94	16.53	16.86	18.06	18.64	18.98	19.57	19.91	21.10
12H	4H	15.31	15.78	16.22	16.70	17.84	17.89	18.37	18.80	19.29	20.42
	6H	15.62	16.01	16.55	16.95	18.09	18.37	18.76	19.30	19.69	20.84
	8H	15.70	16.04	16.63	16.97	18.16	18.54	18.88	19.47	19.81	21.01

END OF REPORT