

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936287

Luminaire Tested: SQ4-FB-025U-050D-B2750-1D-UNV-W2A-W-6-2700K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936287
REPORT IS A COMBINATION OF REPORTS P933445 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-050D-B2750-1D-UNV-W2A-W-6-2700K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3856.5 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936287

CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-W2A-W-6-2700K

Luminous Intensity Polar Plot



TEST NUMBER: P936287

CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-W2A-W-6-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	68	68	68
1	100	95	91	87	93	89	86	82	78	75	73	68	66	64	59	57	56	56	56	51
2	90	82	76	70	84	77	71	66	68	63	59	59	55	52	51	48	46	46	46	42
3	82	72	64	57	76	67	60	55	59	53	49	51	47	43	44	41	38	38	38	34
4	75	63	54	48	69	59	52	46	52	46	41	45	40	37	39	35	32	32	32	29
5	68	56	47	41	63	52	45	39	46	40	35	40	35	31	35	31	28	28	28	24
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	24	24	24	21
7	58	45	36	30	54	42	34	29	37	31	26	33	27	23	28	24	21	21	21	18
8	53	40	32	26	50	38	31	25	34	27	23	30	24	21	26	22	18	18	18	16
9	50	37	29	23	46	35	27	22	31	25	20	27	22	18	24	19	16	16	16	14
10	46	34	26	21	43	32	25	20	28	22	18	25	20	16	22	18	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1927	1927	1927
5°	1883	2227	2591
10°	1707	3246	4295
15°	1450	4239	5186
20°	1180	4912	5286
25°	984	5138	5179
30°	829	5170	5168
35°	733	5082	5302
40°	639	4970	5440
45°	577	4886	5461
50°	529	4811	5371
55°	507	4702	5133
60°	518	4494	4757
65°	537	4177	4240
70°	572	3640	3583
75°	632	2965	2796
80°	684	2053	1884
85°	602	1090	964

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5461 cd/sqm

TEST NUMBER: P936287

CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-W2A-W-6-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.3	1.0
10°-20°	178.6	4.6
20°-30°	312.4	8.1
30°-40°	402.2	10.4
40°-50°	449.2	11.6
50°-60°	430.3	11.2
60°-70°	341.0	8.8
70°-80°	200.5	5.2
80°-90°	56.6	1.5
90°-100°	108.7	2.8
100°-110°	285.7	7.4
110°-120°	296.3	7.7
120°-130°	237.7	6.2
130°-140°	186.5	4.8
140°-150°	143.1	3.7
150°-160°	103.1	2.7
160°-170°	63.1	1.6
170°-180°	21.3	0.6
0°-30°	531.4	13.8
0°-40°	933.6	24.2
0°-60°	1813.1	47.0
0°-90°	2411.2	62.5
90°-120°	690.7	17.9
90°-150°	1257.9	32.6
90°-180°	1445.0	37.5
0°-180°	3856.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	312	312	312	312	312	
5°	304	326	367	415	430	28
15°	227	420	707	858	885	63
25°	145	476	842	880	881	67
35°	98	455	793	838	872	61
45°	67	363	701	804	840	52
55°	48	230	595	691	710	44
65°	38	122	442	497	504	38
75°	28	75	242	266	268	29
85°	10	23	60	66	67	11
90°	2	4	11	6	6	2
95°	14	56	187	96	66	16
105°	52	78	316	480	447	55
115°	91	111	253	505	576	90
125°	127	143	230	389	459	113
135°	152	167	223	314	356	117
145°	176	187	220	268	289	110
155°	199	204	220	242	249	91
165°	214	217	220	229	232	61
175°	223	223	222	224	224	21
180°	223	223	223	223	223	

TEST NUMBER: P936287

CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	311.5	311.5	311.5	311.5	311.5	311.5	311.5	311.5	311.5	311.5	311.5
2.5°	311.5	311.5	313.5	314.5	316.6	317.6	319.6	321.6	327.6	328.6	330.6
5°	303.6	307.6	320.6	325.6	339.6	358.7	366.6	379.7	406.8	414.7	419.8
7.5°	291.5	300.6	332.6	340.6	375.7	425.8	446.8	474.9	517.9	539.0	556.1
10°	272.5	291.5	348.6	367.7	424.8	500.9	540.0	579.1	644.2	673.2	684.3
12.5°	251.5	282.6	365.6	391.7	473.9	585.1	632.2	675.3	749.4	788.4	794.4
15°	227.4	269.5	381.7	419.8	526.0	655.2	707.3	760.4	829.6	857.6	864.6
17.5°	206.4	259.5	396.7	436.8	566.0	718.3	771.4	815.5	871.6	890.6	895.6
20°	180.4	243.4	406.8	458.9	608.2	764.4	815.5	849.6	887.6	899.7	901.7
22.5°	161.3	226.4	412.7	466.8	636.1	792.4	835.5	862.5	888.6	892.6	893.6
25°	145.3	207.4	411.7	475.9	660.2	809.4	842.5	862.5	877.6	879.6	879.6
27.5°	130.3	186.4	407.8	477.9	678.3	813.5	839.5	853.6	860.5	864.6	864.6
30°	117.2	166.3	397.7	473.9	686.2	809.4	830.6	837.5	844.5	850.6	853.6
32.5°	107.2	147.3	382.7	465.8	687.2	799.5	814.5	818.5	828.5	842.5	847.6
35°	98.2	128.3	365.6	454.9	681.3	783.5	793.4	797.5	817.5	838.5	845.5
37.5°	89.1	114.2	343.6	435.8	672.2	764.4	771.4	778.5	809.4	834.5	842.5
40°	80.2	102.2	317.6	414.7	658.3	741.3	747.4	758.4	799.5	828.5	836.5
42.5°	73.1	92.1	289.5	392.7	640.1	715.3	724.3	740.3	787.4	818.5	827.5
45°	67.1	82.2	259.5	362.6	617.1	688.2	701.3	723.3	773.4	803.5	811.4
47.5°	61.2	75.1	228.4	331.6	592.1	661.2	678.3	703.3	754.4	783.5	790.4
50°	56.1	68.1	197.4	298.5	565.0	632.2	652.2	678.3	730.4	757.4	766.4
52.5°	52.1	62.2	168.3	265.5	534.0	602.1	625.2	652.2	701.3	727.4	733.4
55°	48.1	57.1	143.2	230.4	501.9	570.0	595.1	621.1	669.2	691.2	695.3
57.5°	46.1	53.1	122.2	197.4	467.8	534.0	562.0	586.0	631.2	648.2	652.2
60°	43.1	50.1	106.2	169.3	430.8	499.9	524.0	548.0	586.0	600.1	603.1
62.5°	40.0	48.1	94.2	142.2	392.7	459.9	483.9	506.0	537.9	548.0	552.0
65°	38.0	46.1	85.2	122.2	353.7	417.7	441.8	460.8	486.8	496.9	498.9
67.5°	36.1	44.1	78.2	105.2	314.5	375.7	393.7	411.7	431.8	441.8	442.8
70°	33.1	42.0	72.1	93.1	274.5	327.6	342.6	361.6	377.7	382.7	385.8
72.5°	31.1	39.0	68.1	84.2	233.5	281.5	295.5	306.6	320.6	325.6	325.6
75°	28.1	35.1	64.1	75.1	191.3	230.4	242.4	253.5	264.4	266.5	263.4
77.5°	25.0	31.1	55.1	63.1	149.3	182.4	192.3	198.4	207.4	209.4	210.4
80°	21.0	27.1	43.1	49.1	108.2	134.3	141.2	146.3	154.3	154.3	156.3
82.5°	16.0	21.0	31.1	35.1	73.1	92.1	98.2	101.2	106.2	106.2	106.2
85°	10.1	13.0	20.0	23.0	44.1	56.1	60.2	61.2	65.1	66.1	66.1
87.5°	5.0	7.0	13.0	14.0	23.0	29.1	29.1	31.1	31.1	30.1	29.1
90°	1.5	2.7	3.9	4.2	6.6	9.8	11.4	10.1	7.6	5.7	5.7
92.5°	6.0	16.1	26.3	28.9	40.6	56.3	64.0	56.1	40.2	28.4	27.3
95°	14.3	33.0	51.6	56.3	99.9	158.1	187.1	167.0	126.7	96.5	93.1
97.5°	24.8	41.2	57.7	61.8	134.6	231.6	280.1	267.3	241.9	222.8	216.3
100°	33.0	47.8	62.7	66.4	147.2	254.9	308.7	309.6	311.4	312.8	305.1
102.5°	39.8	53.8	67.6	71.1	153.0	262.1	316.7	333.0	365.4	389.8	383.2
105°	51.5	63.2	75.0	78.0	157.3	262.9	315.8	352.2	425.0	479.6	476.0
107.5°	63.4	74.4	85.4	88.1	158.1	251.3	297.9	348.7	450.2	526.3	527.2
110°	71.5	81.5	91.3	93.8	156.9	240.9	283.0	339.7	453.2	538.2	541.9

TEST NUMBER: P936287

CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	79.5	88.9	98.3	100.7	156.9	231.9	269.3	327.4	443.5	530.6	536.2
115°	91.4	100.2	108.9	111.1	158.4	221.4	253.0	309.0	420.8	504.7	512.6
117.5°	103.3	111.2	119.0	121.0	161.3	214.9	241.8	292.3	393.2	468.9	477.7
120°	110.2	117.6	125.0	126.9	163.7	212.8	237.3	283.5	375.7	444.9	453.5
122.5°	116.8	124.4	131.9	133.8	167.1	211.6	233.9	275.4	358.5	420.8	429.3
125°	127.2	134.1	140.9	142.6	171.8	210.8	230.2	265.4	336.1	388.9	396.7
127.5°	135.6	142.4	149.4	151.1	176.4	210.2	227.0	257.3	317.9	363.3	369.9
130°	140.0	147.5	154.9	156.8	179.8	210.5	225.8	252.8	306.7	347.1	353.2
132.5°	144.7	152.2	159.6	161.5	182.6	210.8	224.8	248.9	297.2	333.4	338.7
135°	151.6	158.4	165.1	166.8	185.6	210.6	223.0	243.2	283.7	313.9	318.6
137.5°	158.7	165.3	172.0	173.7	190.0	211.8	222.7	239.8	274.0	299.6	303.4
140°	164.4	170.6	176.8	178.4	192.8	212.0	221.6	236.4	265.9	288.0	291.6
142.5°	168.9	174.6	180.4	181.8	195.0	212.7	221.6	234.6	260.6	280.0	283.1
145°	175.8	180.8	185.8	187.0	198.1	212.7	220.1	230.7	251.9	267.8	270.1
147.5°	182.7	187.5	192.4	193.6	202.5	214.2	220.1	228.5	245.1	257.7	259.6
150°	187.1	191.5	196.0	197.1	204.8	215.0	220.1	227.2	241.2	251.8	253.4
152.5°	191.8	195.1	198.5	199.3	206.3	215.5	220.1	226.1	238.1	247.2	248.4
155°	198.7	201.2	203.7	204.3	209.6	216.6	220.1	224.9	234.5	241.6	242.4
157.5°	203.8	206.2	208.6	209.2	212.8	217.7	220.1	223.8	231.3	236.8	237.4
160°	207.3	209.2	211.0	211.5	214.3	218.2	220.1	223.3	229.7	234.5	234.8
162.5°	210.7	212.0	213.4	213.8	215.9	218.7	220.1	222.8	228.2	232.3	232.6
165°	214.4	215.6	216.9	217.2	218.2	219.5	220.1	222.0	225.9	228.8	229.1
167.5°	217.8	218.4	219.0	219.2	220.0	221.1	221.6	222.9	225.4	227.3	227.4
170°	220.1	220.7	221.3	221.4	221.5	221.6	221.6	222.9	225.4	227.3	227.3
172.5°	221.3	221.4	221.6	221.6	221.6	221.6	221.6	222.6	224.6	226.1	226.0
175°	223.0	223.0	223.0	223.0	222.5	221.9	221.6	222.2	223.5	224.5	224.5
177.5°	223.0	223.0	223.0	223.0	222.6	222.1	221.9	222.4	223.4	224.2	224.1
180°	223.0	223.0	223.0	223.0	223.0	223.0	223.0	223.0	223.0	223.0	223.0

TEST NUMBER: P936287

CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	311.5	311.5
2.5°	332.6	330.6
5°	427.8	429.8
7.5°	576.1	575.1
10°	716.3	725.3
12.5°	818.5	820.5
15°	880.7	884.6
17.5°	904.7	905.7
20°	905.7	903.7
22.5°	894.6	892.6
25°	881.7	880.7
27.5°	869.6	870.6
30°	864.6	867.6
32.5°	864.6	869.6
35°	866.6	871.6
37.5°	865.6	871.6
40°	861.5	868.6
42.5°	850.6	855.6
45°	833.6	839.5
47.5°	811.4	815.5
50°	783.5	787.4
52.5°	748.4	749.4
55°	706.3	710.3
57.5°	661.2	662.2
60°	611.1	614.1
62.5°	558.1	558.1
65°	501.9	503.9
67.5°	443.8	448.8
70°	384.8	385.8
72.5°	326.6	326.6
75°	266.5	267.5
77.5°	209.4	209.4
80°	155.3	156.3
82.5°	107.2	109.2
85°	67.1	67.1
87.5°	31.1	28.1
90°	5.7	5.7
92.5°	22.7	18.2
95°	79.4	65.7
97.5°	190.2	164.1
100°	274.1	243.0
102.5°	356.6	330.0
105°	461.7	447.4
107.5°	530.6	534.1
110°	556.9	571.8

TEST NUMBER: P936287

CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-W2A-W-6-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	559.2	582.1
115°	544.3	576.1
117.5°	512.9	548.1
120°	487.6	521.8
122.5°	462.9	496.6
125°	427.7	458.8
127.5°	396.1	422.3
130°	377.4	401.6
132.5°	360.5	382.2
135°	337.2	356.0
137.5°	318.7	334.0
140°	305.9	320.2
142.5°	295.3	307.7
145°	279.5	288.8
147.5°	267.3	275.0
150°	259.7	265.9
152.5°	253.1	257.9
155°	245.5	248.7
157.5°	239.6	241.8
160°	236.1	237.3
162.5°	233.8	235.0
165°	230.4	231.7
167.5°	228.0	228.5
170°	227.3	227.3
172.5°	225.5	225.1
175°	224.5	224.5
177.5°	223.5	223.0
180°	223.0	223.0

TEST NUMBER: P936287

CATALOG NUMBER: SQ4-FB-025U-050D-B2750-1D-UNV-W2A-W-6-2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.34	5.38	5.18	6.24	7.32	17.51	18.55	18.34	19.41	20.49
	3H	5.06	6.00	5.91	6.87	7.97	19.36	20.29	20.20	21.16	22.27
	4H	5.37	6.25	6.23	7.13	8.25	20.01	20.89	20.87	21.77	22.88
	6H	5.63	6.45	6.50	7.33	8.46	20.44	21.26	21.32	22.15	23.27
	8H	5.70	6.48	6.59	7.39	8.51	20.57	21.35	21.45	22.25	23.38
	12H	5.73	6.47	6.62	7.37	8.52	20.64	21.38	21.53	22.28	23.43
4H	2H	11.57	12.46	12.44	13.34	14.45	17.81	18.69	18.67	19.57	20.68
	3H	13.16	13.90	14.04	14.81	15.94	19.86	20.61	20.74	21.51	22.64
	4H	13.26	13.94	14.15	14.84	16.00	20.63	21.31	21.53	22.22	23.37
	6H	13.28	13.87	14.19	14.80	15.96	21.18	21.77	22.09	22.70	23.85
	8H	13.26	13.81	14.17	14.74	15.91	21.34	21.89	22.25	22.82	23.99
	12H	13.23	13.73	14.16	14.67	15.85	21.44	21.94	22.37	22.88	24.06
8H	4H	14.72	15.27	15.63	16.19	17.36	20.71	21.26	21.62	22.18	23.36
	6H	14.97	15.42	15.90	16.39	17.56	21.34	21.80	22.28	22.77	23.94
	8H	14.99	15.39	15.93	16.35	17.54	21.56	21.97	22.51	22.92	24.11
	12H	14.97	15.32	15.92	16.27	17.51	21.71	22.07	22.66	23.02	24.26
12H	4H	14.87	15.36	15.80	16.31	17.48	20.67	21.17	21.60	22.11	23.29
	6H	15.23	15.63	16.17	16.59	17.78	21.33	21.73	22.27	22.69	23.88
	8H	15.31	15.66	16.26	16.61	17.85	21.57	21.92	22.52	22.87	24.11